


Product: [9261](#)

Electronic, 12 C #20 Str TC, PVC Ins, OA TC Brd, PVC Jkt, CMG

[Request Sample](#)
Product Description

Electronic, 12 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, Overall Tinned Copper Braid(85%) Shield, PVC Outer Jacket, CMG

Technical Specifications
Product Overview

| | |
|------------------------|---|
| Suitable Applications: | low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring |
|------------------------|---|

Construction Details
Conductor

| Element | No. of Elements | Size | Stranding | Material |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 12 | 20 AWG | 7x28 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--------------------------|--------------------|--------------------------|--|
| Conductor(s) | PVC - Polyvinyl Chloride | 0.017 in (0.43 mm) | 0.070 in (1.8 mm) | Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe, Orange/Black Stripe, Blue/Black Stripe, Black/White Stripe |

Outer Shield

| Shield Type | Material | Coverage |
|-------------|--------------------|----------|
| Braid | Tinned Copper (TC) | 85% |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|--------------------------|-------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.040 in (1.0 mm) | 0.396 in (10.1 mm) |

Overall Cable Diameter (Nominal): 0.396 in (10.1 mm)

Electrical Characteristics
Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Capacitance Cond-to-Other (Conds + Shield) | Nom. Inductance | Max. Current |
|--------------|--------------------|-------------------------------|---|------------------------------------|--------------------------------|
| Conductor(s) | 9.5 Ohm/1000ft | 26 pF/ft (85 pF/m) | 57 pF/ft (190 pF/m) | 0.188 μ H/ft (0.617 μ H/m) | 3.2 Amps per Conductor at 25°C |

Nom Outer Shield DCR@Cond DCR1-cnv: 2.4 Ohm/1000ft (7.9 Ohm/km)

Voltage

| UL Voltage Rating |
|----------------------------------|
| 300 V (CMG), 300 V (UL AWM 2464) |

Mechanical Characteristics
Temperature

| UL Temperature | Operating |
|----------------|----------------|
| 80°C | -20°C to +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
|-----------------|-------------------|

4.0 in (100 mm) 4.0 in (100 mm)

Max. Pull Tension: 231 lbs (105 kg)

Bulk Cable Weight: 105 lbs/1000ft

Standards and Compliance

| | |
|----------------------------------|---|
| Environmental Suitability: | Indoor (Not Riser or Plenum), Indoor |
| Sustainability: | CA Prop 65 |
| Flammability / Reaction to Fire: | UL 1685 FT4 Loading, FT4, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca |
| NEC / UL Compliance: | Article 800, CMG |
| AWM Compliance: | AWM 2464 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |

History

Update and Revision: Revision Number: 0.521 Revision Date: 09-07-2025

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC | Footnote |
|--------------|--------|------------|----------|--------------|----------|
| 9261 060100 | Chrome | Reel | 100 ft | 612825225959 | |
| 9261 0601000 | Chrome | Reel | 1,000 ft | 612825225966 | C |

Footnote: C - CRATE REEL PUT-UP.

© 2025 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.