

4-BIT MAGNITUDE COMPARATOR

DESCRIPTION

The M74LS85P is a semiconductor integrated circuit containing a 4-bit digital comparator.

FEATURES

- Easy expansion of number of bits
- Binary or BCD comparison
- Wide operating temperature range ($T_a = -20 \sim +75^\circ\text{C}$)


APPLICATION

General purpose, for use in industrial and consumer equipment.

FUNCTIONAL DESCRIPTION


By applying two sets of 4-bit binary numbers A and B to be compared to comparison inputs $A_0 \sim A_3$ and $B_0 \sim B_3$ and by setting cascade input $I_{A=B}$ high, high appears in outputs $O_{A>B}$, $O_{A<B}$ and $O_{A=B}$ in accordance with the magnitude. This is used for connecting cascade inputs $I_{A>B}$, $I_{A<B}$ and $I_{A=B}$ and increasing the number of bits. (Refer to application example)

PIN CONFIGURATION (TOP VIEW)



Outline 16P4

BLOCK DIAGRAM



4-BIT MAGNITUDE COMPARATOR

FUNCTION TABLE (Note 1)

A_3, B_3	A_2, B_2	A_1, B_1	A_0, B_0	$I_A > B$	$I_A < B$	$I_A = B$	$O_A > B$	$O_A < B$	$O_A = B$
$A_3 > B_3$	X	X	X	X	X	X	H	L	L
$A_3 < B_3$	X	X	X	X	X	X	L	H	L
$A_3 = B_3$	$A_2 > B_2$	X	X	X	X	X	H	L	L
$A_3 = B_3$	$A_2 < B_2$	X	X	X	X	X	L	H	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 > B_1$	X	X	X	X	H	L	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 < B_1$	X	X	X	X	L	H	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 > B_0$	X	X	X	H	L	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 < B_0$	X	X	X	L	H	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 = B_0$	H	L	L	H	L	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 = B_0$	L	H	L	L	H	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 = B_0$	X	X	H	L	L	H
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 = B_0$	H	H	L	L	L	L
$A_3 = B_3$	$A_2 = B_2$	$A_1 = B_1$	$A_0 = B_0$	L	L	L	H	H	L

Note 1. X : Irrelevant

ABSOLUTE MAXIMUM RATINGS ($T_a = -20 \sim +75^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Limits	Unit
V_{CC}	Supply voltage		$-0.5 \sim +7$	V
V_I	Input voltage		$-0.5 \sim +15$	V
V_O	Output voltage	High-level state	$-0.5 \sim V_{CC}$	V
T_{opr}	Operating free-air ambient temperature range		$-20 \sim +75$	$^\circ\text{C}$
T_{stg}	Storage temperature range		$-65 \sim +150$	$^\circ\text{C}$

RECOMMENDED OPERATING CONDITIONS ($T_a = -20 \sim +75^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Limits			Unit
		Min	Typ	Max	
V_{CC}	Supply voltage	4.75	5	5.25	V
I_{OH}	High-level output current	$V_{OH} \geq 2.7\text{V}$	0	-400	μA
I_{OL}	Low-level output current	$V_{OL} \leq 0.4\text{V}$	0	4	mA
		$V_{OL} \leq 0.5\text{V}$	0	8	mA

ELECTRICAL CHARACTERISTICS ($T_a = -20 \sim +75^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ *	Max	
V_{IH}	High-level input voltage		2			V
V_{IL}	Low-level input voltage				0.8	V
V_{IC}	Input clamp voltage	$V_{CC} = 4.75\text{V}$, $I_{IC} = -18\text{mA}$			-1.5	V
V_{OH}	High-level output voltage	$V_{CC} = 4.75\text{V}$, $V_I = 0.8\text{V}$ $V_I = 2\text{V}$, $I_{OH} = -400\mu\text{A}$	2.7	3.4		V
V_{OL}	Low-level output voltage	$V_{CC} = 4.75\text{V}$ $V_I = 0.8\text{V}$, $V_I = 2\text{V}$		0.25	0.4	V
		$I_{OL} = 4\text{mA}$ $I_{OL} = 8\text{mA}$		0.35	0.5	V
I_{IH}	High-level input current	$I_A < B$, $I_A > B$ $A_0 \sim A_3, B_0 \sim B_3, I_A = B$			20	μA
		$I_A < B$, $I_A > B$ $A_0 \sim A_3, B_0 \sim B_3, I_A = B$			60	μA
		$V_{CC} = 5.25\text{V}$ $V_I = 10\text{V}$			0.1	mA
I_{IL}	Low-level input current	$I_A < B$, $I_A > B$ $A_0 \sim A_3, B_0 \sim B_3, I_A = B$			0.3	mA
		$V_{CC} = 5.25\text{V}$ $V_I = 0.4\text{V}$			-0.4	mA
I_{OS}	Short-circuit output current (Note 2)	$V_{CC} = 5.25\text{V}$, $V_O = 0\text{V}$	-20		-100	mA
I_{CC}	Supply current	$V_{CC} = 5.25\text{V}$ (Note 3)		11	20	mA

* : All typical values are at $V_{CC} = 5\text{V}$, $T_a = 25^\circ\text{C}$.

Note 2. All measurements must be done quickly and not more than output should be shorted at a time.


Note 3. I_{CC} is measured with $I_A = B$ at 0V and with all other inputs at 4.5V.

4-BIT MAGNITUDE COMPARATOR

SWITCHING CHARACTERISTICS (V_{CC}=5V, T_a=25°C, unless otherwise noted)


Symbol	Parameter		Test conditions	Limits			Unit
				Min	Typ	Max	
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from inputs, A ₀ ~ A ₃ , B ₀ ~ B ₃ to outputs O _A <B, O _A =B, O _A >B	Number of delay gate steps 1	C _L = 15pF (Note 4)		6		ns
t _{PHL}				11		ns	
t _{PLH}		Number of delay gate steps 2			10		ns
t _{PHL}					18		ns
t _{PLH}		Number of delay gate steps 3			12	36	ns
t _{PHL}					20	30	ns
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from inputs A ₀ ~A ₃ , B ₀ ~B ₃ to outputs O _A <B, O _A =B, O _A >B			16	45	ns	
t _{PHL}				20	45	ns	
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input I _A =B to outputs O _A <B, O _A >B			6	22	ns	
t _{PHL}				12	17	ns	
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input I _A =B to output O _A =B			7	20	ns	
t _{PHL}				13	26	ns	
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from inputs I _A <B, I _A >B to outputs O _A <B, O _A =B, O _A >B			9	22	ns	
t _{PHL}				15	17	ns	

Note 4: Measurement circuit




- (1) The pulse generator (PG) has the following characteristics:
PRR = 1MHz, t_r = 6ns, t_f = 6ns, t_w = 500ns,
V_p = 3V_{PP}, Z₀ = 50Ω.
- (2) C_L includes probe and jig capacitance.

TIMING DIAGRAM (Reference level = 1.3V)




(1) Shown below is a 24-bit (digital) comparator using the M74LS85P. Expansion is possible up to n bits using this type of cascade connection.




TYPE 14P4 14-PIN MOLDED PLASTIC DIL

Dimension in mm



TYPE 16P4 16-PIN MOLDED PLASTIC DIL

Dimension in mm



TYPE 20P4 20-PIN MOLDED PLASTIC DIL

Dimension in mm

