





Date	SYM	REVISION RECORD	AUTH	DR.	CK.
05/08/04	A	ADDED ELECTRICAL SPECS	T.B.	B.S.	
03/14/14	B	DIM. 11.5 WAS 11.40 DIM. 18.0 WAS 17.90 DIM. 23.0 WAS 22.80 DIM. 6.0 WAS 5.80 DIM. Ø1.30 WAS Ø1.50 DIM. 2.0 WAS 1.80 DIM. Ø4.50 WAS Ø4.80	T.B.	B.S.	



SCHEMATIC DIAGRAM

ELECTRICAL SPECS:

1. LIFE: 10,000 INSERTION/WITHDRAWAL CYCLE MINIMUM
2. CONTACT RESISTANCE: 50mΩ MAXIMUM
3. INSULATION RESISTANCE: 1000mΩ MINIMUM
4. DIELECTRIC WITHSTANDING VOLTAGE: 500VAC MAXIMUM
5. MAXIMUM RATING: 5A, 12V DC

ITEM NO.	PART NAME	MATL. SPECIFICATION	Tolerance (Inches)	Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
1	PIN TERMINAL	0.4 THK BRASS, SILVER PLTD.	Decimal ±.5 (.020)		Scale	Drawn By B.S.
2	SLEEVE SPRING	0.2 THK PHOSPHORSCENT BRONZE, SILVER PLTD.				Approved By T.B.
3	BREAK TERMINAL	0.3 THK BRASS, SILVER PLTD.			Fractional ± .8 (.030)	Title DC JACK - PANEL MOUNT TYPE
4	HOUSING	BLACK, P.B.T.				
5	INSULATOR	BAKELITE, NATURAL	Angular ± 3°	Date 03/14/14	Drawing Number EJ505B	
6	PIN (Ø2.1)	COPPER, NICKLE PLTD.				