

## KNIPEX MultiCrimp®

Crimping Pliers with quick changer magazine



97 33 01



97 33 02



97 33 01

Crimping pliers with round magazine and three interchangeable die sets for non-insulated open plug connectors (4.8 + 6.3 mm width) from 0.5 - 6.0 mm<sup>2</sup>; insulated terminals + plug connectors from 0.5 - 6.0 mm<sup>2</sup>; end sleeves (ferrules) from 0.25 - 6.0 mm<sup>2</sup>

97 33 02

Crimping pliers with round magazine and five interchangeable die sets for non-insulated open plug connectors (4.8 + 6.3 mm width) from 0.5 - 6.0 mm<sup>2</sup>; insulated terminals + plug connectors from 0.5 - 6.0 mm<sup>2</sup>; end sleeves (ferrules) from 0.25 - 6.0 mm<sup>2</sup>; non-insulated terminals and plug connectors from 0.5 - 10 mm<sup>2</sup>; non-insulated butt connectors from 1.5 - 10 mm<sup>2</sup>

The MultiCrimp® Pliers are not available in the U.S.A.

Compact, inexpensive and light-weight crimping pliers for fitting and repairs. The electrician needs only one tool now instead of five as before.

- just one tool for the most common crimping applications
- crimping dies changed quickly and easily without any additional tool
- secure and protected storage of the interchangeable dies in a round magazine
- comfortable, powerful crimping pliers in professional quality
- same reliable crimping results as with fixed crimping dies
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Chrome vanadium electric steel in special quality, oil-hardened
- Round magazine: plastic, fibreglass-reinforced



Changing position: service lever opens out for parallel jaw positioning



Changing the crimping dies: unlock the magazine position, take out the set of dies which the pliers have been pushed on



Fold in the service lever and press the pliers – ready for use again

# CRIMPING PLIERS



Magazine for crimping dies can be carried on a belt



Clearly visible marking on the crimping dies with pictograms

The MultiCrimp® Pliers are not available in the U.S.A.

Article No.	EAN 4003773-	↔ mm		Pliers	Handles			Applications	Capacity mm <sup>2</sup>	AWG	Number of crimping positions	ΔΔ g
97 33 01	066927	250	AAA	burnished	with multi-component grips			non-insulated, open plug-type connectors	0.5 - 6.0	20 - 10	3	770
								insulated terminals and plug connectors	0.5 - 6.0	20 - 10	3	
								End Sleeves (ferrules)	0.25 - 6.0	23 - 10	5	
97 33 02	066934	250	AAA	burnished	with multi-component grips			non-insulated, open plug-type connectors	0.5 - 6.0	20 - 10	3	870
								insulated terminals and plug connectors	0.5 - 6.0	20 - 10	3	
								End Sleeves (ferrules)	0.25 - 6.0	23 - 10	5	
								non-insulated terminals and plug connectors	0.5 - 10.0	20 - 7	4	
								non-insulated butt connectors	1.5 - 4.0 6.0 + 10.0*	15 - 11 10 + 7	3 2	

97 39 05	070078	Crimping dies for non-insulated open plug-type connectors 4.8 + 6.3 mm	
97 39 06	070085	Crimping dies for insulated terminals + plug connectors	
97 39 08	070092	Crimping dies for end sleeves (ferrules)	
97 39 13	070108	Crimping dies for non-insulated terminals + plug connectors	
97 39 30	070115	Crimping dies for non-insulated butt connectors	
97 39 90	070061	Quick Changer Magazine empty	

\* compression joints in conformance to DIN 46267