

# E1SEA10-17.1875M



## ITEM DESCRIPTION

Quartz Crystal Resonator HC49/UP Short 2 Pad Surface Mount (SMD) 3.2mm Height Metal Resistance Weld Seal  
17.1875MHz  $\pm 30\text{ppm}$  at 25°C,  $\pm 50\text{ppm}$  over -20°C to +70°C 10pF Parallel Resonant

## ELECTRICAL SPECIFICATIONS


|                               |                                                                    |
|-------------------------------|--------------------------------------------------------------------|
| Nominal Frequency             | 17.1875MHz                                                         |
| Frequency Tolerance/Stability | $\pm 30\text{ppm}$ at 25°C, $\pm 50\text{ppm}$ over -20°C to +70°C |
| Aging at 25°C                 | $\pm 5\text{ppm/year}$ Maximum                                     |
| Load Capacitance              | 10pF Parallel Resonant                                             |
| Shunt Capacitance             | 7pF Maximum                                                        |
| Equivalent Series Resistance  | 50 Ohms Maximum                                                    |
| Mode of Operation             | AT-Cut Fundamental                                                 |
| Drive Level                   | 1mWatt Maximum                                                     |
| Storage Temperature Range     | -40°C to +125°C                                                    |
| Insulation Resistance         | 500 Megaohms Minimum (Measured at 100Vdc)                          |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                               |
|------------------------------|-----------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 1, HBM: 1500V |
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A         |
| Flammability                 | UL94-V0                                       |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C         |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C          |
| Moisture Resistance          | MIL-STD-883, Method 1004                      |
| Moisture Sensitivity         | J-STD-020, MSL1                               |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K          |
| Resistance to Solvents       | MIL-STD-202, Method 215                       |
| Solderability                | MIL-STD-883, Method 2003                      |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B         |
| Vibration                    | MIL-STD-883, Method 2007, Condition A         |

# E1SEA10-17.1875M


## MECHANICAL DIMENSIONS (all dimensions in millimeters)



| LINE | MARKING                                  |
|------|------------------------------------------|
| 1    | <b>E17.187M</b><br>E=Ecliptek Designator |


## Suggested Solder Pad Layout

All Dimensions in Millimeters



All Tolerances are ±0.1

## Recommended Solder Reflow Methods



### High Temperature Infrared/Convection

**Ts MAX to Tl (Ramp-up Rate)** 3°C/Second Maximum

#### Preheat

- Temperature Minimum (Ts MIN) 150°C
- Temperature Typical (Ts TYP) 175°C
- Temperature Maximum (Ts MAX) 200°C
- Time (ts MIN) 60 - 180 Seconds

**Ramp-up Rate (Tl to Tp)** 3°C/Second Maximum

#### Time Maintained Above:

- Temperature (Tl) 217°C
- Time (tL) 60 - 150 Seconds

**Peak Temperature (Tp)** 260°C Maximum for 10 Seconds Maximum

**Target Peak Temperature (Tp Target)** 250°C +0/-5°C

**Time within 5°C of actual peak (tp)** 20 - 40 Seconds


**Ramp-down Rate** 6°C/Second Maximum

**Time 25°C to Peak Temperature (t)** 8 Minutes Maximum

**Moisture Sensitivity Level** Level 1

# E1SEA10-17.1875M

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 245°C Time (t)

**$T_S \text{ MAX}$  to  $T_L$  (Ramp-up Rate)** 5°C/Second Maximum

#### Preheat

- Temperature Minimum ( $T_S \text{ MIN}$ ) N/A
- Temperature Typical ( $T_S \text{ TYP}$ ) 150°C
- Temperature Maximum ( $T_S \text{ MAX}$ ) N/A
- Time ( $t_s \text{ MIN}$ ) 30 - 60 Seconds

**Ramp-up Rate ( $T_L$  to  $T_P$ )** 5°C/Second Maximum

#### Time Maintained Above:

- Temperature ( $T_L$ ) 150°C
- Time ( $t_L$ ) 200 Seconds Maximum

**Peak Temperature ( $T_P$ )** 245°C Maximum

**Target Peak Temperature ( $T_P \text{ Target}$ )** 245°C Maximum 2 Times / 230°C Maximum 1 Time

**Time within 5°C of actual peak ( $t_P$ )** 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time

**Ramp-down Rate** 5°C/Second Maximum

**Time 25°C to Peak Temperature (t)** N/A

**Moisture Sensitivity Level** Level 1

### Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum.