

A			B			C			D			E			F			G			H		
DWG. NO.			ZONE			REV.			DESCRIPTION			DATE			APPROVED								
010-0X3						X1			CUSTOMER APPROVAL			12/22/98			C.V.								
						X2			CHANGE RETRACTED LENGTH FROM 13' TO 24'			12/29/98			C.V.								
						A			PRODUCTION RELEASE			01/04/99			C.V.								
						B			CHAGNE TO ROHS			02/15/06			M.G.								

NOTES: UNLESS OTHERWISE SPECIFIED.

1.0 MATERIAL AND SPECIFICATIONS

1.01 CONDUCTORS: 26 AWG (12/0.12 mm) STRANDED BARE COPPER.

1.02 INSULATION: POLYPROPYLENE

1.03 COLOR: PER CALLOUT

2.0 ELECTRICAL CHARACTERISTICS

2.01 TEMPERATURE & VOLTAGE RATING: 80°C 30 V

2.02 CONDUCTORS RESISTANCE: 148 OHMS/KM MAX. AT 20°C

2.03 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN. AT 20°C

2.04 CAPACITANCE: 15 PF/FT (MAX)


2.05 DIELECTRIC TEST: AC-500V PER 1 MINUTE

3.0 PACKAGING SPECIFICATION



3.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.

3.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

3.03 MAX. DIMENSION OUTSIDE SHIPPING BOX IS L=13.00' x W=25.00' x H=9.00'.



10 CONDUCTOR CABLE



BUNDLE SPECIFICATION

GLF-121-010-003	10	SILVER SATIN	[0.748 REF.] 19.00 REF.
GLF-121-010-013	10	BLACK	[0.748 REF.] 19.00 REF.
GLF-121-010-023	10	WHITE	[0.748 REF.] 19.00 REF.
I/O INTERCONNECT PART NUMBER	NUMBER OF CONDUCTORS	COLOR	φ "A"
THIRD ANGLE PROJECTION			
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER [INCHES] 2) TOLERANCES: X.X ± 0.20 [0.008] X.XX ± 0.25 [0.010]			
I/O INTERCONNECT			
SANTA ANA, CALIFORNIA			
TR. BY: CHAU HAI TR. CHECKER: MEJ	TITLE: 26 AWG (12/0.12 mm) BARE COPPER, 500 FT EXTENDED, 10P 10C NON-UL, UNSHIELD, MODULAR CABLE		
DATE: 02/15/06	PART NO: GLF-121-010-0X3		
ENGINEER: MEJ	DWG NO: GLF-121-010-0X3		
CUST./SALES: B	CUSTOMER: DIGI KEY		
DATE: 02/15/06	SCALE: NONE		
SHEET 1			DF 1