




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		K1	REVISED PER ECR-09-000368	20JAN09	HMR	DD

- 1
- CONTINUOUS STRIP ON REELS.
- 2
- .000100 [0.00254] MIN TIN PLATE.
- 3
- WIRE RANGE: 18-14 AWG.
- 4
- INSULATION RANGE: .120-.170 [3.05-4.32] DIA.



SECTION A-A



SECTION B-B

OBSOLETE	.197[5.00]	10		—	155406-6
	.197[5.00]	10	—	—	155406-5
	.171[4.34]	8		—	155406-4
OBSOLETE	.171[4.34]	8	—	—	155406-3
	.145[3.68]	6		1-155406-2	155406-2
	.145[3.68]	6	—	1-155406-1	155406-1
"D" DIA		STUD SIZE	FINISH	LOOSE PIECE PART NUMBER	STRIP PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN MICHAEL S. FEHER CHK DONALD F. DECKER APVD DONALD F. DECKER	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	
		0 PLC ± — 1 PLC ± — 2 PLC ± .020[0.51] 3 PLC ± .010[0.25] 4 PLC ± — ANGLES ± 1°	— APPLICATION SPEC	TONGUE, RING OPEN BARREL	
MATERIAL		FINISH	WEIGHT	SIZE	RESTRICTED TO
#2 HARD BRASS		SEE TABLE	—	CAGE CODE	—
CUSTOMER DRAWING				DRAWING NO	—
SCALE				SHEET	REV
4:1				1 of 1	K1