



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E	REVISED PER ECR-12-013486	08JAN13	KH	KR



SUGGESTED MATING TAB




- 1 MATL: #2 HARD BRASS OR NICKEL PLATED STEEL.
 - 2 NO BURRS PERMISSIBLE AT HOLE.
 - 3 TIN PLATING IS REQUIRED ON BRASS WHEN TEMPERATURE IS OVER 225°F
 - 4 MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - 5 HOLE MUST BE SYMMETRICAL ABOUT TAB CENTER WITHIN 0.076 [.003].
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2 CONTINUOUS STRIP ON REELS.
- 3 THIS DIMENSIONS MUST BE MAINTAINED FOR PROPER FUNCTION OF THE LATCHING MECHANISM.
- 4 WIRE SIZE IS 0.5-1.4mm [20-16] AWG
- 5 INSULATION RANGE IS 1.52-2.79 [.060-.110] DIA



F OR O	3.56 [.140]	4.78 [.188]	F	2.29 [.090]	1.448 [.057]	1.3mm [.16]
					1.27 [.050]	0.8mm [.18]
					1.143 [.045]	0.5mm [.20]
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.051 [±.002] HEIGHT	WIRE
INSUL BARREL CRIMP	WIRE BARREL CRIMP					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	10/12/89	 TE Connectivity											
		CHK	MS FEHER	10/12/89												
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	R KUZO	10/12/89	NAME	RECEPTACLE, POSITIVE LOCK, 4.75 [.187] SERIES								
		0 PLC ± -		PRODUCT SPEC		APPLICATION SPEC										
		1 PLC ± -		—												
		2 PLC ± -		—												
		3 PLC ± 0.25 [.010]					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
		4 PLC ± -														
MATERIAL		FINISH		WEIGHT		—	A2	00779	C=63498	—						
BRASS		SEE TABLE		CUSTOMER DRAWING							SCALE	5:1	SHEET	1 of 1	REV	E