

- Supports Standard NTSC and PAL Video Specifications¹
- Seamlessly Interfaces With Intel™ DVO Port on Whitney and Future Intel Chipsets
- Supports 24-Bit RGB and YCrCb Input Formats on a 12-Bit Pixel Port
- Supports CCIR-656 YCbCr 4:2:2 Input Format on an 8-Bit Port
- Analog Composite Video Out Formats:
 - NTSC-M
 - PAL-B,D,G,H,I
 - PAL-M
 - PAL-N
 - PAL-Nc
- Simultaneous Composite and S-Video (Y/C Component) or YPrPb Component Output
- SCART Interface (Simultaneous Composite and Interlaced RGB Output)
- Programmable Functionality and I²C Serial Interface²
- Four 10-Bit DACs
- 2X Over-Sampling and Optimized Filters for Luma and Chroma Channels
- Reduced Power Consumption – 1.8 V Digital Core and 3.3 V Analog Circuit
- Lowest Noise and Best Power Dissipation Using TI PowerPAD™ Packaging
- Advanced Technology Using TIs 0.18 μm EPIC-5™ CMOS Process
- TFP6024 Incorporates Macrovision™ 7.11 Support

description

The TFP6022 and TFP6024 are PanelBus™ flat panel display products, part of a comprehensive family of end-to-end PC video solutions. Targeted primarily at desktop and notebook PCs, the TFP6022/6024 finds applications in any design requiring TV-out support, such as PC-to-TV applications with source from DVD players and digital camcorders / cameras.

The scalable (1.1 V to 1.8 V) low-swing digital pixel interface provides a low-EMI and high-speed bus that connects seamlessly with Intel™ digital video out (DVO) port, perfectly linking the graphics controller and the video encoder.

The TFP6022/6024 places a high performance NTSC/PAL video encoder into a compact 64-pin TQFP package, providing a cost-effective video output solution for the most demanding multimedia applications. The video encoder provides advanced horizontal and vertical scaling for overscan compensation and features a 5-tap adaptive anti-flicker filter. These features combine to produce high quality display of noninterlaced data on a traditional interlaced TV.

The TFP6022/6024 combines PanelBus™ circuit innovation with TIs advanced 0.18 μm EPIC-5™ CMOS process technology along with PowerPAD™ ultra-low ground inductance package technology to provide a reliable, low-powered, low noise solution with the highest quality TV output.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

1. The TFP6022 and TFP6024 are compliant to the SMPTE 170M NTSC composite video, and CCIR624/CCIR601 PAL composite video specifications.
2. Programmable functionality includes: arbitrary horizontal and vertical downscaling ratio, sync, black and blank levels, color burst amplitude, luminance and chrominance gains, luminance delay, subcarrier frequency, overscan compensation, flicker removal and SCH.

EPIC-5, PowerPAD, and PanelBus are trademarks of Texas Instruments.

Intel is a trademark of Intel Corporation and Macrovision is a trademark of Macrovision Corporation.

Other trademarks are property of their respective owners.

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2000, Texas Instruments Incorporated

PRODUCT PREVIEW

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Of course, customers are responsible for their applications using TI components.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.