


SOT223 NPN SILICON PLANAR MEDIUM POWER TRANSISTOR

ISSUE 1 - FEBRUARY 1999

FZT491A

PARTMARKING DETAIL – FZT491A



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	40	V
Collector-Emitter Voltage	V_{CEO}	40	V
Emitter-Base Voltage	V_{EBO}	5	V
Peak Pulse Current	I_{CM}	2	A
Continuous Collector Current	I_C	1	A
Base Current	I_B	200	mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	2	W
Operating and Storage Temperature Range	$T_j:T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Breakdown Voltage	$V_{(BR)CBO}$	40			V	$I_C=100\mu A$
	$V_{(BR)CEO}$	40			V	$I_C=10mA^*$
	$V_{(BR)EBO}$	5			V	$I_E=100\mu A$
Collector Cut-Off Current	I_{CBO}			100	nA	$V_{CB}=30V$
Emitter Cut-Off Current	I_{EBO}			100	nA	$V_{EB}=4V$
Collector-Emitter Cut-Off Current	I_{CES}			100	nA	$V_{CES}=30V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$			0.3	V	$I_C=500mA, I_B=50mA^*$
				0.5	V	$I_C=1A, I_B=100mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$			1.1	V	$I_C=1A, I_B=100mA^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$			1.0	V	$I_C=1A, V_{CE}=5V^*$
Static Forward Current	h_{FE}	300		900		$I_C=1mA, V_{CE}=5V$
		300				$I_C=500mA, V_{CE}=5V^*$
		200				$I_C=1A, V_{CE}=5V^*$
		35				$I_C=2A, V_{CE}=5V^*$
Transition Frequency	f_T	150			MHz	$I_C=50mA, V_{CE}=10V, f=100MHz$
Output Capacitance	C_{obo}			10	pF	$V_{CB}=10V, f=1MHz$

*Measured under pulsed conditions. Pulse width=300 μs .

For typical characteristics graphs see FMMT491A datasheet