




NOTE(S):

- 1 TERMINAL MATERIAL: COPPER ALLOY
- 2 FINISH: ELECTROTIN PLATE
- 3 INSULATION MATERIAL: HEAT SHRINKABLE TUBING WITH HOTMELT ADHESIVE INNER LINER. COLOR: SEE CHART
- 4 MWID: MAXIMUM WIRE INSULATION DIAMETER

SALES DRAWING

CHANGED MWID EC NO: ETC2007-0054 DRWN: JLOMASTR006/08/16 CHKD: RDEROSS 2006/08/16 APPR: JMACNEIL 2006/08/17	QUALITY SYMBOLS DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± .02 1 PLACE ± 0.5 ± --- ANGULAR ± 1 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SCALE 1:1 DESIGN UNITS INCH DIMENSION STYLE IN/MM DRAWN BY BENDERLE 2004/08/23 CHECKED BY R DEROSS 2004/08/23 APPROVED BY RDEROSS 2004/08/23	THIRD ANGLE PROJECTION REVISE ON CAD ONLY TITLE .180/4.57 SNAP PLUG NIAC 22-18 16-14 AWG MOLEX INCORPORATED MATERIAL NO. SEE CHART DOCUMENT NO. SD-19164-068 SHEET NO. 1 OF 1