





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		C1	REVISED PER ECO-11-004820	11MAR11	RK	HMR



1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: .5-2mm² [20-14 AWG].
INSULATION RANGE: 1.52-3.30[.060-.130] DIA.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

GOLD 4	0.30 [.012] PH BRZ	1-770251-0
GOLD 1	0.30 [.012] PH BRZ	770251-4
PRE-TIN	0.30 [.012] PH BRZ	770251-3
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 20JAN93	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. SWING 20JAN93				
		APVD M. TRULL 01APR93	NAME SOCKET, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II			
		PRODUCT SPEC	-			
MATERIAL SEE TABLE		APPLICATION SPEC	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-770251	RESTRICTED TO -
FINISH SEE TABLE		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV C1	