

Surface Mount

Voltage Controlled Oscillator



1060 to 1121 MHz

ROS-1121V



CASE STYLE: CK605

Features

- linear tuning characteristic
- low sensitivity, 8-13 MHz/V typ.
- low phase noise, -111 dBc/Hz@10 kHz

Applications

- radio

Electrical Specifications

FREQ. (MHz)	POWER OUTPUT (dBm)	TUNING VOLTAGE		PHASE NOISE dBc/Hz SSB at offset frequencies: Typ.				PULLING pk-pk @ 12 dB (MHz)	PUSHING (MHz/V)	TUNING SENSI- TIVITY (MHz/V)	HARMONICS* (dBc)		3 dB MODULATION BANDWIDTH (kHz) Typ.	POWER SUPPLY		PRICE \$
		Min.	Max.	1 kHz	10 kHz	100 kHz	1 MHz				Typ.	Max.		Voltage (V)	Current (mA) Max.	
1060-1121	2.5	1	11	-88	-111	-131	-149	0.7	0.7	8-13	-11	—	10000	5	30	15.95

* specified to 4th harmonic


Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	+6 V
Absolute Max. Tuning Voltage (Vtune)	+12V
All specifications: 50 ohm system	

Pin Connections

PORT	kg
RF OUT	10
V-CC	14
V-TUNE	2
GND EXT.	all others

Outline drawing



Outline dimensions (inch mm)

A	B	C	D	E	F	G	H	J	
.500	.500	.180	.100	.080	.115	.060	.040	.540	
(12.70)	(12.70)	(4.57)	(2.54)	(2.03)	(2.92)	(1.52)	(1.02)	(13.72)	
K	L	M	N	P	Q	R	S	T	WT GRAMS
.060	.100	.135	.135	.115	.140	.070	.150	.070	1
(1.52)	(2.54)	(3.45)	(3.45)	(2.92)	(3.56)	(1.78)	(3.81)	(1.78)	



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers/ NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-835094 • Fax 44-1252-837010

ISO 9001 CERTIFIED

REV. OR
M70973
ED-8221B/6
ROS-1121V
SK/TD/CP
000316

INTERNET <http://www.minicircuits.com>