




MARKETING SALES DRAWING


DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4251-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4251-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

15,000		50 VDC		10 GΩ		250 VDC		10 A		5		9		18		45		65		70		70						
MIN. CAP.(pf)		+125 °C DC WORKING VOLTAGE		I.R. MIN. @ 100 VDC		DWV		CURRENT		1 MHz	3 MHz	10 MHz	30 MHz	100 MHz	300 MHz	1GHz	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220											
REVISION RECORD Original Release C.O. 6611 HDIM'S REVISED .81 WAS .812 6.7 WAS 6.75. TITLE CHGD. E.C. 5-26-92		1	RDN TO COMP FMT. S.M. 06-03-02		2		DWV 250 WAS 125. S.M. 09-22-03		3		ADDED NOTES 1-3. S.M. 10-06-05		4		20050927-7-03		--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ±  TUSONIX TUCSON, ARIZONA						Title MULTI LAYER BUSHING STYLE EMI FILTER Drawn S. M. 02-28-02 Scale 4 X Approved T.C. 02-58-02 A4251-001					