THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST
CM	0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	ECO-08-028197	12NOV2008	KW	CC

1. WIRE RANGE: 20-14 (0.5-2mm²) AWG
INSULATION RANGE: .125 MAX.





SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

.050	1.27	.139	3.53	.180	4.57		
.043	1.09	.135	3.43	.165	4.19		
.035	0.89	.130	3.30	.156	3.96		
.018	0.46	.125	3.18	.155	3.94	.770	19.56
.015	0.38	.115	2.92	.152	3.86	.750	19.05
.005	0.13	.063	1.60	.148	3.76	.189	4.80
IN	MM	IN	MM	IN	MM	IN	MM

CONVERSION TABLE

TIN	.018 BRASS	61250-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL: BRASS
FINISH: PRE-TIN

METRIC

DWN	B. LEWIS	6-25-96
CHK	R. SWING	6-25-96
APVD	C. MARTIN	6-25-96
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	

Tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
SOCKET, LOOSE PIECE,
.156 MATE-N-LOK(TM)
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-61250	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV J

61250

Translated 081112.075702 (YYMMDD.HHMMSS) from Computervision, Inc., Medusa Revision 12.2.5T