Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AC	140002	LSS	07/22/94		.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
AD	N05-0129	ZC	5/20/05		.XXXX±.0020/.XXX±.051			
AE	N05-0151	WG	7/31/07	angles	0°±2°			
AF	N08-0175	R.B	2008/08/22	dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823
				chr	M. SMYK	1/16/90	scale 5:1	sheet 1 of 21
				appd	M. SMYK	1/16/90		

AE	sheet	revision	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF	AF
21	index	sheet	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire. Propriete de c FCI. Droits de reproduction FCI.



RECOMMENDED HOLE PATTERN
SCALE 10:1



VIEW F-F



SECTION G-G
ROTATED 90°CW

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3				
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	
					.XXXX±.0020/.XXX±.051				
				angles	0°±2°				
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE	code –
				engr	M. SMYK	1/16/90		size A dwg no 65823	sheet 2 of 21
				chr	M. SMYK	1/16/90	scale 5:1		
				appd	M. SMYK	1/16/90			

	sheet	revision
21	index	sheet

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



HEADER WITH LATCHES



2X5
STYLE A



2X5
STYLE B



2X7
STYLE C



2X8 THRU 2X30
(2X10 SHOWN)
STYLE D

ALL SIZES
STYLE E

NOTES:

1. RECOMMENDED MOUNTING SCREW SIZE: #2-56 FILLISTER HD MACH SCREW, 3/8" LG FOR 1/16" & 3/32" BOARD, 7/16" LG FOR 1/8" BOARD.
2. MOLDING MAT'L: 30% GLASS FILLED POLYESTER, FLAME RETARDANT PER UL-94V-0, COLOR: BLUE.
3. PIN MAT'L: 3/4 HARD PHOS BRONZE ALLOY UNS C-51000.
4. 1 ° MAX DRAFT PERMISSIBLE ON ALL SURFACES UNLESS OTHERWISE SPECIFIED.
5. PLATING ON LEAD-IN PORTION OF PIN IS MANUFACTURING OPTION.
6. [B] BASIC DIM SHALL BE LOCATED SYMMETRICAL TO DATUM -Y-.
7. LOW PROFILE LATCHES TO BE USED WITH FEMALE CONNECTOR WITHOUT STRAIN RELIEF.
   STANDARD LATCHES TO BE USED WITH FEMALE CONNECTOR WITH STRAIN RELIEF.
8. .040±.003/1.02±.08 DIA HOLE TYP FOR SQ PINS, .035±.003/.89±.08 DIA HOLE TYP FOR RND PINS.
9. A. RETENTION FEATURE AVAILABLE ON CONNECTORS WITH .105/2.67, .120/3.05, OR .150/3.81 TAIL LENGTH. RETENTION P/N INCLUDES THE LETTER "R" AFTER THE EXISTING P/N.
   EXAMPLE: 65823-XXX FOR EXISTING P/N
   65823-XXXR FOR RETENTION P/N
   RETENTION FEATURE LOCATION IS MANUFACTURERS OPTION.
   B. ROUND PINS HAVE 15 LBS/6.8 KGS MAX INSERTION AND .25 LB/.1 KG MIN RETENTION FORCE WHEN USED IN .035±.003/.89±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.
   C. SQUARE PINS HAVE A 15 LBS/6.8 KG MAX INSERTION AND .5 LB/.2 KG MIN RETENTION FORCE WHEN USED IN .040±.003/1.02±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.
10. 65496-***LF IS JUST A LEAD FREE PRODUCT.
11. THE HOUSING OF XXXXX-XYYLF WILL WITHSTAND EXPOSUURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.
12. PLATING OPTION: MAYBE EITHER GOLD OR GXT PLATING AT MANUFACTURER'S OPTION .

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 3 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-001(LF)	2x5	NO	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76 Au OVER 50u"/1.27uNi	A
-002(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-003(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-004(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-005(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
-006(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/3.81u Sn	A
-007(LF)	2x7		RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u"/.76 Au OVER 50u"/1.27uNi	C
-008(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-009(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-010(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-011(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
-012(LF)	2x7		SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u"/3.81u Sn	C
-013(LF)	2x8		RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u"/.76 Au OVER 50u"/1.27uNi	D
-014(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-015(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-016(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-017(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
-018(LF)	2x8		SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u"/3.81u Sn	
-019(LF)	2x10		RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76 Au OVER 50u"/1.27uNi	
-020(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-021(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-022(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-023(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
-024(LF)	2x10		SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u"/3.81u Sn	
-025(LF)	2x13		RND	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1	30u"/.76 Au OVER 50u"/1.27uNi	
-026(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-027(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-028(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-029(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
-030(LF)	2x13		SQ	2.060/52.32	1.200/30.48	1.520/38.61	.675/17.15	1.66/42.1	150u"/3.81u Sn	
-031(LF)	2x17		RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u"/.76 Au OVER 50u"/1.27uNi	
-032(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-033(LF)			RND				.150/3.81		30u"/.76 Au OVER 50u"/1.27uNi	
-034(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-035(LF)			SQ				.675/17.15		30u"/.76 Au OVER 50u"/1.27uNi	
65823-036(LF)	2x17	NO	SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u"/3.81u Sn	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 4 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-037(LF)	2x20	NO	RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u"/.76u Au OVER 50u"/1.27u Ni	D
-038(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-039(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-040(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-041(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-042(LF)	2x20		SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u"/3.81u Sn	
-043(LF)	2x25		RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni	
-044(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-045(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-046(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-047(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-048(LF)	2x25	NO	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u"/3.81u Sn	D
-049(LF)	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au OVER 50u"/1.27u Ni	A
-050(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-051(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-052(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-053(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-054(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/3.81u Sn	A
-055(LF)	2x7		RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u"/.76u Au OVER 50u"/1.27u Ni	C
-056(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-057(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-058(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-059(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-060(LF)	2x7		SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u"/3.81u Sn	C
-061(LF)	2x8		RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u"/.76u Au OVER 50u"/1.27u Ni	D
-062(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-063(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-064(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-065(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-066(LF)	2x8		SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u"/3.81u Sn	
-067(LF)	2x10		RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76u Au OVER 50u"/1.27u Ni	
-068(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-069(LF)			RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-070(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-071(LF)			SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
65823-072(LF)	2x10	STD	SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u"/3.81u Sn	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

strictly reserved. Reproduction or issue to third parties in any er is not permitted without written authority from the proprietor. f FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code —
				engr	M. SMYK	1/16/90		size dwg no / sheet
				qlty	M. SMYK	1/16/90	scale 5:1	STATUS Released A 65823 5 of 21
				appd	M. SMYK	1/16/90		

PDM: Rev:AF Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-073 (LF)	2x13	STD	RND	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1	30u" /.76u Au OVER 50u" /1.27u Ni	D
-074 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-075 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-076 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-077 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
-078 (LF)	2x13		SQ	2.060/52.32	1.200/30.48	1.520/38.61	.675/17.15	1.66/42.1	150u" /3.81u" 1/27u Ni	
-079 (LF)	2x17		RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u" /.76u Au OVER 50u" /1.27u Ni	
-080 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-081 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-082 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-083 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
-084 (LF)	2x17		SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u" /3.81u" 1/27u Ni	
-085 (LF)	2x20		RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u" /.76u Au OVER 50u" /1.27u Ni	
-086 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-087 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-088 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-089 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
-090 (LF)	2x20		SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u" /3.81u" 1/27u Ni	
-091 (LF)	2x25		RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" /.76u Au OVER 50u" /1.27u Ni	
-092 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-093 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-094 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-095 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
-096 (LF)	2x25	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u" /3.81u" 1/27u Ni	
-097 (LF)	2x30	NO	RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" /.76u Au OVER 50u" /1.27u Ni	
-098 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-099 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-100 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-101 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
-102 (LF)		NO	SQ				.675/17.15		150u" /3.81u" 1/27u Ni	
-103 (LF)		STD	RND				.105/2.67		30u" /.76u Au OVER 50u" /1.27u Ni	
-104 (LF)			SQ				.105/2.67		150u" /3.81u" 1/27u Ni	
-105 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-106 (LF)			SQ				.150/3.81		150u" /3.81u" 1/27u Ni	
-107 (LF)			SQ				.675/17.15		30u" /.76u Au OVER 50u" /1.27u Ni	
65823-108 (LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	150u" /3.81u" 1/27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 6 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-109(LF)	2x5	NO	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au OVER 50u"/1.27u Ni	A
-110(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-111(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-112(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-113(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-114(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-115(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-116(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-117(LF)	2x30	NO		3.760/95.50	2.900/73.66	3.220/81.79		3.36/85.3		D
-118(LF)	2x5	STD		1.260/32.00	.400/10.16	.720/18.29		.86/21.8		A
-119(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-120(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-121(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-122(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-123(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-124(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-125(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-126(LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u"/.76u Au OVER 50u"/1.27u Ni	D
-127(LF)	2x5	NO	RND	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	30u"/.76u GXT/GOLD FLASH	A
-128(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-129(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-130(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-131(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-132(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-133(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-134(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-135(LF)	2x30	NO		3.760/95.50	2.900/73.66	3.220/81.79		3.36/85.3		D
-136(LF)	2x5	STD		1.260/32.00	.400/10.16	.720/18.29		.86/21.8		A
-137(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-138(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-139(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-140(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-141(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-142(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-143(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-144(LF)	2x30	STD	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u"/.76u GXT/GOLD FLASH	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 7 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-145 (LF)	2x5	LP	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" /.76u Au OVER 50u" /1.27u Ni	A
-146 (LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	↑
-147 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-148 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-149 (LF)	↓	↓	SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	↓
-150 (LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u" /3.81u Sn	A
-151 (LF)	2x7		RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u" /.76u Au OVER 50u" /1.27u Ni	C
-152 (LF)	↑		SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	↑
-153 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-154 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-155 (LF)	↓		SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	↓
-156 (LF)	2x7		SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u" /3.81u Sn	C
-157 (LF)	2x8		RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u" /.76u Au OVER 50u" /1.27u Ni	D
-158 (LF)	↑		SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	↑
-159 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-160 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-161 (LF)	↓		SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	↓
-162 (LF)	2x8		SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u" /3.81u Sn	
-163 (LF)	2x10		RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u" /.76u Au OVER 50u" /1.27u Ni	
-164 (LF)	↑		SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	
-165 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-166 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-167 (LF)	↓		SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	
-168 (LF)	2x10		SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u" /3.81u Sn	
-169 (LF)	2x13		RND	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1	30u" /.76u Au OVER 50u" /1.27u Ni	
-170 (LF)	↑		SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	
-171 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-172 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-173 (LF)	↓		SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	
-174 (LF)	2x13		SQ	2.060/52.32	1.200/30.48	1.520/38.61	.675/17.15	1.66/42.1	150u" /3.81u Sn	
-175 (LF)	2x17		RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u" /.76u Au OVER 50u" /1.27u Ni	
-176 (LF)	↑		SQ	↑	↑	↑	.105/2.67	↑	150u" /3.81u Sn	
-177 (LF)			RND				.150/3.81		30u" /.76u Au OVER 50u" /1.27u Ni	
-178 (LF)			SQ				.150/3.81		150u" /3.81u Sn	
-179 (LF)	↓	↓	SQ	↓	↓	↓	.675/17.15	↓	30u" /.76u Au OVER 50u" /1.27u Ni	↓
65823-180 (LF)	2x17	LP	SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u" /3.81u Sn	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 8 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-181(LF)	2x20	LP	RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u"/.76u OVER 50u"/1.27u Ni	D
-182(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-183(LF)			RND				.150/3.81		30u"/.76u OVER 50u"/1.27u Ni	
-184(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-185(LF)			SQ				.675/17.15		30u"/.76u OVER 50u"/1.27u Ni	
-186(LF)	2x20		SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u"/3.81u Sn	
-187(LF)	2x25		RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u OVER 50u"/1.27u Ni	
-188(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-189(LF)			RND				.150/3.81		30u"/.76u OVER 50u"/1.27u Ni	
-190(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-191(LF)			SQ				.675/17.15		30u"/.76u OVER 50u"/1.27u Ni	
-192(LF)	2x25		SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u"/3.81u Sn	
-193(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u"/.76u OVER 50u"/1.27u Ni	
-194(LF)			SQ				.105/2.67		150u"/3.81u Sn	
-195(LF)			RND				.150/3.81		30u"/.76u OVER 50u"/1.27u Ni	
-196(LF)			SQ				.150/3.81		150u"/3.81u Sn	
-197(LF)			SQ				.675/17.15		30u"/.76u OVER 50u"/1.27u Ni	
-198(LF)	2x30			3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	150u"/3.81u Sn	D
-199(LF)	2x5			1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u OVER 50u"/1.27u Ni	A
-200(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-201(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-202(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-203(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-204(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-205(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-206(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-207(LF)	2x30		SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u"/.76u OVER 50u"/1.27u Ni	D
-208(LF)	2x5		RND	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	30u"/.76u GXT/GOLD FLASH	A
-209(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-210(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-211(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-212(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-213(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-214(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-215(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-216(LF)	2x30	LP	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u"/.76u GXT/GOLD FLASH	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified		
linear	.XX±.01/.X±.3	
	.XXX±.005/.XX±.13	
	.XXXX±.0020/.XXX±.051	
angles	0°±2°	
dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 9 of 21

sheet	revision
21	index sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-217(LF)	2x5	NO	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u GXT/GOLD FLASH	A
-218(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-219(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-220(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-221(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-222(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-223(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-224(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-225(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-226(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A
-227(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-228(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-229(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-230(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-231(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-232(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-233(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-234(LF)	2x30	NO	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3		D
-235(LF)	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8		A
-236(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-237(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-238(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-239(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-240(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-241(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-242(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-243(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-244(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A
-245(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-246(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-247(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-248(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-249(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-250(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-251(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-252(LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u"/.76u GXT/GOLD FLASH	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 10 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-253(LF)	2x5	LP	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u GXT/GOLD FLASH	A
-254(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-255(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-256(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-257(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-258(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-259(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-260(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-261(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-262(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A
-263(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-264(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-265(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-266(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-267(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-268(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-269(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-270(LF)	2x30	LP	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	30u"/.76u GXT/GOLD FLASH	D
-271(LF)	2x5	NO	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u".38u Au OVER 50u"/1.27u Ni	A
-272(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-273(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-274(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-275(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-276(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-277(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-278(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-279(LF)	2x30			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-280(LF)	2x5			1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A
-281(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-282(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-283(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-284(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-285(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-286(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-287(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-288(LF)	2x30	NO	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	15u".38u Au OVER 50u"/1.27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 11 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-289(LF)	2x5	NO	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u". 38u Au OVER 50u"/1.27u Ni	A
-290(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-291(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-292(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-293(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-294(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-295(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-296(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-297(LF)	2x30	NO	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-298(LF)	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A
-299(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-300(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-301(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-302(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-303(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-304(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-305(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-306(LF)	2x30			3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3		D
-307(LF)	2x5			1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8		A
-308(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-309(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-310(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-311(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-312(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-313(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-314(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-315(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-316(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A
-317(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-318(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-319(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-320(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-311(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-312(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-313(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-313(LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	15u". 38u Au OVER 50u"/1.27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 12 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE	
65823-325 (LF)	2x5	LP	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u" /.38u Au OVER 50u" /1.27u Ni	A	
-326 (LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C	
-327 (LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D	
-328 (LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5			
-329 (LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1			
-330 (LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3			
-331 (LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9			
-332 (LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6			
-333 (LF)	2x30			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D	
-334 (LF)	2x5			1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A	
-335 (LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C	
-336 (LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D	
-337 (LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5			
-338 (LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1			
-339 (LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3			
-340 (LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9			
-341 (LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6			
-342 (LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3		D	
-343 (LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A	
-344 (LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C	
-345 (LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D	
-346 (LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5			
-347 (LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1			
-348 (LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3			
-349 (LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9			
-350 (LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6			
-351 (LF)	2x30	LP	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	15u" /.38u Au OVER 50u" /1.27u Ni		
-352 (LF)	2x25	66258	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" /.76u Au OVER 50u" /1.27u Ni	D	
-353 (LF)	2x7	NO		1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C	*
-354 (LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D	*
-355 (LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5			*
-356 (LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1			*
-357 (LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3			*
-358 (LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9			*
-359 (LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6			*
65823-360 (LF)	2x30	NO	RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" /.76u Au OVER 50u" /1.27u Ni	D	*

*CUSTOMER SPECIAL

sheet	revision
21	index sheet

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 13 of 21

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-361(LF)	2x5	NO	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au OVER 50u"/1.27u Ni	A *
-362(LF)		NO	RND						30u"/.76u Au OVER 50u"/1.27u Ni	B
-363(LF)		NO	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-364(LF)		NO	RND						30u"/.76u GXT/GOLD FLASH	
-365(LF)		NO	SQ						150u"/3.81u Sn	
-366(LF)		STD	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-367(LF)		STD	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-368(LF)		STD	RND						30u"/.76u GXT/GOLD FLASH	
-369(LF)		STD	SQ						150u"/3.81u Sn	
-370(LF)		LP	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-371(LF)		LP	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-372(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-373(LF)		LP	SQ				.105/2.67		150u"/3.81u Sn	
-374(LF)		NO	RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-375(LF)		NO	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-376(LF)		NO	RND						30u"/.76u GXT/GOLD FLASH	
-377(LF)		NO	SQ						150u"/3.81u Sn	
-378(LF)		STD	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-379(LF)		STD	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-380(LF)		STD	RND						30u"/.76u GXT/GOLD FLASH	
-381(LF)		STD	SQ						150u"/3.81u Sn	
-382(LF)		LP	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-383(LF)		LP	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-384(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-385(LF)		LP	SQ				.150/3.81		150u"/3.81u Sn	
-386(LF)		NO	SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-387(LF)		NO							15"/.38u Au OVER 50u"/1.27u Ni	
-388(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-389(LF)		NO							150u"/3.81u Sn	
-390(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-391(LF)		STD							15"/.38u Au OVER 50u"/1.27u Ni	
-392(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-393(LF)		STD							150u"/3.81u Sn	
-394(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-395(LF)		LP							15"/.38u Au OVER 50u"/1.27u Ni	
65823-396(LF)	2x5	LP	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	30u"/.76u GXT/GOLD FLASH	B

*CUSTOMER SPECIAL

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 14 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-397(LF)	2x5	LP	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/3.81u Sn	B
-398(LF)	2x10	66258-001	RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76u Au OVER 50u"/1.27u Ni	D
-399(LF)	2x5	NO	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u"/.38u Au OVER 50u"/1.27u Ni	A
-400(LF)		STD					.105/2.67			
-401(LF)		LP					.105/2.67			
-402(LF)		NO					.150/3.81			
-403(LF)		STD					.150/3.81			
-404(LF)		LP					.150/3.81			A
-405(LF)		NO					.105/2.67			B
-406(LF)		STD					.105/2.67			
-407(LF)		LP					.105/2.67			
-408(LF)		NO					.150/3.81			
-409(LF)		STD					.150/3.81			
-410(LF)	2x5	LP		1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		B
-411(LF)	2x7	NO		1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9		C
-412(LF)		STD					.105/2.67			
-413(LF)		LP					.105/2.67			
-414(LF)		NO					.150/3.81			
-415(LF)		STD					.150/3.81			
-416(LF)	2x7	LP		1.460/37.08	.600/15.24	.920/23.37	.150/3.81	1.06/26.9		C
-417(LF)	2x8	NO		1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4		D
-418(LF)		STD					.105/2.67			
-419(LF)		LP					.105/2.67			
-420(LF)		NO					.150/3.81			
-421(LF)		STD					.150/3.81			
-422(LF)	2x8	LP		1.560/39.62	.700/17.78	1.020/25.91	.150/3.81	1.16/29.4		
-423(LF)	2x10	NO		1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5		
-424(LF)		STD					.105/2.67			
-425(LF)		LP					.105/2.67			
-426(LF)		NO					.150/3.81			
-427(LF)		STD					.150/3.81			
-428(LF)	2x10	LP		1.760/44.70	.900/22.86	1.220/30.99	.150/3.81	1.36/34.5		
-429(LF)	2x13	NO		2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1		
-430(LF)		STD					.105/2.67			
-431(LF)		LP					.105/2.67			
65823-432(LF)	2x13	NO	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u"/.38u Au OVER 50u"/1.27u Ni	D

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823
				chr	M. SMYK	1/16/90	scale 5:1	sheet 15 of 21
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-433(LF)	2x13	STD	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u"/.38u Au OVER 50u"/1.27u Ni	D
-434(LF)	2x13	LP		2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1		
-435(LF)	2x17	NO		2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3		
-436(LF)		STD					.105/2.67			
-437(LF)		LP					.105/2.67			
-438(LF)		NO					.150/3.81			
-439(LF)		STD					.150/3.81			
-440(LF)	2x17	LP		2.460/62.48	1.600/40.64	1.920/48.77	.150/3.81	2.06/52.3		
-441(LF)	2x20	NO		2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9		
-442(LF)		STD					.105/2.67			
-443(LF)		LP					.105/2.67			
-444(LF)		NO					.150/3.81			
-445(LF)		STD					.150/3.81			
-446(LF)	2x20	LP		2.760/70.10	1.900/48.26	2.220/56.39	.150/3.81	2.36/59.9		
-447(LF)	2x25	NO		3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6		
-448(LF)		STD					.105/2.67			
-449(LF)		LP					.105/2.67			
-450(LF)		NO					.150/3.81			
-451(LF)		STD					.150/3.81			
-452(LF)	2x25	LP		3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6		
-453(LF)	2x30	NO		3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		
-454(LF)		STD					.105/2.67			
-455(LF)		LP					.105/2.67			
-456(LF)		NO					.150/3.81			
-457(LF)		STD					.150/3.81			
-458(LF)	2x30	LP	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3		
-459(LF)	2x12	NO	RND	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6		
-460(LF)		STD								
-461(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-462(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-463(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-464(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-465(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-466(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-467(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
65823-468(LF)	2x12	NO	SQ	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6	150u"/3.81u Sn	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 16 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-469(LF)	2x12	STD	SQ	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.62	150u"/3.81u TIN	D
-470(LF)		LP	SQ				.105/2.67		150u"/3.81u TIN	
-471(LF)		NO	RND				.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-472(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-473(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-474(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-475(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-476(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-477(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-478(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-479(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-480(LF)		NO	SQ						150u"/3.81u TIN	
-481(LF)		STD							150u"/3.81u TIN	
-482(LF)		LP					.150/3.81		150u"/3.81u TIN	
-483(LF)		NO					.105/2.67		15u"/.38u Au OVER 50u"/1.27u Ni	
-484(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-485(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-486(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-487(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-488(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-489(LF)		NO							15u"/.38u Au OVER 50u"/1.27u Ni	
-490(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-491(LF)		LP					.105/2.67		15u"/.38u Au OVER 50u"/1.27u Ni	
-492(LF)		NO					.675/17.15		15u"/.38u Au OVER 50u"/1.27u Ni	
-493(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-494(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-495(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-496(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-497(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-498(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-499(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-500(LF)		LP							30u"/.76u GXT/GOLD FLASH	
-501(LF)		NO							150u"/3.81u TIN	
-502(LF)		STD							150u"/3.81u TIN	
-503(LF)	2x12	LP	SQ	1.960/49.80	1.100/27.94	1.420/36.07	.675/17.15	1.56/39.62	150u"/3.81u TIN	D
65823-504(LF)	2x15	NO	RND	2.260/57.40	1.400/35.56	1.720/43.69	.105/2.67	1.86/47.24	15u"/.38u Au OVER 50u"/1.27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 17 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-505(LF)	2x15	STD	RND	2.260/57.40	1.400/35.56	1.720/43.69	.105/2.67	1.86/47.2	15u"/.38u Au OVER 50u"/1.27u Ni	D
-506(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-507(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-508(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-509(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-510(LF)		NO							30u"/.76u GXT GOLD FLASH	
-511(LF)		STD							30u"/.76u GXT GOLD FLASH	
-512(LF)		LP	RND						30u"/.76u GXT GOLD FLASH	
-513(LF)		NO	SQ						150u"/3.81u TIN	
-514(LF)		STD	SQ						150u"/3.81u TIN	
-515(LF)		LP	SQ				.105/2.67		150u"/3.81u TIN	
-516(LF)		NO	RND				.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-517(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-518(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-519(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-520(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-521(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-522(LF)		NO							30u"/.76u GXT GOLD FLASH	
-523(LF)		STD							30u"/.76u GXT GOLD FLASH	
-524(LF)		LP	RND						30u"/.76u GXT GOLD FLASH	
-525(LF)		NO	SQ						150u"/3.81u TIN	
-526(LF)		STD							150u"/3.81u TIN	
-527(LF)		LP					.150/3.81		150u"/3.81u TIN	
-528(LF)		NO					.105/2.67		15u"/.38u Au OVER 50u"/1.27u Ni	
-529(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-530(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-531(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-532(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-533(LF)		LP					.105/2.67		30u"/.76u Au OVER 50u"/1.27u Ni	
-534(LF)		NO					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-535(LF)		STD					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-536(LF)		LP					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-537(LF)		NO					.675/17.15		15u"/.38u Au OVER 50u"/1.27u Ni	
-538(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-539(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
65823-540(LF)	2x15	NO	SQ	2.260/57.40	1.400/35.56	1.720/43.69	.675/17.15	1.86/47.2	30u"/.76u Au OVER 50u"/1.27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified			
linear	.XX±.01/.X±.3		
	.XXX±.005/.XX±.13		
	.XXXX±.0020/.XXX±.051		
angles	0°±2°		
dr	J. SHREINER	1/16/90	
engr	M. SMYK	1/16/90	
chr	M. SMYK	1/16/90	
appd	M. SMYK	1/16/90	

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 18 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-541(LF)	2x15	STD	SQ	2.260/57.40	1.400/35.56	1.720/43.69	.675/17.15	1.86/47.2	30u"/.76u Au OVER 50u"/1.27u Ni	D
-542(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-543(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-544(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-545(LF)		LP							30u"/.76u GXT/GOLD FLASH	
-546(LF)		NO							150u"/3.81u TIN	
-547(LF)		STD							150u"/3.81u TIN	
-548(LF)	2x15	LP	SQ	2.260/57.40	1.400/35.56	1.720/43.69	.675/17.15	1.86/47.2	150u"/3.81u TIN	
-549(LF)	2x22	NO	RND	2.960/75.20	2.100/53.34	2.420/61.47	.105/2.67	2.56/65.0	15u"/.38u Au OVER 50u"/1.27u Ni	
-550(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-551(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-552(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-553(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-554(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-555(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-556(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-557(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-558(LF)		NO	SQ						150u"/3.81u TIN	
-559(LF)		STD	SQ						150u"/3.81u TIN	
-560(LF)		LP	SQ				.105/2.67		150u"/3.81u TIN	
-561(LF)		NO	RND				.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni	
-562(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-563(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
-564(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni	
-565(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-566(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
-567(LF)		NO							30u"/.76u GXT/GOLD FLASH	
-568(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-569(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-570(LF)		NO	SQ						150u"/3.81u TIN	
-571(LF)		STD							150u"/3.81u TIN	
-572(LF)		LP					.150/3.81		150u"/3.81u TIN	
-573(LF)		NO					.105/2.67		15u"/.38u Au OVER 50u"/1.27u Ni	
-574(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni	
-575(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni	
65823-576(LF)	2x22	NO	SQ	2.960/75.20	2.100/53.34	2.420/61.47	.105/2.67	2.56/65.0	30u"/.76u Au OVER 50u"/1.27u Ni	D

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code			
ltr	ecn no	dr	date
AF			

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

code: –

size: A

dwg no: 65823

sheet: 19 of 21

	sheet	revision
21	index	sheet

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE	
65823-577(LF)	2x22	STD	SQ	2.960/75.18	2.100/53.34	2.420/61.47	.105/2.67	2.56/65.0	30u"/.76u Au OVER 50u"/1.27u Ni	D	
-578(LF)		LP					.105/2.67		30u"/.76u Au OVER 50u"/1.27u Ni		
-579(LF)		NO					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni		
-580(LF)		STD					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni		
-581(LF)		LP					.150/3.81		15u"/.38u Au OVER 50u"/1.27u Ni		
-582(LF)		NO					.675/17.15		15u"/.38u Au OVER 50u"/1.27u Ni		
-583(LF)		STD							15u"/.38u Au OVER 50u"/1.27u Ni		
-584(LF)		LP							15u"/.38u Au OVER 50u"/1.27u Ni		
-585(LF)		NO							30u"/.76u Au OVER 50u"/1.27u Ni		
-586(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni		
-587(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni		
-588(LF)		NO							30u"/.76u GXT/GOLD FLASH		
-589(LF)		STD							30u"/.76u GXT/GOLD FLASH		
-590(LF)		LP							30u"/.76u GXT/GOLD FLASH		
-591(LF)		NO							150u"/3.81u TIN		
-592(LF)		STD							150u"/3.81u TIN		
-593(LF)	2x22	LP	SQ	2.960/75.18	2.100/53.34	2.420/61.47	.675/17.15	2.56/65.0	150u"/3.81u TIN		
-594(LF)	2x25	66258	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni		
-595(LF)	2x25	66258	RND	3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni		
-596(LF)	2x30	STD	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u"/1.27u Au OVER 50u"/1.27u Ni		
-597(LF)	2x25	NO	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u GXT/GOLD FLASH		
-598(LF)	2x25	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u GXT/GOLD FLASH		
-599(LF)	2x25	LP	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u GXT/GOLD FLASH		
-600(LF)	2x30	NO	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u"/1.27u Au OVER 50u"/1.27u Ni		
-601(LF)	2x30	LP	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u"/1.27u Au OVER 50u"/1.27u Ni		
-606(LF)	2x25	STD	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni		*
-607(LF)	2x25	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni	D	
65823-608(LF)	2x25	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u GXT/GOLD FLASH	E	

* CUSTOMER SPECIAL

ltr	ecn no	dr	date
AF			

sheet	revision
21	index sheet

tolerances unless otherwise specified

linear	.XX±.01/.X±.3
	.XXX±.005/.XX±.13
	.XXXX±.0020/.XXX±.051
angles	0°±2°

dr	J. SHREINER	1/16/90
engr	M. SMYK	1/16/90
chr	M. SMYK	1/16/90
appd	M. SMYK	1/16/90

CUSTOMER COPY

projection

INCH/MM

scale 5:1

www.fciconnect.com

title: HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE

product family: QUICKIE

size: A | dwg no: 65823 | code: – | sheet: 20 of 21

PDM: Rev:AF

STATUS: Released

Printed: Apr 12, 2011

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM F	TERMINAL PLATING NOTE 12	STYLE
65823-609 (LF)	2X5	–	RND	32.00	10.16	18.29	2.67	7.24	50u"/1.27 u Au OVER 50u"/1.27u Ni	A
-610 (LF)	2X5	–	↑	32.00	10.16	18.29	↑	↑	↑	B
-611 (LF)	2X7	–		37.00	15.24	23.37				C
-612 (LF)	2X8	–		39.60	17.18	25.91				D
-613 (LF)	2X10	–		44.70	22.86	30.99				↑
-614 (LF)	2X13	–		52.30	30.48	38.61				
-615 (LF)	2X17	–		62.40	40.64	48.77				
-616 (LF)	2X20	–		70.10	48.26	56.39				
-617 (LF)	2X25	–		82.80	60.96	69.09				↓
-618 (LF)	2X30	–		95.50	76.66	81.79				D
-619 (LF)	2X5	STD		32.00	10.16	18.29				A
-620 (LF)	2X3	↑		32.00	10.16	18.29				B
-621 (LF)	2X7			37.00	15.24	23.37				C
-622 (LF)	2X8			39.60	17.18	25.91				D
-623 (LF)	2X10			44.70	22.86	30.99				↑
-624 (LF)	2X13			52.30	30.48	38.61				
-625 (LF)	2X17			62.40	40.64	48.77				
-626 (LF)	2X20			70.10	48.26	56.39				
-627 (LF)	2X25		↓	82.80	60.96	69.09	↓	↓	↓	↓
-628 (LF)	2X30	STD	RND	95.50	76.66	81.79	2.67	7.24	50u"/1.27 u Au OVER 50u"/1.27u Ni	D

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			
AF					.XXX±.005/.XX±.13		projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE
					.XXXX±.0020/.XXX±.051			
				angles	0°±2°			
				dr	J. SHREINER	1/16/90	INCH/MM	product family QUICKIE / code –
				engr	M. SMYK	1/16/90		size A / dwg no 65823 / sheet 21 of 21
				chr	M. SMYK	1/16/90	scale 5:1	
				appd	M. SMYK	1/16/90		

	sheet	revision
21	index	sheet

PDM: Rev:AF STATUS: Released Printed: Apr 12, 2011