


2		1					
LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
NOTES			C	ECR-06-021030	20/09/06	AM	FWK
			C1	REVISED PER ECO-09-024606	02NOV09	KK	AEG
			C2	ECR-10-022205	01FEB11	KK	HMR

NOTES



1. FOR TECHNICAL DATA REFER TO YOUR
LOCAL TYCO ELECTRONICS SALES OFFICE.
2. ALL DIMENSIONS ARE NOMINAL FOR
REFERENCE ONLY UNLESS OTHERWISE STATED.
3. RATING
3.1 RATING : 3 AMPS
3.2 OPERATING TEMPERATURE : - 40°C TO +105°C
4. ELECTRICAL SPECIFICATION
4.1 INSULATION RESISTANCE
5000 MΩ MINIMUM
4.2 WITHSTAND VOLTAGE
500V AC
5. MATERIALS
5.1 CONTACT - BRASS, POST PLATE
Au 0.25µm (10µinch) IN CONTACT AREA
Sn 2 TO 3µm (80 TO 120µinch) IN SOLDER AREA.
5.2 HOUSING - BLACK NYLON 6T UL 94V-0

6. NUMBER OF CONTACT POSITIONS TO BE INDICATED IN
AREA SHOWN.
XX = NUMBER OF POSITONS.
7. TYCO LOGO TO BE PRESENT IN AREA INDICATED.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

8	OBSOLETE	78.74	88.93	64	6-1634689-4
	OBSOLETE	73.66	83.85	60	6-1634689-0
		60.96	71.15	50	5-1634689-0
		48.26	58.45	40	4-1634689-0
		40.64	50.83	34	3-1634689-4
		30.48	40.67	26	2-1634689-6
		22.86	33.05	20	2-1634689-0
		17.78	27.97	16	1-1634689-6
		15.24	25.43	14	1-1634689-4
		10.16	20.35	10	1-1634689-0
	A	B	No Of Contacts	TE Part No	
	Dimensions				



Recommended P.C.Board
Hole Layout



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.MOREY	14JAN04	 TE Connectivity		
		CHK J.SANDWELL	14JAN04			
		APVD F.WHEELER-KING	14JAN04	NAME		
		PRODUCT SPEC		BOX HEADER RIGHT ANGLED		
		APPLICATION SPEC				
		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
				A3	00779	C-1634689
		CUSTOMER DRAWING		SCALE	NTS	SHEET
						1 OF 1
						REV
						C2