

Single Phase Bridge Rectifiers




CP80 Series



Features:

- High surge current capability
- PCB mounted / screw fixing
- Surge overload rating: 200 A peak
- Low forward voltage drop and reverse leakage
- Small size, simple installation
- Reliable low cost construction utilizing moulded plastic technique



Dimensions : Inches (Millimetres)

Mechanical Data:

Mounting Position	: Any
Terminals	: Leads solderable per MIL-STD- 202, Method 208
Mounting	: Through hole for a number 6 screw

Maximum Ratings and Electrical Characteristics

At 25°C ambient temperature unless otherwise noted; resistive or inductive load at 60 Hz

Parameter	CP802	CP806	Unit
Maximum Recurrent Peak Reverse Voltage	200	600	V
Maximum Bridge Input Voltage RMS	140	420	
Maximum Average Rectified Output at See Figure 2	T _C = 50°C T _A = 40°C	8 3	A
Peak One Cycle Surge Overload Current	200		
Maximum Forward Voltage Drop Per Element at 4 A dc and 25°C See Figure 3	1.1		V
Maximum Reverse Leakage at Rated DC Blocking Voltage Per Element at 25°C See Figure 4	10 1		μA mA
I ² t Rating for Fusing (t<8.3 ms)	166		A ² s
Typical Junction Capacitance Per Leg (Note 4) C _J	200		pF
Typical Thermal Resistance Per Leg (Note 3) R _{θJA} Typical Thermal Resistance Per Leg (Note 2) R _{θJL}	21 6		°C / W
Operating Temperature Range	-55 to +125		°C
Storage Temperature Range	-55 to +150		

- Notes :**
1. Bolt down on to a heat-sink with silicon thermal compound between bridge and mounting surface for maximum heat transfer with a number 6 screw
 2. Units mounted on a 8.6 × 8.6 × 24 inches thick (22 × 22 × 0.6 cm) aluminium plate heatsink
 3. Units mounted on PCB at 0.375 inches (9.5 mm) lead length with 0.5 × 0.5 inches (12 × 12 mm) copper pads
 4. Measured at 1 MHz and applied reverse voltage

Single Phase Bridge Rectifiers



CP80 Series

Rating and Characteristic Curves




Figure 2 - Derating Curve for Output Rectified Current




Figure 3 - Typical Forward Characteristics (25°C)





Figure 4 - Reverse Characteristics



Specification Table

V_{RRM} (V)	Maximum Input Voltage (V ac)	I_O (A)	T_A (°C)	I_{FSM} (A)	Body		Lead			Part Number
					Height	Width / Depth	Length	Spacing	Diameter	
200	600	8	50	200	7.6	19.1	19.1	12.7	1.3 Typical	CP802
600	420									CP806

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.