





mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE			
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title RIBCAGE III SMT VERT. HEADER ASS'Y			
AA	M08-0245	MHT	8/27/08		angles		linear		.XX±.01/0.3				
AB	M09-0058	MHT	4/04/09						.XXX±.005/0.13		INCH/MM ↔		
AC	M09-0087	MHT	06/10/09		±2'				.XXXX±.0020/0.051				
AD	N10-0174	YO	6/17/10		dr	M. CORNMAN		6/07/95		scale 3:1 			
AE	ELX-N-004143	YO	06/20/11		enrg	D. WHITING		6/07/95					
AF	ELX-N-004665	YO	07/27/11		chr	D. WHITING		6/07/95		dwg no 95781			
AG	ELX-N-009746	YO	1/20/12		appd	D. WHITING		6/07/95					
sheet		revision		AG	AG	AG	AG	AG	AG	type			
index		sheet		1	2	3	4	5	6	7	8		

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28






SECTION X-X
ROTATED 90° CW









SECTION Y-Y

mat'l. code —				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ⌀	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		INCH/MM scale 3:1	title RIBCAGE III SMT VERT. HEADER ASS'Y		
AG					angles	linear				
					±2°					
					dr	M. CORNMAN	6/07/95	dwg no		sheet 2 of 8
					enrg	D. WHITING	6/07/95	95781		size A3
					chr	D. WHITING	6/07/95			
					appd	D. WHITING	6/07/95	type Product Customer Drawing		
sheet index	revision sheet									



LOCATOR/HOLDDOWN VARIATIONS





$\phi .0520$ [1.321]
 $\phi .040$ [1.02]
 $\phi .004/0.10$ (M) A (S) B (S) (ALL PEG CONFIGURATIONS)



$.0470^{+.0005}_{-.0010}$ [1.194 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.0470^{+.0005}_{-.0010}$ [1.194 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]



$.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]




$.0065 \pm .001$ [0.165 ± 0.025]
 $\phi .0400$ [1.02]
 $.052 \pm .001$ [1.32 ± 0.025]
R.002 [0.05] MAX

$.008$ [0.20] X 45°
 $.0520^{+.0005}_{-.0010}$ [1.321 $^{+0.013}_{-0.025}$]
 $.0030$ [0.076]
 $.040^{+.001}_{-.002}$ [1.02 $^{+0.03}_{-0.05}$]
 $.008 \pm .003$ [0.20 ± 0.08]
 $\phi .034 \pm .001$ [0.86 ± 0.03]


mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
AG					angles	linear	RIBCAGE III SMT		
					$\pm 2^\circ$		VERT. HEADER ASS'Y		
					dr	M. CORNMAN	6/07/95	dwg no	sheet 3 of 8
					enr	D. WHITING	6/07/95	95781	A3
					chr	D. WHITING	6/07/95	type Product Customer Drawing	
					appd	D. WHITING	6/07/95		
sheet index	revision sheet								

RECOMMENDED PCB MOUNTING PAD PATTERN


STYLE 1




STYLE 5




STYLE 4




STYLE 2




STYLE 7



STYLE 6



STYLE 3



mat'l. code —					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE						
ltr ecn no dr date					tolerances unless otherwise specified							title					
AG					angles		linear		.XX±.01/0.3 .XXX±.005/0.13 ±2' .XXXX±.0020/0.051		INCH/MM		RIBCAGE III SMT VERT. HEADER ASS'Y				
											scale 3:1						
					dr		M. CORNMAN		6/07/95				dwg no		sheet 4 of 8		size
					enrg		D. WHITING		6/07/95				95781		A3		
					chr		D. WHITING		6/07/95								
					appd		D. WHITING		6/07/95								
sheet index		revision sheet															

PRODUCT NUMBER NOTE 11,4C	QTY. REEL	TAPE WIDTH PITCH MM	CONNECTOR ORIENTATION IN TAPE POCKET
72428-120TR	500	44/12	VIEW 1
73546-105TR		24/12	
73546-110TR		32/12	
73546-115TR		44/12	
73546-120TR		44/12	
73546-125TR		56/12	
73546-130TR		56/12	
73546-135TR		72/12	
73546-140TR		72/12	
73546-145TR		72/12	
73546-150TR		88/12	
73547-105TR		24/12	
73547-110TR		32/12	
73547-115TR		44/12	
73547-120TR		44/12	
73547-125TR		56/12	
73547-130TR		56/12	
73547-135TR		72/12	
73547-140TR		72/12	
73547-145TR		72/12	
73547-150TR	500	88/12	
84700-105TR	400	24/12	
84700-135TR	500	72/12	
87409-105TR		24/12	
87409-110TR		24/12	
87409-115TR		44/12	
87409-120TR		44/12	
87409-125TR		56/12	
87409-130TR	500	56/12	VIEW 1



TABLE C

OBSOLETE

OBSOLETE

OBSOLETE

REFERENCE ONLY :

TAPE WIDTH 32mm AND ABOVE HAS BOTH FEED TRACKS,
BELOW 32mm HAS TOP FEED TRACK ONLY.

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406 ISO 1101		RIBCAGE
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
AG					linear	INCH/MM	RIBCAGE III SMT
					±.01/0.3		VERT. HEADER ASS'Y
					.xxx±.005/0.13		dwg no
					±2'	scale 3:1	sheet 6 of 8
					dr		size
					M. CORNMAN	6/07/95	A3
					enr	D. WHITING	95781
					chr	D. WHITING	Product Customer Drawing
					appd	D. WHITING	
sheet	revision						
index	sheet						

Copyright FCI

FCIconnect.com

PRODUCT NUMBER NOTE 11,4C	QTY. REEL	TAPE WIDTH PITCH MM	CONNECTOR ORIENTATION IN TAPE POCKET
87409-135TR	500	72/12	VIEW 1
87409-140TR	↑	72/12	↑
87409-145TR		72/12	
87409-150TR		88/12	
87849-105TR		24/12	
87849-110TR		24/12	
87849-115TR		44/12	
87849-120TR		44/12	
87849-125TR		56/12	
87849-130TR		56/12	
87849-135TR		72/12	
87849-140TR		72/12	
87849-145TR		72/12	
87849-150TR		88/12	
88566-110TR		24/12	
88566-115TR	↓	44/12	
88566-130TR	500	56/12	
90098-105TR	400	24/12	
90098-110TR	400	32/12	
90098-115TR	500	44/12	
90098-120TR	500	44/12	
90098-125TR	400	56/12	
90098-130TR	500	56/12	
90098-135TR	↑	72/12	
90098-140TR	↓	72/12	
90098-145TR		72/12	
90098-150TR		88/12	
90863-110	↓	24/12	↓
90863-115	500	44/12	VIEW 1

TABLE C

mat'l. code				surface		tolerance		projection		product family	
-				ISO 1302 ✓		ISO 406 ISO 1101				RIBCAGE	
ltr	ecn	no	dr	date		tolerances unless otherwise specified					
AG						angles	linear	.XX±.01/0.3		INCH/MM	
								.XXX±.005/0.13			
						±2"		.XXXX±.0020/0.051		scale 3:1	
						dr	M. CORNMAN	6/07/95		FCI	
						enrg	D. WHITING	6/07/95		dwg no	
						chr	D. WHITING	6/07/95		sheet 7 of 8	
						appd	D. WHITING	6/07/95		size	
sheet		revision								type	
index		sheet								Product Customer Drawing	

PDS: Rev :AG

STATUS:Released

Printed: Feb 17, 2012

