


# High-Gain IGBT w/ Diode


## IXGH24N60C4D1

### High-Speed PT Trench IGBT



$V_{CES} = 600V$   
 $I_{C110} = 24A$   
 $V_{CE(sat)} \leq 2.70V$   
 $t_{fi(typ)} = 68ns$

TO-247 AD



G = Gate      C = Collector  
 E = Emitter    Tab = Collector

| Symbol                        | Test Conditions                                                                      | Maximum Ratings                   |            |
|-------------------------------|--------------------------------------------------------------------------------------|-----------------------------------|------------|
| $V_{CES}$                     | $T_J = 25^\circ C$ to $150^\circ C$                                                  | 600                               | V          |
| $V_{CGR}$                     | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GE} = 1M\Omega$                            | 600                               | V          |
| $V_{GES}$                     | Continuous                                                                           | $\pm 20$                          | V          |
| $V_{GEM}$                     | Transient                                                                            | $\pm 30$                          | V          |
| $I_{C25}$                     | $T_C = 25^\circ C$                                                                   | 56                                | A          |
| $I_{C110}$                    | $T_C = 110^\circ C$                                                                  | 24                                | A          |
| $I_{F110}$                    | $T_C = 110^\circ C$                                                                  | 18                                | A          |
| $I_{CM}$                      | $T_C = 25^\circ C$ , 1ms                                                             | 130                               | A          |
| <b>SSOA</b><br><b>(RBSOA)</b> | $V_{GE} = 15V$ , $T_{VJ} = 125^\circ C$ , $R_G = 10\Omega$<br>Clamped Inductive Load | $I_{CM} = 48$<br>@ $\leq V_{CES}$ | A          |
| $P_C$                         | $T_C = 25^\circ C$                                                                   | 190                               | W          |
| $T_J$                         |                                                                                      | -55 ... +150                      | $^\circ C$ |
| $T_{JM}$                      |                                                                                      | 150                               | $^\circ C$ |
| $T_{stg}$                     |                                                                                      | -55 ... +150                      | $^\circ C$ |
| $T_L$                         | Maximum Lead Temperature for Soldering                                               | 300                               | $^\circ C$ |
| $T_{SOLD}$                    | 1.6 mm (0.062in.) from Case for 10s                                                  | 260                               | $^\circ C$ |
| $M_d$                         | Mounting Torque                                                                      | 1.13/10                           | Nm/lb.in.  |
| Weight                        |                                                                                      | 6                                 | g          |

### Features

- Optimized for Low Switching Losses
- Square RBSOA
- Anti-Parallel Ultra Fast Diode
- International Standard Package

### Advantages

- High Power Density
- Low Gate Drive Requirement


### Applications

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

| Symbol        | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |                      |
|---------------|-----------------------------------------------------------------------|-----------------------|------|----------------------|
|               |                                                                       | Min.                  | Typ. | Max.                 |
| $V_{GE(th)}$  | $I_C = 250\mu A$ , $V_{CE} = V_{GE}$                                  | 4.0                   |      | 6.5 V                |
| $I_{CES}$     | $V_{CE} = V_{CES}$ , $V_{GE} = 0V$<br>$T_J = 125^\circ C$             |                       |      | 10 $\mu A$<br>1.5 mA |
| $I_{GES}$     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                    |                       |      | $\pm 100$ nA         |
| $V_{CE(sat)}$ | $I_C = I_{C110}$ , $V_{GE} = 15V$ , Note 1<br>$T_J = 125^\circ C$     | 2.28<br>1.95          |      | 2.70 V<br>V          |

| Symbol Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified) |                                                                                                                                           | Characteristic Values |      |                         |
|----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|-------------------------|
|                                                                                  |                                                                                                                                           | Min.                  | Typ. | Max.                    |
| $g_{fs}$                                                                         | $I_C = I_{C110}, V_{CE} = 10\text{V}$ , Note 1                                                                                            | 10                    | 17   | S                       |
| $C_{ies}$                                                                        | $V_{CE} = 25\text{V}$ , $V_{GE} = 0\text{V}$ , $f = 1\text{MHz}$                                                                          |                       | 875  | pF                      |
| $C_{oes}$                                                                        |                                                                                                                                           |                       | 86   | pF                      |
| $C_{res}$                                                                        |                                                                                                                                           |                       | 28   | pF                      |
| $Q_g$                                                                            | $I_C = I_{C110}, V_{GE} = 15\text{V}$ , $V_{CE} = 0.5 \cdot V_{CES}$                                                                      |                       | 64   | nC                      |
| $Q_{ge}$                                                                         |                                                                                                                                           |                       | 7    | nC                      |
| $Q_{gc}$                                                                         |                                                                                                                                           |                       | 28   | nC                      |
| $t_{d(on)}$                                                                      | Inductive Load, $T_J = 25^\circ\text{C}$<br>$I_C = I_{C110}, V_{GE} = 15\text{V}$<br>$V_{CE} = 360\text{V}$ , $R_G = 10\Omega$<br>Note 2  |                       | 21   | ns                      |
| $t_{ri}$                                                                         |                                                                                                                                           |                       | 33   | ns                      |
| $E_{on}$                                                                         |                                                                                                                                           |                       | 0.40 | mJ                      |
| $t_{d(off)}$                                                                     |                                                                                                                                           |                       | 143  | ns                      |
| $t_{fi}$                                                                         |                                                                                                                                           |                       | 68   | ns                      |
| $E_{off}$                                                                        |                                                                                                                                           |                       | 0.30 | 0.55 mJ                 |
| $t_{d(on)}$                                                                      | Inductive Load, $T_J = 125^\circ\text{C}$<br>$I_C = I_{C110}, V_{GE} = 15\text{V}$<br>$V_{CE} = 360\text{V}$ , $R_G = 10\Omega$<br>Note 2 |                       | 20   | ns                      |
| $t_{ri}$                                                                         |                                                                                                                                           |                       | 32   | ns                      |
| $E_{on}$                                                                         |                                                                                                                                           |                       | 0.63 | mJ                      |
| $t_{d(off)}$                                                                     |                                                                                                                                           |                       | 130  | ns                      |
| $t_{fi}$                                                                         |                                                                                                                                           |                       | 118  | ns                      |
| $E_{off}$                                                                        |                                                                                                                                           |                       | 0.50 | mJ                      |
| $R_{thJC}$                                                                       |                                                                                                                                           |                       |      | 0.65 $^\circ\text{C/W}$ |
| $R_{thCS}$                                                                       |                                                                                                                                           |                       | 0.21 | $^\circ\text{C/W}$      |

## TO-247 (IXGH) Outline



Terminals: 1 - Gate 2 - Collector  
3 - Emitter

| Dim.           | Millimeter |       | Inches |       |
|----------------|------------|-------|--------|-------|
|                | Min.       | Max.  | Min.   | Max.  |
| A              | 4.7        | 5.3   | .185   | .209  |
| A <sub>1</sub> | 2.2        | 2.54  | .087   | .102  |
| A <sub>2</sub> | 2.2        | 2.6   | .059   | .098  |
| b              | 1.0        | 1.4   | .040   | .055  |
| b <sub>1</sub> | 1.65       | 2.13  | .065   | .084  |
| b <sub>2</sub> | 2.87       | 3.12  | .113   | .123  |
| C              | .4         | .8    | .016   | .031  |
| D              | 20.80      | 21.46 | .819   | .845  |
| E              | 15.75      | 16.26 | .610   | .640  |
| e              | 5.20       | 5.72  | 0.205  | 0.225 |
| L              | 19.81      | 20.32 | .780   | .800  |
| L1             |            | 4.50  |        | .177  |
| ØP             | 3.55       | 3.65  | .140   | .144  |
| Q              | 5.89       | 6.40  | 0.232  | 0.252 |
| R              | 4.32       | 5.49  | .170   | .216  |
| S              | 6.15       | BSC   | .242   | BSC   |

## Reverse Diode (FRED)







| Symbol Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified) |                                                                                                              | Characteristic Values |      |                        |
|----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-----------------------|------|------------------------|
|                                                                                  |                                                                                                              | Min.                  | Typ. | Max.                   |
| $V_F$                                                                            | $I_F = 15\text{A}$ , $V_{GE} = 0\text{V}$ , Note 1                                                           |                       |      | 2.7 V                  |
|                                                                                  | $T_J = 150^\circ\text{C}$                                                                                    |                       | 1.6  | V                      |
| $I_{RM}$                                                                         | $I_F = 15\text{A}$ , $V_{GE} = 0\text{V}$ , $-di_F/dt = 100\text{A}/\mu\text{s}$ , $T_J = 100^\circ\text{C}$ |                       |      | 2.6 A                  |
| $t_{rr}$                                                                         | $V_R = 100\text{V}$ , $T_J = 100^\circ\text{C}$                                                              |                       | 100  | ns                     |
|                                                                                  | $I_F = 1\text{A}$ , $V_{GE} = 0\text{V}$ , $-di_F/dt = 100\text{A}/\mu\text{s}$ , $V_R = 30\text{V}$         |                       | 25   | ns                     |
| $R_{thJC}$                                                                       |                                                                                                              |                       |      | 1.6 $^\circ\text{C/W}$ |






## Notes:

1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .
2. Switching times & energy losses may increase for higher  $V_{CE}(\text{clamp})$ ,  $T_J$  or  $R_G$ .


IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |              |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|--------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338 B2 |
|                                                                                  | 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |              |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |              |


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4. Dependence of  $V_{CE(sat)}$  on Junction Temperature**

**Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage**

**Fig. 6. Input Admittance**


**Fig. 7. Transconductance**

**Fig. 8. Gate Charge**

**Fig. 9. Capacitance**

**Fig. 10. Reverse-Bias Safe Operating Area**

**Fig. 11. Maximum Transient Thermal Impedance**



**Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance**




**Fig. 13. Inductive Switching Energy Loss vs. Collector Current**




**Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature**




**Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance**




**Fig. 16. Inductive Turn-off Switching Times vs. Collector Current**




**Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature**




**Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance**



**Fig. 19. Inductive Turn-on Switching Times vs. Collector Current**



**Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature**






Fig. 21. Forward Current  $I_F$  vs.  $V_F$




Fig. 22. Reverse Recovery Charge  $Q_r$  vs.  $-di_F/dt$




Fig. 23. Peak Reverse Current  $I_{RM}$  vs.  $-di_F/dt$




Fig. 24. Dynamic Parameters  $Q_r, I_{RM}$  vs.  $T_{WJ}$




Fig. 25. Recovery Time  $t_r$  vs.  $-di_F/dt$




Fig. 26. Peak Forward Voltage  $V_{FR}, t_r$  vs.  $-di_F/dt$




Fig. 27. Transient Thermal Resistance Junction to Case

Constants for  $Z_{\theta JC}$  calculation:

| i | $R_{\theta i}$ (K/W) | $t_i$ (s) |
|---|----------------------|-----------|
| 1 | 0.908                | 0.0052    |
| 2 | 0.35                 | 0.0003    |
| 3 | 0.342                | 0.017     |

NOTE: Fig. 18 to Fig. 22 show typical values