



DESCRIPTION: F JACK SIDE EDGE, PCB MOUNT

MODEL NUMBER: 25-7630

APPLICATION: PCB MOUNT

CRIMP TOOL: N/A

IMPEDANCE: 75 OHM

FREQUENCY RANGE: 0-1 GHz

RETURN LOSS: 34dB (0-250MHz)

23dB (250-750MHz)

19dB (750-1GHz)



MATERIAL: BODY BRASS SN PLATED

INSULATOR PP

CONTACT PHOS. BRNZ SN PLATED

RoHS COMPLIANCE: YES

TECHNICAL DETAIL: REFET TO EMERSON DOCUMENT 25-0000



 This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	3RD ANGLE PROJECTION		AIM-Cambridge	
	RoHS 2002/95/EC		Title: (CPF61SE) F Jack side edge, PCB Mount	
	.XX ±.51 .XXX ±.127 ANGLES ±2°		Model No. 25-7630	
	Size A	DO NOT SCALE DRAWING	Date: 10/16/2013	Sheet 1 of 1