

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

1

2

3

4

5

6

7

8

9

10

11

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECO-16-004940	05AUG2016	NK	MZ
H		REVISED PER ECO-17-009310	28JUN2017	RS	MZ

1

0.76um[.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, 3.81um[.000150] MIN TIN-LEAD IN LOCALIZED TIN PLATE AREA, BOTH OVER 1.27um[.000050] MIN NICKEL.

2

POSITIONS 1 THRU 11 AND 17 THRU 25 ARE LOADED WITH GROUND TYPE CONTACTS, POSITIONS 12 THRU 16 ARE LOADED WITH POWER TYPE CONTACTS.

3

POSITIONS 1 THRU 6 AND 17 THRU 25 ARE LOADED WITH GROUND TYPE CONTACTS, POSITIONS 7 THRU 16 ARE LOADED WITH POWER TYPE CONTACTS.

4

2, 6, 10 TO 16, 20, 21 & 24 ARE LOADED WITH GROUND TYPE CONTACTS.

5

5 TO 9, 11, 13, 14, 15, 20 & 25 ARE LOADED WITH POWER TYPE CONTACTS, POSITION 10 IS LOADED WITH GROUND TYPE CONTACTS.

6

1 THRU 13, 15 THRU 17, 20, 21, 23 & 25 ARE LOADED WITH POWER TYPE CONTACTS, POSITIONS 14 & 24 ARE LOADED WITH GROUND TYPE CONTACTS.

7

2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.

8

CONTACTS: PHOSPHOR BRONZE, HOUSING; POLYSULFONE, BLACK.

9

0.76um[.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, 3.81um[.000150] MIN TIN IN LOCALIZED TIN PLATE AREA, BOTH OVER 1.27um[.000050] MIN NICKEL.

10

2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL.

11

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

11

OBSOLETE

9	6	22	1-796590-6
9	5	12	1-796590-5
9	4	12	1-796590-4
10	2	25	1-796590-3
9	FULL	25	1-796590-2
10	FULL	25	1-796590-1
9	3	25	1-796590-0
OBSOLETE	2	25	796590-9
OBSOLETE	6	22	796590-8
11 OBSOLETE	5	12	796590-7
1	4	12	796590-6
1	2	25	796590-5
1	FULL	25	796590-4
11 OBSOLETE	7	FULL	25-796590-3
1	3	25	796590-2
OBSOLETE	1	25	796590-1
FINISH		LOCATION	QTY
CONTACT			PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± -
± -
± -
± -
± -

0.25 [010]

ANGLES

± -

MATERIAL

-

FINISH

-

DWN
S.WELDON
26SEP00

CHK
K.DOWHOWER
26SEP00

APVD
K.DOWHOWER
26SEP00

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

SIZE
A1

CAGE CODE
00779

DRAWING NO
796590

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
2

REV
H

TE Connectivity

HEADER ASSEMBLY, 25 POSN,
ACTION PIN, METRIMATE

RESTRICTED TO

4805 (1/15)

