


By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of the Huck Manufacturing Company.

REV	DESCRIPTION	DATE
A	RELEASE	



SECTION A-A

MATERIAL:	-	SPEC: -	TOLERANCES UNLESS OTHERWISE SPECIFIED		HUCK MANUFACTURING COMPANY I.E.D. 85 GRAND STREET, P.O. BOX 2270 KINGSTON, NEW YORK 12401		
HARDNESS:	-						
HEAT TREAT:	-	SPEC: -	.XX, .XXX ±		NOSE ASSEMBLY -14 LGPL PULL-IN		
SURF. TREAT:	-	SPEC: -	INT. COR. RADII				
SURFACE FINISH NOT TO EXCEED		Ra	BREAK EDGES		DET: T.L.	CK: -	DATE:08-27-91
IDENTIFICATION PER SPEC 42-311: ★ CHEMICAL ETCH			ANGLES ±		FOC.	B	99-1816
SURFACES TO BE ☉, //, ⊕, ⊥, & ▱ WITHIN			T.I.R.	FINAL ASSY: -	FAC.		