

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	00		A	REVISED PER ECO 06-016786	1/22/2007	DW	KW
			B	REVISED PER ECO-11-025304	19DEC2011	TITAN	MARTIN
			C	REVISED PER ECO-12-006151	29MAR2012	TITAN	MARTIN

- 1

PHOSPHOR BRONZE.
- 2

BRASS.
- 3



PTFE.
- 4

TIN PLATE 2.54 μ m [.000100]
MINIMUM THICK.
- 5

NICKEL PLATE 2.54 μ m [.000100]
MINIMUM THICK.
- 6

CONNECTOR WILL ACCEPT CENTER
CONDUCTOR DIAMETER RANGE OF
0.51[.020] – 1.19[.047].
- 7

BRIGHT GOLD PLATE,
0.13 μ m THICK (.000005) MIN THK.



OBSOLETE	7	3.48 [.137] MAX	25.40 [1.000]	5415302=4
OBSOLETE	6	3.48 [.137] MAX	25.40 [1.000]	5415302=3
OBSOLETE	6	3.94±0.51[.155±.020]	31.75 [1.250]	5415302=2
OBSOLETE	6	3.94±0.51[.155±.020]	25.40 [1.000]	5415302=1
FINISH (SHELL, BARREL)		L	A	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA - DOCK5 01FEB2005 CHK J. HAVENER 01FEB2005 APVD K. WEIDNER 01FEB2005	TE Connectivity	
DIMENSIONS: mm [INCHES]		PRODUCT SPEC 108-1755	NAME JACK, PCB, RIGHT ANGLE, F SERIES	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.20[.008] 4 PLC ± - ANGLES ± 1°		—	A2 00779 C=5415302	
MATERIAL		WEIGHT —	RESTRICTED TO —	
1 2 3		4 5 7	CUSTOMER DRAWING	
SCALE 5:1			SHEET 1 OF 1	
			REV C	