

DM74LS564 Octal D-Type Flip-Flop with TRI-STATE® Outputs

General Description


The 'LS564 is a high speed low power octal flip-flop with a buffered common Clock (CP) and a buffered common Output Enable ($\overline{OE}$). The information presented to the D inputs is stored in the flip-flops on the LOW-to-HIGH Clock (CP) transition

This device is functionally identical to the 'LS574, but has inverted outputs. For complete discussions of operations, truth tables, AC and DC electrical specifications, refer to the 'LS374 data sheet.

Features

- Inputs and outputs on opposite sides of package allowing easy interface with microprocessors
- Useful as input or output port for microprocessors
- Functionally identical to 'LS574
- Input clamp diodes limit high speed termination effects
- Fully TTL and CMOS compatible


Connection Diagram



TL/F/10191-1

Order Number DM74LS564WM or DM74LS564N
See NS Package Number M20B or N20A

Logic Symbol



Pin Names	Description
D0-D7	Data Inputs
CP	Clock Pulse Input (Active Rising Edge)
$\overline{OE}$	TRI-STATE® Output Enable Input (Active LOW)
$\overline{O0}-\overline{O7}$	TRI-STATE Outputs

Absolute Maximum Ratings (Note)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

Supply Voltage	7V
Input Voltage	7V
Operating Free Air Temperature Range	0°C to +70°C
DM74LS	
Storage Temperature Range	−65°C to +150°C

Note: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Recommended Operating Conditions

Symbol	Parameter	DM74LS564			Units
		Min	Nom	Max	
V _{CC}	Supply Voltage	4.75	5	5.25	V
V _{IH}	High Level Input Voltage	2			V
V _{IL}	Low Level Input Voltage			0.8	V
I _{OH}	High Level Output Current			−2.6	mA
I _{OL}	Low Level Output Current			24	mA
T _A	Free Air Operating Temperature	0		70	°C

Electrical Characteristics over recommended operating free air temperature range (unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ (Note 1)	Max	Units
V _I	Input Clamp Voltage	V _{CC} = Min, I _I = −18 mA			−1.5	V
V _{OH}	High Level Output Voltage	V _{CC} = Min, I _{OH} = Max, V _{IL} = Max	2.4	3.4		V
V _{OL}	Low Level Output Voltage	V _{CC} = Min, I _{OL} = Max, V _{IH} = Min		0.35	0.5	V
		I _{OL} = 12 mA, V _{CC} = Min		0.25	0.4	
I _I	Input Current @ Max Input Voltage	V _{CC} = Max, V _I = 7V			0.1	mA
I _{IH}	High Level Input Current	V _{CC} = Max, V _I = 2.7V			20	μA
I _{IL}	Low Level Input Current	V _{CC} = Max, V _I = 0.4V			−0.4	mA
I _{OS}	Short Circuit Output Current	V _{CC} = Max (Note 2)	−30		−130	mA
I _{CC}	Supply Current	V _{CC} = Max			60	mA
I _{OZH}	TRI-STATE Output OFF Current HIGH	V _{CC} = Max, V _O = 2.4V			20	μA
I _{OZL}	TRI-STATE Output OFF Current LOW	V _{CC} = Max, V _O = 0.4V			−20	μA

Note 1: All typicals are at V_{CC} = 5V, T_A = 25°C.


Note 2: Not more than one output should be shorted at a time, and the duration should not exceed one second.

Switching Characteristics

$V_{CC} = +5.0V$, $T_A = +25^{\circ}C$


Symbol	Parameter	Min	Max	Units
t_{PLH}	Propagation Delay CP to $\bar{O}n$		28	ns
t_{PHL}	Propagation Delay CP to $\bar{O}n$		28	ns
t_{PZH}	Enable Time $\bar{O}E$ to $\bar{O}n$		28	ns
t_{PZL}	Enable Time $\bar{O}E$ to $\bar{O}n$		28	ns
t_{PHZ}	Enable Time $\bar{O}E$ to $\bar{O}n$		20	ns
t_{PLZ}	Enable Time $\bar{O}E$ to $\bar{O}n$		25	ns
t_s	Setup Time Dn to CP	20		ns
t_h	Hold Time Dn to CP	5		ns
$t_w (H)$ $t_w (L)$	Pulse Width (HIGH/LOW) CP	20 15		ns

Physical Dimensions inches (millimeters)



20-Lead Wide Small Outline Molded Package (M)
Order Number DM74LS564WM
NS Package Number M20B

Physical Dimensions inches (millimeters) (Continued)



N20A (REV G)

20-Lead Molded Dual-In-Line Package (N)
Order Number DM74LS564N
NS Package Number N20A

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation
1111 West Bardin Road
Arlington, TX 76017
Tel: (800) 272-9959
Fax: (800) 737-7018

National Semiconductor Europe
Fax: (+49) 0-180-530 85 86
Email: cnjwge@tevm2.nsc.com
Deutsch Tel: (+49) 0-180-530 85 85
English Tel: (+49) 0-180-532 78 32
Français Tel: (+49) 0-180-532 93 58
Italiano Tel: (+49) 0-180-534 16 80

National Semiconductor Hong Kong Ltd.
19th Floor, Straight Block,
Ocean Centre, 5 Canton Rd.
Tsimshatsui, Kowloon
Hong Kong
Tel: (852) 2737-1600
Fax: (852) 2736-9960

National Semiconductor Japan Ltd.
Tel: 81-043-299-2309
Fax: 81-043-299-2408

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.