




RING TONGUE (R type) Vinyl-insulated (straight)




T : Material thickness

File No.: UL E42024 SP LR20812 670021

Applicable Wire AWG#(mm ²)	Stud size		Part No.		Standard	Dimensions mm (in.)							Color	Tool No.	Qty/box
	American	Metric	JST	JIS		ø d2	ø D	B	L	F	ℓ	T			
26 to 22 (0.2 to 0.5)	1-2	2	V0.5-2		UL SP	2.2 (.087)	1.9 (.075)	5.2 (.205)	16.4 (.646)	5.8 (.228)	8.0 (.315)	0.5 (.020)	Yellow	YNT-2622 YA-1 YA-2	1,000
	3-4	3	V0.5-3		UL SP	3.2 (.126)		5.2 (.205)	16.4 (.646)	5.8 (.228)					
	5-6	3.5	V0.5-3.7		UL SP	3.7 (.146)		6.6 (.260)	19.0 (.748)	7.7 (.303)					
	8	4	V0.5-4		UL SP	4.3 (.169)		6.6 (.260)	19.0 (.748)	7.7 (.303)					
	10	5	V0.5-5		UL SP	5.3 (.209)		8.0 (.315)	19.0 (.748)	7.0 (.276)					
22 to 16 *(0.25 to 1.65)	1-2	2	V1.25-2		UL SP	2.2 (.087)	3.2 (.126)	5.5 (.217)	15.7 (.618)	4.0 (.157)	9.0 (.354)	0.8 (.031)	Red	YNT-2216 YA-1 YA-2 YA-4	1,000
	3-4	3	V1.25-3	RAV1.25-3	UL SP	3.2 (.126)		5.5 (.217)	15.7 (.618)	4.0 (.157)					
	5-6	3.5	V1.25-3.7		UL SP	3.7 (.146)		5.5 (.217)	15.7 (.618)	4.0 (.157)					
	3-4	3	V1.25-MS3		UL SP	3.2 (.126)		5.5 (.217)	17.4 (.685)	5.6 (.220)					
	5-6	3.5	V1.25-M3	RAV1.25-3.5	UL SP	3.7 (.146)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	3-4	3	V1.25-L3		UL SP	3.2 (.126)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	8	4	V1.25-M4		UL SP	4.3 (.169)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	V1.25-4	RAV1.25-4	UL SP	4.3 (.169)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	10	5	V1.25-5	RAV1.25-5	UL SP	5.3 (.209)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	1/4	6	V1.25-6		UL SP	6.4 (.252)		11.6 (.457)	25.9 (1.020)	11.1 (.437)					
16 to 14 (1.04 to 2.63)	5/16	8	V1.25-8		UL SP	8.4 (.331)	3.9 (.154)	11.6 (.457)	25.9 (1.020)	11.1 (.437)	9.0 (.354)	0.8 (.031)	Blue	YNT-1614 YA-1 YA-2 YA-4	1000
	3/8	10	V1.25-10		UL SP	10.5 (.413)		13.6 (.535)	29.7 (1.169)	13.9 (.547)					
	1-2	2	V2-S2		UL SP	2.2 (.087)		6.4 (.252)	16.5 (.650)	4.3 (.169)					
	3-4	3	V2-MS3		UL SP	3.2 (.126)		5.5 (.217)	17.4 (.685)	5.6 (.220)					
	3-4	3	V2-S3.3		UL SP	3.2 (.126)		6.4 (.252)	16.5 (.650)	4.3 (.169)					
	5-6	3.5	V2-S3		UL SP	3.7 (.146)		6.4 (.252)	16.5 (.650)	4.3 (.169)					
	3-4	3	V2-3		UL SP	3.2 (.126)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	5-6	3.5	V2-P3.5		UL SP	3.7 (.146)		7.0 (.276)	20.2 (.780)	7.7 (.303)					
	5-6	3.5	V2-M3	RAV2-3.5	UL SP	3.7 (.146)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	V2-M4		UL SP	4.3 (.169)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	V2-P4		UL SP	4.3 (.169)		7.0 (.276)	20.2 (.800)	7.7 (.303)					
	8	4	V2-4	RAV2-4	UL SP	4.3 (.169)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	10	5	V2-M5		UL SP	5.3 (.209)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	10	5	V2-5	RAV2-5	UL SP	5.3 (.209)		9.5 (.374)	21.0 (.827)	7.3 (.287)					
	1/4	6	V2-6	RAV2-6	UL SP	6.4 (.252)		12.0 (.472)	26.0 (1.024)	11.0 (.433)					
	5/16	8	V2-8	RAV2-8	UL SP	8.4 (.331)		12.0 (.472)	26.0 (1.024)	11.0 (.433)					
	3/8	10	V2-10		UL SP	10.5 (.413)		13.6 (.535)	29.7 (1.169)	13.9 (.547)					
12 to 10 (2.63 to 6.64)	1/2	12	V2-12		UL SP	13.0 (.512)	5.4 (.213)	19.0 (.748)	35.2 (1.386)	16.7 (.657)	13.5 (.531)	1.0 (.039)	Yellow	YNT-1210S YA-4	500
	1/2	14	V2-14		UL SP	15.0 (.591)		27.0 (1.063)	43.7 (1.720)	21.2 (.835)					
	5/8	16	V2-16		UL SP	17.0 (.669)		27.0 (1.063)	43.7 (1.720)	21.2 (.835)					
	3/4	20	V2-20		UL SP	21.0 (.827)		27.0 (1.063)	43.7 (1.720)	21.2 (.835)					
	5-6	3.5	V5.5-S3		UL SP	3.7 (.146)		7.2 (.283)	23.0 (.906)	5.9 (.232)					
	3-4	3	V5.5-3		UL SP	3.2 (.126)		9.5 (.374)	26.5 (1.403)	8.3 (.327)					
	8	4	V5.5-S4		UL SP	4.3 (.169)		7.2 (.283)	23.0 (.906)	5.9 (.232)					
	8	4	V5.5-4	RAV5.5-4	UL SP	4.3 (.169)		9.5 (.374)	26.5 (1.043)	8.3 (.327)					
	10	5	V5.5-5	RAV5.5-5	UL SP	5.3 (.209)		9.5 (.374)	26.5 (1.043)	8.3 (.327)					
	10	5	V5.5-S5		UL SP	5.3 (.209)		13.2 (.520)	29.1 (1.146)	9.0 (.354)					
	1/4	6	V5.5-6	RAV5.5-6	UL SP	6.4 (.252)		12.0 (.472)	32.5 (1.280)	13.0 (.512)					
	1/4	6	V5.5-S6		UL SP	6.4 (.252)		13.2 (.520)	29.1 (1.146)	9.0 (.354)					
	5/16	8	V5.5-S8		UL SP	8.4 (.331)		13.2 (.520)	29.1 (1.146)	9.0 (.354)					
	5/16	8	V5.5-8	RAV5.5-8	UL SP	8.4 (.331)		15.0 (.591)	34.7 (1.366)	13.7 (.539)					
	3/8	10	V5.5-10	RAV5.5-10	UL SP	10.5 (.413)		15.0 (.591)	34.7 (1.366)	13.7 (.539)					
	1/2	12	V5.5-12		UL SP	13.0 (.512)		19.2 (.756)	39.1 (1.539)	16.0 (.630)					
	1/2	14	V5.5-14		UL SP	15.0 (.591)		32.0 (1.260)	54.8 (2.157)	25.3 (.996)					
	5/8	16	V5.5-16		UL SP	17.0 (.669)		32.0 (1.260)	54.8 (2.157)	25.3 (.996)					
	11/16	18	V5.5-18		UL SP	19.0 (.748)		32.0 (1.260)	54.8 (2.157)	25.3 (.996)					
	3/4	20	V5.5-20		UL SP	21.0 (.827)		32.0 (1.260)	54.8 (2.157)	25.3 (.996)					

Note: 1) Products with the JIS mark ϕ conform to JIS C2805.2) *The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm².Examples: If the cross-sectional area of the wire is 0.3mm², fold the wire in two when crimping the terminal. If the cross-sectional area of the wire is 0.5mm², crimp the terminal onto the wire as it is.3) The part numbers indicated in the above table are for products with a brazed seam. When ordering products with a butted seam, add the prefix "WS" to the part number (ex. V2-4 → **VWS2-4**).

RING TONGUE (R type) Vinyl-insulated (flared)



File No.: E42024 LR20812 670021

Applicable Wire AWG#(mm²)	Stud size		Part No.		Standard	Dimensions mm (in.)							Color	Tool No.	Qty/box
	American	Metric	JST	JIS		ø d2	ø D	B	L	F	ℓ	T			
26 to 22 (0.2 to 0.5)	1-2	2	FV0.5-2		UL SP	2.2 (.087)	2.9 (.114)	5.2 (.205)	16.4 (.646)	5.8 (.228)	8.0 (.315)	0.5 (.020)	Yellow	YNT-2622 YA-1 YA-2	1,000
	3-4	3	FV0.5-3		UL SP	3.2 (.126)		5.2 (.205)	16.4 (.646)	5.8 (.228)					
	5-6	3.5	FV0.5-3.7		UL SP	3.7 (.146)		6.6 (.260)	19.0 (.748)	7.7 (.303)					
	8	4	FV0.5-4		UL SP	4.3 (.169)		6.6 (.260)	19.0 (.748)	7.7 (.303)					
	10	5	FV0.5-5		UL SP	5.3 (.209)		8.0 (.315)	19.0 (.748)	7.0 (.276)					
22 to 16 *(0.25 to 1.65)	1-2	2	FV1.25-2		UL SP	2.2 (.087)	4.0 (.157)	5.5 (.217)	15.7 (.618)	4.0 (.157)	9.0 (.354)	0.8 (.031)	Red	YNT-2216 YA-1 YA-2 YA-4	1,000
	3-4	3	FV1.25-3	RBV1.25-3	UL SP J	3.2 (.126)		5.5 (.217)	15.7 (.618)	4.0 (.157)					
	5-6	3.5	FV1.25-3.7		UL SP	3.7 (.146)		5.5 (.217)	15.7 (.618)	4.0 (.157)					
	3-4	3	FV1.25-MS3		UL SP	3.2 (.126)		5.5 (.217)	17.4 (.685)	5.6 (.220)					
	5-6	3.5	FV1.25-M3	RBV1.25-3.5	UL SP J	3.7 (.146)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	3-4	3	FV1.25-L3		UL SP	3.2 (.126)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	8	4	FV1.25-M4		UL SP	4.3 (.169)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	FV1.25-4	RBV1.25-4	UL SP J	4.3 (.169)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	10	5	FV1.25-5	RBV1.25-5	UL SP J	5.3 (.209)		8.0 (.315)	20.0 (.787)	7.0 (.276)					
	1/4	6	FV1.25-6		UL SP	6.4 (.252)		11.6 (.457)	25.9(1.020)	11.1 (.437)					
	5/16	8	FV1.25-8		UL SP	8.4 (.331)		11.6 (.457)	25.9(1.020)	11.1 (.437)					
3/8	10	FV1.25-10		UL SP	10.5 (.413)	13.6 (.535)	29.7(1.169)	13.9 (.547)							
16 to 14 (1.04 to 2.63)	1-2	2	FV2-S2		UL SP	2.2 (.087)	4.5 (.177)	6.4 (.252)	16.5 (.650)	4.3 (.169)	9.0 (.354)	0.8 (.031)	Blue	YNT-1614 YA-1 YA-2 YA-4	1,000
	3-4	3	FV2-MS3		UL SP	3.2 (.126)		5.5 (.217)	17.4 (.685)	5.6 (.220)					
	3-4	3	FV2-S3.3		UL SP	3.2 (.126)		6.4 (.252)	16.5 (.650)	4.3 (.169)					
	5-6	3.5	FV2-S3		UL SP	3.7 (.146)		6.4 (.252)	16.5 (.650)	4.3 (.169)					
	3-4	3	FV2-3		UL SP	3.2 (.126)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	5-6	3.5	FV2-P3.5		UL SP	3.7 (.146)		7.0 (.276)	20.2 (.780)	7.7 (.303)					
	5-6	3.5	FV2-M3	RBV2-3.5	UL SP J	3.7 (.146)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	FV2-M4		UL SP	4.3 (.169)		6.6 (.260)	18.6 (.732)	6.3 (.248)					
	8	4	FV2-P4		UL SP	4.3 (.169)		7.0 (.276)	20.2 (.800)	7.7 (.303)					
	8	4	FV2-4	RBV2-4	UL SP J	4.3 (.169)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	10	5	FV2-M5		UL SP	5.3 (.209)		8.5 (.335)	21.0 (.827)	7.8 (.307)					
	10	5	FV2-5	RBV2-5	UL SP J	5.3 (.209)		9.5 (.374)	21.0 (.827)	7.3 (.287)					
	1/4	6	FV2-6	RBV2-6	UL SP J	6.4 (.252)		12.0 (.472)	26.0(1.024)	11.0 (.433)					
	5/16	8	FV2-8	RBV2-8	UL SP J	8.4 (.331)		12.0 (.472)	26.0(1.024)	11.0 (.433)					
	3/8	10	FV2-10		UL SP	10.5 (.413)		13.6 (.535)	29.7(1.169)	13.9 (.547)					
	1/2	12	FV2-12		UL SP	13.0 (.512)		19.0 (.748)	35.2(1.386)	16.7 (.657)					
	1/2	14	FV2-14		UL SP	15.0 (.591)		27.0(1.063)	43.7(1.720)	21.2 (.835)					
	5/8	16	FV2-16		UL SP	17.0 (.669)		27.0(1.063)	43.7(1.720)	21.2 (.835)					
3/4	20	FV2-20		UL SP	21.0 (.827)	27.0(1.063)	43.7(1.720)	21.2 (.835)							
12 to 10 (2.63 to 6.64)	3-4	3	FV5.5-S3.3		UL SP	3.2 (.126)	6.8 (.268)	7.2 (.283)	23.0 (.906)	5.9 (.232)	13.5 (.531)	1.0 (.039)	Yellow	YNT-1210S YA-4	500
	5-6	3.5	FV5.5-S3		UL SP	3.7 (.146)		7.2 (.283)	23.0 (.906)	5.9 (.232)					
	3-4	3	FV5.5-3		UL SP	3.2 (.126)		9.5 (.374)	26.5(1.403)	8.3 (.327)					
	8	4	FV5.5-S4		UL SP	4.3 (.169)		7.2 (.283)	23.0 (.906)	5.9 (.232)					
	8	4	FV5.5-4	RBV5.5-4	UL SP J	4.3 (.169)		9.5 (.374)	26.5(1.043)	8.3 (.327)					
	10	5	FV5.5-5	RBV5.5-5	UL SP J	5.3 (.209)		9.5 (.374)	26.5(1.043)	8.3 (.327)					
	10	5	FV5.5-S5		UL SP	5.3 (.209)		13.2 (.520)	29.1(1.146)	9.0 (.354)					
	1/4	6	FV5.5-6	RBV5.5-6	UL SP J	6.4 (.252)		12.0 (.472)	32.5(1.280)	13.0 (.512)					
	1/4	6	FV5.5-S6		UL SP	6.4 (.252)		13.2 (.520)	29.1(1.146)	9.0 (.354)					
	5/16	8	FV5.5-S8		UL SP	8.4 (.331)		13.2 (.520)	29.1(1.146)	9.0 (.354)					
	5/16	8	FV5.5-8	RBV5.5-8	UL SP J	8.4 (.331)		15.0 (.591)	34.7(1.366)	13.7 (.539)					
	3/8	10	FV5.5-10	RBV5.5-10	UL SP J	10.5 (.413)		15.0 (.591)	34.7(1.366)	13.7 (.539)					
	1/2	12	FV5.5-12		UL SP	13.0 (.512)		19.2 (.756)	39.1(1.539)	16.0 (.630)					
	1/2	14	FV5.5-14		UL SP	15.0 (.591)		32.0(1.260)	54.8(2.157)	25.3 (.996)					
	5/8	16	FV5.5-16		UL SP	17.0 (.669)		32.0(1.260)	54.8(2.157)	25.3 (.996)					
	11/16	18	FV5.5-18		UL SP	19.0 (.748)		32.0(1.260)	54.8(2.157)	25.3 (.996)					
	3/4	20	FV5.5-20		UL SP	21.0 (.827)		32.0(1.260)	54.8(2.157)	25.3 (.996)					250

Note: 1) Products with the JIS mark conform to JIS C2805.


2) *The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm².

Examples: If the cross-sectional area of the wire is 0.3mm², fold the wire in two when crimping the terminal. If the cross-sectional area of the wire is 0.5mm², crimp the terminal onto the wire as it is.

3) The part numbers indicated in the above table are for products with a brazed seam. When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FV2-4 → **FVWS2-4**).



RING TONGUE (R type) *With funnel-entry vinyl-insulation*



T : Material thickness


File No.: E42024 LR20812

Applicable Wire AWG#(mm²)	Stud size		Part No.	Standard	Dimensions mm (in.)							Color	Tool No.	Qty/box
	American	Metric			ø d2	ø D	B	L	F	ℓ	T			
22 to 16 *(0.25 to 1.65)	1-2	2	FVX1.25-2		2.2 (.087)	4.0 (.157)	5.5 (.217)	17.5 (.689)	4.0 (.157)	10.8 (.425)	0.8 (.031)	Red	YNT-2216 YA-1 YA-2 YA-4	1,000
	3-4	3	FVX1.25-3		3.2 (.126)		5.5 (.217)	17.5 (.689)	4.0 (.157)					
	5-6	3.5	FVX1.25-3.7		3.7 (.146)		5.5 (.217)	17.5 (.689)	4.0 (.157)					
	3-4	3	FVX1.25-MS3		3.2 (.126)		5.5 (.217)	19.2 (.756)	5.6 (.221)					
	5-6	3.5	FVX1.25-M3		3.7 (.146)		6.6 (.260)	20.4 (.803)	6.3 (.248)					
	3-4	3	FVX1.25-L3		3.2 (.126)		8.0 (.315)	21.8 (.858)	7.0 (.276)					
	8	4	FVX1.25-M4		4.3 (.169)		6.6 (.260)	20.4 (.803)	6.3 (.248)					500
	8	4	FVX1.25-4		4.3 (.169)		8.0 (.315)	21.8 (.858)	7.0 (.276)					
	10	5	FVX1.25-5		5.3 (.209)		8.0 (.315)	21.8 (.858)	7.0 (.276)					
	1/4	6	FVX1.25-6		6.4 (.252)		11.6 (.457)	27.7(1.091)	11.1 (.437)					
	5/6	8	FVX1.25-8		8.4 (.331)		11.6 (.457)	27.7(1.091)	11.1 (.437)					
	3/8	10	FVX1.25-10		10.5 (.413)		13.6 (.535)	31.5(1.240)	13.9 (.547)					
16 to 14 (1.04 to 2.63)	1-2	2	FVX2-S2		2.2 (.087)	4.8 (.189)	6.4 (.252)	18.3 (.720)	4.3 (.169)	10.8 (.425)	0.8 (.031)	Blue	YNT-1614 YA-1 YA-2 YA-4	1,000
	3-4	3	FVX2-MS3		3.2 (.126)		5.5 (.217)	19.2 (.756)	5.6 (.221)					
	3-4	3	FVX2-S3.3		3.2 (.126)		6.4 (.252)	18.3 (.720)	4.3 (.169)					
	5-6	3.5	FVX2-S3		3.7 (.146)		6.4 (.252)	18.3 (.720)	4.3 (.169)					
	3-4	3	FVX2-3		3.2 (.126)		8.5 (.335)	22.8 (.898)	7.8 (.307)					
	5-6	3.5	FVX2-P3.5		3.7 (.146)		7.0 (.276)	22.0 (.866)	7.7 (.303)					
	5-6	3.5	FVX2-M3		3.7 (.146)		6.6 (.260)	20.4 (.803)	6.3 (.248)					
	8	4	FVX2-M4		4.3 (.169)		6.6 (.260)	20.4 (.803)	6.3 (.248)					
	8	4	FVX2-P4		4.3 (.169)		7.0 (.276)	22.0 (.866)	7.7 (.303)					
	8	4	FVX2-4		4.3 (.169)		8.5 (.335)	22.8 (.898)	7.8 (.307)					
	10	5	FVX2-M5		5.3 (.209)		8.5 (.335)	22.8 (.898)	7.8 (.307)					
	10	5	FVX2-5		5.3 (.209)		9.5 (.374)	22.8 (.898)	7.3 (.287)					
	1/4	6	FVX2-6		6.4 (.252)		12.0 (.472)	27.8(1.094)	11.0 (.433)					500
	5/16	8	FVX2-8		8.4 (.331)		12.0 (.472)	27.8(1.094)	11.0 (.433)					
	3/8	10	FVX2-10		10.5 (.413)		13.6 (.535)	31.5(1.240)	13.9 (.547)					
12 to 10 (2.63 to 6.64)	5-6	3.5	FVX5.5-S3		3.7 (.146)	7.0 (.276)	7.2 (.283)	23.5 (.925)	5.9 (.232)	14.0 (.551)	1.0 (.039)	Yellow	YNT-1210S YA-4	500
	3-4	3	FVX5.5-3		3.2 (.126)		9.5 (.374)	27.0(1.063)	8.3 (.327)					
	8	4	FVX5.5-S4		4.3 (.169)		7.2 (.283)	23.5 (.925)	5.9 (.232)					
	8	4	FVX5.5-4		4.3 (.169)		9.5 (.374)	27.0(1.063)	8.3 (.327)					
	10	5	FVX5.5-5		5.3 (.209)		9.5 (.374)	27.0(1.063)	8.3 (.327)					
	10	5	FVX5.5-S5		5.3 (.209)		13.2 (.520)	29.6(1.165)	9.0 (.354)					
	5-6	6	FVX5.5-6		6.4 (.252)		12.0 (.472)	33.0(1.299)	13.0 (.512)					250
	5/16	6	FVX5.5-S6		6.4 (.252)		13.2 (.520)	29.6(1.165)	9.0 (.354)					
	5/16	8	FVX5.5-S8		8.4 (.331)		13.2 (.520)	29.6(1.165)	9.0 (.354)					
	3/8	8	FVX5.5-8		8.4 (.331)		15.0 (.591)	35.2(1.386)	13.7 (.539)					
	3/8	10	FVX5.5-10		10.5 (.413)		15.0 (.591)	35.2(1.386)	13.7 (.539)					

Note:1) The part numbers indicated in the above table are for products with a brazed seam.

When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVX2-4 → **FVXWS2-4**).

RING TONGUE (R type) *With funnel-entry vinyl-insulation*



T : Material thickness

File No.: E42024 LR20812

Applicable Wire AWG#(mm ²)	Stud size		Part No.	Standard	Dimensions mm (in.)							Color	Tool No.	Qty/box
	American	Metric			ϕd_2	ϕD	B	L	F	ℓ	T			
22 to 16 *(0.25 to 1.65)	1-2	2	FVL1.25-2		2.2 (.087)	4.0 (.157)	5.5 (.217)	16.8 (.661)	4.0 (.157)	10.1 (.398)	0.8 (.031)	Red	YNT-2216 YA-1 YA-2 YA-4	1,000
	3-4	3	FVL1.25-3		3.2 (.126)		5.5 (.217)	16.8 (.661)	4.0 (.157)					
	5-6	3.5	FVL1.25-3.7		3.7 (.146)		5.5 (.217)	16.8 (.661)	4.0 (.157)					
	3-4	3	FVL1.25-MS3		3.2 (.126)		5.5 (.217)	18.5 (.728)	5.6 (.221)					
	5-6	3.5	FVL1.25-M3		3.7 (.146)		6.6 (.260)	19.7 (.776)	6.3 (.248)					
	3-4	3	FVL1.25-L3		3.2 (.126)		8.0 (.315)	21.1 (.831)	7.0 (.276)					
	8	4	FVL1.25-M4		4.3 (.169)		6.6 (.260)	19.7 (.776)	6.3 (.248)					
	8	4	FVL1.25-4		4.3 (.169)		8.0 (.315)	21.1 (.831)	7.0 (.276)					
	10	5	FVL1.25-5		5.3 (.209)		8.0 (.315)	21.1 (.831)	7.0 (.276)					
	1/4	6	FVL1.25-6		6.4 (.252)		11.6 (.457)	27.0(1.063)	11.1 (.437)					
	5/6	8	FVL1.25-8		8.4 (.331)		11.6 (.457)	27.0(1.063)	11.1 (.437)					
	3/8	10	FVL1.25-10		10.5 (.413)		13.6 (.535)	30.8(1.213)	13.9 (.547)					
16 to 14 (1.04 to 2.63)	1-2	2	FVL2-S2		2.2 (.087)	4.5 (.177)	6.4 (.252)	17.6 (.693)	4.3 (.169)	10.1 (.398)	0.8 (.031)	Blue	YNT-1614 YA-1 YA-2 YA-4	1,000
	3-4	3	FVL2-MS3		3.2 (.126)		5.5 (.217)	18.5 (.728)	5.6 (.221)					
	3-4	3	FVL2-S3.3		3.2 (.126)		6.4 (.252)	17.6 (.693)	4.3 (.169)					
	5-6	3.5	FVL2-S3		3.7 (.146)		6.4 (.252)	17.6 (.693)	4.3 (.169)					
	3-4	3	FVL2-3		3.2 (.126)		8.5 (.335)	22.1 (.870)	7.8 (.307)					
	5-6	3.5	FVL2-P3.5		3.7 (.146)		7.0 (.276)	21.3 (.839)	7.7 (.303)					
	5-6	3.5	FVL2-M3		3.7 (.146)		6.6 (.260)	19.7 (.776)	6.3 (.248)					
	8	4	FVL2-M4		4.3 (.169)		6.6 (.260)	19.7 (.776)	6.3 (.248)					
	8	4	FVL2-P4		4.3 (.169)		7.0 (.276)	21.3 (.839)	7.7 (.303)					
	8	4	FVL2-4		4.3 (.169)		8.5 (.335)	22.1 (.870)	7.8 (.307)					
	10	5	FVL2-M5		5.3 (.209)		8.5 (.335)	22.1 (.870)	7.8 (.307)					
	10	5	FVL2-5		5.3 (.209)		9.5 (.374)	22.1 (.870)	7.3 (.287)					
	1/4	6	FVL2-6		6.4 (.252)		12.0 (.472)	27.1(1.067)	11.0 (.433)					
	5/16	8	FVL2-8		8.4 (.331)		12.0 (.472)	27.1(1.067)	11.0 (.433)					
	3/8	10	FVL2-10		10.5 (.413)		13.6 (.535)	30.8(1.213)	13.9 (.547)					
	1/2	12	FVL2-12		13.0 (.512)		19.0 (.748)	36.3(1.429)	16.7 (.657)					500
	1/2	14	FVL2-14		15.0 (.591)		27.0(1.063)	44.8(1.764)	21.2 (.835)					250
	5/8	16	FVL2-16		17.0 (.669)		27.0(1.063)	44.8(1.764)	21.2 (.835)					
	3/4	20	FVL2-20		21.0 (.827)		27.0(1.063)	44.8(1.764)	21.2 (.835)					
12 to 10 (2.63 to 6.64)	5-6	3.5	FVL5.5-S3		3.7 (.146)	6.8 (.268)	7.2 (.283)	24.0 (.945)	5.9 (.232)	14.5 (.571)	1.0 (.039)	Yellow	YNT-1210S YA-4	500
	3-4	3	FVL5.5-3		3.2 (.126)		9.5 (.374)	27.5(1.083)	8.3 (.327)					
	8	4	FVL5.5-S4		4.3 (.169)		7.2 (.283)	24.0 (.945)	5.9 (.232)					
	8	4	FVL5.5-4		4.3 (.169)		9.5 (.374)	27.5(1.083)	8.3 (.327)					
	10	5	FVL5.5-5		5.3 (.209)		9.5 (.374)	27.5(1.083)	8.3 (.327)					
	10	5	FVL5.5-S5		5.3 (.209)		13.2 (.520)	30.1(1.185)	9.0 (.354)					
	1/4	6	FVL5.5-6		6.4 (.252)		12.0 (.472)	33.5(1.319)	13.0 (.512)					
	1/4	6	FVL5.5-S6		6.4 (.252)		13.2 (.520)	30.1(1.185)	9.0 (.354)					
	5/16	8	FVL5.5-S8		8.4 (.331)		13.2 (.520)	30.1(1.185)	9.0 (.354)					
	5/16	8	FVL5.5-8		8.4 (.331)		15.0 (.591)	35.7(1.406)	13.7 (.539)					
	3/8	10	FVL5.5-10		10.5 (.413)		15.0 (.591)	35.7(1.406)	13.7 (.539)					
	1/2	12	FVL5.5-12		13.0 (.512)		19.2 (.756)	40.1(1.579)	16.0 (.630)					250
	1/2	14	FVL5.5-14		15.0 (.591)		32.0(1.260)	55.8(2.197)	25.3 (.996)					
	5/8	16	FVL5.5-16		17.0 (.669)		32.0(1.260)	55.8(2.197)	25.3 (.996)					
	11/16	18	FVL5.5-18		19.0 (.748)		32.0(1.260)	55.8(2.197)	25.3 (.996)					
	3/4	20	FVL5.5-20		21.0 (.827)		32.0(1.260)	55.8(2.197)	25.3 (.996)					

Note:1) The part numbers indicated in the above table are for products with a brazed seam.

When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVL2-4 → **FVLWS2-4**).