





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE2-24K




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - NEMA 1, 3, 4, 12 AND 13 SEALING

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 2.7 LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — 1.0 LB MIN			
DIFFERENTIAL TRAVEL — — — .004 MAX			
OVERTRAVEL — — — .118 MIN			
	5A - 250 VAC 1/10HP - 125 OR 250 VAC  		
		ONE PLACE (.0) ± .030	± .030
		TWO PLACE (.00) ± .015	± .015
		THREE PLACE (.000) ± .005	± .005
		ANGLES	±
		WEIGHT	

914CE2-24K

M

DRAWING
NUMBER

2

ISSUE

RELEASE NO. PR-17647 REPLACES

CHECK

REVISIONS

A CO-69061
S A V
31 AUG 91

CHECK

DDM/CAD

DRAWN

S A V 3 SEPT 91