

Kippschalter mit Rast- und Tastfunktion

Toggle Switches with Switch and Touch Function

Allgemeine Hinweise und Technische Daten

Allgemeine Hinweise und technische Daten: siehe Seite 8

Die Kippschalter lassen sich optimal anreihen. Das Anschlußbrastermaß beträgt 2,54 mm. Zur mechanischen Stabilisierung des Kippschalters ist neben Nut, Feder und Gehäusekragen ein Fixierpin vorgesehen.





1-polig · 1 pole		
Funktion · Function	Hebel schwarz lever black Art.-Nr.	Hebel blau lever blue Art.-Nr.
R-R	1847.1031	1842.1031
R-T	1847.6031	1842.6031
R-RO-R	1847.3031	1842.3031
R-RO-T	1847.7031	1842.5031
T-RO-T	1847.4031	1842.4031

General Remarks and Technical Data

General remarks and technical data: see page 8



Toggle Switches can be stringed optimally. The dimension of the connection grid is 0.1". A groove, a spring and a collar as well as a fixing pin are used for additional mechanical stabilization of the toggle switch.



Schaltbild · Wiring Diagram



2-polig · 2 pole		
Funktion · Function	Hebel schwarz lever black Art.-Nr.	Hebel blau lever blue Art.-Nr.
R-R	1847.1032	1842.1032
R-T	1847.6032	1842.6032
R-RO-R	1847.3032	1842.3032
R-RO-T	1847.7032	1842.7032
T-RO-T	1847.4032	1842.4032
R-R-R	1847.3132	1842.3132
T-R-T	1847.4132	1842.4132



Schaltbild · Wiring Diagram