



Features:

- Wide frequency range, 20 Hz to 150 KHz, with flat output response
- Low distortion sine-wave output
- Clean-cut square wave for transient response testing
- 46 steps of selected frequency

Specifications: (at 10°C to 30°C, 80% Relative Humidity)

General

Frequency Range	: X1 range 20 Hz to 1.5 KHz X100 range 2 KHz to 150 KHz both with 23 steps of selected frequency
Accuracy	: 20 Hz to 100 KHz ($\pm 3\%$ or less) 100 KHz to 150 KHz ($\pm 5\%$ or less)
Output Control	: 0 dB, -20 dB and fine adjuster
Output Impedance	: 600 $\Omega \pm 10\%$

Sine Wave Characteristics

Output Voltage	: 1.2 V RMS Maximum (No load)
Output Flatness	: 20 Hz to 150 KHz ± 0.5 dB (Reference Frequency 1 KHz)
Distortion	: 200 Hz to 15 KHz $\pm 0.05\%$ (THD) or less 50 Hz to 30 KHz $\pm 0.1\%$ (THD) or less 20 Hz to 100 KHz $\pm 0.3\%$ (THD) or less

Square Wave Characteristics

Output Voltage	: 8 Vp-p maximum (when on load)
Rise and Fall Time	: Less than 0.5 μ s
Sag	: Less than 5% at 20 Hz
Over Shoot	: Less than 2% at maximum output
Duty Ratio	: 50% $\pm 5\%$

Audio Generator



Synchronization Characteristics

Output Voltage : 1.2 V RMS (no load)
Output Impedance : 1 K Ω $\pm$ 5%
Output spec same as sine wave above

General Information

Operating Temperature : 0°C to 50°C (specifications apply at 10°C to 30°C)
Storage Temperature : -20°C to 60°C (battery removed)
Power Requirements : 9 V battery, NEDA 1604 (included)
Battery Life : Up to 50 hours typical with alkaline
Up to 30 hours typical with zinc carbon
Battery Indicator : LED lamp indicates when approximately 20% battery life remains
Dimensions : 15 cm (L) $\times$ 8.2 cm (W) $\times$ 2.1 cm (H)
Weight : 200 g (with battery)
Includes : User's manual, test leads, 9 V battery (zinc carbon)

Part Number Table

Description	Part Number
Audio Generator	72-505

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA[®] is the registered trademark of the Group. © Premier Farnell plc 2012.

