




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

TUSONIX STYLE	518-016
Capacitance Range:	5.0 - 25 pF
Capacitance Tolerance:	MIN: +0% , MAX: -0, +50%
Temperature Characteristic:	DIELECTRIC CODE A
Rating:	100 VDC @ 85°C
Operating Temperature Range:	-55°C TO + 125°C
To MIL - C - 81/6E CV35A250	



X-2015 Rev-0

REVISION RECORD

Original Release

C.O. ECO-671

A

TOLERANCES
unless otherwise specified

2 PLC.
DECIMAL ± //

3 PLC.
DECIMAL ± .005 [0.13]

ANGLES ± //

TUSONIX
TUCSON, ARIZONA

Title

**MINIATURE
CERAMIC TRIMMER**

Drawn L.E. 04-16-09

Approved R.L. 04-16-09

A

518-016 A 5.0-25