




NOTES:

I. SPECIFICATIONS:

ELECTRICAL:

WITHSTANDING VOLTAGE: MINIMUM 1000 V RMS @ SEA LEVEL
INSULATION RESISTANCE: INITIAL 5000 MEGOHMS MAXIMUM,
1000 MEGOHMS MIN. AFTER ENVIRONMENTAL TESTING.
CONTACT RATING: 5 AMPS
CONTACT RESISTANCE: 2.7 MILLIOHMS MAX

MATERIALS:

INSULATOR: BLACK UL94V-0 RATED GLASS FILLED NYLON
CONTACT(030-1952-000): COPPER ALLOY
CONTACT AREA PLATING: GOLD OVER NICKEL,
CONNECTOR SHELL: STEEL, PLATING ZINC WITH CLEAR CHROMATE.

ENVIRONMENTAL:

OPERATING TEMPERATURE: -65°C TO +125°C

TERMINATION:

CRIMP WILL ACCOMODATE # 20 TO 28 AWG WIRE.


TERMINATION-TOOLS:

CRIMP TOOL: M22520/2-01

INSERTION/EXTRACTION POSITIONED 500

POSITIONER: EP-580

2. DIMENSIONS IN [] ARE IN MILLIMETERS.

[illegible]

9 SIZE 10 6 15 SIZE 10 9 25 SIZE 10 14 37 SIZE 10 20 50 SIZE 1 18 34

CONTACT ARRANGEMENT - AS VIEWED FROM ENGAGING SIDE

ROHS COMPLIANT

UNITS	ENGLISH		PRO/E	Cinch	V.SKUZA 1700 FINLEY RD LOMBARD, IL. 60148	
DO NOT SCALE DRAWING	DRAWN BY V.SKUZA	DATE 06/17/05	TITLE D*U SERIES CRIMP & POKE CONNECTOR PLUG ASS'Y(.120"HOLES)			
	DESIGN ENGINEER A.BALI	06/17/05	MATERIAL		CONTROL SPEC NUMBER	
	DESIGN ENGINEERING MGR. A.SHAH	07/09/05	MATERIAL SPEC NUMBER		FINISH	PROJECT NUMBER CI4740
	MFG. ENGINEERING J.OCEGUERA	07/07/05	CAD FILE NUMBER DXUHXXP	DRAWING NUMBER D*UH-XXP		
QUALITY ASSURANCE A. VAZQUEZ	07/06/05	CAGE IDENT NO. 71785	SIZE B	SCALE 1:1		
SHEET 1 OF 1						