






LOC	DIST	REVISIONS					
AJ	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AV3	REVISED PER ECO-11-005030	11MAR11	RK	HMR



RECOMMENDED STRIP LENGTH

- 1 CABLE USED WITHOUT SPACER
- 2 CABLE USED WITH SPACER
3. SEE INSTRUCTION SHEET 408-2798
4. PARTS PACKAGED UNASSEMBLED
- 5 USE WITH HAND TOOL FRAME 354940-1
- 6 USE WITH HANDTOOL 69710-1, OR
PNEUMATIC TOOL 69365 & 69365-3
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SUPERSEDED BY 8-227079-2	OBsolete	H.P. RED TRIAXIAL	—	58330-1	69477-4	C	1.090	1-938013-3	—	—	9-329461-0	9-227322-0	413530-6	4-227079-0
	OBsolete	RG-180/U,180A/U,180B/U & 195/U	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	9-221607-4	413530-5	3-227079-7
		RG-188/U DOUBLE BRAIDED	—	58330-1	69477-4	A	1.090	—	227194-1	—	9-329049-0	9-227322-0	413530-6	3-227079-3
	OBsolete	BELDEN 9248	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-7	413530-3	3-227079-2
	OBsolete	BELDEN 9248	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-8	413530-3	3-227079-1
	OBsolete	BELDEN 9248 & 9114	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-6	413530-3	3-227079-0
		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-4	227074-2	2-227079-2
SUPERSEDED BY 2-227079-2		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-3	413530-6	2-227079-1
SUPERSEDED BY 2-5227079-0		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	9-227322-1	413530-6	2-227079-0
		BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	2-221607-2	413530-5	1-227079-9
SUPERSEDED BY 1-227079-9		BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	2-221607-1	413530-5	1-227079-8
	OBsolete	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	9-221607-3	413530-5	1-227079-7
		RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-8	227074-2	1-227079-6
SUPERSEDED BY 1-227079-6		RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-7	413530-6	1-227079-5
	OBsolete	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	9-227322-0	413530-6	1-227079-4
	OBsolete	BELDEN 9266	—	220189-5	—	A	1.090	—	—	—	9-50428-0	221607-5	413530-2	1-227079-3
	OBsolete	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	1-329460-1	221607-8	413530-2	1-227079-2
		RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	227423-1	9-50428-0	221607-8	413530-2	1-227079-1
SUPERSEDED BY 227079-6		RG-62/U,62A/U & 62B/U	220217-1	220189-1	220187-1	B	1.280	—	—	—	9-225382-0	221607-7	227074-1	1-227079-0
		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	221607-7	227074-1	227079-9
		RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	9-50427-1	221607-7	227074-1	227079-9
		RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	—	9-50428-0	221607-6	227080-1	227079-7
		RG-62/U,62A/U & 62B/U	220217-1	220189-1	220187-1	B	1.090	—	—	227423-1	9-50428-0	221607-6	227080-1	227079-7
		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	221607-5	227074-1	227079-6
		RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	9-50427-1	221607-5	227074-1	227079-5
	OBsolete	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	1-329460-1	9-221607-1	413530-2	227079-4
		RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
	OBsolete	RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
SUPERSEDED BY 227079-6		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	9-221607-0	227074-1	227079-2
	OBsolete	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	9-50427-1	9-221607-0	227074-1	227079-1
		CABLE SIZE	DIE SET ⚠️	DIE SET ⚠️	CRIMP TOOL	VIEW	A	Ⓜ️ TUBING,HEAT SHRINK QTY=1	Ⓜ️ TUBING QTY=1	Ⓜ️ SPACER QTY=1	Ⓜ️ FERRULE QTY=1	Ⓜ️ CONTACT, PLUG QTY=1	Ⓜ️ PLUG ASSY, COML BNC QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE 10-9-89		 TE Connectivity	
		DRAWN BY D. LAMAN			
		CHECKED BY P. E. RUTH		DATE 10/27/89	
DIMENSIONS: INCHES		APPROVED BY J. GIBBS		NAME	
		TO: FRANCES, UNLESS OTHERWISE SPECIFIED.		PLUG, COMMERCIAL, BNC	
		PRODUCT SPEC			
		108-12044			
		APPLICATION SPEC			
MATERIAL		WEIGHT		RESTRICTED TO	
FINISH		SIZE		CAGE CODE	
		DRAWING NO.		DRAWING NO.	
		A1		00779	
		C		227079	
		SCALE		SHEET	
		4:1		1 OF 2	
		REV		AV	
		CUSTOMER DRAWING			

8	7	6	5	4	3	2	1
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION					
COPYRIGHT - By -		ALL RIGHTS RESERVED.					