


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A2	ECR-12-005726	27MAR12	RK	MY

D




C

B

A



RECOMMENDED STRIP LENGTHS



- 1

MATERIALS:
- BODY: ZINC PER ASTM-B-86.
OUTER CONTACT: BERYLLIUM COPPER PER ASTM-B-194.
CENTER CONTACT: BERYLLIUM COPPER PER ASTM-B-196.
DIELECTRIC: PTFE PER ASTM-D-1710.
- 2

FINISHES:
- BODY: NICKEL PER QQ-N-290.
OUTER CONTACT: GOLD PER MIL-G-45204.
CENTER CONTACT: GOLD PER MIL-G-45204.
- 3

FINISHES:
- BODY: NICKEL PER QQ-N-290.
OUTER CONTACT: NICKEL PER QQ-N-290.
CENTER CONTACT: GOLD PER MIL-G-45204.
- 4


TOOLING INFORMATION:
- CONTACT CRIMP: HAND TOOL M-22520/2-01 WITH DANIELS POSITIONER #K699, USE WITH SELECTOR #4.
BRAID CRIMP: HAND TOOL M-22520/5-01 WITH DANIELS DIE SET #HX4-1637 (.128 HEX) OR TE PRO-CRIMPER WITH DIE SET #58483-1, USE POSITION LETTER B.
5. SEE INSTRUCTION SHEET #2987-12.
- 6

TOOLING INFORMATION:
- CONTACT CRIMP: HAND TOOL M-22520/2-01 WITH DANIELS POSITIONER #K699, USE WITH SELECTOR #4.
BRAID CRIMP: HAND TOOL M-22520/2-01 WITH DANIELS DIE SET #HX4-1637 (.151 HEX) OR TE PRO-CRIMPER WITH DIE SET #58483-1, USE POSITION LETTER C.
- 7

FOR USE WITH RG 179/U CABLE
- 8

FOR USE WITH RD 179/U CABLE

OBSOLETE	8	6	3	415487-3
	7	4	3	415487-2
	7	4	2	415487-1
	CABLE	TOOLING	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.L.GROFT 6-10-97		 TE Connectivity				
DIMENSIONS: mm		CHK S.W.BURKHOLDER 6-10-97						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.3 [.01] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		APVD S.W.BURKHOLDER 6-10-97		NAME CABLE PLUG 75 OHM, MINI-SMB			
			PRODUCT SPEC —					
			APPLICATION SPEC —					
MATERIAL	1	2	3	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=415487	RESTRICTED TO —
CUSTOMER DRAWING					SCALE 6:1	SHEET 1 of 1	REV A2	