

## Shrink sleeve - WMS 9,5 (30X16)R - 0800377

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: Thermomark W, Thermomark R, Thermomark X, Perforated, Mounting type: Slide on, Cable diameter: 3.2-9.5 mm, Lettering field: 30 x 16 mm

The illustration shows WMS 6,4 (30X10)R

### Why buy this product

- ☒ The sleeves remain flexible after shrinking
- ☒ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ☒ The sleeves are pre-assembled for optimum use of material
- ☒ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ☒ The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- ☒ Up to four markers per sleeve are separated by perforations

### Key commercial data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 1                                                                                                       |
| Minimum order quantity | 8                                                                                                       |
| Catalog page           | Page 164 (CL2-2011)                                                                                     |
| GTIN                   | <br>4 046356 626460 |
| Custom tariff number   | 39173200                                                                                                |
| Country of origin      | CHINA                                                                                                   |

### Technical data

#### General

|                                     |                             |
|-------------------------------------|-----------------------------|
| Length (b)                          | 30 mm                       |
| Width (a)                           | 16 mm                       |
| Color                               | white                       |
| Base element material               | polyolefine                 |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation)     | -55 °C ... 125 °C           |
| Components                          | Halogen-free                |
| Material                            | Polyolefine                 |
| Number of individual labels         | 500                         |
| Number of individual labels per row | 2                           |

## Shrink sleeve - WMS 9,5 (30X16)R - 0800377

### Classifications

#### eclass

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27149103 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

#### etim

|          |          |
|----------|----------|
| ETIM 4.0 | EC001530 |
|----------|----------|

#### unspsc

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### Accessories

#### Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSE - 5145724



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSE BU - 5145737



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: blue

Ink ribbon - THERMOMARK-RIBBON 64-WMSE RD - 5145740



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: red

## Shrink sleeve - WMS 9,5 (30X16)R - 0800377

### Accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 305 mm

---

© Phoenix Contact 2012 - all rights reserved  
<http://www.phoenixcontact.com>