







LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L4	WIRE SIZE CORRECTION	05MAR2015	CR	PS

MATERIALS:
HOUSING: POLYAMIDE, UL94V-0
TERMINALS: COPPER ALLOY, TIN PLATED
SCREWS: STEEL, ZINC PLATED, EXCEPT WHERE NOTED.

ELECTRICAL:
RATING: 20A, 150V(300V LIMITED RATING)
UL & CSA.

MECHANICAL:
WIRE RANGE: 12 AWG – 22 AWG
MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.

- | | |
|---|--|
| 1 | SCREWS ARE ALL BOTTOMED, NO RUNNING TORQUE. |
| 2 | PERMANENT WHITE LETTERING. |
| 3 | SCREWS ARE NICKEL PLATED BRASS. |
| 4 | PRELIMINARY PART NUMBER. |
| 5 | PCB RETENTION FEATURE. |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI |



RECOMMENDED HOLE LAYOUT
TOLERANCE ± 0.002 , UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 27JUN02 CHK S. YODER 7/9/02 APVD S. YODER 7/9/02		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		4PCV-XX-006 ASSEMBLY	
MATERIAL		FINISH		SIZE	RESTRICTED TO
-		-		A2 00779	-
CUSTOMER DRAWING				DRAWING NO	
				CAGE CODE	
				WEIGHT	
				SCALE	
				SHEET	
				REV	
				1 of 1	
				14	