


2 WAY-0° 4 kHz to 2 GHz



MODEL NO.	FREQ. RANGE MHz f _L -f _U	ISOLATION dB			INSERTION LOSS, dB Above 3dB						PHASE UNBALANCE Degrees			AMPLITUDE UNBALANCE dB			CASE STYLE Note B	C O N N E C T I O N	PRICE \$ Qty. (1-9)
		L Typ. Min.	M° Typ. Min.	U Typ. Min.	L Typ. Max.	M° Typ. Max.	U Typ. Max.	L Max.	M° Max.	U Max.	L Max.	M° Max.	U Max.						
MSC-2-1	0.1-450	20	15	30	20	30	20	0.3	0.5	0.4	0.75	0.6	1.0	2.0	3.0	4.0	A03	ap	20.95
MSC-2-1W	2-650	22	18	30	20	22	18	0.3	0.5	0.5	0.8	0.8	1.2	1.0	2.0	4.0	A03	ap	22.95
MSC-2-5	5-1500	18	16	20	16	20	14	0.6	0.8	0.6	0.8	0.6	1.1	2.0	3.0	5.0	A03	ap	26.95
MSC-2-11	5-2000	18	16	20	16	18	11	0.6	0.8	0.6	0.8	1.2	1.8	2.0	3.0	5.0	A03	ap	31.95
PSC-2-1	0.1-400	20	15	25	20	25	20	0.2	0.6	0.4	0.75	0.6	1.0	2.0	3.0	4.0	A01	ap	11.95
PSC-2-1W	1-650	25	20	35	20	25	20	0.3	0.6	0.5	0.9	0.7	1.0	2.0	3.0	4.0	A01	ap	18.95
PSC-2-2	0.004-60	27	20	30	20	27	20	0.3	0.6	0.3	0.6	0.6	1.0	2.0	3.0	4.0	A01	ap	25.95
PSC-2-4	10-1000	30	25	25	20	25	20	0.6	1.0	0.6	1.2	0.7	1.3	2.0	4.0	8.0	A01	ap	25.95
PSC-2-5	10-1400	28	18	22	17	24	17	0.3	0.6	0.6	1.0	0.9	1.6	2.0	3.0	4.0	A01	ap	31.95
PSC-2-11	5-2000	21	16	22	18	19	9	0.5	0.8	0.6	0.9	0.7	1.5	1.0	3.0	6.0	A01	ap	36.95
PSC-2-45	700-900			20	17			0.2	0.4		0.4				3.0		A01	ap	24.95
PSC-2-1000	400-1000			35	25			0.5	1.0		1.0				2.0		A06	ap	24.95

L = low range [f_L to 10 f_L]


M = mid range [10 f_L to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

NOTES:

- ✦ When only specification for M range given, specification applies to entire frequency range.
- ✦ At low range frequency band (f_L to 10 f_L), linearly derate maximum input power by 13 dB.
- Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.
- * VSWR typical 1.1:1 over total range of frequency, max 1.2:1 for low and upper range, max 1.15:1 for mid range.
- A. General Quality Control Procedures, Environmental Specifications, Hi-Rel and MIL description are given in General Information (Section 0).
- B. Connector types and case mounted options, case finishes are given in section 0, see "Case styles & Outline Drawings".
- C. Prices and specifications subject to change without notice.
- 1. Absolute maximum power, voltage and current ratings:
 - 1a. Matched power rating,
 - Model PSC-2-11 0.5 Watt
 - All other models 1 Watt
 - 1b. Internal load dissipation, 0.125 Watt

Plug-In



PSC



TSC

MODEL NO.	FREQ. RANGE MHz f _L -f _U	ISOLATION dB			INSERTION LOSS, dB Above 3dB						PHASE UNBALANCE Degrees			AMPLITUDE UNBALANCE dB			CASE STYLE	C O N N E C T I O N	PRICE \$
		L	M°	U	L	M°	U	L	M°	U	L	M°	U	L	M°	U			
		Typ. Min.	Typ. Min.	Typ. Min.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.			Note B
■ PSC-2-1-75	0.25-300	20 15	30 20	20 15	0.4 0.75	0.4 0.75	0.4 1.0	2.0 3.0	3.0 5.0	5.0 10.0	0.15 0.2	0.2 0.3	A01	ap	14.45				
■ PSC-2-1-75A*	1-200	35 27	46 35	36 25	0.1 0.3	0.2 0.4	0.35 0.6	1.0 1.0	1.0 2.0	2.0 10.0	0.1 0.15	0.15 0.15	A06	ap	15.45				
❖ ■ PSC-2-2-75	0.008-60	35 20	40 25	30 22	0.1 0.4	0.15 0.4	0.3 0.8	1.0 1.0	1.0 1.0	1.0 1.0	0.15 0.15	0.15 0.15	A01	ap	25.95				
■ PSC-2-4-752	10-850	31 20	32 23	23 15	0.3 0.5	0.4 0.6	0.5 1.0	2.0 5.0	5.0 10.0	10.0 10.0	0.1 0.2	0.5 0.5	A01	ap	25.95				
■ PSC-2375	55-85		35 25			0.3 0.5		1.0			0.1		A01	ap	25.95				
TSC-2-1	1-400	30 25	30 25	30 20	0.25 0.5	0.4 0.75	0.8 1.0	2.0 3.0	3.0 4.0	4.0 10.0	0.15 0.2	0.6 0.6	B02	aj	17.95				
		L2	U2		L2	U2		L2	U2		L2	U2		L2	U2				
TSC-2-1W	200-1000	26 20	23 14		0.3 0.8	0.7 1.5		5 10			0.7 0.5		B02	aj	21.95				

L = low range [f_L to $10 f_L$]
 $L_2 = (f_L$ to $f_U/2)$

M = mid range [$10 f_L$ to $f_U/2$]
 $U_2 = (f_U/2$ to $f_U)$

U = upper range [$f_U/2$ to f_U]

pin connections

see case style outline drawings for pin locations

PORT	aj	ap
SUM PORT	1	1
PORT 1	2	5
PORT 2	4	6
GND EXT.	3	2,3,4,7,8
CASE GND	3	2,3,4,7,8
NOT USED	—	—

NSN GUIDE

MCL NO.	NSN	MIL-P-23971/15*
MSC-2-1	6625-01-124-8595	02
MSC-2-1W	5985-01-437-3528	
PSC-2-1	6625-00-548-0739	01
PSC-2-1W	5985-01-190-7701	
PSC-2-2	6625-01-143-2571	
PSC-2-4	6625-01-230-0492	
TSC-2-1	5895-01-332-8100	

* units are not QPL listed



The Design Engineers Search Engine

Provides Actual Data Instantly
 At: <http://www.minicircuits.com>

In Stock... Immediate Delivery
 For Custom Versions Of Standard Models
 Consult Our Applications Dept.

