



MASTER TL Mini Super 80

MASTER TL Mini Super 80 13W/840 1FM

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

• General Characteristics

Cap-Base	G5
Bulb	T5 [16 mm]
Life to 10% failures EM	4000 hr
Life to 10% fail	4000 hr
Preheat EL,3h	
Life to 10% fail	3000 hr
Nonpreh EL,3h	
Life to 50% failures EM	8000 hr
Life to 50% fail	8000 hr
Preheat EL,3h	
Life to 50% fail	6000 hr
Nonpreh EL,3h	

• Light Technical Characteristics

Colour Code	840 [CCT of 4000K]
Colour Rendering Index	85 Ra8
Colour Designation	Cool White
Colour Temperature	4000 K
Lamp Luminous Flux EM	1000 Lm
Lamp Luminous Efficacy EM	77 Lm/W
Lumen Maintenance 2000h	90 %
Lumen Maintenance 5000h	77 %
Lumen Maintenance 10000h	71 %
Average Luminance EM	1.20 cd/cm ²
Chromaticity Coordinate X	381 -

Chromaticity Coordinate Y 379 -

• Electrical Characteristics

Lamp Wattage	13 W
Lamp Wattage EM	13.0 W
Lamp Voltage	90 V
Lamp Current EM	0.170 A
Dimmable	yes

• Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	4.4 mg
Energy consumption kWh/1000h	14 kWh

• Product Dimensions

Base Face to Base Face A	516.9 (max) mm
Insertion Length B	521.6 (min), 524.0 (max) mm
Overall Length C	531.1 (max) mm
Diameter D	16 (max) mm

• Product Data

Order code	716859 27
Full product code	871150071685927
Full product name	MASTER TL Mini Super 80 13W/840 1FM
Order product name	MST TL Mini 13W/840 1FM/10X25CC
Pieces per pack	1

PHILIPS

MASTER TL Mini Super 80



Packing configuration 10X25CC
 Packs per outerbox 250
 Bar code on pack - EAN1 8711500716859
 Bar code on intermediate packing - EAN2 8711500716866

Bar code on outerbox - EAN3 8711500716873
 Logistic code(s) - 12NC 928001508450
 ILCOS code FD-13/40/1B-E-G5
 Net weight per piece 40.200 gr

Dimensional drawing



MASTER TL Mini Super 80 13W/840 1FM

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL 13W/840	516.9	521.6	524.0	531.1	16



G5

Photometric data



© 2013 Koninklijke Philips N.V. (Royal Philips)
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2013, July 9
 data subject to change