



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		R	REVISED PER ECR-13-001204	25JUN13	KH	PD




- 1 CONTINUOUS STRIP ON REELS.
- 2 TIN PLATE 0.00381 [.000150] MIN OVER 0.00254 [.000100] MIN THK COPPER OR TIN PLATE 0.00381 [.000150] MIN OVER 0.00127 [.000050] MIN THK NICKEL.
- 3 REELED WITH INTERLEAVING PAPER
- 4 OPTIONAL ID MARK, LOCATED APPROX AS SHOWN.
- 5 PRELIMINARY - NOT FOR PRODUCTION
- 6 PREPRODUCTION - FASR REQUIRED



P.C. BOARD HOLE PATTERN

3 STANDARD	BRASS	6 63824-5
REVERSE	BRASS	63824-3
STANDARD	BRASS	5 63824-2
STANDARD	BRASS	63824-1
REELING	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 20FEB01		TE Connectivity			
		CHK MS FEHER 20FEB01					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD N DEIBERT 20FEB01		NAME	
		0 PLC ± -		PRODUCT SPEC		TAB, FASTON, P.C.BOARD 6.35 [.250]	
		1 PLC ± -		—			
		2 PLC ± 0.25 [.010]		APPLICATION SPEC			
		3 PLC ± -		114-2115		SIZE	
		4 PLC ± -				CAGE CODE	
		ANGLES ± -				DRAWING NO	
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
SEE TABLE				—		A300779C-63824	
CUSTOMER DRAWING						SCALE	
						8:1	
						SHEET	
						1 OF 1	
						REV	
						R	