



Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > Clock Synthesizer by Chipset Vendor > Desktop Chipsets > 954148 > 954148AGLF

[Add to myIDT \[?\]](#)

You may also like...

954148AGLF

Category: Desktop Chipsets**Generic Part:** 954148**Market Group:** PC CLOCK**Description:** PC MAIN CLOCK

General Description ICS954148 follows the Intel CK410-compliant clock specification. This clock synthesizer provides a single chip solution for next generation P4 Intel processors and Intel chipsets. ICS954148 is driven with a 14.318MHz

Output Features:

- 2 - 0.7V current-mode differential CPU pairs
- 1 - 0.7V current mode differential SATA pair
- 1 - 0.7V current mode differential DOT 96/100MHz pair
- 6 - PCI (33MHz)
- 1 - USB, 48MHz
- 2 - REF, 14.318MHz
- 7 - PCI-Express 0.7V current differential pairs

Time is
money

Parameters

Package	TSSOP 56 (PAG56)
Voltage	3.3 V
Package	TSSOP 56
Speed	NA
Temperature	C
Status	Active
Sample	Yes
Minimum Order Quantity	102
Factory Order Increment	34

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	TSSOP 6.10 MM
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Green
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temperature	260°C
Rebake Conditions	NA
Length	14.0
Mark	G
Width	6.1
Pitch	0.5
Thickness	1.0
Status	Active