

# EP1145TTSC-1.507M

[Click part number to visit Part Number Details page](#)

## REGULATORY COMPLIANCE (Data Sheet downloaded on Aug 30, 2016)


[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.



## ITEM DESCRIPTION

Quartz Crystal Clock Oscillators XO (SPXO) HCMOS/TTL (CMOS) 5.0Vdc 14 Pin DIP Metal Thru-Hole 1.507MHz ±50ppm -20°C to +70°C

## ELECTRICAL SPECIFICATIONS

|                                   |                                                                                                                                                                                                                                  |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                 | 1.507MHz                                                                                                                                                                                                                         |
| Frequency Tolerance/Stability     | ±50ppm Maximum (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration) |
| Aging at 25°C                     | ±5ppm/year Maximum                                                                                                                                                                                                               |
| Operating Temperature Range       | -20°C to +70°C                                                                                                                                                                                                                   |
| Supply Voltage                    | 5.0Vdc ±10%                                                                                                                                                                                                                      |
| Input Current                     | 45mA Maximum (Unloaded)                                                                                                                                                                                                          |
| Output Voltage Logic High (Voh)   | Vdd-0.4Vdc Minimum (IOH = -16mA)                                                                                                                                                                                                 |
| Output Voltage Logic Low (Vol)    | 0.4Vdc Maximum (IOL = +16mA)                                                                                                                                                                                                     |
| Rise/Fall Time                    | 4nSec Maximum (Measured at 20% to 80% of waveform)                                                                                                                                                                               |
| Duty Cycle                        | 50 ±5(%) (Measured at 1.4Vdc with TTL Load; Measured at 50% of waveform with HCMOS Load)                                                                                                                                         |
| Load Drive Capability             | 50pF HCMOS Load Maximum                                                                                                                                                                                                          |
| Output Logic Type                 | CMOS                                                                                                                                                                                                                             |
| Pin 1 Connection                  | Tri-State (Disabled Output: High Impedance)                                                                                                                                                                                      |
| Pin 1 Input Voltage (Vih and Vil) | +2.0Vdc Minimum to enable output, +0.8Vdc to disable output, No Connect to enable output.                                                                                                                                        |
| Disable Current                   | 30mA Maximum (Pin 1 = Ground)                                                                                                                                                                                                    |
| Standby Current                   | 50µA Maximum (Pin 1 = Ground)                                                                                                                                                                                                    |
| Peak to Peak Jitter (tPK)         | 500pSec Maximum, 90pSec Typical                                                                                                                                                                                                  |
| RMS Period Jitter (tRMS)          | 50pSec Maximum, 13pSec Typical                                                                                                                                                                                                   |
| Start Up Time                     | 10mSec Maximum                                                                                                                                                                                                                   |
| Storage Temperature Range         | -55°C to +125°C                                                                                                                                                                                                                  |


## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                       |
|------------------------------|---------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C |
| Lead Integrity               | MIL-STD-883, Method 2004              |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210               |
| Resistance to Solvents       | MIL-STD-202, Method 215               |
| Solderability                | MIL-STD-883, Method 2003              |
| Temperature Cycling          | MIL-STD-883, Method 1010              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A |

EP1145TTSC-1.507M

[Click part number to visit Part Number Details page](#)

MECHANICAL DIMENSIONS (all dimensions in millimeters)




| PIN | CONNECTION                 |
|-----|----------------------------|
| 1   | Tri-State (High Impedance) |
| 7   | Ground/Case Ground         |
| 8   | Output                     |
| 14  | Supply Voltage             |

| LINE | MARKING                                                                                     |
|------|---------------------------------------------------------------------------------------------|
| 1    | ECLIPTEK                                                                                    |
| 2    | EP11TS<br>EP11=Product Series                                                               |
| 3    | 1.5070M                                                                                     |
| 4    | XXYYZZ<br>XX=Ecliptek Manufacturing Code<br>Y=Last Digit of the Year<br>ZZ=Week of the Year |

EP1145TTSC-1.507M

[Click part number to visit Part Number Details page](#)

OUTPUT WAVEFORM & TIMING DIAGRAM




EP1145TTSC-1.507M

[Click part number to visit Part Number Details page](#)

Test Circuit for TTL Output

| Output Load Drive Capability | R <sub>L</sub> Value (Ohms) | C <sub>L</sub> Value (pF) |
|------------------------------|-----------------------------|---------------------------|
| 10TTL                        | 390                         | 15                        |
| 5TTL                         | 780                         | 15                        |
| 2TTL                         | 1100                        | 6                         |
| 10LSTTL                      | 2000                        | 15                        |
| 1TTL                         | 2200                        | 3                         |

Table 1: R<sub>L</sub> Resistance Value and C<sub>L</sub> Capacitance Value Vs. Output Load Drive Capability




- Note 1: An external 0.1μF low frequency tantalum bypass capacitor in parallel with a 0.01μF high frequency ceramic bypass capacitor close to the package ground and V<sub>DD</sub> pin is required.
- Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.
- Note 3: Capacitance value C<sub>L</sub> includes sum of all probe and fixture capacitance.
- Note 4: Resistance value R<sub>L</sub> is shown in Table 1. See applicable specification sheet for 'Load Drive Capability'.
- Note 5: All diodes are MM74VHC00, MM74VHC14, or equivalent.

# EP1145TTSC-1.507M

[Click part number to visit Part Number Details page](#)

## Test Circuit for CMOS Output



Note 1: An external  $0.1\mu\text{F}$  low frequency tantalum bypass capacitor in parallel with a  $0.01\mu\text{F}$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.


Note 2: A low capacitance ( $<12\text{pF}$ ), 10X attenuation factor, high impedance ( $>10\text{Mohms}$ ), and high bandwidth ( $>300\text{MHz}$ ) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.

EP1145TTSC-1.507M [Click part number to visit Part Number Details page](#)



Recommended Solder Reflow Methods




High Temperature Solder Bath (Wave Solder)

|                                     |                                                                                                                                          |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Ts MAX to Tl (Ramp-up Rate)         | 3°C/Second Maximum                                                                                                                       |
| Preheat                             |                                                                                                                                          |
| - Temperature Minimum (Ts MIN)      | 150°C                                                                                                                                    |
| - Temperature Typical (Ts TYP)      | 175°C                                                                                                                                    |
| - Temperature Maximum (Ts MAX)      | 200°C                                                                                                                                    |
| - Time (ts MIN)                     | 60 - 180 Seconds                                                                                                                         |
| Ramp-up Rate (Tl to Tp)             | 3°C/Second Maximum                                                                                                                       |
| Time Maintained Above:              |                                                                                                                                          |
| - Temperature (Tl)                  | 217°C                                                                                                                                    |
| - Time (tL)                         | 60 - 150 Seconds                                                                                                                         |
| Peak Temperature (Tp)               | 260°C Maximum for 10 Seconds Maximum                                                                                                     |
| Target Peak Temperature (Tp Target) | 250°C +0/-5°C                                                                                                                            |
| Time within 5°C of actual peak (tp) | 20 - 40 Seconds                                                                                                                          |
| Ramp-down Rate                      | 6°C/Second Maximum                                                                                                                       |
| Time 25°C to Peak Temperature (t)   | 8 Minutes Maximum                                                                                                                        |
| Moisture Sensitivity Level          | Level 1                                                                                                                                  |
| Additional Notes                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

EP1145TTSC-1.507M


[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Infrared/Convection 185°C

|                                     |                                                                                                               |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------|
| Ts MAX to Tl (Ramp-up Rate)         | 5°C/Second Maximum                                                                                            |
| Preheat                             |                                                                                                               |
| - Temperature Minimum (Ts MIN)      | N/A                                                                                                           |
| - Temperature Typical (Ts TYP)      | 150°C                                                                                                         |
| - Temperature Maximum (Ts MAX)      | N/A                                                                                                           |
| - Time (ts MIN)                     | 60 - 120 Seconds                                                                                              |
| Ramp-up Rate (Tl to Tp)             | 5°C/Second Maximum                                                                                            |
| Time Maintained Above:              |                                                                                                               |
| - Temperature (Tl)                  | 150°C                                                                                                         |
| - Time (tL)                         | 200 Seconds Maximum                                                                                           |
| Peak Temperature (Tp)               | 185°C Maximum                                                                                                 |
| Target Peak Temperature (Tp Target) | 185°C Maximum 2 Times                                                                                         |
| Time within 5°C of actual peak (tp) | 10 Seconds Maximum 2 Times                                                                                    |
| Ramp-down Rate                      | 5°C/Second Maximum                                                                                            |
| Time 25°C to Peak Temperature (t)   | N/A                                                                                                           |
| Moisture Sensitivity Level          | Level 1                                                                                                       |
| Additional Notes                    | Temperatures shown are applied to body of device. Use this method only for product with the Gull Wing option. |

**EP1145TTSC-1.507M**
[Click part number to visit Part Number Details page](#)
**Recommended Solder Reflow Methods****Low Temperature Solder Bath (Wave Solder)**

|                                            |                                                                                                                                          |
|--------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <b>TS MAX to TL (Ramp-up Rate)</b>         | 5°C/Second Maximum                                                                                                                       |
| <b>Preheat</b>                             |                                                                                                                                          |
| - Temperature Minimum (TS MIN)             | N/A                                                                                                                                      |
| - Temperature Typical (TS TYP)             | 150°C                                                                                                                                    |
| - Temperature Maximum (TS MAX)             | N/A                                                                                                                                      |
| - Time (ts MIN)                            | 30 - 60 Seconds                                                                                                                          |
| <b>Ramp-up Rate (TL to TP)</b>             | 5°C/Second Maximum                                                                                                                       |
| <b>Time Maintained Above:</b>              |                                                                                                                                          |
| - Temperature (TL)                         | 150°C                                                                                                                                    |
| - Time (tL)                                | 200 Seconds Maximum                                                                                                                      |
| <b>Peak Temperature (TP)</b>               | 245°C Maximum                                                                                                                            |
| <b>Target Peak Temperature (TP Target)</b> | 245°C Maximum 1 Time / 235°C Maximum 2 Times                                                                                             |
| <b>Time within 5°C of actual peak (tp)</b> | 5 Seconds Maximum 1 Time / 15 Seconds Maximum 2 Times                                                                                    |
| <b>Ramp-down Rate</b>                      | 5°C/Second Maximum                                                                                                                       |
| <b>Time 25°C to Peak Temperature (t)</b>   | N/A                                                                                                                                      |
| <b>Moisture Sensitivity Level</b>          | Level 1                                                                                                                                  |
| <b>Additional Notes</b>                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

**Low Temperature Manual Soldering**

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)

**High Temperature Manual Soldering**

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)