



521 SERIES

5mm Discrete LED



3 Leded, Non-Tinted, Diffused

BI-COLOR



PART NUMBER	LED COLOR
521-9450	RED/GREEN
521-9461	YELLOW/GREEN

SPECIFICATIONS

521-9450



521-9461



ABSOLUTE MAXIMUM RATINGS (T_A = 25°C)

Power Dissipation (mW):	135/135	Operating Temperature (°C):	-20/+85
Average Forward Current (mA):	25/25	Storage Temperature (°C):	-55/+85
Derating (mA/°C) From 50°C	.5/.5	Soldering Temperature:	260°C, 5 seconds,
Peak Current (mA):	90/90		1.6 mm from case

OPERATING CHARACTERISTICS (T_A = 25°C)

Part Number	Color	Peak Wavelength (nm)	Luminous Intensity (mcd)	Forward Voltage (V)*	Viewing Angle 2θ 1/2
521-9450	Red/Green	635/565	Min. 2.1/4.2 Typ. 5/8	Typ. 2.1/2.3 Max. 2.5/2.7	65°
521-9461	Yellow/Green	583/565	Min. 2.1/4.2 Typ. 5/8	Typ. 2.1/2.1 Max. 2.5/2.5	65°

*I_F = 10mA



Dialight Corporation
1501 Route 34 South • Farmingdale, NJ 07727 USA
Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com
a Roxboro Group Company

MDEA521X001_A