



PRODUCT NUMBER	DIM. A	DIM. B	DIM C WIREWRAP AREA PLATING	DIM D NOTCH LOCATION	DIM E NOTCH DEPTH	
1B-1A-B	.505	.940	None	—	—	
1B-2A-B	.555	.940	None	—	—	NOT AVAILABLE
1B-3A-B	.505	.940	.200	—	—	
1B-4A-B	.555	.940	.200	—	—	
1B-9A-B	.400	.940	.200 Ni	.325±.005	.0045±.0005	
1B-10A-B	.480	.940	.200 Ni	.325±.005	.0045±.0005	
1B-13A-B	.555	.940	.200 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-14A-B	.605	.940	.200	—	—	
1B-15A-B	.505	.940	.200 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-16A-B	.605	.940	.200 Ni	.325±.005	.0045±.0005	
1B-20A-B	.555	.695	.250	—	—	NOT AVAILABLE
1B-21A-B	.505	.695	.250	—	—	NOT AVAILABLE
1B-22A-B	.605	.695	.250	—	—	NOT AVAILABLE
1B-23A-B	.555	.695	None	—	—	NOT AVAILABLE
1B-24A-B	.505	.695	None	—	—	NOT AVAILABLE
1B-25A-B	.605	.695	None	—	—	NOT AVAILABLE
1B-26A-B	.555	.695	.250 Ni	.325±.005	.0045±.0005	
1B-27A-B	.505	.695	.250 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-28A-B	.605	.695	.250 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-29A-B	.555	.695	.250 Ni	.460±.005	.0060±.0005	NOT AVAILABLE
1B-30A-B	.505	.695	.250 Ni	.460±.005	.0060±.0005	NOT AVAILABLE
1B-31A-B	.555	1.085	.330	—	—	
1B-32A-B	.555	.940	.200 Ni	.480±.005	.0060±.0005	
1B-33A-B	.605	.940	.200 Ni	.480±.005	.0060±.0005	NOT AVAILABLE
1B-34A-B	.505	.940	.200 Ni	.480±.005	.0060±.0005	
1D-4A-B	.555	.695	.250	.091±.005	.0045±.0005	NOT AVAILABLE




mat'l. code				surface		tolerance		projection		product family	
SEE NOTE 1				✓				INCH		FASTECH	
ltr	ec'n no	dr	date	tolerances unless otherwise specified						title	
A	v03-0079	HTB	2006-01-16	angles	linear	.XX±.01				1-TYPE CONTACT ON BANDOLIER	
B	v03-0177	HTB	2003-02-12			.XXX±.003					
C	v06-0486	HTB	2006-05-19	0'±2'		.XXXX±.0020		scale N.T.S.			
D	v06-0592	HTB	2006-06-16	dr	T. BREWBAKER	2003-01-16				dwg no	
E	v08-0400	HTB	2008-09-29	engr	T. BREWBAKER	2003-01-16				sheet 1 of 2	
F	v09-0135	HTB	2009-03-27	chr	T. BREWBAKER	2003-01-16				size	
				appd	T. BREWBAKER	2003-01-16				A3	
										type	
										Product Customer Drawing	
sheet index	revision	F	F								
	sheet	1	2								


FCJ
FCconnect.com
Copyright FCJ

PRODUCT NUMBER
SEE TABLE

PACKAGING TICKET
PLATED PRODUCT
TCS PART #



OPEN SIDE OF "C" DOWN



NOTES:

1. BANDOLIER MATERIAL: C26000, 1/2 HARD, .010 +/- .0005 THICK.
2. PIN RETENTION IN BANDOLIER: 2 LBS MIN, 5 LBS MAX.
3. 1-TYPE CONTACTS MAY BE SLIGHTLY LOOSE IN THE BANDOLIER.
4. SHOULDER WIDTH AFTER BODY CARRIER REMOVAL SHALL BE .0685 MAX INCLUDING BURRS.
5. PIN WIDTH AFTER BODY CARRIER REMOVAL SHALL BE .0285 MAX INCLUDING BURRS.
6. BANDOLIERED PIN PROGRESSION TOLERANCE: .002" / INCH
7. BANDOLIERED PIN CAMBER FOR 3 FOOT LENGTH: .25 MAX.
8. NO SPLICES ARE PERMITTED, NO MORE THAN ONE BREAK PER REEL IS PERMITTED.
9. SEE CUSTOMER DRAWING A93KC4040 FOR PLATING AND ADDITIONAL PIN INFORMATION.

mat'l. code SEE NOTE 1				surface	✓	tolerance	projection	product family FASTECH		
ltr	ecm no	dr	date	tolerances unless otherwise specified			INCH	title 1-TYPE CONTACT ON BANDOLIER		
F				angles	linear	.XX±.01		dwg no 63501 sheet 2 of 2 size A3		
						.XXX±.003				
				0°±2°		.XXX±.0020				
				dr	T. BREWBAKER	2003-01-16	FCJ	type Product Customer Drawing		
				engr	T. BREWBAKER	2003-01-16				
				chr	T. BREWBAKER	2003-01-16				
				appd	T. BREWBAKER	2003-01-16				
sheet	revision			sheet						
index										

form A3