


BANDING PART NUMBER	COIL BAND WIDTH ±.010" [0.25]	MAT'L TYPE	MAT'L COATING	REQ'D. BUCKLE PART NUMBER	MAT'L LENGTH	MAT'L THICKNESS ±.001" [0.03]	MAT'L EDGES
MSW38T15-CR4	.375" [9.52]	304	-----	MSBW38-C4	100.0' [30.5m]	.015" [.38]	NOTE 5
MSW38T15-CR6	.375" [9.52]	316	-----	MSBW38-C6	100.0' [30.5m]	.015" [.38]	NOTE 5
MSCNW38T15-OR6	.375" [9.52]	316	NYLON	MSBW38-C6	82.5' [25.0m]	.015" [.38]	NOTE 6
MSCW38T15-OR6	.375" [9.52]	316	POLYESTER	MSBW38-C6	82.5' [25.0m]	.015" [.38]	NOTE 6



NOTES:

1. INSTALLATION TOOLS: BT2MS75, BT2HT
2. UNLESS OTHERWISE SPECIFIED, DIM IN BRACKETS [] ARE IN MILLIMETERS
3. SEE TABLE FOR COMPATIBLE BUCKLE HEAD PART NUMBERS.
4. TOLERANCES UNLESS OTHERWISE SPECIFIED:
.X ± .13 [3.30]
5. BROKEN EDGES TO ELIMINATE SHARP EDGES.
6. FULLY COATED MATERIAL.
COATING THICKNESS: .003/.007" [.08/.18] PER SIDE

04A	10/08	JAMB	SKB	ORIG CAD FILE SPEC WAS S41153_04. NOTE 1: INSTALLATION TOOL BT1HT REPLACED BY BT2HT
04	11/04	JAMB	EJD	ⓐ ADDED PART NO. MSCW38T15-OR6 TO TABLE
				ⓓⓔ ADDED "MAT'L TYPE" & "MAT'L COATING" INFO TO TABLE.
03	10/04	JAMB	EJD	ⓕ CHANGED TABLE HEADING FROM "BANDING HEAD" TO "REQ'D. BUCKLE"
				ⓖ MAT'L LENGTH FOR PART NO. MSCNW38T15-OR6 CHANGED FROM 100.0' [30.5m] TO 82.5' [25.0m]
				ⓓ ADDED TO NOTE 7: COATING THK.: .003/.007 [.08/.18] PER SIDE
02	9/04	JAMB	EJD	ⓑ UPDATED TABLE TO REFLECT CURRENTLY AVAILABLE PART NUMBERS. REMOVED AISI NO. 3 & 5 MAT'L EDGE DESIGNATIONS FROM TABLE.
01	6/04	BRH	EJD	ⓐ UPDATED TABLE TO REFLECT CURRENTLY AVAILABLE PART NUMBERS
00	3/04	BRH	EJD	RELEASED
REV	10/03	BY	CHK	DESCRIPTION
				ECN#
				PM
				CUST

PANDUIT

CORP.

N41153BS_DC/04A

TINLEY PARK, ILLINOIS

STAINLESS STEEL METAL STRAPPING
CONTINUOUS
CUSTOMER DRAWING

DRAWN BY
BRHCHK'D
EJDSCALE
NO SCALEDRAWING NO.
N41153BS_DC