

## Features


- Dual Zeners in Common Anode Configuration
- 300 mW Power Dissipation Rating
- Ideally Suited for Automated Insertion
- $\Delta V_Z$  For Both Diodes in One Case is  $\leq 5\%$
- Common Cathode Style Available See DZ Series
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Notes 3 & 4)**
- **Qualified to AEC-Q101 Standards for High Reliability**

## ESD Sensitivity Rating

- AEC-Q101, HBM - 8kV, MM - 400V
- IEC 61000-4-2, Air - 15kV, Contact - 8kV

## Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish annealed over Alloy 42 leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208 ②
- Polarity: See Diagram
- Approximate Weight: 0.008 grams




## Ordering Information (Note 5)

| Part Number         | Qualification | Case  | Packaging        |
|---------------------|---------------|-------|------------------|
| (Type Number)-7-F*  | Commercial    | SOT23 | 3000/Tape & Reel |
| (Type Number)Q-7-F* | Automotive    | SOT23 | 3000/Tape & Reel |


\*Add "-7-F" to the appropriate type number in Electrical Characteristics Table on Page 2 example: 6.2V Zener = AZ23C6V2-7F

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
  2. See <http://www.diodes.com> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
  4. Product manufactured with Date Code V9 (week 33, 2008) and newer are built with Green Molding Compound. Product manufactured prior to Date Code V9 are built with Non-Green Molding Compound and may contain Halogens or Sb<sub>2</sub>O<sub>3</sub> Fire Retardants.
  5. For Packaging Details, go to our website at <http://www.diodes.com>.

## Marking Information



K/D = SAT (Shanghai Assembly / Test site)  
xx = Product Type Marking Code  
See Electrical Characteristics Table  
YM = Date Code Marking  
Y = Year (ex: Z = 2012)  
M = Month (ex: 9 = September)



C = CAT (Chengdu Assembly / Test site)  
xx = Product Type Marking Code  
See Electrical Characteristics Table  
YM = Date Code Marking  
Y = Year (ex: Z = 2012)  
M = Month (ex: 9 = September)

### Date Code Key

| Year | 1998 | ... | 2002 | 2003 | 2004 | ... | 2010 | 2011 | 2012 | 2013 | 2014 | 2015 | 2016 | 2017 | 2018 |
|------|------|-----|------|------|------|-----|------|------|------|------|------|------|------|------|------|
| Code | J    | ... | N    | P    | R    | ... | X    | Y    | Z    | A    | B    | C    | D    | E    | F    |

| Month | Jan | Feb | Mar | Apr | May | Jun | Jul | Aug | Sep | Oct | Nov | Dec |
|-------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| Code  | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | O   | N   | D   |

## Thermal Characteristics

| Characteristic                                       | Symbol          | Value       | Unit |
|------------------------------------------------------|-----------------|-------------|------|
| Power Dissipation (Note 6)                           | $P_D$           | 300         | mW   |
| Thermal Resistance, Junction to Ambient Air (Note 6) | $R_{\theta JA}$ | 417         | °C/W |
| Operating and Storage Temperature Range              | $T_J, T_{STG}$  | -65 to +150 | °C   |

Notes: 6. Mounted on FR4 PC Board with recommended pad layout which can be found on our website at <http://www.diodes.com>.

## Electrical Characteristics (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

| Type Number | Marking Code | Zener Voltage Range (Note 7) | Maximum Zener Impedance<br>$f = 1\text{kHz}$ |                                  | Typical Temperature Coefficient<br>$TC (\%/^\circ\text{C})$ | Min. Reverse Voltage (Note 7)<br>@ $I_R = 0.1\mu\text{A}$<br>$V_R$ (Volts) |
|-------------|--------------|------------------------------|----------------------------------------------|----------------------------------|-------------------------------------------------------------|----------------------------------------------------------------------------|
|             |              | @ $I_{ZT} = 5.0\text{mA}$    | $Z_{ZT} @ I_{ZT} = 5.0\text{mA}$             | $Z_{ZK} @ I_{ZK} = 1.0\text{mA}$ |                                                             |                                                                            |
|             |              | $V_Z$ (Volts)                | Ohms                                         | Ohms                             |                                                             |                                                                            |
| AZ23C2V7    | D1           | 2.5 - 2.9                    | 83                                           | 500                              | -0.065                                                      | —                                                                          |
| AZ23C3V0    | D2           | 2.8 - 3.2                    | 95                                           | 500                              | -0.060                                                      | —                                                                          |
| AZ23C3V3    | D3           | 3.1 - 3.5                    | 95                                           | 500                              | -0.055                                                      | —                                                                          |
| AZ23C3V6    | D4           | 3.4 - 3.8                    | 95                                           | 500                              | -0.055                                                      | —                                                                          |
| AZ23C3V9    | D5           | 3.7 - 4.1                    | 95                                           | 500                              | -0.050                                                      | —                                                                          |
| AZ23C4V3    | D6           | 4.0 - 4.6                    | 95                                           | 500                              | -0.035                                                      | —                                                                          |
| AZ23C4V7    | D7           | 4.4 - 5.0                    | 78                                           | 500                              | -0.015                                                      | —                                                                          |
| AZ23C5V1    | D8           | 4.8 - 5.4                    | 60                                           | 480                              | +0.005                                                      | 0.8                                                                        |
| AZ23C5V6    | D9           | 5.2 - 6.0                    | 40                                           | 400                              | +0.020                                                      | 1.0                                                                        |
| AZ23C6V2    | DA           | 5.8 - 6.6                    | 10                                           | 200                              | +0.030                                                      | 2.0                                                                        |
| AZ23C6V8    | DB           | 6.4 - 7.2                    | 8.0                                          | 150                              | +0.045                                                      | 3.0                                                                        |
| AZ23C7V5    | DC           | 7.0 - 7.9                    | 7.0                                          | 50                               | +0.050                                                      | 5.0                                                                        |
| AZ23C8V2    | DD           | 7.7 - 8.7                    | 7.0                                          | 50                               | +0.055                                                      | 6.0                                                                        |
| AZ23C9V1    | DE           | 8.5 - 9.6                    | 10                                           | 50                               | +0.065                                                      | 7.0                                                                        |
| AZ23C10     | DF           | 9.4 - 10.6                   | 15                                           | 70                               | +0.065                                                      | 7.5                                                                        |
| AZ23C11     | DG           | 10.4 - 11.6                  | 20                                           | 70                               | +0.070                                                      | 8.5                                                                        |
| AZ23C12     | DH           | 11.4 - 12.7                  | 20                                           | 90                               | +0.075                                                      | 9.0                                                                        |
| AZ23C13     | DI           | 12.4 - 14.1                  | 25                                           | 110                              | +0.080                                                      | 10.0                                                                       |
| AZ23C15     | DJ           | 13.8 - 15.6                  | 30                                           | 110                              | +0.080                                                      | 11.0                                                                       |
| AZ23C16     | DK           | 15.3 - 17.1                  | 40                                           | 170                              | +0.090                                                      | 12.0                                                                       |
| AZ23C18     | DL           | 16.8 - 19.1                  | 50                                           | 170                              | +0.090                                                      | 14.0                                                                       |
| AZ23C20     | DM           | 18.8 - 21.2                  | 50                                           | 220                              | +0.090                                                      | 15.0                                                                       |
| AZ23C22     | DN           | 20.8 - 23.3                  | 55                                           | 220                              | +0.090                                                      | 17.0                                                                       |
| AZ23C24     | DO           | 22.8 - 25.6                  | 80                                           | 220                              | +0.090                                                      | 18.0                                                                       |
| AZ23C27     | DP           | 25.1 - 28.9                  | 80                                           | 250                              | +0.090                                                      | 20.0                                                                       |
| AZ23C30     | DQ           | 28 - 32                      | 80                                           | 250                              | +0.090                                                      | 22.5                                                                       |
| AZ23C33     | DR           | 31 - 35                      | 80                                           | 250                              | +0.090                                                      | 25.0                                                                       |
| AZ23C36     | DS           | 34 - 38                      | 90                                           | 250                              | +0.090                                                      | 27.0                                                                       |
| AZ23C39     | DT           | 37 - 41                      | 90                                           | 300                              | +0.110                                                      | 29.0                                                                       |
| AZ23C43     | 30           | 40 - 46                      | 100                                          | 700                              | +0.110                                                      | 32.0                                                                       |
| AZ23C47     | 31           | 44 - 50                      | 100                                          | 750                              | +0.110                                                      | 35.0                                                                       |
| AZ23C51     | 32           | 48 - 54                      | 100                                          | 750                              | +0.110                                                      | 38.0                                                                       |

Notes: 7. Short duration pulse test used to minimize self-heating effect.




Fig. 1 Power Derating Curve




Fig. 2 Typical Zener Breakdown Characteristics




Fig. 3 Typical Zener Breakdown Characteristics




Fig. 4 Typical Zener Breakdown Characteristics






Fig. 5 Typical Total Capacitance vs. Nominal Zener Voltage

## Package Outline Dimensions



| SOT23                |       |      |       |
|----------------------|-------|------|-------|
| Dim                  | Min   | Max  | Typ   |
| A                    | 0.37  | 0.51 | 0.40  |
| B                    | 1.20  | 1.40 | 1.30  |
| C                    | 2.30  | 2.50 | 2.40  |
| D                    | 0.89  | 1.03 | 0.915 |
| F                    | 0.45  | 0.60 | 0.535 |
| G                    | 1.78  | 2.05 | 1.83  |
| H                    | 2.80  | 3.00 | 2.90  |
| J                    | 0.013 | 0.10 | 0.05  |
| K                    | 0.903 | 1.10 | 1.00  |
| K1                   | -     | -    | 0.400 |
| L                    | 0.45  | 0.61 | 0.55  |
| M                    | 0.085 | 0.18 | 0.11  |
| α                    | 0°    | 8°   | -     |
| All Dimensions in mm |       |      |       |

## Suggested Pad Layout



| Dimensions | Value (in mm) |
|------------|---------------|
| Z          | 2.9           |
| X          | 0.8           |
| Y          | 0.9           |
| C          | 2.0           |
| E          | 1.35          |

#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2013, Diodes Incorporated

**[www.diodes.com](http://www.diodes.com)**