


QTY REQD PER ASSY		PARTS LIST			
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.		MATERIAL		FIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		HT TR			
2 PLD DEC ±		-		-	
3 PLD DEC ±		-		-	
4 PLD DEC ±		-		-	
ANGLES ±		-		-	
SURF TEXTURE: ✓		-		-	
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX		-		-	
CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING		RESTRICTED TO -	

[illegible]

- 1 RECOMMENDED SPARE PARTS.
- 2 GREASE LIGHTLY.
- 3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
- 4 LUBRICATE DAILY USING NO. 20 MACHINE OIL.
5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.
- 6 MAY NEED TO ADJUST FOR DIFFERENT TERMINAL.
- 7 THIS APPLICATOR APPLIES TERMINAL WITH A SEAL.
- 8 APPLY TORQ-SEAL IN ALLEN SOCKET TO FILL HOLE AFTER FLAT HD HAS BEEN ADJUSTED TO CORRECT HEIGHT AT QUALIFICATION. APPLY PN 1-23419-5 LOC-TITE TO THREADS.
- 9 CUT TO LENGTH AT ASSY