

PART NUMBER CODING





G _ C _ _ SFBN - M30

NUMBER OF POSITIONS PER ROW

PLATING

ALL PLATINGS HAVE .000050" NICKEL UNDERPLATE

	CONTACT	TERMINATION
B =	.000010" GOLD	.000100" PURE TIN, MATTE
C =	.000030" GOLD	.000100" PURE TIN, MATTE
E =	.000100" PURE TIN, MATTE OVERALL	



- NOTES:
1. INSULATOR MATERIAL: PA9T.
 2. CONTACT MATERIAL: PHOSPHOR BRONZE
 3. PLATING: SEE TABLE
 4. OPERATING TEMPERATURE: -65°C TO +125°C
 5. PROCESSING TEMPERATURE: 260°C MAX FOR 120 SECS MAX.
 6. UL FLAMMABILITY: 94V-0
 7. VOLTAGE RATING: 600 VDC MINIMUM AT SEA LEVEL.
 8. CURRENT RATING: 3 AMP
 9. INSULATION RESISTANCE: 5000 MEGA OHMS.
 10. MODIFICATION: SURFACE MOUNT.



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES[MM]
TOLERANCES:
ANGULAR: ± 30'
.XX=± .02 [.508]
.XXX=± .005 [.1270]
.XXXX=± .0005 [.0127]
SURFACE FINISH: 63 R_a
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING PER: ANSI Y14.5M-1994

DRAWN		DATE	NAME
THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			Aria
SIZE		DWG. NO.	REV
C		C10584	D
SCALE: 4:1		SHEET 1 OF 1	

CUSTOMER COPY



DESCRIPTION

HEADER, .100 CC

PART NUMBER

G _ C _ _ SFBN-M30