



Your Sensor Partner

SECATEC electronic GmbH
Knappenstrasse 154
D-57581 Katzwinkel

phone: +49 2741 9460-0
fax: +49 2741 8501

mail: info@secatec.de
web: www.secatec.de

technical data

31.10.2013

ind. high-temp. prox. Switch

DC 3-wire

Sn 10 mm flush M30 x 1,5



ident-no.:
55062_CO
type:
Conrad-Typ: 792844

revision index: 000

rated operating distance Sn / mounting	10 mm / flush
assured operating distance Sa	≤ 8 mm
real switching distance Sr / standard target St37	9,0 - 11,0 mm
reduction factors, dependent on alloy	FE360 1,0/Cu 0,2/Al 0,25/Ms 0,35/V2A 0,7
repeat accuracy R	≤ 0,02 x Sr
differential travel H	3...15 * %
supply voltage UB	10 - 30 V DC *
no-load supply current Io	≤ 5 * mA
rated operational current Ie	max. 150 * mA
voltage drop Ud	≤ 2 * V at Ie = 150 * mA
switching frequency f	max. 100 Hz
operating temperature range	-25°C ... +70°C *
output	PNP-NO *
short circuit protection / at current	integrated * / min. --- mA
reverse polarity protection	integrated *
temperature range of active part	-25°C ... +230°C
	* = values of the amplifier
norm conformity / EMC	EN 60947-5-2
dielectric test voltage ac (rms.) Ui	500 V
degree of protection acc. to DIN 60 529	IP67
on/off indication	LED, on the amplifier.
connection	2m Teflon-cable (prox. Switch to amplifier) 2m PUR-cable (current supply) 3 x 0,75mm²
housing material	stainless steel
fixing torque	max. 30 Nm

Applications are inadmissible when safety of persons depends on the function of the device.

SECATEC electronic GmbH reserves the right to change or discontinue these products without notice and does not assume any liability arising by use the product with non-compliance of this specifications.



Schutzvermerk nach DIN 34 beachten			(Zul.Abw.) Allgemeintol. nach DIN ISO 2768-m	Oberfläche nach DIN 3141	Maßstab 1:1 (Werkstoff, Halbzeug) (Rohteil-Nr.) (Modell- oder Gesenk-Nr.)	(Gewicht)
			2013	Datum	Name	(Benennung)
			Bearb.	31.10.	CS	Ind. Hochtemp. Sensor M30x1,5 Sn=10mm bdg.
			Gepr.			(Zeichnungsnummer)
			 Secatec electronic GmbH Knappenstraße 154 D-57581 Katzwinkel (0049)02741/9460-0 www.secatec.de			Blatt
						Bl.
Änderungsindex	Datum	Name	(Urspr.)	(Ers.f.:	(Ers.d.:	