

28/36/48/64/80-Pin, 16-Bit Digital Signal Controllers with High-Resolution PWM and CAN Flexible Data (CAN FD)

Operating Conditions

3.0V to 3.6V, -40°C to +125°C, DC to 100 MIPS

Core: 16-Bit dsPIC33CK CPU

- 32-256 Kbytes of Program Flash with ECC and 8-24K RAM
- · Fast 6-Cycle Divide
- · LiveUpdate
- · Code Efficient (C and Assembly) Architecture
- · 40-Bit Wide Accumulators
- · Single-Cycle (MAC/MPY) with Dual Data Fetch
- Single-Cycle, Mixed-Sign MUL Plus Hardware Divide
- · 32-Bit Multiply Support
- Four Sets of Interrupt Context Saving Registers which Include Accumulator and STATUS for Fast Interrupt Handling
- · Zero Overhead Looping
- · RAM Memory Built-In Self-Test (MBIST)

Clock Management

- · Internal Oscillator
- · Programmable PLLs and Oscillator Clock Sources
- · Reference Clock Output
- · Fail-Safe Clock Monitor (FSCM)
- · Fast Wake-up and Start-up
- · Backup Internal Oscillator

Power Management

- Low-Power Management Modes (Sleep, Idle, Doze)
- Integrated Power-on Reset and Brown-out Reset

High-Speed PWM

- 8 PWM Pairs
- · Up to 250 ps PWM Resolution
- · Dead Time for Rising and Falling Edges
- · Dead-Time Compensation
- Clock Chopping for High-Frequency Operation
- · PWM Support for:
 - DC/DC, AC/DC, inverters, PFC, lighting
 - BLDC, PMSM, ACIM, SRM motors
- · Fault and Current Limit Inputs
- · Flexible Trigger Configuration for ADC Triggering

Timers/Output Compare/Input Capture

- · One General Purpose Timer
- Peripheral Trigger Generator (PTG):
 - Up to 15 trigger sources to other peripheral modules
 - CPU independent state machine-based instruction sequencer
- Nine MCCP/SCCP modules which Include Timer, Capture/Compare and PWM:
 - 1 MCCP
 - 8 SCCPs
 - 16 or 32-bit time base
 - 16 or 32-bit capture
 - 4-deep capture buffer
- Fully Asynchronous Operation, Available in Sleep Modes

Advanced Analog Features

- · High-Speed ADC module:
 - 12-bit with two dedicated SAR ADC cores and one shared SAR ADC core
 - Configurable resolution (up to 12-bit) for each ADC core
 - Up to 3.5 Msps conversion rate per channel at 12-bit resolution
 - Up to 24 input channels
 - Dedicated result buffer for each analog channel
 - Flexible and independent ADC trigger sources
 - Four digital comparators
 - Four oversampling filters for increased resolution
- · Up to Three Analog Comparators:
 - 15 ns analog comparator
- · Up to Three Op Amps
- · Three 12-Bit DACs:
 - Hardware slope compensation

Communication Interfaces

- Three Protocol UARTs with Automated Protocol Handling Support for:
 - LIN 2.2
 - DMX
 - IrDA®
- Three 4-Wire SPI/I²S modules
- · CAN Flexible Data (FD) module
- Three I²C modules with SMBus Support
- · PPS to Allow Function Remap
- Programmable Cyclic Redundancy Check (CRC)
- · Two SENT modules
- Parallel Master Port (PMP)

Direct Memory Access (DMA)

· Four DMA Channels

Debugger Development Support

- In-Circuit and In-Application Programming and Debugging
- · Three Complex, Five Simple Breakpoints
- IEEE 1149.2 Compatible (JTAG) Boundary Scan
- · Trace Buffer and Run-Time Watch

Safety Features

- · Clock Monitor System with Backup Oscillator
- DMT (Deadman Timer)
- ECC (Error Correcting Code)
- WDT (Watchdog Timer)
- CodeGuard™ Security
- CRC (Cyclic Redundancy Check)
- ICSP™ Write Inhibit
- RAM Memory Built-In Self-Test (MBIST)
- · Two-Speed Start-up
- · Fail-Safe Clock Monitoring (FSCM)
- · Backup FRC (BFRC)
- · Capless Internal Voltage Regulator
- · Virtual Pins for Redundancy and Monitoring

Qualification and Class B Support

- AEC-Q100 REV-H (Grade 1: -40°C to +125°C)
 Compliant
- · Class B Safety Library, IEC 60730

dsPIC33CK256MP508 PRODUCT FAMILIES

The device names, pin counts, memory sizes and peripheral availability of each device are listed in Table 1 and Table 2. The following pages show their pinout diagrams.

C33CK256MP508 FAMILY WITH CAN FD
TABLE 1: dsP

KEFO Clock	_	~	_	_	~	_	_	~	_	_	~	_	1	1	_	-	~	1	1
dWd	1	_	0	0	0	_	_	0	0	0	_	_	0	0	0	1	0	0	0
qmA qO	က	က	က	က	2	က	3	3	က	2	3	က	3	3	2	က	က	3	2
12-Bit DAC	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
Analog Comparators	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
stuqtuO MWq	8	8	8	9	4	8	8	8	9	4	8	8	8	9	4	80	8	9	4
СВС	1	1	_	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
ÐТЧ	_	-	-	_	-	_	_	_	_	_	_	_	1	1	_	-	-	1	7
сгс	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
бEI	2	2	2	7	2	7	7	7	7	7	7	7	2	2	7	2	2	7	2
l ₅ C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
IdS	3	3	3	3	3	3	3	3	3	8	3	3	ε	3	3	3	3	3	3
TAAU	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
SENT	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
Slannsd AMD	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
САИ FD	-	~	-	~	~	~	~	~	~	~	~	~	1	1	~	-	~	_	_
MCCP/SCCP	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8
Timers	_	_	_	_	_	_	_	_	_	_	_	_	1	1	_	_	_	1	7
Sləunsdə ODA	24	20	19	16	12	24	20	19	16	12	24	20	19	16	12	20	19	16	12
eluboM OdA	က	က	က	3	က	3	3	3	3	3	3	3	3	3	3	က	က	3	3
MAЯ sts C	24K	24K	24K	24K	24K	16K	16K	16K	16K	16K	8	8	8k	8k	8	쓪	8	8k	8K
Flash	256K	256K	256K	256K	256K	128K	128K	128K	128K	128K	64k	64k	64k	64k	64k	32k	32k	32k	32k
sniq	80	64	48	36	28	80	64	48	36	28	80	64	48	36	28	64	48	36	28
Product Pins	dsPIC33CK256MP508	dsPIC33CK256MP506	dsPIC33CK256MP505	dsPIC33CK256MP503	dsPIC33CK256MP502	dsPIC33CK128MP508	dsPIC33CK128MP506	dsPIC33CK128MP505	dsPIC33CK128MP503	dsPIC33CK128MP502	dsPIC33CK64MP508	dsPIC33CK64MP506	dsPIC33CK64MP505	dsPIC33CK64MP503	dsPIC33CK64MP502	dsPIC33CK32MP506	dsPIC33CK32MP505	dsPIC33CK32MP503	dsPIC33CK32MP502

	KEFO Clock	~	_	~	-	_	_	_	_	_	-	_	_	_	_	_	_	_	_	_
	РМР	_	_	0	0	0	1	_	0	0	0	_	1	0	0	0	_	0	0	0
	qmA qO	3	3	က	3	2	3	3	3	3	2	3	3	3	3	2	3	3	3	2
	12-Bit DAC	က	3	က	က	3	3	3	3	3	က	3	3	3	3	3	3	3	3	3
	Analog Comparators	က	3	က	က	3	3	3	3	3	က	3	3	3	3	က	3	3	3	3
	stuqtuO MW9	80	80	∞	9	4	8	80	8	9	4	8	8	80	9	4	80	80	9	4
	свс	-	_	-	_	_	_	_	_	_	_	_	_	_	_	-	_	_	1	_
	ÐIA	-	_	~	_	_	_	_	_	_	_	_	_	_	_	~	_	_	_	_
	сгс	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	ØΕΙ	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	l ₅ C	က	3	က	က	3	3	3	3	3	က	3	3	3	3	က	3	3	3	3
	IdS	က	3	က	က	က	က	3	က	က	က	3	3	3	3	က	3	3	3	3
	TAAU	က	3	က	က	3	3	3	3	3	က	3	3	3	3	က	3	3	3	3
	SENT	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
FD	DMA Channels	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
CAN	СРИ ГР	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
THOUT (MCCP/SCCP	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8	1/8
	Timers	-	1	_	_	1	1	1	1	1	_	1	1	1	1	_	1	1	1	7
_≺ W	Slənnsdə ODA	24	20	19	16	12	24	20	19	16	12	24	20	19	16	12	20	19	16	12
AMI	ADC Module	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
508 F	MAЯ sts O	24K	24K	24K	24K	24K	16K	16K	16K	16K	16K	8k	8K	8k	8k	8	8k	8	8k	8
56MP	Flash	256K	256K	256K	256K	256K	128K	128K	128K	128K	128K	64k	64k	64k	64k	64k	32k	32k	32k	32k
3CK2	sni¶	80	64	48	36	28	80	64	48	36	28	80	64	48	36	28	64	48	36	28
TABLE 2: dsPIC33CK256MP508 FAMILY W	Product Pins	dsPIC33CK256MP208	dsPIC33CK256MP206	dsPIC33CK256MP205	dsPIC33CK256MP203	dsPIC33CK256MP202	dsPIC33CK128MP208	dsPIC33CK128MP206	dsPIC33CK128MP205	dsPIC33CK128MP203	dsPIC33CK128MP202	dsPIC33CK64MP208	dsPIC33CK64MP206	dsPIC33CK64MP205	dsPIC33CK64MP203	dsPIC33CK64MP202	dsPIC33CK32MP206	dsPIC33CK32MP205	dsPIC33CK32MP203	dsPIC33CK32MP202
ĭ		ő	ő	ő	ő	ő	ŏ	ő	ő	ŏ	ő	ő	ő	ő	ő	ő	ő	ő	ğ	ő

Pin Diagrams




TABLE 3: 28-PIN SSOP⁽¹⁾

Pin#	Function	Pin#	Function
1	OA1IN-/ANA1/RA1	15	PGC3/RP38/SCL2/RB6
2	OA1IN+/AN9/RA2	16	TDO/AN2/CMP3A/ RP39 /SDA3/RB7
3	DACOUT1/AN3/CMP1C/RA3	17	PGD1/AN10/ RP40 /SCL1/RB8
4	AN4/CMP3B/IBIAS3/RA4	18	PGC1/AN11/ RP41 /SDA1/RB9
5	AVDD	19	Vss
6	AVss	20	VDD
7	VDD	21	TMS/ RP42 /PWM3H/RB10 ⁽²⁾
8	Vss	22	TCK/RP43/PWM3L/RB11
9	OSCI/CLKI/AN5/RP32/RB0	23	TDI/ RP44 /PWM2H/RB12
10	OSCO/CLKO/AN6/RP33/RB1 ⁽³⁾	24	RP45/PWM2L/RB13
11	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/ RP34 / SCL3/INT0/RB2	25	RP46/PWM1H/RB14
12	PGD2/OA2IN-/AN8/RP35/RB3	26	RP47/PWM1L/RB15
13	PGC2/OA2IN+/RP36/RB4	27	MCLR
14	PGD3/ RP37 /SDA2/RB5	28	OA1OUT/AN0/CMP1A/IBIAS0/RA0

Note 1: RPn represents remappable peripheral functions.

^{2:} A pull-up resistor is connected to this pin during power-up and programming.

^{3:} This pin is toggled during programming.

Pin Diagrams (Continued)




TABLE 4: 28-PIN UQFN⁽¹⁾

Pin#	Function	Pin#	Function
1	RP46/PWM1H/RB14	15	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/RP34/SCL3/INT0/RB2
2	RP47/PWM1L/RB15	16	PGD2/OA2IN-/AN8/ RP35 /RB3
3	MCLR	17	PGC2/OA2IN+/RP36/RB4
4	OA1OUT/AN0/CMP1A/IBIAS0/RA0	18	PGD3/RP37/SDA2/RB5
5	OA1IN-/ANA1/RA1	19	PGC3/RP38/SCL2/RB6
6	OA1IN+/AN9/RA2	20	TDO/AN2/CMP3A/RP39/SDA3/RB7
7	DACOUT1/AN3/CMP1C/RA3	21	PGD1/AN10/ RP40 /SCL1/RB8
8	AN4/CMP3B/IBIAS3/RA4	22	PGC1/AN11/ RP41 /SDA1/RB9
9	AVDD	23	Vss
10	AVss	24	VDD
11	VDD	25	TMS/ RP42 /PWM3H/RB10 ⁽²⁾
12	Vss	26	TCK/ RP43 /PWM3L/RB11
13	OSCI/CLKI/AN5/RP32/RB0	27	TDI/ RP44 /PWM2H/RB12
14	OSCO/CLKO/AN6/RP33/RB1(3)	28	RP45/PWM2L/RB13

Note 1: RPn represents remappable peripheral functions.

- 2: A pull-up resistor is connected to this pin during power-up and programming.
- 3: This pin is toggled during programming.

Pin Diagrams (Continued)





TABLE 5: 36-PIN UQFN⁽¹⁾

Pin#	Function	Pin#	Function
1	RP46/PWM1H/RB14	19	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/RP34/SCL3/INT0/RB2
2	RP47/PWM1L/RB15	20	PGD2/OA2IN-/AN8/ RP35 /RB3
3	MCLR	21	PGC2/OA2IN+/RP36/RB4
4	AN12/ANN0/ RP48 /RC0	22	Vss
5	OA1OUT/AN0/CMP1A/IBIAS0/RA0	23	VDD
6	OA1IN-/ANA1/RA1	24	PGD3/RP37/PWM6L/SDA2/RB5
7	OA1IN+/AN9/RA2	25	PGC3/RP38/PWM6H/SCL2/RB6
8	DACOUT1/AN3/CMP1C/RA3	26	TDO/AN2/CMP3A/RP39/SDA3/RB7
9	OA3OUT/AN4/CMP3B/IBIAS3/RA4	27	PGD1/AN10/ RP40 /SCL1/RB8
10	AVDD	28	PGC1/AN11/ RP41 /SDA1/RB9
11	AVss	29	RP52/PWM5H/ASDA2/RC4
12	OA3IN-/AN13/CMP1B/ISRC0/RP49/RC1	30	RP53/PWM5L/ASCL2/RC5
13	OA3IN+/AN14/CMP2B/ISRC1/RP50/RC2	31	Vss
14	VDD	32	VDD
15	Vss	33	TMS/ RP42 /PWM3H/RB10 ⁽²⁾
16	AN15/CMP2A/IBIAS2/RP51/RC3	34	TCK/RP43/PWM3L/RB11
17	OSCI/CLKI/AN5/RP32/RB0	35	TDI/ RP44 /PWM2H/RB12
18	OSCO/CLKO/AN6/ RP33 /RB1 ⁽³⁾	36	RP45/PWM2L/RB13

Note 1: RPn represents remappable peripheral functions.

- 2: A pull-up resistor is connected to this pin during power-up and programming.
- 3: This pin is toggled during programming.





net as the large center pad.

TABLE 6: 48-PIN TQFP, UQFN⁽¹⁾

Pin#	Function	Pin#	Function
1	RP46/PWM1H/RB14	25	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/RP34/SCL3/INT0/RB2
2	RP47/PWM1L/RB15	26	PGD2/OA2IN-/AN8/ RP35 /RB3
3	RP60/PWM8H/RC12	27	PGC2/OA2IN+/RP36/RB4
4	RP61/PWM8L/RC13	28	RP56/ASDA1/SCK2/RC8
5	MCLR	29	RP57/ASCL1/SDI2/RC9
6	ANN2/ RP77 /RD13	30	RP72/SDO2/PCI19/RD8
7	AN12/ANN0/RP48/RC0	31	Vss
8	OA1OUT/AN0/CMP1A/IBIAS0/RA0	32	VDD
9	OA1IN-/ANA1/RA1	33	PGD3/RP37/PWM6L/SDA2/RB5
10	OA1IN+/AN9/RA2	34	PGC3/RP38/PWM6H/SCL2/RB6
11	DACOUT1/AN3/CMP1C/RA3	35	TDO/AN2/CMP3A/RP39/SDA3/RB7
12	OA3OUT/AN4/CMP3B/IBIAS3/RA4	36	PGD1/AN10/ RP40 /SCL1/RB8
13	AVDD	37	PGC1/AN11/ RP41 /SDA1/RB9
14	AVss	38	RP52/PWM5H/ASDA2/RC4
15	OA3IN-/AN13/CMP1B/ISRC0/RP49/RC1	39	RP53/PWM5L/ASCL2/RC5
16	OA3IN+/AN14/CMP2B/ISRC1/RP50/RC2	40	RP58/PWM7H/RC10
17	AN17/ANN1/IBIAS1/ RP54 /RC6	41	RP59/PWM7L/RC11
18	VDD	42	Vss
19	Vss	43	VDD
20	AN15/CMP2A/IBIAS2/RP51/RC3	44	RP65/PWM4H/RD1
21	OSCI/CLKI/AN5/RP32/RB0	45	TMS/ RP42 /PWM3H/RB10 ⁽²⁾
22	OSCO/CLKO/AN6/RP33/RB1(3)	46	TCK/RP43/PWM3L/RB11
23	AN18/CMP3C/ISRC3/RP74/RD10	47	TDI/ RP44 /PWM2H/RB12
24	AN16/ISRC2/ RP55 /RC7	48	RP45/PWM2L/RB13

Note 1: RPn represents remappable peripheral functions.

^{2:} A pull-up resistor is connected to this pin during power-up and programming.

^{3:} This pin is toggled during programming.




TABLE 7: 64-PIN TQFP, QFN⁽¹⁾


Pin#	Function	Pin#	Function
1	RP46/PWM1H/PMD5/RB14	33	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/RP34/SCL3/INT0/RB2
2	RP47/PWM1L/PMD6/RB15	34	PGD2/OA2IN-/AN8/ RP35 /RB3
3	RP60/PWM8H/PMD7/RC12	35	PGC2/OA2IN+/RP36/RB4
4	RP61/PWM8L/PMA5/RC13	36	RP56/ASDA1/SCK2/RC8
5	RP62/PWM6H/PMA4/RC14	37	RP57/ASCL1/SDI2/RC9
6	RP63/PWM6L/PMA3/RC15	38	RP73/PCI20/RD9
7	MCLR	39	RP72/SDO2/PCI19/RD8
8	RP79/PCI22/PMA2/RD15	40	Vss
9	Vss	41	VDD
10	VDD	42	RP71/PMD15/RD7
11	RP78/PCI21/RD14	43	RP70/PMD14/RD6
12	ANN2/ RP77 /RD13	44	RP69/PMA15/PMCS2/RD5
13	AN12/ANN0/RP48/RC0	45	PGD3/RP37/SDA2/PMA14/PMCS1/PSCS/RB5
14	OA1OUT/AN0/CMP1A/IBIAS0/RA0	46	PGC3/RP38/SCL2/RB6
15	OA1IN-/ANA1/RA1	47	TDO/AN2/CMP3A/RP39/SDA3/RB7
16	OA1IN+/AN9/PMA6/RA2	48	PGD1/AN10/ RP40 /SCL1/RB8
17	DACOUT1/AN3/CMP1C/RA3	49	PGC1/AN11/ RP41 /SDA1/RB9
18	OA3OUT/AN4/CMP3B/IBIAS3/RA4	50	RP52/PWM5H/ASDA2/RC4
19	AVDD	51	RP53/PWM5L/ASCL2/PMWR/PMENB/PSWR/RC5
20	AVss	52	RP58/PWM7H/PMRD/PMWR/PSRD/RC10
21	RP76 /RD12	53	RP59/PWM7L/RC11
22	OA3IN-/AN13/CMP1B/ISRC0/RP49/PMA7/RC1	54	RP68/ASDA3/RD4
23	OA3IN+/AN14/CMP2B/ISRC1/ RP50 /PMD13/PMA13/RC2	55	RP67/ASCL3/RD3
24	AN17/ANN1/IBIAS1/ RP54 /PMD12/PMA12/RC6	56	Vss
25	VDD	57	VDD
26	Vss	58	RP66/RD2
27	AN15/CMP2A/IBIAS2/RP51/PMD11/PMA11/RC3	59	RP65/PWM4H/RD1
28	OSCI/CLKI/AN5/RP32/PMD10/PMA10/RB0	60	RP64/PWM4L/PMD0/RD0
29	OSCO/CLKO/AN6/ RP33 /PMA1/PMALH/PSA1/RB1 ⁽³⁾	61	TMS/ RP42 /PWM3H/PMD1/RB10 ⁽²⁾
30	AN19/CMP2C/RP75/PMA0/PMALL/PSA0/RD11	62	TCK/ RP43 /PWM3L/PMD2/RB11
31	AN18/CMP3C/ISRC3/RP74/PMD9/PMA9/RD10	63	TDI/ RP44 /PWM2H/PMD3/RB12
32	AN16/ISRC2/RP55/PMD8/PMA8/RC7	64	RP45/PWM2L/PMD4/RB13

Note 1: RPn represents remappable peripheral functions.

^{2:} A pull-up resistor is connected to this pin during power-up and programming.

^{3:} This pin is toggled during programming.

Pin Diagrams (Continued) 80-Pin TQFP



Note: Shaded pins are up to 5 VDC tolerant.

TABLE 8: 80-PIN TQFP⁽¹⁾

Pin#	Function	Pin#	Function
1	RP46/PWM1H/PMD5/RB14	41	OA2OUT/AN1/AN7/ANA0/CMP1D/CMP2D/CMP3D/RP34/SCL3/INT0/RB2
2	AN20/RE0	42	RE8
3	RP47/PWM1L/PMD6/RB15	43	PGD2/OA2IN-/AN8/ RP35 /RB3
4	AN21/RE1	44	RE9
5	RP60/PWM8H/PMD7/RC12	45	PGC2/OA2IN+/RP36/RB4
6	RP61/PWM8L/PMA5/RC13	46	RP56/ASDA1/SCK2/RC8
7	RP62/PWM6H/PMA4/RC14	47	RP57/ASCL1/SDI2/RC9
8	RP63/PWM6L/PMA3/RC15	48	RP73/PCI20/RD9
9	MCLR	49	RP72/SDO2/PCI19/RD8
10	RP79/PCI22/PMA2/RD15	50	Vss
11	Vss	51	VDD
12	VDD	52	RP71/PMD15/RD7
13	RP78/PCI21/RD14	53	RP70/PMD14/RD6
14	ANN2/ RP77 /RD13	54	RP69/PMA15/PMCS2/RD5
15	AN12/ANN0/RP48/RC0	55	PGD3/RP37/SDA2/PMA14/PMCS1/PSCS/RB5
16	OA1OUT/AN0/CMP1A/IBIAS0/RA0	56	PGC3/RP38/SCL2/RB6
17	AN22/RE2	57	RE10
18	OA1IN-/ANA1/RA1	58	TDO/AN2/CMP3A/RP39/SDA3/RB7
19	AN23/RE3	59	RE11
20	OA1IN+/AN9/PMA6/RA2	60	PGD1/AN10/ RP40 /SCL1/RB8
21	DACOUT1/AN3/CMP1C/RA3	61	PGC1/AN11/ RP41 /SDA1/RB9
22	RE4	62	RE12
23	OA3OUT/AN4/CMP3B/IBIAS3/RA4	63	RP52/PWM5H/ASDA2/RC4
24	RE5	64	RE13
25	AVDD	65	RP53/PWM5L/ASCL2/PMWR/PMENB/PSWR/RC5
26	AVss	66	RP58/PWM7H/PMRD/PMWR/PSRD/RC10
27	RP76 /RD12	67	RP59/PWM7L/RC11
28	OA3IN-/AN13/CMP1B/ISRC0/RP49/PMA7/RC1	68	RP68/ASDA3/RD4
29	OA3IN+/AN14/CMP2B/ISRC1/RP50/PMD13/PMA13/RC2	69	RP67/ASCL3/RD3
30	AN17/ANN1/IBIAS1/RP54/PMD12/PMA12/RC6	70	Vss
31	VDD	71	VDD
32	Vss	72	RP66/RD2
33	AN15/CMP2A/IBIAS2/RP51/PMD11/PMA11/RC3	73	RP65/PWM4H/RD1
34	OSCI/CLKI/AN5/RP32/PMD10/PMA10/RB0	74	RP64/PWM4L/PMD0/RD0
35	OSCO/CLKO/AN6/RP33/PMA1/PMALH/PSA1/RB1(3)	75	TMS/RP42/PWM3H/PMD1/RB10 ⁽²⁾
36	AN19/CMP2C/RP75/PMA0/PMALL/PSA0/RD11	76	TCK/RP43/PWM3L/PMD2/RB11
37	RE6	77	RE14
38	AN18/CMP3C/ISRC3/RP74/PMD9/PMA9/RD10	78	TDI/RP44/PWM2H/PMD3/RB12
39	RE7	79	RE15
40	AN16/ISRC2/RP55/PMD8/PMA8/RC7	80	RP45/PWM2L/PMD4/RB13

Note 1: RPn represents remappable peripheral functions.

^{2:} A pull-up resistor is connected to this pin during power-up and programming.

^{3:} This pin is toggled during programming.

Table of Contents

1.0	Device Overview	17
2.0	Guidelines for Getting Started with 16-Bit Digital Signal Controllers	23
3.0	CPU	
4.0	Memory Organization	41
5.0	Flash Program Memory	
6.0	Resets	
7.0	Interrupt Controller	99
8.0	I/O Ports	119
9.0	Oscillator with High-Frequency PLL	183
10.0	Direct Memory Access (DMA) Controller	207
11.0	Controller Area Network (CAN FD) Module	217
12.0		261
13.0		295
14.0	High-Speed Analog Comparator with Slope Compensation DAC	
15.0	Quadrature Encoder Interface (QEI)	335
16.0	Universal Asynchronous Receiver Transmitter (UART)	
17.0	Serial Peripheral Interface (SPI)	377
18.0	Inter-Integrated Circuit (I ² C)	395
19.0	Parallel Master Port (PMP)	405
20.0	Single-Edge Nibble Transmission (SENT)	419
	Timer1	
22.0	Capture/Compare/PWM/Timer Modules (SCCP/MCCP)	433
23.0	Configurable Logic Cell (CLC)	447
	Peripheral Trigger Generator (PTG)	
25.0	32-Bit Programmable Cyclic Redundancy Check (CRC) Generator	475
26.0	Current Bias Generator (CBG)	479
27.0	Operational Amplifier	483
28.0	Deadman Timer (DMT)	487
29.0	Power-Saving Features	495
30.0	Special Features	507
31.0	Instruction Set Summary	533
32.0	Development Support	543
33.0	Electrical Characteristics	547
34.0	Packaging Information	583
Appe	endix A: Revision History	609
Index	X	611
The I	Microchip Website	619
Custo	omer Change Notification Service	619
Custo	omer Support	619
Drod	luct Identification System	621

TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, please contact the Marketing Communications Department via E-mail at docerrors@microchip.com. We welcome your feedback.

Most Current Data Sheet

To obtain the most up-to-date version of this data sheet, please register at our Worldwide Website at:

http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS30000000A is version A of document DS30000000).

Errata

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, please check with one of the following:

- Microchip's Worldwide Website; http://www.microchip.com
- Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include literature number) you are using.

Customer Notification System

Register on our website at www.microchip.com to receive the most current information on all of our products.

Referenced Sources

This device data sheet is based on the following individual chapters of the "dsPIC33/PIC24 Family Reference Manual". These documents should be considered as the general reference for the operation of a particular module or device feature.

Note 1: To access the documents listed below, browse to the documentation section of the dsPIC33CK256MP508 product page of the Microchip website (www.microchip.com) or select a family reference manual section from the following list.

In addition to parameters, features and other documentation, the resulting page provides links to the related family reference manual sections.

- "Introduction" (www.microchip.com/DS70573)
- "dsPIC33E Enhanced CPU" (www.microchip.com/DS70005158)
- "dsPIC33E/PIC24E Program Memory" (www.microchip.com/DS70000613)
- "Data Memory" (www.microchip.com/DS70595)
- "Dual Partition Flash Program Memory" (www.microchip.com/DS70005156)
- "Flash Programming" (www.microchip.com/DS70609)
- "Reset" (www.microchip.com/DS70602)
- "Interrupts" (www.microchip.com/DS70000600)
- "I/O Ports with Edge Detect" (www.microchip.com/DS70005322)
- "Oscillator Module with High-Speed PLL" (www.microchip.com/DS70005255)
- "Direct Memory Access Controller (DMA)" (www.microchip.com/DS39742)
- "CAN Flexible Data-Rate (FD) Protocol Module" (www.microchip.com/DS70005340)
- "High-Resolution PWM with Fine Edge Placement" (www.microchip.com/DS70005320)
- "12-Bit High-Speed, Multiple SARs A/D Converter (ADC)" (www.microchip.com/DS70005213)
- "High-Speed Analog Comparator Module" (www.microchip.com/DS70005280)
- "Quadrature Encoder Interface (QEI)" (www.microchip.com/DS70000601)
- "Multiprotocol Universal Asynchronous Receiver Transmitter (UART) Module" (www.microchip.com/DS70005288)
- "Serial Peripheral Interface (SPI) with Audio Codec Support" (www.microchip.com/DS70005136)
- "Inter-Integrated Circuit (I²C)" (www.microchip.com/DS70000195)
- "Parallel Master Port (PMP)" (www.microchip.com/DS70005344)
- "Single-Edge Nibble Transmission (SENT) Module" (www.microchip.com/DS70005145)
- "Timer1 Module" (www.microchip.com/DS70005279)
- "Capture/Compare/PWM/Timer (MCCP and SCCP)" (www.microchip.com/DS33035)
- "Configurable Logic Cell (CLC)" (www.microchip.com/DS70005298)
- "Peripheral Trigger Generator (PTG)" (www.microchip.com/DS70000669)
- "32-Bit Programmable Cyclic Redundancy Check (CRC)" (www.microchip.com/DS30009729)
- "Current Bias Generator (CBG)" (www.microchip.com/DS70005253)
- "Deadman Timer" (www.microchip.com/DS70005155)
- "Watchdog Timer and Power-Saving Modes" (www.microchip.com/DS70615)
- "CodeGuard™ Security" (www.microchip.com/DS70634)
- "Dual Watchdog Timer" (www.microchip.com/DS70005250)
- "Programming and Diagnostics" (www.microchip.com/DS70608)

1.0 DEVICE OVERVIEW

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive resource. To complement the information in this data sheet, refer to the related section of the "dsPIC33/PIC24 Family Reference Manual", which is available from the Microchip website (www.microchip.com).

2: Some registers and associated bits described in this section may not be available on all devices. Refer to Section 4.0 "Memory Organization" in this data sheet for device-specific register and bit information. This document contains device-specific information for the dsPIC33CK256MP508 Digital Signal Controller (DSC) and Microcontroller (MCU) devices.

dsPIC33CK256MP508 devices contain extensive Digital Signal Processor (DSP) functionality with a high-performance, 16-bit MCU architecture.

Figure 1-1 shows a general block diagram of the core and peripheral modules of the dsPIC33CK256MP508 family. Table 1-1 lists the functions of the various pins shown in the pinout diagrams.

FIGURE 1-1: dsPIC33CK256MP508 FAMILY BLOCK DIAGRAM⁽¹⁾




TABLE 1-1: PINOUT I/O DESCRIPTIONS

Pin Name ⁽¹⁾	Pin Type	Buffer Type	PPS	Description
AN0-AN23	I	Analog	No	Analog input channels
ANA0-ANA1	I	Analog	No	Analog alternate inputs
ANN0-ANN2	I	Analog	No	Analog negative inputs
ADTRG	I	ST	Yes	ADC Trigger Input 31
CLKI	I	ST/ CMOS	No	External Clock (EC) source input. Always associated with OSCI pin function.
CLKO	0	_	No	Oscillator crystal output. Connects to crystal or resonator in Crystal Oscillator mode. Optionally functions as CLKO in RC and EC modes. Always associated with OSCO pin function.
OSCI	I	ST/ CMOS	No	Oscillator crystal input. ST buffer when configured in RC mode; CMOS otherwise.
osco	I/O	_	No	Oscillator crystal output. Connects to crystal or resonator in Crystal Oscillator mode. Optionally functions as CLKO in RC and EC modes.
REFCLKO REFOI	0	— ST	Yes Yes	Reference clock output Reference clock input
INT0	i	ST	No	External Interrupt 0
INT1	i	ST	Yes	External Interrupt 1
INT2	i	ST	Yes	External Interrupt 2
INT3	I	ST	Yes	External Interrupt 3
IOCA<4:0>	ı	ST	No	Interrupt-on-Change input for PORTA
IOCB<15:0>	- 1	ST	No	Interrupt-on-Change input for PORTB
IOCC<15:0>	I	ST	No	Interrupt-on-Change input for PORTC
IOCD<15:0>		ST	No	Interrupt-on-Change input for PORTD
IOCE<15:0>	1	ST	No	Interrupt-on-Change input for PORTE
RP32-RP71	I/O	ST	Yes	Remappable I/O ports
RA0-RA4	I/O	ST	No	PORTA is a bidirectional I/O port
RB0-RB15	I/O	ST	No	PORTB is a bidirectional I/O port
RC0-RC15	I/O	ST	No	PORTC is a bidirectional I/O port
RD0-RD15	I/O	ST	No	PORTD is a bidirectional I/O port
RE0-RE15	I/O	ST	No	PORTE is a bidirectional I/O port
T1CK	I	ST	Yes	Timer1 external clock input
CAN1RX	I	ST	Yes	CAN1 receive input
CAN1	0	_	Yes	CAN1 transmit output
<u>U1CTS</u>	I	ST	Yes	UART1 Clear-to-Send
U1RTS	0	_	Yes	UART1 Request-to-Send
U1RX		ST	Yes	UART1 receive
U1TX	0		Yes	UART1 transmit
U1DSR		ST	Yes	UART1 Data-Set-Ready
U1DTR	0	_	Yes	UART1 Data-Terminal-Ready

Legend:CMOS = CMOS compatible input or output
ST = Schmitt Trigger input with CMOS levels
PPS = Peripheral Pin SelectAnalog = Analog input
O = Output
TTL = TTL input bufferP = Power
I = Input
DIG = Digital

Note 1: Not all pins are available in all package variants. See the "Pin Diagrams" section for pin availability.

- 2: PWM4L and PWM4H pins are available on PPS as well as dedicated.
- **3:** SPI2 supports dedicated pins as well as PPS on 48, 64 and 80-pin devices.
- **4:** Only 48, 64 and 80-pin devices have all eight PWM output pairs on dedicated pins. Refer to the "Pin Diagrams" for PWM pin availability on other packages.

TABLE 1-1: PINOUT I/O DESCRIPTIONS (CONTINUED)

Pin Name ⁽¹⁾	Pin Type	Buffer Type	PPS	Description
U2CTS	I	ST	Yes	UART2 Clear-to-Send
U2RTS	0	_	Yes	UART2 Request-to-Send
U2RX	1	ST	Yes	UART2 receive
U2TX	0	_	Yes	UART2 transmit
U2DSR	1	ST	Yes	UART2 Data-Set-Ready
U2DTR	0	_	Yes	UART2 Data-Terminal-Ready
U3CTS	I	ST	Yes	UART3 Clear-to-Send
U3RTS	0	_	Yes	UART3 Request-to-Send
U3RX	- 1	ST	Yes	UART3 receive
U3TX	0	_	Yes	UART3 transmit
U3DSR	- 1	ST	Yes	UART3 Data-Set-Ready
U3DTR	Ο	_	Yes	UART3 Data-Terminal-Ready
SCK1	I/O	ST	Yes	Synchronous serial clock input/output for SPI1
SDI1	- 1	ST	Yes	SPI1 data in
SDO1	0	_	Yes	SPI1 data out
SS1	I/O	ST	Yes	SPI1 slave synchronization or frame pulse I/O
SCK2	I/O	ST	Yes ⁽³⁾	
SDI2	- 1	ST	Yes ⁽³⁾	SPI2 data in
SDO2	0	_	Yes ⁽³⁾	SPI2 data out
SS2	I/O	ST	Yes ⁽³⁾	SPI2 slave synchronization or frame pulse I/O
SCK3	I/O	ST	Yes	Synchronous serial clock input/output for SPI3
SDI3	- 1	ST	Yes	SPI3 data in
SDO3	0	_	Yes	SPI3 data out
SS3	I/O	ST	Yes	SPI3 slave synchronization or frame pulse I/O
SCL1	I/O	ST	No	Synchronous serial clock input/output for I2C1
SDA1	I/O	ST	No	Synchronous serial data input/output for I2C1
ASCL1	I/O	ST	No	Alternate synchronous serial clock input/output for I2C1
ASDA1	I/O	ST	No	Alternate synchronous serial data input/output for I2C1
SCL2	I/O	ST	No	Synchronous serial clock input/output for I2C2
SDA2	I/O	ST	No	Synchronous serial data input/output for I2C2
ASCL2	I/O	ST	No	Alternate synchronous serial clock input/output for I2C2
ASDA2	I/O	ST	No	Alternate synchronous serial data input/output for I2C2
SCL3	I/O	ST	No	Synchronous serial clock input/output for I2C3
SDA3	I/O	ST	No	Synchronous serial data input/output for I2C3
ASCL3	I/O	ST	No	Alternate synchronous serial clock input/output for I2C3
ASDA3	I/O	ST	No	Alternate synchronous serial data input/output for I2C3
QEIA1-QEIA2	I	ST	Yes	QEI Inputs A1 and A2
QEIB1-QEIB2	- 1	ST	Yes	QEI Inputs B1 and B2
QEINDX1-QEINDX2	- 1	ST	Yes	QEI Index Inputs 1 and 2
QEIHOM1-QEIHOM2	- 1	ST	Yes	QEI Home Inputs 1 and 2
QEICMP1-QEICMP2	0		Yes	QEI Comparator Outputs 1 and 2
SENT1-SENT2	I	ST	Yes	SENT1 and SENT2 inputs
SENT1OUT-SENT2OUT	0	_	Yes	SENT1 and SENT2 outputs

Legend:CMOS = CMOS compatible input or output
ST = Schmitt Trigger input with CMOS levels
PPS = Peripheral Pin SelectAnalog = Analog input
O = Output
TTL = TTL input bufferP = Power
I = Input
DIG = Digital

- Note 1: Not all pins are available in all package variants. See the "Pin Diagrams" section for pin availability.
 - 2: PWM4L and PWM4H pins are available on PPS as well as dedicated.
 - 3: SPI2 supports dedicated pins as well as PPS on 48, 64 and 80-pin devices.
 - **4:** Only 48, 64 and 80-pin devices have all eight PWM output pairs on dedicated pins. Refer to the "Pin Diagrams" for PWM pin availability on other packages.

TABLE 1-1: PINOUT I/O DESCRIPTIONS (CONTINUED)

TABLE 1-1: TINGOT IN BESONII TIONG (GONTINGEB)				
Pin Name ⁽¹⁾	Pin Type	Buffer Type	PPS	Description
TMS	- 1	ST	No	JTAG Test mode select pin
TCK	- 1	ST	No	JTAG test clock input pin
TDI	I	ST	No	JTAG test data input pin
TDO	0	_	No	JTAG test data output pin
PCI8-PCI18	- 1	ST	Yes	PWM PCI Inputs 8 through 18
PCI19-PCI22	- 1	ST	No	PWM PCI Inputs 19 through 22
PWM1L-PWM8L ⁽²⁾	0	_	No ⁽⁴⁾	PWM Low Outputs 1 through 8
PWM1H-PWM8H ⁽²⁾	0	_	No ⁽⁴⁾	PWM High Outputs 1 through 8
PWMEA-PWMED	0		Yes	PWM Event Outputs A through D
CMP1A-CMP3A	I	Analog	No	Comparator Channels 1A through 3A inputs
CMP1B-CMP3B	- 1	Analog	No	Comparator Channels 1B through 3B inputs
CMP1C-CMP3C	I	Analog	No	Comparator Channels 1C through 3C inputs
CMP1D-CMP3D	I	Analog	No	Comparator Channels 1D through 3D inputs
DACOUT1	0	_	No	DAC output voltage
TCKI1-TCKI9	I	ST	Yes	SCCP/MCCP Timer Inputs 1 through 9
ICM1-ICM9	- 1	ST	Yes	SCCP/MCCP Capture Inputs 1 through 9
OCFA-OCFD	0	_	Yes	SCCP/MCCP Fault Inputs A through D
OCM1-OCM9	0	_	Yes	SCCP/MCCP Compare Outputs 1 through 9
IBIAS0-IBIAS3	0	Analog	No	50 μA Constant-Current Outputs 0 through 3
ISRC0-ISRC3	0	Analog	No	10 μA Constant-Current Outputs 0 through 3
OA1IN+	I	_	No	Op Amp 1+ Input
OA1IN-	- 1	_	No	Op Amp 1- Input
OA1OUT	0	_	No	Op Amp 1 Output
OA2IN+	- 1	_	No	Op Amp 2+ Input
OA2IN-	I	_	No	Op Amp 2- Input
OA2OUT	0	_	No	Op Amp 2 Output
OA3IN+	I	_	No	Op Amp 3+ Input
OA3IN-	I	_	No	Op Amp 3- Input
OA3OUT	0	_	No	Op Amp 3 Output
PMA0/PMALL	0	ST/TTL	No	PMP Address 0 or address latch low
PMA1/PMALH	0	ST/TTL	No	PMP Address 1 or address latch high
PMA14/PMCS1	0	ST/TTL	No	PMP Address 14 or Chip Select 1
PMA15/PMCS2	0	ST/TTL	No	PMP Address 15 or Chip Select 2
PMA2-PMA13	0	ST/TTL	No	PMP Address Lines 2-13
PMD0-PMD15	I/O	ST/TTL	No	PMP Data Lines 0-15
PMRD/PMWR	0	ST/TTL	No	PMP read or read/write signal
PMWR/PMENB	0	ST/TTL	No	PMP write or data enable signal
PSA0		ST/TTL	No	PMP Slave Address 0
PSA1	!	ST/TTL	No	PMP Slave Address 1
PSCS		ST/TTL	No	PMP slave chip select
PSRD	!	ST/TTL	No	PMP slave write
PSWR	I	ST/TTL	No	PMP slave read
CLCINA-CLCIND		ST	Yes	CLC Inputs A through D
CLC10UT-CLC40UT	0	_	Yes	CLC Outputs 1 through 4

Legend:CMOS = CMOS compatible input or output
ST = Schmitt Trigger input with CMOS levels
PPS = Peripheral Pin SelectAnalog = Analog input
O = Output
TTL = TTL input bufferP = Power
I = Input
DIG = Digital

Note 1: Not all pins are available in all package variants. See the "Pin Diagrams" section for pin availability.

- 2: PWM4L and PWM4H pins are available on PPS as well as dedicated.
- 3: SPI2 supports dedicated pins as well as PPS on 48, 64 and 80-pin devices.
- **4:** Only 48, 64 and 80-pin devices have all eight PWM output pairs on dedicated pins. Refer to the "Pin Diagrams" for PWM pin availability on other packages.

TABLE 1-1: PINOUT I/O DESCRIPTIONS (CONTINUED)

Pin Name ⁽¹⁾	Pin Type	Buffer Type	PPS	Description	
ADTRG31	I	ST	No	External ADC trigger source	
PGD1 PGC1	I/O I	ST ST	No No	Data I/O pin for Programming/Debugging Communication Channel 1 Clock input pin for Programming/Debugging Communication Channel 1	
PGD2 PGC2	I/O I	ST ST	No No	Data I/O pin for Programming/Debugging Communication Channel 2 Clock input pin for Programming/Debugging Communication Channel 2	
PGD3 PGC3	I/O I	ST ST	No No	Data I/O pin for Programming/Debugging Communication Channel 3 Clock input pin for Programming/Debugging Communication Channel 3	
MCLR	I/P	ST	No	Master Clear (Reset) input. This pin is an active-low Reset to the device.	
AVDD	Р	Р	No	Positive supply for analog modules. This pin must be connected at all times.	
AVss	Р	Р	No	Ground reference for analog modules. This pin must be connected at all times.	
VDD	Р	_	No	Positive supply for peripheral logic and I/O pins	
Vss	Р	_	No	Ground reference for logic and I/O pins	

Legend:CMOS = CMOS compatible input or output
ST = Schmitt Trigger input with CMOS levelsAnalog = Analog input
O = OutputP = Power
I = InputPPS = Peripheral Pin SelectTTL = TTL input bufferDIG = Digital

Note 1: Not all pins are available in all package variants. See the "Pin Diagrams" section for pin availability.

- 2: PWM4L and PWM4H pins are available on PPS as well as dedicated.
- 3: SPI2 supports dedicated pins as well as PPS on 48, 64 and 80-pin devices.
- **4:** Only 48, 64 and 80-pin devices have all eight PWM output pairs on dedicated pins. Refer to the "Pin Diagrams" for PWM pin availability on other packages.

NOTES:			

2.0 GUIDELINES FOR GETTING STARTED WITH 16-BIT DIGITAL SIGNAL CONTROLLERS

2.1 Basic Connection Requirements

Getting started with the family devices of the dsPIC33CK256MP508 requires attention to a minimal set of device pin connections before proceeding with development. The following is a list of pin names which must always be connected:

- All VDD and Vss pins (see Section 2.2 "Decoupling Capacitors")
- All AVDD and AVSS pins regardless if ADC module is not used (see Section 2.2 "Decoupling Capacitors")
- MCLR pin (see Section 2.3 "Master Clear (MCLR) Pin")
- PGCx/PGDx pins used for In-Circuit Serial Programming™ (ICSP™) and debugging purposes (see Section 2.4 "ICSP Pins")
- OSCI and OSCO pins when an external oscillator source is used (see Section 2.5 "External Oscillator Pins")


2.2 Decoupling Capacitors

The use of decoupling capacitors on every pair of power supply pins, such as VDD, VSS, AVDD and AVss is required.

Consider the following criteria when using decoupling capacitors:

- Value and type of capacitor: Recommendation of 0.1 μ F (100 nF), 10-20V. This capacitor should be a low-ESR and have resonance frequency in the range of 20 MHz and higher. It is recommended to use ceramic capacitors.
- Placement on the printed circuit board: The
 decoupling capacitors should be placed as close
 to the pins as possible. It is recommended to
 place the capacitors on the same side of the
 board as the device. If space is constricted, the
 capacitor can be placed on another layer on the
 PCB using a via; however, ensure that the trace
 length from the pin to the capacitor is within
 one-quarter inch (6 mm) in length.
- Handling high-frequency noise: If the board is experiencing high-frequency noise, above tens of MHz, add a second ceramic-type capacitor in parallel to the above described decoupling capacitor. The value of the second capacitor can be in the range of 0.01 µF to 0.001 µF. Place this second capacitor next to the primary decoupling capacitor. In high-speed circuit designs, consider implementing a decade pair of capacitances as close to the power and ground pins as possible. For example, 0.1 µF in parallel with 0.001 µF.
- Maximizing performance: On the board layout from the power supply circuit, run the power and return traces to the decoupling capacitors first, and then to the device pins. This ensures that the decoupling capacitors are first in the power chain. Equally important is to keep the trace length between the capacitor and the power pins to a minimum, thereby reducing PCB track inductance.

FIGURE 2-1: RECOMMENDED MINIMUM CONNECTION



Note 1: As an option, instead of a hard-wired connection, an inductor (L1) can be substituted between VDD and AVDD to improve ADC noise rejection. The inductor impedance should be less than 1Ω and the inductor capacity greater than 10 mA.

Where

$$f = \frac{FCNV}{2} \qquad \text{(i.e., ADC Conversion Rate/2)}$$

$$f = \frac{1}{(2\pi\sqrt{LC})}$$

$$L = \left(\frac{1}{(2\pi f\sqrt{C})}\right)^2$$

2.2.1 BULK CAPACITORS

On boards with power traces running longer than six inches in length, it is suggested to use a bulk capacitor for integrated circuits, including DSCs, to supply a local power source. The value of the bulk capacitor should be determined based on the trace resistance that connects the power supply source to the device and the maximum current drawn by the device in the application. In other words, select the bulk capacitor so that it meets the acceptable voltage sag at the device. Typical values range from 4.7 μF to 47 μF .

2.3 Master Clear (MCLR) Pin

The $\overline{\text{MCLR}}$ pin provides two specific device functions:


- · Device Reset
- · Device Programming and Debugging.

During device programming and debugging, the resistance and capacitance that can be added to the pin must be considered. Device programmers and debuggers drive the $\overline{\text{MCLR}}$ pin. Consequently, specific voltage levels (VIH and VIL) and fast signal transitions must not be adversely affected. Therefore, specific values of R and C will need to be adjusted based on the application and PCB requirements.

For example, as shown in Figure 2-2, it is recommended that the capacitor, C, be isolated from the $\overline{\text{MCLR}}$ pin during programming and debugging operations.

Place the components, as shown in Figure 2-2, within one-quarter inch (6 mm) from the MCLR pin.

FIGURE 2-2: EXAMPLE OF MCLR PIN CONNECTIONS



- Note 1: $R \le 10 \text{ k}\Omega$ is recommended. A suggested starting value is $10 \text{ k}\Omega$. Ensure that the $\overline{\text{MCLR}}$ pin VIH and VIL specifications are met.
 - 2: $R1 \le 470\Omega$ will limit any current flowing into $\overline{\text{MCLR}}$ from the external capacitor, C, in the event of $\overline{\text{MCLR}}$ pin breakdown due to Electrostatic Discharge (ESD) or Electrical Overstress (EOS). Ensure that the $\overline{\text{MCLR}}$ pin VIH and VIL specifications are met.

2.4 ICSP Pins

The PGCx and PGDx pins are used for ICSP and debugging purposes. It is recommended to keep the trace length between the ICSP connector and the ICSP pins on the device as short as possible. If the ICSP connector is expected to experience an ESD event, a series resistor is recommended, with the value in the range of a few tens of Ohms, not to exceed 100 Ohms.

Pull-up resistors, series diodes and capacitors on the PGCx and PGDx pins are not recommended as they will interfere with the programmer/debugger communications to the device. If such discrete components are an application requirement, they should be removed from the circuit during programming and debugging. Alternatively, refer to the AC/DC characteristics and timing requirements information in the respective device Flash programming specification for information on capacitive loading limits and pin Voltage Input High (VIH) and Voltage Input Low (VIL) requirements.

Ensure that the "Communication Channel Select" (i.e., PGCx/PGDx pins) programmed into the device matches the physical connections for the ICSP to PICkit $^{\text{TM}}$ 3, MPLAB $^{\text{®}}$ ICD 3 or MPLAB REAL ICE $^{\text{TM}}$ emulator.

For more information on MPLAB ICD 2, MPLAB ICD 3 and REAL ICE emulator connection requirements, refer to the following documents that are available on the Microchip website.


- "Using MPLAB[®] ICD 3 In-Circuit Debugger" (poster) (DS51765)
- "Development Tools Design Advisory" (DS51764)
- "MPLAB® REAL ICE™ In-Circuit Emulator User's Guide" (DS51616)
- "Using MPLAB[®] REAL ICE™ In-Circuit Emulator" (poster) (DS51749)

2.5 External Oscillator Pins

Many DSCs have options for at least two oscillators: a high-frequency Primary Oscillator (POSC) and a low-frequency Secondary Oscillator (SOSC). For details, see Section 9.2 "Primary Oscillator (POSC)".

The oscillator circuit should be placed on the same side of the board as the device. Also, place the oscillator circuit close to the respective oscillator pins, not exceeding one-half inch (12 mm) distance between them. The load capacitors should be placed next to the oscillator itself, on the same side of the board. Use a grounded copper pour around the oscillator circuit to isolate them from surrounding circuits. The grounded copper pour should be routed directly to the MCU ground. Do not run any signal traces or power traces inside the ground pour. Also, if using a two-sided board, avoid any traces on the other side of the board where the crystal is placed. A suggested layout is shown in Figure 2-3.

FIGURE 2-3: SUGGESTED PLACEMENT
OF THE OSCILLATOR
CIRCUIT



2.6 Oscillator Value Conditions on Device Start-up

If the PLL of the target device is enabled and configured for the device start-up oscillator, the maximum oscillator source frequency must be limited to a certain frequency (see Section 9.0 "Oscillator with High-Frequency PLL") to comply with device PLL start-up conditions. This means that if the external oscillator frequency is outside this range, the application must start up in the FRC mode first. The default PLL settings after a POR with an oscillator frequency outside this range will violate the device operating speed.

Once the device powers up, the application firmware can initialize the PLL SFRs, CLKDIV and PLLFBD, to a suitable value, and then perform a clock switch to the Oscillator + PLL clock source. Note that clock switching must be enabled in the device Configuration Word.

2.7 Unused I/Os

Unused I/O pins should be configured as outputs and driven to a logic low state.


Alternatively, connect a 1k to 10k resistor between Vss and unused pins, and drive the output to logic low.

2.8 Targeted Applications

- Power Factor Correction (PFC):
 - Interleaved PFC
 - Critical Conduction PFC
 - Bridgeless PFC
- DC/DC Converters:
 - Buck, Boost, Forward, Flyback, Push-Pull
 - Half/Full-Bridge
 - Phase-Shift Full-Bridge
 - Resonant Converters
- · DC/AC:
 - Half/Full-Bridge Inverter
 - Resonant Inverter
- · Motor Control
 - BLDC
 - PMSM
 - SR
 - ACIM

Examples of typical application connections are shown in Figure 2-4 through Figure 2-6.

FIGURE 2-4: INTERLEAVED PFC







FIGURE 2-5: PHASE-SHIFTED FULL-BRIDGE CONVERTER

FIGURE 2-6: OFF-LINE UPS



3.0 CPU

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "dsPIC33E Enhanced CPU" (www.microchip.com/DS70005158) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices. Refer to Section 4.0 "Memory Organization" in this data sheet for device-specific register and bit information.

The dsPIC33CK256MP508 family CPU has a 16-bit (data) modified Harvard architecture with an enhanced instruction set, including significant support for Digital Signal Processing (DSP). The CPU has a 24-bit instruction word with a variable length opcode field. The Program Counter (PC) is 23 bits wide and addresses up to 4M x 24 bits of user program memory space.

An instruction prefetch mechanism helps maintain throughput and provides predictable execution. Most instructions execute in a single-cycle effective execution rate, with the exception of instructions that change the program flow, the double-word move (MOV.D) instruction, PSV accesses and the table instructions. Overhead-free program loop constructs are supported using the DO and REPEAT instructions, both of which are interruptible at any point.

3.1 Registers

The dsPIC33CK256MP508 devices have sixteen, 16-bit Working registers in the programmer's model. Each of the Working registers can act as a Data, Address or Address Offset register. The 16th Working register (W15) operates as a Software Stack Pointer for interrupts and calls.

In addition, the dsPIC33CK256MP508 devices include four Alternate Working register sets, which consist of W0 through W14. The Alternate Working registers can be made persistent to help reduce the saving and restoring of register content during Interrupt Service Routines (ISRs). The Alternate Working registers can be assigned to a specific Interrupt Priority Level (IPL1 through IPL6) by configuring the CTXTx<2:0> bits in the FALTREG Configuration register. The Alternate Working registers can also be accessed manually by using the CTXTSWP instruction. The CCTXI<2:0> and MCTXI<2:0> bits in the CTXTSTAT register can be used to identify the current, and most recent, manually selected Working register sets.

3.2 Instruction Set

The instruction set for dsPIC33CK256MP508 devices has two classes of instructions: the MCU class of instructions and the DSP class of instructions. These two instruction classes are seamlessly integrated into the architecture and execute from a single execution unit. The instruction set includes many addressing modes and was designed for optimum C compiler efficiency.

3.3 Data Space Addressing

The base Data Space can be addressed as up to 4K words or 8 Kbytes, and is split into two blocks, referred to as X and Y data memory. Each memory block has its own independent Address Generation Unit (AGU). The MCU class of instructions operates solely through the X memory AGU, which accesses the entire memory map as one linear Data Space. Certain DSP instructions operate through the X and Y AGUs to support dual operand reads, which splits the data address space into two parts. The X and Y Data Space boundary is device-specific.

The upper 32 Kbytes of the Data Space memory map can optionally be mapped into Program Space (PS) at any 16K program word boundary. The program-to-Data Space mapping feature, known as Program Space Visibility (PSV), lets any instruction access Program Space as if it were Data Space. Refer to "Data Memory" (DS70595) in the "dsPIC33/PIC24 Family Reference Manual" for more details on PSV and table accesses.


On dsPIC33CK256MP508 family devices, overhead-free circular buffers (Modulo Addressing) are supported in both X and Y address spaces. The Modulo Addressing removes the software boundary checking overhead for DSP algorithms. The X AGU Circular Addressing can be used with any of the MCU class of instructions. The X AGU also supports Bit-Reversed Addressing to greatly simplify input or output data re-ordering for radix-2 FFT algorithms.

3.4 Addressing Modes

The CPU supports these addressing modes:

- Inherent (no operand)
- Relative
- Literal
- Memory Direct
- · Register Direct
- · Register Indirect

Each instruction is associated with a predefined addressing mode group, depending upon its functional requirements. As many as six addressing modes are supported for each instruction.



dsPIC33CK256MP508 FAMILY CPU BLOCK DIAGRAM

3.4.1 PROGRAMMER'S MODEL

The programmer's model for the dsPIC33CK256MP508 family is shown in Figure 3-2. All registers in the programmer's model are memory-mapped and can be manipulated directly by instructions. Table 3-1 lists a description of each register.

In addition to the registers contained in the programmer's model, the dsPIC33CK256MP508 devices contain control registers for Modulo Addressing, Bit-Reversed Addressing and interrupts. These registers are described in subsequent sections of this document.


All registers associated with the programmer's model are memory-mapped, as shown in Figure 3-2.

TABLE 3-1: PROGRAMMER'S MODEL REGISTER DESCRIPTIONS

Register(s) Name	Description
W0 through W15 ⁽¹⁾	Working Register Array
W0 through W14 ⁽¹⁾	Alternate Working Register Array 1
W0 through W14 ⁽¹⁾	Alternate Working Register Array 2
W0 through W14 ⁽¹⁾	Alternate Working Register Array 3
W0 through W14 ⁽¹⁾	Alternate Working Register Array 4
ACCA, ACCB	40-Bit DSP Accumulators (Additional 4 Alternate Accumulators)
PC	23-Bit Program Counter
SR	ALU and DSP Engine STATUS Register
SPLIM	Stack Pointer Limit Value Register
TBLPAG	Table Memory Page Address Register
DSRPAG	Extended Data Space (EDS) Read Page Register
RCOUNT	REPEAT Loop Counter Register
DCOUNT	DO Loop Counter Register
DOSTARTH, DOSTARTL ⁽²⁾	DO Loop Start Address Register (High and Low)
DOENDH, DOENDL	DO Loop End Address Register (High and Low)
CORCON	Contains DSP Engine, DO Loop Control and Trap Status bits

Note 1: Memory-mapped W0 through W14 represent the value of the register in the currently active CPU context.

^{2:} The DOSTARTH and DOSTARTL registers are read-only.



3.4.2 CPU RESOURCES

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

3.4.2.1 Key Resources

- "dsPIC33E Enhanced CPU" (DS70005158) in the "dsPIC33/PIC24 Family Reference Manual"
- Code Samples
- · Application Notes
- · Software Libraries
- Webinars
- All related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

3.4.3 CPU CONTROL REGISTERS

REGISTER 3-1: SR: CPU STATUS REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/C-0	R/C-0	R-0	R/W-0
OA	ОВ	SA ⁽³⁾	SB ⁽³⁾	OAB	SAB	DA	DC
bit 15							bit 8

R/W-0 ⁽²⁾	R/W-0 ⁽²⁾	R/W-0 ⁽²⁾	R-0	R/W-0	R/W-0	R/W-0	R/W-0
IPL2 ⁽¹⁾	IPL1 ⁽¹⁾	IPL0 ⁽¹⁾	RA	N	OV	Z	С
bit 7							bit 0

Legend:	C = Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1'= Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 OA: Accumulator A Overflow Status bit

1 = Accumulator A has overflowed

0 = Accumulator A has not overflowed

bit 14 **OB:** Accumulator B Overflow Status bit

1 = Accumulator B has overflowed

0 = Accumulator B has not overflowed

bit 13 **SA:** Accumulator A Saturation 'Sticky' Status bit⁽³⁾

1 = Accumulator A is saturated or has been saturated at some time

0 = Accumulator A is not saturated

bit 12 SB: Accumulator B Saturation 'Sticky' Status bit (3)

1 = Accumulator B is saturated or has been saturated at some time

0 = Accumulator B is not saturated

bit 11 OAB: OA || OB Combined Accumulator Overflow Status bit

1 = Accumulator A or B has overflowed

0 = Neither Accumulator A or B has overflowed

bit 10 SAB: SA | SB Combined Accumulator 'Sticky' Status bit

1 = Accumulator A or B is saturated or has been saturated at some time

0 = Neither Accumulator A or B is saturated

bit 9 DA: DO Loop Active bit

1 = DO loop is in progress

0 = DO loop is not in progress

bit 8 **DC:** MCU ALU Half Carry/Borrow bit

1 = A carry-out from the 4th low-order bit (for byte-sized data) or 8th low-order bit (for word-sized data) of the result occurred

0 = No carry-out from the 4th low-order bit (for byte-sized data) or 8th low-order bit (for word-sized data) of the result occurred

Note 1: The IPL<2:0> bits are concatenated with the IPL<3> bit (CORCON<3>) to form the CPU Interrupt Priority Level. The value in parentheses indicates the IPL, if IPL<3> = 1. User interrupts are disabled when IPL<3> = 1.

2: The IPL<2:0> Status bits are read-only when the NSTDIS bit (INTCON1<15>) = 1.

3: A data write to the SR register can modify the SA and SB bits by either a data write to SA and SB or by clearing the SAB bit. To avoid a possible SA or SB bit write race condition, the SA and SB bits should not be modified using bit operations.

REGISTER 3-1: SR: CPU STATUS REGISTER (CONTINUED)

IPL<2:0>: CPU Interrupt Priority Level Status bits(1,2) bit 7-5 111 = CPU Interrupt Priority Level is 7 (15); user interrupts are disabled 110 = CPU Interrupt Priority Level is 6 (14) 101 = CPU Interrupt Priority Level is 5 (13) 100 = CPU Interrupt Priority Level is 4 (12) 011 = CPU Interrupt Priority Level is 3 (11) 010 = CPU Interrupt Priority Level is 2 (10) 001 = CPU Interrupt Priority Level is 1 (9) 000 = CPU Interrupt Priority Level is 0 (8) bit 4 RA: REPEAT Loop Active bit 1 = REPEAT loop is in progress 0 = REPEAT loop is not in progress bit 3 N: MCU ALU Negative bit 1 = Result was negative

0 = Result was non-negative (zero or positive)

bit 2 **OV:** MCU ALU Overflow bit

This bit is used for signed arithmetic (two's complement). It indicates an overflow of the magnitude that causes the sign bit to change state.

1 = Overflow occurred for signed arithmetic (in this arithmetic operation)

0 = No overflow occurred

bit 1 **Z:** MCU ALU Zero bit

1 = An operation that affects the Z bit has set it at some time in the past

0 = The most recent operation that affects the Z bit has cleared it (i.e., a non-zero result)

bit 0 C: MCU ALU Carry/Borrow bit

1 = A carry-out from the Most Significant bit of the result occurred

0 = No carry-out from the Most Significant bit of the result occurred

- Note 1: The IPL<2:0> bits are concatenated with the IPL<3> bit (CORCON<3>) to form the CPU Interrupt Priority Level. The value in parentheses indicates the IPL, if IPL<3> = 1. User interrupts are disabled when IPL<3> = 1.
 - 2: The IPL<2:0> Status bits are read-only when the NSTDIS bit (INTCON1<15>) = 1.
 - **3:** A data write to the SR register can modify the SA and SB bits by either a data write to SA and SB or by clearing the SAB bit. To avoid a possible SA or SB bit write race condition, the SA and SB bits should not be modified using bit operations.

REGISTER 3-2: CORCON: CORE CONTROL REGISTER

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R-0	R-0	R-0
VAR	_	US1	US0	EDT ⁽¹⁾	DL2	DL1	DL0
bit 15							bit 8

R/W-0	R/W-0	R/W-1	R/W-0	R/C-0	R-0	R/W-0	R/W-0
SATA	SATB	SATDW	ACCSAT	IPL3 ⁽²⁾	SFA	RND	IF
bit 7							bit 0

Legend:	C = Clearable bit					
R = Readable bit	W = Writable bit U = Unimplemented bit, read as '0'					
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown			

bit 15 VAR: Variable Exception Processing Latency Control bit

1 = Variable exception processing is enabled0 = Fixed exception processing is enabled

bit 14 **Unimplemented:** Read as '0'

bit 13-12 US<1:0>: DSP Multiply Unsigned/Signed Control bits

11 = Reserved

10 = DSP engine multiplies are mixed sign01 = DSP engine multiplies are unsigned00 = DSP engine multiplies are signed

bit 11 **EDT:** Early DO Loop Termination Control bit⁽¹⁾

1 = Terminates executing DO loop at the end of the current loop iteration

0 = No effect

bit 10-8 **DL<2:0>:** DO Loop Nesting Level Status bits

111 = Seven DO loops are active

. . .

001 = One DO loop is active 000 = Zero DO loops are active

bit 7 SATA: ACCA Saturation Enable bit

1 = Accumulator A saturation is enabled 0 = Accumulator A saturation is disabled

bit 6 SATB: ACCB Saturation Enable bit

1 = Accumulator B saturation is enabled 0 = Accumulator B saturation is disabled

bit 5 SATDW: Data Space Write from DSP Engine Saturation Enable bit

1 = Data Space write saturation is enabled0 = Data Space write saturation is disabled

bit 4 ACCSAT: Accumulator Saturation Mode Select bit

1 = 9.31 saturation (super saturation)0 = 1.31 saturation (normal saturation)

bit 3 **IPL3:** CPU Interrupt Priority Level Status bit 3⁽²⁾

1 = CPU Interrupt Priority Level is greater than 7 0 = CPU Interrupt Priority Level is 7 or less

Note 1: This bit is always read as '0'.

2: The IPL3 bit is concatenated with the IPL<2:0> bits (SR<7:5>) to form the CPU Interrupt Priority Level.

REGISTER 3-2: CORCON: CORE CONTROL REGISTER (CONTINUED)

bit 2 SFA: Stack Frame Active Status bit

1 = Stack frame is active; W14 and W15 address 0x0000 to 0xFFFF, regardless of DSRPAG

0 = Stack frame is not active; W14 and W15 address the base Data Space

bit 1 RND: Rounding Mode Select bit

1 = Biased (conventional) rounding is enabled
 0 = Unbiased (convergent) rounding is enabled
 IF: Integer or Fractional Multiplier Mode Select bit

1 = Integer mode is enabled for DSP multiply0 = Fractional mode is enabled for DSP multiply

Note 1: This bit is always read as '0'.

2: The IPL3 bit is concatenated with the IPL<2:0> bits (SR<7:5>) to form the CPU Interrupt Priority Level.

REGISTER 3-3: MSTRPR: EDS BUS MASTER PRIORITY CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	U-0	U-0	U-0	R/W-0
_	_	DMAPR	CANPR	_	_	_	NVMPR
bit 7							

Legend:

bit 0

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-6 **Unimplemented:** Read as '0'

bit 5 DMAPR: Modify DMA Controller Bus Master Priority Relative to CPU bit

1 = Raise DMA Controller bus Master priority to above that of the CPU

0 = No change to DMA Controller bus Master priority

bit 4 CANPR: Modify CAN1 Bus Master Priority Relative to CPU bit

1 = Raise CAN1 bus Master priority to above that of the CPU

0 = No change to CAN1 bus Master priority

bit 3-1 **Unimplemented:** Read as '0'

bit 0 NVMPR: Modify NVM Controller Bus Master Priority Relative to CPU bit

1 = Raise NVM Controller bus Master priority to above that of the CPU

0 = No change to NVM Controller bus Master priority

REGISTER 3-4: CTXTSTAT: CPU W REGISTER CONTEXT STATUS REGISTER

U-0	U-0	U-0	U-0	U-0	R-0	R-0	R-0
_	_	_	_	_	CCTXI2	CCTXI1	CCTXI0
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	R-0	R-0	R-0
_	_	_	_	_	MCTXI2	MCTXI1	MCTXI0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 **Unimplemented:** Read as '0'

bit 10-8 CCTXI<2:0>: Current (W Register) Context Identifier bits

111 = Reserved

•

•

100 = Alternate Working Register Set 4 is currently in use

011 = Alternate Working Register Set 3 is currently in use

010 = Alternate Working Register Set 2 is currently in use

001 = Alternate Working Register Set 1 is currently in use

000 = Default register set is currently in use

bit 7-3 **Unimplemented:** Read as '0'

bit 2-0 MCTXI<2:0>: Manual (W Register) Context Identifier bits

111 = Reserved

•

•

100 = Alternate Working Register Set 4 was most recently manually selected

011 = Alternate Working Register Set 3 was most recently manually selected

010 = Alternate Working Register Set 2 was most recently manually selected

001 = Alternate Working Register Set 1 was most recently manually selected

000 = Default register set was most recently manually selected

3.4.4 ARITHMETIC LOGIC UNIT (ALU)

The dsPIC33CK256MP508 family ALU is 16 bits wide and is capable of addition, subtraction, bit shifts and logic operations. Unless otherwise mentioned, arithmetic operations are two's complement in nature. Depending on the operation, the ALU can affect the values of the Carry (C), Zero (Z), Negative (N), Overflow (OV) and Digit Carry (DC) Status bits in the SR register. The C and DC Status bits operate as Borrow and Digit Borrow bits, respectively, for subtraction operations.

The ALU can perform 8-bit or 16-bit operations, depending on the mode of the instruction that is used. Data for the ALU operation can come from the W register array or data memory, depending on the addressing mode of the instruction. Likewise, output data from the ALU can be written to the W register array or a data memory location.

Refer to the "16-Bit MCU and DSC Programmer's Reference Manual" (DS70000157) for information on the SR bits affected by each instruction.

The core CPU incorporates hardware support for both multiplication and division. This includes a dedicated hardware multiplier and support hardware for 16-bit divisor division.

3.4.4.1 Multiplier

Using the high-speed, 17-bit x 17-bit multiplier, the ALU supports unsigned, signed or mixed-sign operation in several MCU multiplication modes:

- 16-bit x 16-bit signed
- 16-bit x 16-bit unsigned
- 16-bit signed x 5-bit (literal) unsigned
- 16-bit signed x 16-bit unsigned
- 16-bit unsigned x 5-bit (literal) unsigned
- 16-bit unsigned x 16-bit signed
- · 8-bit unsigned x 8-bit unsigned

3.4.4.2 Divider

The divide block supports 32-bit/16-bit and 16-bit/16-bit signed and unsigned integer divide operations with the following data sizes:

- · 32-bit signed/16-bit signed divide
- 32-bit unsigned/16-bit unsigned divide
- 16-bit signed/16-bit signed divide
- 16-bit unsigned/16-bit unsigned divide

The 16-bit signed and unsigned DIV instructions can specify any W register for both the 16-bit divisor (Wn) and any W register (aligned) pair (W(m + 1):Wm) for the 32-bit dividend. The divide algorithm takes one cycle per bit of divisor, so both 32-bit/16-bit and 16-bit/16-bit instructions take the same number of cycles to execute. There are additional instructions: DIV2 and DIVF2. Divide instructions will complete in six cycles.

3.4.5 DSP ENGINE

The DSP engine consists of a high-speed 17-bit x 17-bit multiplier, a 40-bit barrel shifter and a 40-bit adder/ subtracter (with two target accumulators, round and saturation logic).

The DSP engine can also perform inherent accumulator-to-accumulator operations that require no additional data. These instructions are, ADD, SUB, NEG, MIN and MAX.

The DSP engine has options selected through bits in the CPU Core Control register (CORCON), as listed below:

- Fractional or integer DSP multiply (IF)
- Signed, unsigned or mixed-sign DSP multiply (USx)
- Conventional or convergent rounding (RND)
- Automatic saturation on/off for ACCA (SATA)
- Automatic saturation on/off for ACCB (SATB)
- Automatic saturation on/off for writes to data memory (SATDW)
- Accumulator Saturation mode selection (ACCSAT)

TABLE 3-2: DSP INSTRUCTIONS SUMMARY

Instruction	Algebraic Operation	ACC Write-Back		
CLR	A = 0	Yes		
ED	$A = (x - y)^2$	No		
EDAC	$A = A + (x - y)^2$	No		
MAC	$A = A + (x \bullet y)$	Yes		
MAC	$A = A + x^2$	No		
MOVSAC	No change in A	Yes		
MPY	$A = x \cdot y$	No		
MPY	$A = x^2$	No		
MPY.N	$A = -x \bullet y$	No		
MSC	$A = A - x \bullet y$	Yes		

NOTES:			

4.0 **MEMORY ORGANIZATION**

Note:

This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "dsPIC33E/PIC24E Pro-Memory" (www.microchip.com/ gram DS70000613) in the "dsPIC33/PIC24 Family Reference Manual".

The dsPIC33CK256MP508 family architecture features separate program and data memory spaces, and buses. This architecture also allows the direct access of program memory from the Data Space (DS) during code execution.

4.1 **Program Address Space**

The program address memory space of the dsPIC33CK256MP508 family devices is 4M instructions. The space is addressable by a 24-bit value derived either from the 23-bit PC during program execution, or from table operation or Data Space remapping, as described in Section 4.4.5 "Interfacing Program and Data Memory Spaces".

User application access to the program memory space is restricted to the lower half of the address range (0x000000 to 0x7FFFFF). The exception is the use of TBLRD operations, which use TBLPAG<7> to permit access to calibration data and Device ID sections of the configuration memory space.

The program memory maps for dsPIC33CK256MP508 devices are shown in Figure 4-1 through Figure 4-5.

PROGRAM MEMORY MAP FOR dsPIC33CKXXXMP50X/20X DEVICES(1) FIGURE 4-1: 0x000000 Code Memory **Jser Memory Space** 0x0XXXFE 0x0XXX00 See Figure 4-2 through **Device Configuration** Figure 4-5 for details. 0x0XXXFE 0x0XXX00 Unimplemented (Read '0's) 0x7FFFFE 0x800000 **Executive Code Memory** 0x800FFE 0x801000 Calibration Data^(2,3) Configuration Memory Space 0x8016FE 0x801700 **OTP Memory** 0x8017FE 0x801800 Reserved 0xF9FFFE 0xFA0000 Write Latches 0xFA0002 0xFA0004 Reserved 0xFEFFFE 0xFF0000 **DEVID** 0xFF0002 0xFF0004 Reserved 0xFFFFFE

Note 1: Memory areas are not shown to scale.

2: Calibration data area must be maintained during programming.

3: Calibration data area includes UDID, ICSP™ Write Inhibit and FBOOT registers locations.

FIGURE 4-2: PROGRAM MEMORY MAP FOR dsPIC33CK256MP50/20X DEVICES⁽¹⁾




FIGURE 4-3: PROGRAM MEMORY MAP FOR dsPIC33CK128MP50X/20X DEVICES⁽¹⁾




FIGURE 4-4: PROGRAM MEMORY MAP FOR dsPIC33CK64MP50X/20X DEVICES⁽¹⁾





FIGURE 4-5: PROGRAM MEMORY MAP FOR dsPIC33CK32MP50X/20X DEVICES⁽¹⁾



4.1.1 PROGRAM MEMORY ORGANIZATION

The program memory space is organized in word-addressable blocks. Although it is treated as 24 bits wide, it is more appropriate to think of each address of the program memory as a lower and upper word, with the upper byte of the upper word being unimplemented. The lower word always has an even address, while the upper word has an odd address (Figure 4-6).


Program memory addresses are always word-aligned on the lower word, and addresses are incremented or decremented, by two, during code execution. This arrangement provides compatibility with data memory space addressing and makes data in the program memory space accessible.

4.1.2 INTERRUPT AND TRAP VECTORS

All dsPIC33CK256MP508 family devices reserve the addresses between 0x000000 and 0x000200 for hard-coded program execution vectors. A hardware Reset vector is provided to redirect code execution from the default value of the PC on device Reset to the actual start of code. A GOTO instruction is programmed by the user application at address, 0x000000, of Flash memory, with the actual address for the start of code at address, 0x0000002, of Flash memory.

A more detailed discussion of the Interrupt Vector Tables (IVTs) is provided in **Section 7.0** "Interrupt Controller".

FIGURE 4-6: PROGRAM MEMORY ORGANIZATION



4.1.3 UNIQUE DEVICE IDENTIFIER (UDID)

All dsPIC33CK256MP508 family devices are individually encoded during final manufacturing with a Unique Device Identifier or UDID. The UDID cannot be erased by a bulk erase command or any other user-accessible means. This feature allows for manufacturing traceability of Microchip Technology devices in applications where this is a requirement. It may also be used by the application manufacturer for any number of things that may require unique identification, such as:

- · Tracking the device
- · Unique serial number
- · Unique security key

The UDID comprises five 24-bit program words. When taken together, these fields form a unique 120-bit identifier.

The UDID is stored in five read-only locations, located between 0x801200 and 0x801208 in the device configuration space. Table 4-1 lists the addresses of the identifier words and shows their contents

TABLE 4-1: UDID ADDRESSES

UDID	Address	Description		
UDID1	0x801200	UDID Word 1		
UDID2	0x801202	UDID Word 2		
UDID3	0x801204	UDID Word 3		
UDID4	0x801206	UDID Word 4		
UDID5	0x801208	UDID Word 5		

4.2 Data Address Space

The dsPIC33CK256MP508 family CPU has a separate 16-bit wide data memory space. The Data Space is accessed using separate Address Generation Units (AGUs) for read and write operations. The data memory maps are shown in Figure 4-7, Figure 4-8 and Figure 4-9.

All Effective Addresses (EAs) in the data memory space are 16 bits wide and point to bytes within the Data Space. This arrangement gives a base Data Space address range of 64 Kbytes or 32K words.

The lower half of the data memory space (i.e., when EA<15>=0) is used for implemented memory addresses, while the upper half (EA<15>=1) is reserved for the Program Space Visibility (PSV).

The dsPIC33CK256MP508 family devices implement up to 16 Kbytes of data memory. If an EA points to a location outside of this area, an all-zero word or byte is returned.

4.2.1 DATA SPACE WIDTH

The data memory space is organized in byte-addressable, 16-bit wide blocks. Data is aligned in data memory and registers as 16-bit words, but all Data Space EAs resolve to bytes. The Least Significant Bytes (LSBs) of each word have even addresses, while the Most Significant Bytes (MSBs) have odd addresses.

4.2.2 DATA MEMORY ORGANIZATION AND ALIGNMENT

To maintain backward compatibility with PIC[®] MCU devices and improve Data Space memory usage efficiency, the dsPIC33CK256MP508 family instruction set supports both word and byte operations. As a consequence of byte accessibility, all Effective Address calculations are internally scaled to step through word-aligned memory. For example, the core recognizes that Post-Modified Register Indirect Addressing mode [Ws++] results in a value of Ws + 1 for byte operations and Ws + 2 for word operations.

A data byte read, reads the complete word that contains the byte, using the LSb of any EA to determine which byte to select. The selected byte is placed onto the LSB of the data path. That is, data memory and registers are organized as two parallel, byte-wide entities with shared (word) address decode, but separate write lines. Data byte writes only write to the corresponding side of the array or register that matches the byte address.

All word accesses must be aligned to an even address. Misaligned word data fetches are not supported, so care must be taken when mixing byte and word operations, or translating from 8-bit MCU code. If a misaligned read or write is attempted, an address error trap is generated. If the error occurred on a read, the instruction underway is completed. If the error occurred on a write, the instruction is executed but the write does not occur. In either case, a trap is then executed, allowing the system and/or user application to examine the machine state prior to execution of the address Fault.

All byte loads into any W register are loaded into the LSB; the MSB is not modified.

A Sign-Extend (SE) instruction is provided to allow user applications to translate 8-bit signed data to 16-bit signed values. Alternatively, for 16-bit unsigned data, user applications can clear the MSB of any W register by executing a Zero-Extend (ZE) instruction on the appropriate address.

4.2.3 SFR SPACE

The first four Kbytes of the Near Data Space, from 0x0000 to 0x0FFF, is primarily occupied by Special Function Registers (SFRs). These are used by the dsPIC33CK256MP508 family core and peripheral modules for controlling the operation of the device.

SFRs are distributed among the modules that they control and are generally grouped together by module. Much of the SFR space contains unused addresses; these are read as '0'.

Note:

The actual set of peripheral features and interrupts varies by the device. Refer to the corresponding device tables and pinout diagrams for device-specific information.

4.2.4 NEAR DATA SPACE

The 8-Kbyte area, between 0x0000 and 0x1FFF, is referred to as the Near Data Space. Locations in this space are directly addressable through a 13-bit absolute address field within all memory direct instructions. Additionally, the whole Data Space is addressable using MOV instructions, which support Memory Direct Addressing mode with a 16-bit address field, or by using Indirect Addressing mode using a Working register as an Address Pointer.




FIGURE 4-7: DATA MEMORY MAP FOR dsPIC33CK256MPX0X DEVICES




FIGURE 4-8: DATA MEMORY MAP FOR dsPIC33CK128MPX0X DEVICES




FIGURE 4-9: DATA MEMORY MAP FOR dsPIC33CK64MPX0X AND dsPIC33CK32MPX0X DEVICES

4.2.5 X AND Y DATA SPACES

The dsPIC33CK256MP508 family core has two Data Spaces, X and Y. These Data Spaces can be considered either separate (for some DSP instructions) or as one unified linear address range (for MCU instructions). The Data Spaces are accessed using two Address Generation Units (AGUs) and separate data paths. This feature allows certain instructions to concurrently fetch two words from RAM, thereby enabling efficient execution of DSP algorithms, such as Finite Impulse Response (FIR) filtering and Fast Fourier Transform (FFT).

The X Data Space is used by all instructions and supports all addressing modes. X Data Space has separate read and write data buses. The X read data bus is the read data path for all instructions that view Data Space as combined X and Y address space. It is also the X data prefetch path for the dual operand DSP instructions (MAC class).

The Y Data Space is used in concert with the X Data Space by the MAC class of instructions (CLR, ED, EDAC, MAC, MOVSAC, MPY, MPY. N and MSC) to provide two concurrent data read paths.

Both the X and Y Data Spaces support Modulo Addressing mode for all instructions, subject to addressing mode restrictions. Bit-Reversed Addressing mode is only supported for writes to X Data Space.

All data memory writes, including in DSP instructions, view Data Space as combined X and Y address space. The boundary between the X and Y Data Spaces is device-dependent and is not user-programmable.

4.2.6 BIST OVERVIEW


The dsPIC33CK256MP508 family features a data memory Built-In Self-Test (BIST) that has the option to be run at start-up or run time. The memory test checks that all memory locations are functional and provides a pass/fail status of the RAM that can be used by software to take action if needed. If a failure is reported, the specific location(s) are not identified.

The MBISTCON register (Register 4-1) contains control and status bits for BIST operation. The MBISTDONE bit (MBISTCON<7>) indicates if a BIST was run since the last Reset and the MBISTSTAT bit (MBISTCON<4>) provides the pass fail result.

4.2.7 BIST AT START-UP

The BIST can be configured to automatically run on a POR type Reset, as shown in Figure 4-10. By default, when BISTDIS (FPOR<6>) = 1, the BIST is disabled and will not be part of device start-up. If the BISTDIS bit is cleared during device programming, the BIST will run after all Configuration registers have been loaded and before code execution begins. BIST will always run on FRC+PLL with PLL settings resulting in a 125 MHz clock rate.

FIGURE 4-10: BIST FLOWCHART



4.2.8 BIST AT RUN TIME

A BIST test can be requested to run on subsequent device Resets at any time.

A BIST will corrupt all of the RAM contents, including the Stack Pointer, and requires a subsequent Reset. The system should be prepared for a Reset before a BIST is performed. The BIST is invoked by setting the MBISTEN bit (MBISTCON<0>) and executing a Reset. The MBISTCON register is protected against accidental writes and requires an unlock sequence prior to writing. Only one bit can be set per unlock sequence. The procedure for a run-time BIST is as follows:

- Execute the unlock sequence by consecutively writing 0x55 and 0xAA to the NVMKEY register.
- 2. Write 0x0001 to the MBISTCON SFR.
- 3. Execute a software RESET command.
- Verify a Software Reset has occurred by reading SWR (RCON<6>) (optional).
- 5. Verify that the MBISTDONE bit is set.
- Take action depending on test result indicated by MBISTSTAT.

4.2.8.1 Fault Simulation

A mechanism is available to simulate a BIST failure to allow testing of Fault handling software. When the FLTINJ bit is set during a run-time BIST, the MBISTSTAT bit will be set regardless of the test result. The procedure for a BIST Fault simulation is as follows:

- 1. Execute the unlock sequence by consecutively writing 0x55 and 0xAA to the NVMKEY register.
- 2. Set the MBISTEN bit (MBISTCON<0>).
- 3. Execute 2nd unlock sequence by consecutively writing 0x55 and 0xAA to the NVMKEY register.
- 4. Set the FLTINJ bit (MBISTCON<8>).
- 5. Execute a software RESET command.
- Verify the MBISTDONE, MBSITSTAT and FLTINJ bits are all set.

REGISTER 4-1: MBISTCON: MBIST CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0 ⁽¹⁾
_	_	_	_	_	_	_	FLTINJ
bit 15							bit 8

R/W/HS-0	U-0	U-0	R-0	U-0	U-0	U-0	R/W/HC-0	
MBISTDONE ⁽¹⁾	_	_	MBISTSTAT	_	_	_	MBISTEN ⁽²⁾	
bit 7 bit								

Legend: HS = Hardware Settable bit		HC = Hardware Clearable bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared $x = Bit$ is unl	known		

bit 15-9 **Unimplemented:** Read as '0'

bit 7

bit 8 FLTINJ: MBIST Fault Inject Control bit (1)

1 = The MBIST test will complete and sets MBISTSTAT = 1, simulating an SRAM test failure

0 = The MBIST test will execute normally **MBISTDONE**: MBIST Done Status bit⁽¹⁾

1 = An MBIST operation has been executed

0 = No MBIST operation has occurred on the last Reset sequence

bit 6-5 Unimplemented: Read as '0' bit 4 MBIST Status bit 1 = The last MBIST failed

 $_{
m 0}$ = The last MBIST passed; all memory may not have been tested

bit 3-1 **Unimplemented:** Read as '0' bit 0 **MBISTEN:** MBIST Enable bit⁽²⁾

1 = MBIST test is armed; an MBIST test will execute at the next device Reset

0 = MBIST test is disarmed

Note 1: HW resets only on a true POR Reset.

2: This bit will self-clear when the MBIST test is complete.

4.3 Memory Resources

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

4.3.1 KEY RESOURCES

- "dsPIC33E Enhanced CPU" (DS70005158) in the "dsPIC33/PIC24 Family Reference Manual"
- · Code Samples
- · Application Notes
- · Software Libraries

- Webinars
- All Related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

4.4 SFR Maps

The following tables show the dsPIC33CK256MP508 family SFR names, addresses and Reset values. These tables contain all registers applicable to the dsPIC33CK256MP508 family. Not all registers are present on all device variants. Refer to Table 1 and Table 2 for peripheral availability. Table 8-1 details port availability for the different package options.

TABLE 4-2: SFR BLOCK 000h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
Core			XMODSRT	048	xxxxxxxxxxxxx	CRC		
WREG0	000	00000000000000000	XMODEND	04A	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	CRCCONL	0B0	000000010000
WREG1	002	00000000000000000	YMODSRT	04C	xxxxxxxxxxxxx0	CRCCONH	0B2	0000000000
WREG2	004	00000000000000000	YMODEND	04E	xxxxxxxxxxxxxxx1	CRCXORL	0B4	0000000000000000
WREG3	006	00000000000000000	XBREV	050	xxxxxxxxxxxxx	CRCXORH	0B6	00000000000000000
WREG4	008	00000000000000000	DISICNT	052	-xxxxxxxxxx00	CRCDATL	0B8	00000000000000000
WREG5	00A	00000000000000000	TBLPAG	054	00000000	CRCDATH	0BA	00000000000000000
WREG6	00C	00000000000000000	YPAG	056	00000001	CRCWDATL	0BC	00000000000000000
WREG7	00E	00000000000000000	MSTRPR	058	000	CRCWDATH	0BE	00000000000000000
WREG8	010	00000000000000000	CTXTSTAT	05A	000000	CLC		
WREG9	012	00000000000000000	DMTCON	05C		CLC1CONL	0C0	0-00000000
WREG10	014	00000000000000000	DMTPRECLR	060	xxxxxxx	CLC1CONH	0C2	0000
WREG11	016	00000000000000000	DMTCLR	064	xxxxxxxx	CLC1SEL	0C4	0000-000-000-000
WREG12	018	00000000000000000	DMTSTAT	068	xxxx	CLC1GLSL	0C8	00000000000000000
WREG13	01A	00000000000000000	DMTCNTL	06C	xxxxxxxxxxxxx	CLC1GLSH	0CA	00000000000000000
WREG14	01C	00000000000000000	DMTCNTH	06E	xxxxxxxxxxxxx	CLC2CONL	0CC	0-00000000
WREG15	01E	00010000000000000	DMTHOLDREG	070	xxxxxxxxxxxxx	CLC2CONH	0CE	0000
SPLIM	020	xxxxxxxxxxxxx	DMTPSCNTL	074	xxxxxxxxxxxxx	CLC2SELL	0D0	0000-000-000-000
ACCAL	022	xxxxxxxxxxxxx	DMTPSCNTH	076	xxxxxxxxxxxxx	CLC2GLSL	0D4	00000000000000000
ACCAH	024	xxxxxxxxxxxxx	DMTPSINTVL	078	xxxxxxxxxxxxx	CLC2GLSH	0D6	00000000000000000
ACCAU	026	xxxxxxxxxxxxx	DMTPSINTVH	07A	xxxxxxxxxxxxx	CLC3CONL	0D8	0-00000000
ACCBL	028	xxxxxxxxxxxxx	SENT			CLC3CONH	0DA	0000
ACCBH	02A	xxxxxxxxxxxxx	SENT1CON1	080	0-000000-0-000	CLC3SELL	0DC	0000-000-000-000
ACCBU	02C	xxxxxxxxxxxxx	SENT1CON2	084	00000000000000000	CLC3GLSL	0E0	00000000000000000
PCL	02E	00000000000000000	SENT1CON3	088	00000000000000000	CLC3GLSH	0E2	00000000000000000
PCH	030	000000000	SENT1STAT	08C	00000000	CLC4CONL	0E4	0-00000000
DSRPAG	032	0000000001	SENT1SYNC	090	00000000000000000	CLC4CONH	0E6	0000
DSWPAG	034	000000001	SENT1DATL	094	00000000000000000	CLC4SELL	0E8	0000-000-000-000
RCOUNT	036	xxxxxxxxxxxxx	SENT1DATH	096	00000000000000000	CLC4GLSL	0EC	00000000000000000
DCOUNT	038	xxxxxxxxxxxxx	SENT2CON1	098	0-000000-0-000	CLC4GLSH	0EE	00000000000000000
DOSTARTL	03A	xxxxxxxxxxxx0	SENT2CON2	09C	00000000000000000	ECC		
DOSTARTH	03C	xxxxxxx	SENT2CON3	0A0	00000000000000000	ECCCONL	0F0	0
DOENDL	03E	xxxxxxxxxxxx0	SENT2STAT	0A4	00000000	ECCCONH	0F2	0000000000000000
DOENDH	040	xxxxxxx	SENT2SYNC	0A8	00000000000000000	ECCADDRL	0F4	00000000000000000
SR	042	00000000000000000	SENT2DATL	0AC	00000000000000000	ECCADDRH	0F6	0000000000000000
CORCON	044	xx000000100000	SENT2DATH	0AE	00000000000000000	ECCSTATL	0F8	0000000000000000
MODCON	046	00000000000000				ECCSTATH	0FA	0000000000

TABLE 4-3: SFR BLOCK 100h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
Timers			INDX1HLD	16A	00000000000000000	INDX2HLD	19E	00000000000000000
T1CON	100	0000000-00-00-	QEI1GECL/ QEI1ICL	16C	00000000000000000	QEI2GECL/ QEI2ICL	1A0	00000000000000000
TMR1	104	00000000000000000	QEI1GECH/ QEI1ICH	16E	000000000000000000000000000000000000000	QEI2GECH/ QEI2ICH	1A2	00000000000000000
PR1	108	00000000000000000	QEI1LECL	170	00000000000000000	QEI2LECL	1A4	00000000000000000
QEI	QEI			172	00000000000000000	QEI2LECH	1A6	00000000000000000
QEI1CON	140	000000-0000000	QEI2CON	174	000000-0000000	PMP		
QEI1IOC	144	000000000000xxxx	QEI2IOC	178	00000000000xxxx	PMCON	1A8	00000000000-00
QEI1IOCH	146	0	QEI2IOCH	17A	0	PMCONH	1AA	00-
QEI1STAT	148	000000000000000	QEI2STAT	17C	000000000000000	PMMODE	1AC	00000000000000000
POS1CNTL	14C	00000000000000000	POS2CNTL	180	00000000000000000	PMADDR	1B0	00000000000000000
POS1CNTH	14E	00000000000000000	POS2CNTH	182	00000000000000000	PMDOUT1	1B4	00000000000000000
POS1HLD	152	00000000000000000	POS2HLD	186	00000000000000000	PMDOUT2	1B6	00000000000000000
VEL1CNT	154	00000000000000000	VEL2CNT	188	00000000000000000	PMDIN1	1B8	00000000000000000
VEL1CNTH	156	00000000000000000	VEL2CNTH	18A	00000000000000000	PMDIN2	1BA	00000000000000000
VEL1HLD	15A	00000000000000000	VEL2HLD	18E	00000000000000000	PMAEN	1BC	00000000000000000
INT1TMRL	15C	00000000000000000	INT2TMRL	190	00000000000000000	PMSTAT	1C0	000000101111
INT1TMRH	15E	00000000000000000	INT2TMRH	192	00000000000000000	PMWADDR	1C4	00000000000000000
INT1HLDL	160	00000000000000000	INT2HLDL	194	00000000000000000	PMRADDR	1C8	00000000000000000
INT1HLDH	162	00000000000000000	INT2HLDH	196	00000000000000000	PMRDIN	1CC	00000000000000000
INDX1CNTL	164	00000000000000000	INDX2CNTL	198	00000000000000000		•	
INDX1CNTH	166	00000000000000000	INDX2CNTH	19A	00000000000000000			

TABLE 4-4: SFR BLOCK 200h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
I2C1 and I2C2	2		U1SCCON	258	00000-	SPI1IMSKH	2C2	0000000-000000
I2C1CONL	200	010000000000000	U1SCINT	25A	00-00000-000	SPI1URDTL	2C4	0000000000000000
I2C1CONH	202	0000000	U1INT	25C	000	SPI1URDTH	2C6	0000000000000000
I2C1STAT	204	00000000000000	U2MODE	260	000-0000000000	SPI2CON1L	2C8	000000000000000
I2C1ADD	208	0000000000	U2MODEH	262	000000000000	SPI2CON1H	2CA	0000000000000000
I2C1MSK	20C	0000000000	U2STA	264	000000010000000	SPI2CON2L	2CC	00000
I2C1BRG	210	00000000000000000	U2STAH	266	0000-00000101110	SPI2CON2H	2CE	
I2C1TRN	214	11111111	U2BRG	268	0000000000000000	SPI2STATL	2D0	000001-1-00
I2C1RCV	218	000000000	U2BRGH	26A	0000	SPI2STATH	2D2	000000000000
I2C2CONL	21C	010000000000000	U2RXREG	26C	xxxxxxxx	SPI2BUFL	2D4	0000000000000000
I2C2CONH	21E	0000000	U2TXREG	270	xxxxxxxx	SPI2BUFH	2D6	0000000000000000
I2C2STAT	220	00000000000000	U2P1	274	000000000	SPI2BRGL	2D8	xxxxxxxxxxx
I2C2ADD	224	0000000000	U2P2	276	000000000	SPI2BRGH	2DA	
I2C2MSK	228	0000000000	U2P3	278	0000000000000000	SPI2IMSKL	2DC	000000-0-00
I2C2BRG	22C	00000000000000000	U2P3H	27A	00000000	SPI2IMSKH	2DE	0000000-000000
I2C2TRN	230	11111111	U2TXCHK	27C	00000000	SPI2URDTL	2E0	00000000000000000
I2C2RCV	234	00000000	U2RXCHK	27E	00000000	SPI2URDTH	2E2	0000000000000000
UART1 and U	IART2		U2SCCON	280	00000-	SPI3CON1L	2E4	000000000000000
U1MODE	238	000-0000000000	U2SCINT	282	00-00000-000	SPI3CON1H	2E6	00000000000000000
U1MODEH	23A	0000000000000	U2INT	284	000	SPI3CON2L	2E8	00000
U1STA	23C	000000010000000	SPI			SPI3CON2H	2EA	
U1STAH	23E	0000-00000101110	SPI1CON1L	2AC	00000000000000	SPI3STATL	2EC	000001-1-00
U1BRG	240	00000000000000000	SPI1CON1H	2AE	0000000000000000	SPI3STATH	2EE	000000000000
U1BRGH	242	0000	SPI1CON2L	2B0	00000	SPI3BUFL	2F0	0000000000000000
U1RXREG	244	xxxxxxxx	SPI1CON2H	2B2		SPI3BUFH	2F2	0000000000000000
U1TXREG	248	xxxxxxxx	SPI1STATL	2B4	000001-1-00	SPI3BRGL	2F4	xxxxxxxxxxx
U1P1	24C	000000000	SPI1STATH	2B6	000000000000	SPI3BRGH	2F6	
U1P2	24E	000000000	SPI1BUFL	2B8	00000000000000000	SPI3IMSKL	2F8	000000-0-00
U1P3	250	00000000000000000	SPI1BUFH	2BA	00000000000000000	SPI3IMSKH	2FA	0000000-000000
U1P3H	252	000000000	SPI1BRGL	2BC	xxxxxxxxxxx	SPI3URDTL	2FC	00000000000000000
U1TXCHK	254	000000000	SPI1BRGH	2BE		SPI3URDTH	2F3	00000000000000000
U1RXCHK	256	000000000	SPI1IMSKL	2C0	000000-0-00			

TABLE 4-5: SFR BLOCK 300h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
High-Speed I	PWM		PG1TRIGA	354	00000000000000000	PG3CLPCIH	3AA	0000-00000000000
PCLKCON	300	00000	PG1TRIGB	356	00000000000000000	PG3FFPCIL	3AC	00000000000000000
FSCL	302	00000000000000000	PG1TRIGC	358	00000000000000000	PG3FFPCIH	3AE	0000-00000000000
FSMINPER	304	00000000000000000	PG1DTL	35A	000000000000000	PG3SPCIL	3B0	00000000000000000
MPHASE	306	00000000000000000	PG1DTH	35C	000000000000000	PG3SPCIH	3B2	0000-00000000000
MDC	308	0000000000000000	PG1CAP	35E	00000000000000000	PG3LEBL	3B4	00000000000000000
MPER	30A	00000000000000000	PG2CONL	360	000000000	PG3LEBH	3B6	0000000
LFSR	30C	00000000000000000	PG2CONH	362	000-0000000000	PG3PHASE	3B8	00000000000000000
CMBTRIGL	30E	00000000	PG2STAT	364	00000000000000000	PG3DC	3BA	00000000000000000
CMBTRIGH	310	00000000	PG2IOCONL	366	00000000000000000	PG3DCA	3BC	00000000
LOGCONA	312	000000000000000000	PG2IOCONH	368	00000-000000	PG3PER	3BE	00000000000000000
LOGCONB	314	000000000000-000	PG2EVTL	36A	00000000000000	PG3TRIGA	3C0	00000000000000000
LOGCONC	316	000000000000-000	PG2EVTH	36C	00000000000000	PG3TRIGB	3C2	00000000000000000
LOGCOND	318	00000000000000000	PG2FPCIL	36E	00000000000000000	PG3TRIGC	3C4	00000000000000000
LOGCONE	31A	00000000000000000	PG2FPCIH	370	0000-00000000000	PG3DTL	3C6	000000000000000
LOGCONF	31C	00000000000000000	PG2CLPCIL	372	00000000000000000	PG3DTH	3C8	000000000000000
PWMEVTA	31E	00000000-000	PG2CLPCIH	374	0000-00000000000	PG3CAP	3CA	00000000000000000
PWMEVTB	320	00000000-000	PG2FFPCIL	376	00000000000000000	PG4CONL	3CC	000000000
PWMEVTC	322	00000000-000	PG2FFPCIH	378	0000-00000000000	PG4CONH	3CE	000-0000000000
PWMEVTD	324	00000000-000	PG2SPCIL	37A	00000000000000000	PG4STAT	3D0	00000000000000000
PWMEVTE	326	00000000-000	PG2SPCIH	37C	0000-00000000000	PG4IOCONL	3D2	00000000000000000
PWMEVTF	328	00000000-000	PG2LEBL	37E	00000000000000000	PG4IOCONH	3D4	00000-000000
PG1CONL	32A	000000000	PG2LEBH	380	0000000	PG4EVTL	3D6	0000000000000
PG1CONH	32C	000-0000000000	PG2PHASE	382	00000000000000000	PG4EVTH	3D8	00000000000000
PG1STAT	32E	0000000000000000	PG2DC	384	00000000000000000	PG4FPCIL	3DA	00000000000000000
PG1IOCONL	330	00000000000000000	PG2DCA	386	000000000	PG4FPCIH	3DC	0000-00000000000
PG1IOCONH	332	00000-000000	PG2PER	388	00000000000000000	PG4CLPCIL	3DE	00000000000000000
PG1EVTL	334	0000000000000	PG2TRIGA	38A	00000000000000000	PG4CLPCIH	3E0	0000-00000000000
PG1EVTH	336	00000000000000	PG2TRIGB	38C	00000000000000000	PG4FFPCIL	3E2	00000000000000000
PG1FPCIL	338	00000000000000000	PG2TRIGC	38E	00000000000000000	PG4FFPCIH	3E4	0000-00000000000
PG1FPCIH	33A	0000-00000000000	PG2DTL	390	000000000000000	PG4SPCIL	3E6	00000000000000000
PG1CLPCIL	33C	0000000000000000	PG2DTH	392	000000000000000	PG4SPCIH	3E8	0000-00000000000
PG1CLPCIH	33E	0000-00000000000	PG2CAP	394	00000000000000000	PG4LEBL	3EA	00000000000000000
PG1FFPCIL	340	0000000000000000	PG3CONL	396	000000000	PG4LEBH	3EC	0000000
PG1FFPCIH	342	0000-00000000000	PG3CONH	398	000-0000000000	PG4PHASE	3EE	00000000000000000
PG1SPCIL	344	00000000000000000	PG3STAT	39A	00000000000000000	PG4DC	3F0	00000000000000000
PG1SPCIH	346	0000-00000000000	PG3IOCONL	39C	00000000000000000	PG4DCA	3F2	00000000
PG1LEBL	348	00000000000000000	PG3IOCONH	39E	00000-000000	PG4PER	3F4	00000000000000000
PG1LEBH	34A	0000000	PG3EVTL	3A0	0000000000000	PG4TRIGA	3F6	00000000000000000
PG1PHASE	34C	00000000000000000	PG3EVTH	3A2	00000000000000	PG4TRIGB	3F8	00000000000000000
PG1DC	34E	00000000000000000	PG3FPCIL	3A4	00000000000000000	PG4TRIGC	3FA	00000000000000000
PG1DCA	350	00000000	PG3FPCIH	3A6	0000-00000000000	PG4DTL	3FC	000000000000000
PG1PER	352	00000000000000000	PG3CLPCIL	3A8	00000000000000000	PG4DTH	3FE	000000000000000

TABLE 4-6: SFR BLOCK 400h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
High-Speed F	WM (Con	tinued)	PG6FPCIH	448	0000-00000000000	PG7DC	492	00000000000000000
PG4CAP	400	00000000000000000	PG6CLPCIL	44A	0000000000000000	PG7DCA	494	00000000
PG5CONL	402	00000000	PG6CLPCIH	44C	0000-00000000000	PG7PER	496	0000000000000000
PG5CONH	404	000-0000000000	PG6FFPCIL	44E	00000000000000000	PG7TRIGA	498	00000000000000000
PG5STAT	406	0000000000000000	PG6FFPCIH	450	0000-00000000000	PG7TRIGB	49A	0000000000000000
PG5IOCONL	408	0000000000000000	PG6SPCIL	452	00000000000000000	PG7TRIGC	49C	0000000000000000
PG5IOCONH	40A	00000-000000	PG6SPCIH	454	0000-00000000000	PG7DTL	49E	00000000000000
PG5EVTL	40C	0000000000000	PG6LEBL	456	00000000000000000	PG7DTH	4A0	00000000000000
PG5EVTH	40E	00000000000000	PG6LEBH	458	0000000	PG7CAP	4A2	00000000000000000
PG5FPCIL	410	00000000000000000	PG6PHASE	45A	00000000000000000	PG8CONL	4A4	000000000
PG5FPCIH	412	0000-00000000000	PG6DC	45C	00000000000000000	PG8CONH	4A6	000-0000000000
PG5CLPCIL	414	00000000000000000	PG6DCA	45E	000000000	PG8STAT	4A8	0000000000000000
PG5CLPCIH	416	0000-00000000000	PG6PER	460	00000000000000000	PG8IOCONL	4AA	0000000000000000
PG5FFPCIL	418	00000000000000000	PG6TRIGA	462	00000000000000000	PG8IOCONH	4AC	00000-000000
PG5FFPCIH	41A	0000-00000000000	PG6TRIGB	464	00000000000000000	PG8EVTL	4AE	0000000000000
PG5SPCIL	41C	00000000000000000	PG6TRIGC	466	00000000000000000	PG8EVTH	4B0	00000000000000
PG5SPCIH	41E	0000-00000000000	PG6DTL	468	000000000000000	PG8FPCIL	4B2	00000000000000000
PG5LEBL	420	00000000000000000	PG6DTH	46A	000000000000000	PG8FPCIH	4B4	0000-00000000000
PG5LEBH	422	0000000	PG6CAP	46C	00000000000000000	PG8CLPCIL	4B6	0000000000000000
PG5PHASE	424	00000000000000000	PG7CONL	46E	000000000	PG8CLPCIH	4B8	0000-00000000000
PG5DC	426	00000000000000000	PG7CONH	470	000-0000000000	PG8FFPCIL	4BA	0000000000000000
PG5DCA	428	00000000	PG7STAT	472	00000000000000000	PG8FFPCIH	4BC	0000-00000000000
PG5PER	42A	00000000000000000	PG7IOCONL	474	00000000000000000	PG8SPCIL	4BE	0000000000000000
PG5TRIGA	42C	00000000000000000	PG7IOCONH	476	00000-000000	PG8SPCIH	4C0	0000-00000000000
PG5TRIGB	42E	0000000000000000	PG7EVTL	478	0000000000000	PG8LEBL	4C2	00000000000000000
PG5TRIGC	430	00000000000000000	PG7EVTH	47A	00000000000000	PG8LEBH	4C4	0000000
PG5DTL	432	00000000000000	PG7FPCIL	47C	00000000000000000	PG8PHASE	4C6	00000000000000000
PG5DTH	434	00000000000000	PG7FPCIH	47E	0000-00000000000	PG8DC	4C8	00000000000000000
PG5CAP	436	00000000000000000	PG7CLPCIL	480	00000000000000000	PG8DCA	4CA	00000000
PG6CONL	438	000000000	PG7CLPCIH	482	0000-00000000000	PG8PER	4CC	00000000000000000
PG6CONH	43A	000-0000000000	PG7FFPCIL	484	00000000000000000	PG8TRIGA	4CE	00000000000000000
PG6STAT	43C	00000000000000000	PG7FFPCIH	486	0000-00000000000	PG8TRIGB	4D0	0000000000000000
PG6IOCONL	43E	00000000000000000	PG7SPCIL	488	00000000000000000	PG8TRIGC	4D2	0000000000000000
PG6IOCONH	440	00000-000000	PG7SPCIH	48A	0000-00000000000	PG8DTL	4D4	00000000000000
PG6EVTL	442	0000000000000	PG7LEBL	48C	00000000000000000	PG8DTH	4D6	000000000000000
PG6EVTH	444	00000000000000	PG7LEBH	48E	0000000	PG8CAP	4D8	0000000000000000
PG6FPCIL	446	00000000000000000	PG7PHASE	490	00000000000000000			

TABLE 4-7: SFR BLOCK 500h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
CAN	CAN		C1TSCONL	5D4	0000000000	C1RXOVIFH	5EA	00000000000000000
C1CONL	5C0	00011101100000	C1TSCONH	5D6	000	C1TXATIFL	5EC	00000000000000000
C1CONH	5C2	0000010010011000	C1VECL	5D8	00000-1000000	C1TXATIFH	5EE	00000000000000000
C1NBTCFGL	5C4	00001111-0001111	C1VECH	5DA	11000000-1000000	C1TXREQL	5F0	00000000000000000
C1NBTCFGH	5C6	0000000000111110	C1INTL	5DC	000000000000	C1TXREQH	5F2	00000000000000000
C1DBTCFGL	5C8	00110011	C1INTH	5DE	000000000000	C1TRECL	5F4	00000000000000000
C1DBTCFGH	5CA	0000000001110	C1RXIFL	5E0	00000000000000000	C1TRECH	5F6	100000
C1TDCL	5CC	00010000000000	C1RXIFH	5E2	00000000000000000	C1BDIAG0L	5F8	00000000000000000
C1TDCH	5CE	10	C1TXIFL	5E4	0000000000000000	C1BDIAG0H	5FA	00000000000000000
C1TBCL	5D0	00000000000000000	C1TXIFH	5E6	00000000000000000	C1BDIAG1L	5FC	00000000000000000
C1TBCH	5D2	00000000000000000	C1RXOVIFL	5E8	0000000000000000	C1BDIAG1H	5FE	00000-000-000000

TABLE 4-8: SFR BLOCK 600h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
CAN (Continue	d)		C1FIFOSTA6	65C	00000000000000	C1FLTOBJ6L	6B0	00000000000000000
C1TEFCONL	600	1-00-0000	C1FIFOUA6L	660	xxxxxxxxxxxxx	C1FLTOBJ6H	6B2	00000000000000000
C1TEFCONH	602	00000	C1FIFOUA6H	662	xxxxxxxxxxxxx	C1MASK6L	6B4	00000000000000000
C1TEFSTA	604	0000	C1FIFOCON7L	664	100x0000000	C1MASK6H	6B6	00000000000000000
C1TEFUAL	608	xxxxxxxxxxxx	C1FIFOCON7H	666	00000000-1100000	C1FLTOBJ7L	7B8	00000000000000000
C1TEFUAH	60A	xxxxxxxxxxxx	C1FIFOSTA7	668	00000000000000	C1FLTOBJ7H	6BA	00000000000000000
C1FIFOBAL	60C	00000000000000000	C1FIFOUA7L	66C	xxxxxxxxxxxxx	C1MASK7L	6BC	00000000000000000
C1FIFOBAH	60E	00000000000000000	C1FIFOUA7H	66E	xxxxxxxxxxxxx	C1MASK7H	6BE	00000000000000000
C1TXQCONL	610	100x0000000	C1FLTCON0L	670	00000000000	C1FLTOBJ8L	6C0	00000000000000000
C1TXQCONH	612	00000000-1100000	C1FLTCON0H	672	00000000000	C1FLTOBJ8H	6C2	00000000000000000
C1TXQSTA	614	000000000-0-0	C1FLTCON1L	674	00000000000	C1MASK8L	6C4	00000000000000000
C1TXQUAL	618	xxxxxxxxxxxx	C1FLTCON1H	676	00000000000	C1MASK8H	6C6	00000000000000000
C1TXQUAH	61A	xxxxxxxxxxxx	C1FLTCON2L	678	00000000000	C1FLTOBJ9L	6C8	00000000000000000
C1FIFOCON1L	61C	100x0000000	C1FLTCON2H	67A	00000000000	C1FLTOBJ9H	6CA	00000000000000000
C1FIFOCON1H	61E	00000000-1100000	C1FLTCON3L	67C	00000000000	C1MASK9L	6CC	00000000000000000
C1FIFOSTA1	620	00000000000000	C1FLTCON3H	67E	00000000000	C1MASK9H	6CE	00000000000000000
C1FIFOUA1L	624	xxxxxxxxxxxx	C1FLTOBJ0L	680	00000000000000000	C1FLTOBJ10L	6D0	00000000000000000
C1FIFOUA1H	626	xxxxxxxxxxxx	C1FLTOBJ0H	682	00000000000000000	C1FLTOBJ10H	6D2	00000000000000000
C1FIFOCON2L	628	100x0000000	C1MASK0L	684	00000000000000000	C1MASK10L	6D4	00000000000000000
C1FIFOCON2H	62A	00000000-1100000	C1MASK0H	686	00000000000000000	C1MASK10H	6D6	00000000000000000
C1FIFOSTA2	62C	00000000000000	C1FLTOBJ1L	688	00000000000000000	C1FLTOBJ11L	6D8	00000000000000000
C1FIFOUA2L	630	xxxxxxxxxxxx	C1FLTOBJ1H	68A	00000000000000000	C1FLTOBJ11H	6DA	00000000000000000
C1FIFOUA2H	632	xxxxxxxxxxxxx	C1MASK1L	68C	00000000000000000	C1MASK11L	6DC	00000000000000000
C1FIFOCON3L	634	100x0000000	C1MASK1H	68E	00000000000000000	C1MASK11H	6DE	00000000000000000
C1FIFOCON3H	636	00000000-1100000	C1FLTOBJ2L	690	00000000000000000	C1FLTOBJ12L	6E0	00000000000000000
C1FIFOSTA3	638	00000000000000	C1FLTOBJ2H	692	00000000000000000	C1FLTOBJ12H	6E2	00000000000000000
C1FIFOUA3L	63C	xxxxxxxxxxxxx	C1MASK2L	694	00000000000000000	C1MASK12L	6E4	00000000000000000
C1FIFOUA3H	63E	xxxxxxxxxxxxx	C1MASK2H	696	00000000000000000	C1MASK12H	6E6	00000000000000000
C1FIFOCON4L	640	100x0000000	C1FLTOBJ3L	698	00000000000000000	C1FLTOBJ13L	6E8	00000000000000000
C1FIFOCON4H	642	00000000-1100000	C1FLTOBJ3H	69A	00000000000000000	C1FLTOBJ13H	6EA	00000000000000000
C1FIFOSTA4	644	00000000000000	C1MASK3L	69C	00000000000000000	C1MASK13L	6EC	00000000000000000
C1FIFOUA4L	648	xxxxxxxxxxxxx	C1MASK3H	69C	00000000000000000	C1MASK13H	6EE	00000000000000000
C1FIFOUA4H	64A	xxxxxxxxxxxxx	C1FLTOBJ4L	6A0	00000000000000000	C1FLTOBJ14L	6F0	00000000000000000
C1FIFOCON5L	64C	100x0000000	C1FLTOBJ4H	6A2	00000000000000000	C1FLTOBJ14H	6F2	00000000000000000
C1FIFOCON5H	64E	00000000-1100000	C1MASK4L	6A4	00000000000000000	C1MASK14L	6F4	00000000000000000
C1FIFOSTA5	650	00000000000000	C1MASK4H	6A6	00000000000000000	C1MASK14H	6F6	00000000000000000
C1FIFOUA5L	654	xxxxxxxxxxxxx	C1FLTOBJ5L	6A8	00000000000000000	C1FLTOBJ15L	6F8	0000000000000000
C1FIFOUA5H	656	xxxxxxxxxxxxx	C1FLTOBJ5H	6AA	00000000000000000	C1FLTOBJ15H	6FA	00000000000000000
C1FIFOCON6L	658	100x0000000	C1MASK5L	6AC	00000000000000000	C1MASK15L	6FC	00000000000000000
C1FIFOCON6H	65A	00000000-1100000	C1MASK5H	6AE	00000000000000000	C1MASK15H	6FE	00000000000000000

TABLE 4-9: SFR BLOCK 800h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
Interrupts			IPC3	846	-100-100-100-100	IPC35	886	-100-100
IFS0	800	0000000000-00000	IPC4	848	-100-100-100-100	IPC36	888	100
IFS1	802	000000000-000000	IPC5	84A	-100100-100	IPC37	88A	100-100
IFS2	804	00000-00-0000	IPC6	84C	-100-100-100-100	IPC38	88C	100-100
IFS3	806	00000000-0-00000	IPC7	84E	-100-100-100-100	IPC40	890	100-100
IFS4	808	0000000000000000	IPC8	850	-100-100	IPC42	894	-100-100-100-100
IFS5	80A	0000000000000000	IPC9	852	100-100-100	IPC43	896	-100-100-100-100
IFS6	80C	00000000000000000	IPC10	854	-100100-100	IPC44	898	-100-100-100-100
IFS7	80E	00000000000000000	IPC11	856	-100-100-100-100	IPC45	89A	100-100-100
IFS8	810	000	IPC12	858	-100-100-100-100	IPC47	89E	-100-100-100
IFS9	812	00-000	IPC13	85A	100100	IPC48	8A0	-100-100-100-100
IFS10	814	0000000000	IPC14	85C	-100-100-100-100	INTCON1	8C0	0000000000-0000-
IFS11	816	0000000000	IPC15	85E	-100-100-100	INTCON2	8C2	00000000
IFS12	818	0000	IPC16	860	-100100-100	INTCON3	8C4	000
IEC0	820	0000000000-00000	IPC17	862	-100-100-100-100	INTCON4	8C6	00
IEC1	822	000000000-000000	IPC18	864	-100-100-100-100	INTTREG	8C8	000-0000-0000000
IEC2	824	00000-00-0000	IPC19	866	-100-100-100-100	Flash		
IEC3	826	00000000-0-00000	IPC20	868	-100-100-100	NVMCON	8D0	000000000000
IEC4	828	0000000000000000	IPC21	86A	-100-100-100-100	NVMADR	8D2	00000000000000000
IEC5	82A	0000000000000000	IPC22	86C	-100-100-100-100	NVMADRU	8D4	000000000
IEC6	82C	00000000000000000	IPC23	86E	-100-100-100-100	NVMKEY	8D6	000000000
IEC7	82E	00000000000000000	IPC24	870	-100-100-100-100	NVMSRCADRL	8D8	00000000000000000
IEC8	830	00	IPC25	872	-100-100-100-100	NVMSRCADRH	8DA	000000000
IEC9	832	00-000	IPC26	874	-100-100-100-100	CBG		
IEC10	834	0000000000	IPC27	876	-100-100-100-100	AMPCON1L	8DC	000
IEC11	836	0000000000	IPC28	878	-100-100-100-100	AMPCON1H	8DE	000
IEC12	838	0000	IPC29	87A	-100-100-100-100	BIASCON	8F0	0000
IPC0	840	-100-100-100-100	IPC30	87C	-100-100-100-100	IBIASCON0L	8F4	000000000000
IPC1	842	-100-100100	IPC31	87E	-100-100-100-100	IBIASCON0H	8F6	000000000000
IPC2	844	-100-100-100-100	IPC32	880	100			_

TABLE 4-10: SFR BLOCK 900h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
PTG			CCP1CON3H	95A	00000-00	CCP3PRL	9AC	11111111111111111
PTGCST	900	00-00000x00	CCP1STATL	95C	000xx0000	CCP3PRH	9AE	1111111111111111
PTGCON	902	000000000000-000	CCP1STATH	95E	00000	CCP3RAL	9B0	00000000000000000
PTGBTE	904	xxxxxxxxxxxxx	CCP1TMRL	960	00000000000000000	CCP3RBL	9B4	00000000000000000
PTGBTEH	906	00000000000000000	CCP1TMRH	962	00000000000000000	CCP3BUFL	9B8	00000000000000000
PTGHOLD	908	00000000000000000	CCP1PRL	964	1111111111111111	CCP3BUFH	9BA	00000000000000000
PTGT0LIM	90C	00000000000000000	CCP1PRH	966	1111111111111111	CCP4CON1L	9BC	000000000000000
PTGT1LIM	910	00000000000000000	CCP1RAL	968	00000000000000000	CCP4CON1H	9BE	00000000000000
PTGSDLIM	914	00000000000000000	CCP1RBL	96C	00000000000000000	CCP4CON2L	9C0	00-000000000
PTGC0LIM	918	00000000000000000	CCP1BUFL	970	00000000000000000	CCP4CON2H	9C2	100-00000
PTGC1LIM	91C	00000000000000000	CCP1BUFH	972	00000000000000000	CCP4CON3H	9C6	00000-00
PTGADJ	920	00000000000000000	CCP2CON1L	974	000000000000000	CCP4STATL	9C8	000xx0000
PTGL0	924	00000000000000000	CCP2CON1H	976	00000000000000	CCP4STATH	9CA	00000
PTGQPTR	928	00000	CCP2CON2L	978	00-000000000	CCP4TMRL	9CC	00000000000000000
PTGQUE0	930	xxxxxxxxxxxxx	CCP2CON2H	97A	0100-00000	CCP4TMRH	9CE	00000000000000000
PTGQUE1	932	xxxxxxxxxxxxx	CCP2CON3H	97E	00000-00	CCP4PRL	9D0	11111111111111111
PTGQUE2	934	xxxxxxxxxxxxx	CCP2STATL	980	000xx0000	CCP4PRH	9D2	11111111111111111
PTGQUE3	936	xxxxxxxxxxxxx	CCP2STATH	982	00000	CCP4RAL	9D4	00000000000000000
PTGQUE4	938	xxxxxxxxxxxxx	CCP2TMRL	984	00000000000000000	CCP4RBL	9D8	00000000000000000
PTGQUE5	93A	xxxxxxxxxxxxx	CCP2TMRH	986	00000000000000000	CCP4BUFL	9DC	00000000000000000
PTGQUE6	93C	xxxxxxxxxxxxx	CCP2PRL	988	1111111111111111	CCP4BUFH	9DE	00000000000000000
PTGQUE7	93E	xxxxxxxxxxxxx	CCP2PRH	98A	1111111111111111	CCP5CON1L	9E0	000000000000000
PTGQUE8	940	xxxxxxxxxxxxx	CCP2RAL	98C	00000000000000000	CCP5CON1H	9E2	00000000000000
PTGQUE9	942	xxxxxxxxxxxxx	CCP2RBL	990	00000000000000000	CCP5CON2L	9E4	00-000000000
PTGQUE10	944	xxxxxxxxxxxxx	CCP2BUFL	994	00000000000000000	CCP5CON2H	9E6	100-00000
PTGQUE11	946	xxxxxxxxxxxxx	CCP2BUFH	996	00000000000000000	CCP5CON3H	9EA	00000-00
PTGQUE12	948	xxxxxxxxxxxxx	CCP3CON1L	998	000000000000000	CCP5STATL	9EC	000xx0000
PTGQUE13	94A	xxxxxxxxxxxxx	CCP3CON1H	99A	00000000000000	CCP5STATH	9EE	00000
PTGQUE14	94C	xxxxxxxxxxxxx	CCP3CON2L	99C	00-000000000	CCP5TMRL	9F0	00000000000000000
PTGQUE15	94E	xxxxxxxxxxxxx	CCP3CON2H	99E	100-00000	CCP5TMRH	9F2	0000000000000000
CCP			CCP3CON3H	9A2	00000-00	CCP5PRL	9F4	11111111111111111
CCP1CON1L	950	000000000000000	CCP3STATL	9A4	000xx0000	CCP5PRH	9F6	11111111111111111
CCP1CON1H	952	00000000000000	CCP3STATH	9A6	00000	CCP5RAL	9F8	00000000000000000
CCP1CON2L	954	00-000000000	CCP3TMRL	9A8	00000000000000000	CCP5RBL	9FC	00000000000000000
CCP1CON2H	956	100-00000	CCP3TMRH	9AA	00000000000000000			

TABLE 4-11: SFR BLOCK A00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
CCP (Continu	ied)		CCP7RBL	A44	00000000000000000	CCP9RAL	A88	00000000000000000
CCP5BUFL	A00	00000000000000000	CCP7BUFL	A48	00000000000000000	CCP9RBL	A8C	00000000000000000
CCP5BUFH	A02	00000000000000000	CCP7BUFH	A4A	00000000000000000	CCP9BUFL	A90	00000000000000000
CCP6CON1L	A04	000000000000000	CCP8CON1L	A4C	000000000000000	CCP9BUFH	A92	00000000000000000
CCP6CON1H	A06	00000000000000	CCP8CON1H	A4E	00000000000000	DMA		
CCP6CON2L	A08	00-000000000	CCP8CON2L	A50	00-000000000	DMACON	ABC	00
CCP6CON2H	A0A	100-00000	CCP8CON2H	A52	0100-00000	DMABUF	ABE	00000000000000000
CCP6CON3H	A0E	00000-00	CCP8CON3H	A56	00000-00	DMAL	AC0	00000000000000000
CCP6STATL	A10	000xx0000	CCP8STATL	A58	000xx0000	DMAH	AC2	00000000000000000
CCP6STATH	A12	00000	CCP8STATH	A5A	00000	DMACH0	AC4	00000000000
CCP6TMRL	A14	00000000000000000	CCP8TMRL	A5C	00000000000000000	DMAINT0	AC6	000000000000
CCP6TMRH	A16	00000000000000000	CCP8TMRH	A5E	00000000000000000	DMASRC0	AC8	00000000000000000
CCP6PRL	A18	1111111111111111	CCP8PRL	A60	1111111111111111	DMADST0	ACA	00000000000000000
CCP6PRH	A1A	1111111111111111	CCP8PRH	A62	1111111111111111	DMACNT0	ACC	00000000000000001
CCP6RAL	A1C	00000000000000000	CCP8RAL	A64	00000000000000000	DMACH1	ACE	00000000000
CCP6RBL	A20	00000000000000000	CCP8RBL	A68	00000000000000000	DMAINT1	AD0	000000000000
CCP6BUFL	A24	00000000000000000	CCP8BUFL	A6C	00000000000000000	DMASRC1	AD2	00000000000000000
CCP6BUFH	A26	00000000000000000	CCP8BUFH	A6E	00000000000000000	DMADST1	AD4	00000000000000000
CCP7CON1L	A28	000000000000000	CCP9CON1L	A70	000000000000000	DMACNT1	AD6	00000000000000001
CCP7CON1H	A2A	00000000000000	CCP9CON1H	A72	00000000000000	DMACH2	AD8	00000000000
CCP7CON2L	A2C	00-000000000	CCP9CON2L	A74	00-000000000	DMAINT2	ADA	000000000000
CCP7CON2H	A2E	100-00000	CCP9CON2H	A76	00000100-00000	DMASRC2	ADC	00000000000000000
CCP7CON3H	A32	00000-00	CCP9CON3L	A78	000000	DMADST2	ADE	00000000000000000
CCP7STATL	A34	000xx0000	CCP9CON3H	A7A	0000-000000000	DMACNT2	AE0	00000000000000001
CCP7STATH	A36	00000	CCP9STATL	A7C	000xx0000	DMACH3	AE2	00000000000
CCP7TMRL	A38	00000000000000000	CCP9STATH	A7E	00000	DMAINT3	AE4	000000000000
CCP7TMRH	A3A	00000000000000000	CCP9TMRL	A80	00000000000000000	DMASRC3	AE6	00000000000000000
CCP7PRL	A3C	1111111111111111	CCP9TMRH	A82	00000000000000000	DMADST3	AE8	00000000000000000
CCP7PRH	A3E	1111111111111111	CCP9PRL	A84	1111111111111111	DMACNT3	AEA	00000000000000001
CCP7RAL	A40	00000000000000000	CCP9PRH	A86	1111111111111111			

TABLE 4-12: SFR BLOCK B00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
ADC			ADCMP1LO	B44	00000000000000000	ADTRIG2H	B8A	00000000000000000
ADCON1L	B00	000-00000000	ADCMP1HI	B46	00000000000000000	ADTRIG3L	B8C	00000000000000000
ADCON1H	B02	011	ADCMP2ENL	B48	00000000000000000	ADTRIG3H	B8E	00000000000000000
ADCON2L	B04	00-0000000000000	ADCMP2ENH	B4A	0000000000	ADTRIG4L	B90	00000000000000000
ADCON2H	B06	00-0000000000000	ADCMP2LO	B4C	00000000000000000	ADTRIG4H	B92	00000000000000000
ADCON3L	B08	00000000000000000	ADCMP2HI	B4E	00000000000000000	ADTRIG5L	B94	00000000000000000
ADCON3H	B0A	000000000xx	ADCMP3ENL	B50	00000000000000000	ADTRIG5H	B96	00000000000000000
ADCON4L	B0C	xx	ADCMP3ENH	B52	0000000000	ADTRIG6L	B98	00000000000000000
ADCON4H	B0E	000000	ADCMP3LO	B54	00000000000000000	ADCMP0CON	BA0	00000000000000000
ADMOD0L	B10	00000000000000000	ADCMP3HI	B56	00000000000000000	ADCMP1CON	BA4	00000000000000000
ADMOD0H	B12	00000000000000000	ADFL0DAT	B68	00000000000000000	ADCMP2CON	BA8	00000000000000000
ADMOD1L	B14	00000000000000000	ADFL0CON	B6A	xxx00000000000000	ADCMP3CON	BAC	00000000000000000
ADMOD1H	B16	0000	ADFL1DAT	B6C	00000000000000000	ADLVLTRGL	BD0	00000000000000000
ADIEL	B20	xxxxxxxxxxxx	ADFL1CON	B6E	xxx00000000000000	ADLVLTRGH	BD2	xxxxxxxxx
ADIEH	B22	xxxxxxxxxx	ADFL2DAT	B70	00000000000000000	ADCORE0L	BD4	00000000000000000
ADSTATL	B30	00000000000000000	ADFL2CON	B72	xxx00000000000000	ADCORE0H	BD6	0000001100000000
ADSTATH	B32	0000000000	ADFL3DAT	B74	00000000000000000	ADCORE1L	BD8	00000000000000000
ADCMP0ENL	B38	00000000000000000	ADFL3CON	B76	xxx00000000000000	ADCORE1H	BDA	0000001100000000
ADCMP0ENH	ВЗА	0000000000	ADTRIG0L	B80	00000000000000000	ADEIEL	BF0	xxxxxxxxxxxxx
ADCMP0LO	B3C	00000000000000000	ADTRIG0H	B82	00000000000000000	ADEIEH	BF2	xxxxxxxxxx
ADCMP0HI	B3E	00000000000000000	ADTRIG1L	B84	00000000000000000	ADEISTATL	BF8	xxxxxxxxxxxx
ADCMP1ENL	B40	00000000000000000	ADTRIG1H	B86	00000000000000000	ADEISTATH	BFA	xxxxxxxxxx
ADCMP1ENH	B42	0000000000	ADTRIG2L	B88	00000000000000000			

TABLE 4-13: SFR BLOCK C00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
ADC (Continu	ied)		ADCBUF16	C2C	00000000000000000	SLP1CONH	C92	000
ADCON5L	C00	0	ADCBUF17	C2E	00000000000000000	SLP1DAT	C94	00000000000000000
ADCON5H	C02	xxxx0	ADCBUF18	C30	00000000000000000	DAC2CONL	C98	000000x0000000
ADCBUF0	C0C	00000000000000000	ADCBUF19	C32	00000000000000000	DAC2CONH	C9A	0000000000
ADCBUF1	C0E	00000000000000000	ADCBUF20	C34	00000000000000000	DAC2DATL	C9C	00000000000000000
ADCBUF2	C10	00000000000000000	ADCBUF21	C36	00000000000000000	DAC2DATH	C9E	00000000000000000
ADCBUF3	C12	00000000000000000	ADCBUF22	C38	00000000000000000	SLP2CONL	CA0	00000000000000000
ADCBUF4	C14	00000000000000000	ADCBUF23	C3A	00000000000000000	SLP2CONH	CA2	000
ADCBUF5	C16	00000000000000000	ADCBUF24	C3C	00000000000000000	SLP2DAT	CA4	00000000000000000
ADCBUF6	C18	00000000000000000	ADCBUF25	C3E	00000000000000000	DAC3CONL	CA8	000000x0000000
ADCBUF7	C1A	00000000000000000	DAC			DAC3CONH	CAA	0000000000
ADCBUF8	C1C	00000000000000000	DACCTRL1L	C80	00000-000	DAC3DATL	CAC	00000000000000000
ADCBUF9	C1E	00000000000000000	DACCTRL2L	C84	0001010101	DAC3DATH	CAE	00000000000000000
ADCBUF10	C20	00000000000000000	DACCTRL2H	C86	0010001010	SLP3CONL	CB0	00000000000000000
ADCBUF11	C22	00000000000000000	DAC1CONL	C88	000000x0000000	SLP3CONH	CB2	000
ADCBUF12	C24	00000000000000000	DAC1CONH	C8A	0000000000	SLP3DAT	CB4	00000000000000000
ADCBUF13	C26	00000000000000000	DAC1DATL	C8C	00000000000000000	VREGCON	CFC	000000
ADCBUF14	C28	00000000000000000	DAC1DATH	C8E	00000000000000000			
ADCBUF15	C2A	000000000000000000000000000000000000000	SLP1CONL	C90	00000000000000000			

TABLE 4-14: SFR BLOCK D00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
PPS			RPINR21	D2E	1111111111111111	RPOR4	D88	000000000000
RPCON	D00	0	RPINR22	D30	1111111111111111	RPOR5	D8A	000000000000
RPINR0	D04	11111111	RPINR23	D32	11111111	RPOR6	D8C	000000000000
RPINR1	D06	1111111111111111	RPINR26	D38	11111111	RPOR7	D8E	000000000000
RPINR2	D08	11111111	RPINR27	D3A	1111111111111111	RPOR8	D90	000000000000
RPINR3	D0A	11111111111111111	RPINR29	D3E	1111111111111111	RPOR9	D92	000000000000
RPINR4	D0C	11111111111111111	RPINR30	D40	111111111	RPOR10	D94	000000000000
RPINR5	D0E	1111111111111111	RPINR32	D44	11111111	RPOR11	D96	000000000000
RPINR6	D10	1111111111111111	RPINR33	D46	11111111	RPOR12	D98	000000000000
RPINR7	D12	1111111111111111	RPINR37	D4E	1111111111111111	RPOR13	D9A	000000000000
RPINR8	D14	11111111111111111	RPINR38	D50	11111111	RPOR14	D9C	000000000000
RPINR9	D16	1111111111111111	RPINR42	D58	1111111111111111	RPOR15	D9E	000000000000
RPINR10	D18	1111111111111111	RPINR43	D5A	1111111111111111	RPOR16	DA0	000000000000
RPINR11	D1A	1111111111111111	RPINR44	D5C	1111111111111111	RPOR17	DA2	000000000000
RPINR12	D1C	1111111111111111	RPINR45	D5E	1111111111111111	RPOR18	DA4	000000000000
RPINR13	D1E	1111111111111111	RPINR46	D60	1111111111111111	RPOR19	DA6	000000000000
RPINR14	D20	1111111111111111	RPINR47	D62	1111111111111111	RPOR20	DA8	000000000000
RPINR15	D22	11111111111111111	RPINR48	D64	1111111111111111	RPOR21	DAA	000000000000
RPINR16	D24	11111111111111111	RPINR49	D66	11111111	RPOR22	DAC	000000000000
RPINR17	D26	1111111111111111	RPOR0	D80	000000000000	RPOR23	DAE	000000000000
RPINR18	D28	1111111111111111	RPOR1	D82	000000000000	RPOR24	DB0	000000000000
RPINR19	D2A	1111111111111111	RPOR2	D84	000000000000	RPOR25	DB2	000000000000
RPINR20	D2C	1111111111111111	RPOR3	D86	000000000000	RPOR26	DB4	000000000000

TABLE 4-15: SFR BLOCK E00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
I/O Ports			CNEN0B	E2C	00000000000000000	CNPUD	E5E	00000000000000000
ANSELA	E00	11111	CNSTATB	E2E	00000000000000000	CNPDD	E60	00000000000000000
TRISA	E02	11111	CNEN1B	E30	00000000000000000	CNCOND	E62	0
PORTA	E04	xxxxx	CNFB	E32	00000000000000000	CNEN0D	E64	00000000000000000
LATA	E06	xxxx	ANSELC	E38	111111	CNSTATD	E66	00000000000000000
ODCA	E08	00000	TRISC	E3A	1111111111111111	CNEN1D	E68	00000000000000000
CNPUA	E0A	00000	PORTC	E3C	xxxxxxxxxxxxx	CNFD	E6A	00000000000000000
CNPDA	E0C	00000	LATC	E3E	xxxxxxxxxxxxx	ANSELE	E70	1111
CNCONA	E0E	0	ODCC	E40	00000000000000000	TRISE	E72	1111111111111111
CNEN0A	E10	00000	CNPUC	E42	00000000000000000	PORTE	E74	xxxxxxxxxxxxx
CNSTATA	E12	00000	CNPDC	E44	00000000000000000	LATE	E76	xxxxxxxxxxxxx
CNEN1A	E14	00000	CNCONC	E46	0	ODCE	E78	00000000000000000
CNFA	E16	00000	CNEN0C	E48	00000000000000000	CNPUE	E7A	00000000000000000
ANSELB	E1C	11111111	CNSTATC	E4A	00000000000000000	CNPDE	E7C	00000000000000000
TRISB	E1E	1111111111111111	CNEN1C	E4C	00000000000000000	CNCONE	E7E	0
PORTB	E20	xxxxxxxxxxxxxx	CNFC	E4E	00000000000000000	CNEN0E	E80	00000000000000000
LATB	E22	xxxxxxxxxxxxxx	ANSELD	E54	1-11	CNSTATE	E82	00000000000000000
ODCB	E24	00000000000000000	TRISD	E56	1111111111111111	CNEN1E	E84	00000000000000000
CNPUB	E26	00000000000000000	PORTD	E58	xxxxxxxxxxxxx	CNFE	E86	00000000000000000
CNPDB	E28	00000000000000000	LATD	E5A	xxxxxxxxxxxxx	Memory BIST		
CNCONB	E2A	0	ODCD	E5C	00000000000000000	MBISTCON	EFC	1

TABLE 4-16: SFR BLOCK F00h

Register	Address	All Resets	Register	Address	All Resets	Register	Address	All Resets
UART3			I2C3TRN	F70	11111111	WDTCONH	FB6	0000000000000000
U3MODE	F00	000-0000000000	I2C3RCV	F74	000000000	REFO		
U3MODEH	F02	0000000000000	Reset and Oscillator			REFOCONL	FB8	000-000000
U3STA	F04	0000000010000000	RCON	F80	xxx01x0xxxxx	REFOCONH	FBA	00000000000000000
U3STAH	F06	0000-00000101110	OSCCON	F84	0000-ууу0-0-0-0	REFOTRIML	FBC	000000000
U3BRG	F08	00000000000000000	CLKDIV	F86	00110000000001	Processor		
U3BRGH	F0A	0000	PLLFBD	F88	000010010110	PCTRAPL	FC0	xxxxxxxxxxxxx
U3RXREG	F0C	xxxxxxxx	PLLDIV	F8A	00-001-001	PCTRAPH	FC2	xxxxxxxx
U3TXREG	F10	xxxxxxxx	OSCTUN	F8C	000000	FEXL	FC4	xxxxxxxxxxxxx
U3P1	F14	000000000	ACLKCON1	F8E	000-00001	FEXH	FC6	xxxxxxxx
U3P2	F16	000000000	APLLFBD1	F90	000010010110	FEX2L	FC8	xxxxxxxxxxxxx
U3P3	F18	00000000000000000	APLLDIV1	F92	00-001-001	FEX2H	FCA	xxxxxxxx
U3P3H	F1A	00000000	CANCLKCON	F9A	00000-0000000	VISI	FCC	xxxxxxxxxxxxx
U3TXCHK	F1C	00000000	DCOTUN	F9C	000000000000	DPCL	FCE	xxxxxxxxxxxxx
U3RXCHK	F1E	000000000	DCOCON	F9E	0-xxxx	DPCH	FD0	xxxxxxxx
U3SCCON	F20	00000-	PMD		APPO	FD2	xxxxxxxxxxxxx	
U3SCINT	F22	00-00000-000	PMD1	FA4	000-00000-00	APPI	FD4	xxxxxxxxxxxxx
U3INT	F24	000-	PMD2	FA6	000000000	APPS	FD6	xxxx
I2C3			PMD3	FA8	00-0-000-	STROUTL	FD8	xxxxxxxxxxxxx
I2C3CONL	F5C	010000000000000	PMD4	FAA	0	STROUTH	FDA	xxxxxxxxxxxxx
I2C3CONH	F5E	0000000	PMD6	FAE	0000	STROVCNT	FDC	xxxxxxxxxxxxx
I2C3 STAT	F60	00000000000000	PMD7	FB0	0000	JDATAL	FFA	00000000000000000
I2C3ADD	F64	0000000000	PMD8	FB2	000000000-	JDATAH	FFC	00000000000000000
I2C3MSK	F68	0000000000	WDT					
I2C3BRG	F6C	00000000000000000	WDTCONL	FB4	00000000000000			

Legend: x = unknown or indeterminate value; "-" =unimplemented bits; y = value set by Configuration bits. Address values are in hexadecimal. Reset values are in binary.

4.4.1 PAGED MEMORY SCHEME


The dsPIC33CK256MP508 architecture extends the available Data Space through a paging scheme, which allows the available Data Space to be accessed using MOV instructions in a linear fashion for pre- and post-modified Effective Addresses (EAs). The upper half of the base Data Space address is used in conjunction with the Data Space Read Page (DSRPAG) register to form the Program Space Visibility (PSV) address.


The Data Space Read Page (DSRPAG) register is located in the SFR space. Construction of the PSV address is shown in Figure 4-11. When DSRPAG<9> = 1 and the base address bit, EA<15> = 1, the DSRPAG<8:0> bits are concatenated onto EA<14:0> to form the 24-bit PSV read address.

The paged memory scheme provides access to multiple 32-Kbyte windows in the PSV memory. The Data Space Read Page (DSRPAG) register, in combination with the upper half of the Data Space address, can provide up to 8 Mbytes of PSV address space. The paged data memory space is shown in Figure 4-12.

The Program Space (PS) can be accessed with a DSRPAG of 0x200 or greater. Only reads from PS are supported using the DSRPAG.

FIGURE 4-11: PROGRAM SPACE VISIBILITY (PSV) READ ADDRESS GENERATION





When a PSV page overflow or underflow occurs, EA<15> is cleared as a result of the register indirect EA calculation. An overflow or underflow of the EA in the PSV pages can occur at the page boundaries when:

- The initial address, prior to modification, addresses the PSV page
- The EA calculation uses Pre- or Post-Modified Register Indirect Addressing; however, this does not include Register Offset Addressing

In general, when an overflow is detected, the DSRPAG register is incremented and the EA<15> bit is set to keep the base address within the PSV window. When an underflow is detected, the DSRPAG register is decremented and the EA<15> bit is set to keep the base

address within the PSV window. This creates a linear PSV address space, but only when using Register Indirect Addressing modes.

Exceptions to the operation described above arise when entering and exiting the boundaries of Page 0 and PSV spaces. Table 4-17 lists the effects of overflow and underflow scenarios at different boundaries.

In the following cases, when overflow or underflow occurs, the EA<15> bit is set and the DSRPAG is not modified; therefore, the EA will wrap to the beginning of the current page:

- · Register Indirect with Register Offset Addressing
- · Modulo Addressing
- · Bit-Reversed Addressing

TABLE 4-17: OVERFLOW AND UNDERFLOW SCENARIOS AT PAGE 0 AND PSV SPACE BOUNDARIES^(2,3,4)

O/U, R/W	Operation		Before		After			
		DSRPAG	DS EA<15>	Page Description	DSRPAG	DS EA<15>	Page Description	
O, Read	[++Wn]	DSRPAG = 0x2FF	1	PSV: Last Isw page	DSRPAG = 0x300	1	PSV: First MSB page	
O, Read	or [Wn++]	DSRPAG = 0x3FF	1	PSV: Last MSB page	DSRPAG = 0x3FF	0	See Note 1	
U, Read		DSRPAG = 0x001	1	PSV page	DSRPAG = 0x001	0	See Note 1	
U, Read	[Wn] or [Wn]	DSRPAG = 0x200	1	PSV: First Isw page	DSRPAG = 0x200	0	See Note 1	
U, Read		DSRPAG = 0x300	1	PSV: First MSB page	DSRPAG = 0x2FF	1	PSV: Last Isw page	

Legend: O = Overflow, U = Underflow, R = Read, W = Write

- Note 1: The Register Indirect Addressing now addresses a location in the base Data Space (0x0000-0x8000).
 - 2: An EDS access, with DSRPAG = 0x000, will generate an address error trap.
 - 3: Only reads from PS are supported using DSRPAG.
 - **4:** Pseudolinear Addressing is not supported for large offsets.

4.4.1.1 Extended X Data Space

The lower portion of the base address space range, between 0x0000 and 0x7FFF, is always accessible, regardless of the contents of the Data Space Read Page register. It is indirectly addressable through the register indirect instructions. It can be regarded as being located in the default EDS Page 0 (i.e., EDS address range of 0x0000000 to 0x007FFF with the base address bit, EA<15> = 0, for this address range). However, Page 0 cannot be accessed through the upper 32 Kbytes, 0x8000 to 0xFFFF, of base Data Space in combination with DSRPAG = 0x00. Consequently, DSRPAG is initialized to 0x001 at Reset.

- Note 1: DSRPAG should not be used to access Page 0. An EDS access with DSRPAG set to 0x000 will generate an address error trap.
 - 2: Clearing the DSRPAG in software has no effect

The remaining PSV pages are only accessible using the DSRPAG register in combination with the upper 32 Kbytes, 0x8000 to 0xFFFF, of the base address, where the base address bit. EA<15> = 1.

4.4.1.2 Software Stack

The W15 register serves as a dedicated Software Stack Pointer (SSP), and is automatically modified by exception processing, subroutine calls and returns; however, W15 can be referenced by any instruction in the same manner as all other W registers. This simplifies reading, writing and manipulating the Stack Pointer (for example, creating stack frames).

Note: To protect against misaligned stack accesses, W15<0> is fixed to '0' by the hardware.


W15 is initialized to 0x1000 during all Resets. This address ensures that the SSP points to valid RAM in all dsPIC33CK256MP508 devices and permits stack availability for non-maskable trap exceptions. These can occur before the SSP is initialized by the user software. You can reprogram the SSP during initialization to any location within Data Space.

The Software Stack Pointer always points to the first available free word and fills the software stack, working from lower toward higher addresses. Figure 4-13 illustrates how it pre-decrements for a stack pop (read) and post-increments for a stack push (writes).

When the PC is pushed onto the stack, PC<15:0> are pushed onto the first available stack word, then PC<22:16> are pushed into the second available stack location. For a PC push during any CALL instruction, the MSB of the PC is zero-extended before the push, as shown in Figure 4-13. During exception processing, the MSB of the PC is concatenated with the lower eight bits of the CPU STATUS Register, SR. This allows the contents of SRL to be preserved automatically during interrupt processing.

- Note 1: To maintain system Stack Pointer (W15) coherency, W15 is never subject to (EDS) paging, and is therefore, restricted to an address range of 0x0000 to 0xFFFF. The same applies to the W14 when used as a Stack Frame Pointer (SFA = 1).
 - 2: As the stack can be placed in, and can access X and Y spaces, care must be taken regarding its use, particularly with regard to local automatic variables in a C development environment

FIGURE 4-13: CALL STACK FRAME



4.4.2 INSTRUCTION ADDRESSING MODES

The addressing modes shown in Table 4-18 form the basis of the addressing modes optimized to support the specific features of individual instructions. The addressing modes provided in the MAC class of instructions differ from those in the other instruction types.

4.4.2.1 File Register Instructions

Most file register instructions use a 13-bit address field (f) to directly address data present in the first 8192 bytes of data memory (Near Data Space). Most file register instructions employ a Working register, W0, which is denoted as WREG in these instructions. The destination is typically either the same file register or WREG (with the exception of the MUL instruction), which writes the result to a register or register pair. The MOV instruction allows additional flexibility and can access the entire Data Space.

4.4.2.2 MCU Instructions

The three-operand MCU instructions are of the form:

Operand 3 = Operand 1 <function> Operand 2

where Operand 1 is always a Working register (that is, the addressing mode can only be Register Direct), which is referred to as Wb. Operand 2 can be a W register fetched from data memory or a 5-bit literal. The result location can either be a W register or a data memory location. The following addressing modes are supported by MCU instructions:

- · Register Direct
- · Register Indirect
- · Register Indirect Post-Modified
- · Register Indirect Pre-Modified
- · 5-Bit or 10-Bit Literal

Note: Not all instructions support all the addressing modes given above. Individual instructions can support different subsets of these addressing modes.

TABLE 4-18: FUNDAMENTAL ADDRESSING MODES SUPPORTED

Addressing Mode	Description			
File Register Direct	The address of the file register is specified explicitly.			
Register Direct	The contents of a register are accessed directly.			
Register Indirect	The contents of Wn form the Effective Address (EA).			
Register Indirect Post-Modified	The contents of Wn form the EA. Wn is post-modified (incremented or decremented) by a constant value.			
Register Indirect Pre-Modified	Wn is pre-modified (incremented or decremented) by a signed constant value to form the EA.			
Register Indirect with Register Offset (Register Indexed)	The sum of Wn and Wb forms the EA.			
Register Indirect with Literal Offset	The sum of Wn and a literal forms the EA.			

4.4.2.3 Move and Accumulator Instructions

Move instructions, and the DSP accumulator class of instructions, provide a greater degree of addressing flexibility than other instructions. In addition to the addressing modes supported by most MCU instructions, move and accumulator instructions also support Register Indirect with Register Offset Addressing mode, also referred to as Register Indexed mode.

Note: For the MOV instructions, the addressing mode specified in the instruction can differ for the source and destination EA. However, the 4-bit Wb (Register Offset) field is shared by both source and destination (but typically only used by one).

In summary, the following addressing modes are supported by move and accumulator instructions:

- · Register Direct
- · Register Indirect
- · Register Indirect Post-Modified
- · Register Indirect Pre-Modified
- Register Indirect with Register Offset (Indexed)
- Register Indirect with Literal Offset
- · 8-Bit Literal
- 16-Bit Literal

Note:

Not all instructions support all the addressing modes given above. Individual instructions may support different subsets of these addressing modes.

4.4.2.4 MAC Instructions

The dual source operand DSP instructions (CLR, ED, EDAC, MAC, MPY, MPY.N, MOVSAC and MSC), also referred to as MAC instructions, use a simplified set of addressing modes to allow the user application to effectively manipulate the Data Pointers through register indirect tables.

The two-source operand prefetch registers must be members of the set {W8, W9, W10, W11}. For data reads, W8 and W9 are always directed to the X RAGU, and W10 and W11 are always directed to the Y AGU. The Effective Addresses generated (before and after modification) must therefore, be valid addresses within X Data Space for W8 and W9, and Y Data Space for W10 and W11.

Note: Register Indirect with Register Offset Addressing mode is available only for W9 (in X space) and W11 (in Y space).

In summary, the following addressing modes are supported by the ${\tt MAC}$ class of instructions:

- · Register Indirect
- · Register Indirect Post-Modified by 2
- · Register Indirect Post-Modified by 4
- · Register Indirect Post-Modified by 6
- Register Indirect with Register Offset (Indexed)

4.4.2.5 Other Instructions

Besides the addressing modes outlined previously, some instructions use literal constants of various sizes. For example, BRA (branch) instructions use 16-bit signed literals to specify the branch destination directly, whereas the DISI instruction uses a 14-bit unsigned literal field. In some instructions, such as ULNK, the source of an operand or result is implied by the opcode itself. Certain operations, such as a NOP, do not have any operands.

4.4.3 MODULO ADDRESSING

Modulo Addressing mode is a method of providing an automated means to support circular data buffers using hardware. The objective is to remove the need for software to perform data address boundary checks when executing tightly looped code, as is typical in many DSP algorithms.

Modulo Addressing can operate in either Data or Program Space (since the Data Pointer mechanism is essentially the same for both). One circular buffer can be supported in each of the X (which also provides the pointers into Program Space) and Y Data Spaces. Modulo Addressing can operate on any W Register Pointer. However, it is not advisable to use W14 or W15 for Modulo Addressing since these two registers are used as the Stack Frame Pointer and Stack Pointer, respectively.

In general, any particular circular buffer can be configured to operate in only one direction, as there are certain restrictions on the buffer start address (for incrementing buffers) or end address (for decrementing buffers), based upon the direction of the buffer.

The only exception to the usage restrictions is for buffers that have a power-of-two length. As these buffers satisfy the start and end address criteria, they can operate in a Bidirectional mode (that is, address boundary checks are performed on both the lower and upper address boundaries).

4.4.3.1 Start and End Address

The Modulo Addressing scheme requires that a starting and ending address be specified and loaded into the 16-bit Modulo Buffer Address registers: XMODSRT, XMODEND, YMODSRT and YMODEND (see Table 4-2).

Note: Y space Modulo Addressing EA calculations assume word-sized data (LSb of every EA is always clear).

The length of a circular buffer is not directly specified. It is determined by the difference between the corresponding start and end addresses. The maximum possible length of the circular buffer is 32K words (64 Kbytes).

4.4.3.2 W Address Register Selection


The Modulo and Bit-Reversed Addressing Control register, MODCON<15:0>, contains enable flags, as well as a W register field to specify the W Address registers. The XWM and YWM fields select the registers that operate with Modulo Addressing:

- If XWM = 1111, X RAGU and X WAGU Modulo Addressing is disabled
- If YWM = 1111, Y AGU Modulo Addressing is disabled

The X Address Space Pointer W (XWM) register, to which Modulo Addressing is to be applied, is stored in MODCON<3:0> (see Table 4.1). Modulo Addressing is enabled for X Data Space when XWM is set to any value other than '1111' and the XMODEN bit is set (MODCON<15>).

The Y Address Space Pointer W (YWM) register, to which Modulo Addressing is to be applied, is stored in MODCON<7:4>. Modulo Addressing is enabled for Y Data Space when YWM is set to any value other than '1111' and the YMODEN bit (MODCON<14>) is set.

FIGURE 4-14: MODULO ADDRESSING OPERATION EXAMPLE



4.4.3.3 Modulo Addressing Applicability

Modulo Addressing can be applied to the Effective Address (EA) calculation associated with any W register. Address boundaries check for addresses equal to:

- The upper boundary addresses for incrementing buffers
- The lower boundary addresses for decrementing buffers

It is important to realize that the address boundaries check for addresses less than, or greater than, the upper (for incrementing buffers) and lower (for decrementing buffers) boundary addresses (not just equal to). Address changes can, therefore, jump beyond boundaries and still be adjusted correctly.

Note:

The modulo corrected Effective Address is written back to the register only when Pre-Modify or Post-Modify Addressing mode is used to compute the Effective Address. When an address offset (such as [W7 + W2]) is used, Modulo Addressing correction is performed, but the contents of the register remain unchanged.

4.4.4 BIT-REVERSED ADDRESSING

Bit-Reversed Addressing mode is intended to simplify data reordering for radix-2 FFT algorithms. It is supported by the X AGU for data writes only.

The modifier, which can be a constant value or register contents, is regarded as having its bit order reversed. The address source and destination are kept in normal order. Thus, the only operand requiring reversal is the modifier.

4.4.4.1 Bit-Reversed Addressing Implementation

Bit-Reversed Addressing mode is enabled in any of these situations:

- BWMx bits (W register selection) in the MODCON register are any value other than '1111' (the stack cannot be accessed using Bit-Reversed Addressing)
- · The BREN bit is set in the XBREV register
- The addressing mode used is Register Indirect with Pre-Increment or Post-Increment

If the length of a bit-reversed buffer is $M = 2^N$ bytes, the last 'N' bits of the data buffer start address must be zeros

XB<14:0> is the Bit-Reversed Addressing modifier, or 'pivot point', which is typically a constant. In the case of an FFT computation, its value is equal to half of the FFT data buffer size.

Note:

All bit-reversed EA calculations assume word-sized data (LSb of every EA is always clear). The XB value is scaled accordingly to generate compatible (byte) addresses.

When enabled, Bit-Reversed Addressing is executed only for Register Indirect with Pre-Increment or Post-Increment Addressing and word-sized data writes. It does not function for any other addressing mode or for byte-sized data and normal addresses are generated instead. When Bit-Reversed Addressing is active, the W Address Pointer is always added to the address modifier (XB) and the offset associated with the Register Indirect Addressing mode is ignored. In addition, as word-sized data is a requirement, the LSb of the EA is ignored (and always clear).

Note:

Modulo Addressing and Bit-Reversed Addressing can be enabled simultaneously using the same W register, but Bit-Reversed Addressing operation will always take precedence for data writes when enabled.

If Bit-Reversed Addressing has already been enabled by setting the BREN (XBREV<15>) bit, a write to the XBREV register should not be immediately followed by an indirect read operation using the W register that has been designated as the Bit-Reversed Pointer.

FIGURE 4-15: BIT-REVERSED ADDRESSING EXAMPLE




TABLE 4-19: BIT-REVERSED ADDRESSING SEQUENCE (16-ENTRY)

		Norma	al Addres	ss	Bit-Reversed Address					
A3	A2	A1	A0	Decimal	А3	A2	A1	A0	Decimal	
0	0	0	0	0	0	0	0	0	0	
0	0	0	1	1	1	0	0	0	8	
0	0	1	0	2	0	1	0	0	4	
0	0	1	1	3	1	1	0	0	12	
0	1	0	0	4	0	0	1	0	2	
0	1	0	1	5	1	0	1	0	10	
0	1	1	0	6	0	1	1	0	6	
0	1	1	1	7	1	1	1	0	14	
1	0	0	0	8	0	0	0	1	1	
1	0	0	1	9	1	0	0	1	9	
1	0	1	0	10	0	1	0	1	5	
1	0	1	1	11	1	1	0	1	13	
1	1	0	0	12	0	0	1	1	3	
1	1	0	1	13	1	0	1	1	11	
1	1	1	0	14	0	1	1	1	7	
1	1	1	1	15	1	1	1	1	15	

4.4.5 INTERFACING PROGRAM AND DATA MEMORY SPACES

The dsPIC33CK256MP508 family architecture uses a 24-bit wide Program Space (PS) and a 16-bit wide Data Space (DS). The architecture is also a modified Harvard scheme, meaning that data can also be present in the Program Space. To use this data successfully, it must be accessed in a way that preserves the alignment of information in both spaces.

Aside from normal execution, the architecture of the dsPIC33CK256MP508 family devices provides two methods by which Program Space can be accessed during operation:


- Using table instructions to access individual bytes or words anywhere in the Program Space
- Remapping a portion of the Program Space into the Data Space (Program Space Visibility)

Table instructions allow an application to read or write to small areas of the program memory. This capability makes the method ideal for accessing data tables that need to be updated periodically. It also allows access to all bytes of the program word. The remapping method allows an application to access a large block of data on a read-only basis, which is ideal for look-ups from a large table of static data. The application can only access the least significant word of the program word.

TABLE 4-20: PROGRAM SPACE ADDRESS CONSTRUCTION

Access Turns	Access	Program Space Address						
Access Type	Space	<23>	<22:16>	<15>	<14:1>	<0>		
Instruction Access	User	0 PC<22:1>				0		
(Code Execution)		0xxx xxxx xxxx xxxx xxx0						
TBLRD/TBLWT	User	ТВ	LPAG<7:0>	Data EA<15:0>				
(Byte/Word Read/Write)		0	xxx xxxx	xxxx xxxx xxxx xxxx				
	Configuration	TBLPAG<7:0>		Data EA<15:0>				
		1	xxx xxxx	XXXX	xxxx xxxx xxx	X		

FIGURE 4-16: DATA ACCESS FROM PROGRAM SPACE ADDRESS GENERATION



- **Note 1:** The Least Significant bit (LSb) of Program Space addresses is always fixed as '0' to maintain word alignment of data in the Program and Data Spaces.
 - **2:** Table operations are not required to be word-aligned. Table Read operations are permitted in the configuration memory space.

4.4.5.1 Data Access from Program Memory Using Table Instructions

The TBLRDL and TBLWTL instructions offer a direct method of reading or writing the lower word of any address within the Program Space without going through Data Space. The TBLRDH and TBLWTH instructions are the only method to read or write the upper 8 bits of a Program Space word as data.

The PC is incremented by two for each successive 24-bit program word. This allows program memory addresses to directly map to Data Space addresses. Program memory can thus be regarded as two 16-bit wide word address spaces, residing side by side, each with the same address range. TBLRDL and TBLWTL access the space that contains the least significant data word. TBLRDH and TBLWTH access the space that contains the upper data byte.

Two table instructions are provided to move byte or word-sized (16-bit) data to and from Program Space. Both function as either byte or word operations.


- TBLRDL (Table Read Low):
 - In Word mode, this instruction maps the lower word of the Program Space location (P<15:0>) to a data address (D<15:0>)
 - In Byte mode, either the upper or lower byte of the lower program word is mapped to the lower byte of a data address. The upper byte is selected when Byte Select is '1'; the lower byte is selected when it is '0'.

- TBLRDH (Table Read High):
 - In Word mode, this instruction maps the entire upper word of a program address (P<23:16>) to a data address. The 'phantom' byte (D<15:8>) is always '0'.
 - In Byte mode, this instruction maps the upper or lower byte of the program word to D<7:0> of the data address in the TBLRDL instruction. The data is always '0' when the upper 'phantom' byte is selected (Byte Select = 1).

In a similar fashion, two table instructions, TBLWTH and TBLWTL, are used to write individual bytes or words to a Program Space address. The details of their operation are explained in **Section 5.0 "Flash Program Memory"**.

For all table operations, the area of program memory space to be accessed is determined by the Table Page register (TBLPAG). TBLPAG covers the entire program memory space of the device, including user application and configuration spaces. When TBLPAG<7> = 0, the table page is located in the user memory space. When TBLPAG<7> = 1, the page is located in configuration space.





<u> </u>			
NOTES:			

5.0 FLASH PROGRAM MEMORY

- Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Dual Partition Flash Program Memory" (www.microchip.com/DS70005156) in the "dsPIC33/PIC24 Family Reference Manual").
 - 2: Some registers and associated bits described in this section may not be available on all devices.

The dsPIC33CK256MP508 family devices contain internal Flash program memory for storing and executing application code. The memory is readable, writable and erasable during normal operation over the entire VDD range.

Flash memory can be programmed in three ways:

- In-Circuit Serial Programming™ (ICSP™) programming capability
- · Enhanced In-Circuit Serial Programming (Enhanced ICSP)
- Run-Time Self-Programming (RTSP)

ICSP allows for a dsPIC33CK256MP508 family device to be serially programmed while in the end application circuit. This is done with a Programming Clock and Programming Data (PGCx/PGDx) line, and three other lines for power (VDD), ground (VSS) and Master Clear (MCLR). This allows customers to manufacture boards with unprogrammed devices and then program the

device just before shipping the product. This also allows the most recent firmware or a custom firmware to be programmed.

Enhanced In-Circuit Serial Programming uses an on-board bootloader, known as the Program Executive, to manage the programming process. Using an SPI data frame format, the Program Executive can erase, program and verify program memory. For more information on Enhanced ICSP, see the device programming specification.

RTSP is accomplished using TBLRD (Table Read) and TBLWT (Table Write) instructions. With RTSP, the user application can write program memory data, two instruction words or a row at a time, and erase a program memory page.

5.1 Table Instructions and Flash **Programming**

Regardless of the method used, all programming of Flash memory is done with the Table Read and Table Write instructions. These allow direct read and write access to the program memory space from the data memory while the device is in normal operating mode. The 24-bit target address in the program memory is formed using bits<7:0> of the TBLPAG register and the Effective Address (EA) from a W register, specified in the table instruction, as shown in Figure 5-1. The TBLRDL and TBLWTL instructions are used to read or write to bits<15:0> of program memory. TBLRDL and TBLWTL can access program memory in both Word and Byte modes. The TBLRDH and TBLWTH instructions are used to read or write to bits<23:16> of program memory. TBLRDH and TBLWTH can also access program memory in Word or Byte mode.




FIGURE 5-1: ADDRESSING FOR TABLE REGISTERS

5.2 RTSP Operation

The dsPIC33CK256MP508 family Flash program memory array is organized into rows of 128 instructions or 384 bytes. RTSP allows the user application to erase a single page (eight rows or 1024 instructions) of memory at a time and to program one row at a time. It is possible to program two instructions at a time as well.

The page erase and single row write blocks are edge-aligned, from the beginning of program memory, on boundaries of 3072 bytes and 384 bytes, respectively. Table 33-18 in **Section 33.0 "Electrical Characteristics"** lists the typical erase and programming times.

Row programming is performed by loading 384 bytes into data memory and then loading the address of the first byte in that row into the NVMSRCADRL/H register. Once the write has been initiated, the device will automatically load the write latches, and increment the NVMSRCADRL/H and the NVMADR(U) registers until all bytes have been programmed. The RPDF bit (NVMCON<9>) selects the format of the stored data in RAM to be either compressed or uncompressed. See Figure 5-2 for data formatting. Compressed data helps to reduce the amount of required RAM by using the upper byte of the second word for the MSB of the second instruction.

The basic sequence for RTSP word programming is to use the <code>TBLWTL</code> and <code>TBLWTH</code> instructions to load two of the 24-bit instructions into the write latches found in configuration memory space. Refer to Figure 4-1 through Figure 4-5 for write latch addresses. Programming is performed by unlocking and setting the control bits in the NVMCON register as follows:


- Write 0x55 to NVMKEY.
- 2. Write 0xAA to NVMKEY.
- Set the WR bit (NVMCON<15>) as a single operation.

All erase and program operations may optionally use the NVM interrupt to signal the successful completion of the operation. For example, when performing Flash write operations on the Inactive Partition in Dual Partition mode, where the CPU remains running, it is necessary to wait for the NVM interrupt before programming the next block of Flash program memory.

Note: MPLAB® XC16 provides a built-in C language function for unlocking and modifying the NVMCON register:

__builtin_write_NVM()
For more information, see the "MPLAB® XC16 C Compiler User's Guide" (DS50002071).

FIGURE 5-2: UNCOMPRESSED/
COMPRESSED FORMAT



5.3 Programming Operations

A complete programming sequence is necessary for programming or erasing the internal Flash in RTSP mode. The processor stalls (waits) until the programming operation is finished. Setting the WR bit (NVMCON<15>) starts the operation and the WR bit is automatically cleared when the operation is finished.

5.3.1 PROGRAMMING ALGORITHM FOR FLASH PROGRAM MEMORY

Programmers can program two adjacent words (24 bits x 2) of Program Flash Memory at a time on every other word address boundary (0x000002,

0x000006, 0x00000A, etc.). To do this, it is necessary to erase the page that contains the desired address of the location the user wants to change. For protection against accidental operations, the write initiate sequence for NVMKEY must be used to allow any erase or program operation to proceed. After the programming command has been executed, the user application must wait for the programming time until programming is complete. The two instructions following the start of the programming sequence should be NOPS. Refer to Example 5-1 for Flash read and write operations.

EXAMPLE 5-1: FLASH WRITE/READ

```
//Sample code for writing 0x123456 to address locations 0x10000 / 10002
NVMCON = 0x4001;
TBLPAG = 0xFA;
                                 // write latch upper address
NVMADR = 0x0000;
                                 // set target write address of general segment
NVMADRU = 0x0001;
__builtin_tblwtl(0, 0x3456);
                                // load write latches
builtin tblwth (0,0x12);
 builtin tblwtl(2, 0x3456);
                                 // load write latches
builtin tblwth (2,0x12);
asm volatile ("disi #5");
 builtin write NVM();
while ( WR == 1 );
////////Flash Read////////////
//Sample code to read the Flash content of address 0x10000
// readDataL/ readDataH variables need to defined
TBLPAG = 0 \times 0001;
readDataL = __builtin_tblrdl(0x0000);
readDataH = __builtin_tblrdh(0x0000);
```

5.3.2 ERROR CORRECTING CODE (ECC)

In order to improve program memory performance and durability, these devices include Error Correcting Code (ECC) functionality as an integral part of the Flash memory controller. ECC can determine the presence of single bit errors in program data, including which bit is in error, and correct the data automatically without user intervention. ECC cannot be disabled.

When data is written to program memory, ECC generates a 7-bit Hamming code parity value for every two (24-bit) instruction words. The data is stored in blocks of 48 data bits and 7 parity bits; parity data is not memory-mapped and is inaccessible. When the data is read back, the ECC calculates the parity on it and compares it to the previously stored parity value. If a parity mismatch occurs, there are two possible outcomes:

- Single bit error has occurred and has been automatically corrected on readback.
- Double-bit error has occurred and the read data is not changed.

Single bit error occurrence can be identified by the state of the ECCSBEIF (IFS0<13>) bit. An interrupt can be generated when the corresponding interrupt enable bit is set, ECCSBEIE (IEC0<13>). The ECCSTATL register contains the parity information for single bit errors. The SECOUT<7:0> bits field contains the expected calculated SEC parity and the SECIN<7:0> bits contain the actual value from a Flash read operation. The SECSYNDx bits (ECCSTATH<7:0>) indicate the bit position of the single bit error within the 48-bit pair of instruction words. When no error is present, SECINx equals SECOUTx and SECSYNDx is zero.

Double-bit errors result in a generic hard trap. The ECCDBE bit (INTCON4<1>) will be set to identify the source of the hard trap. If no Interrupt Service Routine is implemented for the hard trap, a device Reset will also occur. The ECCSTATH register contains double-bit error status information. The DEDOUT bit is the expected calculated DED parity and DEDIN is the actual value from a Flash read operation. When no error is present, DEDIN equals DEDOUT.

5.3.3 ECC FAULT INJECTION

To test Fault handling, an EEC error can be generated. Both single and double-bit errors can be generated in both the read and write data paths. Read path Fault injection first reads the Flash data and then modifies it prior to entering the ECC logic. Write path Fault injection modifies the actual data prior to it being written into the target Flash and will cause an EEC error on a subsequent Flash read. The following procedure is used to inject a Fault:

- Load the Flash target address into the ECCADDR register.
- Select 1st Fault bit determined by FLT1PTRx (ECCCONH<7:0>). The target bit is inverted to create the Fault.
- If a double Fault is desired, select the 2nd Fault bit determined by FLT2PTRx (ECCCONH<15:8>), otherwise set to all '1's.
- 4. Write 0x55 to NVMKEY.
- 5. Write 0xAA to NVMKEY.
- Set the FLTINJ bit (ECCCONL<0>) in a single operation to enable the ECC Fault injection logic.
- Perform a read or write to the Flash target address.

5.4 ICSP™ Write Inhibit

ICSP Write Inhibit is an access restriction feature that, when activated, restricts all of Flash memory. Once activated, ICSP Write Inhibit permanently prevents ICSP Flash programming and erase operations, and cannot be deactivated. This feature is intended to prevent alteration of Flash memory contents, with behavior similar to One-Time-Programmable (OTP) devices.

RTSP, including erase and programming operations, is not restricted when ICSP Write Inhibit is activated; however, code to perform these actions must be programmed into the device before ICSP Write Inhibit is activated. This allows for a bootloader-type application to alter Flash contents with ICSP Write Inhibit activated.

Entry into ICSP and Enhanced ICSP modes is not affected by ICSP Write Inhibit. In these modes, it will continue to be possible to read configuration memory space and any user memory space regions which are not code protected. With ICSP writes inhibited, an attempt to set WR (NVMCON<15>) = 1 will maintain WR = 0, and instead, set WRERR (NVMCON<13>) = 1. All Enhanced ICSP erase and programming commands will have no effect with self-checked programming commands returning a FAIL response opcode (PASS if the destination already exactly matched the requested programming data).

Once ICSP Write Inhibit is activated, it is not possible for a device executing in Debug mode to erase/write Flash, nor can a debug tool switch the device to Production mode. ICSP Write Inhibit should therefore only be activated on devices programmed for production.

The JTAG port, when enabled, can be used to map ICSP signals to JTAG I/O pins. All Flash erase/ programming operations initiated via the JTAG port will therefore also be blocked after activating ICSP Write Inhibit.

5.4.1 ACTIVATING ICSP™ WRITE INHIBIT

Caution: It is not possible to deactivate ICSP Write Inhibit.

ICSP Write Inhibit is activated by executing a pair of NVMCON double-word programming commands to save two 16-bit activation values in the configuration memory space. The target NVM addresses and values required for activation are shown in Table 5-1. Once both addresses contain their activation values, ICSP Write Inhibit will take permanent effect on the next device Reset. Neither address can be reset, erased or otherwise modified, through any means, after being successfully programmed, even if one of the addresses has not been programmed.

Only the lower 16 data bits stored at the activation addresses are evaluated; the upper 8 bits and second 24-bit word written by the double-word programming (NVMOP<3:0>) should be written as '0's. The addresses can be programmed in any order and also during separate ICSP/Enhanced ICSP/RTSP sessions, but any attempt to program an incorrect 16-bit value or use a row programming operation to program the values will be aborted without altering the existing data.

TABLE 5-1: ICSP™ WRITE INHIBIT ACTIVATION ADDRESSES AND DATA

	Configuration Memory Address	ICSP Write Inhibit Activation Value	
Write Lock 1	0x801034	0x006D63	
Write Lock 2	0x801038	0x006870	

5.5 Dual Partition Flash Configuration

For dsPIC33CK256MP508 devices operating in Dual Partition Flash Program Memory modes, the Inactive Partition can be erased and programmed without stalling the processor. The same programming algorithms are used for programming and erasing the Flash in the Inactive Partition, as described in **Section 5.2** "RTSP **Operation**". On top of the page erase option, the entire Flash memory of the Inactive Partition can be erased by configuring the NVMOP<3:0> bits in the NVMCON register.

Note 1: The application software to be loaded into the Inactive Partition will have the address of the Active Partition. The bootloader firmware will need to offset the address by 0x400000 in order to write to the Inactive Partition.

5.5.1 FLASH PARTITION SWAPPING

The Boot Sequence Number is used for determining the Active Partition at start-up and is encoded within the FBTSEQ Configuration register bits. Unlike most Configuration registers, which only utilize the lower 16 bits of the program memory, FBTSEQ is a 24-bit Configuration Word. The Boot Sequence Number (BSEQ) is a 12-bit value and is stored in FBTSEQ twice. The true value is stored in bits, FBTSEQ<11:0>, and its complement is stored in bits, FBTSEQ<23:12>. At device Reset, the sequence numbers are read and the partition with the lowest sequence number becomes the Active Partition. If one of the Boot Sequence Numbers is invalid, the device will select the partition with the valid Boot Sequence Number, or default to Partition 1 if both sequence numbers are invalid. See Section 30.0 "Special Features" for more information.

The BOOTSWP instruction provides an alternative means of swapping the Active and Inactive Partitions (soft swap) without the need for a device Reset. The BOOTSWP must always be followed by a GOTO instruction. The BOOTSWP instruction swaps the Active and Inactive Partitions, and the PC vectors to the location specified by the GOTO instruction in the newly Active Partition.

It is important to note that interrupts should temporarily be disabled while performing the soft swap sequence and that after the partition swap, all peripherals and interrupts which were enabled remain enabled. Additionally, the RAM and stack will maintain state after the switch. As a result, it is recommended that applications using soft swaps jump to a routine that will reinitialize the device in order to ensure the firmware runs as expected. The Configuration registers will have no effect during a soft swap.

For robustness of operation, in order to execute the BOOTSWP instruction, it is necessary to execute the NVM unlocking sequence as follows:

- 1. Write 0x55 to NVMKEY.
- 2. Write 0xAA to NVMKEY.
- 3. Execute the BOOTSWP instruction.


If the unlocking sequence is not performed, the <code>BOOTSWP</code> instruction will be executed as a forced <code>NOP</code> and a <code>GOTO</code> instruction, following the <code>BOOTSWP</code> instruction, will be executed, causing the PC to jump to that location in the current operating partition.

The SFTSWP and P2ACTIV bits in the NVMCON register are used to determine a successful swap of the Active and Inactive Partitions, as well as which partition is active. After the BOOTSWP and GOTO instructions, the SFTSWP bit should be polled to verify the partition swap has occurred and then cleared for the next panel swap event.

5.5.2 DUAL PARTITION MODES

While operating in Dual Partition mode, the dsPIC33CK256MP508 family devices have the option for both partitions to have their own defined security segments, as shown in Figure 30-4. Alternatively, the device can operate in Protected Dual Partition mode, where Partition 1 becomes permanently erase/write-protected. Protected Dual Partition mode allows for a "Factory Default" mode, which provides a fail-safe backup image to be stored in Partition 1.

dsPIC33CK256MP508 family devices can also operate in Privileged Dual Partition mode, where additional security protections are implemented to allow for protection of intellectual property when multiple parties have software within the device. In Privileged Dual Partition mode, both partitions place additional restrictions on the FBSLIM register. These prevent changes to the size of the Boot Segment and General Segment, ensuring that neither segment will be altered.



5.5.3 PROGRAM FLASH MEMORY CONTROL REGISTERS

Five SFRs are used to write and erase the Program Flash Memory: NVMCON, NVMKEY, NVMADR, NVMADRU and NVMSRCADRL/H.

The NVMCON register (Register 5-1) selects the operation to be performed (page erase, word/row program, Inactive Partition erase) and initiates the program or erase cycle.

NVMKEY (Register 5-4) is a write-only register that is used for write protection. To start a programming or erase sequence, the user application must consecutively write 0x55 and 0xAA to the NVMKEY register.

There are two NVM Address registers: NVMADRU and NVMADR. These two registers, when concatenated, form the 24-bit Effective Address (EA) of the selected word/row for programming operations, or the selected page for erase operations. The NVMADRU register is used to hold the upper eight bits of the EA, while the NVMADR register is used to hold the lower 16 bits of the EA.

For row programming operation, data to be written to Program Flash Memory is written into data memory space (RAM) at an address defined by the NVMSRCADRL/H register (location of first element in row programming data).

REGISTER 5-1: NVMCON: NONVOLATILE MEMORY (NVM) CONTROL REGISTER

R/SO-0 ⁽¹⁾	R/W-0 ⁽¹⁾	R/W-0 ⁽¹⁾	R/W-0	R/C-0	R-0	R/W-0	R/C-0
WR	WREN	WRERR	NVMSIDL ⁽²⁾	SFTSWP	P2ACTIV	RPDF	URERR
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0 ⁽¹⁾	R/W-0 ⁽¹⁾	R/W-0 ⁽¹⁾	R/W-0 ⁽¹⁾
_	_	_	_	NVMOP3 ^(3,4)	NVMOP2 ^(3,4)	NVMOP1 ^(3,4)	NVMOP0 ^(3,4)
bit 7							bit 0

Legend:	C = Clearable bit	SO = Settable Only bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15 WR: Write Control bit⁽¹⁾

- 1 = Initiates a Flash memory program or erase operation; the operation is self-timed and the bit is cleared by hardware once the operation is complete
- 0 = Program or erase operation is complete and inactive
- bit 14 WREN: Write Enable bit⁽¹⁾
 - 1 = Enables Flash program/erase operations
 - 0 = Inhibits Flash program/erase operations
- bit 13 WRERR: Write Sequence Error Flag bit (1)
 - 1 = An improper program or erase sequence attempt, or termination has occurred (bit is set automatically on any set attempt of the WR bit)
 - 0 = The program or erase operation completed normally
- bit 12 **NVMSIDL:** NVM Stop in Idle Control bit⁽²⁾
 - 1 = Flash voltage regulator goes into Standby mode during Idle mode
 - 0 = Flash voltage regulator is active during Idle mode
- bit 11 SFTSWP: Partition Soft Swap Status bit
 - 1 = Partitions have been successfully swapped using the BOOTSWP instruction (soft swap)
 - 0 = Awaiting successful partition swap using the BOOTSWP instruction or a device Reset will determine the Active Partition based on the FBTSEQ register
- bit 10 **P2ACTIV:** Partition 2 Active Status bit
 - 1 = Partition 2 Flash is mapped into the active region
 - 0 = Partition 1 Flash is mapped into the active region
- bit 9 **RPDF:** Row Programming Data Format bit
 - 1 = Row data to be stored in RAM is in compressed format
 - 0 = Row data to be stored in RAM is in uncompressed format
- bit 8 **URERR:** Row Programming Data Underrun Error bit
 - 1 = Indicates row programming operation has been terminated
 - 0 = No data underrun error is detected
- bit 7-4 **Unimplemented:** Read as '0'
- **Note 1:** These bits can only be reset on a POR.
 - 2: If this bit is set, there will be minimal power savings (IIDLE), and upon exiting Idle mode, there is a delay (TVREG) before Flash memory becomes operational.
 - **3:** All other combinations of NVMOP<3:0> are unimplemented.
 - 4: Execution of the PWRSAV instruction is ignored while any of the NVM operations are in progress.
 - 5: Two adjacent words on a 4-word boundary are programmed during execution of this operation.

REGISTER 5-1: NVMCON: NONVOLATILE MEMORY (NVM) CONTROL REGISTER (CONTINUED)

```
bit 3-0

NVMOP<3:0>: NVM Operation Select bits<sup>(1,3,4)</sup>

1111 = Reserved

1110 = User memory bulk erase operation

1101 = Reserved

1100 = Reserved

1011 = Reserved

1010 = Reserved

1010 = Reserved
```

1000 = Boot mode (FBOOT) double-word program operation

0111 = Reserved 0101 = Reserved

0100 = Inactive Partition memory erase operation

0011 = Memory page erase operation 0010 = Memory row program operation

0001 = Memory double-word operation⁽⁵⁾

0000 = Reserved

Note 1: These bits can only be reset on a POR.

- 2: If this bit is set, there will be minimal power savings (IIDLE), and upon exiting Idle mode, there is a delay (TVREG) before Flash memory becomes operational.
- **3:** All other combinations of NVMOP<3:0> are unimplemented.
- 4: Execution of the PWRSAV instruction is ignored while any of the NVM operations are in progress.
- 5: Two adjacent words on a 4-word boundary are programmed during execution of this operation.

REGISTER 5-2: NVMADR: NONVOLATILE MEMORY LOWER ADDRESS REGISTER

R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x			
	NVMADR<15:8>									
bit 15							bit 8			

R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x			
	NVMADR<7:0>									
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **NVMADR<15:0>:** Nonvolatile Memory Lower Write Address bits

Selects the lower 16 bits of the location to program or erase in Program Flash Memory. This register may be read or written to by the user application.

REGISTER 5-3: NVMADRU: NONVOLATILE MEMORY UPPER ADDRESS REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x		
NVMADRU<23:16>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 NVMADRU<23:16>: Nonvolatile Memory Upper Write Address bits

Selects the upper eight bits of the location to program or erase in Program Flash Memory. This register

may be read or written to by the user application.

REGISTER 5-4: NVMKEY: NONVOLATILE MEMORY KEY REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

W-0	W-0	W-0	W-0	W-0	W-0	W-0	W-0		
NVMKEY<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 **NVMKEY<7:0>:** NVM Key Register bits (write-only)

NVMSRCADRL: NVM SOURCE DATA ADDRESS REGISTER LOW REGISTER 5-5:

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			NVMSRCA	DR<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
NVMSRCADR<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

NVMSRCADR<15:0>: NVM Source Data Address bits bit 15-0

> The RAM address of the data to be programmed into Flash when the NVMOP<3:0> bits are set to row programming.

REGISTER 5-6: NVMSRCADRH: NVM SOURCE DATA ADDRESS REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
NVMSRCADR<23:16>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 NVMSRCADR<23:16>: NVM Source Data Address bits

The RAM address of the data to be programmed into Flash when the NVMOP<3:0> bits are set to row

programming.

5.5.4 ECC CONTROL REGISTERS

REGISTER 5-7: ECCCONL: ECC FAULT INJECTION CONFIGURATION REGISTER LOW

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	FLTINJ
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-1 Unimplemented: Read as '0'

bit 0 FLTINJ: Fault Injection Sequence Enable bit

1 = Enabled
0 = Disabled

REGISTER 5-8: ECCCONH: ECC FAULT INJECTION CONFIGURATION REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
FLT2PTR<7:0>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
FLT1PTR<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 FLT2PTR<7:0>: ECC Fault Injection Bit Pointer 2 bits

11111111-00111000 = No Fault injection occurs

00110111 = Fault injection (bit inversion) occurs on bit 55 of ECC bit order

.

•

00000001 = Fault injection (bit inversion) occurs on bit 1 of ECC bit order 00000000 = Fault injection (bit inversion) occurs on bit 0 of ECC bit order

bit 0 FLT1PTR<7:0>: ECC Fault Injection Bit Pointer 1 bits

11111111-00111000 = No Fault injection occurs

00110111 = Fault injection occurs on bit 55 of ECC bit order

•

•

00000001 = Fault injection occurs on bit 1 of ECC bit order 00000000 = Fault injection occurs on bit 0 of ECC bit order

REGISTER 5-9: ECCADDRL: ECC FAULT INJECT ADDRESS COMPARE REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
ECCADDR<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			ECCADI	DR<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 ECCADDR<15:0>: ECC Fault Injection NVM Address Match Compare bits

REGISTER 5-10: ECCADDRH: ECC FAULT INJECT ADDRESS COMPARE REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
ECCADDR<23:16>										
bit 7										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 ECCADDR<23:16>: ECC Fault Injection NVM Address Match Compare bits

REGISTER 5-11: ECCSTATL: ECC SYSTEM STATUS DISPLAY REGISTER LOW

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0			
SECOUT<7:0>										
bit 15										

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0			
SECIN<7:0>										
bit 7						bit 0				

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **SECOUT<7:0>:** Calculated Single Error Correction Parity Value bits

bit 7-0 SECIN<7:0>: Read Single Error Correction Parity Value bits

SECIN<7:0> bits are the actual parity value of a Flash read operation.

REGISTER 5-12: ECCSTATH: ECC SYSTEM STATUS DISPLAY REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	R-0	R-0
_	_	_	_	_	_	DEDOUT	DEDIN
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0			
SECSYND<7:0>										
bit 7										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9 **DEDOUT:** Calculated Dual Bit Error Detection Parity bit

bit 8 **DEDIN:** Read Dual Bit Error Detection Parity bit

DEDIN is the actual parity value of a Flash read operation.

bit 7-0 **SECSYND<7:0>:** Calculated ECC Syndrome Value bits

Indicates the bit location that contains the error.

6.0 RESETS

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Reset" (www.microchip.com/DS70602) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices.

The Reset module combines all Reset sources and controls the device Master Reset Signal, SYSRST. The following is a list of device Reset sources:

POR: Power-on Reset

· BOR: Brown-out Reset

MCLR: Master Clear Pin Reset

• SWR: RESET Instruction

· WDTO: Watchdog Timer Time-out Reset

· CM: Configuration Mismatch Reset

· TRAPR: Trap Conflict Reset

· IOPUWR: Illegal Condition Device Reset

- Illegal Opcode Reset

- Uninitialized W Register Reset

Security Reset

A simplified block diagram of the Reset module is shown in Figure 6-1.

Any active source of Reset will make the SYSRST signal active. On system Reset, some of the registers associated with the CPU and peripherals are forced to a known Reset state, and some are unaffected.

Note: Refer to the specific peripheral section or Section 4.0 "Memory Organization" of this data sheet for register Reset states.

All types of device Reset set a corresponding status bit in the RCON register to indicate the type of Reset (see Register 6-1).


A POR clears all the bits, except for the BOR and POR bits (RCON<1:0>) that are set. The user application can set or clear any bit, at any time, during code execution. The RCON bits only serve as status bits. Setting a particular Reset status bit in software does not cause a device Reset to occur.

The RCON register also has other bits associated with the Watchdog Timer and device power-saving states. The function of these bits is discussed in other sections of this data sheet.

Note: The status bits in the RCON register should be cleared after they are read so that the next RCON register value after a device Reset is meaningful.

For all Resets, the default clock source is determined by the FNOSC<2:0> bits in the FOSCSEL Configuration register. The value of the FNOSCx bits is loaded into the NOSC<2:0> (OSCCON<10:8>) bits on Reset, which in turn, initializes the system clock.

FIGURE 6-1: RESET SYSTEM BLOCK DIAGRAM



6.1 Reset Resources

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

6.1.1 KEY RESOURCES

- "Reset" (DS70602) in the "dsPIC33/PIC24 Family Reference Manual"
- · Code Samples
- · Application Notes
- · Software Libraries
- Webinars
- All Related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

REGISTER 6-1: RCON: RESET CONTROL REGISTER⁽¹⁾

R/W-0	R/W-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
TRAPR	IOPUWR	_	_	_	_	CM	VREGS
bit 15							bit 8

R/W-1	R/W-0	r-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-1
EXTR	SWR	_	WDTO	SLEEP	IDLE	BOR	POR
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 TRAPR: Trap Reset Flag bit

1 = A Trap Conflict Reset has occurred0 = A Trap Conflict Reset has not occurred

bit 14 IOPUWR: Illegal Opcode or Uninitialized W Register Access Reset Flag bit

1 = An illegal opcode detection, an illegal address mode or Uninitialized W register used as an

Address Pointer caused a Reset

0 = An illegal opcode or Uninitialized W Register Reset has not occurred

bit 13-10 Unimplemented: Read as '0'

bit 9 CM: Configuration Mismatch Flag bit

1 = A Configuration Mismatch Reset has occurred.0 = A Configuration Mismatch Reset has not occurred

bit 8 **VREGS:** Voltage Regulator Standby During Sleep bit

1 = Voltage regulator is active during Sleep

0 = Voltage regulator goes into Standby mode during Sleep

bit 7 EXTR: External Reset (MCLR) Pin bit

1 = A Master Clear (pin) Reset has occurred 0 = A Master Clear (pin) Reset has not occurred

bit 6 SWR: Software RESET (Instruction) Flag bit

1 = A RESET instruction has been executed 0 = A RESET instruction has not been executed

bit 5 Reserved: Read as '0'

bit 4 WDTO: Watchdog Timer Time-out Flag bit

1 = WDT time-out has occurred0 = WDT time-out has not occurred

bit 3 SLEEP: Wake-up from Sleep Flag bit

1 = Device has been in Sleep mode0 = Device has not been in Sleep mode

bit 2 IDLE: Wake-up from Idle Flag bit

1 = Device has been in Idle mode0 = Device has not been in Idle mode

bit 1 BOR: Brown-out Reset Flag bit

1 = A Brown-out Reset has occurred

0 = A Brown-out Reset has not occurred

Note 1: All of the Reset status bits can be set or cleared in software. Setting one of these bits in software does not cause a device Reset.

REGISTER 6-1: RCON: RESET CONTROL REGISTER⁽¹⁾ (CONTINUED)

bit 0 **POR:** Power-on Reset Flag bit

1 = A Power-on Reset has occurred 0 = A Power-on Reset has not occurred

Note 1: All of the Reset status bits can be set or cleared in software. Setting one of these bits in software does not cause a device Reset.

7.0 INTERRUPT CONTROLLER

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Interrupts" (www.microchip.com/DS70000600) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices.

The dsPIC33CK256MP508 family interrupt controller reduces the numerous peripheral interrupt request signals to a single interrupt request signal to the dsPIC33CK256MP508 family CPU.

The interrupt controller has the following features:

- · Six Processor Exceptions and Software Traps
- · Seven User-Selectable Priority Levels
- Interrupt Vector Table (IVT) with a Unique Vector for each Interrupt or Exception Source
- · Fixed Priority within a Specified User Priority Level
- · Fixed Interrupt Entry and Return Latencies
- Alternate Interrupt Vector Table (AIVT) for Debug Support

7.1 Interrupt Vector Table

The dsPIC33CK256MP508 family Interrupt Vector Table (IVT), shown in Figure 7-1, resides in program memory, starting at location, 000004h. The IVT contains six non-maskable trap vectors and up to 246 sources of interrupts. In general, each interrupt source has its own vector. Each interrupt vector contains a 24-bit wide address. The value programmed into each interrupt vector location is the starting address of the associated Interrupt Service Routine (ISR).

Interrupt vectors are prioritized in terms of their natural priority. This priority is linked to their position in the vector table. Lower addresses generally have a higher natural priority. For example, the interrupt associated with Vector 0 takes priority over interrupts at any other vector address.

7.1.1 ALTERNATE INTERRUPT VECTOR TABLE

The Alternate Interrupt Vector Table (AIVT), shown in Figure 7-2, is available only when the Boot Segment (BS) is defined and the AIVT has been enabled. To enable the Alternate Interrupt Vector Table, the Configuration bit, AIVTDIS in the FSEC register, must be programmed and the AIVTEN bit must be set (INTCON2<8> = 1). When the AIVT is enabled, all interrupt and exception processes use the alternate vectors instead of the default vectors. The AIVT begins at the start of the last page of the Boot Segment, defined by BSLIM<12:0>. The second half of the page is no longer usable space. The Boot Segment must be at least two pages to enable the AIVT.


Note: Although the Boot Segment must be enabled in order to enable the AIVT, application code does not need to be present inside of the Boot Segment. The AIVT (and IVT) will inherit the Boot Segment code protection.

The AIVT supports debugging by providing a means to switch between an application and a support environment without requiring the interrupt vectors to be reprogrammed. This feature also enables switching between applications for evaluation of different software algorithms at run time.

7.2 Reset Sequence

A device Reset is not a true exception because the interrupt controller is not involved in the Reset process. The dsPIC33CK256MP508 family devices clear their registers in response to a Reset, which forces the PC to zero. The device then begins program execution at location, 0x000000. A GOTO instruction at the Reset address can redirect program execution to the appropriate start-up routine.

Note: Any unimplemented or unused vector locations in the IVT should be programmed with the address of a default interrupt handler routine that contains a RESET instruction.






TABLE 7-1: TRAP VECTOR DETAILS

Tron Description	MPLAB [®] XC16	\/a-4#	IVT		Trap Bit Location	า	Dui a vita a
Trap Description	Trap ISR Name	Vector #	Address	Interrupt Flag	Type	Enable	Priority
Oscillator Failure	_OscillatorFail	0	0x000004	INTCON1<1>	_	_	15
Address Error	_AddressError	1	0x000006	INTCON1<3>	_	_	14
ECC Double-Bit Error	_HardTrapError	2	0x000008	INTCON4<1>	_	_	13
Software Generated Trap	_HardTrapError	2	0x000008	INTCON4<0>	_	INTCON2<13>	13
Stack Error	_StackError	3	0x00000A	INTCON1<2>	_	_	12
Overflow Accumulator A	_MathError	4	0x00000C	INTCON1<4>	INTCON1<14>	INTCON1<10>	11
Overflow Accumulator B	_MathError	4	0x00000C	INTCON1<4>	INTCON1<13>	INTCON1<9>	11
Catastrophic Overflow Accumulator A	_MathError	4	0x00000C	INTCON1<4>	INTCON1<12>	INTCON1<8>	11
Catastrophic Overflow Accumulator B	_MathError	4	0x00000C	INTCON1<4>	INTCON1<11>	INTCON1<8>	11
Shift Accumulator Error	_MathError	4	0x00000C	INTCON1<4>	INTCON1<7>	INTCON1<8>	11
Divide-by-Zero Error	_MathError	4	0x00000C	INTCON1<4>	INTCON1<6>	INTCON1<8>	11
Reserved	Reserved	5	0x00000E	_	_	_	_
CAN Address Error	_SoftTrapError	6	0x000010	INTCON3<9>	_	_	9
NVM Address Error	_SoftTrapError	6	0x000010	INTCON3<8>			9
DO Stack Overflow	_SoftTrapError	6	0x000010	INTCON3<4>	_	_	9
APLL Loss of Lock	_SoftTrapError	6	0x000010	INTCON3<0>	_	_	9
Reserved	Reserved	7	0x000012	_	_	_	_

TABLE 7-2: INTERRUPT VECTOR DETAILS

luta mund O a mara	MPLAB® XC16	Vector	IRQ	DOT Address	Int	errupt Bit Lo	cation
Interrupt Source	ISR Name	#	#	IVT Address	Flag	Enable	Priority
External Interrupt 0	_INT0Interrupt	8	0	0x000014	IFS0<0>	IEC0<0>	IPC0<2:0>
Timer1	_T1Interrupt	9	1	0x000016	IFS0<1>	IEC0<1>	IPC0<6:4>
Change Notice Interrupt A	_CNAInterrupt	10	2	0x000018	IFS0<2>	IEC0<2>	IPC0<10:8>
Change Notice Interrupt B	_CNBInterrupt	11	3	0x00001A	IFS0<3>	IEC0<3>	IPC0<14:12>
DMA Channel 0	_DMA0Interrupt	12	4	0x00001C	IFS0<4>	IEC0<4>	IPC1<2:0>
Reserved	Reserved	13	5	0x00001E	_	_	_
Input Capture/Output Compare 1	_CCP1Interrupt	14	6	0x000020	IFS0<6>	IEC0<6>	IPC1<10:8>
CCP1 Timer	_CCT1Interrupt	15	7	0x000022	IFS0<7>	IEC0<7>	IPC1<14:12>
DMA Channel 1	_DMA1Interrupt	16	8	0x000024	IFS0<8>	IEC0<8>	IPC2<2:0>
SPI1 Receiver	_SPI1RXInterrupt	17	9	0x000026	IFS0<9>	IEC0<9>	IPC2<6:4>
SPI1 Transmitter	_SPI1TXInterrupt	18	10	0x000028	IFS0<10>	IEC0<10>	IPC2<10:8>
UART1 Receiver	_U1RXInterrupt	19	11	0x00002A	IFS0<11>	IEC0<11>	IPC2<14:12>
UART1 Transmitter	_U1TXInterrupt	20	12	0x00002C	IFS0<12>	IEC0<12>	IPC3<2:0>
ECC Single Bit Error	_ECCSBEInterrupt	21	13	0x00002E	IFS0<13>	IEC0<13>	IPC3<6:4>
NVM Write Complete	_NVMInterrupt	22	14	0x000030	IFS0<14>	IEC0<14>	IPC3<10:8>
External Interrupt 1	_INT1Interrupt	23	15	0x000032	IFS0<15>	IEC0<15>	IPC3<14:12>
I2C1 Slave Event	_SI2C1Interrupt	24	16	0x000034	IFS1<0>	IEC1<0>	IPC4<2:0>
I2C1 Master Event	_MI2C1Interrupt	25	17	0x000036	IFS1<1>	IEC1<1>	IPC4<6:4>
DMA Channel 2	_DMA2Interrupt	26	18	0x000038	IFS1<2>	IEC1<2>	IPC4<10:8>
Change Notice Interrupt C(2)	_CNCInterrupt	27	19	0x00003A	IFS1<3>	IEC1<3>	IPC4<14:12>
External Interrupt 2	_INT2Interrupt	28	20	0x00003C	IFS1<4>	IEC1<4>	IPC5<2:0>
DMA Channel 3	_DMA3Interrupt	29	21	0x00003E	IFS1<5>	IEC1<5>	IPC5<6:4>
Reserved	Reserved	30	22	0x000040	_	_	_
Input Capture/Output Compare 2	_CCP2Interrupt	31	23	0x000042	IFS1<7>	IEC1<7>	IPC5<14:12>
CCP2 Timer	_CCT2Interrupt	32	24	0x000044	IFS1<8>	IEC1<8>	IPC6<2:0>
CAN1 Combined Error ⁽³⁾	_CAN1Interrupt	33	25	0x000046	IFS1<9>	IEC1<9>	IPC6<6:4>
External Interrupt 3	_INT3Interrupt	34	26	0x000048	IFS1<10>	IEC1<10>	IPC6<10:8>
UART2 Receiver	_U2RXInterrupt	35	27	0x00004A	IFS1<11>	IEC1<11>	IPC6<14:12>
UART2 Transmitter	_U2TXInterrupt	36	28	0x00004C	IFS1<12>	IEC1<12>	IPC7<2:0>
SPI2 Receiver	_SPI2RXInterrupt	37	29	0x00004E	IFS1<13>	IEC1<13>	IPC7<6:4>
SPI2 Transmitter	_SPI2TXInterrupt	38	30	0x000050	IFS1<14>	IEC1<14>	IPC7<10:8>
CAN1 RX Data Ready ⁽³⁾	_C1RXInterrupt	39	31	0x000052	IFS1<15>	IEC1<15>	IPC7<14:12>
Reserved	Reserved	40-42	32-34	0x000054-0x000058	_	_	_
Input Capture/Output Compare 3	_CCP3Interrupt	43	35	0x00005A	IFS2<3>	IEC2<3>	IPC8<14:12>
CCP3 Timer	_CCT3Interrupt	44	36	0x00005C	IFS2<4>	IEC2<4>	IPC9<2:0>
I2C2 Slave Event	_SI2C2Interrupt	45	37	0x00005E	IFS2<5>	IEC2<5>	IPC9<6:4>
I2C2 Master Event	_MI2C2Interrupt	46	38	0x000060	IFS2<6>	IEC2<6>	IPC9<10:8>
Reserved	Reserved	47	39	0x000062	_	_	_
Input Capture/Output Compare 4	_CCP4Interrupt	48	40	0x000064	IFS2<8>	IEC2<8>	IPC10<2:0>
CCP4 Timer	_CCT4Interrupt	49	41	0x000066	IFS2<9>	IEC2<9>	IPC10<6:4>
Reserved	Reserved	50	42	0x000068	_	_	_

Note 1: Availability dependent on number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

^{2:} Availability dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

^{3:} Availability dependent on supported peripherals, refer to Table 1 and Table 2.

TABLE 7-2: INTERRUPT VECTOR DETAILS (CONTINUED)

	MPLAB® XC16	Vector	IRQ		Int	terrupt Bit Lo	cation
Interrupt Source	ISR Name	#	#	IVT Address	Flag	Enable	Priority
Input Capture/Output Compare 5	_CCP5Interrupt	51	43	0x00006A	IFS2<11>	IEC2<11>	IPC10<14:12>
CCP5 Timer	_CCT5Interrupt	52	44	0x00006C	IFS2<12>	IEC2<12>	IPC11<2:0>
Deadman Timer	_DMTInterrupt	53	45	0x00006E	IFS2<13>	IEC2<13>	IPC11<6:4>
Input Capture/Output Compare 6	_CCP6Interrupt	54	46	0x000070	IFS2<14>	IEC2<14>	IPC11<10:8>
CCP6 Timer	_CCT6Interrupt	55	47	0x000072	IFS2<15>	IEC2<15>	IPC11<14:12>
QEI Position Counter Compare	_QEI1Interrupt	56	48	0x000074	IFS3<0>	IEC3<0>	IPC12<2:0>
UART1 Error	_U1EInterrupt	57	49	0x000076	IFS3<1>	IEC3<1>	IPC12<6:4>
UART2 Error	_U2EInterrupt	58	50	0x000078	IFS3<2>	IEC3<2>	IPC12<10:8>
CRC Generator	_CRCInterrupt	59	51	0x00007A	IFS3<3>	IEC3<3>	IPC12<14:12>
CAN1 TX Data Request ⁽³⁾	_C1TXInterrupt	60	52	0x00007C	IFS3<4>	IEC3<4>	IPC13<2:0>
Reserved	Reserved	61	53	0x00007E	_	_	_
QEI Position Counter Compare	_QEI2Interrupt	62	54	0x000080	IFS3<6>	IEC3<6>	IPC13<10:8>
Reserved	Reserved	63	55	0x000082	_	_	_
UART3 Error	_U3EInterrupt	64	56	0x000084	IFS3<8>	IEC3<8>	IPC14<2:0>
UART3 Receiver	_U3RXInterrupt	65	57	0x000086	IFS3<9>	IEC3<9>	IPC14<6:4>
UART3 Transmitter	_U3TXInterrupt	66	58	0x000088	IFS3<10>	IEC3<10>	IPC14<10:8>
SPI3 Receiver	_SPI3RXInterrupt	67	59	A80000x0	IFS3<11>	IEC3<11>	IPC14<14:12>
SPI3 Transmitter	_SPI3TXInterrupt	68	60	0x00008C	IFS3<12>	IEC3<12>	IPC15<2:0>
In-Circuit Debugger	_ICDInterrupt	69	61	0x00008E	IFS3<13>	IEC3<13>	IPC15<6:4>
JTAG Programming	_JTAGInterrupt	70	62	0x000090	IFS3<14>	IEC3<14>	IPC15<10:8>
PTG Step	_PTGSTEPInterrupt	71	63	0x000092	IFS3<15>	IEC3<15>	IPC15<14:12>
I2C1 Bus Collision	_I2C1BCInterrupt	72	64	0x000094	IFS4<0>	IEC4<0>	IPC16<2:0>
I2C2 Bus Collision	_I2C2BCInterrupt	73	65	0x000096	IFS4<1>	IEC4<1>	IPC16<6:4>
Reserved	Reserved	74	66	0x000098	_	_	_
PWM Generator 1	_PWM1Interrupt	75	67	0x00009A	IFS4<3>	IEC4<3>	IPC16<14:12>
PWM Generator 2	_PWM2Interrupt	76	68	0x00009C	IFS4<4>	IEC4<4>	IPC17<2:0>
PWM Generator 3	_PWM3Interrupt	77	69	0x00009E	IFS4<5>	IEC4<5>	IPC17<6:4>
PWM Generator 4	_PWM4Interrupt	78	70	0x0000A0	IFS4<6>	IEC4<6>	IPC17<10:8>
PWM Generator 5	_PWM5Interrupt	79	71	0x0000A2	IFS4<7>	IEC4<7>	IPC17<14:12>
PWM Generator 6	_PWM6Interrupt	80	72	0x0000A4	IFS4<8>	IEC4<8>	IPC18<2:0>
PWM Generator 7	_PWM7Interrupt	81	73	0x0000A6	IFS4<9>	IEC4<9>	IPC18<6:4>
PWM Generator 8	_PWM8Interrupt	82	74	0x0000A8	IFS4<10>	IEC4<10>	IPC18<10:8>
Change Notice D ⁽²⁾	_CNDInterrupt	83	75	0x0000AA	IFS4<11>	IEC4<11>	IPC18<14:12>
Change Notice E ⁽²⁾	_CNEInterrupt	84	76	0x0000AC	IFS4<12>	IEC4<12>	IPC19<2:0>
Comparator 1	_CMP1Interrupt	85	77	0x0000AE	IFS4<13>	IEC4<13>	IPC19<6:4>
Comparator 2	_CMP2Interrupt	86	78	0x0000B0	IFS4<14>	IEC4<14>	IPC19<10:8>
Comparator 3	_CMP3Interrupt	87	79	0x0000B2	IFS4<15>	IEC4<15>	IPC19<14:12>
Reserved	Reserved	88	80	0x0000B4	_	_	_
PTG Watchdog Timer Time-out	_PTGWDTInterrupt	89	81	0x0000B6	IFS5<1>	IEC5<1>	IPC20<6:4>
PTG Trigger 0	_PTG0Interrupt	90	82	0x0000B8	IFS5<2>	IEC5<2>	IPC20<10:8>
PTG Trigger 1	_PTG1Interrupt	91	83	0x0000BA	IFS5<3>	IEC5<3>	IPC20<14:12>
PTG Trigger 2	_PTG2Interrupt	92	84	0x0000BC	IFS5<4>	IEC5<4>	IPC21<2:0>
PTG Trigger 3	_PTG3Interrupt	93	85	0x0000BE	IFS5<5>	IEC5<6>	IPC21<6:4>

Note 1: Availability dependent on number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

^{2:} Availability dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

^{3:} Availability dependent on supported peripherals, refer to Table 1 and Table 2.

TABLE 7-2: INTERRUPT VECTOR DETAILS (CONTINUED)

	MPLAB® XC16	Vector	IRQ		Interrupt Bit Location		
Interrupt Source	ISR Name	#	#	IVT Address	Flag	Enable	Priority
SENT1 TX/RX	_SENT1Interrupt	94	86	0x0000C0	IFS5<6>	IEC5<6>	IPC21<10:8>
SENT1 Error	_SENT1EInterrupt	95	87	0x0000C2	IFS5<7>	IEC5<7>	IPC21<14:12>
SENT2 TX/RX	_SENT2Interrupt	96	88	0x0000C4	IFS5<8>	IEC5<8>	IPC22<2:0>
SENT2 Error	_SENT2EInterrupt	97	89	0x0000C6	IFS5<9>	IEC5<9>	IPC22<6:4>
ADC Global Interrupt	_ADCInterrupt	98	90	0x0000C8	IFS5<10>	IEC5<10>	IPC22<10:8>
ADC AN0 Interrupt	_ADCAN0Interrupt	99	91	0x0000CA	IFS5<11>	IEC5<11>	IPC22<14:12>
ADC AN1 Interrupt	_ADCAN1Interrupt	100	92	0x0000CC	IFS5<12>	IEC5<12>	IPC23<2:0>
ADC AN2 Interrupt	_ADCAN2Interrupt	101	93	0x0000CE	IFS5<13>	IEC5<13>	IPC23<6:4>
ADC AN3 Interrupt	_ADCAN3Interrupt	102	94	0x0000D0	IFS5<14>	IEC5<14>	IPC23<10:8>
ADC AN4 Interrupt	_ADCAN4Interrupt	103	95	0x0000D2	IFS5<15>	IEC5<15>	IPC23<14:12>
ADC AN5 Interrupt	_ADCAN5Interrupt	104	96	0x0000D4	IFS6<0>	IEC6<0>	IPC24<2:0>
ADC AN6 Interrupt	_ADCAN6Interrupt	105	97	0x0000D6	IFS6<1>	IEC6<1>	IPC24<6:4>
ADC AN7 Interrupt	_ADCAN7Interrupt	106	98	0x0000D8	IFS6<2>	IEC6<2>	IPC24<10:8>
ADC AN8 Interrupt	_ADCAN8Interrupt	107	99	0x0000DA	IFS6<3>	IEC6<3>	IPC24<14:12>
ADC AN9 Interrupt	_ADCAN9Interrupt	108	100	0x0000DC	IFS6<4>	IEC6<4>	IPC25<2:0>
ADC AN10 Interrupt	_ADCAN10Interrupt	109	101	0x0000DE	IFS6<5>	IEC6<5>	IPC25<6:4>
ADC AN11 Interrupt	_ADCAN11Interrupt	110	102	0x0000E0	IFS6<6>	IEC6<6>	IPC25<10:8>
ADC AN12 Interrupt ⁽¹⁾	_ADCAN12Interrupt	111	103	0x0000E2	IFS6<7>	IEC6<7>	IPC25<14:12>
ADC AN13 Interrupt ⁽¹⁾	_ADCAN13Interrupt	112	104	0x0000E4	IFS6<8>	IEC6<8>	IPC26<2:0>
ADC AN14 Interrupt ⁽¹⁾	_ADCAN14Interrupt	113	105	0x0000E6	IFS6<9>	IEC6<9>	IPC26<6:4>
ADC AN15 Interrupt ⁽¹⁾	_ADCAN15Interrupt	114	106	0x0000E8	IFS6<10>	IEC6<10>	IPC26<10:8>
ADC AN16 Interrupt ⁽¹⁾	_ADCAN16Interrupt	115	107	0x0000EA	IFS6<11>	IEC6<11>	IPC26<14:12>
ADC AN17 Interrupt ⁽¹⁾	_ADCAN17Interrupt	116	108	0x0000EC	IFS6<12>	IEC6<12>	IPC27<2:0>
ADC AN18 Interrupt ⁽¹⁾	_ADCAN18Interrupt	117	109	0x0000EE	IFS6<13>	IEC6<13>	IPC27<6:4>
ADC AN19 Interrupt ⁽¹⁾	_ADCAN19Interrupt	118	110	0x0000F0	IFS6<14>	IEC6<14>	IPC27<10:8>
ADC AN20 Interrupt ⁽¹⁾	_ADCAN20Interrupt	119	111	0x0000F2	IFS6<15>	IEC6<15>	IPC27<14:12>
ADC AN21 Interrupt ⁽¹⁾	_ADCAN21Interrupt	120	112	0x0000F4	IFS7<0>	IEC7<0>	IPC28<2:0>
ADC AN22 Interrupt ⁽¹⁾	_ADCAN22Interrupt	121	113	0x0000F6	IFS7<1>	IEC7<1>	IPC28<6:4>
ADC AN23 Interrupt ⁽¹⁾	_ADCAN23Interrupt	122	114	0x0000F8	IFS7<2>	IEC7<2>	IPC28<10:8>
ADC Fault	_ADFLTInterrupt	123	115	0x0000FA	IFS7<3>	IEC7<3>	IPC28<14:12>
ADC Digital Comparator 0	_ADCMP0Interrupt	124	116	0x0000FC	IFS7<4>	IEC7<4>	IPC29<2:0>
ADC Digital Comparator 1	_ADCMP1Interrupt	125	117	0x0000FE	IFS7<5>	IEC7<5>	IPC29<6:4>
ADC Digital Comparator 2	_ADCMP2Interrupt	126	118	0x000100	IFS7<6>	IEC7<6>	IPC29<10:8>
ADC Digital Comparator 3	_ADCMP3Interrupt	127	119	0x000102	IFS7<7>	IEC7<7>	IPC29<14:12>
ADC Oversample Filter 0	_ADFLTR0Interrupt	128	120	0x000104	IFS7<8>	IEC7<8>	IPC30<2:0>
ADC Oversample Filter 1	_ADFLTR1Interrupt	129	121	0x000106	IFS7<9>	IEC7<9>	IPC30<6:4>
ADC Oversample Filter 2	_ADFLTR2Interrupt	130	122	0x000108	IFS7<10>	IEC7<10>	IPC30<10:8>
ADC Oversample Filter 3	_ADFLTR3Interrupt	131	123	0x00010A	IFS7<11>	IEC7<11>	IPC30<14:12>
CLC1 Positive Edge	_CLC1PInterrupt	132	124	0x00010C	IFS7<12>	IEC7<12>	IPC31<2:0>
CLC2 Positive Edge	_CLC2PInterrupt	133	125	0x00010E	IFS7<13>	IEC7<13>	IPC31<6:4>
SPI1 Error	_SPI1GInterrupt	134	126	0x000110	IFS7<14>	IEC7<14>	IPC31<10:8>
SPI2 Error	_SPI2GInterrupt	135	127	0x000112	IFS7<15>	IEC7<15>	IPC31<14:12>
SPI3 Error	_SPI3GInterrupt	136	128	0x000114	IFS8<0>	IEC8<0>	IPC32<2:0>

Note 1: Availability dependent on number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

^{2:} Availability dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

^{3:} Availability dependent on supported peripherals, refer to Table 1 and Table 2.

TABLE 7-2: INTERRUPT VECTOR DETAILS (CONTINUED)

_	MPLAB [®] XC16	Vector	IRQ		Int	errupt Bit Lo	cation
Interrupt Source	ISR Name	#	#	IVT Address	Flag	Enable	Priority
Reserved	Reserved	137-149	129-141	0x000116-0x00012E	_	_	_
I2C3 Slave Event	_SI2C3Interrupt	150	142	0x000130	IFS8<14>	IEC8<14>	IPC35<10:8>
I2C3 Master Event	_MI2C3Interrupt	151	143	0x000132	IFS8<15>	IEC8<15>	IPC35<14:12>
I2C3 Bus Collision	_I2C3BCInterrupt	152	144	0x000134	IFS9<0>	IEC9<0>	IPC36<2:0>
Reserved	Reserved	153-156	145-148	0x000136-0x00013C	_	_	_
Input Capture/Output Compare 7	_CCP7Interrupt	157	149	0x00013E	IFS9<5>	IEC9<5>	IPC37<6:4>
CCP7 Timer	_CCT7Interrupt	158	150	0x000140	IFS9<6>	IEC9<6>	IPC37<10:8>
Reserved	Reserved	159	151	0x000142		_	_
Input Capture/Output Compare 8	_CCP8Interrupt	160	152	0x000144	IFS9<8>	IEC9<8>	IPC38<2:0>
CCP8 Timer	_CCT8Interrupt	161	153	0x000146	IFS9<9>	IEC9<9>	IPC38<6:4>
Reserved	Reserved	162-175	154-167	0x000148-0x000162	-	_	_
ADC FIFO Ready	_ADFIFOInterrupt	176	168	0x000164	IFS10<8>	IEC10<8>	IPC42<2:0>
PWM Event A	_PEVTAInterrupt	177	169	0x000166	IFS10<9>	IEC10<9>	IPC42<6:4>
PWM Event B	_PEVTBInterrupt	178	170	0x000168	IFS10<10>	IEC10<10>	IPC42<10:8>
PWM Event C	_PEVTCInterrupt	179	171	0x00016A	IFS10<11>	IEC10<11>	IPC42<14:12>
PWM Event D	_PEVTDInterrupt	180	172	0x00016C	IFS10<12>	IEC10<12>	IPC43<2:0>
PWM Event E	_PEVTEInterrupt	181	173	0x00016E	IFS10<13>	IEC10<13>	IPC43<6:4>
PWM Event F	_PEVTFInterrupt	182	174	0x000170	IFS10<14>	IEC10<14>	IPC43<10:8>
CLC3 Positive Edge	_CLC3PInterrupt	183	175	0x000172	IFS10<15>	IEC10<15>	IPC43<14:12>
CLC4 Positive Edge	_CLC4PInterrupt	184	176	0x000174	IFS11<0>	IEC11<0>	IPC44<2:0>
CLC1 Negative Edge	_CLC1NInterrupt	185	177	0x000176	IFS11<1>	IEC11<1>	IPC44<6:4>
CLC2 Negative Edge	_CLC2NInterrupt	186	178	0x000178	IFS11<2>	IEC11<2>	IPC44<10:8>
CLC3 Negative Edge	_CLC3NInterrupt	187	179	0x00017A	IFS11<3>	IEC11<3>	IPC44<14:>12>
CLC4 Negative Edge	_CLC4NInterrupt	188	180	0x00017C	IFS11<4>	IEC11<4>	IPC45<2:0>
Input Capture/Output Compare 9	_CCP9Interrupt	189	181	0x00017E	IFS11<5>	IEC11<5>	IPC45<6:4>
CCP9 Timer	_CCT9Interrupt	190	182	0x000180	IFS11<6>	IEC11<6>	IPC45<10:8>
Reserved	Reserved	191-196	183-188	0x00182-0x0018C	_	_	_
UART1 Event	_U1EVTInterrupt	197	189	0x00018E	IFS11<13>	IF2C11<13>	IPC47<6:4>
UART2 Event	_U2EVTInterrupt	198	190	0x000190	IFS11<14>	IF2C11<14>	IPC47<12:8>
UART3 Event	_U3EVTInterrupt	199	191	0x000192	IFS11<15>	IF2C11<15>	IPC47<14:12>
AN24 Done	_AD1AN24Interrupt	200	192	0x000194	IFS12<0>	IEC12<0>	IPC48<2:0>
AN25 Done	_AD1AN25Interrupt	201	193	0x000196	IFS12<1>	IEC12<1>	IPC48<6:4>
PMP Event ⁽³⁾	_PMPInterrupt	202	194	0x000198	IFS12<2>	IEC12<2>	IPC48<10:8>
PMP Error Event ⁽³⁾	_PMPEInterrupt	203	195	0x00019A	IFS12<3>	IEC12<3>	IPC48<14:12>

Note 1: Availability dependent on number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

^{2:} Availability dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

^{3:} Availability dependent on supported peripherals, refer to Table 1 and Table 2.

ERS
REGIST
FLAG F
RUPT F
INTERI
.: -3:
ABLE 7
\vdash

Register	Address	Bit 15	Bit14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
IFS0	800h	INT1IF	NVMIF	ECCSBEIF	U1TXIF	U1RXIF	SPI1TXIF	SPI1RXIF	DMA11F	CCT1IF	CCP1IF	I	DMA0IF	CNBIF	CNAIF	T1IF	INTOIF
IFS1	802h	C1RXIF	SPI2TXIF	SPI2RXIF	U2TXIF	U2RXIF	INT3IF	C1IF	CCT2IF	CCP2IF	Ι	DMA3IF	INT2IF	CNCIF	DMA2IF	MI2C1IF	SI2C1IF
IFS2	804h	CCT6IF	CCP6IF	DMTIF	CCT5IF	CCP5IF	I	CCT4IF	CCP4IF	I	MI2C2IF	SI2C2IF	CCT3IF	CCP3IF	Ι	I	I
IFS3	806h	PTGSTEPIF	JTAGIF	ICDIF	SPI3TXIF	SPI3RXIF	U3TXIF	U3RXIF	U3EIF	I	QEIZIF	Ι	C1TXIF	CRCIF	UZEIF	U1EIF	QEI1IF
FS4	808h	CMP3IF	CMP2IF	CMP1IF	CNEIF	CNDIF	PWM8IF	PWM71F	PWM6IF	PWM5IF	PWM41F	PWM3IF	PWM2IF	PWM11F	Ι	12C2BCIF	12C1BCIF
IFS5	80Ah	ADCAN4IF	ADCAN3IF	ADCANZIF	ADCAN1IF	ADCANOIF	ADCIF	SENT2EIF	SENT2IF	SENT1EIF	SENT11F	PTG3IF	PTG2IF	PTG1IF	PTG0IF	PTGWDTIF	I
IFS6	80Ch	ADCAN20IF	ADCAN19IF	ADCAN18IF	ADCAN17IF	ADCAN16IF	ADCAN15IF	ADCAN14IF	ADCAN13IF	ADCAN12IF	ADCAN11IF	ADCAN10IF	ADCAN9IF	ADCAN8IF	ADCAN7IF	ADCAN6IF	ADCAN5IF
IFS7	80Eh	SPIZGIF	SPI1GIF	CLC2PIF	CLC1PIF	ADFLTR3IF	ADFLTR2IF	ADFLTR11F	ADFLTR0IF	ADCMP3IF	ADCMP2IF	ADCMP1IF	ADCMP0IF	ADFLTIF	ADCAN23IF	ADCAN22IF	ADCAN21IF
IFS8	810h	MI2C3IF	SI2C3IF	Ι	ı	I	I	Ι	I	I	Ι	I	Ι	Ι	Ι	I	SPI3GIF
IFS9	812h	-	_	Ι	-	-	I	CCT8IF	CCP8IF	_	CCT7IF	CCP7IF	Ι	_	Ι	-	12C3BCIF
IFS10	814h	CLC3PIF	PEVTFIF	PEVTEIF	PEVTDIF	PEVTCIF	PEVTBIF	PEVTAIF	ADFIFOIF	_	_	_	Ι	_	Ι	_	I
IFS11	816h	U3EVTIF	UZEVTIF	U1EVTIF	-	-	Ι	_	I	_	CCT9IF	CCP9IF	CLC4NIF	CLC3NIF	CLC2NIF	CLC1NIF	CLC4PIF
IFS12	818h	-	_	Ι	-	-	Ι	_	I	_	_	_	Ι	PMPEIF	PMPIF	ADCAN25IF ADCAN24IF	ADCAN24IF
- Passagi		- I laimin lamin lamin la															

— = Unimplemented.

INTERRUPT ENABLE REGISTERS TABLE 7-4:

Register	Address	Bit 15	Bit14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
IEC0	820h	INT1IE	NVMIE	ECCSBEIE	U1TXIE	U1RXIE	SPI1TXIE	SPI1RXIE	DMA11E	CCT11E	CCP11E	1	DMA0IE	CNBIE	CNAIE	T1E	INTOIE
IEC1	822h	C1RXIE	SPI2TXIE	SPI2RXIE	UZTXIE	U2RXIE	INT3IE	C1E	CCT2IE	CCP2IE	I	DMA3IE	INT2IE	CNCIE	DMA2IE	MI2C1IE	SI2C1IE
IEC2	824h	CCT6IE	SCP6IE	DMTIE	CCT5IE	CCP5IE	I	CCT4IE	CCP4IE	I	MI2C2IE	SI2C2IE	CCT3IE	CCP3IE	1	_	I
IEC3	826h	PTGSTEPIE	JTAGIE	ICDIE	SPI3TXIE	SPI3RXIE	U3TXIE	U3RXIE	U3EIE	I	QEIZIE	1	C1TXIE	CRCIE	UZEIE	U1EIE	QEI1IE
IEC4	828h	CMP3IE	CMP2IE	CMP1IE	CNEIE	CNDIE	PWW8IE	PWM7IE	PWM6IE	PWM5IE	PWM4IE	PWM3IE	PWM2IE	PWM11E	1	12C2BCIE	I2C1BCIE
IEC5	82Ah	ADCAN4IE	ADCAN3IE	ADCANZIE	ADCAN11E	ADCANOIE	ADCIE	SENTZEIE	SENT2IE	SENT1EIE	SENT11E	PTG3IE	PTG2IE	PTG11E	PTG0IE	PTGWDTIE	I
IEC6	82Ch	ADCAN20IE	ADCAN19IE	ADCAN18IE	ADCAN17IE	ADCAN16IE	ADCAN15IE	ADCAN14IE	ADCAN13IE	ADCAN12IE	ADCAN11IE	ADCAN10IE	ADCAN9IE	ADCAN8IE	ADCAN7IE	ADCANGE	ADCANSIE
IEC7	82Eh	SPI2GIE	SPI1GIE	CLC2PIE	CLC1PIE	ADFLTR3IE	ADFLTR2IE	ADFLTR11E	ADFLTR0IE	ADCMP3IE	ADCMP2IE	ADCMP1IE	ADCMP0IE	ADFLTIE	ADCAN23IE	ADCAN22IE	ADCAN21IE
IEC8	830h	MI2C3IE	SIZC3IE	I	Ι	Ι	I	I	I	I	I	1	I	I	1	_	SPI3GIE
IEC9	832h	Ι	Ι	I	Ι	Ι	I	CCT8IE	CCP8IE	I	CCT7IE	CCP7IE	I	I	1	_	I2C3BCIE
IEC10	834h	CLC3PIE	PEVTFIE	PEVTEIE	PEVTDIE	PEVTCIE	PEVTBIE	PEVTAIE	ADFIFOIE	I	I	1	I	I	1	_	I
IEC11	836h	U3EVTIE	UZEVTIE	U1EVTIE	Ι	Ι	I	I	I	I	CCT9IE	CCP9IE	CLC4NIE	CLC3NIE	CLC2NIE	CLC1NIE	CLC4PIE
IEC12	4858	_	_	Ι	_	Ι	-	Ι	I	I	I	Ι	I	PMPEIE	PMPIE	ADCAN25IE	ADCAN25IE ADCAN24IE
- 00000	- I Ini	- Unimplement															

STERS
ď
Ш
F
<u>ഗ</u>
G
REGIS.
α
>
⊣
$\overline{\mathbf{c}}$
ᇹ
PRIORIT
4
ㄷ
≒
₹
~
Ш
\vdash
INTERRUPT
7-5:

TABLE 7-5:	<u>:</u> 7-5:	Z	TERRUP	T PRIORI	INTERRUPT PRIORITY REGISTE	STEF	RS										
Register	Address	Bit 15	Bit14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
IPC0	840h	Ι	CNBIP2	CNBIP1	CNBIP0	I	CNAIP2	CNAIP1	CNAIPO	Ι	T11P2	T1IP1	T1IP0	I	INT0IP2	INTOIP1	INTOIPO
IPC1	842h	Ι	CCT1IP2	CCT1IP1	CCT1IP0	I	CCP1IP2	CCP11P1	CCP1IP0	-	Ι	Ι	1	_	DMA0IP2	DMA0IP1	DMA0IP0
IPC2	844h	Ι	U1RXIP2	U1RXIP1	U1RXIP0	Ι	SPI1TXIP2	SPI1TXIP1	SPI1TXIP0	-	SPI1RXIP2	SPI1RXIP1	SPI1RXIP0	Ι	DMA11P2	DMA1IP1	DMA1IP0
PG	846h	Ι	INT1IP2	INT1IP1	INT1IP0	I	NVMIP2	NVMIP1	NVMIPO	I	ECCSBEIP2	ECCSBEIP1	ECCSBEIP0	1	U1TXIP2	U1TXIP1	U1TXIP0
PQ4	848h	Ι	CNCIP2	CNCIP1	CNCIP0	I	DMA2IP2	DMA2IP1	DMA2IP0	I	MI2C1IP2	MI2C1IP1	MI2C1IP0	1	SI2C1IP2	SI2C1IP1	SI2C1IP0
IPC5	84Ah	Ι	CCP2IP2	CCP2IP1	CCP2IP0	I	I	I	I	I	DMA3IP2	DMA3IP1	DMA3IP20	1	INT2IP2	INTZIP1	INT2IP0
IPC6	84Ch	I	U2RXIP2	U2RXIP1	U2RXIP0	I	INT3IP2	INT3IP1	0dlsTNI	Ι	C1IP2	C1IP1	C1IP0	I	CCT2IP2	CCT2IP1	CCT2IP0
IPC7	84Eh	ı	C1RXIP2	C1RXIP1	C1RXIP0	Ι	SPI2TXIP2	SPI2TXIP1	SPI2TXIP0	Ι	SPI2RXIP2	SPI2RXIP1	SPI2RXIP0	Ι	UZTXIP2	U2TXIP1	U2TXIP0
IPC8	850h	ı	CCP3IP2	CCP3IP1	CCP3IP0	I	I	I	I	Ι	I	I	I	1	Ι	I	1
IPC9	852h	ı	I	Ι	Ι	I	MI2C2IP2	MI2C2IP1	MI2C2IP0	I	SI2C2IP2	SI2C2IP1	SI2C2IP0	1	CCT3IP2	CCT3IP1	CCT3IP0
IPC10	854h	ı	CCP5IP2	CCP5IP1	CCP5IP0	I	I	I	I	I	CCT4IP2	CCT4IP1	CCT4IP0	1	CCP4IP2	CCP4IP1	CCP4IP0
IPC11	856h	ı	CCT6IP2	CCT6IP1	CCT6IP0	I	CCP6IP2	CCP6IP1	CCP6IP0	I	DMTIP2	DMTIP1	DMTIP0	1	CCT5IP2	CCT5IP1	CCT5IP0
IPC12	858h	ı	CRCIP2	CRCIP1	CRCIP0	I	U2EIP2	U2EIP1	U2EIP0	I	U1EIP2	U1EIP1	U1EIP0	1	QEI1IP2	QEI1IP1	QEI1IP0
IPC13	85Ah	ı	I	Ι	Ι	I	QEI2IP2	QEI2IP1	QEIZIPO	Ι	I	I	I	1	C1TXIP2	C1TXIP1	C1TXIP0
IPC14	85Ch	ı	SPI3RXIP2	SPI3RXIP1	SPI3RXIP0	Ι	U3TXIP2	U3TXIP1	U3TXIP1	Ι	U3RXIP2	U3RXIP1	U3RXIP0	Ι	U3EIP2	U3EIP1	U3EIPO
IPC15	85Eh	ı	PTGSTEPIP2	PTGSTEPIP1	PTGSTEPIP0	Ι	JTAGIP2	JTAGIP1	JTAGIP0	Ι	ICDIP2	ICDIP1	ICDIP0	Ι	SPI3TXIP2	SPI3TXIP1	SPI3TXIP0
IPC16	860h	Ι	PWM1IP2	PWM1IP1	PWM1IP0	Ι	Ι	Ι	Ι	-	I2C2BCIP2	I2C2BCIP1	I2C2BCIP0	Ι	12C1BCIP2	I2C1BCIP1	I2C1BCIP0
IPC17	862h	Ι	PWM5IP2	PWM5IP1	PWM5IP0	I	PWM4IP2	PWM4IP1	PWM4IP0	Ι	PWM3IP2	PWM3IP1	PWM3IP0	Ι	PWW2IP2	PWM2IP1	PWMZIP0
IPC18	864h	Ι	CNDIP2	CNDIP1	CNDIP0	Ι	PWM8IP2	PWM8IP1	PWM8IP0	_	PWM7IP2	PWM7IP1	PWM7IP0	_	PWM6IP2	PWM6IP1	PWM6IP0
IPC19	998	Ι	CMP3IP2	CMP3IP1	CMP3IP0	I	CMP2IP2	CMP2IP1	CMP2IP0	-	CMP1IP2	CMP1IP1	CMP1IP0	Ι	CNEIP2	CNEIP1	CNEIP0
IPC20	968h	Ι	PTG1IP2	PTG1IP1	PTG1IP0	I	PTG0IP2	PTG0IP1	PTG0IP0	I	PTGWDTIP2	PTGWDTIP1	PTGWDTIP0	1	Ι	I	I
IPC21	86Ah	ı	SENT1EIP2	SENT1EIP1	SENT1EIP0	I	SENT1IP2	SENT1IP1	SENT1IP0	I	PTG3IP2	PTG3IP1	PTG3IP0	1	PTG2IP2	PTG2IP1	PTG2IP0
IPC22	86Ch	Ι	ADCAN0IP2	ADCAN0IP1	ADCAN0IP0	Ι	ADCIP2	ADCIP1	ADCIP0	1	SENT2EIP2	SENT2EIP1	SENT2EIP0	_	SENT2IP2	SENT2IP1	SENT2IP0
IPC23	86Eh	Ι	ADCAN4IP2	ADCAN4IP1	ADCAN4IP0	ı	ADCAN3IP2	ADCAN3IP1	ADCAN3IP0	-	ADCAN2IP2	ADCAN2IP1	ADCAN2IP0	_	ADCAN11P2	ADCAN1IP1	ADCAN1IP0
IPC24	870h	Ι	ADCAN8IP2	ADCAN8IP1	ADCAN8IP0	Ι	ADCAN7IP2	ADCAN7IP1	ADCAN7IP0	Ι	ADCAN6IP2	ADCAN6IP1	ADCAN6IP0	_	ADCAN5IP2	ADCAN5IP1	ADCAN5IP0
IPC25	872h	1	ADCAN12IP2	ADCAN12IP1	ADCAN12IP0	I	ADCAN11IP2	ADCAN11IP1	ADCAN11IP0	Ι	ADCAN10IP2	ADCAN10IP1	ADCAN10IP0	_	ADCAN9IP2	ADCAN9IP1	ADCAN9IP0
IPC26	874h	Ι	ADCAN16IP2	ADCAN16IP2	ADCAN16IP2	ı	ADCAN15IP2	ADCAN15IP1	ADCAN15IP0	-	ADCAN14IP2	ADCAN14IP1	ADCAN14IP0	_	ADCAN13IP2	ADCAN13IP1	ADCAN13IP0
IPC27	876h	Ι	ADCAN201P2	ADCAN20IP1	ADCAN20IP0	ı	ADCAN19IP2	ADCAN19IP1	ADCAN19IP0	-	ADCAN18IP2	ADCAN18IP1	ADCAN18IP0	_	ADCAN17IP2	ADCAN17IP1	ADCAN17IP0
IPC28	878h	Ι	ADFLTIP2	ADFLTIP1	ADFLTIP0	ı	ADCAN23IP2	ADCAN23IP1	ADCAN22IP0	-	ADCAN22IP2	ADCAN22IP1	ADCAN22IP0	_	ADCAN21IP2	ADCAN21IP1	ADCAN211P0
IPC29	87Ah	Ι	ADCMP3IP2	ADCMP3IP1	ADCMP3IP0	Ι	ADCMP2IP2	ADCMP2IP1	ADCMP2IP0	_	ADCMP1IP2	ADCMP1IP1	ADCMP11P0	_	ADCMP0IP2	ADCMP0IP1	ADCMP0IP0
IPC30	87Ch	Ι	ADFLTR3IP2	ADFLTR3IP1	ADFLTR3IP0	ı	ADFLTR2IP2	ADFLTR2IP1	ADFLTR2IP0	-	ADFLTR1IP2	ADFLTR1IP1	ADFLTR1IP0	_	ADFLTR0IP2	ADFLTR0IP1	ADFLTR0IP0
IPC31	87Eh	Ι	SPI2GIP0	SPI2GIP1	SPI2GIP0	ı	SPI1GIP2	SPI1GIP1	SPI1GIP0	-	CLC2PIP2	CLC2PIP1	CLC2PIP0	_	CLC1PIP2	CLC1PIP1	CLC1PIP0
IPC32	880h	1	Ι	1	-	I	Ι	-	-	-	1	Ι	_	_	SPI3GIP2	SPI3GIP1	SPI3GIP0
IPC33	882h	1	I	Ι	I	Ι	Ι	I	I	Ι	Ι	Ι	1	_	1	1	1
IPC34	884h	Ι		1	1	Ι	1	-	1	Ι	1	1	1	_	1	1	1
Legend:	— = Unimplemented	nplemer	nted.														

TABLE 7-5: INTERRUPT PRIORITY REGISTERS (CONTINUED)

egister	Address	Bit 15	Bit14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
35	886h	Ι	MI2C3IP2	MI2C3IP1	MI2C3IP1	I	SI2C3IP2	SI2C3IP1	SI2C3IP0	I	I	I	I	1	1	I	1
36	888h	I	I	Ι	Ι	I	I	I	Ι	I	I	Ι	I	I	12C3BCIP2	I2C3BCIP1	I2C3BCIP0
C37	88Ah	I	I	I	Ι	I	CCT7IP2	CCT7IP1	CCT7IP0	I	CCP7IP2	CCP7IP1	CCP71P0	I	Ι	I	I
C38	88Ch	1	-	Ι	Ι	Ι	_	-	Ι	I	CCT8IP2	CCT8IP1	CCT8IP0	Ι	CCP8IP2	CCP8IP1	CCP8IP0
623	88Eh	1	-	Ι	Ι	Ι	_	-	Ι	I	_	Ι	_	Ι	_	Ι	I
C40	890h	1	-	Ι	Ι	Ι	_	-	Ι	I	_	Ι	_	Ι	_	Ι	I
42	892h	1	-	Ι	Ι	Ι	_	-	Ι	I	_	Ι	_	Ι	_	Ι	I
C42	894h	Ι	PEVTCIP2	PEVTCIP1	PEVTCIP0	Ι	PEVTBIP2	PEVTBIP1	PEVTBIP0	I	PEVTAIP2	PEVTAIP1	PEVTAIP0	Ι	ADF1F0IP2	ADFIFOIP1	ADFIFOIP0
C43	896h	Ι	CLC3PIP2	CLC3PIP1	CLC3PIP0	Ι	PEVTFIP2	PEVTFIP1	PEVTFIP0	I	PEVTEIP2	PEVTEIP1	PEVTEIP0	Ι	PEVTDIP2	PEVTDIP1	PEVTDIP0
Q4 4	898h	Ι	CLC3NIP2	CLC3NIP1	CLC3NIP0	Ι	CLC2NIP2	CLC2NIP1	CLC2NIP0	I	CLC1NIP2	CLC1NIP1	CLC1NIP0	Ι	CLC4PIP2	CLC4PIP1	CLC4PIP0
C45	89Ah	1	-	Ι	Ι	Ι	CCT9IP2	CCT9IP1	CCT9IP0	I	CCP9IP2	CCP9IP1	CCP9IP0	Ι	CLC4NIP2	CLC4NIP1	CLC4NIP0
C46	89Ch	1	-	Ι	Ι	Ι	_	-	Ι	I	_	Ι	_	Ι	_	Ι	I
C47	89Eh	Ι	U3EVTIP2	U3EVTIP1	U3EVTIP0	Ι	U2EVTIP2	U2EVTIP1	UZEVTIPO	I	U1EVTIP2	U1EVTIP1	U1EVTIP0	Ι	_	Ι	I
C48	900h	_	PMPEIP2	PMPEIP1	PMPEIP0		PMPIP2	PMPIP1	PMPIP0		ADCAN25IP2	ADCAN25IP2 ADCAN25IP1 ADCAN25IP0	ADCAN25IP0		ADCAN24IP2 ADCAN24IP1 ADCAN24IP0	ADCAN24IP1	ADCAN24IP0
gend:	—= Uni	— = Unimplemented	nted.														

7.3 Interrupt Resources

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

7.3.1 KEY RESOURCES

- "Interrupts" (DS70000600) in the "dsPIC33/ PIC24 Family Reference Manual"
- · Code Samples
- · Application Notes
- · Software Libraries
- Webinars
- All Related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

7.4 Interrupt Control and Status Registers

The dsPIC33CK256MP508 family devices implement the following registers for the interrupt controller:

- INTCON1
- INTCON2
- INTCON3
- INTCON4
- INTTREG

7.4.1 INTCON1 THROUGH INTCON4

Global interrupt control functions are controlled from INTCON1, INTCON2, INTCON3 and INTCON4.

INTCON1 contains the Interrupt Nesting Disable bit (NSTDIS), as well as the control and status flags for the processor trap sources.

The INTCON2 register controls external interrupt request signal behavior, contains the Global Interrupt Enable bit (GIE) and the Alternate Interrupt Vector Table Enable bit (AIVTEN).

INTCON3 contains the status flags for the Auxiliary PLL and DO stack overflow status trap sources.

The INTCON4 register contains the Software Generated Hard Trap Status bit (SGHT).

7.4.2 IFSx

The IFSx registers maintain all of the interrupt request flags. Each source of interrupt has a status bit, which is set by the respective peripherals or external signal and is cleared via software.

7.4.3 IECx

The IECx registers maintain all of the interrupt enable bits. These control bits are used to individually enable interrupts from the peripherals or external signals.

7.4.4 IPCx

The IPCx registers are used to set the Interrupt Priority Level (IPL) for each source of interrupt. Each user interrupt source can be assigned to one of seven priority levels.

7.4.5 INTTREG

The INTTREG register contains the associated interrupt vector number and the new CPU Interrupt Priority Level, which are latched into the Vector Number (VECNUM<7:0>) and Interrupt Level bits (ILR<3:0>) fields in the INTTREG register. The new Interrupt Priority Level is the priority of the pending interrupt.

The interrupt sources are assigned to the IFSx, IECx and IPCx registers in the same sequence as they are listed in Table 7-2. For example, INTO (External Interrupt 0) is shown as having Vector Number 8 and a natural order priority of 0. Thus, the INTOIF bit is found in IFSO<0>, the INTOIE bit in IECO<0> and the INTOIP<2:0> bits in the first position of IPCO (IPCO<2:0>).

7.4.6 STATUS/CONTROL REGISTERS

Although these registers are not specifically part of the interrupt control hardware, two of the CPU Control registers contain bits that control interrupt functionality. For more information on these registers, refer to "dsPIC33E Enhanced CPU" (DS70005158) in the "dsPIC33/PIC24 Family Reference Manual".

- The CPU STATUS Register, SR, contains the IPL<2:0> bits (SR<7:5>). These bits indicate the current CPU Interrupt Priority Level. The user software can change the current CPU Interrupt Priority Level by writing to the IPLx bits.
- The CORCON register contains the IPL3 bit, which together with IPL<2:0>, also indicates the current CPU priority level. IPL3 is a read-only bit so that trap events cannot be masked by the user software.

All Interrupt registers are described in Register 7-3 through Register 7-7 in the following pages.

REGISTER 7-1: SR: CPU STATUS REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/C-0	R/C-0	R-0	R/W-0
OA	ОВ	SA	SB	OAB	SAB	DA	DC
bit 15							bit 8

R/W-0 ⁽³⁾	R/W-0 ⁽³⁾	R/W-0 ⁽³⁾	R-0	R/W-0	R/W-0	R/W-0	R/W-0
IPL2 ⁽²⁾	IPL1 ⁽²⁾	IPL0 ⁽²⁾	RA	N	OV	Z	С
bit 7							bit 0

Legend:	C = Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit,	, read as '0'
-n = Value at POR	'1'= Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-5 IPL<2:0>: CPU Interrupt Priority Level Status bits^(2,3)

111 = CPU Interrupt Priority Level is 7 (15); user interrupts are disabled

110 = CPU Interrupt Priority Level is 6 (14)

101 = CPU Interrupt Priority Level is 5 (13)

100 = CPU Interrupt Priority Level is 4 (12)

011 = CPU Interrupt Priority Level is 3 (11)

010 = CPU Interrupt Priority Level is 2 (10)

001 = CPU Interrupt Priority Level is 1 (9)

000 = CPU Interrupt Priority Level is 0 (8)

Note 1: For complete register details, see Register 3-1.

- 2: The IPL<2:0> bits are concatenated with the IPL<3> bit (CORCON<3>) to form the CPU Interrupt Priority Level. The value in parentheses indicates the IPL, if IPL<3> = 1. User interrupts are disabled when IPL<3> = 1.
- 3: The IPL<2:0> Status bits are read-only when the NSTDIS bit (INTCON1<15>) = 1.

REGISTER 7-2: CORCON: CORE CONTROL REGISTER⁽¹⁾

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R-0	R-0	R-0
VAR	_	US1	US0	EDT	DL2	DL1	DL0
bit 15							bit 8

R/W-0	R/W-0	R/W-1	R/W-0	R/C-0	R-0	R/W-0	R/W-0
SATA	SATB	SATDW	ACCSAT	IPL3 ⁽²⁾	SFA	RND	IF
bit 7							bit 0

Legend:C = Clearable bitR = Readable bitW = Writable bitU = Unimplemented bit, read as '0'-n = Value at POR'1'= Bit is set'0' = Bit is clearedx = Bit is unknown

bit 15 VAR: Variable Exception Processing Latency Control bit

1 = Variable exception processing is enabled0 = Fixed exception processing is enabled

bit 3 IPL3: CPU Interrupt Priority Level Status bit 3⁽²⁾

 $_1$ = CPU Interrupt Priority Level is greater than 7

0 = CPU Interrupt Priority Level is 7 or less

Note 1: For complete register details, see Register 3-2.

2: The IPL3 bit is concatenated with the IPL<2:0> bits (SR<7:5>) to form the CPU Interrupt Priority Level.

REGISTER 7-3: INTCON1: INTERRUPT CONTROL REGISTER 1

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
NSTDIS	OVAERR	OVBERR	COVAERR	COVBERR	OVATE	OVBTE	COVTE
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0
SFTACERR	DIV0ERR	DMACERR	MATHERR	ADDRERR	STKERR	OSCFAIL	_
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read a	as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

NSTDIS: Interrupt Nesting Disable bit
1 = Interrupt nesting is disabled
0 = Interrupt nesting is enabled
OVAERR: Accumulator A Overflow Trap Flag bit
1 = Trap was caused by an overflow of Accumulator A
0 = Trap was not caused by an overflow of Accumulator A
OVBERR: Accumulator B Overflow Trap Flag bit
1 = Trap was caused by an overflow of Accumulator B
0 = Trap was not caused by an overflow of Accumulator B
COVAERR: Accumulator A Catastrophic Overflow Trap Flag bit
1 = Trap was caused by a catastrophic overflow of Accumulator A
0 = Trap was not caused by a catastrophic overflow of Accumulator A
COVBERR: Accumulator B Catastrophic Overflow Trap Flag bit
1 = Trap was caused by a catastrophic overflow of Accumulator B
0 = Trap was not caused by a catastrophic overflow of Accumulator B
OVATE: Accumulator A Overflow Trap Enable bit
1 = Trap overflow of Accumulator A 0 = Trap is disabled
OVBTE: Accumulator B Overflow Trap Enable bit
1 = Trap overflow of Accumulator B
0 = Trap is disabled
COVTE: Catastrophic Overflow Trap Enable bit
1 = Trap catastrophic overflow of Accumulator A or B is enabled
0 = Trap is disabled
SFTACERR: Shift Accumulator Error Status bit
1 = Math error trap was caused by an invalid accumulator shift
0 = Math error trap was not caused by an invalid accumulator shift
DIV0ERR: Divide-by-Zero Error Status bit
1 = Math error trap was caused by a divide-by-zero
0 = Math error trap was not caused by a divide-by-zero
DMACERR: DMA Controller Trap Status bit
1 = DMAC error trap has occurred
0 = DMAC error trap has not occurred
MATHERR: Math Error Status bit
1 = Math error trap has occurred
0 = Math error trap has not occurred

REGISTER 7-3: INTCON1: INTERRUPT CONTROL REGISTER 1 (CONTINUED)

bit 3

ADDRERR: Address Error Trap Status bit

1 = Address error trap has occurred

0 = Address error trap has not occurred

bit 2

STKERR: Stack Error Trap Status bit

1 = Stack error trap has occurred0 = Stack error trap has not occurred

bit 1 OSCFAIL: Oscillator Failure Trap Status bit

 ${\tt 1}$ = Oscillator failure trap has occurred ${\tt 0}$ = Oscillator failure trap has not occurred

bit 0 **Unimplemented:** Read as '0'

REGISTER 7-4: INTCON2: INTERRUPT CONTROL REGISTER 2

R/W-1	R/W-0	R/W-0	U-0	U-0	U-0	U-0	R/W-0
GIE	DISI	SWTRAP	_	_	_	_	AIVTEN
bit 15	•		•				bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	INT3EP	INT2EP	INT1EP	INT0EP
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	as '0'
n = Value at POP	'1' = Rit is set	'0' = Rit is cleared	v = Rit is unknown

bit 15 GIE: Global Interrupt Enable bit 1 = Interrupts and associated IE bits are enabled 0 = Interrupts are disabled, but traps are still enabled bit 14 DISI: DISI Instruction Status bit 1 = DISI instruction is active 0 = DISI instruction is not active bit 13 SWTRAP: Software Trap Status bit 1 = Software trap is enabled 0 = Software trap is disabled bit 12-9 Unimplemented: Read as '0' bit 8 **AIVTEN:** Alternate Interrupt Vector Table Enable bit 1 = Uses Alternate Interrupt Vector Table 0 = Uses standard Interrupt Vector Table Unimplemented: Read as '0' bit 7-4 bit 3 INT3EP: External Interrupt 3 Edge Detect Polarity Select bit 1 = Interrupt on negative edge 0 = Interrupt on positive edge bit 2 INT2EP: External Interrupt 2 Edge Detect Polarity Select bit 1 = Interrupt on negative edge 0 = Interrupt on positive edge bit 1 INT1EP: External Interrupt 1 Edge Detect Polarity Select bit 1 = Interrupt on negative edge 0 = Interrupt on positive edge bit 0 INTOEP: External Interrupt 0 Edge Detect Polarity Select bit 1 = Interrupt on negative edge 0 = Interrupt on positive edge

REGISTER 7-5: INTCON3: INTERRUPT CONTROL REGISTER 3

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	CAN ⁽¹⁾	NAE
bit 15							bit 8

U-0	U-0	U-0	R/W-0	U-0	U-0	U-0	R/W-0
_	_	_	DOOVR	_	_	_	APLL
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9 CAN: CAN Address Error Soft Trap Status bit (1)

1 = CAN address error soft trap has occurred

0 = CAN address error soft trap has not occurred

bit 8 NAE: NVM Address Error Soft Trap Status bit

1 = NVM address error soft trap has occurred

0 = NVM address error soft trap has not occurred

bit 7-5 **Unimplemented:** Read as '0'

bit 4 DOOVR: DO Stack Overflow Soft Trap Status bit

1 = DO stack overflow soft trap has occurred

0 = DO stack overflow soft trap has not occurred

bit 3-1 **Unimplemented:** Read as '0'

bit 0 APLL: Auxiliary PLL Loss of Lock Soft Trap Status bit

1 = APLL lock soft trap has occurred

0 = APLL lock soft trap has not occurred

Note 1: The CAN peripheral is not available on all devices. Refer to Table 1 and Table 2 for availability.

REGISTER 7-6: INTCON4: INTERRUPT CONTROL REGISTER 4

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0			
_	_	_	_	_	_	ECCDBE	SGHT			
bit 7 bit 0										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-2 **Unimplemented:** Read as '0'

bit 1 **ECCDBE:** ECC Double-Bit Error Trap bit

1 = ECC double-bit error trap has occurred 0 = ECC double-bit error trap has not occurred

bit 0 SGHT: Software Generated Hard Trap Status bit

1 = Software generated hard trap has occurred

0 = Software generated hard trap has not occurred

REGISTER 7-7: INTTREG: INTERRUPT CONTROL AND STATUS REGISTER

U-0	U-0	R-0	U-0	R-0	R-0	R-0	R-0
_	_	VHOLD	_	ILR3	ILR2	ILR1	ILR0
bit 15							bit 8

| R-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| VECNUM7 | VECNUM6 | VECNUM5 | VECNUM4 | VECNUM3 | VECNUM2 | VECNUM1 | VECNUM0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13 VHOLD: Vector Number Capture Enable bit

1 = VECNUM<7:0> bits read current value of vector number encoding tree (i.e., highest priority pending

interrupt)

0 = Vector number latched into VECNUM<7:0> at Interrupt Acknowledge and retained until next IACK

bit 12 **Unimplemented:** Read as '0'

bit 11-8 ILR<3:0>: New CPU Interrupt Priority Level bits

1111 = CPU Interrupt Priority Level is 15

. . .

0001 = CPU Interrupt Priority Level is 1 0000 = CPU Interrupt Priority Level is 0

bit 7-0 VECNUM<7:0>: Vector Number of Pending Interrupt bits

11111111 = 255, Reserved; do not use

. . .

00001001 = 9, IC1 - Input Capture 1

00001000 = 8, INT0 – External Interrupt 0

00000111 **= 7**, Reserved; do not use

00000110 = 6, Generic soft error trap

00000101 = 5, Reserved; do not use

00000100 **= 4**, Math error trap

00000011 **= 3**, Stack error trap

00000010 **= 2**, Generic hard trap

00000001 = 1, Address error trap

00000000 = 0, Oscillator fail trap

8.0 I/O PORTS

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "I/O Ports with Edge Detect" (www.microchip.com/DS70005322) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices.

Many of the device pins are shared among the peripherals and the Parallel I/O ports. All I/O input ports feature Schmitt Trigger inputs for improved noise immunity. The PORT registers are located in the SFR.

Some of the key features of the I/O ports are:

- · Individual Output Pin Open-Drain Enable/Disable
- · Individual Input Pin Weak Pull-up and Pull-Down
- Monitor Selective Inputs and Generate Interrupt when Change in Pin State is Detected
- · Operation during Sleep and Idle modes

8.1 Parallel I/O (PIO) Ports

All port pins have 12 registers directly associated with their operation as digital I/Os. The Data Direction register (TRISx) determines whether the pin is an input or an output. If the data direction bit is a '1', then the pin is an input.

All port pins are defined as inputs after a Reset. Reads from the latch (LATx), read the latch. Writes to the latch, write the latch. Reads from the port (PORTx), read the port pins, while writes to the port pins, write the latch. Any bit and its associated data and control registers that are not valid for a particular device are disabled. This means the corresponding LATx and TRISx registers, and the port pin are read as zeros.

When a pin is shared with another peripheral or function that is defined as an input only, it is nevertheless regarded as a dedicated port because there is no other competing source of outputs. Table 8-1 shows the pin availability. Table 8-2 shows the 5V input tolerant pins across this device.

TABLE 8-1: PIN AND ANSELX AVAILABILITY

Device	Rx15	Rx14	Rx13	Rx12	Rx11	Rx10	Rx9	Rx8	Rx7	Rx6	Rx5	Rx4	Rx3	Rx2	Rx1	Rx0
						POR	ГА									
dsPIC33XXXMP508/208	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
dsPIC33XXXMP506/206	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
dsPIC33XXXMP504/204	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
dsPIC33XXXMP503/203	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
dsPIC33XXXMP502/202	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
ANSELA	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х
						POR	ГВ									
dsPIC33XXXMP508/208	Х	Х	Х	Χ	Х	Х	Х	Χ	Х	Х	Χ	Χ	Χ	Х	Х	Χ
dsPIC33XXXMP506/206	Х	Χ	Х	Χ	Χ	Χ	Χ	Χ	Χ	Χ	Χ	Χ	Χ	Х	Χ	Χ
dsPIC33XXXMP504/204	Х	Х	Х	Х	Х	Х	Х	Х	Х	Χ	Х	Х	Х	Х	Х	Χ
dsPIC33XXXMP503/203	Х	Х	Х	Χ	Х	Х	Х	Χ	Х	Х	Χ	Χ	Χ	Х	Х	Χ
dsPIC33XXXMP502/202	Х	Х	Х	Х	Х	Х	Х	Х	Х	Χ	Х	Х	Х	Х	Х	Χ
ANSELB	_	_	_	_	_	_	Х	Χ	Χ	_	_	Х	Χ	Х	Х	Х
						POR	ГС									
dsPIC33XXXMP508/208	Х	Х	Х	Х	Х	Х	Х	Χ	Х	Х	Χ	Х	Х	Х	Х	Χ
dsPIC33XXXMP506/206	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Χ
dsPIC33XXXMP504/204	_	_	Х	Х	Х	Х	Х	Х	Х	Χ	Х	Х	Х	Х	Х	Χ
dsPIC33XXXMP503/203	_	_	_	_	_	_	_	_	_	_	Χ	Х	Χ	Х	Х	Х
dsPIC33XXXMP502/202	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
ANSELC	_	_	_	_	_	_	_	_	Х	Χ	_	_	Χ	Х	Х	Х
						POR	ΓD									
dsPIC33XXXMP508/208	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
dsPIC33XXXMP506/206	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Χ
dsPIC33XXXMP504/204	_	_	Х	_	_	Х	_	Х	_	_	_	_	_	_	Х	_
dsPIC33XXXMP503/203	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
dsPIC33XXXMP502/202	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
ANSELD	_	_	Х	_	Х	Х	_	_	_	_	_	_	_	_	_	_
PORTE																
dsPIC33XXXMP508/208	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
dsPIC33XXXMP506/206	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
dsPIC33XXXMP504/204	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
dsPIC33XXXMP503/203	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
dsPIC33XXXMP502/202	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_
ANSELE	_	_	_	_	_	_	_	_	_	_	_	Х	Х	Х	Х	Х

TABLE 8-2: 5V INPUT TOLERANT PORTS

PORTA	_	_	_	_	_	_	_	_	_	_	_	RA4	RA3	RA2	RA1	RA0
PORTB	RB15	RB14	RB13	RB12	RB11	RB10	RB9	RB8	RB7	RB6	RB5	RB4	RB3	RB2	RB1	RB0
PORTC	RC15	RC14	RC13	RC12	RC11	RC10	RC9	RC8	RC7	RC6	RC5	RC4	RC3	RC2	RC1	RC0
PORTD	RD15	RD14	RD13	RD12	RD11	RD10	RD9	RD8	RD7	RD6	RD5	RD4	RD3	RD2	RD1	RD0
PORTE	RE15	RE14	RE13	RE12	RE11	RE10	RE9	RE8	RE7	RE6	RE5	RE4	RE3	RE2	RE1	RE0

Legend: Shaded pins are up to 5.5 VDC input tolerant.




FIGURE 8-1: BLOCK DIAGRAM OF A TYPICAL SHARED PORT STRUCTURE

8.1.1 OPEN-DRAIN CONFIGURATION

In addition to the PORTx, LATx and TRISx registers for data control, port pins can also be individually configured for either digital or open-drain output. This is controlled by the Open-Drain Enable for PORTx register, ODCx, associated with each port. Setting any of the bits configures the corresponding pin to act as an open-drain output.

The open-drain feature allows the generation of outputs, other than VDD, by using external pull-up resistors. The maximum open-drain voltage allowed on any pin is the same as the maximum VIH specification for that particular pin.

8.2 Configuring Analog and Digital Port Pins

The ANSELx registers control the operation of the analog port pins. The port pins that are to function as analog inputs or outputs must have their corresponding ANSELx and TRISx bits set. In order to use port pins for I/O functionality with digital modules, such as timers, UARTs, etc., the corresponding ANSELx bit must be cleared.

The ANSELx registers have a default value of 0xFFFF; therefore, all pins that share analog functions are analog (not digital) by default.

Pins with analog functions affected by the ANSELx registers are listed with a buffer type of analog in the Pinout I/O Descriptions (see Table 1-1).

If the TRISx bit is cleared (output) while the ANSELx bit is set, the digital output level (VOH or VOL) is converted by an analog peripheral, such as the ADC module or comparator module.

When the PORTx register is read, all pins configured as analog input channels are read as cleared (a low level).

Pins configured as digital inputs do not convert an analog input. Analog levels on any pin, defined as a digital input (including the ANx pins), can cause the input buffer to consume current that exceeds the device specifications.

8.2.1 I/O PORT WRITE/READ TIMING

One instruction cycle is required between a port direction change or port write operation and a read operation of the same port. Typically, this instruction would be a NOP.

8.3 PORT Control Registers

The following registers are in the PORT module:

- Register 8-1: ANSELx (one per port)
- Register 8-2: TRISx (one per port)
- Register 8-3: PORTx (one per port)
- Register 8-4: LATx (one per port)
- Register 8-5: ODCx (one per port)
- Register 8-6: CNPUx (one per port)
- Register 8-7: CNPDx (one per port)
- Register 8-8: CNCONx (one per port optional)
- Register 8-9: CNEN0x (one per port)
- Register 8-10: CNSTATx (one per port optional)
- Register 8-11: CNEN1x (one per port)
- Register 8-12: CNFx (one per port)

REGISTER 8-1: ANSELX: ANALOG SELECT FOR PORTX REGISTER

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1						
	ANSELx<15:8>												
bit 15 bit 8													

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1					
	ANSELx<7:0>											
bit 7												

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 ANSELx<15:0>: Analog Select for PORTx bits

- 1 = Analog input is enabled and digital input is disabled on the PORTx[n] pin
- 0 = Analog input is disabled and digital input is enabled on the PORTx[n] pin

REGISTER 8-2: TRISx: OUTPUT ENABLE FOR PORTx REGISTER

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1					
	TRISx<15:8>											
bit 15												

| R/W-1 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | TRIS | <7:0> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 TRISx<15:0>: Output Enable for PORTx bits

1 = LATx[n] is not driven on the PORTx[n] pin

0 = LATx[n] is driven on the PORTx[n] pin

REGISTER 8-3: PORTX: INPUT DATA FOR PORTX REGISTER

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1		
PORTx<15:8>									
bit 15		bit 8							

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1		
PORTx<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PORTx<15:0>:** PORTx Data Input Value bits

REGISTER 8-4: LATX: OUTPUT DATA FOR PORTX REGISTER

R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x
			LATx<	:15:8>			
bit 15							bit 8

| R/W-x |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | LATx | <7:0> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 LATx<15:0>: PORTx Data Output Value bits

REGISTER 8-5: ODCx: OPEN-DRAIN ENABLE FOR PORTx REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			ODCx	<15:8>			
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | ODC | <7:0> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 ODCx<15:0>: PORTx Open-Drain Enable bits

1 = Open-drain is enabled on the PORTx pin

0 = Open-drain is disabled on the PORTx pin

REGISTER 8-6: CNPUx: CHANGE NOTIFICATION PULL-UP ENABLE FOR PORTX REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
CNPUx<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			CNPU	x<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 CNPUx<15:0>: Change Notification Pull-up Enable for PORTx bits

1 = The pull-up for PORTx[n] is enabled – takes precedence over the pull-down selection

0 = The pull-up for PORTx[n] is disabled

REGISTER 8-7: CNPDx: CHANGE NOTIFICATION PULL-DOWN ENABLE FOR PORTX REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			CNPD	<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	CNPDx<7:0>								
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **CNPDx<15:0>:** Change Notification Pull-Down Enable for PORTx bits

1 = The pull-down for PORTx[n] is enabled (if the pull-up for PORTx[n] is not enabled)

0 = The pull-down for PORTx[n] is disabled

REGISTER 8-8: CNCONx: CHANGE NOTIFICATION CONTROL FOR PORTX REGISTER

R/W-0	U-0	U-0	U-0	R/W-0	U-0	U-0	U-0
ON	_	_	_	CNSTYLE	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 ON: Change Notification (CN) Control for PORTx On bit

1 = CN is enabled 0 = CN is disabled

bit 14-12 **Unimplemented:** Read as '0'

bit 11 CNSTYLE: Change Notification Style Selection bit

1 = Edge style (detects edge transitions, CNFx<15:0> bits are used for a Change Notification event)

0 = Mismatch style (detects change from last port read, CNSTATx<15:0> bits are used for a Change

Notification event)

bit 10-0 **Unimplemented:** Read as '0'

REGISTER 8-9: CNEN0x: INTERRUPT CHANGE NOTIFICATION ENABLE FOR PORTX REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CNEN0x<15:8>							
bit 15						bit 8	

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | | | | | |
| bit 7 | | | | | | bit 0 | |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 CNEN0x<15:0>: Interrupt Change Notification Enable for PORTx bits

1 = Interrupt-on-change (from the last read value) is enabled for PORTx[n]

0 = Interrupt-on-change is disabled for PORTx[n]

REGISTER 8-10: CNSTATX: INTERRUPT CHANGE NOTIFICATION STATUS FOR PORTX REGISTER

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			CNSTAT	Гx<15:8>			
bit 15						bit 8	

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
bit 7						bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 CNSTATx<15:0>: Interrupt Change Notification Status for PORTx bits

When CNSTYLE (CNCONx<11>) = 0:

1 = Change occurred on PORTx[n] since last read of PORTx[n]

0 = Change did not occur on PORTx[n] since last read of PORTx[n]

REGISTER 8-11: CNEN1x: INTERRUPT CHANGE NOTIFICATION EDGE SELECT FOR PORTX REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			CNEN1	x<15:8>			
bit 15						bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			CNEN1	1x<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 CNEN1x<15:0>: Interrupt Change Notification Edge Select for PORTx bits

REGISTER 8-12: CNFx: INTERRUPT CHANGE NOTIFICATION FLAG FOR PORTx REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CNFx<15:8>							
bit 15					bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CNFx<7:0>							
bit 7						bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15- CNFx<15:0>: Interrupt Change Notification Flag for PORTx bits

When CNSTYLE (CNCONx<11>) = 1:

1 = An enabled edge event occurred on the PORTx[n] pin

0 = An enabled edge event did not occur on the PORTx[n] pin

8.4 Input Change Notification (ICN)

The Input Change Notification function of the I/O ports allows the dsPIC33CK256MP508 family devices to generate interrupt requests to the processor in response to a Change-of-State (COS) on selected input pins. This feature can detect input Change-of-States, even in Sleep mode, when the clocks are disabled. Every I/O port pin can be selected (enabled) for generating an interrupt request on a Change-of-State. Five control registers are associated with the Change Notification (CN) functionality of each I/O port. To enable the Change Notification feature for the port, the ON bit (CNCONx<15>) must be set.

The CNEN0x and CNEN1x registers contain the CN interrupt enable control bits for each of the input pins. The setting of these bits enables a CN interrupt for the corresponding pins. Also, these bits, in combination with the CNSTYLE bit (CNCONx<11>), define a type of transition when the interrupt is generated. Possible CN event options are listed in Table 8-3.

TABLE 8-3: CHANGE NOTIFICATION EVENT OPTIONS

CNSTYLE Bit (CNCONx<11>)	CNEN1x Bit	CNEN0x Bit	Change Notification Event Description
0	Does not matter	0	Disabled
0	Does not matter	1	Detects a mismatch between the last read state and the current state of the pin
1	0	0	Disabled
1	0	1	Detects a positive transition only (from '0' to '1')
1	1	0	Detects a negative transition only (from '1' to '0')
1	1	1	Detects both positive and negative transitions

The CNSTATx register indicates whether a change occurred on the corresponding pin since the last read of the PORTx bit. In addition to the CNSTATx register, the CNFx register is implemented for each port. This register contains flags for Change Notification events. These flags are set if the valid transition edge, selected in the CNEN0x and CNEN1x registers, is detected. CNFx stores the occurrence of the event. CNFx bits must be cleared in software to get the next Change Notification interrupt. The CN interrupt is generated only for the I/Os configured as inputs (corresponding TRISx bits must be set).

Note: Pull-ups and pull-downs on Input Change Notification pins should always be disabled when the port pin is configured as a digital output.

8.5 Peripheral Pin Select (PPS)

A major challenge in general purpose devices is providing the largest possible set of peripheral features, while minimizing the conflict of features on I/O pins. The challenge is even greater on low pin count devices. In an application where more than one peripheral needs to be assigned to a single pin, inconvenient work arounds in application code, or a complete redesign, may be the only option.

Peripheral Pin Select configuration provides an alternative to these choices by enabling peripheral set selection and placement on a wide range of I/O pins. By increasing the pinout options available on a particular device, users can better tailor the device to their entire application, rather than trimming the application to fit the device.

The Peripheral Pin Select configuration feature operates over a fixed subset of digital I/O pins. Users may independently map the input and/or output of most digital peripherals to any one of these I/O pins. Hardware safeguards are included that prevent accidental or spurious changes to the peripheral mapping once it has been established.

8.5.1 AVAILABLE PINS

The number of available pins is dependent on the particular device and its pin count. Pins that support the Peripheral Pin Select feature include the label, "RPn", in their full pin designation, where "n" is the remappable pin number. "RP" is used to designate pins that support both remappable input and output functions.

8.5.2 AVAILABLE PERIPHERALS

The peripherals managed by the Peripheral Pin Select are all digital only peripherals. These include general serial communications (UART and SPI), general purpose timer clock inputs, timer-related peripherals (input capture and output compare) and interrupt-on-change inputs.

In comparison, some digital only peripheral modules are never included in the Peripheral Pin Select feature. This is because the peripheral's function requires special I/O circuitry on a specific port and cannot be easily connected to multiple pins. One example includes I²C modules. A similar requirement excludes all modules with analog inputs, such as the A/D Converter (ADC)

A key difference between remappable and non-remappable peripherals is that remappable peripherals are not associated with a default I/O pin. The peripheral must always be assigned to a specific I/O pin before it can be used. In contrast, non-remappable peripherals are always available on a default pin, assuming that the peripheral is active and not conflicting with another peripheral.

When a remappable peripheral is active on a given I/O pin, it takes priority over all other digital I/Os and digital communication peripherals associated with the pin. Priority is given regardless of the type of peripheral that is mapped. Remappable peripherals never take priority over any analog functions associated with the pin.

8.5.3 CONTROLLING CONFIGURATION CHANGES

Because peripheral mapping can be changed during run time, some restrictions on peripheral remapping are needed to prevent accidental configuration changes. The dsPIC33CK256MP508 devices have implemented the control register lock sequence.

8.5.3.1 Control Register Lock

Under normal operation, writes to the RPINRx and RPORx registers are not allowed. Attempted writes will appear to execute normally, but the contents of the registers will remain unchanged. To change these registers, they must be unlocked in hardware. The register lock is controlled by the IOLOCK bit (RPCON<11>).

Setting IOLOCK prevents writes to the control registers; clearing IOLOCK allows writes. To set or clear IOLOCK, the NVMKEY unlock sequence must be executed:

- Write 0x55 to NVMKEY.
- 2. Write 0xAA to NVMKEY.
- 3. Clear (or set) IOLOCK as a single operation.

IOLOCK remains in one state until changed. This allows all of the Peripheral Pin Selects to be configured with a single unlock sequence, followed by an update to all of the control registers. Then, IOLOCK can be set with a second lock sequence.

8.5.4 CONSIDERATIONS FOR PERIPHERAL PIN SELECTION

The ability to control Peripheral Pin Selection introduces several considerations into application design that most users would never think of otherwise. This is particularly true for several common peripherals, which are only available as remappable peripherals.

The main consideration is that the Peripheral Pin Selects are not available on default pins in the device's default (Reset) state. More specifically, because all RPINRx registers reset to '1's and RPORx registers reset to '0's, this means all PPS inputs are tied to Vss, while all PPS outputs are disconnected. This means that before any other application code is executed, the user must initialize the device with the proper peripheral configuration. Because the IOLOCK bit resets in the unlocked state, it is not necessary to execute the unlock sequence after the device has come out of Reset. For application safety, however, it is always better to set IOLOCK and lock the configuration after writing to the control registers.

The NVMKEY unlock sequence must be executed as an Assembly language routine. If the bulk of the application is written in C, or another high-level language, the unlock sequence should be performed by writing in-line assembly or by using the __builtin_write_RPCON(value) function provided by the compiler.

Choosing the configuration requires a review of all Peripheral Pin Selects and their pin assignments, particularly those that will not be used in the application. In all cases, unused pin-selectable peripherals should be disabled completely. Unused peripherals should have their inputs assigned to an unused RPn pin function. I/O pins with unused RPn functions should be configured with the null peripheral output.

Note: MPLAB® XC16 provides a built-in C language function for unlocking and modifying the RPCON register:

__builtin_write_RPCON(value);
For more information, see the "MPLAB® XC16 C Compiler User's Guide" (DS50002071).

8.5.5 INPUT MAPPING

The inputs of the Peripheral Pin Select options are mapped on the basis of the peripheral. That is, a control register associated with a peripheral dictates the pin it will be mapped to. The RPINRx registers are used to configure peripheral input mapping. Each register contains sets of 8-bit fields, with each set associated with one of the remappable peripherals. Programming a given peripheral's bit field with an appropriate 8-bit index value maps the RPn pin with the corresponding value, or internal signal, to that peripheral. See Table 8-4 for a list of available inputs.


For example, Figure 8-2 illustrates remappable pin selection for the U1RX input. Example 8-1 provides a configuration for bidirectional communication with flow control using UART1. The following input and output functions are used:

Input Functions: U1RX, U1CTSOutput Functions: U1TX, U1RTS

EXAMPLE 8-1: CONFIGURING UART1 INPUT AND OUTPUT FUNCTIONS

```
// Unlock Registers
//*********
 builtin write RPCON(0x0000);
//**********
// Configure Input Functions (See Table 8-5)
// Assign U1Rx To Pin RP35
U1RXR = 35;
// Assign U1CTS To Pin RP36
U1CTSR = 36;
//*********
// Configure Output Functions (See Table 8-7)
//**********
// Assign UlTx To Pin RP37
RP37 = 1;
//*******
// Assign U1RTS To Pin RP38
RP38 = 2;
//**********
// Lock Registers
//**********
_builtin_write_RPCON(0x0800);
```

FIGURE 8-2: REMAPPABLE INPUT FOR U1RX



Note: For input only, Peripheral Pin Select functionality does not have priority over TRISx settings. Therefore, when configuring an RPn pin for input, the corresponding bit in the TRISx register must also be configured for input (set to '1'). Physical connection to a pin can be made through RP32 through RP71. There are internal signals and virtual pins that can be connected to an input. Table 8-4 shows the details of the input assignment.

TABLE 8-4: REMAPPABLE PIN INPUTS

RPINRx<15:8> or RPINRx<7:0>	Function	Available on Ports		
0	Vss	Internal		
1	Comparator 1	Internal		
2	Comparator 2	Internal		
3	Comparator 3	Internal		
4-5	RP4-RP5	Reserved		
6	PTG Trigger 26	Internal		
7	PTG Trigger 27	Internal		
8-10	RP8-RP10	Reserved		
11	PWM Event Out C	Internal		
12	PWM Event Out D	Internal		
13	PWM Event Out E	Internal		
14-31	RP14-RP31	Reserved		
32	RP32	Port Pin RB0		
33	RP33	Port Pin RB1		
34	RP34	Port Pin RB2		
35	RP35	Port Pin RB3		
36	RP36	Port Pin RB4		
37	RP37	Port Pin RB5		
38	RP38	Port Pin RB6		
39	RP39	Port Pin RB7		
40	RP40	Port Pin RB8		
41	RP41	Port Pin RB9		
42	RP42	Port Pin RB10		
43	RP43	Port Pin RB11		
44	RP44	Port Pin RB12		
45	RP45	Port Pin RB13		
46	RP46	Port Pin RB14		
47	RP47	Port Pin RB15		
48	RP48	Port Pin RC0		
49	RP49	Port Pin RC1		
50	RP50	Port Pin RC2		
51	RP51	Port Pin RC3		
52	RP52	Port Pin RC4		
53	RP53	Port Pin RC5		
54	RP54	Port Pin RC6		
55	RP55	Port Pin RC7		
56	RP56	Port Pin RC8		
57	RP57	Port Pin RC9		
58	RP58	Port Pin RC10		
59	RP59	Port Pin RC11		
60	RP60	Port Pin RC12		
61	RP61	Port Pin RC12 Port Pin RC13		
62	RP62	Port Pin RC14		

TABLE 8-4: REMAPPABLE PIN INPUTS (CONTINUED)

RPINRx<15:8> or RPINRx<7:0>	Function	Available on Ports		
63	RP63	Port Pin RC15		
64	RP64	Port Pin RD0		
65	RP65	Port Pin RD1		
66	RP66	Port Pin RD2		
67	RP67	Port Pin RD3		
68	RP68	Port Pin RD4		
69	RP69	Port Pin RD5		
70	RP70	Port Pin RD6		
71	RP71	Port Pin RD7		
72	RP72	Port Pin RD8		
73	RP73	Port Pin RD9		
74	RP74	Port Pin RD10		
75	RP75	Port Pin RD11		
76	RP76	Port Pin RD12		
77	RP77	Port Pin RD13		
78	RP78	Port Pin RD14		
79	RP79	Port Pin RD15		
80-175	RP80-RP175	Reserved		
176	RP176	Virtual RPV0		
177	RP177	Virtual RPV1		
178	RP178	Virtual RPV2		
179	RP179	Virtual RPV3		
180	RP180	Virtual RPV4		
181	RP181	Virtual RPV5		

8.5.6 VIRTUAL CONNECTIONS

The dsPIC33CK256MP508 devices support six virtual RPn pins (RP176-RP181), which are identical in functionality to all other RPn pins, with the exception of pinouts. These six pins are internal to the devices and are not connected to a physical device pin.

These pins provide a simple way for inter-peripheral connection without utilizing a physical pin. For example, the output of the analog comparator can be connected to RP176 and the PWM Fault input can be configured for RP176 as well. This configuration allows the analog comparator to trigger PWM Faults without the use of an actual physical pin on the device.

TABLE 8-5: SELECTABLE INPUT SOURCES (MAPS INPUT TO FUNCTION)

Input Name ⁽¹⁾	Function Name	Register	Register Bits
External Interrupt 1	INT1	RPINR0	INT1R<7:0>
External Interrupt 2	INT2	RPINR1	INT2R<7:0>
External Interrupt 3	INT3	RPINR1	INT3R<7:0>
Timer1 External Clock	T1CK	RPINR2	T1CK<7:0>
SCCP Timer1	TCKI1	RPINR3	TCKI1R<7:0>
SCCP Capture 1	ICM1	RPINR3	ICM1R<7:0>
SCCP Timer2	TCKI2	RPINR4	TCKI2R<7:0>
SCCP Capture 2	ICM2	RPINR4	ICM2R<7:0>
SCCP Timer3	TCKI3	RPINR5	TCKI3R<7:0>
SCCP Capture 3	ICM3	RPINR5	ICM3R<7:0>
SCCP Timer4	TCKI4	RPINR6	TCKI4R<7:0>
SCCP Capture 4	ICM4	RPINR6	ICM4R<7:0>
SCCP Timer5	TCKI5	RPINR7	TCKI5R<7:0>
SCCP Capture 5	ICM5	RPINR7	ICM5R<7:0>
SCCP Timer6	TCKI6	RPINR8	TCKI6R<7:0>
SCCP Capture 6	ICM6	RPINR8	ICM6R<7:0>
SCCP Timer7	TCKI7	RPINR9	TCKI7R<7:0>
SCCP Capture 7	ICM7	RPINR9	ICM7R<7:0>
SCCP Timer8	TCKI8	RPINR10	TCKI8R<7:0>
SCCP Capture 8	ICM8	RPINR10	ICM8R<7:0>
CCP Fault A	OCFA	RPINR11	OCFAR<7:0>
CCP Fault B	OCFB	RPINR11	OCFBR<7:0>
PWM PCI 8	PCI8	RPINR12	PCI8R<7:0>
PWM PCI 9	PCI9	RPINR12	PCI9R<7:0>
PWM PCI 10	PCI10	RPINR13	PCI10R<7:0>
PWM PCI 11	PCI11	RPINR13	PCI11R<7:0>
QEI1 Input A	QEIA1	RPINR14	QEIA1R<7:0>
QEI1 Input B	QEIB1	RPINR14	QEIB1R<7:0>
QEI1 Index 1 Input	QEINDX1	RPINR15	QEINDX1R<7:0>
QEI1 Home 1 Input	QEIHOM1	RPINR15	QEIHOM1R<7:0>
QEI2 Input A	QEIA2	RPINR16	QEIA2R<7:0>
QEI2 Input B	QEIB2	RPINR16	QEIB2R<7:0>
QEI2 Index 1 Input	QEINDX2	RPINR17	QEINDX2R<7:0>
QEI2 Home 1 Input	QEIHOM2	RPINR17	QEIHOM2R<7:0>
JART1 Receive	U1RX	RPINR18	U1RXR<7:0>
JART1 Data-Set-Ready	U1DSR	RPINR18	U1DSRR<7:0>
JART2 Receive	U2RX	RPINR19	U2RXR<7:0>
JART2 Data-Set-Ready	U2DSR	RPINR19	U2DSRR<7:0>
SPI1 Data Input	SDI1	RPINR20	SDI1R<7:0>
SPI1 Clock Input	SCK1IN	RPINR20	SCK1R<7:0>
SPI1 Slave Select	SS1	RPINR21	SS1R<7:0>
Reference Clock Input	REFOI	RPINR21	REFOIR<7:0>
SPI2 Data Input	SDI2	RPINR22	SDI2R<7:0>

Note 1: Unless otherwise noted, all inputs use the Schmitt Trigger input buffers.

TABLE 8-5: SELECTABLE INPUT SOURCES (MAPS INPUT TO FUNCTION) (CONTINUED)

Input Name ⁽¹⁾	Function Name	Register	Register Bits
SPI2 Clock Input	SCK2IN	RPINR22	SCK2R<7:0>
SPI2 Slave Select	SS2	RPINR23	SS2R<7:0>
CAN1 Input	CAN1RX	RPINR26	CAN1RXR<7:0>
UART3 Receive	U3RX	RPINR27	U3RXR<7:0>
UART3 Data-Set-Ready	U3DSR	RPINR27	U3DSRR<7:0>
SPI3 Data Input	SDI3	RPINR29	SDI3R<7:0>
SPI3 Clock Input	SCK3IN	RPINR29	SCK3R<7:0>
SPI3 Slave Select	SS3	RPINR30	SS3R<7:0>
MCCP Timer9	TCKI9	RPINR32	TCKI9R<7:0>
MCCP Capture 9	ICM9	RPINR33	ICM9R<7:0>
xCCP Fault C	OCFC	RPINR37	OCFCR<7:0>
PWM Input 17	PCI17	RPINR37	PCI17R<7:0>
PWM Input 18	PCI18	RPINR38	PCI18R<7:0>
PWM Input 12	PCI12	RPINR42	PCI12R<7:0>
PWM Input 13	PCI13	RPINR42	PCI13R<7:0>
PWM Input 14	PCI14	RPINR43	PCI14R<7:0>
PWM Input 15	PCI15	RPINR43	PCI15R<7:0>
PWM Input 16	PCI16	RPINR44	PCI16R<7:0>
SENT1 Input	SENT1	RPINR44	SENT1R<7:0>
SENT2 Input	SENT2	RPINR45	SENT2R<7:0>
CLC Input A	CLCINA	RPINR45	CLCINAR<7:0>
CLC Input B	CLCINB	RPINR46	CLCINBR<7:0>
CLC Input C	CLCINC	RPINR46	CLCINCR<7:0>
CLC Input D	CLCIND	RPINR47	CLCINDR<7:0>
ADC Trigger Input (ADTRIG31)	ADCTRG	RPINR47	ADCTRGR<7:0>
xCCP Fault D	OCFD	RPINR48	OCFDR<7:0>
UART1 Clear-to-Send	U1CTS	RPINR48	U1CTSR<7:0>
UART2 Clear-to-Send	U2CTS	RPINR49	U2CTSR<7:0>
UART3 Clear-to-Send	U3CTS	RPINR49	U3CTSR<7:0>


Note 1: Unless otherwise noted, all inputs use the Schmitt Trigger input buffers.

8.5.7 OUTPUT MAPPING

In contrast to inputs, the outputs of the Peripheral Pin Select options are mapped on the basis of the pin. In this case, a control register associated with a particular pin dictates the peripheral output to be mapped. The RPORx registers are used to control output mapping. Each register contains sets of 6-bit fields, with each set associated with one RPn pin (see Register 8-54 through Register 8-80). The value of the bit field corresponds to one of the peripherals and that peripheral's output is mapped to the pin (see Table 8-7 and Figure 8-3).

A null output is associated with the output register Reset value of '0'. This is done to ensure that remappable outputs remain disconnected from all output pins by default.

FIGURE 8-3: MULTIPLEXING REMAPPABLE OUTPUTS FOR RPn



Note 1: There are 6 virtual output ports which are not connected to any I/O ports (RP176-RP181). These virtual ports can be accessed by RPOR20, RPOR21 and RPOR22.

8.5.8 MAPPING LIMITATIONS

The control schema of the peripheral select pins is not limited to a small range of fixed peripheral configurations. There are no mutual or hardware-enforced lockouts between any of the peripheral mapping SFRs. Literally, any combination of peripheral mappings, across any or all of the RPn pins, is possible. This includes both many-to-one and one-to-many mappings of peripheral inputs, and outputs to pins. While such mappings may be technically possible from a configuration point of view, they may not be supportable from an electrical point of view (see Table 8-6).

TABLE 8-6: REMAPPABLE OUTPUT PIN REGISTERS

Register	RP Pin	I/O Port
RPOR0<5:0>	RP32	Port Pin RB0
RPOR0<13:8>	RP33	Port Pin RB1
RPOR1<5:0>	RP34	Port Pin RB2
RPOR1<13:8>	RP35	Port Pin RB3
RPOR2<5:0>	RP36	Port Pin RB4
RPOR2<13:8>	RP37	Port Pin RB5
RPOR3<5:0>	RP38	Port Pin RB6
RPOR3<13:8>	RP39	Port Pin RB7
RPOR4<5:0>	RP40	Port Pin RB8
RPOR4<13:8>	RP41	Port Pin RB9
RPOR5<5:0>	RP42	Port Pin RB10
RPOR5<13:8>	RP43	Port Pin RB11
RPOR6<5:0>	RP44	Port Pin RB12
RPOR6<13:8>	RP45	Port Pin RB13
RPOR7<5:0>	RP46	Port Pin RB14
RPOR7<13:8>	RP47	Port Pin RB15
RPOR8<5:0>(1)	RP48	Port Pin RC0
RPOR8<13:8> ⁽¹⁾	RP49	Port Pin RC1
RPOR9<5:0>(1)	RP50	Port Pin RC2
RPOR9<13:8> ⁽¹⁾	RP51	Port Pin RC3
RPOR10<5:0> ⁽¹⁾	RP52	Port Pin RC4
RPOR10<13:8>(1)	RP53	Port Pin RC5
RPOR11<5:0> ⁽¹⁾	RP54	Port Pin RC6
RPOR11<13:8> ⁽¹⁾	RP55	Port Pin RC7
RPOR12<5:0> ⁽¹⁾	RP56	Port Pin RC8
RPOR12<13:8>(1)	RP57	Port Pin RC9
RPOR13<5:0> ⁽¹⁾	RP58	Port Pin RC10
RPOR13<13:8> ⁽¹⁾	RP59	Port Pin RC11
RPOR14<5:0> ⁽¹⁾	RP60	Port Pin RC12
RPOR14<13:8> ⁽¹⁾	RP61	Port Pin RC13
RPOR15<5:0> ⁽¹⁾	RP62	Port Pin RC14
RPOR15<13:8> ⁽¹⁾	RP63	Port Pin RC15
RPOR16<5:0> ⁽¹⁾	RP64	Port Pin RD0
RPOR16<13:8> ⁽¹⁾	RP65	Port Pin RD1
RPOR17<5:0> ⁽¹⁾	RP66	Port Pin RD2
RPOR17<13:8> ⁽¹⁾	RP67	Port Pin RD3
RPOR18<5:0> ⁽¹⁾	RP68	Port Pin RD4
RPOR18<13:8>(1)	RP69	Port Pin RD5
RPOR19<5:0> ⁽¹⁾	RP70	Port Pin RD6
RPOR19<13:8>(1)	RP71	Port Pin RD7
RPOR20<5:0> ⁽¹⁾	RP72	Port Pin RD8
RPOR20<13:8>(1)	RP73	Port Pin RD9
RPOR21<5:0> ⁽¹⁾	RP74	Port Pin D10

Note 1: Availability is dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

TABLE 8-6: REMAPPABLE OUTPUT PIN REGISTERS (CONTINUED)

Register	RP Pin	I/O Port
RPOR21<13:8> ⁽¹⁾	RP75	Port Pin RD11
RPOR22<5:0> ⁽¹⁾	RP76	Port Pin RD12
RPOR22<13:8> ⁽¹⁾	RP77	Port Pin RD13
RPOR23<5:0> ⁽¹⁾	RP78	Port Pin RD14
RPOR23<13:8> ⁽¹⁾	RP79	Port Pin RD15
	RP80-RP175	Reserved
RPOR24<5:0>	RP176	Virtual Pin RPV0
RPOR24<13:8>	RP177	Virtual Pin RPV1
RPOR25<5:0>	RP178	Virtual Pin RPV2
RPOR25<13:8>	RP179	Virtual Pin RPV3
RPOR26<5:0>	RP180	Virtual Pin RPV4
RPOR26<13:8>	RP181	Virtual Pin RPV5

Note 1: Availability is dependent on supported I/O ports. Refer to Table 8-1 for availability on package variants.

TABLE 8-7: OUTPUT SELECTION FOR REMAPPABLE PINS (RPn)

Function	RPnR<5:0>	Output Name
Default PORT	000000	RPn tied to Default Pin
U1TX	000001	RPn tied to UART1 Transmit
Ū1RTS	000010	RPn tied to UART1 Request-to-Send
U2TX	000011	RPn tied to UART2 Transmit
U2RTS	000100	RPn tied to UART2 Request-to-Send
SDO1	000101	RPn tied to SPI1 Data Output
SCK1	000110	RPn tied to SPI1 Clock Output
SS1	000111	RPn tied to SPI1 Slave Select
SDO2	001000	RPn tied to SPI2 Data Output
SCK2	001001	RPn tied to SPI2 Clock Output
SS2	001010	RPn tied to SPI2 Slave Select
SDO3	001011	RPn tied to SPI3 Data Output
SCK3	001100	RPn tied to SPI3 Clock Output
SS3	001101	RPn tied to SPI3 Slave Select
REFCLKO	001110	RPn tied to Reference Clock Output
OCM1	001111	RPn tied to SCCP1 Output
OCM2	010000	RPn tied to SCCP2 Output
OCM3	010001	RPn tied to SCCP3 Output
OCM4	010010	RPn tied to SCCP4 Output
OCM5	010011	RPn tied to SCCP5 Output
OCM6	010100	RPn tied to SCCP6 Output
CAN1	010101	RPn tied to CAN1 Output
CMP1	010111	RPn tied to Comparator 1 Output
CMP2	011000	RPn tied to Comparator 2 Output
CMP3	011001	RPn tied to Comparator 3 Output
U3TX	011011	RPn tied to UART3 Transmit
U3RTS	011100	RPn tied to UART3 Request-to-Send
PWM4H	100010	RPn tied to PWM4H Output
PWM4L	100011	RPn tied to PWM4L Output
PWMEA	100100	RPn tied to PWM Event A Output
PWMEB	100101	RPn tied to PWM Event B Output
QEICMP1	100110	RPn tied to QEI1 Comparator Output
QEICMP2	100111	RPn tied to QEI2 Comparator Output
CLC10UT	101000	RPn tied to CLC1 Output
CLC2OUT	101001	RPn tied to CLC2 Output
OCM7	101010	RPn tied to SCCP7 Output
OCM8	101011	RPn tied to SCCP8 Output
PWMEC	101100	RPn tied to PWM Event C Output
PWMED	101101	RPn tied to PWM Event D Output
PTGTRG24	101110	PTG Trigger Output 24
PTGTRG25	101111	PTG Trigger Output 25
SENT1OUT	110000	RPn tied to SENT1 Output
SENT2OUT	110001	RPn tied to SENT2 Output

TABLE 8-7: OUTPUT SELECTION FOR REMAPPABLE PINS (RPn) (CONTINUED)

Function	RPnR<5:0>	Output Name
MCCP9A	110010	RPn tied to MCCP9 Output A
МССР9В	110011	RPn tied to MCCP9 Output B
MCCP9C	110100	RPn tied to MCCP9 Output C
MCCP9D	110101	RPn tied to MCCP9 Output D
MCCP9E	110110	RPn tied to MCCP9 Output E
MCCP9F	110111	RPn tied to MCCP9 Output F
CLC3OUT	111011	RPn tied to CLC4 Output
CLC4OUT	111100	RPn tied to CLC4 Output
U1DTR	111101	RPn tied to UART1 DTR
U2DTR	111110	RPn tied to UART2 DTR
U3DTR	111111	RPn tied to UART3 DTR

8.5.9 I/O HELPFUL TIPS

- 1. In some cases, certain pins, as defined in Table 33-15 under "Injection Current", have internal protection diodes to VDD and Vss. The term, "Injection Current", is also referred to as "Clamp Current". On designated pins, with sufficient external current-limiting precautions by the user, I/O pin input voltages are allowed to be greater or lesser than the data sheet absolute maximum ratings, with respect to the Vss and VDD supplies. Note that when the user application forward biases either of the high or low-side internal input clamp diodes, that the resulting current being injected into the device that is clamped internally by the VDD and Vss power rails, may affect the ADC accuracy by four to six counts.
- 2. I/O pins that are shared with any analog input pin (i.e., ANx) are always analog pins, by default, after any Reset. Consequently, configuring a pin as an analog input pin automatically disables the digital input pin buffer and any attempt to read the digital input level by reading PORTx or LATx will always return a '0', regardless of the digital logic level on the pin. To use a pin as a digital I/O pin on a shared ANx pin, the user application needs to configure the Analog Select for PORTx registers in the I/O ports module (i.e., ANSELx) by setting the appropriate bit that corresponds to that I/O port pin to a '0'.

Note: Although it is not possible to use a digital input pin when its analog function is enabled, it is possible to use the digital I/O output function, TRISx = 0x0, while the analog function is also enabled. However, this is not recommended, particularly if the analog input is connected to an external analog voltage source, which would create signal contention between the analog signal and the output pin driver.

- 3. Most I/O pins have multiple functions. Referring to the device pin diagrams in this data sheet, the priorities of the functions allocated to any pins are indicated by reading the pin name, from left-to-right. The left most function name takes precedence over any function to its right in the naming convention. For example: AN16/T2CK/T7CK/RC1; this indicates that AN16 is the highest priority in this example and will supersede all other functions to its right in the list. Those other functions to its right, even if enabled, would not work as long as any other function to its left was enabled. This rule applies to all of the functions listed for a given pin.
- 4. Each pin has an internal weak pull-up resistor and pull-down resistor that can be configured using the CNPUx and CNPDx registers, respectively. These resistors eliminate the need for external resistors in certain applications. The internal pull-up is up to ~(VDD 0.8), not VDD. This value is still above the minimum VIH of CMOS and TTL devices.
- 5. When driving LEDs directly, the I/O pin can source or sink more current than what is specified in the VoH/IOH and VoL/IOL DC characteristics specification. The respective IOH and IOL current rating only applies to maintaining the corresponding output at or above the VOH, and at or below the VOL levels. However, for LEDs, unlike digital inputs of an externally connected device, they are not governed by the same minimum VIH/VIL levels. An I/O pin output can safely sink or source any current less than that listed in the Absolute Maximum Ratings in Section 33.0 "Electrical Characteristics" of this data sheet. For example:

Voh = 2.4v @ Ioh = -8 mA and Vob = 3.3V The maximum output current sourced by any 8 mA I/O pin = 12 mA.

LED source current < 12 mA is technically permitted.

- The Peripheral Pin Select (PPS) pin mapping rules are as follows:
 - a) Only one "output" function can be active on a given pin at any time, regardless if it is a dedicated or remappable function (one pin, one output).
 - b) It is possible to assign a "remappable output" function to multiple pins and externally short or tie them together for increased current drive.
 - c) If any "dedicated output" function is enabled on a pin, it will take precedence over any remappable "output" function.
 - d) If any "dedicated digital" (input or output) function is enabled on a pin, any number of "input" remappable functions can be mapped to the same pin.
 - e) If any "dedicated analog" function(s) are enabled on a given pin, "digital input(s)" of any kind will all be disabled, although a single "digital output", at the user's cautionary discretion, can be enabled and active as long as there is no signal contention with an external analog input signal. For example, it is possible for the ADC to convert the digital output logic level, or to toggle a digital output on a comparator or ADC input, provided there is no external analog input, such as for a built-in self-test.
 - f) Any number of "input" remappable functions can be mapped to the same pin(s) at the same time, including to any pin with a single output from either a dedicated or remappable "output".
 - g) The TRISx registers control only the digital I/O output buffer. Any other dedicated or remappable active "output" will automatically override the TRISx setting. The TRISx register does not control the digital logic "input" buffer. Remappable digital "inputs" do not automatically override TRISx settings, which means that the TRISx bit must be set to input for pins with only remappable input function(s) assigned.
 - h) All analog pins are enabled by default after any Reset and the corresponding digital input buffer on the pin has been disabled. Only the Analog Select for PORTx (ANSELx) registers control the digital input buffer, *not* the TRISx register. The user must disable the analog function on a pin using the Analog Select for PORTx registers in order to use any "digital input(s)" on a corresponding pin, no exceptions.

8.5.10 I/O PORTS RESOURCES

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

8.5.10.1 Key Resources

- "I/O Ports with Edge Detect" (DS70005322) in the "dsPIC33/PIC24 Family Reference Manual"
- Code Samples
- · Application Notes
- · Software Libraries
- Webinars
- All Related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

TABLE 8-8: PORTA REGISTER SUMMARY

Register	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
ANSELA	I	Ι	I	I	Ι	I	I	I	ı	I	I		Ā	ANSELA<4:0>	_	
TRISA	_	_	_	_	_	1	_	-	_	_	_		-	TRISA<4:0>		
PORTA	_	-	_	1	_	Ι	1	1	1	-	1			RA<4:0>		
LATA	_	-	-	Ι	_	I	1	I	I	I	1			LATA<4:0>		
ODCA	_	_	_	_	_	1	_	-	_	_	_)	ODCA<4:0>		
CNPUA	_	-	_	1	_	Ι	1	1	1	-	1		0	CNPUA<4:0>		
CNPDA	_	-	_	1	_	Ι	1	1	1	1	1		S	CNPDA<4:0>		
CNCONA	NO	_	_	_	CNSTYLE	1	_	-	_	_	-	ı	_	-	-	I
CNEN0A	_	-	_	1	_	Ι	1	1	1	-	1		Ö	CNEN0A<4:0>	_	
CNSTATA	_	-	_	1	_	Ι	1	1	1	1	1		C	CNSTATA<4:0>	Δ	
CNEN1A	1	1		I	1	1	1	1	1	1	1		C	CNEN1A<4:0>	^	
CNFA	Ι	Ι	1	Ι	Ι	Ι	Ι	I	Ι	Ι	1		-	CNFA<4:0>		

ABLE 8-9: PORTB REGISTER SUMMARY

IABLE 8-9:		PORTB REGISTER SUMMARY	SISIER S	UMMAKY												
Register	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
ANSELB	I	I	I	I	I	1	AN	ANSELB<9:7>	۸	I	1		AN	ANSELB<4:0>	<0	
TRISB							TR	TRISB<15:0>								
PORTB							2	RB<15:0>								
LATB							Ā	LATB<15:0>								
ODCB							ОО	ODCB<15:0>								
CNPUB							CNF	CNPUB<15:0>								
CNPDB							CNF	CNPDB<15:0>	_							
CNCONB	NO	I	I	I	CNSTYLE	I	I	ı	I	ı	ı	I	1	I	I	1
CNENOB							CNE	CNEN0<15:0>								
CNSTATB							CNS	CNSTATB<15:0>	^							
CNEN1B							CNE	CNEN1B<15:0>	^							
CNFB							CN	CNFB<15:0>								

SUMMARY
C REGISTER
: PORT
LE 8-10
IAB

יסורט דומרו		LONIO REGISTEN SOMIMANT	֡֝֞֜֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֝֟֓֓֓֓֓֓֓֓֓֓֓	לואוואסס												
Register	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
ANSELC	I	I	I	Ι	I	I	I	I	ANSELC<7:6>	<9:2>	I	I		ANSELC<3:0>	C<3:0>	
TRISC								TRISC<15:0>	5:0>							
PORTC								RC<15:0>	<0							
LATC								LATC<15:0>	2:0>							
ODCC								ODCC<15:0>	5:0>							
CNPUC								CNPUC<15:0>	15:0>							
CNPDC								CNPDC<15:0>	15:0>							
CNCONC	NO	I	I	Ι	CNSTYLE	ı	-	I	1	1	I	I	I	Ι	1	I
CNEN0C)	CNEN0C<15:0>	15:0>							
CNSTATC)	CNSTATC<15:0>	:15:0>							
CNEN1C)	CNEN1C<15:0>	15:0>							
CNFC								CNFC<15:0>	2:0>							
																Ī

TABLE 8-11: PORTD REGISTER SUMMARY

						•	•				•		•	•	•	
Register	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
ANSELD	I	Ι	ANSELD<13>	I	ANSELD<11:10>	<11:10>	I	I	I	I	1	I	I	I	I	I
TRISD							TRISE	TRISD<15:0>								
PORTD							RD*	RD<15:0>								
LATD							LATE	LATD<15:0>								
ОДС							ODCE	ODCD<15:0>								
CNPUD							CNPU	CNPUD<15:0>								
CNPDD							CNPD	CNPDD<15:0>								
CNCOND	NO	Ι	I	_	CNSTYLE	_	Ι	Ι	I	1	Ι	1	I	Ι	_	I
CNENOD							CNENC	CNEN0D<15:0>								
CNSTATD							CNSTA	CNSTATD<15:0>								
CNEN1D							CNEN	CNEN1D<15:0>								
CNFD							CNFL	CNFD<15:0>								

Bit 0 Bit 1 Bit 2 Bit 3 Bit 4 Bit 5 Bit 6 Bit 7 CNSTATE<15:0> CNEN0E<15:0> CNEN1E<15:0> CNPUE<15:0> CNPDE<15:0> TRISE<15:0> ODCE<15:0> CNFE<15:0> LATE<15:0> RE<15:0> Bit 8 Bit 9 Bit 10 CNSTYLE Bit 11 PORTE REGISTER SUMMARY Bit 12 Bit 13 Bit 14 Bit 15 N O **FABLE 8-12:** CNSTATE CNCONE Register **CNEN1E CNEN0E** CNPUE CNPDE ANSLE PORTE TRISE ODCE CNFE LATE

8.5.11 PERIPHERAL PIN SELECT REGISTERS

REGISTER 8-13: RPCON: PERIPHERAL REMAPPING CONFIGURATION REGISTER⁽¹⁾

U-0	U-0	U-0	U-0	R/W-0	U-0	U-0	U-0
_	_	_	_	IOLOCK	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 Unimplemented: Read as '0'

bit 11 IOLOCK: Peripheral Remapping Register Lock bit

1 = All Peripheral Remapping registers are locked and cannot be written 0 = All Peripheral Remapping registers are unlocked and can be written

bit 10-0 Unimplemented: Read as '0'

Note 1: Writing to this register needs an unlock sequence (see Section 8.5.3 "Controlling Configuration Changes").

REGISTER 8-14: RPINRO: PERIPHERAL PIN SELECT INPUT REGISTER

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| INT1R7 | INT1R6 | INT1R5 | INT1R4 | INT1R3 | INT1R2 | INT1R1 | INT1R0 |
| bit 15 | | | | | | | bit 8 |

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 INT1R<7:0>: Assign External Interrupt 1 (INT1) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 **Unimplemented:** Read as '0'

REGISTER 8-15: RPINR1: PERIPHERAL PIN SELECT INPUT REGISTER 1

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| INT3R7 | INT3R6 | INT3R5 | INT3R4 | INT3R3 | INT3R2 | INT3R1 | INT3R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| INT2R7 | INT2R6 | INT2R5 | INT2R4 | INT2R3 | INT2R2 | INT2R1 | INT2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 INT3R<7:0>: Assign External Interrupt 3 (INT3) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 INT2R<7:0>: Assign External Interrupt 2 (INT2) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-16: RPINR2: PERIPHERAL PIN SELECT INPUT REGISTER 2

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| T1CKR7 | T1CKR6 | T1CKR5 | T1CKR4 | T1CKR3 | T1CKR2 | T1CKR1 | T1CKR0 |
| bit 15 | | | | | | | bit 8 |

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 T1CKR<7:0>: Assign Timer1 External Clock (T1CK) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 **Unimplemented:** Read as '0'

REGISTER 8-17: RPINR3: PERIPHERAL PIN SELECT INPUT REGISTER 3

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM1R7 | ICM1R6 | ICM1R5 | ICM1R4 | ICM1R3 | ICM1R2 | ICM1R1 | ICM1R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI1R7 | TCKI1R6 | TCKI1R5 | TCKI1R4 | TCKI1R3 | TCKI1R2 | TCKI1R1 | TCKI1R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM1R<7:0>: Assign SCCP Capture 1 (ICM1) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI1<7:0>: Assign SCCP Timer1 (TCKI1) Input to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-18: RPINR4: PERIPHERAL PIN SELECT INPUT REGISTER 4

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM2R7 | ICM2R6 | ICM2R5 | ICM2R4 | ICM2R3 | ICM2R2 | ICM2R1 | ICM2R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI2R7 | TCKI2R6 | TCKI2R5 | TCKI2R4 | TCKI2R3 | TCKI2R2 | TCKI2R1 | TCKI2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM2R<7:0>: Assign SCCP Capture 2 (ICM2) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI2R<7:0>: Assign SCCP Timer2 (TCKI2) Input to the Corresponding RPn Pin bits

REGISTER 8-19: RPINR5: PERIPHERAL PIN SELECT INPUT REGISTER 5

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM3R7 | ICM3R6 | ICM3R5 | ICM3R4 | ICM3R3 | ICM3R2 | ICM3R1 | ICM3R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI3R7 | TCKI3R6 | TCKI3R5 | TCKI3R4 | TCKI3R3 | TCKI3R2 | TCKI3R1 | TCKI3R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM3R<7:0>: Assign SCCP Capture 3 (ICM3) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI3R<7:0>: Assign SCCP Timer3 (TCKI3) Input to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-20: RPINR6: PERIPHERAL PIN SELECT INPUT REGISTER 6

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM4R7 | ICM4R6 | ICM4R5 | ICM4R4 | ICM4R3 | ICM4R2 | ICM4R1 | ICM4R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI4R7 | TCKI4R6 | TCKI4R5 | TCKI4R4 | TCKI4R3 | TCKI4R2 | TCKI4R1 | TCKI4R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM4R<7:0>: Assign SCCP Capture 4 (ICM4) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI4R<7:0>: Assign SCCP Timer4 (TCKI4) Input to the Corresponding RPn Pin bits

REGISTER 8-21: RPINR7: PERIPHERAL PIN SELECT INPUT REGISTER 7

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM5R7 | ICM5R6 | ICM5R5 | ICM5R4 | ICM5R3 | ICM5R2 | ICM5R1 | ICM5R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI5R7 | TCKI5R6 | TCKI5R5 | TCKI5R4 | TCKI5R3 | TCKI5R2 | TCKI5R1 | TCKI5R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM5R<7:0>: Assign SCCP Capture 5 (ICM5) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI5R<7:0>: Assign SCCP Timer5 (TCKI5) Input to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-22: RPINR8: PERIPHERAL PIN SELECT INPUT REGISTER 8

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM6R7 | ICM6R6 | ICM6R5 | ICM6R4 | ICM6R3 | ICM6R2 | ICM6R1 | ICM6R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI6R7 | TCKI6R6 | TCKI6R5 | TCKI6R4 | TCKI6R3 | TCKI6R2 | TCKI6R1 | TCKI6R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM6R<7:0>: Assign SCCP Capture 6 (ICM6) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI6R<7:0>: Assign SCCP Timer6 (TCKI6) Input to the Corresponding RPn Pin bits

REGISTER 8-23: RPINR9: PERIPHERAL PIN SELECT INPUT REGISTER 9

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM7R7 | ICM7R6 | ICM7R5 | ICM7R4 | ICM7R3 | ICM7R2 | ICM7R1 | ICM7R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI7R7 | TCKI7R6 | TCKI7R5 | TCKI7R4 | TCKI7R3 | TCKI7R2 | TCKI7R1 | TCKI7R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM7R<7:0>: Assign SCCP Capture 7 (ICM7) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI7R<7:0>: Assign SCCP Timer7 (TCKI7) Input to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-24: RPINR10: PERIPHERAL PIN SELECT INPUT REGISTER 10

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM8R7 | ICM8R6 | ICM8R5 | ICM8R4 | ICM8R3 | ICM8R2 | ICM8R1 | ICM8R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI8R7 | TCKI8R6 | TCKI8R5 | TCKI8R4 | TCKI8R3 | TCKI8R2 | TCKI8R1 | TCKI8R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ICM8R<7:0>: Assign SCCP Capture 8 (ICM8) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 TCKI8R<7:0>: Assign SCCP Timer8 (TCKI8) Input to the Corresponding RPn Pin bits

REGISTER 8-25: RPINR11: PERIPHERAL PIN SELECT INPUT REGISTER 11

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| OCFBR7 | OCFBR6 | OCFBR5 | OCFBR4 | OCFBR3 | OCFBR2 | OCFBR1 | OCFBR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| OCFAR7 | OCFAR6 | OCFAR5 | OCFAR4 | OCFAR3 | OCFAR2 | OCFAR1 | OCFAR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 OCFBR<7:0>: Assign SCCP Fault B (OCFB) Input to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 OCFAR<7:0>: Assign SCCP Fault A (OCFA) Input to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-26: RPINR12: PERIPHERAL PIN SELECT INPUT REGISTER 12

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| PCI9R7 | PCI9R6 | PCI9R5 | PCI9R4 | PCI9R3 | PCI9R2 | PCI9R1 | PCI9R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| PCI8R7 | PCI8R6 | PCI8R5 | PCI8R4 | PCI8R3 | PCI8R2 | PCI8R1 | PCI8R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 PCI9R<7:0>: Assign PWM Input 9 (PCI9) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 PCI8R<7:0>: Assign PWM Input 8 (PCI8) to the Corresponding RPn Pin bits

REGISTER 8-27: RPINR13: PERIPHERAL PIN SELECT INPUT REGISTER 13

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI11R7 | PCI11R6 | PCI11R5 | PCI11R4 | PCI11R3 | PCI11R2 | PCI11R1 | PCI11R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI10R7 | PCI10R6 | PCI10R5 | PCI10R4 | PCI10R3 | PCI10R2 | PCI10R1 | PCI10R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 PCI11R<7:0>: Assign PWM Input 11 (PCI11) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 PCI10R<7:0>: Assign PWM Input 10 (PCI10) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-28: RPINR14: PERIPHERAL PIN SELECT INPUT REGISTER 14

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| QEIB1R7 | QEIB1R6 | QEIB1R5 | QEIB1R4 | QEIB1R3 | QEIB1R2 | QEIB1R1 | QEIB1R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| QEIA1R7 | QEIA1R6 | QEIA1R5 | QEIA1R4 | QEIA1R3 | QEIA1R2 | QEIA1R1 | QEIA1R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 QEIB1R<7:0>: Assign QEI1 Input B (QEIB1) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 QEIA1R<7:0>: Assign QEI1 Input A (QEIA1) to the Corresponding RPn Pin bits

REGISTER 8-29: RPINR15: PERIPHERAL PIN SELECT INPUT REGISTER 15

| R/W-0 |
|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| QEIHOM1R7 | QEIHOM1R6 | QEIHOM1R5 | QEIHOM1R4 | QEIHOM1R3 | QEIHOM1R2 | QEIHOM1R1 | QEIHOM1R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| QEINDX1R7 | QEINDX1R6 | QEINDX1R5 | QEINDX1R4 | QEINDX1R3 | QEINDX1R2 | QEINDX1R1 | QEINDX1R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 QEIHOM1R<7:0>: Assign QEI Home 1 Input (QEIHOM1) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 QEINDX1R<7:0>: Assign QEI Index 1 Input (QEINDX1) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-30: RPINR16: PERIPHERAL PIN SELECT INPUT REGISTER 16

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| QEIB2R7 | QEIB2R6 | QEIB2R5 | QEIB2R4 | QEIB2R3 | QEIB2R2 | QEIB2R1 | QEIB2R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| QEIA2R7 | QEIA2R6 | QEIA2R5 | QEIA2R4 | QEIA2R3 | QEIA2R2 | QEIA2R1 | QEIA2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 QEIB2R<7:0>: Assign QEI2 Input B (QEIB2) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 QEIA2R<7:0>: Assign QEI2 Input A (QEIA2) to the Corresponding RPn Pin bits

REGISTER 8-31: RPINR17: PERIPHERAL PIN SELECT INPUT REGISTER 17

	R/W-0							
ĺ	QEIHOM2R7	QEIHOM2R6	QEIHOM2R5	QEIHOM2R4	QEIHOM2R3	QEIHOM2R2	QEIHOM2R1	QEIHOM2R0
ĺ	bit 15							bit 8

| R/W-0 |
|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| QEINDX2R7 | QEINDX2R6 | QEINDX2R5 | QEINDX2R4 | QEINDX2R3 | QEINDX2R2 | QEINDX2R1 | QEINDX2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 QEIHOM2R<7:0>: Assign QEI Home 2 Input (QEIHOM2) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 QEINDX2R<7:0>: Assign QEI Index 2 Input (QEINDX2) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-32: RPINR18: PERIPHERAL PIN SELECT INPUT REGISTER 18

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U1DSRR7 | U1DSRR6 | U1DSRR5 | U1DSRR4 | U1DSRR3 | U1DSRR2 | U1DSRR1 | U1DSRR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| U1RXR7 | U1RXR6 | U1RXR5 | U1RXR4 | U1RXR3 | U1RXR2 | U1RXR1 | U1RXR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 U1DSRR<7:0>: Assign UART1 Data-Set-Ready (U1DSR) to the Corresponding RPn Pin bits

See Table 8-4

bit 7-0 U1RXR<7:0>: Assign UART1 Receive (U1RX) to the Corresponding RPn Pin bits

REGISTER 8-33: RPINR19: PERIPHERAL PIN SELECT INPUT REGISTER 19

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U2DSRR7 | U2DSRR6 | U2DSRR5 | U2DSRR4 | U2DSRR3 | U2DSRR2 | U2DSRR1 | U2DSRR0 |
| bit 15 | • | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| U2RXR7 | U2RXR6 | U2RXR5 | U2RXR4 | U2RXR3 | U2RXR2 | U2RXR1 | U2RXR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **U2DSRR<7:0>:** Assign UART2 Data-Set-Ready (U2DSR) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 U2RXR<7:0>: Assign UART2 Receive (U2RX) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-34: RPINR20: PERIPHERAL PIN SELECT INPUT REGISTER 20

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SCK1R7 | SCK1R6 | SCK1R5 | SCK1R4 | SCK1R3 | SCK1R2 | SCK1R1 | SCK1R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SDI1R7 | SDI1R6 | SDI1R5 | SDI1R4 | SDI1R3 | SDI1R2 | SDI1R1 | SDI1R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 SCK1R<7:0>: Assign SPI1 Clock Input (SCK1IN) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 SDI1R<7:0>: Assign SPI1 Data Input (SDI1) to the Corresponding RPn Pin bits

REGISTER 8-35: RPINR21: PERIPHERAL PIN SELECT INPUT REGISTER 21

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| REFOIR7 | REFOIR6 | REFOIR5 | REFOIR4 | REFOIR3 | REFOIR2 | REFOIR1 | REFOIR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| SS1R7 | SS1R6 | SS1R5 | SS1R4 | SS1R3 | SS1R2 | SS1R1 | SS1R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 REFOIR<7:0>: Assign Reference Clock Input (REFOI) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 SS1R<7:0>: Assign SPI1 Slave Select (SS1) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-36: RPINR22: PERIPHERAL PIN SELECT INPUT REGISTER 22

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SCK2R7 | SCK2R6 | SCK2R5 | SCK2R4 | SCK2R3 | SCK2R2 | SCK2R1 | SCK2R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SDI2R7 | SDI2R6 | SDI2R5 | SDI2R4 | SDI2R3 | SDI2R2 | SDI2R1 | SDI2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 SCK2R<7:0>: Assign SPI2 Clock Input (SCK2IN) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 SDI2R<7:0>: Assign SPI2 Data Input (SDI2) to the Corresponding RPn Pin bits

REGISTER 8-37: RPINR23: PERIPHERAL PIN SELECT INPUT REGISTER 23

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| SS2R7 | SS2R6 | SS2R5 | SS2R4 | SS2R3 | SS2R2 | SS2R1 | SS2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 SS2R<7:0>: Assign SPI2 Slave Select (SS2) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-38: RPINR26: PERIPHERAL PIN SELECT INPUT REGISTER 26

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| CAN1RXR7 | CAN1RXR6 | CAN1RXR5 | CAN1RXR4 | CAN1RXR3 | CAN1RXR2 | CAN1RXR1 | CAN1RXR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 CAN1RXR<7:0>: Assign CAN1 Input (CAN1RX) to the Corresponding RPn Pin bits

REGISTER 8-39: RPINR27: PERIPHERAL PIN SELECT INPUT REGISTER 27

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U3DSRR7 | U3DSRR6 | U3DSRR5 | U3DSRR4 | U3DSRR3 | U3DSRR2 | U3DSRR1 | U3DSRR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| U3RXR7 | U3RXR6 | U3RXR5 | U3RXR4 | U3RXR3 | U3RXR2 | U3RXR1 | U3RXR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **U3DSRR<7:0>:** Assign UART3 Data-Set-Ready (U3DSR) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 U3RXR<7:0>: Assign UART3 Receive (U3RX) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-40: RPINR29: PERIPHERAL PIN SELECT INPUT REGISTER 29

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SCK3R7 | SCK3R6 | SCK3R5 | SCK3R4 | SCK3R3 | SCK3R2 | SCK3R1 | SCK3R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| SDI3R7 | SDI3R6 | SDI3R5 | SDI3R4 | SDI3R3 | SDI3R2 | SDI3R1 | SDI3R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 SCK3R<7:0>: Assign SPI3 Clock Input (SCK3IN) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 SDI3R<7:0>: Assign SPI3 Data Input (SDI3) to the Corresponding RPn Pin bits

REGISTER 8-41: RPINR30: PERIPHERAL PIN SELECT INPUT REGISTER 30

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| SS3R7 | SS3R6 | SS3R5 | SS3R4 | SS3R3 | SS3R2 | SS3R1 | SS3R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 SS3R<7:0>: Assign SPI3 Slave Select (SS2) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-42: RPINR32: PERIPHERAL PIN SELECT INPUT REGISTER 32

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| TCKI9R7 | TCKI9R6 | TCKI9R5 | TCKI9R4 | TCKI9R3 | TCKI9R2 | TCKI9R1 | TCKI9R0 |
| bit 15 | | | | | | | bit 8 |

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **TCKI9R<7:0>:** Assign MCCP Timer9 Input (TCKI9) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 **Unimplemented:** Read as '0'

REGISTER 8-43: RPINR33: PERIPHERAL PIN SELECT INPUT REGISTER 33

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| ICM9R7 | ICM9R6 | ICM9R5 | ICM9R4 | ICM9R3 | ICM9R2 | ICM9R1 | ICM9R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 ICM9R<7:0>: Assign MCCP Capture 9 Input (ICM9) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-44: RPINR37: PERIPHERAL PIN SELECT INPUT REGISTER 37

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI17R7 | PCI17R6 | PCI17R5 | PCI17R4 | PCI17R3 | PCI17R2 | PCI17R1 | PCI17R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| OCFCR7 | OCFCR6 | OCFCR5 | OCFCR4 | OCFCR3 | OCFCR2 | OCFCR1 | OCFCR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 PCI17R<7:0>: Assign PWM Input 17 (PCI17) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 OCFCR<7:0>: Assign xCCP Fault C (OCFC) to the Corresponding RPn Pin bits

REGISTER 8-45: RPINR38: PERIPHERAL PIN SELECT INPUT REGISTER 38

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI18R7 | PCI18R6 | PCI18R5 | PCI18R4 | PCI18R3 | PCI18R2 | PCI18R1 | PCI18R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 PCI17R<7:0>: Assign PWM Input 17 (PCI17) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-46: RPINR42: PERIPHERAL PIN SELECT INPUT REGISTER 42

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI13R7 | PCI13R6 | PCI13R5 | PCI13R4 | PCI13R3 | PCI13R2 | PCI13R1 | PCI13R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI12R7 | PCI12R6 | PCI12R5 | PCI12R4 | PCI12R3 | PCI12R2 | PCI12R1 | PCI12R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 PCI13R<7:0>: Assign PWM Input 13 (PCI13) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 PCI12R<7:0>: Assign PWM Input 12 (PCI12) to the Corresponding RPn Pin bits

REGISTER 8-47: RPINR43: PERIPHERAL PIN SELECT INPUT REGISTER 43

ſ	R/W-0							
ſ	PCI15R7	PCI15R6	PCI15R5	PCI15R4	PCI15R3	PCI15R2	PCI15R1	PCI15R0
Ī	bit 15							bit 8

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI14R7 | PCI14R6 | PCI14R5 | PCI14R4 | PCI14R3 | PCI14R2 | PCI14R1 | PCI14R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 PCI15R<7:0>: Assign PWM Input 15 (PCI15) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 PCI14R<7:0>: Assign PWM Input 14 (PCI14) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-48: RPINR44: PERIPHERAL PIN SELECT INPUT REGISTER 44

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| SENT1R7 | SENT1R6 | SENT1R5 | SENT1R4 | SENT1R3 | SENT1R2 | SENT1R1 | SENT1R0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PCI16R7 | PCI16R6 | PCI16R5 | PCI16R4 | PCI16R3 | PCI16R2 | PCI16R1 | PCI16R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 SENT1R<7:0>: Assign SENT1 Input (SENT1) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 PCI16<7:0>: Assign PWM Input 16 (PCI16) to the Corresponding RPn Pin bits

REGISTER 8-49: RPINR45: PERIPHERAL PIN SELECT INPUT REGISTER 45

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| CLCINAR7 | CLCINAR6 | CLCINAR5 | CLCINAR4 | CLCINAR3 | CLCINAR2 | CLCINAR1 | CLCINAR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| SENT2R7 | SENT2R6 | SENT2R5 | SENT2R4 | SENT2R3 | SENT2R2 | SENT2R1 | SENT2R0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 CLCINAR<7:0>: Assign CLC Input A (CLCINA) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 SENT2R<7:0>: Assign SENT2 Input (SENT2) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-50: RPINR46: PERIPHERAL PIN SELECT INPUT REGISTER 46

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| CLCINCR7 | CLCINCR6 | CLCINCR5 | CLCINCR4 | CLCINCR3 | CLCINCR2 | CLCINCR1 | CLCINCR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| CLCINBR7 | CLCINBR6 | CLCINBR5 | CLCINBR4 | CLCINBR3 | CLCINBR2 | CLCINBR1 | CLCINBR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 CLCINCR<7:0>: Assign CLC Input C (CLCINC) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 CLCINBR<7:0>: Assign CLC Input B (CLCINB) to the Corresponding RPn Pin bits

REGISTER 8-51: RPINR47: PERIPHERAL PIN SELECT INPUT REGISTER 47

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| ADCTRGR7 | ADCTRGR6 | ADCTRGR5 | ADCTRGR4 | ADCTRGR3 | ADCTRGR2 | ADCTRGR1 | ADCTRGR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| CLCINDR7 | CLCINDR6 | CLCINDR5 | CLCINDR4 | CLCINDR3 | CLCINDR2 | CLCINDR1 | CLCINDR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 ADCTRGR<7:0>: Assign ADC Trigger Input (ADCTRG) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 CLCINDR<7:0>: Assign CLC Input D (CLCIND) to the Corresponding RPn Pin bits

See Table 8-4.

REGISTER 8-52: RPINR48: PERIPHERAL PIN SELECT INPUT REGISTER 48

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U1CTSR7 | U1CTSR6 | U1CTSR5 | U1CTSR4 | U1CTSR3 | U1CTSR2 | U1CTSR1 | U1CTSR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| OCFDR7 | OCFDR6 | OCFDR5 | OCFDR4 | OCFDR3 | OCFDR2 | OCFDR1 | OCFDR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **U1CTSR<7:0>:** Assign UART1 Clear-to-Send (U1CTS) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 OCFDR<7:0>: Assign xCCP Fault D (OCFD) to the Corresponding RPn Pin bits

REGISTER 8-53: RPINR49: PERIPHERAL PIN SELECT INPUT REGISTER 49

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U3CTSR7 | U3CTSR6 | U3CTSR5 | U3CTSR4 | U3CTSR3 | U3CTSR2 | U3CTSR1 | U3CTSR0 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| U2CTSR7 | U2CTSR6 | U2CTSR5 | U2CTSR4 | U2CTSR3 | U2CTSR2 | U2CTSR1 | U2CTSR0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **U3CTSR<7:0>:** Assign UART3 Clear-to-Send (U3CTS) to the Corresponding RPn Pin bits

See Table 8-4.

bit 7-0 **U2CTSR<7:0>:** Assign UART2 Clear-to-Send (U2CTS) to the Corresponding RPn Pin bits

REGISTER 8-54: RPOR0: PERIPHERAL PIN SELECT OUTPUT REGISTER 0

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP33R5	RP33R4	RP33R3	RP33R2	RP33R1	RP33R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP32R5	RP32R4	RP32R3	RP32R2	RP32R1	RP32R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP33R<5:0>: Peripheral Output Function is Assigned to RP33 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP32R<5:0>: Peripheral Output Function is Assigned to RP32 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-55: RPOR1: PERIPHERAL PIN SELECT OUTPUT REGISTER 1

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP35R5	RP35R4	RP35R3	RP35R2	RP35R1	RP35R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP34R5	RP34R4	RP34R3	RP34R2	RP34R1	RP34R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP35R<5:0>: Peripheral Output Function is Assigned to RP35 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP34R<5:0>: Peripheral Output Function is Assigned to RP34 Output Pin bits

REGISTER 8-56: RPOR2: PERIPHERAL PIN SELECT OUTPUT REGISTER 2

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP37R5	RP37R4	RP37R3	RP37R2	RP37R1	RP37R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP36R5	RP36R4	RP36R3	RP36R2	RP36R1	RP36R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP37R<5:0>: Peripheral Output Function is Assigned to RP37 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP36R<5:0>: Peripheral Output Function is Assigned to RP36 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-57: RPOR3: PERIPHERAL PIN SELECT OUTPUT REGISTER 3

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP39R5	RP39R4	RP39R3	RP39R2	RP39R1	RP39R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP38R5	RP38R5	RP38R5	RP38R5	RP38R5	RP38R5
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP39R<5:0>: Peripheral Output Function is Assigned to RP39 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP38R<5:0>: Peripheral Output Function is Assigned to RP38 Output Pin bits

REGISTER 8-58: RPOR4: PERIPHERAL PIN SELECT OUTPUT REGISTER 4

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP41R5	RP41R4	RP41R3	RP41R2	RP41R1	RP41R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP40R5	RP40R4	RP40R3	RP40R2	RP40R1	RP40R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP41R<5:0>: Peripheral Output Function is Assigned to RP41 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP40R<5:0>: Peripheral Output Function is Assigned to RP40 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-59: RPOR5: PERIPHERAL PIN SELECT OUTPUT REGISTER 5

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP43R5	RP43R4	RP43R3	RP43R2	RP43R1	RP43R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP42R5	RP42R4	RP42R3	RP42R2	RP42R1	RP42R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP43R<5:0>: Peripheral Output Function is Assigned to RP43 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP42R<5:0>: Peripheral Output Function is Assigned to RP42 Output Pin bits

REGISTER 8-60: RPOR6: PERIPHERAL PIN SELECT OUTPUT REGISTER 6

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP45R5	RP45R4	RP45R3	RP45R2	RP45R1	RP45R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP44R5	RP44R4	RP44R3	RP44R2	RP44R1	RP44R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP45R<5:0>: Peripheral Output Function is Assigned to RP45 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP44R<5:0>: Peripheral Output Function is Assigned to RP44 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-61: RPOR7: PERIPHERAL PIN SELECT OUTPUT REGISTER 7

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP47R5	RP47R4	RP47R3	RP47R2	RP47R1	RP47R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP46R5	RP46R4	RP46R3	RP46R2	RP46R1	RP46R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP47R<5:0>: Peripheral Output Function is Assigned to RP47 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP46R<5:0>: Peripheral Output Function is Assigned to RP46 Output Pin bits

REGISTER 8-62: RPOR8: PERIPHERAL PIN SELECT OUTPUT REGISTER 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP49R5	RP49R4	RP49R3	RP49R2	RP49R1	RP49R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP48R5	RP48R4	RP48R3	RP48R2	RP48R1	RP48R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP49R<5:0>: Peripheral Output Function is Assigned to RP49 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 Unimplemented: Read as '0'

bit 5-0 RP48R<5:0>: Peripheral Output Function is Assigned to RP48 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-63: RPOR9: PERIPHERAL PIN SELECT OUTPUT REGISTER 9

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP51R5	RP51R4	RP51R3	RP51R2	RP51R1	RP51R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP50R5	RP50R4	RP50R3	RP50R2	RP50R1	RP50R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP51R<5:0>: Peripheral Output Function is Assigned to RP51 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP50R<5:0>: Peripheral Output Function is Assigned to RP50 Output Pin bits

REGISTER 8-64: RPOR10: PERIPHERAL PIN SELECT OUTPUT REGISTER 10

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP53R5	RP53R4	RP53R3	RP53R2	RP53R1	RP53R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP52R5	RP52R4	RP52R3	RP52R2	RP52R1	RP52R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP53<5:0>: Peripheral Output Function is Assigned to RP53 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP52R<5:0>: Peripheral Output Function is Assigned to RP52 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-65: RPOR11: PERIPHERAL PIN SELECT OUTPUT REGISTER 11

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP55R5	RP55R4	RP55R3	RP55R2	RP55R1	RP55R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP54R5	RP54R4	RP54R3	RP54R2	RP54R1	RP54R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP55R<5:0>: Peripheral Output Function is Assigned to RP55 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP54R<5:0>: Peripheral Output Function is Assigned to RP54 Output Pin bits

REGISTER 8-66: RPOR12: PERIPHERAL PIN SELECT OUTPUT REGISTER 12

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP57R5	RP57R4	RP57R3	RP57R2	RP57R1	RP57R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP56R5	RP56R4	RP56R3	RP56R2	RP56R1	RP56R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP57R<5:0>: Peripheral Output Function is Assigned to RP57 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP56R<5:0>: Peripheral Output Function is Assigned to RP56 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-67: RPOR13: PERIPHERAL PIN SELECT OUTPUT REGISTER 13

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP59R5	RP59R4	RP59R3	RP59R2	RP59R1	RP59R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP58R5	RP58R4	RP58R3	RP58R2	RP58R1	RP58R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP59R<5:0>: Peripheral Output Function is Assigned to RP59 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP58R<5:0>: Peripheral Output Function is Assigned to RP58 Output Pin bits

REGISTER 8-68: RPOR14: PERIPHERAL PIN SELECT OUTPUT REGISTER 14

	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
Ī	_	_	RP61R5	RP61R4	RP61R3	RP61R2	RP61R1	RP61R0
Ī	bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP60R5	RP60R4	RP60R3	RP60R2	RP60R1	RP60R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP61R<5:0>: Peripheral Output Function is Assigned to RP61 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP60R<5:0>: Peripheral Output Function is Assigned to RP60 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-69: RPOR15: PERIPHERAL PIN SELECT OUTPUT REGISTER 15

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP63R5	RP63R4	RP63R3	RP63R2	RP63R1	RP63R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP62R5	RP62R4	RP62R3	RP62R2	RP62R1	RP62R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP63R<5:0>: Peripheral Output Function is Assigned to RP63 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP62R<5:0>: Peripheral Output Function is Assigned to RP62 Output Pin bits

REGISTER 8-70: RPOR16: PERIPHERAL PIN SELECT OUTPUT REGISTER 16

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP65R5	RP65R4	RP65R3	RP65R2	RP65R1	RP65R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP64R5	RP64R4	RP64R3	RP64R2	RP64R1	RP64R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP65R<5:0>: Peripheral Output Function is Assigned to RP65 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP64R<5:0>: Peripheral Output Function is Assigned to RP64 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-71: RPOR17: PERIPHERAL PIN SELECT OUTPUT REGISTER 17

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP67R5	RP67R4	RP67R3	RP67R2	RP67R1	RP67R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP66R5	RP66R4	RP66R3	RP66R2	RP66R1	RP66R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP67R<5:0>: Peripheral Output Function is Assigned to RP67 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP66R<5:0>: Peripheral Output Function is Assigned to RP66 Output Pin bits

REGISTER 8-72: RPOR18: PERIPHERAL PIN SELECT OUTPUT REGISTER 18

	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ſ	_	_	RP69R5	RP69R4	RP69R3	RP69R2	RP69R1	RP69R0
Γ	bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP68R5	RP68R4	RP68R3	RP68R2	RP68R1	RP68R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP69R<5:0>: Peripheral Output Function is Assigned to RP69 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP68R<5:0>: Peripheral Output Function is Assigned to RP68 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-73: RPOR19: PERIPHERAL PIN SELECT OUTPUT REGISTER 19

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP71R5	RP71R4	RP71R3	RP71R2	RP71R1	RP71R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP70R5	RP70R4	RP70R3	RP70R2	RP70R1	RP70R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 **RP71R<5:0>:** Peripheral Output Function is Assigned to RP71 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 Unimplemented: Read as '0'

bit 5-0 RP70R<5:0>: Peripheral Output Function is Assigned to RP70 Output Pin bits

REGISTER 8-74: RPOR20: PERIPHERAL PIN SELECT OUTPUT REGISTER 20

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP73R5	RP73R4	RP73R3	RP73R2	RP73R1	RP73R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP72R5	RP72R4	RP72R3	RP72R2	RP72R1	RP72R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP73R<5:0>: Peripheral Output Function is Assigned to RP73 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP72R<5:0>: Peripheral Output Function is Assigned to RP72 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-75: RPOR21: PERIPHERAL PIN SELECT OUTPUT REGISTER 21

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP75R5	RP75R4	RP75R3	RP75R2	RP75R1	RP75R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP74R5	RP74R4	RP74R3	RP74R2	RP74R1	RP74R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP75R<5:0>: Peripheral Output Function is Assigned to RP75 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 Unimplemented: Read as '0'

bit 5-0 RP74R<5:0>: Peripheral Output Function is Assigned to RP74 Output Pin bits

REGISTER 8-76: RPOR22: PERIPHERAL PIN SELECT OUTPUT REGISTER 22

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP77R5	RP77R4	RP77R3	RP77R2	RP77R1	RP77R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP76R5	RP76R4	RP76R3	RP76R2	RP76R1	RP76R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP77R<5:0>: Peripheral Output Function is Assigned to RP77 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP76R<5:0>: Peripheral Output Function is Assigned to RP76 Output Pin bits

(see Table 8-7 for peripheral function numbers)

REGISTER 8-77: RPOR23: PERIPHERAL PIN SELECT OUTPUT REGISTER 23

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP79R5	RP79R4	RP79R3	RP79R2	RP79R1	RP79R0
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP78R5	RP78R4	RP78R3	RP78R2	RP78R1	RP78R0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 RP79R<5:0>: Peripheral Output Function is Assigned to RP79 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 Unimplemented: Read as '0'

bit 5-0 RP78R<5:0>: Peripheral Output Function is Assigned to RP78 Output Pin bits

REGISTER 8-78: RPOR24: PERIPHERAL PIN SELECT OUTPUT REGISTER 24

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP177R5 ⁽¹⁾	RP177R4 ⁽¹⁾	RP177R3 ⁽¹⁾	RP177R2 ⁽¹⁾	RP177R1 ⁽¹⁾	RP177R0 ⁽¹⁾
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP176R5 ⁽¹⁾	RP176R4 ⁽¹⁾	RP176R3 ⁽¹⁾	RP176R2 ⁽¹⁾	RP176R1 ⁽¹⁾	RP176R0 ⁽¹⁾
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP177R<5:0>: Peripheral Output Function is Assigned to RP177 Output Pin bits⁽¹⁾

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP176R<5:0>: Peripheral Output Function is Assigned to RP176 Output Pin bits⁽¹⁾

(see Table 8-7 for peripheral function numbers)

Note 1: These are virtual output ports.

REGISTER 8-79: RPOR25: PERIPHERAL PIN SELECT OUTPUT REGISTER 25

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP179R5 ⁽¹⁾	RP179R4 ⁽¹⁾	RP179R3 ⁽¹⁾	RP179R2 ⁽¹⁾	RP179R1 ⁽¹⁾	RP179R0 ⁽¹⁾
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP178R5 ⁽¹⁾	RP178R4 ⁽¹⁾	RP178R3 ⁽¹⁾	RP178R2 ⁽¹⁾	RP178R1 ⁽¹⁾	RP178R0 ⁽¹⁾
bit 7 bit 0							

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-8 **RP179R<5:0>:** Peripheral Output Function is Assigned to RP179 Output Pin bits⁽¹⁾

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 **RP178R<5:0>:** Peripheral Output Function is Assigned to RP178 Output Pin bits⁽¹⁾

(see Table 8-7 for peripheral function numbers)

Note 1: These are virtual output ports.

REGISTER 8-80: RPOR26: PERIPHERAL PIN SELECT OUTPUT REGISTER 26

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP181R5 ⁽¹⁾	RP181R4 ⁽¹⁾	RP181R3 ⁽¹⁾	RP181R2 ⁽¹⁾	RP181R1 ⁽¹⁾	RP181R0 ⁽¹⁾
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	RP180R5 ⁽¹⁾	RP180R4 ⁽¹⁾	RP180R3 ⁽¹⁾	RP180R2 ⁽¹⁾	RP180R1 ⁽¹⁾	RP180R0 ⁽¹⁾
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 RP181R<5:0>: Peripheral Output Function is Assigned to RP181 Output Pin bits

(see Table 8-7 for peripheral function numbers)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 RP180R<5:0>: Peripheral Output Function is Assigned to RP180 Output Pin bits

(see Table 8-7 for peripheral function numbers)

Note 1: These are virtual output ports.

TABLE 8-13: PPS INPUT CONTROL REGISTERS

RPCON —	-	-	_	IOLOCK	-	1	-	_	_	1	1	-	-	_	-
RPINR0 INT1R7	INT1R6	INT1R5	INT1R4	INT1R3	INT1R2	INT1R1	INT1R0	Ι	Ι	Ι	Ι	Ι	1	1	1
RPINR1 INT3R7	INT3R6	INT3R5	INT3R4	INT3R3	INT3R2	INT3R1	INT3R0	INT2R7	INT2R6	INT2R5	INT2R4	INT2R3	INT2R2	INT2R1	INT2R0
RPINR2 T1CKR7	T1CKR6	T1CKR5	T1CKR4	T1CKR3	T1CKR2	T1CKR1	T1CKR0	I	I	I	I	Ι	I	1	1
RPINR3 ICM1R7	ICM1R6	ICM1R5	ICM1R4	ICM1R3	ICM1R2	ICM1R1	ICM1R0	TCKI1R7	TCKI1R6	TCK11R5	TCK11R4	TCK11R3	TCKI1R2	TCKI1R1	TCKI1R0
RPINR4 ICM2R7	ICM2R6	ICM2R5	ICM2R4	ICM2R3	ICM2R2	ICM2R1	ICM2R0	TCKI2R7	TCK12R6	TCKI2R5	TCKI2R4	TCKI2R3	TCKI2R2	TCKI2R1	TCKI2R0
RPINR5 ICM3R7	ICM3R6	ICM3R5	ICM3R4	ICM3R3	ICM3R2	ICM3R1	ICM3R0	TCKI3R7	TCKI3R6	TCKI3R5	TCKI3R4	TCKI3R3	TCKI3R2	TCKI3R1	TCKI3R0
RPINR6 ICM4R7	ICM4R6	ICM4R5	ICM4R4	ICM4R3	ICM4R2	ICM4R1	ICM4R0	TCKI4R7	TCKI4R	TCKI4R5	TCKI4R4	TCKI4R3	TCKI4R2	TCKI4R1	TCKI4R0
RPINR7 ICM5R7	ICM5R6	ICM5R5	ICM5R4	ICM5R3	ICM5R2	ICM5R1	ICM5R0	TCKI5R7	TCKI5R6	TCKI5R5	TCKI5R4	TCKI5R3	TCKI5R2	TCKI5R1	TCKI5R0
RPINR8 ICM6R7	ICM6R6	ICM6R5	ICM6R4	ICM6R3	ICM6R2	ICM6R1	ICM6R0	TCKI6R7	TCKI6R6	TCKI6R5	TCKI6R4	TCKI6R3	TCKI6R2	TCKI6R1	TCKI6R0
RPINR9 ICM7R7	ICM7R6	ICM7R5	ICM7R4	ICM7R3	ICM7R2	ICM7R1	ICM7R0	TCKI7R7	TCKI7R6	TCKI7R5	TCKI7R4	TCKI7R3	TCKI7R2	TCKI7R1	TCKI7R0
RPINR10 ICM8R7	ICM8R6	ICM8R5	ICM8R4	ICM8R3	ICM8R2	ICM8R1	ICM8R0	TCKI8R7	TCK18R6	TCKI8R5	TCKI8R4	TCK18R3	TCKI8R2	TCKI8R1	TCKI8R0
RPINR11 OCFBR7	OCFBR6	OCFBR5	OCFBR4	OCFBR3	OCFBR2	OCFBR1	OCFBR0	OCFAR7	OCFAR6	OCFAR5	OCFAR4	OCFAR3	OCFAR2	OCFAR1	OCFAR0
RPINR12 PCI9R7	PC19R6	PC19R5	PCI9R4	PC19R3	PCI9R2	PCI9R1	PCI9R0	PCI8R7	PCI8R6	PCI8R5	PCI8R4	PCI8R3	PCI8R2	PCI8R1	PCI8R0
RPINR13 PCI11R7	PCI11R6	PCI11R5	PCI11R4	PCI11R3	PCI11R2	PCI11R1	PCI11R0	PCI10R7	PCI10R6	PCI10R5	PCI10R4	PCI10R3	PCI10R2	PCI10R1	PCI10R0
RPINR14 QEIB1R7	QEIB1R6	QEIB1R5	QEIB1R4	QEIB1R3	QEIB1R2	QEIB1R1	QEIB1R0	QEIA1R7	QEIA1R6	QEIA1R5	QEIA1R4	QEIA1R3	QEIA1R2	QEIA1R1	QEIA1R0
RPINR15 QEIHOM1R7	7 QEIHOM1R6	QEIHOM1R5	QEIHOM1R4	QEIHOM1R3	QEIHOM1R2	QEIHOM1R1	QEIHOM1R0	QEINDX1R7	QEINDX1R6	QEINDX1R5	QEINDX1R4	QEINDX1R3	QEINDX1R2	QEINDX1R1	QEINDX1R0
RPINR16 QEIB2R7	QEIB2R6	QEIB2R5	QEIB2R4	QEIB2R3	QEIB2R2	QEIB2R1	QEIB2R0	QEIA2R7	QEIA2R6	QEIA2R5	QEIA2R4	QEIA2R3	QEIA2R2	QEIA2R1	QEIA2R0
RPINR17 QEIHOM2R7	QEIHOM2R6	QEIHOM2R5	QEIHOM2R4	QEIHOM2R3	QEIHOM2R2	QEIHOM2R1	QEIHOM2R0	QEINDX2R7	QEINDX2R6	QEINDX2R5	QEINDX2R4	QEINDX2R3	QEINDX2R2	QEINDX2R1	QEINDX2R0
RPINR18 U1DSRR7	. U1DSRR6	U1DSRR5	U1DSRR4	U1DSRR3	U1DSRR2	U1DSRR1	U1DSRR0	U1RXR7	U1RXR6	U1RXR5	U1RXR4	U1RXR3	U1RXR2	U1RXR1	U1RXR0
RPINR19 U2DSRR7	. U2DSRR6	U2DSRR5	U2DSRR4	U2DSRR3	U2DSRR2	U2DSRR1	UZDSRR0	U2RXR7	U2RXR6	U2RXR5	U2RXR4	U2RXR3	U2RXR2	U2RXR1	U2RXR0
RPINR20 SCK1R7	SCK1R6	SCK1R5	SCK1R4	SCK1R3	SCK1R2	SCK1R1	SCK1R0	SDI1R7	SDI1R6	SD11R5	SDI1R4	SDI1R3	SDI1R2	SDI1R1	SD11R0
RPINR21 REFOIR7	REFOIR6	REFOIRS	REFOIR4	REFOIR3	REFOIR2	REFOIR1	REFOIR0	SS1R7	SS1R6	SS1R5	SS1R4	SS1R3	SS1R2	SS1R1	SS1R0
RPINR22 SCK2R7	SCK2R6	SCK2R5	SCK2R4	SCK2R3	SCK2R2	SCK2R1	SCK2R0	SDI2R7	SDI2R6	SDI2R5	SDI2R4	SDI2R3	SDI2R2	SDI2R1	SDI2R0
RPINR23 —	I	Ι	I	Ι	I	1	1	SS2R7	SS2R6	SS2R5	SS2R4	SS2R3	SS2R2	SS2R1	SS2R0
RPINR26 —	1	-	I	Ι	I	1	1	CAN1RXR7	CAN1RXR6	CAN1RXR5	CAN1RXR4	CAN1RXR3	CAN1RXR2	CAN1RXR1	CAN1RXR0
RPINR27 U3DSRR7	U3DSRR6	U3DSRR5	U3DSRR4	U3DSRR3	U3DSRR2	U3DSRR1	U3DSRR0	U3RXR7	U3RXR6	U3RXR5	U3RXR4	U3RXR3	U3RXR2	U3RXR1	U3RXR0
RPINR29 SCK3R7	SCK3R6	SCK3R5	SCK3R4	SCK3R3	SCK3R2	SCK3R1	SCK3R0	SDI3R7	SDI3R6	SD13R5	SDI3R4	SDI3R3	SDI3R2	SDI3R1	SDI3R0
RPINR30 —	1	_	-	-	1	1	1	SS3R7	SS3R6	SS3R5	SS3R4	SS3R3	SS3R2	SS3R1	SS3R0
RPINR32 TCKI9R7	TCKI9R6	TCK19R5	TCKI9R4	TCK19R3	TCKI9R2	TCKI9R1	TCK19R0	Ι	Ι	Ι	Ι	Ι	1	1	1
RPINR33 —	1	_	-	-	1	1	1	ICM9R7	ICM9R6	ICM9R5	ICM9R4	ICM9R3	ICM9R2	ICM9R1	ICM9R0
RPINR37 PC117R7	PCI17R6	PCI17R5	PCI17R4	PCI17R3	PCI17R2	PCI17R1	PCI17R0	OCFCR7	OCFCR6	OCFCR5	OCFCR4	OCFCR3	OCFCR2	OCFCR1	OCFCR0
RPINR38 —	1	1	I	Ι	1	1	1	PCI18R7	PCI18R6	PCI18R5	PCI18R4	PCI18R3	PCI18R2	PCI18R1	PCI18R0
RPINR42 PCI13R7	PCI13R6	PCI13R5	PC113R4	PCI13R3	PCI13R2	PC113R1	PC113R0	PC112R7	PCI12R6	PCI12R5	PC112R4	PCI12R3	PCI12R2	PCI12R1	PCI12R0
RPINR43 PCI15R7	PCI15R6	PCI15R5	PCI15R4	PCI15R3	PCI15R2	PCI15R1	PCI15R0	PCI14R7	PCI14R6	PCI14R5	PC114R4	PCI14R3	PCI14R2	PCI14R1	PCI14R0
RPINR44 SENT1R7	SENT1R6	SENT1R5	SENT1R4	SENT1R3	SENT1R2	SENT1R1	SENT1R0	PCI16R7	PCI16R6	PCI16R5	PCI16R4	PCI16R3	PCI16R2	PCI16R1	PCI16R0
RPINR45 CLCINAR7	7 CLCINAR6	CLCINAR5	CLCINAR4	CLCINAR3	CLCINAR2	CLCINAR1	CLCINAR0	SENT2R7	SENT2R6	SENT2R5	SENT2R4	SENT2R3	SENT2R2	SENT2R1	SENT2R0
RPINR46 CLCINCR7	' CLCINCR6	CLCINCR5	CLCINCR4	CLCINCR3	CLCINCR2	CLCINCR1	CLCINCR0	CLCINBR7	CLCINBR6	CLCINBR5	CLCINBR4	CLCINBR3	CLCINBR2	CLCINBR1	CLCINBR0
RPINR47 ADCTRGR7	7 ADCTRGR6	ADCTRGR5	ADCTRGR4	ADCTRGR3	ADCTRGR2	ADCTRGR1	ADCTRGR0	CLCINDR7	CLCINDR6	CLCINDR5	CLCINDR4	CLCINDR3	CLCINDR2	CLCINDR1	CLCINDR0
Н	Н	U1CTSR5	U1CTSR4	U1CTSR3	U1CTSR2	U1CTSR1	U1CTSR0	OCFDR7	OCFDR6	OCFDR5	OCFDR4	OCFDR3	OCFDR2	OCFDR1	OCFDR0
DDINIDAG 113CTCD7	OFOTO														

TABLE 8-14: PPS OUTPUT CONTROL REGISTERS

Bit 15 Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
	RP33R5	RP33R4	RP33R3	RP33R2	RP33R1	RP33R0	I	I	RP32R5	RP32R4	RP32R3	RP32R2	RP32R1	RP32R0
	RP35R5	RP35R4	RP35R3	RP35R2	RP35R1	RP35R0	Ι	Ι	RP34R5	RP34R4	RP34R3	RP34R2	RP34R1	RP34R0
	RP37R5	RP37R4	RP37R3	RP37R2	RP37R1	RP37R0	Ι	Ι	RP36R5	RP36R4	RP36R3	RP36R2	RP36R1	RP36R0
	RP39R5	RP39R4	RP39R3	RP39R2	RP39R1	0A6E4A	Ι	Ι	RP38R5	RP38R4	RP38R3	RP38R2	RP38R1	RP38R0
	RP41R5	RP41R4	RP41R3	RP41R2	RP41R1	RP41R0	Ι	1	RP40R5	RP40R4	RP40R3	RP40R2	RP40R1	RP40R0
	RP43R5	RP43R4	RP43R3	RP43R2	RP43R1	RP43R0	1	1	RP42R5	RP42R4	RP42R3	RP42R2	RP42R1	RP42R0
	RP45R5	RP45R4	RP45R3	RP45R2	RP45R1	RP45R0	Ι	Ι	RP44R5	RP44R4	RP44R3	RP44R2	RP44R1	RP44R0
	RP47R5	RP47R4	RP47R3	RP47R2	RP47R1	RP47R0	Ι	Ι	RP46R5	RP46R4	RP46R3	RP46R2	RP46R1	RP46R0
	RP49R5	RP49R4	RP49R3	RP49R2	RP49R1	RP49R0	1	1	RP48R5	RP48R4	RP48R3	RP48R2	RP48R1	RP48R0
	RP51R5	RP51R4	RP51R3	RP51R2	RP51R1	RP51R0	1	1	RP50R5	RP50R4	RP50R3	RP50R2	RP50R1	RP50R0
	RP53R5	RP53R4	RP53R3	RP53R2	RP53R1	RP53R0	Ι	1	RP52R5	RP52R4	RP52R3	RP52R2	RP52R1	RP52R0
	RP55R5	RP55R4	RP55R3	RP55R2	RP55R1	RP55R0	1	1	RP54R5	RP54R4	RP54R3	RP54R2	RP54R1	RP54R0
1	RP57R5	RP57R4	RP57R3	RP57R2	RP57R1	RP57R0	1	1	RP56R5	RP56R4	RP56R3	RP56R2	RP56R1	RP56R0
ı	RP59R5	RP59R4	RP59R3	RP59R2	RP59R1	0A654A	1	1	RP58R5	RP58R4	RP58R3	RP58R2	RP58R1	RP58R0
	RP61R5	RP61R4	RP61R3	RP61R2	RP61R1	RP61R0	_	_	RP60R5	RP60R4	RP60R3	RP60R2	RP60R1	RP60R0
	RP63R5	RP63R4	RP63R3	RP63R2	RP63R1	RP63R0	_	_	RP62R5	RP62R4	RP62R3	RP62R2	RP62R1	RP62R0
	RP65R5	RP65R4	RP65R3	RP65R2	RP65R1	RP65R0	_	_	RP64R5	RP64R4	RP64R3	RP64R2	RP64R1	RP64R0
1	RP67R5	RP67R4	RP67R3	RP67R2	RP67R1	RP67R0	1	1	RP66R5	RP66R4	RP66R3	RP66R2	RP66R1	RP66R0
1	RP69R5	RP69R4	RP69R3	RP69R2	RP69R1	0X694X	Ι	Ι	RP68R5	RP68R4	RP68R3	RP68R2	RP68R1	RP68R0
1	RP71R5	RP71R4	RP71R3	RP71R2	RP71R1	RP71R0	Ι	Ι	RP70R5	RP70R4	RP70R3	RP70R2	RP70R1	RP70R0
-	RP73R5	RP73R4	RP73R3	RP73R2	RP73R1	RP73R0	_	_	RP72R5	RP72R4	RP72R3	RP72R2	RP72R1	RP72R0
ı	RP75R5	RP75R4	RP75R3	RP75R2	RP75R1	RP75R0	Ι	Ι	RP74R5	RP74R4	RP74R3	RP74R2	RP74R1	RP74R0
1	RP77R5	RP77R4	RP77R3	RP77R2	RP77R1	RP77R0	Ι	Ι	RP76R5	RP76R4	RP76R3	RP76R2	RP76R1	RP76R0
ı	RP79R5	RP79R4	RP79R3	RP79R2	RP79R1	0A674A	1	1	RP78R5	RP78R4	RP78R3	RP78R2	RP78R1	RP78R0
	RP177R5	RP177R4	RP177R3	RP177R2	RP177R1	RP177R0	_	_	RP176R5	RP176R4	RP176R3	RP176R2	RP176R1	RP176R0
-	RP179R5	RP179R4	RP179R3	RP179R2	RP179R1	RP179R0	_	_	RP178R5	RP178R4	RP178R3	RP178R2	RP178R1	RP178R0
1	RP181R5	RP181R4	RP181R3	RP181R2	RP181R1	RP181R0	_	_	RP180R5	RP180R4	RP180R3	RP180R2	RP180R1	RP180R0

Note 1: Availability is dependent on supported I/O ports. Refer to Table 8-1 and Table 8-6 for availability on package variants.

9.0 OSCILLATOR WITH HIGH-FREQUENCY PLL

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Oscillator Module with High-Speed PLL" (www.microchip.com/DS70005255) in the "dsPIC33/PIC24 Family Reference Manual".

The dsPIC33CK256MP508 family oscillator with high-frequency PLL includes these characteristics:

- On-Chip Phase-Locked Loop (PLL) to Boost Internal Operating Frequency on Select Internal and External Oscillator Sources
- Auxiliary PLL (APLL) Clock Generator to Boost Operating Frequency for Peripherals
- Doze mode for System Power Savings
- Scalable Reference Clock Output (REFCLKO)
- On-the-Fly Clock Switching between Various Clock Sources
- Fail-Safe Clock Monitoring (FSCM) that Detects Clock Failure and Permits Safe Application Recovery or Shutdown

A block diagram of the dsPIC33CK256MP508 oscillator system is shown in Figure 9-1.





FIGURE 9-1: dsPIC33CK256MP508 CORE CLOCK SOURCES BLOCK DIAGRAM




The Primary Oscillator and internal FRC Oscillator sources can optionally use an on-chip PLL to obtain higher operating speeds. Figure 9-3 illustrates a block diagram of the PLL module.

For PLL operation, the following requirements must be met at all times without exception:

- The PLL Input Frequency (FPLLI) must be in the range of 8 MHz to 64 MHz
- The PFD Input Frequency (FPFD) must be in the range of 8 MHz to (Fvco/16) MHz

The VCO Output Frequency (Fvco) must be in the range of 400 MHz to 1600 MHz

FIGURE 9-3: PLL AND VCO DETAIL



Equation 9-1 provides the relationship between the PLL Input Frequency (FPLLI) and VCO Output Frequency (FVCO).

EQUATION 9-1: Fyco CALCULATION

$$FVCO = FPLLI \times \left(\frac{M}{N1}\right) = FPLLI \times \left(\frac{PLLFBDIV < 7:0>}{PLLPRE < 3:0>}\right)$$

Equation 9-2 provides the relationship between the PLL Input Frequency (FPLLI) and PLL Output Frequency (FPLLO).

EQUATION 9-2: FPLLO CALCULATION

```
FPLLO = FPLLI \times \left(\frac{M}{N1 \times N2 \times N3}\right) = FPLLI \times \left(\frac{PLLFBDIV < 7:0>}{PLLPRE < 3:0> \times POSTIDIV < 2:0> \times POST2DIV < 2:0>}\right) Where: M = PLLFBDIV < 7:0> N1 = PLLPRE < 3:0> N2 = POST1DIV < 2:0> N3 = POST2DIV < 2:0>
```

Note: The PLL Phase Detector Input Divider Select (PLLPREx) bits and the PLL Feedback Divider (PLLFBDIVx) bits should not be changed when operating in PLL mode. Therefore, the user must start in either a non-PLL mode or clock switch to a non-PLL mode (e.g., internal FRC Oscillator) to make any necessary changes and then clock switch to the desired PLL mode.

It is not permitted to directly clock switch from one PLL clock source to a different PLL clock source. The user would need to transition between PLL clock sources with a clock switch to a non-PLL clock source.

EXAMPLE 9-1: CODE EXAMPLE FOR USING PRIMARY PLL WITH 8 MHz INTERNAL FRC


```
//code example for 50 MIPS system clock using 8MHz FRC
// Select FRC on POR
#pragma config FNOSC = FRC
                              // Oscillator Source Selection (Internal Fast RC (FRC))
#pragma config IESO = OFF
// Enable Clock Switching
#pragma config FCKSM = CSECMD
int
    main()
// Configure PLL prescaler, both PLL postscalers, and PLL feedback divider
CLKDIVbits.PLLPRE = 1; // N1=1
PLLFBDbits.PLLFBDIV = 125;
                              // M = 125
PLLDIVbits.POST1DIV = 5;
                              // N2=5
PLLDIVbits.POST2DIV = 1;
                              // N3=1
// Initiate Clock Switch to FRC with PLL (NOSC=0b001)
 builtin write OSCCONH(0x01);
 builtin write OSCCONL(OSCCON | 0x01);
while (OSCCONbits.OSWEN!= 0);
```

The dsPIC33CK256MP508 device family implements an Auxiliary PLL (APLL) module, which is used to generate various peripheral clock sources independent of the system clock. Figure 9-4 shows a block diagram of the APLL module.

For APLL operation, the following requirements must be met at all times without exception:

- The APLL Input Frequency (AFPLLI) must be in the range of 8 MHz to 64 MHz
- The APFD Input Frequency (AFPFD) must be in the range of 8 MHz to (AFVCO/16) MHz
- The AVCO Output Frequency (AFvco) must be in the range of 400 MHz to 1600 MHz

FIGURE 9-4: APLL AND VCO DETAIL



Equation 9-3 provides the relationship between the APLL Input Frequency (AFPLLI) and the AVCO Output Frequency (AFVCO).

EQUATION 9-3: AFVCO CALCULATION

$$AFVCO = AFPLLI \times \left(\frac{M}{N!}\right) = AFPLLI \times \left(\frac{APLLFBDIV < 7:0>}{APLLPRE < 3:0>}\right)$$

Equation 9-4 provides the relationship between the APLL Input Frequency (AFPLLI) and APLL Output Frequency (AFPLLO).

EQUATION 9-4: AFPLLO CALCULATION

$$AFPLLO = AFPLLI \times \left(\frac{M}{N1 \times N2 \times N3}\right) = AFPLLI \times \left(\frac{APLLFBDIV < 7:0>}{APLLPRE < 3:0> \times APOSTIDIV < 2:0> \times APOST2DIV < 2:0>}\right)$$
 Where:
$$M = APLLFBDIV < 7:0>$$

$$N1 = APLLPRE < 3:0>$$

$$N2 = APOST1DIV < 2:0>$$

$$N3 = APOST2DIV < 2:0>$$

EXAMPLE 9-2: CODE EXAMPLE FOR USING AUXILIARY PLL WITH THE INTERNAL FRC OSCILLATOR

Note: Even with the APLLEN bit set, another peripheral must generate a clock request before the APLL will start.

9.1 CPU Clocking


The dsPIC33CK256MP508 devices can be configured to use any of the following clock configurations:

- Primary Oscillator (POSC) on the OSCI and OSCO pins
- Internal Fast RC Oscillator (FRC) with optional clock divider
- Internal Low-Power RC Oscillator (LPRC)
- Primary Oscillator with PLL (ECPLL, HSPLL, XTPLL)
- Internal Fast RC Oscillator with PLL (FRCPLL)
- Backup Internal Fast RC Oscillator (BFRC)

The system clock source is divided by two to produce the internal instruction cycle clock. In this document, the instruction cycle clock is denoted by Fcy. The timing diagram in Figure 9-5 illustrates the relationship between the system clock (Fosc), the instruction cycle clock (Fcy) and the Program Counter (PC).

The internal instruction cycle clock (FCY) can be output on the OSCO I/O pin if the Primary Oscillator mode (POSCMD<1:0>) is not configured as HS/XT. For more information, see Section 9.0 "Oscillator with High-Frequency PLL".





9.2 Primary Oscillator (POSC)

The dsPIC33CK256MP508 family devices feature a Primary Oscillator (POSC) and it is available on the OSCI and OSCO pins. This connection enables an external crystal (or ceramic resonator) to provide the clock to the device. The Primary Oscillator provides three modes of operation:

- Medium Speed Oscillator (XT Mode):
 The XT mode is a Medium Gain, Medium Frequency mode used to work with crystal frequencies of 3.5 MHz to 10 MHz.
- High-Speed Oscillator (HS Mode):
 The HS mode is a High-Gain, High-Frequency mode used to work with crystal frequencies of 10 MHz to 32 MHz.
- External Clock Source Operation (EC Mode):
 If the on-chip oscillator is not used, the EC mode allows the internal oscillator to be bypassed. The device clocks are generated from an external source (0 MHz to up to 64 MHz) and input on the OSCI pin.

9.3 Internal Fast RC (FRC) Oscillator

The dsPIC33CK256MP508 family devices contain one instance of the internal Fast RC (FRC) Oscillator and it provides a nominal 8 MHz clock without requiring an external crystal or ceramic resonator, which results in system cost savings for applications that do not require a precise clock reference.

The application software can tune the frequency of the oscillator using the FRC Oscillator Tuning bits (TUN<5:0>) in the FRC Oscillator Tuning register (OSCTUN<5:0>).

9.4 Low-Power RC (LPRC) Oscillator

The dsPIC33CK256MP508 family devices contain one instance of the Low-Power RC (LPRC) Oscillator and it provides a nominal clock frequency of 32 kHz, and is the clock source for the Power-up Timer (PWRT), Watchdog Timer (WDT) and Fail-Safe Clock Monitor (FSCM) circuits in the clock subsystem.

The LPRC Oscillator is the clock source for the PWRT, WDT and FSCM. The LPRC Oscillator is enabled at power-on.

The LPRC Oscillator remains enabled under these conditions:

- · The FSCM is enabled
- · The WDT is enabled
- The LPRC Oscillator is selected as the system clock

If none of these conditions is true, the LPRC Oscillator shuts off after the PWRT expires. The LPRC Oscillator is shut off in Sleep mode.

Example 9-3 illustrates code for using the PLL (50 MIPS) with the Primary Oscillator.

EXAMPLE 9-3: CODE EXAMPLE FOR USING PLL (50 MIPS) WITH PRIMARY OSCILLATOR (POSC)

```
//code example for 50 MIPS system clock using POSC with 10 MHz external crystal
// Select FRC on POR
#pragma config FNOSC = FRC
                                   // Oscillator Source Selection (Internal Fast RC (FRC))
#pragma config IESO = OFF
/// Enable Clock Switching and Configure POSC in XT mode
#pragma config POSCMD = XT
#pragma config FCKSM = CSECMD
int
       main()
       // Configure PLL prescaler, both PLL postscalers, and PLL feedback divider
       CLKDIVbits.PLLPRE = 1; // N1=1
       PLLFBDbits.PLLFBDIV = 100; // M = 100
       PLLDIVbits.POST1DIV = 5; // N2=5
       PLLDIVbits.POST2DIV = 1;
                                   // N3=1
      // Initiate Clock Switch to Primary Oscillator with PLL (NOSC=0b011)
       __builtin_write_OSCCONH(0x03);
       _builtin_write_OSCCONL(OSCCON | 0x01);
       // Wait for Clock switch to occur
       while (OSCCONbits.OSWEN!= 0);
       // Wait for PLL to lock
       while (OSCCONbits.LOCK!= 1);
```

9.5 Oscillator Configuration

The oscillator system has both Configuration registers and SFRs to configure, control and monitor the system. The FOSCSEL and FOSC Configuration registers (Register 30-4 and Register 30-5, respectively) are used for initial setup.

Table 9-1 lists the configuration settings that select the device's oscillator source and operating mode at a Power-on Reset (POR).

TABLE 9-1: CONFIGURATION BIT VALUES FOR CLOCK SELECTION

Oscillator Source	Oscillator Mode	FNOSC<2:0> Value	POSCMD<1:0> Value	Notes
S0	Fast RC Oscillator (FRC)	000	XX	1
S1	Fast RC Oscillator with PLL (FRCPLL)	001	xx	1
S2	Primary Oscillator (EC)	010	00	1
S2	Primary Oscillator (XT)	010	01	
S2	Primary Oscillator (HS)	010	10	
S3	Primary Oscillator with PLL (ECPLL)	011	00	1
S3	Primary Oscillator with PLL (XTPLL)	011	01	
S3	Primary Oscillator with PLL (HSPLL)	011	10	
S4	Reserved	100	XX	
S5	Low-Power RC Oscillator (LPRC)	101	XX	1
S6	Backup FRC (BFRC)	110	XX	1
S7	Fast RC Oscillator with ÷ N Divider (FRCDIVN)	111	XX	1, 2

Note 1: The OSCO pin function is determined by the OSCIOFNC Configuration bit.

2: This is the default oscillator mode for an unprogrammed (erased) device.

9.6 OSCCON Unlock Sequence

The OSCCON register is protected against unintended writes through a lock mechanism. The upper and lower bytes of OSCCON have their own unlock sequence, and both must be used when writing to both bytes of the register.

Before OSCCON can be written to, the following unlock sequence must be used:

 Execute the unlock sequence for the OSCCON high byte.

In two back-to-back instructions:

- Write 0x78 to OSCCON<15:8>
- Write 0x9A to OSCCON<15:8>
- In the instruction immediately following the unlock sequence, the OSCCON<10:8> bits can be modified.

Execute the unlock sequence for the OSCCON low byte.

In two back-to-back instructions:

- Write 0x46 to OSCCON<7:0>
- Write 0x57 to OSCCON<7:0>
- In the instruction immediately following the unlock sequence, the OSCCON<7:0> bits can be modified.

Note: MPLAB® XC16 provides built-in C language function for unlocking the OSCCON register:

__builtin_write_OSCCONH(value)
__builtin_write_OSCCONL(OSCCON | value)
For more information, see the "MPLAB® XC16 C Compiler User's Guide" (DS50002071).

9.7 Oscillator Control Registers

REGISTER 9-1: OSCCON: OSCILLATOR CONTROL REGISTER⁽¹⁾

U-0	R-0	R-0	R-0	U-0	R/W-y	R/W-y	R/W-y
_	COSC2	COSC1	COSC0	_	NOSC2 ⁽²⁾	NOSC1 ⁽²⁾	NOSCO ⁽²⁾
bit 15							bit 8

R/W-0	U-0	R-0	U-0	R/W-0	U-0	U-0	R/W-0
CLKLOCK	_	LOCK	_	CF ⁽³⁾	_	_	OSWEN
bit 7							bit 0

 Legend:
 y = Value set from Configuration bits on POR

 R = Readable bit
 W = Writable bit
 U = Unimplemented bit, read as '0'

 -n = Value at POR
 '1' = Bit is set
 '0' = Bit is cleared
 x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-12 **COSC<2:0>:** Current Oscillator Selection bits (read-only)

111 = Fast RC Oscillator (FRC) with Divide-by-n (FRCDIVN)

110 = Backup FRC (BFRC)

101 = Low-Power RC Oscillator (LPRC)

100 = Reserved - default to FRC

011 = Primary Oscillator (XT, HS, EC) with PLL (XTPLL, HSPLL, ECPLL)

010 = Primary Oscillator (XT, HS, EC)

001 = Fast RC Oscillator (FRC) with PLL (FRCPLL)

000 = Fast RC Oscillator (FRC)

bit 11 **Unimplemented:** Read as '0'

bit 10-8 NOSC<2:0>: New Oscillator Selection bits⁽²⁾

111 = Fast RC Oscillator (FRC) with Divide-by-n (FRCDIVN)

110 = Backup FRC (BFRC)

101 = Low-Power RC Oscillator (LPRC)

100 = Reserved - default to FRC

011 = Primary Oscillator (XT, HS, EC) with PLL (XTPLL, HSPLL, ECPLL)

010 = Primary Oscillator (XT, HS, EC)

001 = Fast RC Oscillator (FRC) with PLL (FRCPLL)

000 = Fast RC Oscillator (FRC)

bit 7 CLKLOCK: Clock Lock Enable bit

1 = If (FCKSM0 = 1), then clock and PLL configurations are locked; if (FCKSM0 = 0), then clock and PLL configurations may be modified

PLL configurations may be modified

0 = Clock and PLL selections are not locked, configurations may be modified

bit 6 **Unimplemented:** Read as '0'

bit 5 **LOCK:** PLL Lock Status bit (read-only)

1 = Indicates that PLL is in lock or PLL start-up timer is satisfied

0 = Indicates that PLL is out of lock, start-up timer is in progress or PLL is disabled

bit 4 Unimplemented: Read as '0'

Note 1: Writes to this register require an unlock sequence (see Section 9.6 "OSCCON Unlock Sequence").

2: Direct clock switches between any Primary Oscillator mode with PLL and FRCPLL mode are not permitted. This applies to clock switches in either direction. In these instances, the application must switch to FRC mode as a transitional clock source between the two PLL modes.

3: This bit should only be cleared in software. Setting the bit in software (= 1) will have the same effect as an actual oscillator failure and will trigger an oscillator failure trap.

REGISTER 9-1: OSCCON: OSCILLATOR CONTROL REGISTER⁽¹⁾ (CONTINUED)

bit 3 **CF**: Clock Fail Detect bit⁽³⁾

1 = FSCM has detected a clock failure 0 = FSCM has not detected a clock failure

bit 2-1 Unimplemented: Read as '0'

bit 0 OSWEN: Oscillator Switch Enable bit

1 = Requests oscillator switch to the selection specified by the NOSC<2:0> bits

0 = Oscillator switch is complete

Note 1: Writes to this register require an unlock sequence (see Section 9.6 "OSCCON Unlock Sequence").

- 2: Direct clock switches between any Primary Oscillator mode with PLL and FRCPLL mode are not permitted. This applies to clock switches in either direction. In these instances, the application must switch to FRC mode as a transitional clock source between the two PLL modes.
- **3:** This bit should only be cleared in software. Setting the bit in software (= 1) will have the same effect as an actual oscillator failure and will trigger an oscillator failure trap.

REGISTER 9-2: CLKDIV: CLOCK DIVIDER REGISTER

R/W-0	R/W-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0
ROI	DOZE2 ⁽¹⁾	DOZE1 ⁽¹⁾	DOZE0 ⁽¹⁾	DOZEN ^(2,3)	FRCDIV2	FRCDIV1	FRCDIV0
bit 15							bit 8

U-0	U-0	r-0	r-0	R/W-0	R/W-0	R/W-0	R/W-1
_	_	_	_	PLLPRE3 ⁽⁴⁾	PLLPRE2 ⁽⁴⁾	PLLPRE1 ⁽⁴⁾	PLLPRE0 ⁽⁴⁾
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 ROI: Recover on Interrupt bit

1 = Interrupts will clear the DOZEN bit and the processor clock, and the peripheral clock ratio is set to 1:1

0 = Interrupts have no effect on the DOZEN bit

bit 14-12 **DOZE<2:0>:** Processor Clock Reduction Select bits⁽¹⁾

111 = FP divided by 128

110 **=** FP divided by 64

101 = FP divided by 32

100 = FP divided by 16

011 = FP divided by 8 (default)

010 = FP divided by 4

001 = FP divided by 2

000 = FP divided by 1

bit 11 **DOZEN:** Doze Mode Enable bit^(2,3)

1 = DOZE<2:0> field specifies the ratio between the peripheral clocks and the processor clocks

0 = Processor clock and peripheral clock ratio is forced to 1:1

bit 10-8 FRCDIV<2:0>: Internal Fast RC Oscillator Postscaler bits

111 = FRC divided by 256

110 = FRC divided by 64

101 = FRC divided by 32

100 = FRC divided by 16

011 = FRC divided by 8

010 = FRC divided by 4

001 = FRC divided by 2

000 = FRC divided by 1 (default)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-4 **Reserved:** Read as '0'

Note 1: The DOZE<2:0> bits can only be written to when the DOZEN bit is clear. If DOZEN = 1, any writes to DOZE<2:0> are ignored.

2: This bit is cleared when the ROI bit is set and an interrupt occurs.

- 3: The DOZEN bit cannot be set if DOZE<2:0> = 000. If DOZE<2:0> = 000, any attempt by user software to set the DOZEN bit is ignored.
- 4: PLLPRE<3:0> may be updated while the PLL is operating, but the VCO may overshoot.

REGISTER 9-2: CLKDIV: CLOCK DIVIDER REGISTER (CONTINUED)

bit 3-0

PLLPRE<3:0>: PLL Phase Detector Input Divider Select bits (also denoted as 'N1', PLL prescaler)

11111 = Reserved

...

1001 = Reserved

1000 = Input divided by 8

0111 = Input divided by 7

0110 = Input divided by 6

0101 = Input divided by 5

0100 = Input divided by 4

0011 = Input divided by 3

0010 = Input divided by 2

0001 = Input divided by 1 (power-on default selection)

0000 = Reserved

- **Note 1:** The DOZE<2:0> bits can only be written to when the DOZEN bit is clear. If DOZEN = 1, any writes to DOZE<2:0> are ignored.
 - 2: This bit is cleared when the ROI bit is set and an interrupt occurs.
 - 3: The DOZEN bit cannot be set if DOZE<2:0> = 000. If DOZE<2:0> = 000, any attempt by user software to set the DOZEN bit is ignored.
 - **4:** PLLPRE<3:0> may be updated while the PLL is operating, but the VCO may overshoot.

REGISTER 9-3: PLLFBD: PLL FEEDBACK DIVIDER REGISTER

U-0	U-0	U-0	U-0	r-0	r-0	r-0	r-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-1	R/W-0	R/W-0	R/W-1	R/W-0	R/W-1	R/W-1	R/W-0
			PLLFBD)IV<7:0>			
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-12 **Unimplemented:** Read as '0' bit 11-8 **Reserved:** Maintain as '0'

bit 7-0 PLLFBDIV<7:0>: PLL Feedback Divider bits (also denoted as 'M', PLL multiplier)

11111111 = Reserved
...

11001000 = 200 Maximum⁽¹⁾
...

10010110 = 150 (default)
...

00010000 = 16 Minimum⁽¹⁾
...

00000010 = Reserved
00000001 = Reserved
00000000 = Reserved

Note 1: The allowed range is 16-200 (decimal). The rest of the values are reserved and should be avoided. The power on the default feedback divider is 150 (decimal) with an 8 MHz FRC input clock. The VCO frequency is 1.2 GHz.

REGISTER 9-4: OSCTUN: FRC OSCILLATOR TUNING REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_			TUN	<5:0>		
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-6 **Unimplemented:** Read as '0'

bit 5-0 **TUN<5:0>:** FRC Oscillator Tuning bits

011111 = Maximum frequency deviation of 1.45% (MHz)

011110 = Center frequency + 1.40% (MHz)

. . .

000001 = Center frequency + 0.047% (MHz)

000000 = Center frequency (8.00 MHz nominal)

111111 = Center frequency – 0.047% (MHz)

. . .

100001 = Center frequency – 1.45% (MHz)

100000 = Minimum frequency deviation of -1.50% (MHz)

REGISTER 9-5: PLLDIV: PLL OUTPUT DIVIDER REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	VCODIV1	VCODIV0
bit 15							bit 8

U-0	R/W-1	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-1
_	POST1DIV2 ^(1,2)	POST1DIV1 ^(1,2)	POST1DIV0(1,2)	_	POST2DIV2 ^(1,2)	POST2DIV1(1,2)	POST2DIV0(1,2)
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-8 VCODIV<1:0>: PLL VCO Output Divider Select bits

11 **=** Fvco

10 = Fvco/2

01 = Fvco/3

00 = Fvco/4

bit 7 **Unimplemented:** Read as '0'

bit 6-4 **POST1DIV<2:0>:** PLL Output Divider #1 Ratio bits^(1,2)

POST1DIV<2:0> can have a valid value, from 1 to 7 (POST1DIVx value should be greater than or equal to the POST2DIVx value). The POST1DIVx divider is designed to operate at higher clock rates than the POST2DIVx divider.

bit 3 Unimplemented: Read as '0'

bit 2-0 **POST2DIV<2:0>:** PLL Output Divider #2 Ratio bits^(1,2)

POST2DIV<2:0> can have a valid value, from 1 to 7 (POST2DIVx value should be less than or equal to the POST1DIVx value). The POST1DIVx divider is designed to operate at higher clock rates than the POST2DIVx divider.

- Note 1: The POST1DIVx and POST2DIVx divider values must not be changed while the PLL is operating.
 - 2: The default values for POST1DIVx and POST2DIVx are 4 and 1, respectively, yielding a 150 MHz system source clock.

REGISTER 9-6: ACLKCON1: AUXILIARY CLOCK CONTROL REGISTER

R/W-0	R/W-0	U-0	U-0	U-0	U-0	U-0	R/W-0
APLLEN ⁽¹⁾	APLLCK	_	_	_	_	_	FRCSEL
bit 15							bit 8

U-0	U-0	r-0	r-0	R/W-0	R/W-0	R/W-0	R/W-1
_	_	_	_	APLLPRE3	APLLPRE2	APLLPRE1	APLLPRE0
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

APLLEN: Auxiliary PLL Enable/Bypass select bit(1) bit 15

1 = AFPLLO is connected to the APLL post-divider output (bypass disabled)

0 = AFPLLO is connected to the APLL input clock (bypass enabled)

bit 14 APLLCK: APLL Phase-Locked State Status bit

> 1 = Auxiliary PLL is in lock 0 = Auxiliary PLL is not in lock

bit 13-9 Unimplemented: Read as '0'

bit 8 FRCSEL: FRC Clock Source Select bit

1 = FRC is the clock source for APLL

0 = Primary Oscillator is the clock source for APLL

bit 7-6 Unimplemented: Read as '0'

bit 5-4 Reserved: Maintain as '0'

bit 3-0 APLLPRE<3:0>: Auxiliary PLL Phase Detector Input Divider bits

1111 = Reserved

1001 = Reserved

1000 = Input divided by 8

0111 = Input divided by 7

0110 = Input divided by 6

0101 = Input divided by 5

0100 = Input divided by 4

0011 = Input divided by 3

0010 = Input divided by 2

0001 = Input divided by 1 (power-on default selection)

0000 = Reserved

Note 1: Even with the APLLEN bit set, another peripheral must generate a clock request before the APLL will start.

REGISTER 9-7: APLLFBD1: APLL FEEDBACK DIVIDER REGISTER

U-0	U-0	U-0	U-0	r-0	r-0	r-0	r-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-1	R/W-0	R/W-0	R/W-1	R/W-0	R/W-1	R/W-1	R/W-0
			APLLFE	3DIV<7:0>			
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-12 **Unimplemented:** Read as '0' bit 11-8 **Reserved:** Maintain as '0'

bit 7-0 APLLFBDIV<7:0>: APLL Feedback Divider bits

11111111 = Reserved
...
11001000 = 200 maximum⁽¹⁾
...
10010110 = 150 (default)
...
00010000 = 16 minimum⁽¹⁾
...
00000010 = Reserved
0000001 = Reserved

00000000 = Reserved

Note 1: The allowed range is 16-200 (decimal). The rest of the values are reserved and should be avoided. The power-on default feedback divider is 150 (decimal) with an 8 MHz FRC input clock; the VCO frequency is 1.2 GHz.

REGISTER 9-8: APLLDIV1: APLL OUTPUT DIVIDER REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	AVCOD	IV<1:0>
bit 15							bit 8

U-0	R/W-1	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-1	
_	APOST1DIV<2:0>(1,2)			_	APOST2DIV<2:0>(1,2)			
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-8 AVCODIV<1:0>: APLL VCO Output Divider Select bits

11 = AFVCO 10 = AFVCO/2 01 = AFVCO/3 00 = AFVCO/4

bit 7 **Unimplemented:** Read as '0'

bit 6-4 APOST1DIV<2:0>: APLL Output Divider #1 Ratio bits^(1,2)

APOST1DIV<2:0> can have a valid value, from 1 to 7 (the APOST1DIVx value should be greater than or equal to the APOST2DIVx value). The APOST1DIVx divider is designed to operate at higher clock

rates than the APOST2DIVx divider.

bit 3 **Unimplemented:** Read as '0'

bit 2-0 APOST2DIV<2:0>: APLL Output Divider #2 Ratio bits^(1,2)

APOST2DIV < 2:0 > can have a valid value, from 1 to 7 (the APOST2DIVx value should be less than or equal to the APOST1DIVx value). The APOST1DIVx divider is designed to operate at higher clock

rates than the APOST2DIVx divider.

Note 1: The APOST1DIVx and APOST2DIVx values must not be changed while the PLL is operating.

2: The default values for APOST1DIVx and APOST2DIVx are 4 and 1, respectively, yielding a 150 MHz system source clock.

REGISTER 9-9: CANCLKCON: CAN CLOCK CONTROL REGISTER

R/W-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
CANCLKEN	_	_	_		CANCLKS	EL<3:0> ⁽¹⁾	
bit 15							bit 8

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
_		CANCLKDIV<6:0> ^(2,3)							
bit 7							bit 0		

Legend: R = Readable bit W = Writable bit U = Unimplemented bit, read as '0' -n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **CANCLKEN:** Enables the CAN Clock Generator bit

> 1 = CAN clock generation circuitry is enabled 0 = CAN clock generation circuitry is disabled

bit 14-12 Unimplemented: Read as '0'

CANCLKSEL<3:0>: CAN Clock Source Select bits(1) bit 11-8

1011-1111 = Reserved (no clock selected)

1010 = AFvco/4

1001 = AFvco/3

1000 = AFvco/2

0111 **= AF**vco

0110 **= AFPLLO**

0101 = Fvco/4 0100 = Fvco/3

0011 = Fvco/2

0010 **= F**PLLO

0001 **=** Fvco

0000 = 0 (no clock selected)

bit 7 Unimplemented: Read as '0'

bit 6-0 CANCLKDIV<6:0>: CAN Clock Divider Select bits(2,3)

1111111 = Divide-by-128

0000010 = Divide-by-3

0000001 = Divide-by-2

0000000 = Divide-by-1

- Note 1: The user must ensure the input clock source is 640 MHz or less. Operation with input reference frequency above 640 MHz will result in unpredictable behavior.
 - 2: The CANCLKDIVx divider value must not be changed during CAN module operation.
 - 3: The user must ensure the maximum clock output frequency of the divider is 80 MHz or less.

REGISTER 9-10: REFOCONL: REFERENCE CLOCK CONTROL LOW REGISTER

R/W-0	U-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0, HC	R-0, HSC
ROEN	_	ROSIDL	ROOUT	ROSLP	_	ROSWEN	ROACTIV
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	ROSEL3	ROSEL2	ROSEL1	ROSEL0
bit 7							bit 0

Legend: HC = Hardware Clearable bit		HSC = Hardware Settable/Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15 ROEN: Reference Clock Enable bit

1 = Reference Oscillator is enabled on the REFCLKO pin

0 = Reference Oscillator is disabled

bit 14 **Unimplemented:** Read as '0'

bit 13 ROSIDL: Reference Clock Stop in Idle bit

1 = Reference Oscillator continues to run in Idle mode

0 = Reference Oscillator is disabled in Idle mode

bit 12 ROOUT: Reference Clock Output Enable bit

1 = Reference clock external output is enabled and available on the REFCLKO pin

0 = Reference clock external output is disabled

bit 11 ROSLP: Reference Clock Stop in Sleep bit

1 = Reference Oscillator continues to run in Sleep modes

0 = Reference Oscillator is disabled in Sleep modes

bit 10 **Unimplemented:** Read as '0'

bit 9 ROSWEN: Reference Clock Output Enable bit

1 = Clock divider change (requested by changes to RODIVx) is requested or is in progress (set in software, cleared by hardware upon completion)

0 = Clock divider change has completed or is not pending

bit 8 ROACTIV: Reference Clock Status bit

1 = Reference clock is active; do not change clock source

0 = Reference clock is stopped; clock source and configuration may be safely changed

bit 7-4 **Unimplemented:** Read as '0'

bit 3-0 ROSEL<3:0>: Reference Clock Source Select bits

1111 = Reserved

... = Reserved

1000 = Reserved

0111 = REFI pin

0110 = Fvco/4

0101 = BFRC

0100 **= LPRC**

0011 = FRC

0010 = Primary Oscillator

0001 = Peripheral clock (FP)

0000 = System clock (Fosc)

REGISTER 9-11: REFOCONH: REFERENCE CLOCK CONTROL HIGH REGISTER

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_				RODIV<14:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
RODIV<7:0>								
bit 7	bit 7							

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	l as '0'
-n = Value at POR	'1' = Rit is set	'0' = Rit is cleared	v = Rit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-0 RODIV<14:0>: Reference Clock Integer Divider Select bits

NOTES:			
10120.			

10.0 DIRECT MEMORY ACCESS (DMA) CONTROLLER

Note 1: This data sheet summarizes the features of this group of dsPIC33 devices. It is not intended to be a comprehensive reference source. For more information, refer to "Direct Memory Access Controller (DMA)" (www.microchip.com/DS39742) in the "dsPIC33/PIC24 Family Reference Manual".

The Direct Memory Access (DMA) Controller is designed to service high data throughput peripherals operating on the SFR bus, allowing them to access data memory directly and alleviating the need for CPU-intensive management. By allowing these data-intensive peripherals to share their own data path, the main data bus is also deloaded, resulting in additional power savings.

The DMA Controller functions both as a peripheral and a direct extension of the CPU. It is located on the microcontroller data bus, between the CPU and DMA-enabled peripherals, with direct access to SRAM. This partitions the SFR bus into two buses, allowing the DMA Controller access to the DMA-capable peripherals located on the new DMA SFR bus. The controller serves as a Master device on the DMA SFR bus, controlling data flow from DMA-capable peripherals.

The controller also monitors CPU instruction processing directly, allowing it to be aware of when the CPU requires access to peripherals on the DMA bus and automatically relinquishing control to the CPU as needed. This increases the effective bandwidth for handling data without DMA operations, causing a processor Stall. This makes the controller essentially transparent to the user.

The DMA Controller has these features:

- · Four Independently Programmable Channels
- Concurrent Operation with the CPU (no DMA caused Wait states)
- · DMA Bus Arbitration
- · Five Programmable Address modes
- · Four Programmable Transfer modes
- · Four Flexible Internal Data Transfer modes
- Byte or Word Support for Data Transfer
- 16-Bit Source and Destination Address Register for each Channel, Dynamically Updated and Reloadable
- 16-Bit Transaction Count Register, Dynamically Updated and Reloadable
- Upper and Lower Address Limit Registers
- · Counter Half-Full Level Interrupt
- · Software Triggered Transfer
- Null Write mode for Symmetric Buffer Operations

A simplified block diagram of the DMA Controller is shown if Figure 10-1.




FIGURE 10-1: DMA FUNCTIONAL BLOCK DIAGRAM

10.1 Summary of DMA Operations

The DMA Controller is capable of moving data between addresses according to a number of different parameters. Each of these parameters can be independently configured for any transaction. In addition, any or all of the DMA channels can independently perform a different transaction at the same time. Transactions are classified by these parameters:

- · Source and destination (SFRs and data RAM)
- Data size (byte or word)
- · Trigger source
- Transfer mode (One-Shot, Repeated or Continuous)
- Addressing modes (Fixed Address or Address Blocks with or without Address Increment/Decrement)

In addition, the DMA Controller provides channel priority arbitration for all channels.

10.1.1 SOURCE AND DESTINATION

Using the DMA Controller, data may be moved between any two addresses in the Data Space. The SFR space (0000h to 0FFFh) or the data RAM space (1000h to 4FFFh) can serve as either the source or the destination. Data can be moved between these areas in either direction or between addresses in either area. The four different combinations are shown in Figure 10-2.

If it is necessary to protect areas of data RAM, the DMA Controller allows the user to set upper and lower address boundaries for operations in the Data Space above the SFR space. The boundaries are set by the DMAH and DMAL Limit registers. If a DMA channel attempts an operation outside of the address boundaries, the transaction is terminated and an interrupt is generated.

10.1.2 DATA SIZE

The DMA Controller can handle both 8-bit and 16-bit transactions. Size is user-selectable using the SIZE bit (DMACHn<1>). By default, each channel is configured for word-size transactions. When byte-size transactions are chosen, the LSB of the source and/or destination address determines if the data represents the upper or lower byte of the data RAM location.

10.1.3 TRIGGER SOURCE

The DMA Controller can use 82 of the device's interrupt sources to initiate a transaction. The DMA trigger sources occur in reverse order from their natural interrupt priority and are shown in Table 10-1.

Since the source and destination addresses for any transaction can be programmed independently of the trigger source, the DMA Controller can use any trigger to perform an operation on any peripheral. This also allows DMA channels to be cascaded to perform more complex transfer operations.

10.1.4 TRANSFER MODE

The DMA Controller supports four types of data transfers, based on the volume of data to be moved for each trigger.

- One-Shot: A single transaction occurs for each trigger.
- Continuous: A series of back-to-back transactions occur for each trigger; the number of transactions is determined by the DMACNTn transaction counter.
- Repeated One-Shot: A single transaction is performed repeatedly, once per trigger, until the DMA channel is disabled.
- Repeated Continuous: A series of transactions are performed repeatedly, one cycle per trigger, until the DMA channel is disabled.

All transfer modes allow the option to have the source and destination addresses, and counter value, automatically reloaded after the completion of a transaction.


10.1.5 ADDRESSING MODES

The DMA Controller also supports transfers between single addresses or address ranges. The four basic options are:

- Fixed-to-Fixed: Between two constant addresses
- Fixed-to-Block: From a constant source address to a range of destination addresses
- Block-to-Fixed: From a range of source addresses to a single, constant destination address
- Block-to-Block: From a range of source addresses to a range of destination addresses

The option to select auto-increment or auto-decrement of source and/or destination addresses is available for Block Addressing modes.

In addition to the four basic modes, the DMA Controller also supports Peripheral Indirect Addressing (PIA) mode, where the source or destination address is generated jointly by the DMA Controller and a PIA-capable peripheral. When enabled, the DMA channel provides a base source and/or destination address, while the peripheral provides a fixed range offset address.



10.1.6 CHANNEL PRIORITY

Each DMA channel functions independently of the others, but also competes with the others for access to the data and DMA buses. When access collisions occur, the DMA Controller arbitrates between the channels using a user-selectable priority scheme. Two schemes are available:

- Round Robin: When two or more channels collide, the lower numbered channel receives priority on the first collision. On subsequent collisions, the higher numbered channels each receive priority based on their channel number.
- Fixed: When two or more channels collide, the lowest numbered channel always receives priority, regardless of past history; however, any channel being actively processed is not available for an immediate retrigger. If a higher priority channel is continually requesting service, it will be scheduled for service after the next lower priority channel with a pending request.

10.2 Typical Setup

To set up a DMA channel for a basic data transfer:

- Enable the DMA Controller (DMAEN = 1) and select an appropriate channel priority scheme by setting or clearing PRSSEL.
- 2. Program DMAH and DMAL with appropriate upper and lower address boundaries for data RAM operations.
- 3. Select the DMA channel to be used and disable its operation (CHEN = 0).
- Program the appropriate source and destination addresses for the transaction into the channel's DMASRCn and DMADSTn registers. For PIA mode addressing, use the base address value.
- Program the DMACNTn register for the number of triggers per transfer (One-Shot or Continuous modes) or the number of words (bytes) to be transferred (Repeated modes).
- 6. Set or clear the SIZE bit to select the data size.
- Program the TRMODE<1:0> bits to select the Data Transfer mode.
- 8. Program the SAMODE<1:0> and DAMODE<1:0> bits to select the addressing mode.
- 9. Enable the DMA channel by setting CHEN.
- 10. Enable the trigger source interrupt.

10.3 Peripheral Module Disable

The channels of the DMA Controller can be individually powered down using the Peripheral Module Disable (PMD) registers.

10.4 Registers

The DMA Controller uses a number of registers to control its operation. The number of registers depends on the number of channels implemented for a particular device.

There are always four module-level registers (one control and three buffer/address):

- DMACON: DMA Engine Control Register (Register 10-1)
- DMAH and DMAL: DMA High and Low Address Limit Registers
- · DMABUF: DMA Transfer Data Buffer

Each of the DMA channels implements five registers (two control and three buffer/address):

- DMACHn: DMA Channel n Control Register (Register 10-2)
- DMAINTn: DMA Channel n Interrupt Register (Register 10-3)
- DMASRCn: DMA Data Source Address Pointer for Channel n Register
- DMADSTn: DMA Data Destination Source for Channel n Register
- DMACNTn: DMA Transaction Counter for Channel n Register

For dsPIC33CK256MP508 devices, there are a total of 34 registers.

REGISTER 10-1: DMACON: DMA ENGINE CONTROL REGISTER

R/W-0	U-0	R/W-0	U-0	U-0	U-0	U-0	U-0
DMAEN	_	DMASIDL	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	PRSSEL
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **DMAEN:** DMA Module Enable bit

1 = Enables module

0 = Disables module and terminates all active DMA operation(s)

bit 14 Unimplemented: Read as '0'

bit 13 DMASIDL: DMA Stop in Idle bit

1 = DMA continues to run in Idle mode

0 = DMA is disabled in Idle mode

bit 12-1 **Unimplemented:** Read as '0'

bit 0 PRSSEL: Channel Priority Scheme Selection bit

1 = Round robin scheme0 = Fixed priority scheme

REGISTER 10-2: DMACHn: DMA CHANNEL n CONTROL REGISTER

U-0	U-0	U-0	r-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	NULLW	RELOAD ⁽¹⁾	CHREQ ⁽³⁾
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SAMODE1	SAMODE0	DAMODE1	DAMODE0	TRMODE1	TRMODE0	SIZE	CHEN
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, rea	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-13 Unimplemented: Read as '0'
bit 12 Reserved: Maintain as '0'
bit 11 Unimplemented: Read as '0'
bit 10 NULLW: Null Write Mode bit

1 = A dummy write is initiated to DMASRCn for every write to DMADSTn

0 = No dummy write is initiated

bit 9 **RELOAD:** Address and Count Reload bit⁽¹⁾

1 = DMASRCn, DMADSTn and DMACNTn registers are reloaded to their previous values upon the

start of the next operation

0 = DMASRCn, DMADSTn and DMACNTn are not reloaded on the start of the next operation (2)

bit 8 CHREQ: DMA Channel Software Request bit (3)

1 = A DMA request is initiated by software; automatically cleared upon completion of a DMA transfer

0 = No DMA request is pending

bit 7-6 SAMODE<1:0>: Source Address Mode Selection bits

11 = DMASRCn is used in Peripheral Indirect Addressing and remains unchanged

10 = DMASRCn is decremented based on the SIZE bit after a transfer completion

01 = DMASRCn is incremented based on the SIZE bit after a transfer completion

00 = DMASRCn remains unchanged after a transfer completion

bit 5-4 DAMODE<1:0>: Destination Address Mode Selection bits

11 = DMADSTn is used in Peripheral Indirect Addressing and remains unchanged

10 = DMADSTn is decremented based on the SIZE bit after a transfer completion

01 = DMADSTn is incremented based on the SIZE bit after a transfer completion

00 = DMADSTn remains unchanged after a transfer completion

bit 3-2 **TRMODE<1:0>:** Transfer Mode Selection bits

11 = Repeated Continuous

10 = Continuous

01 = Repeated One-Shot

00 = One-Shot

bit 1 SIZE: Data Size Selection bit

1 = Byte (8-bit) 0 = Word (16-bit)

bit 0 CHEN: DMA Channel Enable bit

1 = The corresponding channel is enabled

0 = The corresponding channel is disabled

Note 1: Only the original DMACNTn is required to be stored to recover the original DMASRCn and DMADSTn values.

2: DMACNTn will always be reloaded in Repeated mode transfers, regardless of the state of the RELOAD bit.

3: The number of transfers executed while CHREQ is set depends on the configuration of TRMODE<1:0>.

REGISTER 10-3: DMAINTn: DMA CHANNEL n INTERRUPT REGISTER

R-0	R/W-0						
DBUFWF ⁽¹⁾	CHSEL6	CHSEL5	CHSEL4	CHSEL3	CHSEL2	CHSEL1	CHSEL0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0	R/W-0
HIGHIF ^(1,2)	LOWIF ^(1,2)	DONEIF ⁽¹⁾	HALFIF ⁽¹⁾	OVRUNIF ⁽¹⁾	_	_	HALFEN
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **DBUFWF:** DMA Buffered Data Write Flag bit⁽¹⁾

- 1 = The content of the DMA buffer has not been written to the location specified in DMADSTn or DMASRCn in Null Write mode
- 0 = The content of the DMA buffer has been written to the location specified in DMADSTn or DMASRCn in Null Write mode
- bit 14-8 CHSEL<6:0>: DMA Channel Trigger Selection bits

See Table 10-1 for a complete list.

bit 7 HIGHIF: DMA High Address Limit Interrupt Flag bit (1,2)

- 1 = The DMA channel has attempted to access an address higher than DMAH or the upper limit of the data RAM space
- 0 = The DMA channel has not invoked the high address limit interrupt
- bit 6 **LOWIF:** DMA Low Address Limit Interrupt Flag bit^(1,2)
 - 1 = The DMA channel has attempted to access the DMA SFR address lower than DMAL, but above the SFR range (07FFh)
 - 0 = The DMA channel has not invoked the low address limit interrupt
- bit 5 **DONEIF:** DMA Complete Operation Interrupt Flag bit⁽¹⁾

If CHEN = 1:

- 1 = The previous DMA session has ended with completion
- 0 = The current DMA session has not yet completed

If CHEN = 0:

- 1 = The previous DMA session has ended with completion
- 0 = The previous DMA session has ended without completion
- bit 4 HALFIF: DMA 50% Watermark Level Interrupt Flag bit (1)
 - 1 = DMACNTn has reached the halfway point to 0000h
 - 0 = DMACNTn has not reached the halfway point
- bit 3 **OVRUNIF:** DMA Channel Overrun Flag bit⁽¹⁾
 - 1 = The DMA channel is triggered while it is still completing the operation based on the previous trigger
 - 0 = The overrun condition has not occurred
- bit 2-1 **Unimplemented:** Read as '0'
- bit 0 HALFEN: Halfway Completion Watermark bit
 - 1 = Interrupts are invoked when DMACNTn has reached its halfway point and at completion
 - 0 = An interrupt is invoked only at the completion of the transfer
- Note 1: Setting these flags in software does not generate an interrupt.
 - 2: Testing for address limit violations (DMASRCn or DMADSTn is either greater than DMAH or less than DMAL) is NOT done before the actual access.

TABLE 10-1: DMA CHANNEL TRIGGER SOURCES

CHSEL<6:0>		Trigger (Interrupt)	CHSEL<6:0> Trigger (Interrupt)		CHSEL<6:0>		Trigger (Interrupt)	
0000000	00h	INT0 – External Interrupt 0	0100011	23h	PWM Generator 8	1000100	44h	CLC1 Positive Edge Interrupt
0000001	01h	SCCP1 Interrupt	0100100	24h	PWM Event C	1000101	45h	CLC2 Positive Edge Interrupt
0000010	02h	SPI1 Receiver	0100101	25h	SENT1 TX/RX	1000110	46h	SPI1 – Fault Interrupt
0000011	03h	SPI1 Transmitter	0100110	26h	SENT2 TX/RX	1000111	47h	SPI2 – Fault Interrupt
0000100	04h	UART1 Receiver	0100111	27h	ADC1 Group Convert Done	1001000	48h	
0000101	05h	UART1 Transmitter	0101000	28h	ADC Done AN0			(Reserved, do not use)
0000110	06h	ECC Single Bit Error	0101001	29h	ADC Done AN1	1010110	56h	
0000111	07h	NVM Write Complete	0101010	2Ah	ADC Done AN2	1010111	57h	PWM Event D
0001000	08h	INT1 – External Interrupt 1	0101011	2Bh	ADC Done AN3	1011000	58h	PWM Event E
0001001	09h	SI2C1 – I2C1 Slave Event	0101100	2Ch	ADC Done AN4	1011001	59h	PWM Event F
0001010	0Ah	MI2C1 – I2C1 Master Event	0101101	2Dh	ADC Done AN5	1011010	5Ah	(Reserved, do not use)
0001011	0Bh	INT2 – External Interrupt 2	0101110	2Eh	ADC Done AN6	1011011	5Bh	(Reserved, do not use)
0001100	0Ch	SCCP2 Interrupt	0101111	2Fh	ADC Done AN7	1011100	5Ch	SCCP7 Interrupt
0001101	0Dh	INT3 – External Interrupt 3	0110000	30h	ADC Done AN8	1011101	5Dh	SCCP8 Interrupt
0001110	0Eh	UART2 Receiver	0110001	31h	ADC Done AN9	1011110	5Eh	(Reserved, do not use)
0001111	0Fh	UART2 Transmitter	0110010	32h	ADC Done AN10	1011111	5Fh	ADC FIFO Ready Interrupt
0010000	10h	SPI2 Receiver	0110011	33h	ADC Done AN11	1100000	60h	CLC3 Positive Edge Interrupt
0010001	11h	SPI2 Transmitter	0110100	34h	ADC Done AN12	1100001	61h	CLC4 Positive Edge Interrupt
0010010	12h	SCCP3 Interrupt	0110101	35h	ADC Done AN13	1100010	62h	SPI3 Receiver
0010011	13h	SI2C2 – I2C2 Slave Event	0110110	36h	ADC Done AN14	1100011	63h	SPI3 Transmitter
0010100	14h	MI2C2 – I2C1 Master Event	0110111	37h	ADC Done AN15	1100100	64h	SI2C3 – I2C3 Slave Event
0010101	15h	SCCP4 Interrupt	0111000	38h	ADC Done AN16	1100101	65h	MI2C3 – I2C3 Master Event
0010110	16h	SCCP5 Interrupt	0111001	39h	ADC Done AN17	1100110	66h	SPI3 Fault
0010111	17h	SCCP6 Interrupt	0111010	3Ah	ADC Done AN18	1100111	67h	MCCP9
0011000	18h	CRC Generator Interrupt	0111011	3Bh	ADC Done AN19	1101000	68h	UART3 Receiver
0011001	19h	PWM Event A	0111100	3Ch	ADC Done AN20	1101001	69h	UART3 Transmitter
0011010	1Ah	(Reserved, do not use)	0111101	3Dh	ADC Done AN21	1101010	6Ah	ADC Done AN24
0011011	1Bh	PWM Event B	0111110	3Eh	ADC Done AN22	1101011	6Bh	ADC Done AN25
0011100	1Ch	PWM Generator 1	0111111	3Fh	ADC Done AN23	1101100	6Ch	PMP Event
0011101	1Dh	PWM Generator 2	1000000	40h	AD1FLTR1 – Oversample Filter 1	1101101	6Dh	PMP Error Event
0011110	1Eh	PWM Generator 3	1000001	41h	AD1FLTR2 – Oversample Filter 2	1101110	6Eh	
0011111	1Fh	PWM Generator 4	1000010	42h	AD1FLTR3 – Oversample Filter 3			(Reserved, do not use)
0100000	20h	PWM Generator 5	1000011	43h	AD1FLTR4 – Oversample Filter 4	1111111	7Fh	
0100001	21h	PWM Generator 6						
0100010	22h	PWM Generator 7						

431 10330			
NOTES:			

11.0 CONTROLLER AREA NETWORK (CAN FD) MODULE

- Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. For more information, refer to "CAN Flexible Data-Rate (FD) Protocol Module" (www.microchip.com/DS70005340) in the "dsPIC33/PIC24 Family Reference Manual".
 - 2: Not all device variants include the CAN FD peripheral. Refer to Table 1 and Table 2 for availability.

11.1 Features

The CAN FD module has the following features:

General

- · Nominal (Arbitration) Bit Rate up to 1 Mbps
- · Data Bit Rate up to 8 Mbps
- · CAN FD Controller modes:
 - Mixed CAN 2.0B and CAN FD mode
 - CAN 2.0B mode
- Conforms to ISO11898-1:2015

Message FIFOs

- Seven FIFOs, Configurable as Transmit or Receive FIFOs
- One Transmit Queue (TXQ)
- · Transmit Event FIFO (TEF) with 32-Bit Timestamp

Message Transmission


- Message Transmission Prioritization:
 - Based on priority bit field, and/or
 - Message with lowest ID gets transmitted first using the TXQ
- Programmable Automatic Retransmission Attempts: Unlimited, Three Attempts or Disabled

Message Reception

- · 16 Flexible Filter and Mask Objects.
- Each Object can be Configured to Filter either:
 - Standard ID + first 18 data bits or
 - Extended ID
- 32-Bit Timestamp.
- The CAN FD Bit Stream Processor (BSP)
 Implements the Medium Access Control of the CAN FD Protocol Described in ISO11898-1:2015.

 It serializes and deserializes the bit stream, encodes and decodes the CAN FD frames, manages the medium access, Acknowledges frames, and detects and signals errors.
- The TX Handler Prioritizes the Messages that are Requested for Transmission by the Transmit FIFOs. It uses the RAM interface to fetch the transmit data from RAM and provides it to the BSP for transmission.
- The BSP provides Received Messages to the RX Handler. The RX handler uses acceptance filters to filter out messages that shall be stored in the Receive FIFOs. It uses the RAM interface to store received data into RAM.
- Each FIFO can be Configured either as a Transmit or Receive FIFO. The FIFO control keeps track of the FIFO head and tail, and calculates the user address. In a TX FIFO, the user address points to the address in RAM where the data for the next transmit message shall be stored. In an RX FIFO, the user address points to the address in RAM where the data of the next receive message shall be read. The user notifies the FIFO that a message was written to or read from RAM by incrementing the head/tail of the FIFO.
- The Transmit Queue (TXQ) is a Special Transmit FIFO that Transmits the Messages based on the ID of the Messages Stored in the Queue.
- The Transmit Event FIFO (TEF) Stores the Message IDs of the Transmitted Messages.
- A Free-Running Time Base Counter is used to Timestamp Received Messages. Messages in the TEF can also be timestamped.
- The CAN FD Controller module Generates Interrupts when New Messages are Received or when Messages were Transmitted Successfully.

Figure 11-1 shows the CAN FD system block diagram.



11.2 Can Control Registers

REGISTER 11-1: C1CONH: CAN CONTROL REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	S/HC-0	R/W-1	R/W-0	R/W-0
TXBWS3	TXBWS2	TXBWS1	TXBWS0	ABAT	REQOP2	REQOP1	REQOP0
bit 15							bit 8

R-1	R-0	R-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0
OPMOD2	OPMOD1	OPMOD0	TXQEN ⁽¹⁾	STEF ⁽¹⁾	SERRLOM ⁽¹⁾	ESIGM ⁽¹⁾	RTXAT ⁽¹⁾
bit 7							bit 0

Legend:	S = Settable bit	HC = Hardware Cleara	ble bit
R = Readable bit	W = Writable bit	U = Unimplemented bit	r, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-12 **TXBWS<3:0>:** Transmit Bandwidth Sharing bits

1111-1100 = 4096

1011 **= 2048**

1010 = 1024

1001 = 512

1000 = 256

0111 = 128

0110 = 64

0101 = 32

0100 = 16

0011 = 8

0010 = 4

bit 11

0001 = 2

0000 = No delay

ABAT: Abort All Pending Transmissions bit

1 = Signals all transmit buffers to abort transmission

0 = Module will clear this bit when all transmissions are aborted

bit 10-8 **REQOP<2:0>:** Request Operation Mode bits

111 = Sets Restricted Operation mode

110 = Sets Normal CAN 2.0 mode; error frames on CAN FD frames

101 = Sets External Loopback mode

100 = Sets Configuration mode

011 = Sets Listen Only mode

010 = Sets Internal Loopback mode

001 = Sets Disable mode

000 = Sets Normal CAN FD mode; supports mixing of full CAN FD and classic CAN 2.0 frames

bit 7-5 **OPMOD<2:0>:** Operation Mode Status bits

111 = Module is in Restricted Operation mode

110 = Module is in Normal CAN 2.0 mode; error frames on CAN FD frames

101 = Module is in External Loopback mode

100 = Module is in Configuration mode

011 = Module is in Listen Only mode

010 = Module is in Internal Loopback mode

001 = Module is in Disable mode

000 = Module is in Normal CAN FD mode; supports mixing of full CAN FD and classic CAN 2.0 frames

REGISTER 11-1: C1CONH: CAN CONTROL REGISTER HIGH (CONTINUED)

bit 4	TXQEN: Enable Transmit Queue bit ⁽¹⁾
	1 = Enables Transmit Message Queue (TXQ) and reserves space in RAM
	0 = Does not reserve space in RAM for TXQ
bit 3	STEF: Store in Transmit Event FIFO bit ⁽¹⁾
	1 = Saves transmitted messages in TEF
	0 = Does not save transmitted messages in TEF
bit 2	SERRLOM: Transition to Listen Only Mode on System Error bit ⁽¹⁾
	1 = Transitions to Listen Only mode
	0 = Transitions to Restricted Operation mode
bit 1	ESIGM: Transmit ESI in Gateway Mode bit ⁽¹⁾
	1 = ESI is transmitted as recessive when ESI of the message is high or CAN controller is error passive
	0 = ESI reflects error status of CAN controller
bit 0	RTXAT: Restrict Retransmission Attempts bit ⁽¹⁾
	1 = Restricted retransmission attempts, uses TXAT<1:0> bits (C1TXQCONH<6:5>)
	0 = Unlimited number of retransmission attempts. TXAT<1:0> bits will be ignored

REGISTER 11-2: C1CONL: CAN CONTROL REGISTER LOW

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-1	R/W-1
CON	_	SIDL	BRSDIS	BUSY	WFT1	WFT0	WAKFIL ⁽¹⁾
bit 15							bit 8

R/W-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CLKSEL ⁽¹⁾	PXEDIS ⁽¹⁾	ISOCRCEN ⁽¹⁾	DNCNT4	DNCNT3	DNCNT2	DNCNT1	DNCNT0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 CON: CAN Enable bit

1 = CAN module is enabled

0 = CAN module is disabled

bit 14 **Unimplemented:** Read as '0'

bit 13 SIDL: CAN Stop in Idle Control bit

1 = Stops module operation in Idle mode

 $_{
m 0}$ = Does not stop module operation in Idle mode

bit 12 BRSDIS: Bit Rate Switching (BRS) Disable bit

1 = Bit Rate Switching is disabled, regardless of BRS in the transmit message object

0 = Bit Rate Switching depends on BRS in the transmit message object

bit 11 BUSY: CAN Module is Busy bit

1 = The CAN module is active

0 = The CAN module is inactive

bit 10-9 WFT<1:0>: Selectable Wake-up Filter Time bits

11 **= T11**FILTER

10 **= T10**FILTER

01 = **T01**FILTER

00 **= T00**FILTER

bit 8 **WAKFIL:** Enable CAN Bus Line Wake-up Filter bit⁽¹⁾

1 = Uses CAN bus line filter for wake-up

0 = CAN bus line filter is not used for wake-up

bit 7 CLKSEL: Module Clock Source Select bit (1)

1 = Auxiliary clock is active when module is enabled

0 = CAN clock is not active when module is enabled

bit 6 **PXEDIS:** Protocol Exception Event Detection Disabled bit⁽¹⁾

A recessive "reserved bit" following a recessive FDF bit is called a Protocol Exception.

1 = Protocol Exception is treated as a form error

0 = If a Protocol Exception is detected, CAN will enter the bus integrating state

bit 5 **ISOCRCEN:** Enable ISO CRC in CAN FD Frames bit⁽¹⁾

1 = Includes stuff bit count in CRC field and uses non-zero CRC initialization vector

0 = Does not include stuff bit count in CRC field and uses CRC initialization vector with all zeros

bit 4-0 **DNCNT<4:0>:** DeviceNet™ Filter Bit Number bits

10011-11111 = Invalid selection (compares up to 18 bits of data with EID)

10010 = Compares up to Data Byte 2, bit 6 with EID17

. . .

00001 = Compares up to Data Byte 0, bit 7 with EID0

00000 = Does not compare data bytes

REGISTER 11-3: C1NBTCFGH: CAN NOMINAL BIT TIME CONFIGURATION REGISTER HIGH⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	BRP<7:0>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-1	R/W-1	R/W-1	R/W-1	R/W-0	R/W-0			
	TSEG1<7:0>									
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 BRP<7:0>: Baud Rate Prescaler bits

1111 1111 = TQ = 256/Fsys

000

0000 0000 = TQ = 1/Fsys

bit 7-0 TSEG1<7:0>: Time Segment 1 bits (Propagation Segment + Phase Segment 1)

1111 1111 = Length is 256 x TQ

• • •

0000 0000 = Length is 1 x TQ

Note 1: These bits can only be modified in Configuration mode (OPMOD<2:0> = 100).

REGISTER 11-4: C1NBTCFGL: CAN NOMINAL BIT TIME CONFIGURATION REGISTER LOW⁽¹⁾

U-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-1	R/W-1	R/W-1		
_		TSEG2<6:0>							
bit 15							bit 8		

U-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-1	R/W-1	R/W-1
_				SJW<6:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-8 **TSEG2<6:0>:** Time Segment 2 bits (Phase Segment 2)

111 1111 = Length is 128 x TQ

. . .

000 0000 = Length is 1 x TQ

bit 7 **Unimplemented:** Read as '0'

bit 6-0 **SJW<6:0>:** Synchronization Jump Width bits

111 1111 = Length is 128 x TQ

• •

000 0000 = Length is 1 x TQ

REGISTER 11-5: C1DBTCFGH: CAN DATA BIT TIME CONFIGURATION REGISTER HIGH⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	BRP<7:0>								
bit 15							bit 8		

U-0	U-0	U-0	R/W-0	R/W-1	R/W-1	R/W-1	R/W-0
_	_	_			TSEG1<4:0>		
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 BRP<7:0>: Baud Rate Prescaler bits

1111 1111 = TQ = 256/Fsys

0000 0000 = TQ = 1/Fsys

bit 7-5 **Unimplemented:** Read as '0'

bit 4-0 **TSEG1<4:0>:** Time Segment 1 bits (Propagation Segment + Phase Segment 1)

1 1111 = Length is 32 x TQ

0 0000 = Length is 1 x TQ

Note 1: This register can only be modified in Configuration mode (OPMOD<2:0> = 100).

REGISTER 11-6: C1DBTCFGL: CAN DATA BIT TIME CONFIGURATION REGISTER LOW⁽¹⁾

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-1	R/W-1
_	_	_	_		TSEG	2<3:0>	
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-1	R/W-1	
_	_	_	_	SJW<3:0>				
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 **Unimplemented:** Read as '0'

bit 11-8 **TSEG2<3:0>:** Time Segment 2 bits (Phase Segment 2)

1111 = Length is 16 x TQ

• • •

0000 = Length is 1 x TQ

bit 7-4 **Unimplemented:** Read as '0'

bit 3-0 **SJW<3:0>:** Synchronization Jump Width bits

1111 = Length is 16 x TQ

 $0000 = \text{Length is } 1 \times \text{TQ}$

2000 Longario I X 1 Q

REGISTER 11-7: C1TDCH: CAN TRANSMITTER DELAY COMPENSATION REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	EDGFLTEN	SID11EN
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	R/W-1	R/W-0
_	_	_	_	_	_	TDCMOD1	TDCMOD0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9 **EDGFLTEN:** Enable Edge Filtering During Bus Integration State bit

1 = Edge filtering is enabled according to ISO11898-1:2015

0 = Edge filtering is disabled

bit 8 SID11EN: Enable 12-Bit SID in CAN FD Base Format Messages bit

1 = RRS is used as SID11 in CAN FD base format messages: SID<11:0> = {SID<10:0>, SID11}

0 = Does not use RRS; SID<10:0>

bit 7-2 **Unimplemented:** Read as '0'

bit 1-0 **TDCMOD<1:0>:** Transmitter Delay Compensation Mode bits (Secondary Sample Point (SSP))

10-11 = Auto: Measures delay and adds TSEG1<4:0> (C1DBTCFGH<4:0>), adds TDCO<6:0>

01 = Manual: Does not measure, uses TDCV<5:0> + TDCO<6:0> from register

00 = Disable

REGISTER 11-8: C1TDCL: CAN TRANSMITTER DELAY COMPENSATION REGISTER LOW⁽¹⁾

U-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0
_				TDCO<6:0>			
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_			TDCV	/<5:0>		
bit 7							bit 0

Legend:				1
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

```
bit 15

Unimplemented: Read as '0'

bit 14-8

TDCO<6:0>: Transmitter Delay Compensation Offset bits (Secondary Sample Point (SSP))

111 1111 = -64 x Tsys
...
011 1111 = 63 x Tsys
...
000 0000 = 0 x Tsys

bit 7-6

Unimplemented: Read as '0'

bit 5-0

TDCV<5:0>: Transmitter Delay Compensation Value bits (Secondary Sample Point (SSP))
11 1111 = FP
...
00 0000 = 0 x FP
```

Note 1: This register can only be modified in Configuration mode (OPMOD<2:0> = 100).

REGISTER 11-9: C1TBCH: CAN TIME BASE COUNTER REGISTER HIGH^(1,2)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			TBC<3	1:24>			
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | TBC<2 | 3:16> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 TBC<31:16> CAN Time Base Counter bits

This is a free-running timer that increments every TBCPREx clock when TBCEN is set.

Note 1: The Time Base Counter (TBC) will be stopped and reset when TBCEN = 0 to save power.

2: The TBC prescaler count will be reset on any write to C1TBCH/L (TBCPREx will be unaffected).

REGISTER 11-10: C1TBCL: CAN TIME BASE COUNTER REGISTER LOW^(1,2)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
TBC<15:8>								
bit 15							bit 8	

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | TBC< | 7:0> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **TBC<15:0>** CAN Time Base Counter bits

This is a free-running timer that increments every TBCPREx clock when TBCEN is set.

Note 1: The TBC will be stopped and reset when TBCEN = 0 to save power.

2: The TBC prescaler count will be reset on any write to C1TBCH/L (TBCPREx will be unaffected).

REGISTER 11-11: C1TSCONH: CAN TIMESTAMP CONTROL REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	TSRES	TSEOF	TBCEN
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-3 **Unimplemented:** Read as '0'

bit 2 TSRES: Timestamp Reset bit (CAN FD frames only)

1 = At sample point of the bit following the FDF bit

0 = At sample point of Start-of-Frame (SOF)

bit 1 TSEOF: Timestamp End-of-Frame (EOF) bit

1 = Timestamp when frame is taken valid (11898-1 10.7):

- RX no error until last, but one bit of EOF

- TX no error until the end of EOF

0 = Timestamp at "beginning" of frame:

- Classical Frame: At sample point of SOF

- FD Frame: See TSRES bit

bit 0 TBCEN: Time Base Counter Enable bit

1 = Enables TBC

0 = Stops and resets TBC

REGISTER 11-12: C1TSCONL: CAN TIMESTAMP CONTROL REGISTER LOW

	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
	_	_	_	_	_	_	TBCPRE<9:8>	
k	oit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
TBCPRE<7:0>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 TBCPRE<9:0>: CAN Time Base Counter Prescaler bits

1023 = TBC increments every 1024 clocks

. . .

0 = TBC increments every 1 clock

REGISTER 11-13: C1VECH: CAN INTERRUPT CODE REGISTER HIGH

U-0	R-1	R-0	R-0	R-0	R-0	R-0	R-0
_			1	RXCODE<6:0>	>		
bit 15							bit 8

U-0	R-1	R-0	R-0	R-0	R-0	R-0	R-0			
_		TXCODE<6:0>								
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-8 **RXCODE<6:0>:** Receive Interrupt Flag Code bits

1000001-1111111 = Reserved

1000000 **= No interrupt**

0001000-0111111 = Reserved

0000111 = FIFO 7 interrupt (RFIF7 is set)

. . .

0000010 = FIFO 2 interrupt (RFIF2 is set) 0000001 = FIFO 1 interrupt (RFIF1 is set)

0000000 = Reserved; FIFO 0 cannot receive

bit 7 **Unimplemented:** Read as '0'

bit 6-0 **TXCODE<6:0>:** Transmit Interrupt Flag Code bits

1000001-1111111 = Reserved

1000000 **= No interrupt**

0001000-0111111 = Reserved

0000111 = FIFO 7 interrupt (TFIF7 is set)

. . .

0000001 = FIFO 1 interrupt (TFIF1 is set)

0000000 = FIFO 0 interrupt (TFIF0 is set)

REGISTER 11-14: C1VECL: CAN INTERRUPT CODE REGISTER LOW

U-0	U-0	U-0	R-0	R-0	R-0	R-0	R-0
_	_	_			FILHIT<4:0>		
bit 15							bit 8

U-0	R-1	R-0	R-0	R-0	R-0	R-0	R-0
_				ICODE<6:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 **Unimplemented:** Read as '0'

bit 12-8 FILHIT<4:0>: Filter Hit Number bits

01111 = Filter 15 01110 = Filter 14

00001 = Filter 1

00000 = Filter 0

bit 7 **Unimplemented:** Read as '0'

bit 6-0 **ICODE<6:0>:** Interrupt Flag Code bits

1001011-1111111 = Reserved

1001010 = Transmit attempt interrupt (any bit in C1TXATIF is set)

1001001 = Transmit event FIFO interrupt (any bit in C1TEFSTA is set)

1001000 = Invalid message occurred (IVMIF/IE)

1000111 = CAN module mode change occurred (MODIF/IE)

1000110 = CAN timer overflow (TBCIF/IE)

1000101 = RX/TX MAB overflow/underflow (RX: Message received before previous message was

saved to memory; TX: Can't feed TX MAB fast enough to transmit consistent data)

1000100 = Address error interrupt (illegal FIFO address presented to system)

1000011 = Receive FIFO overflow interrupt (any bit in C1RXOVIF is set)

1000010 = Wake-up interrupt (WAKIF/WAKIE)

1000001 = Error interrupt (CERRIF/IE)

1000000 = **No** interrupt

0001000-0111111 = Reserved

0000111 = FIFO 7 interrupt (TFIF7 or RFIF7 is set)

. .

0000001 = FIFO 1 interrupt (TFIF1 or RFIF1 is set)

0000000 = FIFO 0 interrupt (TFIF0 is set)

REGISTER 11-15: C1INTH: CAN INTERRUPT REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0
IVMIE	WAKIE	CERRIE	SERRIE	RXOVIE	TXATIE	_	_
bit 15							bit 8

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	TEFIE	MODIE	TBCIE	RXIE	TXIE
bit 7							bit 0

Legend	:
--------	---

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **IVMIE:** Invalid Message Interrupt Enable bit

1 = Invalid message interrupt is enabled

0 = Invalid message interrupt is disabled

bit 14 WAKIE: Bus Wake-up Activity Interrupt Enable bit

1 = Wake-up activity interrupt is enabled

0 = Wake-up Activity Interrupt is disabled

bit 13 CERRIE: CAN Bus Error Interrupt Enable bit

1 = CAN bus error interrupt is enabled 0 = CAN bus error interrupt is disabled

bit 12 SERRIE: System Error Interrupt Enable bit

1 = System error interrupt is enabled

0 = System error interrupt is disabled

bit 11 RXOVIE: Receive Buffer Overflow Interrupt Enable bit

1 = Receive buffer overflow interrupt is enabled

0 = Receive buffer overflow interrupt is disabled

bit 10 **TXATIE:** Transmit Attempt Interrupt Enable bit

1 = Transmit attempt interrupt is enabled

0 = Transmit attempt interrupt is disabled

bit 9-5 **Unimplemented:** Read as '0'

bit 4 **TEFIE:** Transmit Event FIFO Interrupt Enable bit

1 = Transmit event FIFO interrupt is enabled

0 = Transmit event FIFO interrupt is disabled

bit 3 MODIE: Mode Change Interrupt Enable bit

1 = Mode change interrupt is enabled

0 = Mode change interrupt is disabled

bit 2 TBCIE: CAN Timer Interrupt Enable bit

1 = CAN timer interrupt is enabled

0 = CAN timer interrupt is disabled

RXIE: Receive Object Interrupt Enable bit

1 = Receive object interrupt is enabled

0 = Receive object interrupt is disabled

bit 0 **TXIE:** Transmit Object Interrupt Enable bit

1 = Transmit object interrupt is enabled

0 = Transmit object interrupt is disabled

bit 1

REGISTER 11-16: C1INTL: CAN INTERRUPT REGISTER LOW

HS/C-0	HS/C-0	HS/C-0	HS/C-0	R-0	R-0	U-0	U-0
IVMIF ⁽¹⁾	WAKIF ⁽¹⁾	CERRIF ⁽¹⁾	SERRIF ⁽¹⁾	RXOVIF	TXATIF	_	_
bit 15							bit 8

U-0	U-0	U-0	R-0	HS/C-0	HS/C-0	R-0	R-0
_	_	_	TEFIF	MODIF ⁽¹⁾	TBCIF ⁽¹⁾	RXIF	TXIF
bit 7							bit 0

Legend:	C = Clearable bit	HS = Hardware Settable	HS = Hardware Settable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15	IVMIF: Invalid Message Interrupt Flag bit ⁽¹⁾
	1 = Invalid message interrupt occurred
	0 = No invalid message interrupt occurred
bit 14	WAKIF: Bus Wake-up Activity Interrupt Flag bit ⁽¹⁾
	1 = Wake-up activity interrupt occurred
h:: 40	0 = No wake-up activity interrupt occurred
bit 13	CERRIF: CAN Bus Error Interrupt Flag bit ⁽¹⁾ 1 = CAN bus error interrupt occurred
	0 = No CAN bus error interrupt occurred
bit 12	SERRIF: System Error Interrupt Flag bit ⁽¹⁾
	1 = System error interrupt occurred
	0 = No system error interrupt occurred
bit 11	RXOVIF: Receive Buffer Overflow Interrupt Flag bit
	1 = Receive buffer overflow interrupt occurred
	0 = No receive buffer overflow interrupt occurred
bit 10	TXATIF: Transmit Attempt Interrupt Flag bit
	1 = Transmit attempt interrupt occurred0 = No transmit attempt Interrupt occurred
bit 9-5	Unimplemented: Read as '0'
bit 4	TEFIF: Transmit Event FIFO Interrupt Flag bit
DIL 4	1 = Transmit event FIFO interrupt occurred
	0 = No transmit event FIFO interrupt occurred
bit 3	MODIF: CAN Mode Change Interrupt Flag bit ⁽¹⁾
	1 = CAN module mode change occurred (OPMOD<2:0> have changed to reflect REQOP<2:0>)
	0 = No mode change occurred
bit 2	TBCIF: CAN Timer Overflow Interrupt Flag bit ⁽¹⁾
	1 = TBC has overflowed
1.11.4	0 = TBC has not overflowed
bit 1	RXIF: Receive Object Interrupt Flag bit
	1 = Receive object interrupt is pending0 = No receive object interrupts are pending
bit 0	TXIF: Transmit Object Interrupt Flag bit
2.0	1 = Transmit object interrupt is pending
	0 = No transmit object interrupts are pending

Note 1: C1INTL: Flags are set by hardware and cleared by application.

REGISTER 11-17: C1RXIFH: CAN RECEIVE INTERRUPT STATUS REGISTER HIGH⁽¹⁾

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
	RFIF<31:24>								
bit 15 bit 8									

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0			
	RFIF<23:16>									
bit 7										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 RFIF<31:16>: Unimplemented

Note 1: C1RXIFH: FIFO: RFIFx = 'or' of enabled RX FIFO flags (flags need to be cleared in the FIFO register).

REGISTER 11-18: C1RXIFL: CAN RECEIVE INTERRUPT STATUS REGISTER LOW(1)

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
	RFIF<15:8>								
bit 15									

R-0	R-0	R-0	R-0	R-0	R-0	R-0	U-0
			RFIF<7:1>				_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 RFIF<15:8>: Unimplemented

bit 7-1 RFIF<7:1>: Receive FIFO Interrupt Pending bits

1 = One or more enabled receive FIFO interrupts are pending

0 = No enabled receive FIFO interrupts are pending

bit 0 **Unimplemented:** Read as '0'

Note 1: C1RXIFL: FIFO: RFIFx = 'or' of enabled RX FIFO flags (flags need to be cleared in the FIFO register).

REGISTER 11-19: C1RXOVIFH: CAN RECEIVE OVERFLOW INTERRUPT STATUS REGISTER HIGH⁽¹⁾

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	
RFOVIF<31:24>								
bit 15								

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	
RFOVIF<23:16>								
bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 RFOVIF<31:16>: Unimplemented

Note 1: C1RXOVIFH: FIFO: RFOVIFx (flag needs to be cleared in the FIFO register).

REGISTER 11-20: C1RXOVIFL: CAN RECEIVE OVERFLOW INTERRUPT STATUS REGISTER LOW(1)

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	
RFOVIF<15:8>								
bit 15		bit 8						

R-0	R-0	R-0	R-0	R-0	R-0	R-0	U-0
		1	RFOVIF<7:1>				_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **RFOVIF<15:8>:** Unimplemented

bit 7-1 Receive FIFO Overflow Interrupt Pending bits

1 = Interrupt is pending 0 = Interrupt is not pending

bit 0 **Unimplemented:** Read as '0'

Note 1: C1RXOVIFL: FIFO: RFOVIFx (flag needs to be cleared in the FIFO register).

REGISTER 11-21: C1TXIFH: CAN TRANSMIT INTERRUPT STATUS REGISTER HIGH⁽¹⁾

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
	TFIF<31:24>								
bit 15									

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
	TFIF<23:16>								
bit 7		bit 0							

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 TFIF<31:16>: Unimplemented

Note 1: C1TXIFH: FIFO: TFIFx = 'or' of the enabled TX FIFO flags (flags need to be cleared in the FIFO register).

REGISTER 11-22: C1TXIFL: CAN TRANSMIT INTERRUPT STATUS REGISTER LOW(1)

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
TFIF<15:8>							
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
TFIF<7:0> ⁽²⁾							
bit 7					bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 TFIF<15:8>: Unimplemented

bit 7-0 TFIF<7:0>: Transmit FIFO/TXQ Interrupt Pending bits⁽²⁾

1 = One or more enabled transmit FIFO/TXQ interrupts are pending

0 = No enabled transmit FIFO/TXQ interrupts are pending

Note 1: C1TXIFL: FIFO: TFIFx = 'or' of the enabled TX FIFO flags (flags need to be cleared in the FIFO register).

2: TFIF0 is for the transmit queue.

REGISTER 11-23: C1TXATIFH: CAN TRANSMIT ATTEMPT INTERRUPT STATUS REGISTER HIGH⁽¹⁾

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			TFATIF<	:31:24>			
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			TFATIF<	<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 TFATIF<31:16>: Unimplemented

Note 1: C1TXATIFH: FIFO: TFATIFx (flag needs to be cleared in the FIFO register).

REGISTER 11-24: C1TXATIFL: CAN TRANSMIT ATTEMPT INTERRUPT STATUS REGISTER LOW(1)

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
TFATIF<15:8>							
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			TFATIF<	<7:0> ⁽²⁾			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 TFATIF<15:8>: Unimplemented

bit 7-0 **TFATIF<7:0>:** Transmit FIFO/TXQ Attempt Interrupt Pending bits⁽²⁾

1 = Interrupt is pending0 = Interrupt is not pending

Note 1: C1TXATIFL: FIFO: TFATIFx (flag needs to be cleared in the FIFO register).

2: TFATIF0 is for the transmit queue.

REGISTER 11-25: C1TXREQH: CAN TRANSMIT REQUEST REGISTER HIGH

S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0
TXREQ<31:24>							
bit 15							bit 8

S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0
TXREQ<23:16>							
bit 7 bi							bit 0

Legend:	S = Settable bit	HC = Hardware Cleara	ble bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15-0 **TXREQ<31:16>:** Unimplemented

REGISTER 11-26: C1TXREQL: CAN TRANSMIT REQUEST REGISTER LOW

S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0
TXREQ<15:8>							
bit 15							bit 8

S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0	S/HC-0
		-	TXREQ<7:1>				TXREQ0
bit 7							bit 0

Legend:	S = Settable bit	HC = Hardware Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15-8 **TXREQ<15:8>:** Unimplemented

bit 7-1 **TXREQ<7:1>:** Message Send Request bits

TXEN = 1 (object configured as a transmit object):

Setting this bit to '1' requests sending a message. The bit will automatically clear when the message(s) queued in the object is (are) successfully sent. This bit can NOT be used for aborting a transmission.

TXEN = 0 (object configured as a receive object):

This bit has no effect.

bit 0 TXREQ0: Transmit Queue Message Send Request bit

Setting this bit to '1' requests sending a message. The bit will automatically clear when the message(s) queued in the object is (are) successfully sent. This bit can NOT be used for aborting a transmission.

REGISTER 11-27: C1FIFOBAH: CAN MESSAGE MEMORY BASE ADDRESS REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
FIFOBA<31:24>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
FIFOBA<23:16>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FIFOBA<31:16>: Message Memory Base Address bits

Defines the base address for the transmit event FIFO followed by the message objects.

REGISTER 11-28: C1FIFOBAL: CAN MESSAGE MEMORY BASE ADDRESS REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
FIFOBA<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R-0	R-0		
FIFOBA<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FIFOBA<15:0>: Message Memory Base Address bits

Defines the base address for the transmit event FIFO followed by the message objects.

REGISTER 11-29: C1TXQCONH: CAN TRANSMIT QUEUE CONTROL REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PLSIZE2 ⁽¹⁾	PLSIZE1 ⁽¹⁾	PLSIZE0 ⁽¹⁾	FSIZE4 ⁽¹⁾	FSIZE3 ⁽¹⁾	FSIZE2 ⁽¹⁾	FSIZE1 ⁽¹⁾	FSIZE0 ⁽¹⁾
bit 15							bit 8

U-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	TXAT1	TXAT0	TXPRI4	TXPRI3	TXPRI2	TXPRI1	TXPRI0
bit 7							bit 0

Legend:R = Readable bitW = Writable bitU = Unimplemented bit, read as '0'-n = Value at POR'1' = Bit is set'0' = Bit is clearedx = Bit is unknown

bit 15-13 PLSIZE<2:0>: Payload Size bits⁽¹⁾

111 = 64 data bytes

110 = 48 data bytes

101 = 32 data bytes

100 = 24 data bytes

011 = 20 data bytes 010 = 16 data bytes 001 = 12 data bytes

000 = 8 data bytes

bit 12-8 **FSIZE<4:0>:** FIFO Size bits⁽¹⁾

11111 = FIFO is 32 messages deep

...
00010 = FIFO is 3 messages deep
00001 = FIFO is 2 messages deep
00000 = FIFO is 1 message deep

bit 7 **Unimplemented:** Read as '0'

bit 6-5 **TXAT<1:0>:** Retransmission Attempts bits

This feature is enabled when RTXAT (C1CONH<0>) is set.

11 = Unlimited number of retransmission attempts10 = Unlimited number of retransmission attempts

01 = Three retransmission attempts00 = Disables retransmission attempts

bit 4-0 **TXPRI<4:0>:** Message Transmit Priority bits

11111 = Highest message priority

0000

00000 = Lowest message priority

REGISTER 11-30: C1TXQCONL: CAN TRANSMIT QUEUE CONTROL REGISTER LOW

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	FRESET	TXREQ	UINC
bit 15							bit 8

R-0	U-0	U-0	R/W-0	U-0	R/W-0	U-0	R/W-0
TXEN	_	_	TXATIE	_	TXQEIE	_	TXQNIE
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 **Unimplemented:** Read as '0'

bit 10 FRESET: FIFO Reset bit

1 = FIFO will be reset when bit is set, cleared by hardware when FIFO is reset; user should poll

whether this bit is clear before taking any action

0 = No effect

bit 9 TXREQ: Message Send Request bit

1 = Requests sending a message; the bit will automatically clear when all the messages queued in

the TXQ are successfully sent

0 = Clearing the bit to '0' while set ('1') will request a message abort

bit 8 UINC: Increment Head/Tail bit

When this bit is set, the FIFO head will increment by a single message.

bit 7 TXEN: TX Enable bit

bit 6-5 **Unimplemented:** Read as '0'

bit 4 **TXATIE:** Transmit Attempts Exhausted Interrupt Enable bit

1 = Enables interrupt0 = Disables interrupt

bit 3 **Unimplemented:** Read as '0'

bit 2 **TXQEIE:** Transmit Queue Empty Interrupt Enable bit

1 = Interrupt is enabled for TXQ empty0 = Interrupt is disabled for TXQ empty

bit 1 **Unimplemented:** Read as '0'

bit 0 **TXQNIE:** Transmit Queue Not Full Interrupt Enable bit

1 = Interrupt is enabled for TXQ not full0 = Interrupt is disabled for TXQ not full

REGISTER 11-31: C1TXQSTA: CAN TRANSMIT QUEUE STATUS REGISTER

U-0	U-0	U-0	R-0	R-0	R-0	R-0	R-0
_	_	_	TXQCI4 ⁽¹⁾	TXQCI3 ⁽¹⁾	TXQCI2 ⁽¹⁾	TXQCI1 ⁽¹⁾	TXQCI0 ⁽¹⁾
bit 15							bit 8

R-0	R-0	R-0	C/HS-0	U-0	R-1	U-0	R-1
TXABT ⁽²⁾	TXLARB	TXERR	TXATIF	_	TXQEIF	_	TXQNIF
bit 7							bit 0

Legend:	C = Clearable bit	HS = Hardware Settabl	e bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown			

bit 15-13 **Unimplemented:** Read as '0'

bit 12-8 **TXQCI<4:0>:** Transmit Message Queue Index bits⁽¹⁾

A read of this register will return an index to the message that the FIFO will next attempt to transmit.

bit 7 **TXABT:** Message Aborted Status bit⁽²⁾

1 = Message was aborted

0 = Message completed successfully

bit 6 TXLARB: Message Lost Arbitration Status bit

1 = Message lost arbitration while being sent

 \circ = Message did not lose arbitration while being sent

bit 5 TXERR: Error Detected During Transmission bit

1 = A bus error occurred while the message was being sent

0 = A bus error did not occur while the message was being sent

bit 4 **TXATIF:** Transmit Attempts Exhausted Interrupt Pending bit

1 = Interrupt is pending

0 = Interrupt is not pending

bit 3 **Unimplemented:** Read as '0'

bit 2 TXQEIF: Transmit Queue Empty Interrupt Flag bit

1 = TXQ is empty

0 = TXQ is not empty, at least 1 message is queued to be transmitted

bit 1 **Unimplemented:** Read as '0'

bit 0 TXQNIF: Transmit Queue Not Full Interrupt Flag bit

1 = TXQ is not full

0 = TXQ is full

Note 1: The TXQCI<4:0> bits give a zero-indexed value to the message in the TXQ. If the TXQ is four messages deep (FSIZE<4:0> = 3), TXQCIx will take on a value of 0 to 3, depending on the state of the TXQ.

2: This bit is updated when a message completes (or aborts) or when the TXQ is reset.

REGISTER 11-32: C1FIFOCONHx: CAN FIFO CONTROL REGISTER x (x = 1 TO 7) HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PLSIZE2 ⁽¹⁾	PLSIZE1 ⁽¹⁾	PLSIZE0 ⁽¹⁾	FSIZE4 ⁽¹⁾	FSIZE3 ⁽¹⁾	FSIZE2 ⁽¹⁾	FSIZE1 ⁽¹⁾	FSIZE0 ⁽¹⁾
bit 15							bit 8

U-0	R/W-1	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	TXAT1	TXAT0	TXPRI4	TXPRI3	TXPRI2	TXPRI1	TXPRI0
bit 7							bit 0

Legend:						
R = Readable bit	= Readable bit W = Writable bit U = Unimplemented bit, read as '0'					
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown			

```
PLSIZE<2:0>: Payload Size bits(1)
bit 15-13
               111 = 64 data bytes
               110 = 48 data bytes
               101 = 32 data bytes
               100 = 24 data bytes
               011 = 20 data bytes
               010 = 16 data bytes
               001 = 12 data bytes
               000 = 8 data bytes
              FSIZE<4:0>: FIFO Size bits<sup>(1)</sup>
bit 12-8
               11111 = FIFO is 32 messages deep
               00010 = FIFO is 3 messages deep
               00001 = FIFO is 2 messages deep
               00000 = FIFO is 1 message deep
bit 7
               Unimplemented: Read as '0'
bit 6-5
               TXAT<1:0>: Retransmission Attempts bits
              This feature is enabled when RTXAT (C1CONH<0>) is set.
               11 = Unlimited number of retransmission attempts
               10 = Unlimited number of retransmission attempts
               01 = Three retransmission attempts
               00 = Disables retransmission attempts
bit 4-0
              TXPRI<4:0>: Message Transmit Priority bits
               11111 = Highest message priority
               00000 = Lowest message priority
```

Note 1: These bits can only be modified in Configuration mode (OPMOD<2:0> = 100).

REGISTER 11-33: C1FIFOCONLx: CAN FIFO CONTROL REGISTER x (x = 1 TO 7) LOW

U-0	U-0	U-0	U-0	U-0	S/HC-1	R/W/HC-0	S/HC-0
_	_	_	_	_	FRESET	TXREQ	UINC
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TXEN	RTREN	RXTSEN ⁽¹⁾	TXATIE	RXOVIE	TFERFFIE	TFHRFHIE	TFNRFNIE
bit 7							bit 0

Legend:	S = Settable bit	HC = Hardware Clearable bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15-11 **Unimplemented:** Read as '0'

bit 10 FRESET: FIFO Reset bit

1 = FIFO will be reset when bit is set, cleared by hardware when FIFO is reset; user should poll whether this bit is clear before taking any action

0 = No effect

bit 9 **TXREQ:** Message Send Request bit

TXEN = 1 (FIFO configured as a transmit FIFO):

1 = Requests sending a message; the bit will automatically clear when all the messages queued in the FIFO are successfully sent

0 = Clearing the bit to '0' while set ('1') will request a message abort

TXEN = 0 (FIFO configured as a receive FIFO):

This bit has no effect.

bit 8 UINC: Increment Head/Tail bit

TXEN = 1 (FIFO configured as a transmit FIFO):

When this bit is set, the FIFO head will increment by a single message.

TXEN = 0 (FIFO configured as a receive FIFO):

When this bit is set, the FIFO tail will increment by a single message.

bit 7 TXEN: TX/RX Buffer Selection bit

1 = Transmits message object

0 = Receives message object

bit 6 RTREN: Auto-Remote Transmit (RTR) Enable bit

1 = When a Remote Transmit is received, TXREQ will be set

0 = When a Remote Transmit is received, TXREQ will be unaffected

bit 5 **RXTSEN:** Received Message Timestamp Enable bit (1)

1 = Captures timestamp in received message object in RAM

0 = Does not capture timestamp

bit 4 **TXATIE:** Transmit Attempts Exhausted Interrupt Enable bit

1 = Enables interrupt

0 = Disables interrupt

bit 3 **RXOVIE:** Overflow Interrupt Enable bit

1 = Interrupt is enabled for overflow event

0 = Interrupt is disabled for overflow event

REGISTER 11-33: C1FIFOCONLx: CAN FIFO CONTROL REGISTER x (x = 1 TO 7) LOW (CONTINUED)

bit 2 TFERFFIE: Transmit/Receive FIFO Empty/Full Interrupt Enable bit

TXEN = 1 (FIFO configured as a transmit FIFO):

Transmit FIFO Empty Interrupt Enable

1 = Interrupt is enabled for FIFO empty

0 = Interrupt is disabled for FIFO empty

TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Full Interrupt Enable 1 = Interrupt is enabled for FIFO full 0 = Interrupt is disabled for FIFO full

bit 1 TFHRFHIE: Transmit/Receive FIFO Half Empty/Half Full Interrupt Enable bit

TXEN = 1 (FIFO configured as a transmit FIFO):
Transmit FIFO Half Empty Interrupt Enable
1 = Interrupt is enabled for FIFO half empty
0 = Interrupt is disabled for FIFO half empty
TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Half Full Interrupt Enable

1 = Interrupt is enabled for FIFO half full

0 = Interrupt is disabled for FIFO half full

bit 0 TFNRFNIE: Transmit/Receive FIFO Not Full/Not Empty Interrupt Enable bit

TXEN = 1 (FIFO configured as a transmit FIFO):

Transmit FIFO Not Full Interrupt Enable
1 = Interrupt is enabled for FIFO not full
0 = Interrupt is disabled for FIFO not full

TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Not Empty Interrupt Enable
1 = Interrupt is enabled for FIFO not empty
0 = Interrupt is disabled for FIFO not empty

REGISTER 11-34: C1FIFOSTAX: CAN FIFO STATUS REGISTER x (x = 1 TO 7)

U-0	U-0	U-0	R-0	R-0	R-0	R-0	R-0
_	_	_	FIFOCI4 ⁽¹⁾	FIFOCI3 ⁽¹⁾	FIFOCI2 ⁽¹⁾	FIFOCI1 ⁽¹⁾	FIFOCI0 ⁽¹⁾
bit 15							bit 8

R-0	R-0	R-0	C/HS-0	C/HS-0	R-0	R-0	R-0
TXABT ⁽³⁾	TXLARB ⁽²⁾	TXERR ⁽²⁾	TXATIF	RXOVIF	TFERFFIF	TFHRFHIF	TFNRFNIF
bit 7							bit 0

Legend: C = Clearable bit		HS = Hardware Settable bit				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'				
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared $x = I$	Bit is unknown			

bit 15-13 **Unimplemented:** Read as '0'

bit 12-8 FIFOCI<4:0>: FIFO Message Index bits⁽¹⁾

TXEN = 1 (FIFO configured as a transmit buffer):

A read of this register will return an index to the message that the FIFO will next attempt to transmit.

TXEN = 0 (FIFO configured as a receive buffer):

A read of this register will return an index to the message that the FIFO will use to save the next

message.

bit 7 **TXABT:** Message Aborted Status bit⁽³⁾

1 = Message was aborted

0 = Message completed successfully

bit 6 TXLARB: Message Lost Arbitration Status bit (2)

1 = Message lost arbitration while being sent

0 = Message did not lose arbitration while being sent

bit 5 **TXERR:** Error Detected During Transmission bit⁽²⁾

1 = A bus error occurred while the message was being sent

0 = A bus error did not occur while the message was being sent

bit 4 **TXATIF:** Transmit Attempts Exhausted Interrupt Pending bit

TXEN = 1 (FIFO configured as a transmit buffer):

1 = Interrupt is pending

0 = Interrupt is not pending

TXEN = 0 (FIFO configured as a receive buffer):

Unused, read as '0'.

bit 3 RXOVIF: Receive FIFO Overflow Interrupt Flag bit

TXEN = 1 (FIFO configured as a transmit buffer):

Unused, read as '0'.

TXEN = 0 (FIFO configured as a receive buffer):

1 = Overflow event has occurred

0 = No overflow event has occurred

Note 1: FIFOCI<4:0> gives a zero-indexed value to the message in the FIFO. If the FIFO is 4 messages deep (FSIZE<4:0> = 3), FIFOCIx will take on a value of 0 to 3, depending on the state of the FIFO.

2: These bits are updated when a message completes (or aborts) or when the FIFO is reset.

3: This bit is reset on any read of this register or when the TXQ is reset. The bits are cleared when TXREQ is set or using an SPI write.

REGISTER 11-34: C1FIFOSTAX: CAN FIFO STATUS REGISTER x (x = 1 TO 7) (CONTINUED)

bit 2 TFERFFIF: Transmit/Receive FIFO Empty/Full Interrupt Flag bit

TXEN = 1 (FIFO configured as a transmit FIFO):

Transmit FIFO Empty Interrupt Flag

1 = FIFO is empty

0 = FIFO is not empty, at least 1 message is queued to be transmitted

TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Full Interrupt Flag

1 = FIFO is full

0 = FIFO is not full

bit 1 TFHRFHIF: Transmit/Receive FIFO Half Empty/Half Full Interrupt Flag bit

TXEN = 1 (FIFO configured as a transmit FIFO):

Transmit FIFO Half Empty Interrupt Flag

1 = FIFO is \leq half full

0 = FIFO is > half full

TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Half Full Interrupt Flag

1 = FIFO is \geq half full

0 = FIFO is < half full

bit 0 TFNRFNIF: Transmit/Receive FIFO Not Full/Not Empty Interrupt Flag bit

TXEN = 1 (FIFO configured as a transmit FIFO):

Transmit FIFO Not Full Interrupt Flag

1 = FIFO is not full

0 = FIFO is full

TXEN = 0 (FIFO configured as a receive FIFO):

Receive FIFO Not Empty Interrupt Flag

1 = FIFO is not empty, has at least 1 message

0 = FIFO is empty

- **Note 1:** FIFOCI<4:0> gives a zero-indexed value to the message in the FIFO. If the FIFO is 4 messages deep (FSIZE<4:0> = 3), FIFOCIx will take on a value of 0 to 3, depending on the state of the FIFO.
 - 2: These bits are updated when a message completes (or aborts) or when the FIFO is reset.
 - 3: This bit is reset on any read of this register or when the TXQ is reset. The bits are cleared when TXREQ is set or using an SPI write.

REGISTER 11-35: C1TEFCONH: CAN TRANSMIT EVENT FIFO CONTROL REGISTER HIGH

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_			FSIZE<4:0>(1)	
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 **Unimplemented:** Read as '0' bit 12-8 **FSIZE<4:0>:** FIFO Size bits⁽¹⁾

11111 = FIFO is 32 messages deep

. . .

00010 = FIFO is 3 messages deep 00001 = FIFO is 2 messages deep 00000 = FIFO is 1 message deep

bit 7-0 **Unimplemented:** Read as '0'

REGISTER 11-36: C1TEFCONL: CAN TRANSMIT EVENT FIFO CONTROL REGISTER LOW

U-0	U-0	U-0	U-0	U-0	S/HC-0	U-0	S/HC-0
_	_	_	_	_	FRESET	_	UINC
bit 15							bit 8

U-0	U-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	TEFTSEN ⁽¹⁾	_	TEFOVIE	TEFFIE	TEFHIE	TEFNEIE
bit 7							bit 0

Legend:	S = Settable bit	HC = Hardware Clearable bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15-11 **Unimplemented:** Read as '0' bit 10 **FRESET:** FIFO Reset bit

1 = FIFO will be reset when bit is set, cleared by hardware when FIFO is reset; the user should poll

whether this bit is clear before taking any action

0 = No effect

bit 9 **Unimplemented:** Read as '0'

bit 8 UINC: Increment Tail bit

1 = When this bit is set, the FIFO tail will increment by a single message

0 = FIFO tail will not increment

bit 7-6 **Unimplemented:** Read as '0'

bit 5 **TEFTSEN:** Transmit Event FIFO Timestamp Enable bit⁽¹⁾

1 = Timestamps elements in TEF

0 = Does not timestamp elements in TEF

bit 4 Unimplemented: Read as '0'

bit 3 **TEFOVIE:** Transmit Event FIFO Overflow Interrupt Enable bit

1 = Interrupt is enabled for overflow event0 = Interrupt is disabled for overflow event

bit 2 **TEFFIE:** Transmit Event FIFO Full Interrupt Enable bit

1 = Interrupt is enabled for FIFO full0 = Interrupt is disabled for FIFO full

bit 1 **TEFHIE:** Transmit Event FIFO Half Full Interrupt Enable bit

1 = Interrupt is enabled for FIFO half full 0 = Interrupt is disabled for FIFO half full

bit 0 **TEFNEIE**: Transmit Event FIFO Not Empty Interrupt Enable bit

1 = Interrupt is enabled for FIFO not empty0 = Interrupt is disabled for FIFO not empty

REGISTER 11-37: C1TEFSTA: CAN TRANSMIT EVENT FIFO STATUS REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	S/HC-0	R-0	R-0	R-0
_	_	_	_	TEFOVIF	TEFFIF ⁽¹⁾	TEFHIF ⁽¹⁾	TEFNEIF ⁽¹⁾
bit 7							bit 0

Legend:	d: HC = Hardware Clearable bit S = Settable bit Can Set by '1'		'1'	
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15-4 Unimplemented: Read as '0'

bit 3 **TEFOVIF:** Transmit Event FIFO Overflow Interrupt Flag bit

1 = Overflow event has occurred0 = No overflow event has occurred

bit 2 **TEFFIF:** Transmit Event FIFO Full Interrupt Flag bit⁽¹⁾

1 = FIFO is full 0 = FIFO is not full

bit 1 **TEFHIF:** Transmit Event FIFO Half Full Interrupt Flag bit⁽¹⁾

1 = FIFO is \geq half full 0 = FIFO is < half full

bit 0 **TEFNEIF:** Transmit Event FIFO Not Empty Interrupt Flag bit⁽¹⁾

1 = FIFO is not empty 0 = FIFO is empty

Note 1: These bits are read-only and reflect the status of the FIFO.

REGISTER 11-38: C1FIFOUAHx: CAN FIFO USER ADDRESS REGISTER x (x = 1 TO 7) HIGH⁽¹⁾

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
	FIFOUA<31:24>								
bit 15							bit 8		

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x	
FIFOUA<23:16>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FIFOUA<31:16>: FIFO User Address bits

TXEN = 1 (FIFO configured as a transmit buffer):

A read of this register will return the address where the next message is to be written (FIFO head).

TXEN = 0 (FIFO configured as a receive buffer):

A read of this register will return the address where the next message is to be read (FIFO tail).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-39: C1FIFOUALx: CAN FIFO USER ADDRESS REGISTER x (x = 1 TO 7) LOW⁽¹⁾

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x	
FIFOUA<15:8>								
bit 15							bit 8	

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
	FIFOUA<7:0>								
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FIFOUA<15:0>: FIFO User Address bits

TXEN = 1 (FIFO configured as a transmit buffer):

A read of this register will return the address where the next message is to be written (FIFO head).

TXEN = 0 (FIFO configured as a receive buffer):

A read of this register will return the address where the next message is to be read (FIFO tail).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-40: C1TEFUAH: CAN TRANSMIT EVENT FIFO USER ADDRESS REGISTER HIGH⁽¹⁾

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x
			TEFUA<	31:24>			
bit 15							bit 8

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x	
TEFUA<23:16>								
bit 7 bit								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **TEFUA<31:16>:** Transmit Event FIFO User Address bits

A read of this register will return the address where the next event is to be read (FIFO tail).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-41: C1TEFUAL: CAN TRANSMIT EVENT FIFO USER ADDRESS REGISTER LOW(1)

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x	
TEFUA<15:8>								
bit 15 bi								

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
TEFUA<7:0>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **TEFUA<15:0>:** Transmit Event FIFO User Address bits

A read of this register will return the address where the next event is to be read (FIFO tail).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-42: C1TXQUAH: CAN TRANSMIT QUEUE USER ADDRESS REGISTER HIGH⁽¹⁾

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
TXQUA<31:24>									
bit 15							bit 8		

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
TXQUA<23:16>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **TXQUA<31:16>:** TXQ User Address bits

A read of this register will return the address where the next message is to be written (TXQ head).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-43: C1TXQUAL: CAN TRANSMIT QUEUE USER ADDRESS REGISTER LOW(1)

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
TXQUA<15:8>									
bit 15									

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
TXQUA<7:0>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **TXQUA<15:0>:** TXQ User Address bits

A read of this register will return the address where the next message is to be written (TXQ head).

Note 1: This register is not ensured to read correctly in Configuration mode and should only be accessed when the module is not in Configuration mode.

REGISTER 11-44: C1TRECH: CAN TRANSMIT/RECEIVE ERROR COUNT REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R-1	R-0	R-0	R-0	R-0	R-0
_	_	TXBO	TXBP	RXBP	TXWARN	RXWARN	EWARN
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-6 **Unimplemented:** Read as '0'

bit 5 **TXBO:** Transmitter in Error State Bus Off bit (TERRCNT<7:0> > 255)

In Configuration mode, TXBO is set since the module is not on the bus.

bit 4 **TXBP:** Transmitter in Error State Bus Passive bit (TERRCNT<7:0> > 127)

bit 3 **RXBP:** Receiver in Error State Bus Passive bit (RERRCNT<7:0> > 127)

bit 2 **TXWARN:** Transmitter in Error State Warning bit (128 > TERRCNT<7:0> > 95)

bit 1 RXWARN: Receiver in Error State Warning bit (128 > RERRCNT<7:0> > 95)

bit 0 **EWARN:** Transmitter or Receiver in Error State Warning bit

REGISTER 11-45: C1TRECL: CAN TRANSMIT/RECEIVE ERROR COUNT REGISTER LOW

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
TERRCNT<7:0>									
bit 15									

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
RERRCNT<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **TERRCNT<7:0>:** Transmit Error Counter bits bit 7-0 **RERRCNT<7:0>:** Receive Error Counter bits

REGISTER 11-46: C1BDIAG0H: CAN BUS DIAGNOSTICS REGISTER 0 HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
DTERRCNT<7:0>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
DRERRCNT<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **DTERRCNT<7:0>:** Data Bit Rate Transmit Error Counter bits bit 7-0 **DRERRCNT<7:0>:** Data Bit Rate Receive Error Counter bits

REGISTER 11-47: C1BDIAG0L: CAN BUS DIAGNOSTICS REGISTER 0 LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
NTERRCNT<7:0>										
bit 15							bit 8			

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
NRERRCNT<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **NTERRCNT<7:0>:** Nominal Bit Rate Transmit Error Counter bits bit 7-0 **NRERRCNT<7:0>:** Nominal Bit Rate Receive Error Counter bits

REGISTER 11-48: C1BDIAG1H: CAN BUS DIAGNOSTICS REGISTER 1 HIGH

R/W-0	R/W-0	R/C-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
DLCMM	ESI	DCRCERR	DSTUFERR	DFORMERR	_	DBIT1ERR	DBIT0ERR
bit 15							bit 8

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TXBOERR	_	NCRCERR	NSTUFERR	NFORMERR	NACKERR	NBIT1ERR	NBIT0ERR
bit 7							bit 0

Legend:	C = Clearable bit				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

atch bit
ć

During a transmission or reception, the specified DLC is larger than the PLSIZE<2:0> of the FIFO element.

bit 14 ESI: ESI Flag of a Received CAN FD Message Set bit

bit 13 DCRCERR: Same as for nominal bit rate
bit 12 DSTUFERR: Same as for nominal bit rate
bit 11 DFORMERR: Same as for nominal bit rate

bit 10 **Unimplemented:** Read as '0'

bit 9 **DBIT1ERR:** Same as for nominal bit rate bit 8 **DBIT0ERR:** Same as for nominal bit rate

bit 7 **TXBOERR:** Device Went to Bus Off bit (and auto-recovered)

bit 6 Unimplemented: Read as '0'

bit 5 NCRCERR: Received Message with CRC Incorrect Checksum bit

The CRC checksum of a received message was incorrect. The CRC of an incoming message does not match with the CRC calculated from the received data.

bit 4 NSTUFERR: Received Message with Illegal Sequence bit

More than 5 equal bits in a sequence have occurred in a part of a received message where this is not allowed.

bit 3 NFORMERR: Received Frame Fixed Format bit

A fixed format part of a received frame has the wrong format.

bit 2 NACKERR: Transmitted Message Not Acknowledged bit

Transmitted message was not acknowledged.

bit 1 NBIT1ERR: Transmitted Message Recessive Level bit

During the transmission of a message (with the exception of the arbitration field), the device wanted to send a recessive level (bit of logical value '1'), but the monitored bus value was dominant.

bit 0 NBIT0ERR: Transmitted Message Dominant Level bit

During the transmission of a message (or Acknowledge bit, active error flag or overload flag), the device wanted to send a dominant level (data or identifier bit of logical value '0'), but the monitored bus value was recessive. During bus off recovery, this status is set each time a sequence of 11 recessive bits has been monitored. This enables the CPU to monitor the proceeding of the bus off recovery sequence (indicating the bus is not stuck at dominant or continuously disturbed).

REGISTER 11-49: C1BDIAG1L: CAN BUS DIAGNOSTICS REGISTER 1 LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
EFMSGCNT<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
EFMSGCNT<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **EFMSGCNT<15:0>:** Error Free Message Counter bits

REGISTER 11-50: C1FLTCONxH: CAN FILTER CONTROL REGISTER x HIGH (x = 0 TO 3; c = 2, 6, 10, 14; d = 3, 7, 11, 15)

R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FLTENd	_	_	FdBP4	FdBP3	FdBP2	FdBP1	FdBP0
bit 15							bit 8

R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FLTENc	_	_	FcBP4	FcBP3	FcBP2	FcBP1	FcBP0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 FLTENd: Enable Filter d to Accept Messages bit

1 = Filter is enabled0 = Filter is disabled

bit 14-13 **Unimplemented:** Read as '0'

bit 12-8 **FdBP<4:0>:** Pointer to Object When Filter d Hits bits

11111 to 11000 = Reserved

00111 = Message matching filter is stored in Object 7 00110 = Message matching filter is stored in Object 6

. . .

00010 = Message matching filter is stored in Object 2 00001 = Message matching filter is stored in Object 1

00000 = Reserved; Object 0 is the TX Queue and can't receive messages

bit 7 FLTENc: Enable Filter c to Accept Messages bit

1 = Filter is enabled0 = Filter is disabled

bit 6-5 **Unimplemented:** Read as '0'

bit 4-0 FcBP<4:0>: Pointer to Object When Filter c Hits bits

11111 to 11000 = Reserved

00111 = Message matching filter is stored in Object 7 00110 = Message matching filter is stored in Object 6

. . .

00010 = Message matching filter is stored in Object 2 00001 = Message matching filter is stored in Object 1

00000 = Reserved; Object 0 is the TX Queue and can't receive messages

REGISTER 11-51: C1FLTCONxL: CAN FILTER CONTROL REGISTER x LOW (x = 0 TO 3; a = 0, 4, 8, 12; b = 1, 5, 9, 13)

R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FLTENb	_	_	FbBP4	FbBP3	FbBP2	FbBP1	FbBP0
bit 15							bit 8

R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FLTENa	_	_	FaBP4	FaBP3	FaBP2	FaBP1	FaBP0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 FLTENb: Enable Filter b to Accept Messages bit

1 = Filter is enabled

0 = Filter is disabled

bit 14-13 **Unimplemented:** Read as '0'

bit 12-8 **FbBP<4:0>:** Pointer to Object When Filter b Hits bits

11111 to 11000 = Reserved

00111 = Message matching filter is stored in Object 7 00110 = Message matching filter is stored in Object 6

. . .

00010 = Message matching filter is stored in Object 2 00001 = Message matching filter is stored in Object 1

00000 = Reserved; Object 0 is the TX Queue and can't receive messages

bit 7 FLTENa: Enable Filter a to Accept Messages bit

1 = Filter is enabled0 = Filter is disabled

bit 6-5 **Unimplemented:** Read as '0'

bit 4-0 **FaBP<4:0>:** Pointer to Object When Filter a Hits bits

11111 to 11000 = Reserved

00111 = Message matching filter is stored in Object 7 00110 = Message matching filter is stored in Object 6

. . .

00010 = Message matching filter is stored in Object 2

00001 = Message matching filter is stored in Object 1

00000 = Reserved; Object 0 is the TX Queue and can't receive messages

REGISTER 11-52: C1FLTOBJxH: CAN FILTER OBJECT REGISTER x HIGH (x = 0 TO 15)

U-0	R/W-0						
_	EXIDE	SID11	EID17	EID16	EID15	EID14	EID13
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| EID12 | EID11 | EID10 | EID9 | EID8 | EID7 | EID6 | EID5 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14 **EXIDE:** Extended Identifier Enable bit

If MIDE = 1:

1 = Matches only messages with Extended Identifier addresses

0 = Matches only messages with Standard Identifier addresses

bit 13 SID11: Standard Identifier Filter bit

bit 12-0 **EID<17:5>:** Extended Identifier Filter bits

In DeviceNet™ mode, these are the filter bits for the first two data bytes.

REGISTER 11-53: C1FLTOBJxL: CAN FILTER OBJECT REGISTER x LOW (x = 0 TO 15)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
EID4	EID3	EID2	EID1	EID0	SID10	SID9	SID8
bit 15				•			bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| SID7 | SID6 | SID5 | SID4 | SID3 | SID2 | SID1 | SID0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 **EID<4:0>:** Extended Identifier Filter bits

In DeviceNet™ mode, these are the filter bits for the first two data bytes.

bit 10-0 **SID<10:0>:** Standard Identifier Filter bits

REGISTER 11-54: C1MASKxH: CAN MASK REGISTER x HIGH (x = 0 TO 15)

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	MIDE	MSID11	MEID17	MEID16	MEID15	MEID14	MEID13
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
MEID12	MEID11	MEID10	MEID9	MEID8	MEID7	MEID6	MEID5
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14 MIDE: Identifier Receive Mode bit

1 = Matches only message types (standard or extended address) that correspond to the EXIDE bit in the filter

0 = Matches either standard or extended address message if filters match (i.e., if (Filter SID) = (Message SID) or if (Filter SID/EID) = (Message SID/EID))

bit 13 MSID11: Standard Identifier Mask bit

bit 12-0 MEID<17:5>: Extended Identifier Mask bits

In DeviceNet™ mode, these are the mask bits for the first two data bytes.

REGISTER 11-55: C1MASKxL: CAN MASK REGISTER x LOW (x = 0 TO 15)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
MEID4	MEID3	MEID2	MEID1	MEID0	MSID10	MSID9	MSID8
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| MSID7 | MSID6 | MSID5 | MSID4 | MSID3 | MSID2 | MSID1 | MSID0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 MEID<4:0>: Extended Identifier Mask bits

In DeviceNet™ mode, these are the mask bits for the first two data bytes.

bit 10-0 MSID<10:0>: Standard Identifier Mask bits

NOTES:			

12.0 HIGH-RESOLUTION PWM WITH FINE EDGE PLACEMENT

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "High-Resolution PWM with Fine Edge Placement" (www.microchip.com/DS70005320) in the "dsPIC33/PIC24 Family Reference Manual".

The High-Speed PWM (HSPWM) module is a Pulse-Width Modulated (PWM) module to support both motor control and power supply applications. This flexible module provides features to support many types of Motor Control (MC) and Power Control (PC) applications, including:

- · AC-to-DC Converters
- · DC-to-DC Converters
- · AC and DC Motors: BLDC, PMSM, ACIM, SRM, etc.
- · Inverters
- · Battery Chargers
- · Digital Lighting
- Power Factor Correction (PFC)

Due to pin limitations, only the larger pin count packages have all eight pairs of PWM outputs available. PWM4H and PWM4L are always available on Peripheral Pin Select (PPS). See Table 12-1 for PWM output availability.

TABLE 12-1: PWM OUTPUT AVAILABILITY

Package Type	Total PGx Instances	Dedicated Outputs	Dedicated + PPS Outputs	
28-pin	8	8 pairs	8 pairs	
36-pin	8	8 pairs	8 pairs	
48-pin	8	8 pairs	8 pairs	
64-pin	8	5 pairs	6 pairs	
80-pin	8	3 pairs	4 pairs	

12.1 Features


- Eight Independent PWM Generators, each with Dual Outputs
- · Operating modes:
 - Independent Edge mode
 - Variable Phase PWM mode
 - Center-Aligned mode
 - Double Update Center-Aligned mode
 - Dual Edge Center-Aligned mode
 - Dual PWM mode
- · Output modes:
 - Complementary
 - Independent
 - Push-Pull
- · Dead-Time Generator
- · Leading-Edge Blanking (LEB)
- Output Override for Fault Handling
- · Flexible Period/Duty Cycle Updating Options
- · Programmable Control Inputs (PCI)
- · Advanced Triggering Options
- Six Combinatorial Logic Outputs
- · Six PWM Event Outputs

12.2 Architecture Overview

The PWM module consists of a common set of controls and features, and multiple instantiations of PWM Generators (PGs). Each PWM Generator can be independently configured or multiple PWM Generators can

be used to achieve complex multiphase systems. PWM Generators can also be used to implement sophisticated triggering, protection and logic functions. A high-level block diagram is shown in Figure 12-1.

FIGURE 12-1: PWM HIGH-LEVEL BLOCK DIAGRAM



12.3 Lock and Write Restrictions

The LOCK bit (PCLKCON<8>) may be set in software to block writes to certain registers. For more information, refer to "High-Resolution PWM with Fine Edge Placement" (DS70005320) in the "dsPIC33/PIC24 Family Reference Manual".

The following lock/unlock sequence is required to set or clear the LOCK bit.

- 1. Write 0x55 to NVMKEY.
- 2. Write 0xAA to NVMKEY.
- Clear (or set) the LOCK bit (PCLKCON<8>) as a single operation.

In general, modifications to configuration controls should not be done while the module is running, as indicated by the ON bit (PGxCONL<15>) being set.

12.4 Control Registers

There are two categories of Special Function Registers (SFRs) used to control the operation of the PWM module:

- · Common, shared by all PWM Generators
- · PWM Generator-specific

An 'x' in the register name denotes an instance of a PWM Generator.

A 'y' in the register name denotes an instance of the common function.

REGISTER 12-1: PCLKCON: PWM CLOCK CONTROL REGISTER

R/W-0	R/W-0	U-0	U-0	U-0	U-0	U-0	R/W-0
HRRDY	HRERR	_	_	_	_	_	LOCK ⁽¹⁾
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0
_	_	DIVSEL1	DIVSEL0	_	_	MCLKSEL1 ⁽²⁾	MCLKSEL0 ⁽²⁾
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	

bit 15 **HRRDY:** High-Resolution Ready bit

1 = The high-resolution circuitry is ready0 = The high-resolution circuitry is not ready

bit 14 HRERR: High-Resolution Error bit

1 = An error has occurred; PWM signals will have limited resolution

0 = No error has occurred; PWM signals will have full resolution when HRRDY = 1

bit 13-9 Unimplemented: Read as '0'

bit 8 LOCK: Lock bit⁽¹⁾

1 = Write-protected registers and bits are locked0 = Write-protected registers and bits are unlocked

bit 7-6 **Unimplemented:** Read as '0'

bit 5-4 DIVSEL<1:0>: PWM Clock Divider Selection bits

11 = Divide ratio is 1:16 10 = Divide ratio is 1:8 01 = Divide ratio is 1:4 00 = Divide ratio is 1:2

bit 3-2 **Unimplemented:** Read as '0'

bit 1-0 MCLKSEL<1:0>: PWM Master Clock Selection bits⁽²⁾

11 = AFPLLO – Auxiliary PLL post-divider output 10 = FPLLO – Primary PLL post-divider output

01 = AFvco/2 - Auxiliary VCO/2

00 = Fosc

Note 1: An unlock sequence must be performed before this bit can be cleared (see Section 12.3 "Lock and Write Restrictions").

2: Changing the MCLKSEL<1:0> bits while ON (PGxCONL<15>) = 1 is not recommended.

REGISTER 12-2: FSCL: FREQUENCY SCALE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			FSCL•	<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
FSCL<7:0>									
bit 7 bi									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FSCL<15:0>: Frequency Scale Register bits

The value in this register is added to the frequency scaling accumulator at each pwm_master_clk. When the accumulated value exceeds the value of FSMINPER, a clock pulse is produced.

REGISTER 12-3: FSMINPER: FREQUENCY SCALING MINIMUM PERIOD REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			FSMINPE	R<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
FSMINPER<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 FSMINPER<15:0>: Frequency Scaling Minimum Period Register bits

This register holds the minimum clock period (maximum clock frequency) that can be produced by the frequency scaling circuit.

REGISTER 12-4: MPHASE: MASTER PHASE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
MPHASE<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
MPHASE<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 MPHASE<15:0>: Master Phase Register bits

This register holds the phase offset value that can be shared by multiple PWM Generators.

REGISTER 12-5: MDC: MASTER DUTY CYCLE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
MDC<15:8> ⁽¹⁾									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
MDC<7:0> ⁽¹⁾									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 MDC<15:0>: Master Duty Cycle Register bits⁽¹⁾

This register holds the duty cycle value that can be shared by multiple PWM Generators.

Note 1: Duty cycle values less than '0x0008' should not be used ('0x0020' in High-Resolution mode).

REGISTER 12-6: MPER: MASTER PERIOD REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
MPER<15:8> ⁽¹⁾								
bit 15								

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			MPER-	<7:0> ⁽¹⁾			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 MPER<15:0>: Master Period Register bits⁽¹⁾

This register holds the period value that can be shared by multiple PWM Generators.

Note 1: Period values less than '0x0010' should not be used ('0x0080' in High-Resolution mode).

REGISTER 12-7: CMBTRIGL: COMBINATIONAL TRIGGER REGISTER LOW

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| CTA8EN | CTA7EN | CTA6EN | CTA5EN | CTA4EN | CTA3EN | CTA2EN | CTA1EN |
| bit 7 | | | | | | | bit 0 |

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-8	Unimplemented: Read as '0'
bit 7	CTA8EN: Enable Trigger Output from PWM Generator #8 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 6	CTA7EN: Enable Trigger Output from PWM Generator #7 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 5	CTA6EN: Enable Trigger Output from PWM Generator #6 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 4	CTA5EN: Enable Trigger Output from PWM Generator #5 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 3	CTA4EN: Enable Trigger Output from PWM Generator #4 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 2	CTA3EN: Enable Trigger Output from PWM Generator #3 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 1	CTA2EN: Enable Trigger Output from PWM Generator #2 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled
bit 0	CTA1EN: Enable Trigger Output from PWM Generator #1 as Source for Combinational Trigger A bit 1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger A signal 0 = Disabled

REGISTER 12-8: CMBTRIGH: COMBINATIONAL TRIGGER REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| CTB8EN | CTB7EN | CTB6EN | CTB5EN | CTB4EN | CTB3EN | CTB2EN | CTB1EN |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0' **CTB8EN:** Enable Trigger Output from

oit 7 CTB8EN: Enable Trigger Output from PWM Generator #8 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 6 CTB7EN: Enable Trigger Output from PWM Generator #7 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 5 CTB6EN: Enable Trigger Output from PWM Generator #6 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 4 CTB5EN: Enable Trigger Output from PWM Generator #5 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 3 CTB4EN: Enable Trigger Output from PWM Generator #4 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 2 CTB3EN: Enable Trigger Output from PWM Generator #3 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 1 CTB2EN: Enable Trigger Output from PWM Generator #2 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

bit 0 CTB1EN: Enable Trigger Output from PWM Generator #1 as Source for Combinational Trigger B bit

1 = Enables specified trigger signal to be OR'd into the Combinatorial Trigger B signal

0 = Disabled

REGISTER 12-9: LOGCONy: COMBINATORIAL PWM LOGIC CONTROL REGISTER $\mathbf{v}^{(2)}$

| R/W-0 |
|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| PWMS1y3 ⁽¹⁾ | PWMS1y2 ⁽¹⁾ | PWMS1y1 ⁽¹⁾ | PWMS1y0 ⁽¹⁾ | PWMS2y3 ⁽¹⁾ | PWMS2y2 ⁽¹⁾ | PWMS2y1 ⁽¹⁾ | PWMS2y0 ⁽¹⁾ |
| bit 15 | | | | | | | bit 8 |

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
S1yPOL	S2yPOL	PWMLFy1	PWMLFy0	_	PWMLFyD2 ⁽³⁾	PWMLFyD1 ⁽³⁾	PWMLFyD0 ⁽³⁾
bit 7							bit 0

 Legend:
 R = Readable bit
 W = Writable bit
 U = Unimplemented bit, read as '0'

 -n = Value at POR
 '1' = Bit is set
 '0' = Bit is cleared
 x = Bit is unknown

```
PWMS1y<3:0>: Combinatorial PWM Logic Source #1 Selection bits<sup>(1)</sup>
bit 15-12
            1111 = PWM8L
            1110 = PWM8H
            1101 = PWM7L
            1100 = PWM7H
            1011 = PWM6L
            1010 = PWM6H
            1001 = PWM5L
            1000 = PWM5H
            0111 = PWM4L
            0110 = PWM4H
            0101 = PWM3L
            0100 = PWM3H
            0011 = PWM2L
            0010 = PWM2H
            0001 = PWM1L
            0000 = PWM1H
            PWMS2y<3:0>: Combinatorial PWM Logic Source #2 Selection bits<sup>(1)</sup>
bit 11-8
            1111 = PWM8L
            1110 = PWM8H
            1101 = PWM7L
            1100 = PWM7H
            1011 = PWM6L
            1010 = PWM6H
            1001 = PWM5L
            1000 = PWM5H
            0111 = PWM4L
            0110 = PWM4H
            0101 = PWM3L
            0100 = PWM3H
            0011 = PWM2L
            0010 = PWM2H
            0001 = PWM1L
            0000 = PWM1H
```

- **Note 1:** Logic function input will be connected to '0' if the PWM channel is not present.
 - 2: 'y' denotes a common instance (A-F).
 - **3:** Instances of y = A, C, E of LOGCONy assign logic function output to the PWMxH pin. Instances of y = B, D, F of LOGCONy assign logic function to the PWMxL pin.

REGISTER 12-9: LOGCONY: COMBINATORIAL PWM LOGIC CONTROL REGISTER y⁽²⁾ (CONTINUED)

bit 7 S1yPOL: Combinatorial PWM Logic Source #1 Polarity bit

1 = Input is inverted0 = Input is positive logic

bit 6 S2yPOL: Combinatorial PWM Logic Source #2 Polarity bit

1 = Input is inverted0 = Input is positive logic

bit 5-4 **PWMLFy<1:0>:** Combinatorial PWM Logic Function Selection bits

11 = Reserved

10 = PWMS1y ^ PWMS2y (XOR) 01 = PWMS1y & PWMS2y (AND) 00 = PWMS1y | PWMS2y (OR)

bit 3 **Unimplemented:** Read as '0'

bit 2-0 **PWMLFyD<2:0>:** Combinatorial PWM Logic Destination Selection bits⁽³⁾

111 = Logic function is assigned to PWM8H or PWM8L pin 110 = Logic function is assigned to PWM7H or PWM7L pin 101 = Logic function is assigned to PWM6H or PWM6L pin 100 = Logic function is assigned to PWM5H or PWM5L pin 011 = Logic function is assigned to PWM4H or PWM4L pin 010 = Logic function is assigned to PWM3H or PWM3L pin 001 = Logic function is assigned to PWM2H or PWM2L pin

000 = No assignment, combinatorial PWM logic function is disabled

Note 1: Logic function input will be connected to '0' if the PWM channel is not present.

2: 'y' denotes a common instance (A-F).

3: Instances of y = A, C, E of LOGCONy assign logic function output to the PWMxH pin. Instances of y = B, D, F of LOGCONy assign logic function to the PWMxL pin.

REGISTER 12-10: PWMEVTy: PWM EVENT OUTPUT CONTROL REGISTER y⁽⁵⁾

R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0	U-0	U-0
EVTyOEN	EVTyPOL	EVTySTRD	EVTySYNC	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
EVTySEL3	EVTySEL2	EVTySEL1	EVTySEL0	_	EVTyPGS2 ⁽²⁾	EVTyPGS1 ⁽²⁾	EVTyPGS0 ⁽²⁾
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	r, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 **EVTyOEN:** PWM Event Output Enable bit 1 = Event output signal is output on PWMEy pin

0 = Event output signal is internal only

bit 14 **EVTyPOL:** PWM Event Output Polarity bit

1 = Event output signal is active-low0 = Event output signal is active-high

bit 13 **EVTySTRD:** PWM Event Output Stretch Disable bit

1 = Event output signal pulse width is not stretched

0 = Event output signal is stretched to eight PWM clock cycles minimum⁽¹⁾

bit 12 **EVTySYNC:** PWM Event Output Sync bit

1 = Event output signal is synchronized to the system clock

0 = Event output is not synchronized to the system clock

Event output signal pulse will be two system clocks when this bit is set and EVTySTRD = 1.

bit 11-8 **Unimplemented:** Read as '0'

bit 7-4 **EVTySEL<3:0>:** PWM Event Selection bits

1111 = High-resolution error event signal

1110-1010 = Reserved

1001 = ADC Trigger 2 signal

1000 = ADC Trigger 1 signal

0111 = STEER signal (available in Push-Pull Output modes only)(4)

0110 = CAHALF signal (available in Center-Aligned modes only)(4)

0101 = PCI Fault active output signal

0100 = PCI Current-limit active output signal

0011 = PCI Feed-forward active output signal

0010 = PCI Sync active output signal

0001 = PWM Generator output signal⁽³⁾

0000 = Source is selected by the PGTRGSEL<2:0> bits

bit 3 **Unimplemented:** Read as '0'

Note 1: The event signal is stretched using peripheral_clk because different PWM Generators may be operating from different clock sources.

- 2: No event will be produced if the selected PWM Generator is not present.
- 3: This is the PWM Generator output signal prior to output mode logic and any output override logic.
- **4:** This signal should be the PGx_clk domain signal prior to any synchronization into the system clock domain.
- 5: 'y' denotes a common instance (A-F).

REGISTER 12-10: PWMEVTy: PWM EVENT OUTPUT CONTROL REGISTER y⁽⁵⁾ (CONTINUED)

bit 2-0

EVTyPGS<2:0>: PWM Event Source Selection bits⁽²⁾

111 = PWM Generator 8

110 = PWM Generator 7

...

000 = PWM Generator 1

- Note 1: The event signal is stretched using peripheral_clk because different PWM Generators may be operating from different clock sources.
 - 2: No event will be produced if the selected PWM Generator is not present.
 - 3: This is the PWM Generator output signal prior to output mode logic and any output override logic.
 - **4:** This signal should be the PGx_clk domain signal prior to any synchronization into the system clock domain.
 - 5: 'y' denotes a common instance (A-F).

REGISTER 12-11: LFSR: LINEAR FEEDBACK SHIFT REGISTER

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_				LFSR<14:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
LFSR<7:0>								
bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-0 LFSR<14:0>: Linear Feedback Shift Register bits

A read of this register will provide a 15-bit pseudorandom value.

REGISTER 12-12: PGxCONL: PWM GENERATOR x CONTROL REGISTER LOW

R/W-0	r-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
ON	_	_	_	_	TRGCNT2	TRGCNT1	TRGCNT0
bit 15							bit 8

R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
HREN	_	_	CLKSEL1	CLKSEL0	MODSEL2	MODSEL1	MODSEL0
bit 7							bit 0

Legend:	r = Reserved bit			
R = Readable bit	W = Writable bit U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15 ON: Enable bit

1 = PWM Generator is enabled0 = PWM Generator is not enabled

bit 14 **Reserved:** Maintain as '0' bit 13-11 **Unimplemented:** Read as '0'

bit 10-8 TRGCNT<2:0>: Trigger Count Select bits

111 = PWM Generator produces eight PWM cycles after triggered 110 = PWM Generator produces seven PWM cycles after triggered 101 = PWM Generator produces six PWM cycles after triggered 100 = PWM Generator produces five PWM cycles after triggered 011 = PWM Generator produces four PWM cycles after triggered 010 = PWM Generator produces three PWM cycles after triggered 001 = PWM Generator produces two PWM cycles after triggered 000 = PWM Generator produces one PWM cycle after triggered

bit 7 **HREN:** PWM Generator x High-Resolution Enable bit

1 = PWM Generator x operates in High-Resolution mode⁽²⁾ 0 = PWM Generator x operates in standard resolution

bit 6-5 **Unimplemented:** Read as '0'

bit 4-3 CLKSEL<1:0>: Clock Selection bits

11 = PWM Generator uses Master clock scaled by frequency scaling circuit⁽¹⁾

10 = PWM Generator uses Master clock divided by clock divider circuit⁽¹⁾

01 = PWM Generator uses Master clock selected by the MCLKSEL<1:0> (PCLKCON<1:0>) control bits

00 = No clock selected, PWM Generator is in lowest power state (default)

bit 2-0 MODSEL<2:0>: Mode Selection bits

111 = Dual Edge Center-Aligned PWM mode (interrupt/register update twice per cycle)

110 = Dual Edge Center-Aligned PWM mode (interrupt/register update once per cycle)

101 = Double-Update Center-Aligned PWM mode

100 = Center-Aligned PWM mode

011 = Reserved

010 = Independent Edge PWM mode, dual output

001 = Variable Phase PWM mode000 = Independent Edge PWM mode

Note 1: The PWM Generator time base operates from the frequency scaling circuit clock, effectively scaling the duty cycle and period of the PWM Generator output.

2: Input frequency of 500 MHz must be used for High-Resolution mode.

REGISTER 12-13: PGxCONH: PWM GENERATOR x CONTROL REGISTER HIGH

R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
MDCSEL	MPERSEL	MPHSEL	_	MSTEN	UPDMOD2	UPDMOD1	UPDMOD0
bit 15							bit 8

r-0	R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	TRGMOD	_	_	SOCS3 ^(1,2,3)	SOCS2 ^(1,2,3)	SOCS1 ^(1,2,3)	SOCS0 ^(1,2,3)
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as	s 'O'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 MDCSEL: Master Duty Cycle Register Select bit

1 = PWM Generator uses MDC register

0 = PWM Generator uses PGxDC register

bit 14 MPERSEL: Master Period Register Select bit

1 = PWM Generator uses MPER register

0 = PWM Generator uses PGxPER register

bit 13 MPHSEL: Master Phase Register Select bit

1 = PWM Generator uses MPHASE register

0 = PWM Generator uses PGxPHASE register

bit 12 **Unimplemented:** Read as '0'

bit 11 MSTEN: Master Update Enable bit

- 1 = PWM Generator broadcasts software set/clear of the UPDREQ status bit and EOC signal to other PWM Generators
- 0 = PWM Generator does not broadcast the UPDREQ status bit state or EOC signal

bit 10-8 **UPDMOD<2:0>:** PWM Buffer Update Mode Selection bits

011 = Slaved immediate update

Data registers immediately, or as soon as possible, when a Master update request is received. A Master update request will be transmitted if MSTEN = 1 and UPDATE = 1 for the requesting PWM Generator.

010 = Slaved SOC update

Data registers at start of next cycle if a Master update request is received. A master update request will be transmitted if MSTEN = 1 and UPDATE = 1 for the requesting PWM Generator.

001 = Immediate update

Data registers immediately, or as soon as possible, if UPDATE = 1. The UPDATE status bit will be cleared automatically after the update occurs (UPDATE = 1). The UPDATE status bit will be cleared automatically after the update occurs.

000 = SOC update

Data registers at start of next PWM cycle if UPDATE = 1. The UPDATE status bit will be cleared automatically after the update occurs. (1)

- bit 7 Reserved: Maintain as '0'
- **Note 1:** The PCI selected Sync signal is always available to be OR'd with the selected SOC signal per the SOCS<3:0> bits if the PCI Sync function is enabled.
 - 2: The source selected by the SOCS<3:0> bits MUST operate from the same clock source as the local PWM Generator. If not, the source must be routed through the PCI Sync logic so the trigger signal may be synchronized to the PWM Generator clock domain.
 - **3:** PWM Generators are grouped into groups of four: PG1-PG4 and PG5-PG8, if available. Any generator within a group of four may be used to trigger another generator within the same group.

REGISTER 12-13: PGxCONH: PWM GENERATOR x CONTROL REGISTER HIGH (CONTINUED)

- bit 6

 TRGMOD: PWM Generator Trigger Mode Selection bit

 1 = PWM Generator operates in Retriggerable mode

 0 = PWM Generator operates in Single Trigger mode

 bit 5-4

 Unimplemented: Read as '0'

 SOCS<3:0>: Start-of-Cycle Selection bits(1,2,3)

 1111 = TRIG bit or PCI Sync function only (no hardware trigger source is selected)

 1110-0101 = Reserved

 0100 = Trigger output selected by PG4 or PG8 PGTRGSEL<2:0> bits (PGxEVTL<2:0>)

 0011 = Trigger output selected by PG3 or PG7 PGTRGSEL<2:0> bits (PGxEVTL<2:0>)

 0010 = Trigger output selected by PG2 or PG6 PGTRGSEL<2:0> bits (PGxEVTL<2:0>)

 0001 = Trigger output selected by PG1 or PG5 PGTRGSEL<2:0> bits (PGxEVTL<2:0>)

 0000 = Local EOC PWM Generator is self-triggered
- **Note 1:** The PCI selected Sync signal is always available to be OR'd with the selected SOC signal per the SOCS<3:0> bits if the PCI Sync function is enabled.
 - 2: The source selected by the SOCS<3:0> bits MUST operate from the same clock source as the local PWM Generator. If not, the source must be routed through the PCI Sync logic so the trigger signal may be synchronized to the PWM Generator clock domain.
 - **3:** PWM Generators are grouped into groups of four: PG1-PG4 and PG5-PG8, if available. Any generator within a group of four may be used to trigger another generator within the same group.

REGISTER 12-14: PGxSTAT: PWM GENERATOR x STATUS REGISTER

HS/C-0	HS/C-0	HS/C-0	HS/C-0	R-0	R-0	R-0	R-0
SEVT	FLTEVT	CLEVT	FFEVT	SACT	FLTACT	CLACT	FFACT
bit 15							bit 8

W-0	W-0	HS/R/W-0	R-0	W-0	R-0	R-0	R-0
TRSET	TRCLR	CAP ⁽¹⁾	UPDATE	UPDREQ	STEER	CAHALF	TRIG
bit 7							bit 0

Legend:	C = Clearable bit	HC = Hardware Clearable bit	HS = Hardware Settable bit
R = Readable bit	W = Writable bit	'0' = Bit is cleared	x = Bit is unknown
-n = Value at POR	'1' = Bit is set	U = Unimplemented bit, read	as '0'

- bit 15 **SEVT:** PCI Sync Event bit
 - 1 = A PCI Sync event has occurred (rising edge on PCI Sync output or PCI Sync output is high when module is enabled)
 - 0 = No PCI Sync event has occurred
- bit 14 FLTEVT: PCI Fault Active Status bit
 - 1 = A Fault event has occurred (rising edge on PCI Fault output or PCI Fault output is high when module is enabled)
 - 0 = No Fault event has occurred
- bit 13 CLEVT: PCI Current-Limit Status bit
 - 1 = A PCI current-limit event has occurred (rising edge on PCI current-limit output or PCI current-limit output is high when module is enabled)
 - 0 = No PCI current-limit event has occurred
- bit 12 FFEVT: PCI Feed-Forward Active Status bit
 - 1 = A PCI feed-forward event has occurred (rising edge on PCI feed-forward output or PCI feed-forward output is high when module is enabled)
 - 0 = No PCI feed-forward event has occurred
- bit 11 SACT: PCI Sync Status bit
 - 1 = PCI Sync output is active
 - 0 = PCI Sync output is inactive
- bit 10 FLTACT: PCI Fault Active Status bit
 - 1 = PCI Fault output is active
 - 0 = PCI Fault output is inactive
- bit 9 CLACT: PCI Current-Limit Status bit
 - 1 = PCI current-limit output is active
 - 0 = PCI current-limit output is inactive
- bit 8 FFACT: PCI Feed-Forward Active Status bit
 - 1 = PCI feed-forward output is active0 = PCI feed-forward output is inactive
- bit 7 TRSET: PWM Generator Software Trigger Set bit

User software writes a '1' to this bit location to trigger a PWM Generator cycle. The bit location always reads as '0'. The TRIG bit will indicate '1' when the PWM Generator is triggered.

bit 6 TRCLR: PWM Generator Software Trigger Clear bit

User software writes a '1' to this bit location to stop a PWM Generator cycle. The bit location always reads as '0'. The TRIG bit will indicate '0' when the PWM Generator is not triggered.

Note 1: User software may write a '1' to CAP as a request to initiate a software capture. The CAP status bit will be set when the capture event has occurred. No further captures will occur until CAP is cleared by software.

REGISTER 12-14: PGxSTAT: PWM GENERATOR x STATUS REGISTER (CONTINUED)

bit 5 CAP: Capture Status bit⁽¹⁾

bit 0

1 = PWM Generator time base value has been captured in PGxCAP

0 = No capture has occurred

bit 4 **UPDATE:** PWM Data Register Update Status/Control bit

1 = PWM Data register update is pending – user Data registers are not writable

0 = No PWM Data register update is pending

bit 3 **UPDREQ:** PWM Data Register Update Request bit

User software writes a '1' to this bit location to request a PWM Data register update. The bit location

always reads as '0'. The UPDATE status bit will indicate '1' when an update is pending.

bit 2 STEER: Output Steering Status bit (Push-Pull Output mode only)

1 = PWM Generator is in 2nd cycle of Push-Pull mode

0 = PWM Generator is in 1st cycle of Push-Pull mode

bit 1 CAHALF: Half Cycle Status bit (Center-Aligned modes only)

1 = PWM Generator is in 2nd half of time base cycle0 = PWM Generator is in 1st half of time base cycle

TRIG: PWM Trigger Status bit

1 = PWM Generator is triggered and PWM cycle is in progress

0 = No PWM cycle is in progress

Note 1: User software may write a '1' to CAP as a request to initiate a software capture. The CAP status bit will be set when the capture event has occurred. No further captures will occur until CAP is cleared by software.

REGISTER 12-15: PGXIOCONL: PWM GENERATOR x I/O CONTROL REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CLMOD	SWAP	OVRENH	OVRENL	OVRDAT1	OVRDAT0	OSYNC1	OSYNC0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FLTDAT1	FLTDAT0	CLDAT1	CLDAT0	FFDAT1	FFDAT0	DBDAT1	DBDAT0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 CLMOD: Current-Limit Mode Select bit

1 = If PCI current limit is active, then the PWMxH and PWMxL output signals are inverted (bit flipping), and the CLDAT<1:0> bits are not used

0 = If PCI current limit is active, then the CLDAT<1:0> bits define the PWM output levels

bit 14 SWAP: Swap PWM Signals to PWMxH and PWMxL Device Pins bit

1 = The PWMxH signal is connected to the PWMxL pin and the PWMxL signal is connected to the PWMxH pin

0 = PWMxH/L signals are mapped to their respective pins

bit 13 **OVRENH:** User Override Enable for PWMxH Pin bit

1 = OVRDAT1 provides data for output on the PWMxH pin

0 = PWM Generator provides data for the PWMxH pin

bit 12 **OVRENL:** User Override Enable for PWMxL Pin bit

1 = OVRDAT0 provides data for output on the PWMxL pin

0 = PWM Generator provides data for the PWMxL pin

bit 11-10 **OVRDAT<1:0>:** Data for PWMxH/PWMxL Pins if Override is Enabled bits

If OVERENH = 1, then OVRDAT1 provides data for PWMxH.

If OVERENL = 1, then OVRDAT0 provides data for PWMxL.

bit 9-8 OSYNC<1:0>: User Output Override Synchronization Control bits

11 = Reserved

10 = User output overrides via the OVRENH/L and OVRDAT<1:0> bits occur when specified by the UPDMOD<2:0> bits in the PGxCONH register

01 = User output overrides via the OVRENH/L and OVRDAT<1:0> bits occur immediately (as soon as possible)

00 = User output overrides via the OVRENH/L and OVRDAT<1:0> bits are synchronized to the local PWM time base (next Start-of-Cycle)

bit 7-6 FLTDAT<1:0>: Data for PWMxH/PWMxL Pins if Fault Event is Active bits

If Fault is active, then FLTDAT1 provides data for PWMxH.

If Fault is active, then FLTDAT0 provides data for PWMxL.

bit 5-4 CLDAT<1:0>: Data for PWMxH/PWMxL Pins if Current-Limit Event is Active bits

If current limit is active, then CLDAT1 provides data for PWMxH.

If current limit is active, then CLDAT0 provides data for PWMxL.

bit 3-2 FFDAT<1:0>: Data for PWMxH/PWMxL Pins if Feed-Forward Event is Active bits

If feed-forward is active, then FFDAT1 provides data for PWMxH.

If feed-forward is active, then FFDAT0 provides data for PWMxL.

bit 1-0 DBDAT<1:0>: Data for PWMxH/PWMxL Pins if Debug Mode is Active bits

If Debug mode is active and device halted, then DBDAT1 provides data for PWMxH.

If Debug mode is active and device halted, then DBDAT0 provides data for PWMxL.

REGISTER 12-16: PGXIOCONH: PWM GENERATOR x I/O CONTROL REGISTER HIGH

U-0	R/W-0	R/W-0	R/W-0	U-0	U-0	U-0	R/W-0
_	CAPSRC2 ⁽¹⁾	CAPSRC1 ⁽¹⁾	CAPSRC0 ⁽¹⁾	_	_	_	DTCMPSEL
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	PMOD1	PMOD0	PENH	PENL	POLH	POLL
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-12 CAPSRC<2:0>: Time Base Capture Source Selection bits⁽¹⁾

111 = Reserved

110 = Reserved

101 = Reserved

100 = Capture time base value at assertion of selected PCI Fault signal

011 = Capture time base value at assertion of selected PCI current-limit signal

010 = Capture time base value at assertion of selected PCI feed-forward signal

001 = Capture time base value at assertion of selected PCI Sync signal

000 = No hardware source selected for time base capture – software only

bit 11-9 **Unimplemented:** Read as '0'

bit 8 DTCMPSEL: Dead-Time Compensation Select bit

1 = Dead-time compensation is controlled by PCI feed-forward limit logic

0 = Dead-time compensation is controlled by PCI Sync logic

bit 7-6 **Unimplemented:** Read as '0'

bit 5-4 PMOD<1:0>: PWM Generator Output Mode Selection bits

11 = Reserved

10 = PWM Generator outputs operate in Push-Pull mode

01 = PWM Generator outputs operate in Independent mode

00 = PWM Generator outputs operate in Complementary mode

bit 3 **PENH:** PWMxH Output Port Enable bit

1 = PWM Generator controls the PWMxH output pin

0 = PWM Generator does not control the PWMxH output pin

bit 2 PENL: PWMxL Output Port Enable bit

1 = PWM Generator controls the PWMxL output pin

0 = PWM Generator does not control the PWMxL output pin

bit 1 **POLH:** PWMxH Output Polarity bit

1 = Output pin is active-low

0 = Output pin is active-high

bit 0 POLL: PWMxL Output Polarity bit

1 = Output pin is active-low

0 = Output pin is active-high

Note 1: A capture may be initiated in software at any time by writing a '1' to CAP (PGxSTAT<5>).

REGISTER 12-17: PGxEVTL: PWM GENERATOR x EVENT REGISTER LOW

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| ADTR1PS4 | ADTR1PS3 | ADTR1PS2 | ADTR1PS1 | ADTR1PS0 | ADTR1EN3 | ADTR1EN2 | ADTR1EN1 |
| bit 15 | | | | | | | bit 8 |

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	UPDTRG1	UPDTRG0	PGTRGSEL2 ⁽¹⁾	PGTRGSEL1 ⁽¹⁾	PGTRGSEL0 ⁽¹⁾
bit 7							bit 0

bit 15-11 ADTR1PS<4:0>: ADC Trigger 1 Postscaler Selection bits

11111 = 1:32

. . .

00010 = 1:3

00001 = 1:2

00000 = 1:1

bit 10 ADTR1EN3: ADC Trigger 1 Source is PGxTRIGC Compare Event Enable bit

1 = PGxTRIGC register compare event is enabled as trigger source for ADC Trigger 1

0 = PGxTRIGC register compare event is disabled as trigger source for ADC Trigger 1

bit 9 ADTR1EN2: ADC Trigger 1 Source is PGxTRIGB Compare Event Enable bit

1 = PGxTRIGB register compare event is enabled as trigger source for ADC Trigger 1

0 = PGxTRIGB register compare event is disabled as trigger source for ADC Trigger 1

bit 8 ADTR1EN1: ADC Trigger 1 Source is PGxTRIGA Compare Event Enable bit

1 = PGxTRIGA register compare event is enabled as trigger source for ADC Trigger 1

0 = PGxTRIGA register compare event is disabled as trigger source for ADC Trigger 1

bit 7-5 **Unimplemented:** Read as '0'

bit 4-3 **UPDTRG<1:0>:** Update Trigger Select bits

11 = A write of the PGxTRIGA register automatically sets the UPDATE bit

10 = A write of the PGxPHASE register automatically sets the UPDATE bit

01 = A write of the PGxDC register automatically sets the UPDATE bit

00 = User must set the UPDATE bit (PGxSTAT<4>) manually

bit 2-0 **PGTRGSEL<2:0>:** PWM Generator Trigger Output Selection bits⁽¹⁾

111 = Reserved

110 = Reserved

101 = Reserved

100 = Reserved

011 = PGxTRIGC compare event is the PWM Generator trigger

010 = PGxTRIGB compare event is the PWM Generator trigger

001 = PGxTRIGA compare event is the PWM Generator trigger

000 = EOC event is the PWM Generator trigger

Note 1: These events are derived from the internal PWM Generator time base comparison events.

REGISTER 12-18: PGxEVTH: PWM GENERATOR x EVENT REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0
FLTIEN ⁽¹⁾	CLIEN ⁽²⁾	FFIEN ⁽³⁾	SIEN ⁽⁴⁾	_	_	IEVTSEL1	IEVTSEL0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ADTR2EN3	ADTR2EN2	ADTR2EN1	ADTR1OFS4	ADTR1OFS3	ADTR1OFS2	ADTR1OFS1	ADTR1OFS0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 FLTIEN: PCI Fault Interrupt Enable bit (1)

1 = Fault interrupt is enabled

0 = Fault interrupt is disabled

bit 14 **CLIEN:** PCI Current-Limit Interrupt Enable bit⁽²⁾

1 = Current-limit interrupt is enabled

0 = Current-limit interrupt is disabled

bit 13 FFIEN: PCI Feed-Forward Interrupt Enable bit (3)

1 = Feed-forward interrupt is enabled

0 = Feed-forward interrupt is disabled

bit 12 SIEN: PCI Sync Interrupt Enable bit (4)

1 = Sync interrupt is enabled

0 = Sync interrupt is disabled

bit 11-10 Unimplemented: Read as '0'

bit 9-8 **IEVTSEL<1:0>:** Interrupt Event Selection bits

11 = Time base interrupts are disabled (Sync, Fault, current-limit and feed-forward events can be independently enabled)

10 = Interrupts CPU at ADC Trigger 1 event

01 = Interrupts CPU at TRIGA compare event

00 = Interrupts CPU at EOC

bit 7 ADTR2EN3: ADC Trigger 2 Source is PGxTRIGC Compare Event Enable bit

1 = PGxTRIGC register compare event is enabled as trigger source for ADC Trigger 2

0 = PGxTRIGC register compare event is disabled as trigger source for ADC Trigger 2

bit 6 ADTR2EN2: ADC Trigger 2 Source is PGxTRIGB Compare Event Enable bit

1 = PGxTRIGB register compare event is enabled as trigger source for ADC Trigger 2

0 = PGxTRIGB register compare event is disabled as trigger source for ADC Trigger 2

bit 5 ADTR2EN1: ADC Trigger 2 Source is PGxTRIGA Compare Event Enable bit

1 = PGxTRIGA register compare event is enabled as trigger source for ADC Trigger 2

0 = PGxTRIGA register compare event is disabled as trigger source for ADC Trigger 2

bit 4-0 ADTR10FS<4:0>: ADC Trigger 1 Offset Selection bits

11111 = Offset by 31 trigger events

. .

00010 = Offset by 2 trigger events

00001 = Offset by 1 trigger event

00000 = No offset

Note 1: An interrupt is only generated on the rising edge of the PCI Fault active signal.

An interrupt is only generated on the rising edge of the PCI current-limit active signal.

3: An interrupt is only generated on the rising edge of the PCI feed-forward active signal.

4: An interrupt is only generated on the rising edge of the PCI Sync active signal.

REGISTER 12-19: PGxyPCIL: PWM GENERATOR xy PCI REGISTER LOW (x = PWM GENERATOR #; y = F, CL, FF OR S)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TSYNCDIS	TERM2	TERM1	TERM0	AQPS	AQSS2	AQSS1	AQSS0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SWTERM	PSYNC	PPS	PSS4	PSS3	PSS2	PSS1	PSS0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 TSYNCDIS: Termination Synchronization Disable bit

1 = Termination of latched PCI occurs immediately

0 = Termination of latched PCI occurs at PWM EOC

bit 14-12 **TERM<2:0>:** Termination Event Selection bits

111 = Selects PCI Source #9

110 = Selects PCI Source #8

101 = Selects PCI Source #1 (PWM Generator output selected by the PWMPCI<2:0> bits)

100 = PGxTRIGC trigger event

011 = PGxTRIGB trigger event

010 = PGxTRIGA trigger event

001 = Auto-Terminate: Terminate when PCI source transitions from active to inactive

000 = Manual Terminate: Terminate on a write of '1' to the SWTERM bit location

bit 11 AQPS: Acceptance Qualifier Polarity Select bit

1 = Inverted

0 = Not inverted

bit 10-8 AQSS<2:0>: Acceptance Qualifier Source Selection bits

111 = SWPCI control bit only (qualifier forced to '0')

110 = Selects PCI Source #9

101 = Selects PCI Source #8

100 = Selects PCI Source #1 (PWM Generator output selected by the PWMPCI<2:0> bits)

011 = PWM Generator is triggered

010 = LEB is active

001 = Duty cycle is active (base PWM Generator signal)

000 = No acceptance qualifier is used (qualifier forced to '1')

bit 7 **SWTERM:** PCI Software Termination bit

A write of '1' to this location will produce a termination event. This bit location always reads as '0'.

bit 6 **PSYNC:** PCI Synchronization Control bit

1 = PCI source is synchronized to PWM EOC

0 = PCI source is not synchronized to PWM EOC

bit 5 PPS: PCI Polarity Select bit

1 = Inverted

0 = Not inverted

REGISTER 12-19: PGxyPCIL: PWM GENERATOR xy PCI REGISTER LOW (x = PWM GENERATOR #; y = F, CL, FF OR S) (CONTINUED)

```
bit 4-0
           PSS<4:0>: PCI Source Selection bits
           11111 = CLC1
           11110 = Reserved
           11101 = Comparator 3 output
           11100 = Comparator 2 output
           11011 = Comparator 1 output
           11010 = PWM Event D
           11001 = PWM Event C
           11000 = PWM Event B
           10111 = PWM Event A
           10110 = Device pin, PCI<22>
           10101 = Device pin, PCI<21>
           10100 = Device pin, PCI<20>
           10011 = Device pin, PCI<19>
           10010 = RPn input, PCI18R
           10001 = RPn input, PCI17R
           10000 = RPn input, PCI16R
           01111 = RPn input, PCI15R
           01110 = RPn input, PCI14R
           01101 = RPn input, PCI13R
           01100 = RPn input, PCI12R
           01011 = RPn input, PCI11R
           01010 = RPn input, PCI10R
           01001 = RPn input, PCI9R
           01000 = RPn input, PCI8R
           00111 = Reserved
           00110 = Reserved
           00101 = Reserved
           00100 = Reserved
           00011 = Internally connected to Combo Trigger B
           00010 = Internally connected to Combo Trigger A
           00001 = Internally connected to the output of PWMPCI<2:0> MUX
           00000 = Tied to '0'
```

REGISTER 12-20: PGxyPCIH: PWM GENERATOR xy PCI REGISTER HIGH (x = PWM GENERATOR #; y = F, CL, FF OR S)

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
BPEN	BPSEL2 ⁽¹⁾	BPSEL1 ⁽¹⁾	BPSEL0 ⁽¹⁾	_	ACP2	ACP1	ACP0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SWPCI	SWPCIM1	SWPCIM0	LATMOD	TQPS	TQSS2	TQSS1	TQSS0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 BPEN: PCI Bypass Enable bit

1 = PCI function is enabled and local PCI logic is bypassed; PWM Generator will be controlled by PCI function in the PWM Generator selected by the BPSEL<2:0> bits

0 = PCI function is not bypassed

bit 14-12 BPSEL<2:0>: PCI Bypass Source Selection bits⁽¹⁾

111 = PCI control is sourced from PWM Generator 8 PCI logic when BPEN = 1

110 = PCI control is sourced from PWM Generator 7 PCI logic when BPEN = 1

101 = PCI control is sourced from PWM Generator 6 PCI logic when BPEN = 1

100 = PCI control is sourced from PWM Generator 5 PCI logic when BPEN = 1

011 = PCI control is sourced from PWM Generator 4 PCI logic when BPEN = 1

010 = PCI control is sourced from PWM Generator 3 PCI logic when BPEN = 1

001 = PCI control is sourced from PWM Generator 2 PCI logic when BPEN = 1

000 = PCI control is sourced from PWM Generator 1 PCI logic when BPEN = 1

bit 11 **Unimplemented:** Read as '0'

bit 10-8 ACP<2:0>: PCI Acceptance Criteria Selection bits

111 = Reserved

110 = Reserved

101 = Latched any edge

100 = Latched rising edge

011 = Latched

010 = Any edge

001 = Rising edge

000 = Level-sensitive

bit 7 **SWPCI:** Software PCI Control bit

1 = Drives a '1' to PCI logic assigned to by the SWPCIM<1:0> control bits

0 = Drives a '0' to PCI logic assigned to by the SWPCIM<1:0> control bits

bit 6-5 **SWPCIM<1:0>:** Software PCI Control Mode bits

11 = Reserved

10 = SWPCI bit is assigned to termination qualifier logic

01 = SWPCI bit is assigned to acceptance qualifier logic

00 = SWPCI bit is assigned to PCI acceptance logic

bit 4 LATMOD: PCI SR Latch Mode bit

1 = SR latch is Reset-dominant in Latched Acceptance modes

0 = SR latch is Set-dominant in Latched Acceptance modes

Note 1: Selects '0' if selected PWM Generator is not present.

REGISTER 12-20: PGxyPCIH: PWM GENERATOR xy PCI REGISTER HIGH (x = PWM GENERATOR #; y = F, CL, FF OR S) (CONTINUED)

bit 3 TQPS: Termination Qualifier Polarity Select bit

1 = Inverted

0 = Not inverted

bit 2-0 TQSS<2:0>: Termination Qualifier Source Selection bits

111 = SWPCI control bit only (qualifier forced to '0')

110 = Selects PCI Source #9 101 = Selects PCI Source #8

100 = Selects PCI Source #1 (PWM Generator output selected by the PWMPCI<2:0> bits)

011 = PWM Generator is triggered

010 = LEB is active

001 = Duty cycle is active (base PWM Generator signal)000 = No termination qualifier used (qualifier forced to '1')

Note 1: Selects '0' if selected PWM Generator is not present.

REGISTER 12-21: PGXLEBL: PWM GENERATOR x LEADING-EDGE BLANKING REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			LEB	<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R-0 ⁽¹⁾	R-0 ⁽¹⁾	R-0 ⁽¹⁾	
LEB<7:0>								
bit 7							bit 0	

Legend:				
R = Readable bit	= Readable bit W = Writable bit U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15-0 **LEB<15:0>:** Leading-Edge Blanking Period bits

Leading-Edge Blanking period. The three LSbs of the blanking time are not used, providing a blanking resolution of eight PGx_clks. The minimum blanking period is eight PGx_clks which occurs when LEB<15:3> = 0.

Note 1: Bits<2:0> are read-only and always remain as '0'.

REGISTER 12-22: PGxLEBH: PWM GENERATOR x LEADING-EDGE BLANKING REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	PWMPCI2 ⁽¹⁾	PWMPCI1 ⁽¹⁾	PWMPCI0 ⁽¹⁾
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	PHR	PHF	PLR	PLF
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 **Unimplemented:** Read as '0'

bit 10-8 **PWMPCI<2:0>:** PWM Source for PCI Selection bits⁽¹⁾

111 = PWM Generator #8 output is made available to PCI logic

110 = PWM Generator #7 output is made available to PCI logic

101 = PWM Generator #6 output is made available to PCI logic

100 = PWM Generator #5 output is made available to PCI logic

011 = PWM Generator #4 output is made available to PCI logic

010 = PWM Generator #3 output is made available to PCI logic

001 = PWM Generator #2 output is made available to PCI logic

000 = PWM Generator #1 output is made available to PCI logic

bit 7-4 **Unimplemented:** Read as '0'

bit 3 PHR: PWMxH Rising Edge Trigger Enable bit

1 = Rising edge of PWMxH will trigger the LEB duration counter

0 = LEB ignores the rising edge of PWMxH

bit 2 PHF: PWMxH Falling Edge Trigger Enable bit

1 = Falling edge of PWMxH will trigger the LEB duration counter

0 = LEB ignores the falling edge of PWMxH

bit 1 PLR: PWMxL Rising Edge Trigger Enable bit

1 = Rising edge of PWMxL will trigger the LEB duration counter

0 = LEB ignores the rising edge of PWMxL

bit 0 PLF: PWMxL Falling Edge Trigger Enable bit

1 = Falling edge of PWMxL will trigger the LEB duration counter

0 = LEB ignores the falling edge of PWMxL

Note 1: The selected PWM Generator source does not affect the LEB counter. This source can be optionally used as a PCI input, PCI qualifier, PCI terminator or PCI terminator qualifier (see the description in Register 12-19 and Register 12-20 for more information).

REGISTER 12-23: PGxPHASE: PWM GENERATOR x PHASE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxPH <i>A</i>	ASE<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxPH	ASE<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxPHASE<15:0>:** PWM Generator x Phase Register bits

REGISTER 12-24: PGxDC: PWM GENERATOR x DUTY CYCLE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PGxDC<15:8> ⁽¹⁾								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxD(C<7:0> ⁽¹⁾			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxDC<15:0>:** PWM Generator x Duty Cycle Register bits⁽¹⁾

Note 1: Duty cycle values less than '0x0008' should not be used ('0x0020' in High-Resolution mode).

REGISTER 12-25: PGxDCA: PWM GENERATOR x DUTY CYCLE ADJUSTMENT REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxD	CA<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 Unimplemented: Read as '0'

bit 7-0 PGxDCA<7:0>: PWM Generator x Duty Cycle Adjustment Value bits

Depending on the state of the selected PCI source, the PGxDCA value will be added to the value in the PGxDC register to create the effective duty cycle. When the PCI source is active, PGxDCA is added.

REGISTER 12-26: PGxPER: PWM GENERATOR x PERIOD REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	PGxPER<15:8> ⁽¹⁾								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PGxPER<7:0> ⁽¹⁾								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxPER<15:0>:** PWM Generator x Period Register bits⁽¹⁾

Note 1: Period values less than '0x0010' should not be used ('0x0080' in High-Resolution mode).

REGISTER 12-27: PGxTRIGA: PWM GENERATOR x TRIGGER A REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	PGxTRIGA<15:8>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxTR	NGA<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxTRIGA<15:0>:** PWM Generator x Trigger A Register bits

REGISTER 12-28: PGxTRIGB: PWM GENERATOR x TRIGGER B REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PGxTRI	IGB<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PGxTRIGB<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxTRIGB<15:0>:** PWM Generator x Trigger B Register bits

REGISTER 12-29: PGxTRIGC: PWM GENERATOR x TRIGGER C REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PGxTRIGC<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PGxTRIGC<7:0>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PGxTRIGC<15:0>:** PWM Generator x Trigger C Register bits

REGISTER 12-30: PGxDTL: PWM GENERATOR x DEAD-TIME REGISTER LOW

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_			DTL<1	3:8> ⁽¹⁾		
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
DTL<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-0 DTL<13:0>: PWMxL Dead-Time Delay bits⁽¹⁾

Note 1: DTL<13:11> bits are not available when HREN (PGxCONL<7>) = 0.

REGISTER 12-31: PGxDTH: PWM GENERATOR x DEAD-TIME REGISTER HIGH

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_			DTH<1	13:8> ⁽¹⁾		
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
DTH<7:0>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 Unimplemented: Read as '0'

bit 13-0 **DTH<13:0>:** PWMxH Dead-Time Delay bits⁽¹⁾

Note 1: DTH<13:11> bits are not available when HREN (PGxCONL<7>) = 0.

REGISTER 12-32: PGxCAP: PWM GENERATOR x CAPTURE REGISTER

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
	_	_	PGxCAP	?<15:8>			
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			PGxCAP-	<7:0> ⁽¹⁾			
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-0 **PGxCAP<15:0>:** PGx Time Base Capture bits⁽¹⁾

Note 1: PGxCAP<1:0> will read as '0' in Standard Resolution mode. PGxCAP<4:0> will read as '0' in High-Resolution mode.

NOTES:			

13.0 HIGH-SPEED, 12-BIT ANALOG-TO-DIGITAL CONVERTER (ADC)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "12-Bit High-Speed, Multiple SARs A/D Converter (ADC)" (www.microchip.com/DS70005213) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices due to the number of implemented ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

The dsPIC33CK256MP508 devices have a high-speed, 12-bit Analog-to-Digital Converter (ADC) that features a low conversion latency, high resolution and oversampling capabilities to improve performance in AC/DC, DC/DC power converters. The devices implement the ADC with three SAR cores, two dedicated and one shared.

13.1 ADC Features Overview

The High-Speed, 12-Bit Multiple SARs Analog-to-Digital Converter (ADC) includes the following features:

- Three ADC Cores: Two Dedicated Cores and One Shared (common) Core
- User-Configurable Resolution of up to 12 Bits for each Core
- Up to 3.5 Msps Conversion Rate per Channel at 12-Bit Resolution
- Low-Latency Conversion
- Up to 24 Analog Input Channels, with a Separate 16-Bit Conversion Result Register for each Input
- Conversion Result can be Formatted as Unsigned or Signed Data, on a per Channel Basis, for All Channels

- Simultaneous Sampling of up to Three Analog Inputs
- · Channel Scan Capability
- Multiple Conversion Trigger Options for each Core, including:
 - PWM triggers from CPU cores
 - MCCP/SCCP modules triggers
 - CLC modules triggers
 - External pin trigger event (ADTRG31)
 - Software trigger
- Four Integrated Digital Comparators with Dedicated Interrupts:
 - Multiple comparison options
 - Assignable to specific analog inputs
- Four Oversampling Filters with Dedicated Interrupts:
 - Provide increased resolution
 - Assignable to a specific analog input

The module consists of three independent SAR ADC cores. Simplified block diagrams of the Multiple SARs 12-Bit ADC are shown in Figure 13-1 and Figure 13-2.

The analog inputs (channels) are connected through multiplexers and switches to the Sample-and-Hold (S&H) circuit of each ADC core. The core uses the channel information (the output format, the Measurement mode and the input number) to process the analog sample. When conversion is complete, the result is stored in the result buffer for the specific analog input, and passed to the digital filter and digital comparator if they were configured to use data from this particular channel.

The ADC module can sample up to three inputs at a time (two inputs from the dedicated SAR cores and one from the shared SAR core). If multiple ADC inputs request conversion on the shared core, the module will convert them in a sequential manner, starting with the lowest order input.

The ADC provides each analog input the ability to specify its own trigger source. This capability allows the ADC to sample and convert analog inputs that are associated with PWM generators operating on independent time bases.




FIGURE 13-1: ADC MODULE BLOCK DIAGRAM

FIGURE 13-2: ADC SHARED CORE BLOCK DIAGRAM





FIGURE 13-3: DEDICATED ADC CORE



13.2 Analog-to-Digital Converter Resources

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

13.2.1 KEY RESOURCES

- "12-Bit High-Speed, Multiple SARs A/D Converter (ADC)" (DS70005213) in the "dsPIC33/PIC24 Family Reference Manual"
- · Code Samples
- · Application Notes
- · Software Libraries
- · Webinars
- All Related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

13.3 **Control Registers**

REGISTER 13-1: ADCON1L: ADC CONTROL REGISTER 1 LOW

R/W-0	U-0	R/W-0	U-0	r-0	U-0	U-0	U-0
ADON ⁽¹⁾	_	ADSIDL	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

ADON: ADC Enable bit⁽¹⁾ bit 15 1 = ADC module is enabled

0 = ADC module is off

bit 14 Unimplemented: Read as '0' bit 13

ADSIDL: ADC Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 Unimplemented: Read as '0' bit 11 Reserved: Maintain as '0' bit 10-0 Unimplemented: Read as '0'

Note 1: Set the ADON bit only after the ADC module has been configured. Changing ADC Configuration bits when ADON = 1 will result in unpredictable behavior.

REGISTER 13-2: ADCON1H: ADC CONTROL REGISTER 1 HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-1	R/W-1	U-0	U-0	U-0	U-0	U-0
FORM	SHRRES1	SHRRES0	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7 FORM: Fractional Data Output Format bit

1 = Fractional0 = Integer

bit 6-5 SHRRES<1:0>: Shared ADC Core Resolution Selection bits

11 = 12-bit resolution 10 = 10-bit resolution 01 = 8-bit resolution 00 = 6-bit resolution

bit 4-0 **Unimplemented:** Read as '0'

REGISTER 13-3: ADCON2L: ADC CONTROL REGISTER 2 LOW

R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
REFCIE	REFERCIE	_	EIEN	PTGEN	SHREISEL2 ⁽¹⁾	SHREISEL1 ⁽¹⁾	SHREISEL0 ⁽¹⁾
bit 15							bit 8

U-0	R/W-0						
_	SHRADCS6	SHRADCS5	SHRADCS4	SHRADCS3	SHRADCS2	SHRADCS1	SHRADCS0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 REFCIE: Band Gap and Reference Voltage Ready Common Interrupt Enable bit

1 = Common interrupt will be generated when the band gap will become ready

0 = Common interrupt is disabled for the band gap ready event

bit 14 REFERCIE: Band Gap or Reference Voltage Error Common Interrupt Enable bit

1 = Common interrupt will be generated when a band gap or reference voltage error is detected

0 = Common interrupt is disabled for the band gap and reference voltage error event

bit 13 **Unimplemented:** Read as '0'

bit 12 **EIEN:** Early Interrupts Enable bit

1 = The early interrupt feature is enabled for the input channel interrupts (when the EISTATx flag is set)

0 = The individual interrupts are generated when conversion is done (when the ANxRDY flag is set)

bit 11 PTGEN: External Conversion Request Interface bit

Setting this bit will enable the PTG to request conversion of an ADC input.

bit 10-8 SHREISEL<2:0>: Shared Core Early Interrupt Time Selection bits⁽¹⁾

111 = Early interrupt is set and interrupt is generated 8 TADCORE clocks prior to when the data is ready

110 = Early interrupt is set and interrupt is generated 7 TADCORE clocks prior to when the data is ready

101 = Early interrupt is set and interrupt is generated 6 TADCORE clocks prior to when the data is ready

100 = Early interrupt is set and interrupt is generated 5 TADCORE clocks prior to when the data is ready

011 = Early interrupt is set and interrupt is generated 4 TADCORE clocks prior to when the data is ready

010 = Early interrupt is set and interrupt is generated 3 TADCORE clocks prior to when the data is ready

001 = Early interrupt is set and interrupt is generated 2 TADCORE clocks prior to when the data is ready

000 = Early interrupt is set and interrupt is generated 1 TADCORE clock prior to when the data is ready

bit 7 **Unimplemented:** Read as '0'

bit 6-0 SHRADCS<6:0>: Shared ADC Core Input Clock Divider bits

These bits determine the number of TCORESRC (Source Clock Periods) for one shared TADCORE (Core Clock Period).

1111111 = 254 Source Clock Periods

. .

0000011 = 6 Source Clock Periods

0000010 = 4 Source Clock Periods

0000001 = 2 Source Clock Periods

0000000 = 2 Source Clock Periods

Note 1: For the 6-bit shared ADC core resolution (SHRRES<1:0> = 00), the SHREISEL<2:0> settings, from '100' to '111', are not valid and should not be used. For the 8-bit shared ADC core resolution (SHRRES<1:0> = 01), the SHREISEL<2:0> settings, '110' and '111', are not valid and should not be used.

REGISTER 13-4: ADCON2H: ADC CONTROL REGISTER 2 HIGH

HSC/R-0	HSC/R-0	U-0	r-0	r-0	r-0	R/W-0	R/W-0
REFRDY	REFERR	_	_	_	_	SHRSAMC9	SHRSAMC8
bit 15							bit 8

| R/W-0 |
|----------|----------|----------|----------|----------|----------|----------|----------|
| SHRSAMC7 | SHRSAMC6 | SHRSAMC5 | SHRSAMC4 | SHRSAMC3 | SHRSAMC2 | SHRSAMC1 | SHRSAMC0 |
| bit 7 | | | | | | | bit 0 |

Legend:	r = Reserved bit	erved bit U = Unimplemented bit, read as '0'	
R = Readable bit	W = Writable bit	HSC = Hardware Settat	ole/Clearable bit
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 **REFRDY:** Band Gap and Reference Voltage Ready Flag bit

1 = Band gap is ready0 = Band gap is not ready

bit 14 REFERR: Band Gap or Reference Voltage Error Flag bit

1 = Band gap was removed after the ADC module was enabled (ADON = 1)

0 = No band gap error was detected

bit 13 **Unimplemented:** Read as '0' bit 12-10 **Reserved:** Maintain as '0'

bit 9-0 SHRSAMC<9:0>: Shared ADC Core Sample Time Selection bits

These bits specify the number of shared ADC Core Clock Periods (TADCORE) for the shared ADC core

sample time.

1111111111 = **1025** TADCORE

. . .

0000000001 = 3 TADCORE 0000000000 = 2 TADCORE

REGISTER 13-5: ADCON3L: ADC CONTROL REGISTER 3 LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	HSC/R-0	R/W-0	HSC/R-0
REFSEL2	REFSEL1	REFSEL0	SUSPEND	SUSPCIE	SUSPRDY	SHRSAMP	CNVRTCH
bit 15							bit 8

R/W-0	HSC/R-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SWLCTRG	SWCTRG	CNVCHSEL5	CNVCHSEL4	CNVCHSEL3	CNVCHSEL2	CNVCHSEL1	CNVCHSEL0
bit 7							bit 0

Legend: U = Unimplemented bit, read as '0'

R = Readable bit W = Writable bit HSC = Hardware Settable/Clearable bit

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 **REFSEL<2:0>:** ADC Reference Voltage Selection bits

Value	VREFH	VREFL
000	AVDD	AVss

001-111 = Unimplemented: Do not use

bit 12 SUSPEND: All ADC Core Triggers Disable bit

1 = All new trigger events for all ADC cores are disabled

0 = All ADC cores can be triggered

bit 11 SUSPCIE: Suspend All ADC Cores Common Interrupt Enable bit

1 = Common interrupt will be generated when ADC core triggers are suspended (SUSPEND bit = 1) and all previous conversions are finished (SUSPRDY bit becomes set)

0 = Common interrupt is not generated for suspend ADC cores event

bit 10 SUSPRDY: All ADC Cores Suspended Flag bit

1 = All ADC cores are suspended (SUSPEND bit = 1) and have no conversions in progress

0 = ADC cores have previous conversions in progress

bit 9 SHRSAMP: Shared ADC Core Sampling Direct Control bit

This bit should be used with the individual channel conversion trigger controlled by the CNVRTCH bit. It connects an analog input, specified by the CNVCHSEL<5:0> bits, to the shared ADC core and allows extending the sampling time. This bit is not controlled by hardware and must be cleared before the conversion starts (setting CNVRTCH to '1').

- 1 = Shared ADC core samples an analog input specified by the CNVCHSEL<5:0> bits
- 0 = Sampling is controlled by the shared ADC core hardware

bit 8 CNVRTCH: Software Individual Channel Conversion Trigger bit

- 1 = Single trigger is generated for an analog input specified by the CNVCHSEL<5:0> bits; when the bit is set, it is automatically cleared by hardware on the next instruction cycle
- 0 = Next individual channel conversion trigger can be generated

bit 7 SWLCTRG: Software Level-Sensitive Common Trigger bit

- 1 = Triggers are continuously generated for all channels with the software, level-sensitive common trigger selected as a source in the ADTRIGxL and ADTRIGxH registers
- 0 = No software, level-sensitive common triggers are generated

bit 6 **SWCTRG:** Software Common Trigger bit

- 1 = Single trigger is generated for all channels with the software; common trigger selected as a source in the ADTRIGnL and ADTRIGxH registers; when the bit is set, it is automatically cleared by hardware on the next instruction cycle
- 0 = Ready to generate the next software common trigger
- bit 5-0 **CNVCHSEL <5:0>:** Channel Number Selection for Software Individual Channel Conversion Trigger bits These bits define a channel to be converted when the CNVRTCH bit is set.

REGISTER 13-6: ADCON3H: ADC CONTROL REGISTER 3 HIGH

| R/W-0 |
|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| CLKSEL1 ⁽¹⁾ | CLKSEL0 ⁽¹⁾ | CLKDIV5 ⁽²⁾ | CLKDIV4 ⁽²⁾ | CLKDIV3 ⁽²⁾ | CLKDIV2 ⁽²⁾ | CLKDIV1 ⁽²⁾ | CLKDIV0 ⁽²⁾ |
| bit 15 | | | | | | | bit 8 |

R/W-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
SHREN	_	_	_	_	_	C1EN	C0EN
bit 7							bit 0

 Legend:
 R = Readable bit
 W = Writable bit
 U = Unimplemented bit, read as '0'

 -n = Value at POR
 '1' = Bit is set
 '0' = Bit is cleared
 x = Bit is unknown

bit 15-14 CLKSEL<1:0>: ADC Module Clock Source Selection bits(1)

11 = Fvco/4

10 = AFVCODIV

01 = Fosc

00 = FP (Peripheral Clock)

bit 13-8 CLKDIV<5:0>: ADC Module Clock Source Divider bits⁽²⁾

The divider forms a TCORESRC clock used by all ADC cores (shared and dedicated) from the TSRC ADC module clock source selected by the CLKSEL<1:0> bits. Then, each ADC core individually divides the TCORESRC clock to get a core-specific TADCORE clock using the ADCS<6:0> bits in the ADCOREXH register or the SHRADCS<6:0> bits in the ADCON2L register.

111111 = 64 Source Clock Periods

• •

000011 = 4 Source Clock Periods

000010 = 3 Source Clock Periods

000001 = 2 Source Clock Periods

000000 = 1 Source Clock Period

bit 7 SHREN: Shared ADC Core Enable bit

1 = Shared ADC core is enabled

0 = Shared ADC core is disabled

bit 6-2 **Unimplemented:** Read as '0'

bit 1 C1EN: Dedicated ADC Core 1 Enable bits

1 = Dedicated ADC Core 1 is enabled

0 = Dedicated ADC Core 1 is disabled

bit 0 COEN: Dedicated ADC Core 0 Enable bits

1 = Dedicated ADC Core 0 is enabled

0 = Dedicated ADC Core 0 is disabled

Note 1: The ADC input clock frequency, selected by the CLKSEL<1:0> bits, must not exceed 560 MHz.

2: The ADC clock frequency, after the divider selected by the CLKDIV<5:0> bits, must not exceed 280 MHz.

REGISTER 13-7: ADCON4L: ADC CONTROL REGISTER 4 LOW

U-0	U-0	U-0	U-0	U-0	U-0	r-0	r-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	SAMC1EN	SAMC0EN
bit 7							bit 0

Legend:	r = Reserved bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-10 Unimplemented: Read as '0' bit 9-8 Reserved: Must be written as '0' bit 7-2 Unimplemented: Read as '0'

bit 1 SAMC1EN: Dedicated ADC Core 1 Conversion Delay Enable bit

- 1 = After trigger, the conversion will be delayed and the ADC core will continue sampling during the time specified by the SAMC<9:0> bits in the ADCORE1L register
- 0 = After trigger, the sampling will be stopped immediately and the conversion will be started on the next core clock cycle
- bit 0 SAMC0EN: Dedicated ADC Core 0 Conversion Delay Enable bit
 - 1 = After trigger, the conversion will be delayed and the ADC core will continue sampling during the time specified by the SAMC<9:0> bits in the ADCOREOL register
 - 0 = After trigger, the sampling will be stopped immediately and the conversion will be started on the next core clock cycle

REGISTER 13-8: ADCON4H: ADC CONTROL REGISTER 4 HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	C1CHS1	C1CHS0	C0CHS1	C0CHS0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-4 **Unimplemented:** Read as '0'

bit 3-2 C1CHS<1:0>: Dedicated ADC Core 1 Input Channel Selection bits

11 = Reserved

10 = Reserved

01 = ANA1

00 **= AN1**

bit 1-0 **C0CHS<1:0>:** Dedicated ADC Core 0 Input Channel Selection bits

11 = Reserved

10 = Reserved

01 = ANA0

00 **= AN0**

REGISTER 13-9: ADCON5L: ADC CONTROL REGISTER 5 LOW

HSC/R-0	U-0	U-0	U-0	U-0	U-0	HSC/R-0	HSC/R-0
SHRRDY	_	_	_	_		C1RDY	C0RDY
bit 15							bit 8

R/W-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
SHRPWR	_	_	_	_	_	C1PWR	C0PWR
bit 7							bit 0

Legend: U = Unimplemented bit, read as '0'

R = Readable bit W = Writable bit HSC = Hardware Settable/Clearable bit

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 SHRRDY: Shared ADC Core Ready Flag bit

1 = ADC core is powered and ready for operation

0 = ADC core is not ready for operation

bit 14-10 **Unimplemented:** Read as '0'

bit 9 C1RDY: Dedicated ADC Core 1 Ready Flag bit

1 = ADC Core 1 is powered and ready for operation

0 = ADC Core 1 is not ready for operation

bit 8 **CORDY:** Dedicated ADC Core 0 Ready Flag bit

1 = ADC Core 0 is powered and ready for operation

0 = ADC Core 0 is not ready for operation

bit 7 SHRPWR: Shared ADC Core Power Enable bit

1 = ADC core is powered

0 = ADC core is off

bit 6-2 **Unimplemented:** Read as '0'

bit 1 C1PWR: Dedicated ADC Core 1 Power Enable bit

1 = ADC Core 1 is powered 0 = ADC Core 1 is off

bit 0 COPWR: Dedicated ADC Core 0 Power Enable bit

1 = ADC Core 0 is powered 0 = ADC Core 0 is off

REGISTER 13-10: ADCON5H: ADC CONTROL REGISTER 5 HIGH

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	WARMTIME3	WARMTIME2	WARMTIME1	WARMTIME0
bit 15							bit 8

R/W-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
SHRCIE	_	_	_	_	_	C1CIE	C0CIE
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 **Unimplemented:** Read as '0'

bit 11-8 WARMTIME<3:0>: ADC Dedicated Core x Power-up Delay bits

These bits determine the power-up delay in the number of the Core Source Clock Periods (TCORESRC)

for all ADC cores.

1111 = 32768 Source Clock Periods

1110 = 16384 Source Clock Periods

1101 = 8192 Source Clock Periods

1100 = 4096 Source Clock Periods

1011 = 2048 Source Clock Periods

1010 = 1024 Source Clock Periods

1001 = 512 Source Clock Periods

1000 = 256 Source Clock Periods

0111 = 128 Source Clock Periods 0110 = 64 Source Clock Periods

0101 = 32 Source Clock Periods

0100 = 16 Source Clock Periods

00xx = 16 Source Clock Periods

bit 7 SHRCIE: Shared ADC Core Ready Common Interrupt Enable bit

1 = Common interrupt will be generated when ADC core is powered and ready for operation

0 = Common interrupt is disabled for an ADC core ready event

bit 6-2 **Unimplemented:** Read as '0'

bit 1 C1CIE: Dedicated ADC Core 1 Ready Common Interrupt Enable bit

1 = Common interrupt will be generated when ADC Core 1 is powered and ready for operation

0 = Common interrupt is disabled for an ADC Core 1 ready event

bit 0 Cocle: Dedicated ADC Core 0 Ready Common Interrupt Enable bit

1 = Common interrupt will be generated when ADC Core 0 is powered and ready for operation

0 = Common interrupt is disabled for an ADC Core 0 ready event

REGISTER 13-11: ADCOREXL: DEDICATED ADC CORE x CONTROL REGISTER LOW (x = 0 TO 1)

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	SAMO	C<9:8>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
SAMC<7:0>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 **SAMC<9:0>:** Dedicated ADC Core x Conversion Delay Selection bits

These bits determine the time between the trigger event and the start of conversion in the number of the Core Clock Periods (TADCORE). During this time, the ADC Core x still continues sampling. This feature is enabled by the SAMCxEN bits in the ADCON4L register.

1111111111 = 1025 TADCORE

. . .

0000000001 = 3 TADCORE 0000000000 = 2 TADCORE

REGISTER 13-12: ADCOREXH: DEDICATED ADC CORE x CONTROL REGISTER HIGH (x = 0 TO 1)

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	EISEL2	EISEL1	EISEL0	RES1	RES2
bit 15							bit 8

U-0	R/W-0						
_	ADCS6	ADCS5	ADCS4	ADCS3	ADCS2	ADCS1	ADCS0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-13 Unimplemented: Read as '0'

bit 12-10 EISEL<2:0>: ADC Core x Early Interrupt Time Selection bits

111 = Early interrupt is set and an interrupt is generated 8 TADCORE clocks prior to when the data is ready

110 = Early interrupt is set and an interrupt is generated 7 TADCORE clocks prior to when the data is ready

101 = Early interrupt is set and an interrupt is generated 6 TADCORE clocks prior to when the data is ready

100 = Early interrupt is set and an interrupt is generated 5 TADCORE clocks prior to when the data is ready

011 = Early interrupt is set and an interrupt is generated 4 TADCORE clocks prior to when the data is ready

010 = Early interrupt is set and an interrupt is generated 3 TADCORE clocks prior to when the data is ready

001 = Early interrupt is set and an interrupt is generated 2 TADCORE clocks prior to when the data is ready

000 = Early interrupt is set and an interrupt is generated 1 TADCORE clock prior to when the data is ready

bit 9-8 **RES<1:0>:** ADC Core x Resolution Selection bits

11 = 12-bit resolution

10 = 10-bit resolution

01 = 8-bit resolution⁽¹⁾

00 = 6-bit resolution⁽¹⁾

bit 7 **Unimplemented:** Read as '0'

bit 6-0 ADCS<6:0>: ADC Core x Input Clock Divider bits

These bits determine the number of Source Clock Periods (TCORESRC) for one Core Clock Period (TADCORE).

1111111 = 254 Source Clock Periods

. . .

0000011 = 6 Source Clock Periods

0000010 = 4 Source Clock Periods

0000001 = 2 Source Clock Periods

0000000 = 2 Source Clock Periods

Note 1: For the 6-bit ADC core resolution (RES<1:0> = 00), the EISEL<2:0> bits settings, from '100' to '111', are not valid and should not be used. For the 8-bit ADC core resolution (RES<1:0> = 01), the EISEL<2:0> bits settings, '110' and '111', are not valid and should not be used.

REGISTER 13-13: ADLVLTRGL: ADC LEVEL-SENSITIVE TRIGGER CONTROL REGISTER LOW⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
LVLEN<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
LVLEN<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 LVLEN<15:0>: Level Trigger for Corresponding Analog Input Enable bits

 $_1$ = Input trigger is level-sensitive

0 = Input trigger is edge-sensitive

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-14: ADLVLTRGH: ADC LEVEL-SENSITIVE TRIGGER CONTROL REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	LVLEN	<25:24>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
LVLEN<23:16>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 Unimplemented: Read as '0'

bit 9-0 LVLEN<25:16>: Level Trigger for Corresponding Analog Input Enable bits

1 = Input trigger is level-sensitive0 = Input trigger is edge-sensitive

REGISTER 13-15: ADEIEL: ADC EARLY INTERRUPT ENABLE REGISTER LOW(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
EIEN<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0				
	EIEN<7:0>										
bit 7							bit 0				

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **EIEN<15:0>:** Early Interrupt Enable for Corresponding Analog Inputs bits

1 = Early interrupt is enabled for the channel

0 = Early interrupt is disabled for the channel

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-16: ADEIEH: ADC EARLY INTERRUPT ENABLE REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	-	_	_		EIEN<25:24>	
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
EIEN<23:16>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 EIEN<25:16>: Early Interrupt Enable for Corresponding Analog Inputs bits

1 = Early interrupt is enabled for the channel

0 = Early interrupt is disabled for the channel

REGISTER 13-17: ADEISTATL: ADC EARLY INTERRUPT STATUS REGISTER LOW(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
EISTAT<15:8>							
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
EISTAT<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 EISTAT<15:0>: Early Interrupt Status for Corresponding Analog Inputs bits

1 = Early interrupt was generated

0 = Early interrupt was not generated since the last ADCBUFx read

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-18: ADEISTATH: ADC EARLY INTERRUPT STATUS REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	EISTAT<25:24>	
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
EISTAT<23:16>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 EISTAT<25:16>: Early Interrupt Status for Corresponding Analog Inputs bits

1 = Early interrupt was generated

0 = Early interrupt was not generated since the last ADCBUFx read

REGISTER 13-19: ADMODOL: ADC INPUT MODE CONTROL REGISTER 0 LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
DIFF7	SIGN7	DIFF6	SIGN6	DIFF5	SIGN5	DIFF4	SIGN4
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| DIFF3 | SIGN3 | DIFF2 | SIGN2 | DIFF1 | SIGN1 | DIFF0 | SIGN0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 through DIFF<1:0>: Differential-Mode for Corresponding Analog Inputs bits

bit 1 (odd) 1 = Channel is differential

0 = Channel is single-ended

bit 14 through SIGN<1:0>: Output Data Sign for Corresponding Analog Inputs bits

bit 0 (even) 1 = Channel output data is signed

0 = Channel output data is unsigned

REGISTER 13-20: ADMOD0H: ADC INPUT MODE CONTROL REGISTER 0 HIGH(1)

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| DIFF15 | SIGN15 | DIFF14 | SIGN14 | DIFF13 | SIGN13 | DIFF12 | SIGN12 |
| bit 15 | | | | | | | bit 8 |

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
DIFF11	SIGN11	DIFF10	SIGN10	DIFF9	SIGN9	DIFF8	SIGN8
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 through DIFF<15:8>: Differential-Mode for Corresponding Analog Inputs bits

bit 1 (odd) 1 = Channel is differential

0 = Channel is single-ended

bit 14 through SIGN<15:8>: Output Data Sign for Corresponding Analog Inputs bits

bit 0 (even) 1 = Channel output data is signed

0 = Channel output data is unsigned

REGISTER 13-21: ADMOD1L: ADC INPUT MODE CONTROL REGISTER 1 LOW⁽¹⁾

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| DIFF23 | SIGN23 | DIFF22 | SIGN22 | DIFF21 | SIGN21 | DIFF20 | SIGN20 |
| bit 15 | | | | | | | bit 8 |

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| DIFF19 | SIGN19 | DIFF18 | SIGN18 | DIFF17 | SIGN17 | DIFF16 | SIGN16 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 through DIFF<23:16>: Differential-Mode for Corresponding Analog Inputs bits

bit 1 (odd) 1 = Channel is differential

0 = Channel is single-ended

bit 14 through SIGN<23:16>: Output Data Sign for Corresponding Analog Inputs bits

bit 0 (even) 1 = Channel output data is signed

0 = Channel output data is unsigned

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-22: ADMOD1H: ADC INPUT MODE CONTROL REGISTER 1 HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_		_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	DIFF25	SIGN25	DIFF24	SIGN24
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 3 through DIFF<25:24>: Differential-Mode for Corresponding Analog Inputs bits

bit 1 (odd) 1 = Channel is differential

0 = Channel is single-ended

bit 2 through SIGN<25:24>: Output Data Sign for Corresponding Analog Inputs bits

bit 0 (even) 1 = Channel output data is signed

0 = Channel output data is unsigned

REGISTER 13-23: ADIEL: ADC INTERRUPT ENABLE REGISTER LOW(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
IE<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
IE<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **IE<15:0>:** Common Interrupt Enable bits

1 = Common and individual interrupts are enabled for the corresponding channel

0 = Common and individual interrupts are disabled for the corresponding channel

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-24: ADIEH: ADC INTERRUPT ENABLE REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	IE<25	5:24>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
IE<23:16>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 Unimplemented: Read as '0'

bit 9-0 **IE<25:16>:** Common Interrupt Enable bits

1 = Common and individual interrupts are enabled for the corresponding channel

0 = Common and individual interrupts are disabled for the corresponding channel

REGISTER 13-25: ADSTATL: ADC DATA READY STATUS REGISTER LOW(1)

HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0		
AN<15:8>RDY									
bit 15							bit 8		

HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	
AN<7:0>RDY								
bit 7							bit 0	

Legend: U = Unimplemented bit, read as '0'

R = Readable bit W = Writable bit HSC = Hardware Settable/Clearable bit

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 AN<15:0>RDY: Common Interrupt Enable for Corresponding Analog Inputs bits

1 = Channel conversion result is ready in the corresponding ADCBUFx register

0 = Channel conversion result is not ready

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-26: ADSTATH: ADC DATA READY STATUS REGISTER HIGH⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	HSC/R-0	HSC/R-0
_	_	_	_	_	_		
bit 15							bit 8

HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0		
AN<23:16>RDY									
bit 7							bit 0		

Legend: U = Unimplemented bit, read as '0'

R = Readable bit W = Writable bit HSC = Hardware Settable/Clearable bit

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 AN<25:16>RDY: Common Interrupt Enable for Corresponding Analog Inputs bits

1 = Channel conversion result is ready in the corresponding ADCBUFx register

0 = Channel conversion result is not ready

REGISTER 13-27: ADTRIGNL/ADTRIGNH: ADC CHANNEL TRIGGER n(x) SELECTION REGISTERS LOW AND HIGH $(x = 0 \text{ TO } 25; n = 0 \text{ TO } 6)^{(1)}$

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	TRGSRC(x+1)4	TRGSRC(x+1)3	TRGSRC(x+1)2	TRGSRC(x+1)1	TRGSRC(x+1)0
bit 15							bit 8

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	TRGSRCx4	TRGSRCx3	TRGSRCx2	TRGSRCx1	TRGSRCx0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 Unimplemented: Read as '0'

bit 12-8 TRGSRC(x+1)<4:0>: Trigger Source Selection for Corresponding Analog Inputs bits

(TRGSRC1 to TRGSRC25 - Odd)

11111 = ADTRG31 (PPS input)

11110 = PTG

11101 = CLC2

11100 **= CLC1**

11011 = MCCP9

11010 **= SCCP7**

11001 = SCCP6

11000 = SCCP5

10111 **= SCCP4**

10110 **= SCCP3**

10101 = SCCP2 10100 = SCCP1

10011 = PWM8 Trigger 2

10010 = PWM8 Trigger 1

10001 = PWM7 Trigger 2

10000 **= PWM7 Trigger 1**

01111 = PWM6 Trigger 2

01110 = PWM6 Trigger 1

01101 = PWM5 Trigger 2

01100 = PWM5 Trigger 1

01011 = PWM4 Trigger 2

01010 = PWM4 Trigger 1

01001 = PWM3 Trigger 2

010001 = PWM3 Trigger 1

00111 = PWM2 Trigger 2

00111 = PWM2 Trigger 1

00101 = PWM1 Trigger 2

00100 = PWM1 Trigger 1

00011 = Reserved

00010 = Level software trigger

00001 = Common software trigger

00000 = No trigger is enabled

bit 7-5 Unimplemented: Read as '0'

Note 1: The number of implemented registers is dependent on the number of available ADC channels. Refer to Table 1 and Table 2 for ADC channel availability of package variants.

REGISTER 13-27: ADTRIGNL/ADTRIGNH: ADC CHANNEL TRIGGER n(x) SELECTION REGISTERS LOW AND HIGH $(x = 0 \text{ TO } 25; n = 0 \text{ TO } 6)^{(1)}$ (CONTINUED)

```
bit 4-0
          TRGSRCx<4:0>: Common Interrupt Enable for Corresponding Analog Inputs bits
          (TRGSRC0 to TRGSRC24 – Even)
          11111 = ADTRG31 (PPS input)
          11110 = PTG
          11101 = CLC2
          11100 = CLC1
          11011 = MCCP9
          11010 = SCCP7
          11001 = SCCP6
          11000 = SCCP5
          10111 = SCCP4
          10110 = SCCP3
          10101 = SCCP2
          10100 = SCCP1
          10011 = PWM8 Trigger 2
          10010 = PWM8 Trigger 1
          10001 = PWM7 Trigger 2
          10000 = PWM7 Trigger 1
          01111 = PWM6 Trigger 2
          01110 = PWM6 Trigger 1
          01101 = PWM5 Trigger 2
          01100 = PWM5 Trigger 1
          01011 = PWM4 Trigger 2
          01010 = PWM4 Trigger 1
          01001 = PWM3 Trigger 2
          01000 = PWM3 Trigger 1
          00111 = PWM2 Trigger 2
          00110 = PWM2 Trigger 1
          00101 = PWM1 Trigger 2
          00100 = PWM1 Trigger 1
          00011 = Reserved
          00010 = Level software trigger
          00001 = Common software trigger
          00000 = No trigger is enabled
```

Note 1: The number of implemented registers is dependent on the number of available ADC channels. Refer to Table 1 and Table 2 for ADC channel availability of package variants.

REGISTER 13-28: ADCMPxCON: ADC DIGITAL COMPARATOR x CONTROL REGISTER (x = 0, 1, 2, 3)

U-0	U-0	U-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0
_	_	_	CHNL4	CHNL3	CHNL2	CHNL1	CHNL0
bit 15							bit 8

R/W-0	R/W-0	HS/HC/R-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CMPEN	IE	STAT	BTWN	HIHI	HILO	LOHI	LOLO
bit 7							bit 0

Legend:	HC = Hardware Clearable bit	oit U = Unimplemented bit, read as '0'		
R = Readable bit	W = Writable bit	HSC = Hardware Settable/Clearable bit		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	HS = Hardware Settable bit	

bit 15-13 Unimplemented: Read as '0'

bit 12-8 CHNL<4:0>: Input Channel Number bits

If the comparator has detected an event for a channel, this channel number is written to these bits.

11111 = Reserved

11010 = Reserved

11001 = Band gap, 1.2V (AN25)

11000 = Temperature sensor (AN24)

10111 **= AN23**

00011 = AN3

00010 = AN2

00001 = AN1

00000 = ANO

bit 7 **CMPEN:** Comparator Enable bit

1 = Comparator is enabled

0 = Comparator is disabled and the STAT status bit is cleared

IE: Comparator Common ADC Interrupt Enable bit bit 6

1 = Common ADC interrupt will be generated if the comparator detects a comparison event

0 = Common ADC interrupt will not be generated for the comparator

bit 5 **STAT:** Comparator Event Status bit

> This bit is cleared by hardware when the channel number is read from the CHNL<4:0> bits. 1 = A comparison event has been detected since the last read of the CHNL<4:0> bits

0 = A comparison event has not been detected since the last read of the CHNL<4:0> bits

bit 4 BTWN: Between Low/High Comparator Event bit

1 = Generates a comparator event when ADCMPxLO ≤ ADCBUFx < ADCMPxHI

0 = Does not generate a digital comparator event when ADCMPxLO ≤ ADCBUFx < ADCMPxHI</p>

bit 3 HIHI: High/High Comparator Event bit

1 = Generates a digital comparator event when ADCBUFx ≥ ADCMPxHI

0 = Does not generate a digital comparator event when ADCBUFx ≥ ADCMPxHI

bit 2 **HILO:** High/Low Comparator Event bit

1 = Generates a digital comparator event when ADCBUFx < ADCMPxHI

0 = Does not generate a digital comparator event when ADCBUFx < ADCMPxHI

bit 1 LOHI: Low/High Comparator Event bit

1 = Generates a digital comparator event when ADCBUFx ≥ ADCMPxLO

0 = Does not generate a digital comparator event when ADCBUFx ≥ ADCMPxLO

bit 0 LOLO: Low/Low Comparator Event bit

1 = Generates a digital comparator event when ADCBUFx < ADCMPxLO

0 = Does not generate a digital comparator event when ADCBUFx < ADCMPxLO

REGISTER 13-29: ADCMPXENL: ADC DIGITAL COMPARATOR x CHANNEL ENABLE REGISTER LOW (x = 0, 1, 2, 3)⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CMPEN<15:8>							
bit 15						bit 8	

R/W/0	R/W-0						
CMPEN<7:0>							
bit 7 bit							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 CMPEN<15:0>: Comparator Enable for Corresponding Input Channels bits

1 = Conversion result for corresponding channel is used by the comparator

0 = Conversion result for corresponding channel is not used by the comparator

Note 1: Bit availability is dependent on the number of supported ADC channels. Refer to Table 1 and Table 2 for ADC channel availability on package variants.

REGISTER 13-30: ADCMPXENH: ADC DIGITAL COMPARATOR x CHANNEL ENABLE REGISTER HIGH (x = 0, 1, 2, 3)⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	CMPEN	<25:24>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CMPEN<23:16>							
bit 7 bit (bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 CMPEN<25:16>: Comparator Enable for Corresponding Input Channels bits

1 = Conversion result for corresponding channel is used by the comparator

0 = Conversion result for corresponding channel is not used by the comparator

REGISTER 13-31: ADFLxCON: ADC DIGITAL FILTER x CONTROL REGISTER (x = 0, 1, 2, 3)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	HSC/R-0
FLEN	MODE1	MODE0	OVRSAM2	OVRSAM1	OVRSAM0	ΙE	RDY
bit 15							bit 8

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	FLCHSEL4	FLCHSEL3	FLCHSEL2	FLCHSEL1	FLCHSEL0
bit 7							bit 0

Legend:	U = Unimplemented bit, read as '0'				
R = Readable bit	W = Writable bit HSC = Hardware Settable/Clearable bit				
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15 **FLEN:** Filter Enable bit

1 = Filter is enabled

0 = Filter is disabled and the RDY bit is cleared

bit 14-13 MODE<1:0>: Filter Mode bits

11 = Averaging mode

10 = Reserved

01 = Reserved

00 = Oversampling mode

bit 12-10 **OVRSAM<2:0>:** Filter Averaging/Oversampling Ratio bits

If MODE<1:0> = 00:

111 = 128x (16-bit result in the ADFLxDAT register is in 12.4 format)

110 = 32x (15-bit result in the ADFLxDAT register is in 12.3 format)

101 = 8x (14-bit result in the ADFLxDAT register is in 12.2 format)

100 = 2x (13-bit result in the ADFLxDAT register is in 12.1 format)

011 = 256x (16-bit result in the ADFLxDAT register is in 12.4 format)

010 = 64x (15-bit result in the ADFLxDAT register is in 12.3 format)

001 = 16x (14-bit result in the ADFLxDAT register is in 12.2 format)

000 = 4x (13-bit result in the ADFLxDAT register is in 12.1 format)

If MODE<1:0> = 11 (12-bit result in the ADFLxDAT register in all instances):

111 = 256x

110 **= 128x**

101 = 64x

100 **= 32x**

011 = 16x

110 **= 8x**

001 = 4x

000 **= 2**x

bit 9 IE: Filter Common ADC Interrupt Enable bit

1 = Common ADC interrupt will be generated when the filter result will be ready

0 = Common ADC interrupt will not be generated for the filter

bit 8 RDY: Oversampling Filter Data Ready Flag bit

This bit is cleared by hardware when the result is read from the ADFLxDAT register.

1 = Data in the ADFLxDAT register is ready

0 = The ADFLxDAT register has been read and new data in the ADFLxDAT register is not ready

bit 7-5 **Unimplemented:** Read as '0'

REGISTER 13-31: ADFLxCON: ADC DIGITAL FILTER x CONTROL REGISTER (x = 0, 1, 2, 3) (CONTINUED)

```
bit 4-0

FLCHSEL<4:0>: Oversampling Filter Input Channel Selection bits

11111 = Reserved
...

11010 = Reserved
11001 = Band gap, 1.2V (AN25)
11000 = Temperature sensor (AN24)
10111 = AN23
...

00011 = AN3
00010 = AN2
00001 = AN1
00000 = AN0
```

14.0 HIGH-SPEED ANALOG COMPARATOR WITH SLOPE COMPENSATION DAC

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "High-Speed Analog Comparator Module" (www.microchip.com/DS70005280) in the "dsPIC33/PIC24 Family Reference Manual".

The high-speed analog comparator module provides a method to monitor voltage, current and other critical signals in a power conversion application that may be too fast for the CPU and ADC to capture. There are a total of 3 comparator modules. The analog comparator module can be used to implement Peak Current mode control, Critical Conduction mode (variable frequency) and Hysteretic Control mode.

14.1 Overview

The high-speed analog comparator module is comprised of a high-speed comparator, Pulse Density Modulation (PDM) DAC and a slope compensation unit. The slope compensation unit provides a user-defined slope which can be used to alter the DAC output. This feature is useful in applications, such as Peak Current mode control, where slope compensation is required to maintain the stability of the power supply. The user simply specifies the direction and rate of change for the slope compensation and the output of the DAC is modified accordingly.

The DAC consists of a PDM unit, followed by a digitally controlled multiphase RC filter. The PDM unit uses a phase accumulator circuit to generate an output stream of pulses. The density of the pulse stream is proportional to the input data value, relative to the maximum value supported by the bit width of the accumulator. The output pulse density is representative of the desired output voltage. The pulse stream is filtered with an RC filter to yield an analog voltage. The output of the DAC is connected to the negative input of the comparator. The positive input of the comparator can be selected using a MUX from either of the input pins. The comparator provides a high-speed operation with a typical delay of 15 ns.

The output of the comparator is processed by the pulse stretcher and the digital filter blocks, which prevent comparator response to unintended fast transients in the inputs. Figure 14-1 shows a block diagram of the high-speed analog comparator module. The DAC module can be operated in one of three modes: Slope Generation mode, Hysteretic mode and Triangle Wave mode. Each of these modes can be used in a variety of power supply applications.

Note:

The DACOUT1 pin can only be associated with a single DAC output at any given time. If more than one DACOEN bit is set, the DACOUT1 pin will be a combination of the signals.




FIGURE 14-1: HIGH-SPEED ANALOG COMPARATOR MODULE BLOCK DIAGRAM

14.2 Features Overview

- Three Rail-to-Rail Analog Comparators
- Up to Four Selectable Input Sources per Comparator
- Programmable Comparator Hysteresis
- Programmable Output Polarity
- · Interrupt Generation Capability
- Dedicated Pulse Density Modulation DAC for each Analog Comparator:
 - PDM unit followed by a digitally controlled multimode multipole RC filter
- Multimode Multipole RC Output Filter:
 - Transition mode: Provides the fastest response
 - Fast mode: For tracking DAC slopes
 - Steady-State mode: Provides 12-bit resolution
- Slope Compensation along with each DAC:
 - Slope Generation mode
 - Hysteretic Control mode
 - Triangle Wave mode
- Functional Support for the High-Speed PWM module which Includes:
 - PWM duty cycle control
 - PWM period control
 - PWM Fault detect

14.3 Control Registers

The DACCTRL1L and DACCTRL2H/L registers are common configuration registers for DAC modules.

The DACxCON, DACxDAT, SLPxCON and SLPxDAT registers specify the operation of individual modules.

REGISTER 14-1: DACCTRL1L: DAC CONTROL 1 LOW REGISTER

R/W-0	U-0	R/W-0	U-0	U-0	U-0	U-0	U-0
DACON	_	DACSIDL	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
CLKSEL1 ^(1,3)	CLKSEL0 ^(1,3)	CLKDIV1 ^(1,3)	CLKDIV0 ^(1,3)	_	FCLKDIV2 ⁽²⁾	FCLKDIV1 ⁽²⁾	FCLKDIV0 ⁽²⁾
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15 DACON: Common DAC Module Enable bit

1 = Enables DAC modules

0 = Disables DAC modules and disables FSCM clocks to reduce power consumption; any pending Slope mode and/or underflow conditions are cleared

bit 14 **Unimplemented:** Read as '0'

bit 13 DACSIDL: DAC Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12-8 **Unimplemented:** Read as '0'

bit 7-6 CLKSEL<1:0>: DAC Clock Source Select bits^(1,3)

11 = FPLLO

10 = AFPLLO

01 = Fvco/2

00 = AFvco/2

bit 5-4 CLKDIV<1:0>: DAC Clock Divider bits^(1,3)

11 = Divide-by-4

10 = Divide-by-3 (non-uniform duty cycle)

01 = Divide-by-2

00 = 1x

bit 3 **Unimplemented:** Read as '0'

bit 2-0 FCLKDIV<2:0>: Comparator Filter Clock Divider bits⁽²⁾

111 = Divide-by-8

110 = Divide-by-7

101 = Divide-by-6

100 = Divide-by-5

011 = Divide-by-4

010 = Divide-by-3

001 = Divide-by-2

000 = 1x

Note 1: These bits should only be changed when DACON = 0 to avoid unpredictable behavior.

2: The input clock to this divider is the selected clock input, CLKSEL<1:0>, and then divided by two.

3: Clock source and dividers should yield an effective DAC clock input of 500 MHz.

REGISTER 14-2: DACCTRL2H: DAC CONTROL 2 HIGH REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	SSTIME	<9:8> ⁽¹⁾
bit 15							bit 8

R/W-1	R/W-0	R/W-0	R/W-0	R/W-1	R/W-0	R/W-1	R/W-0	
SSTIME<7:0>(1)								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 SSTIME<9:0>: Time from Start of Transition Mode until Steady-State Filter is Enabled bits⁽¹⁾

Note 1: The value for SSTIME<9:0> should be greater than the TMODTIME<9:0> value.

REGISTER 14-3: DACCTRL2L: DAC CONTROL 2 LOW REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	TMODTIM	1E<9:8> ⁽¹⁾
bit 15							bit 8

R/W-0	R/W-1	R/W-0	R/W-1	R/W-0	R/W-1	R/W-0	R/W-1
			TMODTIN	1E<7:0> ⁽¹⁾			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 **TMODTIME<9:0>:** Transition Mode Duration bits⁽¹⁾

Note 1: The value for TMODTIME<9:0> should be less than the SSTIME<9:0> value.

REGISTER 14-4: DACxCONH: DACx CONTROL HIGH REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
_	_	_	_	_	_	TMCE	3<9:8>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			TMCE	3<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 TMCB<9:0>: DACx Leading-Edge Blanking bits

These register bits specify the blanking period for the comparator, following changes to the DAC output during Change-of-State (COS), for the input signal selected by the HCFSEL<3:0> bits in Register 14-9.

REGISTER 14-5: DACxCONL: DACx CONTROL LOW REGISTER

R/W-0	R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0
DACEN	IRQM1 ^(1,2)	IRQM0 ^(1,2)	_	_	CBE	DACOEN	FLTREN
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CMPSTAT	CMPPOL	INSEL2	INSEL1	INSEL0	HYSPOL	HYSSEL1	HYSSEL0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15 DACEN: Individual DACx Module Enable bit

1 = Enables DACx module

0 = Disables DACx module to reduce power consumption; any pending Slope mode and/or underflow conditions are cleared

bit 14-13 IRQM<1:0>: Interrupt Mode select bits^(1,2)

11 = Generates an interrupt on either a rising or falling edge detect

10 = Generates an interrupt on a falling edge detect

01 = Generates an interrupt on a rising edge detect

00 = Interrupts are disabled

bit 12-11 **Unimplemented:** Read as '0'

Note 1: Changing these bits during operation may generate a spurious interrupt.

2: The edge selection is a post-polarity selection via the CMPPOL bit.

REGISTER 14-5: DACxCONL: DACx CONTROL LOW REGISTER (CONTINUED)

bit 10 CBE: Comparator Blank Enable bit

- 1 = Enables the analog comparator output to be blanked (gated off) during the recovery transition following the completion of a slope operation
- 0 = Disables the blanking signal to the analog comparator; therefore, the analog comparator output is always active
- bit 9 DACOEN: DACx Output Buffer Enable bit
 - 1 = DACx analog voltage is connected to the DACOUT1 pin
 - 0 = DACx analog voltage is not connected to the DACOUT1 pin
- bit 8 FLTREN: Comparator Digital Filter Enable bit
 - 1 = Digital filter is enabled
 - 0 = Digital filter is disabled
- bit 7 CMPSTAT: Comparator Status bits
 - The current state of the comparator output including the CMPPOL selection.
- bit 6 CMPPOL: Comparator Output Polarity Control bit
 - 1 = Output is inverted
 - 0 = Output is non-inverted
- bit 5-3 INSEL<2:0>: Comparator Input Source Select bits
 - 111 = Reserved
 - 110 = Reserved
 - 101 = Reserved
 - 100 = Reserved
 - 011 = CMPxD input pin
 - 010 = CMPxC input pin
 - 001 = CMPxB input pin
 - 000 = CMPxA input pin
- bit 2 HYSPOL: Comparator Hysteresis Polarity Select bit
 - 1 = Hysteresis is applied to the falling edge of the comparator output
 - 0 = Hysteresis is applied to the rising edge of the comparator output
- bit 1-0 **HYSSEL<1:0>:** Comparator Hysteresis Select bits
 - 11 = 45 mv hysteresis
 - 10 = 30 mv hysteresis
 - 01 = 15 mv hysteresis
 - 00 = No hysteresis is selected
- **Note 1:** Changing these bits during operation may generate a spurious interrupt.
 - 2: The edge selection is a post-polarity selection via the CMPPOL bit.

REGISTER 14-6: DACxDATH: DACx DATA HIGH REGISTER

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_		DACDA	T<11:8>	
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			DACDA	AT<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-12 **Unimplemented:** Read as '0' bit 11-0 **DACDAT<11:0>:** DACx Data bits

This register specifies the high DACx data value. Valid values are from 205 to 3890.

REGISTER 14-7: DACXDATL: DACX DATA LOW REGISTER

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_		DACLO	W<11:8>	
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
DACLOW<7:0>							
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-12 **Unimplemented:** Read as '0'

bit 11-0 DACLOW<11:0>: DACx Low Data bits

In Hysteretic mode, Slope Generator mode and Triangle mode, this register specifies the low data value and/or limit for the DACx module. Valid values are from 205 to 3890.

REGISTER 14-8: SLPxCONH: DACx SLOPE CONTROL HIGH REGISTER

R/W-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	U-0
SLOPEN	_	_	_	HME ⁽¹⁾	TWME ⁽²⁾	PSE	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15 **SLOPEN:** Slope Function Enable/On bit

1 = Enables slope function

0 = Disables slope function; slope accumulator is disabled to reduce power consumption

bit 14-12 **Unimplemented:** Read as '0'

bit 11 **HME**: Hysteretic Mode Enable bit⁽¹⁾

1 = Enables Hysteretic mode for DACx

0 = Disables Hysteretic mode for DACx

bit 10 **TWME:** Triangle Wave Mode Enable bit⁽²⁾

1 = Enables Triangle Wave mode for DACx

0 = Disables Triangle Wave mode for DACx

bit 9 PSE: Positive Slope Mode Enable bit

1 = Slope mode is positive (increasing)

0 = Slope mode is negative (decreasing)

bit 8-0 **Unimplemented:** Read as '0'

Note 1: HME mode requires the user to disable the slope function (SLOPEN = 0).

2: TWME mode requires the user to enable the slope function (SLOPEN = 1).

REGISTER 14-9: SLPxCONL: DACx SLOPE CONTROL LOW REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
HCFSEL3	HCFSEL2	HCFSEL1	HCFSEL0	SLPSTOPA3	SLPSTOPA2	SLPSTOPA1	SLPSTOPA0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SLPSTOPB3	SLPSTOPB2	SLPSTOPB1	SLPSTOPB0	SLPSTRT3	SLPSTRT2	SLPSTRT1	SLPSTRT0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set0 '0' = Bit is cleared

bit 15-12 **HCFSEL<3:0>:** Hysteretic Comparator Function Input Select bits

The selected input signal controls the switching between the DACx high limit (DACxDATH) and the DACx low limit (DACxDATL) as the data source for the PDM DAC. It modifies the polarity of the comparator, and the rising and falling edges initiate the start of the LEB counter (TMCB<9:0> bits in Register 14-4).

Input Selection	Source
1111	1
1100	0
1011	0
1010	0
1001	0
1000	PWM8H
0111	PWM7H
0110	PWM6H
0101	PWM5H
0100	PWM4H
0011	PWM3H
0010	PWM2H
0001	PWM1H
0000	0

REGISTER 14-9: SLPxCONL: DACx SLOPE CONTROL LOW REGISTER (CONTINUED)

bit 11-8 SLPSTOPA<3:0>: Slope Stop A Signal Select bits

The selected Slope Stop A signal is logically OR'd with the selected Slope Stop B signal to terminate the slope function.

Slope Stop A Signal Selection	Master
1101-1111	1
1000	PWM8 Trigger 2
0111	PWM7 Trigger 2
0110	PWM6 Trigger 2
0101	PWM5 Trigger 2
0100	PWM4 Trigger 2
0011	PWM3 Trigger 2
0010	PWM2 Trigger 2
0001	PWM1 Trigger 2
0000	0

bit 7-4 **SLPSTOPB<3:0>:** Slope Stop B Signal Select bits

The selected Slope Stop B signal is logically OR'd with the selected Slope Stop A signal to terminate the slope function.

Slope Start B Signal Selection	Master
0100-1111	1
0011	CMP3 Out
0010	CMP2 Out
0001	CMP1 Out
0000	0

bit 3-0 **SLPSTRT<3:0>:** Slope Start Signal Select bits

Slope Start Signal Selection	Master
1101-1111	1
1000	PWM8 Trigger 1
0111	PWM7 Trigger 1
0110	PWM6 Trigger 1
0101	PWM5 Trigger 1
0100	PWM4 Trigger 1
0011	PWM3 Trigger 1
0010	PWM2 Trigger 1
0001	PWM1 Trigger 1
0000	0

REGISTER 14-10: SLPxDAT: DACx SLOPE DATA REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			SLPDA	Γ<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			SLPDA	T<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared

bit 15-0 **SLPDAT<15:0>:** Slope Ramp Rate Value bits

The SLPDATx value is in 12.4 format.

Note 1: Register data is left justified.

15.0 QUADRATURE ENCODER INTERFACE (QEI)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive resource. For more information, refer to "Quadrature Encoder Interface (QEI)" (www.microchip.com/DS70000601) in the "dsPIC33/PIC24 Family Reference Manual".

The Quadrature Encoder Interface (QEI) module provides the interface to incremental encoders for obtaining mechanical position data. The dsPIC33CK256MP508 family implements two instances of the QEI. Quadrature Encoders, also known as incremental encoders or optical encoders, detect position and speed of rotating motion systems. Quadrature Encoders enable closed-loop control of motor control applications, such as Switched Reluctance (SR) and AC Induction Motors (ACIM).

A typical Quadrature Encoder includes a slotted wheel attached to the shaft of the motor and an emitter/detector module that senses the slots in the wheel. Typically, three output channels, Phase A (QEAx),

Phase B (QEBx) and Index (INDXx), provide information on the movement of the motor shaft, including distance and direction.

The two channels, Phase A (QEAx) and Phase B (QEBx), are typically 90 degrees out of phase with respect to each other. The Phase A and Phase B channels have a unique relationship. If Phase A leads Phase B, the direction of the motor is deemed positive or forward. If Phase A lags Phase B, the direction of the motor is deemed negative or reverse. The Index pulse occurs once per mechanical revolution and is used as a reference to indicate an absolute position. Figure 15-1 illustrates the Quadrature Encoder Interface signals.

The Quadrature signals from the encoder can have four unique states ('01', '00', '10' and '11') that reflect the relationship between QEAx and QEBx. Figure 15-1 illustrates these states for one count cycle. The order of the states get reversed when the direction of travel changes.

The Quadrature Decoder increments or decrements the 32-bit up/down Position x Counter (POSxCNTH/L) registers for each Change-of-State (COS). The counter increments when QEAx leads QEBx and decrements when QEBx leads QEAx.




FIGURE 15-1: QUADRATURE ENCODER INTERFACE SIGNALS

Table 15-1 shows the truth table that describes how the Quadrature signals are decoded.


TABLE 15-1: TRUTH TABLE FOR QUADRATURE ENCODER

Quad	rent rature ate	Quad	rious rature ate	Action
QEA	QEB	QEA	QEB	
1	1	1	1	No count or direction change
1	1	1	0	Count up
1	1	0	1	Count down
1	1	0	0	Invalid state change; ignore
1	0	1	1	Count down
1	0	1	0	No count or direction change
1	0	0	1	Invalid state change; ignore
1	0	0	0	Count up
0	1	1	1	Count up
0	1	1	0	Invalid state change; ignore
0	1	0	1	No count or direction change
0	1	0	0	Count down
0	0	1	1	Invalid state change; ignore
0	0	1	0	Count down
0	0	0	1	Count up
0	0	0	0	No count or direction change

Figure 15-2 illustrates the simplified block diagram of the QEI module. The QEI module consists of decoder logic to interpret the Phase A (QEAx) and Phase B (QEBx) signals, and an up/down counter to accumulate the count. The counter pulses are generated when the Quadrature state changes. The count direction information must be maintained in a register until a direction change is detected. The module also includes digital noise filters, which condition the input signal.

The QEI module consists of the following major features:

- Four Input Pins: Two Phase Signals, an Index Pulse and a Home Pulse
- · Programmable Digital Noise Filters on Inputs
- Quadrature Decoder providing Counter Pulses and Count Direction
- · Count Direction Status
- · 4x Count Resolution
- Index (INDXx) Pulse to Reset the Position Counter
- General Purpose 32-Bit Timer/Counter mode
- · Interrupts generated by QEI or Counter Events
- · 32-Bit Velocity Counter
- · 32-Bit Position Counter
- · 32-Bit Index Pulse Counter
- · 32-Bit Interval Timer
- · 32-Bit Position Initialization/Capture Register
- 32-Bit Compare Less Than and Greater Than Registers
- · External Up/Down Count mode
- · External Gated Count mode
- · External Gated Timer mode
- · Interval Timer mode



15.1 QEI Control and Status Registers

REGISTER 15-1: QEIXCON: QEIX CONTROL REGISTER

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
QEIEN	_	QEISIDL	PIMOD2 ^(1,5)	PIMOD1 ^(1,5)	PIMOD0 ^(1,5)	IMV1 ⁽²⁾	IMV0 ⁽²⁾
bit 15							bit 8

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	INTDIV2 ⁽³⁾	INTDIV1 ⁽³⁾	INTDIV0 ⁽³⁾	CNTPOL	GATEN	CCM1	CCM0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 QEIEN: Quadrature Encoder Interface Module Enable bit

1 = Module counters are enabled

0 = Module counters are disabled, but SFRs can be read or written

bit 14 Unimplemented: Read as '0'

bit 13 QEISIDL: QEI Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12-10 PIMOD<2:0>: Position Counter Initialization Mode Select bits^(1,5)

111 = Modulo Count mode for position counter and every Index event resets the position counter (4)

110 = Modulo Count mode for position counter

101 = Resets the position counter when the position counter equals the QEIxGEC register

100 = Second Index event after Home event initializes position counter with contents of QEIxIC register

011 = First Index event after Home event initializes position counter with contents of QEIxIC register

010 = Next Index input event initializes the position counter with contents of QEIxIC register

001 = Every Index input event resets the position counter

000 = Index input event does not affect the position counter

bit 9-8 **IMV<1:0>:** Index Match Value bits⁽²⁾

11 = Index match occurs when QEBx = 1 and QEAx = 1

10 = Index match occurs when QEBx = 1 and QEAx = 0

01 = Index match occurs when QEBx = 0 and QEAx = 1

00 = Index match occurs when QEBx = 0 and QEAx = 0

bit 7 **Unimplemented:** Read as '0'

Note 1: When CCMx = 10 or CCMx = 11, all of the QEI counters operate as timers and the PIMOD<2:0> bits are ignored.

- 2: When CCMx = 00, and QEAx and QEBx values match the Index Match Value (IMV), the POSxCNTH and POSxCNTL registers are reset.
- 3: The selected clock rate should be at least twice the expected maximum quadrature count rate.
- 4: Not all devices support this mode.
- **5:** The QCAPEN and HCAPEN bits must be cleared during PIMODx Modes 2 through 7 to ensure proper functionality. Not all devices support HCAPEN.

REGISTER 15-1: QEIXCON: QEIX CONTROL REGISTER (CONTINUED)

bit 6-4 INTDIV<2:0>: Timer Input Clock Prescale Select bits⁽³⁾

(interval timer, main timer (position counter), velocity counter and Index counter internal clock divider select)

- 111 = 1:256 prescale value
- 110 = 1:64 prescale value
- 101 = 1:32 prescale value
- 100 = 1:16 prescale value
- 011 = 1:8 prescale value
- 010 = 1:4 prescale value
- 001 = 1:2 prescale value
- 000 = 1:1 prescale value
- bit 3 CNTPOL: Position and Index Counter/Timer Direction Select bit
 - 1 = Counter direction is negative unless modified by external up/down signal
 - 0 = Counter direction is positive unless modified by external up/down signal
- bit 2 GATEN: External Count Gate Enable bit
 - 1 = External gate signal controls position counter operation
 - 0 = External gate signal does not affect position counter operation
- bit 1-0 CCM<1:0>: Counter Control Mode Selection bits
 - 11 = Internal Timer mode
 - 10 = External Clock Count with External Gate mode
 - 01 = External Clock Count with External Up/Down mode
 - 00 = Quadrature Encoder mode
- Note 1: When CCMx = 10 or CCMx = 11, all of the QEI counters operate as timers and the PIMOD<2:0> bits are ignored.
 - 2: When CCMx = 00, and QEAx and QEBx values match the Index Match Value (IMV), the POSxCNTH and POSxCNTL registers are reset.
 - 3: The selected clock rate should be at least twice the expected maximum quadrature count rate.
 - **4:** Not all devices support this mode.
 - **5:** The QCAPEN and HCAPEN bits must be cleared during PIMODx Modes 2 through 7 to ensure proper functionality. Not all devices support HCAPEN.

REGISTER 15-2: QEIXIOC: QEIX I/O CONTROL REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
QCAPEN	FLTREN	QFDIV2	QFDIV1	QFDIV0	OUTFNC1	OUTFNC0	SWPAB
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R-x	R-x	R-x	R-x
HOMPOL	IDXPOL	QEBPOL	QEAPOL	HOME	INDEX	QEB	QEA
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 QCAPEN: QEIx Position Counter Input Capture Enable bit

1 = HOMEx input event (positive edge) triggers a position capture event (HCAPEN must be cleared)

0 = HOMEx input event (positive edge) does not trigger a position capture event

bit 14 FLTREN: QEAx/QEBx/INDXx/HOMEx Digital Filter Enable bit

1 = Input pin digital filter is enabled

0 = Input pin digital filter is disabled (bypassed)

bit 13-11 QFDIV<2:0>: QEAx/QEBx/INDXx/HOMEx Digital Input Filter Clock Divide Select bits

111 = 1:256 clock divide

110 = 1:64 clock divide

101 = 1:32 clock divide

100 = 1:16 clock divide

011 = 1:8 clock divide

010 = 1:4 clock divide

001 = 1:2 clock divide

000 = 1:1 clock divide

bit 10-9 OUTFNC<1:0>: QEIx Module Output Function Mode Select bits

11 = The QEICMPx pin goes high when POSxCNT < QEIxLEC or POSxCNT > QEIxGEC

10 = The QEICMPx pin goes high when POSxCNT ≤ QEIxLEC

01 = The QEICMPx pin goes high when POSxCNT ≥ QEIxGEC

00 = Output is disabled

bit 8 SWPAB: Swap QEAx and QEBx Inputs bit

1 = QEAx and QEBx are swapped prior to Quadrature Decoder logic

0 = QEAx and QEBx are not swapped

bit 7 HOMPOL: HOMEx Input Polarity Select bit

1 = Input is inverted

0 = Input is not inverted

bit 6 IDXPOL: INDXx Input Polarity Select bit

1 = Input is inverted

0 = Input is not inverted

bit 5 **QEBPOL:** QEBx Input Polarity Select bit

1 = Input is inverted

0 = Input is not inverted

bit 4 QEAPOL: QEAx Input Polarity Select bit

1 = Input is inverted

0 = Input is not inverted

bit 3 **HOME:** Status of HOMEx Input Pin After Polarity Control bit (read-only)

1 = Pin is at logic '1' if the HOMPOL bit is set to '0'; pin is at logic '0' if the HOMPOL bit is set to '1'

0 = Pin is at logic '0' if the HOMPOL bit is set to '0'; pin is at logic '1' if the HOMPOL bit is set to '1'

REGISTER 15-2: QEIXIOC: QEIX I/O CONTROL REGISTER (CONTINUED)

- bit 2 INDEX: Status of INDXx Input Pin After Polarity Control bit (read-only)
 - 1 = Pin is at logic '1' if the IDXPOL bit is set to '0'; pin is at logic '0' if the IDXPOL bit is set to '1'
 - 0 = Pin is at logic '0' if the IDXPOL bit is set to '0'; pin is at logic '1' if the IDXPOL bit is set to '1'
- bit 1 QEB: Status of QEBx Input Pin After Polarity Control and SWPAB Pin Swapping bit (read-only)
 - 1 = Physical pin, QEBx, is at logic '1' if the QEBPOL bit is set to '0' and the SWPAB bit is set to '0'; physical pin, QEBx, is at logic '0' if the QEBPOL bit is set to '1' and the SWPAB bit is set to '0'; physical pin, QEAx, is at logic '1' if the QEBPOL bit is set to '0' and the SWPAB bit is set to '1'; physical pin, QEAx, is at logic '0' if the QEBPOL bit is set to '1' and the SWPAB bit is set to '1'
 - 0 = Physical pin, QEBx, is at logic '0' if the QEBPOL bit is set to '0' and the SWPAB bit is set to '0'; physical pin, QEBx, is at logic '1' if the QEBPOL bit is set to '1' and the SWPAB bit is set to '0'; physical pin, QEAx, is at logic '0' if the QEBPOL bit is set to '0' and the SWPAB bit is set to '1'; physical pin, QEAx, is at logic '1' if the QEBPOL bit is set to '1' and the SWPAB bit is set to '1'
- bit 0 QEA: Status of QEAx Input Pin After Polarity Control and SWPAB Pin Swapping bit (read-only)
 - 1 = Physical pin, QEAx, is at logic '1' if the QEAPOL bit is set to '0' and the SWPAB bit is set to '0'; physical pin, QEAx, is at logic '0' if the QEAPOL bit is set to '1' and the SWPAB bit is set to '0'; physical pin, QEBx, is at logic '1' if the QEAPOL bit is set to '0' and the SWPAB bit is set to '1'; physical pin, QEBx, is at logic '0' if the QEAPOL bit is set to '1' and the SWPAB bit is set to '1'
 - 0 = Physical pin, QEAx, is at logic '0' if the QEAPOL bit is set to '0' and the SWPAB bit is set to '0'; physical pin, QEAx, is at logic '1' if the QEAPOL bit is set to '1' and the SWPAB bit is set to '0'; physical pin, QEBx, is at logic '0' if the QEAPOL bit is set to '0' and the SWPAB bit is set to '1'; physical pin, QEBx, is at logic '1' if the QEAPOL bit is set to '1' and the SWPAB bit is set to '1'

REGISTER 15-3: QEIXIOCH: QEIX I/O CONTROL HIGH REGISTER⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	HCAPEN
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-1 Unimplemented: Read as '0'

bit 0 HCAPEN: Position Counter Input Capture by Home Event Enable bit

1 = HOMEx input event (positive edge) triggers a position capture event

0 = HOMEx input event (positive edge) does not trigger a position capture event

Note 1: This register is not present on all devices.

REGISTER 15-4: QEIXSTAT: QEIX STATUS REGISTER

U-0	U-0	HS/R/C-0	R/W-0	HS/R/C-0	R/W-0	HS/R/C-0	R/W-0
_	_	PCHEQIRQ	PCHEQIEN	PCLEQIRQ	PCLEQIEN	POSOVIRQ	POSOVIEN
bit 15		•					bit 8

HS/R/C-0	R/W-0	HS/R/C-0	R/W-0	HS/R/C-0	R/W-0	HS/R/C-0	R/W-0
PCIIRQ ⁽¹⁾	PCIIEN	VELOVIRQ	VELOVIEN	HOMIRQ	HOMIEN	IDXIRQ	IDXIEN
bit 7		•					bit 0

Legend:	C = Clearable bit	HS = Hardware Settable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15-14 Unimplemented: Read as '0'

bit 13 PCHEQIRQ: Position Counter Greater Than Compare Status bit

1 = POSxCNT ≥ QEIxGEC 0 = POSxCNT < QEIxGEC

bit 12 PCHEQIEN: Position Counter Greater Than Compare Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 11 PCLEQIRQ: Position Counter Less Than Compare Status bit

1 = POSxCNT ≤ QEIxLEC 0 = POSxCNT > QEIxLEC

bit 10 PCLEQIEN: Position Counter Less Than Compare Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 9 **POSOVIRQ:** Position Counter Overflow Status bit

1 = Overflow has occurred0 = No overflow has occurred

bit 8 **POSOVIEN:** Position Counter Overflow Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 7 **PCIIRQ:** Position Counter (Homing) Initialization Process Complete Status bit⁽¹⁾

1 = POSxCNT was reinitialized0 = POSxCNT was not reinitialized

bit 6 PCIIEN: Position Counter (Homing) Initialization Process Complete Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 5 **VELOVIRQ:** Velocity Counter Overflow Status bit

1 = Overflow has occurred0 = No overflow has occurred

bit 4 **VELOVIEN:** Velocity Counter Overflow Interrupt Enable bit

1 = Interrupt is enabled 0 = Interrupt is disabled

bit 3 **HOMIRQ:** Status Flag for Home Event Status bit

1 = Home event has occurred 0 = No Home event has occurred

Note 1: This status bit is only applicable to PIMOD<2:0> modes, '011' and '100'.

REGISTER 15-4: QEIXSTAT: QEIX STATUS REGISTER (CONTINUED)

bit 2 **HOMIEN:** Home Input Event Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 1

IDXIRQ: Status Flag for Index Event Status bit

1 = Index event has occurred0 = No Index event has occurred

bit 0 IDXIEN: Index Input Event Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

Note 1: This status bit is only applicable to PIMOD<2:0> modes, '011' and '100'.

REGISTER 15-5: POSxCNTL: POSITION x COUNTER REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			POSCN	T<15:8>			
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | | | | | |
| bit 7 | | | | | | bit 0 | |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 POSCNT<15:0>: Low Word Used to Form 32-Bit Position Counter Register (POSxCNT) bits

REGISTER 15-6: POSxCNTH: POSITION x COUNTER REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			POSCN ⁻	Γ<31:24>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			POSCN ⁻	T<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 POSCNT<31:16>: High Word Used to Form 32-Bit Position Counter Register (POSxCNT) bits

REGISTER 15-7: POSxHLD: POSITION x COUNTER HOLD REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	POSHLD<15:8>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			POSH	LD<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **POSHLD<15:0>:** Hold Register for Reading/Writing Position x Counter High Word Register (POSxCNTH) bits

REGISTER 15-8: VELXCNT: VELOCITY x COUNTER REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
VELCNT<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			VELCN	IT<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **VELCNT<15:0>:** Velocity Counter bits

REGISTER 15-9: VELxCNTH: VELOCITY x COUNTER REGISTER HIGH(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			VELCN1	Γ<31:24>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			VELCN	Γ<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **VELCNT<31:16>:** Velocity Counter bits

Note 1: This register is not present on all devices.

REGISTER 15-10: VELXHLD: VELOCITY x COUNTER HOLD REGISTER(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			VELHLI	D<15:8>			
bit 15							bit 8
R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			VELHL	.D<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **VELHLD<15:0>:** Hold for Reading/Writing Velocity Counter Register (VELxCNT) bits

Note 1: This register is not present on all devices.

REGISTER 15-11: INTXTMRL: INTERVAL x TIMER REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
INTTMR<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
INTTMR<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INTTMR<15:0>: Low Word Used to Form 32-Bit Interval Timer Register (INTxTMR) bits

REGISTER 15-12: INTXTMRH: INTERVAL x TIMER REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTTMF	R<31:24>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTTMR	?<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INTTMR<31:16>: High Word Used to Form 32-Bit Interval Timer Register (INTxTMR) bits

REGISTER 15-13: INTXxHLDL: INTERVAL x TIMER HOLD REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTHLE	0<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTHL	D<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INTHLD<15:0>: Low Word Used to Form 32-Bit Interval Timer Hold Register (INTxHLD) bits

REGISTER 15-14: INTXxHLDH: INTERVAL x TIMER HOLD REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTHLD	<31:24>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INTHLD	<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INTHLD<31:16>: High Word Used to Form 32-Bit Interval Timer Hold Register (INTxHLD) bits

REGISTER 15-15: INDXxCNTL: INDEX x COUNTER REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INDXCN	IT<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INDXCI	NT<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INDXCNT<15:0>: Low Word Used to Form 32-Bit Index x Counter Register (INDXxCNT) bits

REGISTER 15-16: INDXxCNTH: INDEX x COUNTER REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INDXCN	T<31:24>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INDXCN	T<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INDXCNT<31:16>: High Word Used to Form 32-Bit Index x Counter Register (INDXxCNT) bits

REGISTER 15-17: INDXxHLD: INDEX x COUNTER HOLD REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
INDXHLD<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			INDXHI	_D<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 INDXHLD<15:0>: Hold Register for Reading/Writing Index x Counter High Word Register (INDXxCNTH) bits

REGISTER 15-18: QEIXICL: QEIX INITIALIZATION/CAPTURE REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			QEIIC	<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
QEIIC<7:0>								
bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 QEIIC<15:0>: Low Word Used to Form 32-Bit Initialization/Capture Register (QEIxIC) bits

REGISTER 15-19: QEIXICH: QEIX INITIALIZATION/CAPTURE REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEIIC<31:24>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEIIC<23:16>									
bit 7	bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 QEIIC<31:16>: High Word Used to Form 32-Bit Initialization/Capture Register (QEIxIC) bits

REGISTER 15-20: QEIXLECL: QEIX LESS THAN OR EQUAL COMPARE REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEILEC<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
QEILEC<7:0>								
bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 QEILEC<15:0>: Low Word Used to Form 32-Bit Less Than or Equal Compare Register (QEIxLEC) bits

REGISTER 15-21: QEIXLECH: QEIX LESS THAN OR EQUAL COMPARE REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
	QEILEC<31:24>									
bit 15				bit 8						

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEILEC<23:16>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **QEILEC<31:16>:** High Word Used to Form 32-Bit Less Than or Equal Compare Register (QEIxLEC) bits

REGISTER 15-22: QEIXGECL: QEIX GREATER THAN OR EQUAL COMPARE REGISTER LOW

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEIGEC<15:8>									
bit 15									

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
QEIGEC<7:0>								
bit 7			bit 0					

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 QEIGEC<15:0>: Low Word Used to Form 32-Bit Greater Than or Equal Compare Register (QEIxGEC) bits

REGISTER 15-23: QEIXGECH: QEIX GREATER THAN OR EQUAL COMPARE REGISTER HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEIGEC<31:24>									
bit 15						bit 8			

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
QEIGEC<23:16>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 QEIGEC<31:16>: High Word Used to Form 32-Bit Greater Than or Equal Compare Register (QEIxGEC) bits

16.0 UNIVERSAL ASYNCHRONOUS RECEIVER TRANSMITTER (UART)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Multiprotocol Universal Asynchronous Receiver Transmitter (UART) Module" (www.microchip.com/DS70005288) in the "dsPIC33/PIC24 Family Reference Manual".

The Universal Asynchronous Receiver Transmitter (UART) is a flexible serial communication peripheral used to interface dsPIC[®] microcontrollers with other equipment, including computers and peripherals. The UART is a full-duplex, asynchronous communication channel that can be used to implement protocols, such as RS-232 and RS-485. The UART also supports the following hardware extensions:

- LIN/J2602
- IrDA[®]
- · Direct Matrix Architecture (DMX)
- · Smart Card

The primary features of the UART are:


- · Full or Half-Duplex Operation
- Up to 8-Deep TX and RX First In, First Out (FIFO) Buffers
- · 8-Bit or 9-Bit Data Width
- · Configurable Stop Bit Length
- · Flow Control
- · Auto-Baud Calibration
- Parity, Framing and Buffer Overrun Error Detection
- · Address Detect
- · Break Transmission
- · Transmit and Receive Polarity Control
- · Manchester Encoder/Decoder
- · Operation in Sleep mode
- Wake from Sleep on Sync Break Received Interrupt

16.1 Architectural Overview

The UART transfers bytes of data, to and from device pins, using First-In First-Out (FIFO) buffers up to eight bytes deep. The status of the buffers and data is made available to user software through Special Function

Registers (SFRs). The UART implements multiple interrupt channels for handling transmit, receive and error events. A simplified block diagram of the UART is shown in Figure 16-1.


FIGURE 16-1: SIMPLIFIED UARTX BLOCK DIAGRAM



16.2 Character Frame

A typical UART character frame is shown in Figure 16-2. The Idle state is high with a 'Start' condition indicated by a falling edge. The Start bit is followed by the number of data, parity/address detect and Stop bits defined by the MOD<3:0> (UxMODE<3:0>) bits selected.

FIGURE 16-2: UART CHARACTER FRAME



16.3 Data Buffers

Both transmit and receive functions use buffers to store data shifted to/from the pins. These buffers are FIFOs and are accessed by reading the SFRs, UxTXREG and UxRXREG, respectively. Each data buffer has multiple flags associated with its operation to allow software to read the status. Interrupts can also be configured based on the space available in the buffers. The transmit and receive buffers can be cleared and their pointers reset using the associated TX/RX Buffer Empty Status bits, UTXBE (UxSTAH<5>) and URXBE (UxSTAH<1>).

16.4 Protocol Extensions

The UART provides hardware support for LIN/J2602, IrDA®, DMX and smart card protocol extensions to reduce software overhead. A protocol extension is enabled by writing a value to the MOD<3:0> (UxMODE<3:0>) selection bits and further configured using the UARTx Timing Parameter registers, UxP1 (Register 16-9), UxP2 (Register 16-10), UxP3 (Register 16-11) and UxP3H (Register 16-12). Details regarding operation and usage are discussed in their respective chapters. Not all protocols are available on all devices. Please refer to the specific device data sheet for availability.

16.5 UART Control Registers

REGISTER 16-1: UxMODE: UARTX CONFIGURATION REGISTER

R/W-0	U-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	HC/R/W-0 ⁽¹⁾
UARTEN	_	USIDL	WAKE	RXBIMD	_	BRKOVR	UTXBRK
bit 15	•	•					bit 8

R/W-0	HC/R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
BRGH	ABAUD	UTXEN	URXEN	MOD3	MOD2	MOD1	MOD0
bit 7							bit 0

Legend: HC = Hardware Clearable bit		HS = Hardware Settable bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15 **UARTEN:** UART Enable bit

1 = UART is ready to transmit and receive

0 = UART state machine, FIFO Buffer Pointers and counters are reset; registers are readable and writable

bit 14 **Unimplemented:** Read as '0'

bit 13 USIDL: UART Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 WAKE: Wake-up Enable bit

1 = Module will continue to sample the RX pin – interrupt generated on falling edge, bit cleared in hardware on following rising edge; if ABAUD is set, Auto-Baud Detection (ABD) will begin immediately

0 = RX pin is not monitored nor rising edge detected

bit 11 **RXBIMD:** Receive Break Interrupt Mode bit

1 = RXBKIF flag when a minimum of 23 (DMX)/11 (asynchronous or LIN/J2602) low bit periods are detected

0 = RXBKIF flag when the Break makes a low-to-high transition after being low for at least 23/11 bit periods

bit 10 Unimplemented: Read as '0'

bit 9 BRKOVR: Send Break Software Override bit

Overrides the TX Data Line:

1 = Makes the TX line active (Output 0 when UTXINV = 0, Output 1 when UTXINV = 1)

0 = TX line is driven by the shifter

bit 8 **UTXBRK:** UART Transmit Break bit⁽¹⁾

1 = Sends Sync Break on next transmission; cleared by hardware upon completion

0 = Sync Break transmission is disabled or has completed

bit 7 BRGH: High Baud Rate Select bit

1 = High Speed: Baud rate is baudclk/4

0 = Low Speed: Baud rate is baudclk/16

bit 6 **ABAUD:** Auto-Baud Detect Enable bit (read-only when MOD<3:0> = 1xxx)

1 = Enables baud rate measurement on the next character – requires reception of a Sync field (55h); cleared in hardware upon completion

0 = Baud rate measurement is disabled or has completed

Note 1: R/HS/HC in DMX and LIN mode.

REGISTER 16-1: UxMODE: UARTX CONFIGURATION REGISTER (CONTINUED)

bit 5 UTXEN: UART Transmit Enable bit

- 1 = Transmit enabled except during Auto-Baud Detection
- 0 = Transmit disabled all transmit counters, pointers and state machines are reset; TX buffer is not flushed, status bits are not reset

bit 4 URXEN: UART Receive Enable bit

- 1 = Receive enabled except during Auto-Baud Detection
- 0 = Receive disabled all receive counters, pointers and state machines are reset; RX buffer is not flushed, status bits are not reset
- bit 3-0 MOD<3:0>: UART Mode bits

Other = Reserved

1111 = Smart card

 $1110 = IrDA^{\otimes}$

1101 = Reserved

1100 = LIN Master/Slave

1011 = LIN Slave only

1010 = DMX

1001 = Reserved

1000 = Reserved

0111 = Reserved

0110 = Reserved

0101 = Reserved

0100 = Asynchronous 9-bit UART with address detect, ninth bit = 1 signals address

0011 = Asynchronous 8-bit UART without address detect, ninth bit is used as an even parity bit

0010 = Asynchronous 8-bit UART without address detect, ninth bit is used as an odd parity bit

0001 = Asynchronous 7-bit UART

0000 = Asynchronous 8-bit UART

Note 1: R/HS/HC in DMX and LIN mode.

REGISTER 16-2: UxMODEH: UARTX CONFIGURATION REGISTER HIGH

R/W-0	R-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
SLPEN	ACTIVE	_	_	BCLKMOD	BCLKSEL1	BCLKSEL0	HALFDPLX
bit 15 bit 8							

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
RUNOVF	URXINV	STSEL1	STSEL0	C0EN	UTXINV	FLO1	FLO0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 SLPEN: Run During Sleep Enable bit

1 = UART BRG clock runs during Sleep

0 = UART BRG clock is turned off during Sleep

bit 14 ACTIVE: UART Running Status bit

1 = UART clock request is active (user can not update the UxMODE/UxMODEH registers)

0 = UART clock request is not active (user can update the UxMODE/UxMODEH registers)

bit 13-12 **Unimplemented:** Read as '0'

bit 11 BCLKMOD: Baud Clock Generation Mode Select bit

1 = Uses fractional Baud Rate Generation

0 = Uses legacy divide-by-x counter for baud clock generation (x = 4 or 16 depending on the BRGH bit)

bit 10-9 BCLKSEL<1:0>: Baud Clock Source Selection bits

11 = AFvco/3

10 = Fosc

01 = Reserved

00 = Fosc/2 (FP)

bit 8 HALFDPLX: UART Half-Duplex Selection Mode bit

1 = Half-Duplex mode: UxTX is driven as an output when transmitting and tri-stated when TX is Idle

0 = Full-Duplex mode: UxTX is driven as an output at all times when both UARTEN and UTXEN are set

bit 7 RUNOVF: Run During Overflow Condition Mode bit

1 = When an Overflow Error (OERR) condition is detected, the RX shifter continues to run so as to remain synchronized with incoming RX data; data is not transferred to UxRXREG when it is full (i.e., no UxRXREG data is overwritten)

0 = When an Overflow Error (OERR) condition is detected, the RX shifter stops accepting new data

(Legacy mode)

bit 6 **URXINV:** UART Receive Polarity bit

1 = Inverts RX polarity; Idle state is low

0 = Input is not inverted; Idle state is high

bit 5-4 STSEL<1:0>: Number of Stop Bits Selection bits

11 = 2 Stop bits sent, 1 checked at receive

10 = 2 Stop bits sent, 2 checked at receive

01 = 1.5 Stop bits sent, 1.5 checked at receive

00 = 1 Stop bit sent, 1 checked at receive

bit 3 **C0EN:** Enable Legacy Checksum (C0) Transmit and Receive bit

1 = Checksum Mode 1 (enhanced LIN checksum in LIN mode; add all TX/RX words in all other modes)

0 = Checksum Mode 0 (legacy LIN checksum in LIN mode; not used in all other modes)

REGISTER 16-2: UxMODEH: UARTX CONFIGURATION REGISTER HIGH (CONTINUED)

bit 2 UTXINV: UART Transmit Polarity bit

1 = Inverts TX polarity; TX is low in Idle state

0 = Output data is not inverted; TX output is high in Idle state

bit 1-0 **FLO<1:0>:** Flow Control Enable bits (only valid when MOD<3:0> = 0xxx)

11 = Reserved

10 = $\overline{\text{RTS-DSR}}$ (for TX side)/ $\overline{\text{CTS-DTR}}$ (for RX side) hardware flow control

01 = XON/XOFF software flow control

00 = Flow control off

REGISTER 16-3: UXSTA: UARTX STATUS REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TXMTIE	PERIE	ABDOVE	CERIE	FERIE	RXBKIE	OERIE	TXCIE
bit 15							bit 8

R-1	R-0	HS/R/W-0	HS/R/W-0	R-0	HS/R/W-0	HS/R/W-0	HS/R/W-0
TRMT	PERR	ABDOVF	CERIF	FERR	RXBKIF	OERR	TXCIF
bit 7							bit 0

Legend: HS = Hardware Settable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **TXMTIE:** Transmit Shifter Empty Interrupt Enable bit

1 = Interrupt is enabled

0 = Interrupt is disabled

bit 14 **PERIE:** Parity Error Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 13 ABDOVE: Auto-Baud Rate Acquisition Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 12 CERIE: Checksum Error Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 11 FERIE: Framing Error Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 10 RXBKIE: Receive Break Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 9 **OERIE:** Receive Buffer Overflow Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 8 TXCIE: Transmit Collision Interrupt Enable bit

1 = Interrupt is enabled0 = Interrupt is disabled

bit 7 TRMT: Transmit Shifter Empty Interrupt Flag bit (read-only)

1 = Transmit Shift Register (TSR) is empty (end of last Stop bit when STPMD = 1 or middle of first Stop bit when STPMD = 0)

0 = Transmit Shift Register is not empty

bit 6 PERR: Parity Error/Address Received/Forward Frame Interrupt Flag bit

LIN and Parity Modes:

1 = Parity error detected

0 = No parity error detected

Address Mode:

1 = Address received

0 = No address detected

All Other Modes:

Not used.

REGISTER 16-3: UxSTA: UARTX STATUS REGISTER (CONTINUED)

bit 5	ABDOVF: Auto-Baud Rate Acquisition Interrupt Flag bit (must be cleared by software) 1 = BRG rolled over during the auto-baud rate acquisition sequence (must be cleared in software) 0 = BRG has not rolled over during the auto-baud rate acquisition sequence
bit 4	CERIF: Checksum Error Interrupt Flag bit (must be cleared by software)
	1 = Checksum error 0 = No checksum error
bit 3	FERR: Framing Error Interrupt Flag bit
	 1 = Framing Error: Inverted level of the Stop bit corresponding to the topmost character in the buffer propagates through the buffer with the received character 0 = No framing error
bit 2	RXBKIF: Receive Break Interrupt Flag bit (must be cleared by software)
	1 = A Break was received0 = No Break was detected
bit 1	OERR: Receive Buffer Overflow Interrupt Flag bit (must be cleared by software)
	1 = Receive buffer has overflowed0 = Receive buffer has not overflowed
bit 0	TXCIF: Transmit Collision Interrupt Flag bit (must be cleared by software) 1 = Transmitted word is not equal to the received word 0 = Transmitted word is equal to the received word

REGISTER 16-4: UxSTAH: UARTX STATUS REGISTER HIGH

U-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	
_	UTXISEL2	UTXISEL1	UTXISEL0	_	URXISEL2 ⁽¹⁾	URXISEL1(1)	URXISEL0 ⁽¹⁾	
bit 15								

HS/R/W-0	R/W-0	R/S-1	R-0	R-1	R-1	R/S-1	R-0
TXWRE	STPMD	UTXBE	UTXBF	RIDLE	XON	URXBE	URXBF
bit 7							bit 0

Legend: HS = Hardware Settable bit S = Settable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-12 UTXISEL<2:0>: UART Transmit Interrupt Select bits

111 = Sets transmit interrupt when there is one empty slot left in the buffer

. . .

010 = Sets transmit interrupt when there are six empty slots or more in the buffer

001 = Sets transmit interrupt when there are seven empty slots or more in the buffer

000 = Sets transmit interrupt when there are eight empty slots in the buffer; TX buffer is empty

bit 11 **Unimplemented:** Read as '0'

bit 10-8 URXISEL<2:0>: UART Receive Interrupt Select bits⁽¹⁾

111 = Triggers receive interrupt when there are eight words in the buffer; RX buffer is full

. . .

001 = Triggers receive interrupt when there are two words or more in the buffer

000 = Triggers receive interrupt when there is one word or more in the buffer

bit 7 TXWRE: TX Write Transmit Error Status bit

LIN and Parity Modes:

1 = A new byte was written when the buffer was full or when P2<8:0> = 0 (must be cleared by software)

0 = No error

Address Detect Mode:

1 = A new byte was written when the buffer was full or to P1<8:0> when P1x was full (must be cleared by software)

0 = No error

Other Modes:

1 = A new byte was written when the buffer was full (must be cleared by software)

0 = No error

bit 6 **STPMD:** Stop Bit Detection Mode bit

1 = Triggers RXIF at the end of the last Stop bit

0 = Triggers RXIF in the middle of the first (or second, depending on the STSEL<1:0> setting) Stop bit

bit 5 UTXBE: UART TX Buffer Empty Status bit

1 = Transmit buffer is empty; writing '1' when UTXEN = 0 will reset the TX FIFO Pointers and counters

0 = Transmit buffer is not empty

bit 4 UTXBF: UART TX Buffer Full Status bit

1 = Transmit buffer is full

0 = Transmit buffer is not full

bit 3 RIDLE: Receive Idle bit

1 = UART RX line is in the Idle state

0 = UART RX line is receiving something

Note 1: The receive watermark interrupt is not set if PERR or FERR is set and the corresponding IE bit is set.

REGISTER 16-4: UxSTAH: UARTx STATUS REGISTER HIGH (CONTINUED)

bit 2 XON: UART in XON Mode bit

Only valid when FLO<1:0> control bits are set to XON/XOFF mode.

1 = UART has received XON

0 = UART has not received XON or XOFF was received

bit 1 URXBE: UART RX Buffer Empty Status bit

1 = Receive buffer is empty; writing '1' when URXEN = 0 will reset the RX FIFO Pointers and counters

0 = Receive buffer is not empty

bit 0 URXBF: UART RX Buffer Full Status bit

1 = Receive buffer is full 0 = Receive buffer is not full

Note 1: The receive watermark interrupt is not set if PERR or FERR is set and the corresponding IE bit is set.

REGISTER 16-5: UxBRG: UARTX BAUD RATE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
BRG<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
BRG<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 BRG<15:0>: Baud Rate Divisor bits

REGISTER 16-6: UxBRGH: UARTX BAUD RATE REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_		_
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	
_	_	_	_	BRG<19:16>				
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-4 Unimplemented: Read as '0'

bit 3-0 BRG<19:16>: Baud Rate Divisor bits

REGISTER 16-7: UXRXREG: UARTX RECEIVE BUFFER REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_		_
bit 15							bit 8

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x		
RXREG<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 **RXREG<7:0>:** Received Character Data bits 7-0

REGISTER 16-8: UXTXREG: UARTX TRANSMIT BUFFER REGISTER

W-x	U-0						
LAST	_	_	_	_	_	_	_
bit 15							bit 8

| W-x |
|--------|--------|--------|--------|--------|--------|--------|--------|
| TXREG7 | TXREG6 | TXREG5 | TXREG4 | TXREG3 | TXREG2 | TXREG1 | TXREG0 |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 Last Byte Indicator for Smart Card Support bit

bit 14-8 **Unimplemented:** Read as '0'

bit 7-0 **TXREG<7:0>:** Transmitted Character Data bits 7-0

If the buffer is full, further writes to the buffer are ignored.

REGISTER 16-9: UxP1: UARTX TIMING PARAMETER 1 REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	P1<8>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
P1<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-9 **Unimplemented:** Read as '0'

bit 8-0 **P1<8:0>:** Parameter 1 bits

DMX TX:

Number of Bytes to Transmit – 1 (not including Start code).

LIN Master TX:

PID to transmit (bits<5:0>).

Asynchronous TX with Address Detect:

Address to transmit. A '1' is automatically inserted into bit 9 (bits<7:0>).

Smart Card Mode:

Guard Time Counter bits. This counter is operated on the bit clock whose period is always equal to one ETU (bits<8:0>).

Other Modes:

Not used.

REGISTER 16-10: UxP2: UARTx TIMING PARAMETER 2 REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	P2<8>
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
P2<7:0>									
bit 7				bit 0					

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-9 **Unimplemented:** Read as '0' bit 8-0 **P2<8:0>:** Parameter 2 bits

DMX RX:

The first byte number to receive – 1, not including Start code (bits<8:0>).

LIN Slave TX:

Number of bytes to transmit (bits<7:0>). Asynchronous RX with Address Detect: Address to start matching (bits<7:0>).

Smart Card Mode:

Block Time Counter bits. This counter is operated on the bit clock whose period is always equal to one ETU (bits<8:0>).

Other Modes: Not used.

REGISTER 16-11: UxP3: UARTx TIMING PARAMETER 3 REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			P3<1	5:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
P3<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **P3<15:0>:** Parameter 3 bits

DMX RX:

The last byte number to receive – 1, not including Start code (bits<8:0>).

LIN Slave RX:

Number of bytes to receive (bits<7:0>).

Asynchronous RX:

Used to mask the UxP2 address bits; 1 = P2 address bit is used, 0 = P2 address bit is masked off (bits<7:0>).

Smart Card Mode:

Waiting Time Counter bits (bits<15:0>).

Other Modes:

Not used.

REGISTER 16-12: UxP3H: UARTX TIMING PARAMETER 3 REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
	P3<23:16>									
bit 7										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 **P3<23:16>:** Parameter 3 High bits

Smart Card Mode:

Waiting Time Counter bits (bits<23:16>).

Other Modes: Not used.

REGISTER 16-13: UXTXCHK: UARTX TRANSMIT CHECKSUM REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
TXCHK<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 **TXCHK<7:0>:** Transmit Checksum bits (calculated from TX words)

LIN Modes:

C0EN = 1: Sum of all transmitted data + addition carries, including PID. C0EN = 0: Sum of all transmitted data + addition carries, excluding PID.

LIN Slave:

Cleared when Break is detected.

LIN Master/Slave:

Cleared when Break is detected.

Other Modes:

C0EN = 1: Sum of every byte transmitted + addition carries.

C0EN = 0: Value remains unchanged.

REGISTER 16-14: UXRXCHK: UARTX RECEIVE CHECKSUM REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
RXCHK<7:0>								
bit 7								

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7-0 **RXCHK<7:0>:** Receive Checksum bits (calculated from RX words)

<u>LIN Modes:</u>

C0EN = 1: Sum of all received data + addition carries, including PID. C0EN = 0: Sum of all received data + addition carries, excluding PID.

LIN Slave:

Cleared when Break is detected.

LIN Master/Slave:

Cleared when Break is detected.

Other Modes:

C0EN = 1: Sum of every byte received + addition carries.

C0EN = 0: Value remains unchanged.

REGISTER 16-15: UXSCCON: UARTX SMART CARD CONFIGURATION REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0
_	_	TXRPT1	TXRPT0	CONV	T0PD	PRTCL	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-6 **Unimplemented:** Read as '0'

bit 5-4 TXRPT<1:0>: Transmit Repeat Selection bits

11 = Retransmit the error byte four times10 = Retransmit the error byte three times

01 = Retransmit the error byte twice 00 = Retransmit the error byte once

bit 3 CONV: Logic Convention Selection bit

1 = Inverse logic convention0 = Direct logic convention

bit 2 **TOPD:** Pull-Down Duration for T = 0 Error Handling bit

1 = Two ETU 0 = One ETU

bit 1 PRTCL: Smart Card Protocol Selection bit

1 = T = 10 = T = 0

bit 0 **Unimplemented:** Read as '0'

REGISTER 16-16: UxSCINT: UARTX SMART CARD INTERRUPT REGISTER

U-0	U-0	HS/R/W-0	HS/R/W-0	U-0	HS/R/W-0	HS/R/W-0	HS/R/W-0
_	_	RXRPTIF	TXRPTIF	_	BTCIF	WTCIF	GTCIF
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
_	_	RXRPTIE	TXRPTIE	_	BTCIE	WTCIE	GTCIE
bit 7							bit 0

Legend: HS = Hardware Settable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13 RXRPTIF: Receive Repeat Interrupt Flag bit

1 = Parity error has persisted after the same character has been received five times (four retransmits)

0 = Flag is cleared

bit 12 **TXRPTIF:** Transmit Repeat Interrupt Flag bit

1 = Line error has been detected after the last retransmit per TXRPT<1:0>

0 = Flag is cleared

bit 11 **Unimplemented:** Read as '0'

bit 10 BTCIF: Block Time Counter Interrupt Flag bit

1 = Block Time Counter has reached 0

0 = Block Time Counter has not reached 0

bit 9 WTCIF: Waiting Time Counter Interrupt Flag bit

1 = Waiting Time Counter has reached 0

0 = Waiting Time Counter has not reached 0

bit 8 GTCIF: Guard Time Counter Interrupt Flag bit

1 = Guard Time Counter has reached 0

0 = Guard Time Counter has not reached 0

bit 7-6 **Unimplemented:** Read as '0'

bit 5 RXRPTIE: Receive Repeat Interrupt Enable bit

1 = An interrupt is invoked when a parity error has persisted after the same character has been

received five times (four retransmits)

0 = Interrupt is disabled

bit 4 **TXRPTIE:** Transmit Repeat Interrupt Enable bit

1 = An interrupt is invoked when a line error is detected after the last retransmit per TXRPT<1:0> has

been completed

0 = Interrupt is disabled

bit 3 **Unimplemented:** Read as '0'

bit 2 BTCIE: Block Time Counter Interrupt Enable bit

1 = Block Time Counter interrupt is enabled

0 = Block Time Counter interrupt is disabled

bit 1 WTCIE: Waiting Time Counter Interrupt Enable bit

1 = Waiting Time Counter interrupt is enabled

0 = Waiting Time Counter Interrupt is disabled

bit 0 GTCIE: Guard Time Counter interrupt enable bit

1 = Guard Time Counter interrupt is enabled

0 = Guard Time Counter interrupt is disabled

REGISTER 16-17: UXINT: UARTX INTERRUPT REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15	_		_		_		bit 8

HS/R/W-0	HS/R/W-0	U-0	U-0	U-0	R/W-0	U-0	U-0
WUIF	ABDIF	_	_	_	ABDIE	_	_
bit 7							bit 0

 Legend:
 HS = Hardware Settable bit

 R = Readable bit
 W = Writable bit
 U = Unimplemented bit, read as '0'

 -n = Value at POR
 '1' = Bit is set
 '0' = Bit is cleared
 x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0' bit 7 **WUIF:** Wake-up Interrupt Flag bit

1 = Sets when WAKE = 1 and RX makes a '1'-to-'0' transition; triggers event interrupt (must be cleared by software)

0 = WAKE is not enabled or WAKE is enabled, but no wake-up event has occurred

bit 6 ABDIF: Auto-Baud Completed Interrupt Flag bit

1 = Sets when ABD sequence makes the final '1'-to-'0' transition; triggers event interrupt (must be

cleared by software)

0 = ABAUD is not enabled or ABAUD is enabled but auto-baud has not completed

bit 5-3 **Unimplemented:** Read as '0'

bit 2 ABDIE: Auto-Baud Completed Interrupt Enable Flag bit

1 = Allows ABDIF to set an event interrupt0 = ABDIF does not set an event interrupt

bit 1-0 **Unimplemented:** Read as '0'

NOTES			
NOTES:			

17.0 SERIAL PERIPHERAL INTERFACE (SPI)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Serial Peripheral Interface (SPI) with Audio Codec Support" (www.microchip.com/DS70005136) in the "dsPIC33/PIC24 Family Reference Manual".

The Serial Peripheral Interface (SPI) module is a synchronous serial interface, useful for communicating with other peripheral or microcontroller devices. These peripheral devices may be serial EEPROMs, shift registers, display drivers, A/D Converters, etc. The SPI module is compatible with the Motorola[®] SPI and SIOP interfaces. All devices in the dsPIC33CK256MP508 family include three SPI modules. On 48, 64 and 80-pin devices, SPI instance SPI2 can work up to 50 MHz speed when selected as a non-PPS pin. The selection is done using the SPI2PIN bit (FDEVOPT<13>). If the bit for SPI2PIN is '1', the PPS pin will be used. When SPI2PIN is '0', the SPI signals are routed to dedicated pins.

The module supports operation in two Buffer modes. In Standard mode, data is shifted through a single serial buffer. In Enhanced Buffer mode, data is shifted through a FIFO buffer. The FIFO level depends on the configured mode.

Note: FIFO depth for this device is four (in 8-Bit Data mode).

Variable length data can be transmitted and received, from 2 to 32 bits.

Note: Do not perform Read-Modify-Write operations (such as bit-oriented instructions) on the SPIxBUF register in either Standard or Enhanced Buffer mode.

The module also supports a basic framed SPI protocol while operating in either Master or Slave mode. A total of four framed SPI configurations are supported.

The module also supports Audio modes. Four different Audio modes are available.

- I²S mode
- · Left Justified mode
- · Right Justified mode
- · PCM/DSP mode

In each of these modes, the serial clock is free-running and audio data is always transferred.

If an audio protocol data transfer takes place between two devices, then usually one device is the Master and the other is the Slave. However, audio data can be transferred between two Slaves. Because the audio protocols require free-running clocks, the Master can be a third-party controller. In either case, the Master generates two free-running clocks: SCKx and LRC (Left, Right Channel Clock/SSx/FSYNC).

The SPI serial interface consists of four pins:

- · SDIx: Serial Data Input
- · SDOx: Serial Data Output
- · SCKx: Shift Clock Input or Output
- SSx: Active-Low Slave Select or Frame Synchronization I/O Pulse

The SPI module can be configured to operate using two, three or four pins. In the 3-pin mode, \overline{SSx} is not used. In the 2-pin mode, both SDOx and \overline{SSx} are not used.

The SPI module has the ability to generate three interrupts reflecting the events that occur during the data communication. The following types of interrupts can be generated:

- Receive interrupts are signalled by SPIxRXIF. This event occurs when:
 - RX watermark interrupt
 - SPIROV = 1
 - SPIRBF = 1
 - SPIRBE = 1

provided the respective mask bits are enabled in SPIxIMSKL/H.

- Transmit interrupts are signalled by SPIxTXIF. This event occurs when:
 - TX watermark interrupt
 - SPITUR = 1
 - SPITBF = 1
 - SPITBE = 1

provided the respective mask bits are enabled in SPIxIMSKL/H.

- General interrupts are signalled by SPIxGIF. This event occurs when:
 - FRMERR = 1
 - SPIBUSY = 1
 - SRMT = 1

provided the respective mask bits are enabled in SPIxIMSKL/H.

Block diagrams of the module in Standard and Enhanced modes are shown in Figure 17-1 and Figure 17-2.

referred to together as SPIx, or separately as SPI1, SPI2 or SPI3. Special Function Registers will follow a similar notation. For example, SPIxCON1 and SPIxCON2 refer to the control registers for any of the three SPI modules.

To set up the SPIx module for the Standard Master mode of operation:

- 1. If using interrupts:
 - Clear the interrupt flag bits in the respective IFSx register.
 - b) Set the interrupt enable bits in the respective IECx register.
 - c) Write the SPIxIP bits in the respective IPCx register to set the interrupt priority.
- Write the desired settings to the SPIxCON1L and SPIxCON1H registers with the MSTEN bit (SPIxCON1L<5>) = 1.
- 3. Clear the SPIROV bit (SPIxSTATL<6>).
- 4. Enable SPIx operation by setting the SPIEN bit (SPIxCON1L<15>).
- Write the data to be transmitted to the SPIxBUFL and SPIxBUFH registers. Transmission (and reception) will start as soon as data is written to the SPIxBUFL and SPIxBUFH registers.

To set up the SPIx module for the Standard Slave mode of operation:

- 1. Clear the SPIxBUF registers.
- 2. If using interrupts:
 - a) Clear the SPIxBUFL and SPIxBUFH registers.
 - b) Set the interrupt enable bits in the respective IECx register.
 - Write the SPIxIP bits in the respective IPCx register to set the interrupt priority.
- 3. Write the desired settings to the SPIxCON1L, SPIxCON1H and SPIxCON2L registers with the MSTEN bit (SPIxCON1L<5>) = 0.
- 4. Clear the SMP bit.
- 5. If the CKE bit (SPIxCON1L<8>) is set, then the SSEN bit (SPIxCON1L<7>) must be set to enable the SSx pin.
- 6. Clear the SPIROV bit (SPIxSTATL<6>).
- 7. Enable SPIx operation by setting the SPIEN bit (SPIxCON1L<15>).




FIGURE 17-1: SPIX MODULE BLOCK DIAGRAM (STANDARD MODE)


To set up the SPIx module for the Enhanced Buffer Master mode of operation:

- 1. If using interrupts:
 - a) Clear the interrupt flag bits in the respective IFSx register.
 - b) Set the interrupt enable bits in the respective IECx register.
 - Write the SPIxIP bits in the respective IPCx register.
- Write the desired settings to the SPIxCON1L, SPIxCON1H and SPIxCON2L registers with MSTEN (SPIxCON1L<5>) = 1.
- 3. Clear the SPIROV bit (SPIxSTATL<6>).
- 4. Select Enhanced Buffer mode by setting the ENHBUF bit (SPIxCON1L<0>).
- Enable SPIx operation by setting the SPIEN bit (SPIxCON1L<15>).
- Write the data to be transmitted to the SPIxBUFL and SPIxBUFH registers. Transmission (and reception) will start as soon as data is written to the SPIxBUFL and SPIxBUFH registers.

To set up the SPIx module for the Enhanced Buffer Slave mode of operation:

- 1. Clear the SPIxBUFL and SPIxBUFH registers.
- 2. If using interrupts:
 - Clear the interrupt flag bits in the respective IFSx register.
 - b) Set the interrupt enable bits in the respective IECx register.
 - Write the SPIxIP bits in the respective IPCx register to set the interrupt priority.
- Write the desired settings to the SPIxCON1L, SPIxCON1H and SPIxCON2L registers with the MSTEN bit (SPIxCON1L<5>) = 0.
- 4. Clear the SMP bit.
- 5. If the CKE bit is set, then the SSEN bit must be set, thus enabling the SSx pin.
- 6. Clear the SPIROV bit (SPIxSTATL<6>).
- 7. Select Enhanced Buffer mode by setting the ENHBUF bit (SPIxCON1L<0>).
- 8. Enable SPIx operation by setting the SPIEN bit (SPIxCON1L<15>).

FIGURE 17-2: SPIX MODULE BLOCK DIAGRAM (ENHANCED MODE)



To set up the SPIx module for Audio mode:

- 1. Clear the SPIxBUFL and SPIxBUFH registers.
- 2. If using interrupts:
 - a) Clear the interrupt flag bits in the respective IFSx register.
 - b) Set the interrupt enable bits in the respective IECx register.
 - a) Write the SPIxIP bits in the respective IPCx register to set the interrupt priority.
- 3. Write the desired settings to the SPIxCON1L, SPIxCON1H and SPIxCON2L registers with AUDEN (SPIxCON1H<15>) = 1.
- 4. Clear the SPIROV bit (SPIxSTATL<6>).
- 5. Enable SPIx operation by setting the SPIEN bit (SPIxCON1L<15>).
- 6. Write the data to be transmitted to the SPIxBUFL and SPIxBUFH registers. Transmission (and reception) will start as soon as data is written to the SPIxBUFL and SPIxBUFH registers.

17.1 Control Registers

REGISTER 17-1: SPIXCON1L: SPIX CONTROL REGISTER 1 LOW

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SPIEN	_	SPISIDL	DISSDO	MODE32 ^(1,4)	MODE16 ^(1,4)	SMP	CKE ⁽¹⁾
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
SSEN ⁽²⁾	CKP	MSTEN	DISSDI	DISSCK	MCLKEN ⁽³⁾	SPIFE	ENHBUF
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 SPIEN: SPIx On bit

1 = Enables module

0 = Turns off and resets module, disables clocks, disables interrupt event generation, allows SFR modifications

bit 14 Unimplemented: Read as '0'

bit 13 SPISIDL: SPIx Stop in Idle Mode bit

1 = Halts in CPU Idle mode

0 = Continues to operate in CPU Idle mode

bit 12 DISSDO: Disable SDOx Output Port bit

1 = SDOx pin is not used by the module; pin is controlled by port function

0 = SDOx pin is controlled by the module

bit 11-10 MODE32 and MODE16: Serial Word Length Select bits^(1,4)

MODE32	MODE16	AUDEN	Communication
1	X		32-Bit
0	1	0	16-Bit
0	0		8-Bit
1	1		24-Bit Data, 32-Bit FIFO, 32-Bit Channel/64-Bit Frame
1	0	1	32-Bit Data, 32-Bit FIFO, 32-Bit Channel/64-Bit Frame
0	1	1	16-Bit Data, 16-Bit FIFO, 32-Bit Channel/64-Bit Frame
0	0		16-Bit FIFO, 16-Bit Channel/32-Bit Frame

bit 9 SMP: SPIx Data Input Sample Phase bit

Master Mode:

- 1 = Input data is sampled at the end of data output time
- 0 = Input data is sampled at the middle of data output time

Slave Mode:

Input data is always sampled at the middle of data output time, regardless of the SMP setting.

bit 8 **CKE:** SPIx Clock Edge Select bit⁽¹⁾

- 1 = Transmit happens on transition from active clock state to Idle clock state
- 0 = Transmit happens on transition from Idle clock state to active clock state
- Note 1: When AUDEN (SPIxCON1H<15>) = 1, this module functions as if CKE = 0, regardless of its actual value.
 - 2: When FRMEN = 1, SSEN is not used.
 - 3: MCLKEN can only be written when the SPIEN bit = 0.
 - 4: This channel is not meaningful for DSP/PCM mode as LRC follows FRMSYPW.

REGISTER 17-1: SPIxCON1L: SPIx CONTROL REGISTER 1 LOW (CONTINUED)

SSEN: Slave Select Enable bit (Slave mode)⁽²⁾ bit 7 $1 = \overline{SSx}$ pin is used by the macro in Slave mode; \overline{SSx} pin is used as the Slave select input $0 = \overline{SSx}$ pin is not used by the macro (\overline{SSx} pin will be controlled by the port I/O) bit 6 CKP: Clock Polarity Select bit 1 = Idle state for clock is a high level; active state is a low level 0 = Idle state for clock is a low level; active state is a high level bit 5 MSTEN: Master Mode Enable bit 1 = Master mode 0 = Slave mode bit 4 **DISSDI:** Disable SDIx Input Port bit 1 = SDIx pin is not used by the module; pin is controlled by port function 0 = SDIx pin is controlled by the module bit 3 **DISSCK:** Disable SCKx Output Port bit 1 = SCKx pin is not used by the module; pin is controlled by port function 0 = SCKx pin is controlled by the module MCLKEN: Master Clock Enable bit(3) bit 2 1 = REFO is used by the BRG 0 = FP is used by the BRG bit 1 SPIFE: Frame Sync Pulse Edge Select bit 1 = Frame Sync pulse (Idle-to-active edge) coincides with the first bit clock 0 = Frame Sync pulse (Idle-to-active edge) precedes the first bit clock bit 0 **ENHBUF:** Enhanced Buffer Enable bit 1 = Enhanced Buffer mode is enabled 0 = Enhanced Buffer mode is disabled

- Note 1: When AUDEN (SPIxCON1H<15>) = 1, this module functions as if CKE = 0, regardless of its actual value.
 - 2: When FRMEN = 1, SSEN is not used.
 - 3: MCLKEN can only be written when the SPIEN bit = 0.
 - 4: This channel is not meaningful for DSP/PCM mode as LRC follows FRMSYPW.

REGISTER 17-2: SPIXCON1H: SPIX CONTROL REGISTER 1 HIGH

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
AUDEN ⁽¹⁾	SPISGNEXT	IGNROV	IGNTUR	AUDMONO ⁽²⁾	URDTEN ⁽³⁾	AUDMOD1 ⁽⁴⁾	AUDMOD0 ⁽⁴⁾
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
FRMEN	FRMSYNC	FRMPOL	MSSEN	FRMSYPW	FRMCNT2	FRMCNT1	FRMCNT0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 AUDEN: Audio Codec Support Enable bit⁽¹⁾

- 1 = Audio protocol is enabled; MSTEN controls the direction of both SCKx and frame (a.k.a. LRC), and this module functions as if FRMEN = 1, FRMSYNC = MSTEN, FRMCNT<2:0> = 001 and SMP = 0, regardless of their actual values
- 0 = Audio protocol is disabled
- bit 14 SPISGNEXT: SPIx Sign-Extend RX FIFO Read Data Enable bit
 - 1 = Data from RX FIFO is sign-extended
 - 0 = Data from RX FIFO is not sign-extended
- bit 13 IGNROV: Ignore Receive Overflow bit
 - 1 = A Receive Overflow (ROV) is NOT a critical error; during ROV, data in the FIFO is not overwritten by the receive data
 - 0 = A ROV is a critical error that stops SPI operation
- bit 12 IGNTUR: Ignore Transmit Underrun bit
 - 1 = A Transmit Underrun (TUR) is NOT a critical error and data indicated by URDTEN is transmitted until the SPIxTXB is not empty
 - 0 = A TUR is a critical error that stops SPI operation
- bit 11 AUDMONO: Audio Data Format Transmit bit⁽²⁾
 - 1 = Audio data is mono (i.e., each data word is transmitted on both left and right channels)
 - 0 = Audio data is stereo
- bit 10 **URDTEN:** Transmit Underrun Data Enable bit⁽³⁾
 - 1 = Transmits data out of SPIxURDT register during Transmit Underrun conditions
 - 0 = Transmits the last received data during Transmit Underrun conditions
- bit 9-8 AUDMOD<1:0>: Audio Protocol Mode Selection bits⁽⁴⁾
 - 11 = PCM/DSP mode
 - 10 = Right Justified mode: This module functions as if SPIFE = 1, regardless of its actual value
 - 01 = Left Justified mode: This module functions as if SPIFE = 1, regardless of its actual value
 - 00 = I²S mode: This module functions as if SPIFE = 0, regardless of its actual value
- bit 7 FRMEN: Framed SPIx Support bit
 - 1 = Framed SPIx support is enabled (\overline{SSx} pin is used as the FSYNC input/output)
 - 0 = Framed SPIx support is disabled
- **Note 1:** AUDEN can only be written when the SPIEN bit = 0.
 - 2: AUDMONO can only be written when the SPIEN bit = 0 and is only valid for AUDEN = 1.
 - 3: URDTEN is only valid when IGNTUR = 1.
 - **4:** AUDMOD<1:0> can only be written when the SPIEN bit = 0 and is only valid when AUDEN = 1. When NOT in PCM/DSP mode, this module functions as if FRMSYPW = 1, regardless of its actual value.

REGISTER 17-2: SPIxCON1H: SPIx CONTROL REGISTER 1 HIGH (CONTINUED)

- bit 6 FRMSYNC: Frame Sync Pulse Direction Control bit
 - 1 = Frame Sync pulse input (Slave)
 - 0 = Frame Sync pulse output (Master)
- bit 5 FRMPOL: Frame Sync/Slave Select Polarity bit
 - 1 = Frame Sync pulse/Slave select is active-high
 - 0 = Frame Sync pulse/Slave select is active-low
- bit 4 MSSEN: Master Mode Slave Select Enable bit
 - 1 = SPIx Slave select support is enabled with polarity determined by FRMPOL (SSx pin is automatically driven during transmission in Master mode)
 - 0 = Slave select SPIx support is disabled (SSx pin will be controlled by port I/O)
- bit 3 FRMSYPW: Frame Sync Pulse-Width bit
 - 1 = Frame Sync pulse is one serial word length wide (as defined by MODE<32,16>/WLENGTH<4:0>)
 - 0 = Frame Sync pulse is one clock (SCKx) wide
- bit 2-0 FRMCNT<2:0>: Frame Sync Pulse Counter bits

Controls the number of serial words transmitted per Sync pulse.

- 111 = Reserved
- 110 = Reserved
- 101 = Generates a Frame Sync pulse on every 32 serial words
- 100 = Generates a Frame Sync pulse on every 16 serial words
- 011 = Generates a Frame Sync pulse on every 8 serial words
- 010 = Generates a Frame Sync pulse on every 4 serial words
- 001 = Generates a Frame Sync pulse on every 2 serial words (value used by audio protocols)
- 000 = Generates a Frame Sync pulse on each serial word
- **Note 1:** AUDEN can only be written when the SPIEN bit = 0.
 - 2: AUDMONO can only be written when the SPIEN bit = 0 and is only valid for AUDEN = 1.
 - **3:** URDTEN is only valid when IGNTUR = 1.
 - **4:** AUDMOD<1:0> can only be written when the SPIEN bit = 0 and is only valid when AUDEN = 1. When NOT in PCM/DSP mode, this module functions as if FRMSYPW = 1, regardless of its actual value.

REGISTER 17-3: SPIxCON2L: SPIx CONTROL REGISTER 2 LOW

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
_	_	_	WLENGTH<4:0> ^(1,2)					
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-5 **Unimplemented:** Read as '0'

bit 4-0 WLENGTH<4:0>: Variable Word Length bits^(1,2)

11111 = **32**-bit data

11110 **= 31-bit data**

11101 = 30-bit data

11100 **= 29-bit data**

11011 **= 28-bit data**

11010 **= 27-bit data**

11001 **= 26-bit data**

11000 **= 25-bit data**

10111 = 24-bit data

10110 **= 23-bit data**

10101 = 22-bit data

10100 **= 21-bit data**

10011 = **20**-bit data

10010 = **19-bit data** 10001 = **18-bit data**

100001 = 10 bit data

01111 = **16-bit data**

01110 **= 15-bit data**

01101 **= 14-bit data**

01100 **= 13-bit data**

01011 **= 12-bit data**

01010 = 11-bit data

01001 **= 10-bit data**

01000 **= 9-bit data**

00111 **= 8-bit data**

00110 = **7-bit data**

00101 **= 6-bit data**

00100 **= 5-bit data**

00011 **= 4-bit data**

00010 = 3-bit data

00001 = 2-bit data

00000 = See MODE<32,16> bits in SPIxCON1L<11:10>

Note 1: These bits are effective when AUDEN = 0 only.

2: Varying the length by changing these bits does not affect the depth of the TX/RX FIFO.

REGISTER 17-4: SPIXSTATL: SPIX STATUS REGISTER LOW

U-0	U-0	U-0	HS/R/C-0	HSC/R-0	U-0	U-0	HSC/R-0
_	_	_	FRMERR	SPIBUSY	_	_	SPITUR ⁽¹⁾
bit 15							bit 8

HSC/R-0	HS/R/C-0	HSC/R-1	U-0	HSC/R-1	U-0	HSC/R-0	HSC/R-0
SRMT	SPIROV	SPIRBE	_	SPITBE	_	SPITBF	SPIRBF
bit 7							bit 0

Legend:	C = Clearable bit	U = Unimplemented, rea	U = Unimplemented, read as '0'		
R = Readable bit	W = Writable bit	HSC = Hardware Settat	HSC = Hardware Settable/Clearable bit		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	HS = Hardware Settable bit		

bit 15-13 **Unimplemented:** Read as '0'

bit 12 FRMERR: SPIx Frame Error Status bit

1 = Frame error is detected 0 = No frame error is detected

bit 11 SPIBUSY: SPIx Activity Status bit

1 = Module is currently busy with some transactions

0 = No ongoing transactions (at time of read)

bit 10-9 Unimplemented: Read as '0'

bit 8 SPITUR: SPIx Transmit Underrun Status bit (1)

1 = Transmit buffer has encountered a Transmit Underrun condition 0 = Transmit buffer does not have a Transmit Underrun condition

bit 7 SRMT: Shift Register Empty Status bit

1 = No current or pending transactions (i.e., neither SPIxTXB or SPIxTXSR contains data to transmit)

0 = Current or pending transactions

bit 6 SPIROV: SPIx Receive Overflow Status bit

1 = A new byte/half-word/word has been completely received when the SPIxRXB was full

0 = No overflow

bit 5 SPIRBE: SPIx RX Buffer Empty Status bit

1 = RX buffer is empty0 = RX buffer is not emptyStandard Buffer Mode:

Automatically set in hardware when SPIxBUF is read from, reading SPIxRXB. Automatically cleared in

hardware when SPIx transfers data from SPIxRXSR to SPIxRXB.

Enhanced Buffer Mode:

Indicates RXELM<5:0> = 000000.

bit 4 **Unimplemented:** Read as '0'

Note 1: SPITUR is cleared when SPIEN = 0. When IGNTUR = 1, SPITUR provides dynamic status of the Transmit Underrun condition, but does not stop RX/TX operation and does not need to be cleared by software.

REGISTER 17-4: SPIXSTATL: SPIX STATUS REGISTER LOW (CONTINUED)

bit 3 SPITBE: SPIx Transmit Buffer Empty Status bit

1 = SPIxTXB is empty 0 = SPIxTXB is not empty Standard Buffer Mode:

Automatically set in hardware when SPIx transfers data from SPIxTXB to SPIxTXSR. Automatically

cleared in hardware when SPIxBUF is written, loading SPIxTXB.

Enhanced Buffer Mode:

Indicates TXELM<5:0> = 000000.

bit 2 Unimplemented: Read as '0'

bit 1 SPITBF: SPIx Transmit Buffer Full Status bit

1 = SPIxTXB is full 0 = SPIxTXB not full Standard Buffer Mode:

Automatically set in hardware when SPIxBUF is written, loading SPIxTXB. Automatically cleared in

hardware when SPIx transfers data from SPIxTXB to SPIxTXSR.

Enhanced Buffer Mode:

Indicates TXELM<5:0> = 111111.

bit 0 SPIRBF: SPIx Receive Buffer Full Status bit

1 = SPIxRXB is full 0 = SPIxRXB is not full Standard Buffer Mode:

Automatically set in hardware when SPIx transfers data from SPIxRXSR to SPIxRXB. Automatically

cleared in hardware when SPIxBUF is read from, reading SPIxRXB.

Enhanced Buffer Mode:

Indicates RXELM<5:0> = 111111.

Note 1: SPITUR is cleared when SPIEN = 0. When IGNTUR = 1, SPITUR provides dynamic status of the Transmit Underrun condition, but does not stop RX/TX operation and does not need to be cleared by software.

REGISTER 17-5: SPIXSTATH: SPIX STATUS REGISTER HIGH

U-0	U-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0
_	_	RXELM5 ⁽³⁾	RXELM4 ⁽²⁾	RXELM3 ⁽¹⁾	RXELM2	RXELM1	RXELM0
bit 15							bit 8

U-0	U-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0
_	_	TXELM5 ⁽³⁾	TXELM4 ⁽²⁾	TXELM3 ⁽¹⁾	TXELM2	TXELM1	TXELM0
bit 7							bit 0

Legend:	HSC = Hardware Settable/Clearable bit				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15-14 **Unimplemented:** Read as '0'

bit 13-8 **RXELM<5:0>:** Receive Buffer Element Count bits (valid in Enhanced Buffer mode)^(1,2,3)

bit 7-6 **Unimplemented:** Read as '0'

bit 5-0 **TXELM<5:0>:** Transmit Buffer Element Count bits (valid in Enhanced Buffer mode)^(1,2,3)

Note 1: RXELM3 and TXELM3 bits are only present when FIFODEPTH = 8 or higher.

2: RXELM4 and TXELM4 bits are only present when FIFODEPTH = 16 or higher.

3: RXELM5 and TXELM5 bits are only present when FIFODEPTH = 32.

REGISTER 17-6: SPIXIMSKL: SPIX INTERRUPT MASK REGISTER LOW

U-0	U-0	U-0	R/W-0	R/W-0	U-0	U-0	R/W-0
_	_	_	FRMERREN	BUSYEN	_	_	SPITUREN
bit 15							bit 8

R/W-0	R/W-0	R/W-0	U-0	R/W-0	U-0	R/W-0	R/W-0
SRMTEN	SPIROVEN	SPIRBEN	_	SPITBEN	_	SPITBFEN	SPIRBFEN
bit 7							bit 0

Legend:

bit 6

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 **Unimplemented:** Read as '0'

bit 12 FRMERREN: Enable Interrupt Events via FRMERR bit

1 = Frame error generates an interrupt event

0 = Frame error does not generate an interrupt event

bit 11 BUSYEN: Enable Interrupt Events via SPIBUSY bit

1 = SPIBUSY generates an interrupt event

0 = SPIBUSY does not generate an interrupt event

bit 10-9 **Unimplemented:** Read as '0'

bit 8 SPITUREN: Enable Interrupt Events via SPITUR bit

1 = Transmit Underrun (TUR) generates an interrupt event

0 = Transmit Underrun does not generate an interrupt event

bit 7 SRMTEN: Enable Interrupt Events via SRMT bit

1 = Shift Register Empty (SRMT) generates interrupt events

0 = Shift Register Empty does not generate interrupt events

SPIROVEN: Enable Interrupt Events via SPIROV bit

1 = SPIx Receive Overflow (ROV) generates an interrupt event

0 = SPIx Receive Overflow does not generate an interrupt event

bit 5 SPIRBEN: Enable Interrupt Events via SPIRBE bit

1 = SPIx RX buffer empty generates an interrupt event

0 = SPIx RX buffer empty does not generate an interrupt event

bit 4 Unimplemented: Read as '0'

bit 3 SPITBEN: Enable Interrupt Events via SPITBE bit

1 = SPIx transmit buffer empty generates an interrupt event

 $_{
m 0}$ = SPIx transmit buffer empty does not generate an interrupt event

bit 2 Unimplemented: Read as '0'

bit 1 SPITBFEN: Enable Interrupt Events via SPITBF bit

1 = SPIx transmit buffer full generates an interrupt event

0 = SPIx transmit buffer full does not generate an interrupt event

bit 0 SPIRBFEN: Enable Interrupt Events via SPIRBF bit

1 = SPIx receive buffer full generates an interrupt event

0 = SPIx receive buffer full does not generate an interrupt event

REGISTER 17-7: SPIXIMSKH: SPIX INTERRUPT MASK REGISTER HIGH

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
RXWIEN	_	RXMSK5 ⁽¹⁾	RXMSK4 ^(1,4)	RXMSK3 ^(1,3)	RXMSK2 ^(1,2)	RXMSK1 ⁽¹⁾	RXMSK0 ⁽¹⁾
bit 15							bit 8

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TXWIEN	_	TXMSK5 ⁽¹⁾	TXMSK4 ^(1,4)	TXMSK3 ^(1,3)	TXMSK2 ^(1,2)	TXMSK1 ⁽¹⁾	TXMSK0 ⁽¹⁾
bit 7							bit 0

Legend:			
R = Readable bit	le bit W = Writable bit U = Unimplemented bit, read as '0'		d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 **RXWIEN:** Receive Watermark Interrupt Enable bit

1 = Triggers receive buffer element watermark interrupt when RXMSK<5:0> ≤ RXELM<5:0>

0 = Disables receive buffer element watermark interrupt

bit 14 **Unimplemented:** Read as '0'

bit 13-8 **RXMSK<5:0>:** RX Buffer Mask bits^(1,2,3,4)

RX mask bits; used in conjunction with the RXWIEN bit.

bit 7 TXWIEN: Transmit Watermark Interrupt Enable bit

1 = Triggers transmit buffer element watermark interrupt when TXMSK<5:0> = TXELM<5:0>

0 = Disables transmit buffer element watermark interrupt


bit 6 **Unimplemented:** Read as '0'

bit 5-0 **TXMSK<5:0>:** TX Buffer Mask bits^(1,2,3,4)

TX mask bits; used in conjunction with the TXWIEN bit.

Note 1: Mask values higher than FIFODEPTH are not valid. The module will not trigger a match for any value in this case.

- 2: RXMSK2 and TXMSK2 bits are only present when FIFODEPTH = 8 or higher.
- 3: RXMSK3 and TXMSK3 bits are only present when FIFODEPTH = 16 or higher.
- 4: RXMSK4 and TXMSK4 bits are only present when FIFODEPTH = 32.



User must write transmit data to read the received data from SPIxBUF. The SPIxTXB and SPIxRXB registers are memory-mapped to SPIxBUF.




FIGURE 17-4: SPIX MASTER/SLAVE CONNECTION (ENHANCED BUFFER MODES)

FIGURE 17-5: SPIX MASTER, FRAME MASTER CONNECTION DIAGRAM




FIGURE 17-6: SPIX MASTER, FRAME SLAVE CONNECTION DIAGRAM




FIGURE 17-7: SPIX SLAVE, FRAME MASTER CONNECTION DIAGRAM





FIGURE 17-8: SPIX SLAVE, FRAME SLAVE CONNECTION DIAGRAM



EQUATION 17-1: RELATIONSHIP BETWEEN DEVICE AND SPIx CLOCK SPEED

$$Baud Rate = \frac{FPB}{(2 * (SPIxBRG + 1))}$$

Where:

FPB is the Peripheral Bus Clock Frequency.

18.0 INTER-INTEGRATED CIRCUIT (I²C)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. For more information, refer to "Inter-Integrated Circuit (I²C)" (www.microchip.com/DS70000195) in the "dsPIC33/PIC24 Family Reference Manual".

The Inter-Integrated Circuit (I²C) module is a serial interface useful for communicating with other peripheral or microcontroller devices. These peripheral devices may be serial EEPROMs, display drivers, A/D Converters, etc.

The I²C module supports these features:


- · Independent Master and Slave Logic
- · 7-Bit and 10-Bit Device Addresses
- General Call Address as Defined in the I²C Protocol
- Clock Stretching to Provide Delays for the Processor to Respond to a Slave Data Request
- · Both 100 kHz and 400 kHz Bus Specifications
- · Configurable Address Masking
- Multi-Master modes to Prevent Loss of Messages in Arbitration
- Bus Repeater mode, Allowing the Acceptance of All Messages as a Slave, regardless of the Address
- · Automatic SCL
- · SMBus Compatible Voltage Thresholds

A block diagram of the module is shown in Figure 18-1.

18.1 Communicating as a Master in a Single Master Environment

The details of sending a message in Master mode depends on the communication protocol for the device being communicated with. Typically, the sequence of events is as follows:

- 1. Assert a Start condition on SDAx and SCLx.
- Send the I²C device address byte to the Slave with a write indication.
- Wait for and verify an Acknowledge from the Slave.
- 4. Send the first data byte (sometimes known as the command) to the Slave.
- Wait for and verify an Acknowledge from the Slave.
- Send the serial memory address low byte to the Slave
- Repeat Steps 4 and 5 until all data bytes are sent
- Assert a Repeated Start condition on SDAx and SCLx.
- 9. Send the device address byte to the Slave with a read indication.
- Wait for and verify an Acknowledge from the Slave.
- Enable Master reception to receive serial memory data.
- 12. Generate an ACK or NACK condition at the end of a received byte of data.
- 13. Generate a Stop condition on SDAx and SCLx.



18.2 Setting Baud Rate When Operating as a Bus Master

To compute the Baud Rate Generator reload value, use Equation 18-1.

EQUATION 18-1: COMPUTING BAUD RATE RELOAD VALUE^(1,2,3,4)

 $I2CxBRG = ((1/FSCL - Delay) \cdot FCY/2) - 2$

Note 1: Based on Fcy = Fosc/2; Doze mode and PLL are disabled.

- 2: These clock rate values are for guidance only. The actual clock rate can be affected by various system-level parameters. The actual clock rate should be measured in its intended application.
- **3:** Typical value of delay varies from 110 ns to 150 ns.
- 4: I2CxBRG values of 0 to 3 are expressly forbidden. The user should never program the I2CxBRG with a value of 0x0, 0x1, 0x2 or 0x3 as indeterminate results may occur.

18.3 Slave Address Masking

The I2CxMSK register (Register 18-4) designates address bit positions as "don't care" for both 7-Bit and 10-Bit Addressing modes. Setting a particular bit location (= 1) in the I2CxMSK register causes the Slave module to respond, whether the corresponding address bit value is a '0' or a '1'. For example, when I2CxMSK is set to '00100000000', the Slave module will detect both addresses, '00000000000' and '0010000000'.

To enable address masking, the Intelligent Peripheral Management Interface (IPMI) must be disabled by clearing the STRICT bit (I2CxCONL<11>).

Note: As a result of changes in the I²C protocol, the addresses in Table 18-2 are reserved and will not be Acknowledged in Slave mode. This includes any address mask settings that include any of these addresses.

TABLE 18-1: I2Cx CLOCK RATES^(1,2)

Foy	Foot	I2CxB	RG Value
FcY	FSCL	Decimal	Hexadecimal
100 MHz	1 MHz	41	29
100 MHz	400 kHz	116	74
100 MHz	100 kHz	491	1EB
80 MHz	1 MHz	32	20
80 MHz	400 kHz	92	5C
80 MHz	100 kHz	392	188
60 MHz	1 MHz	24	18
60 MHz	400 kHz	69	45
60 MHz	100 kHz	294	126
40 MHz	1 MHz	15	0F
40 MHz	400 kHz	45	2D
40 MHz	100 kHz	195	C3
20 MHz	1 MHz	7	7
20 MHz	400 kHz	22	16
20 MHz	100 kHz	97	61

Note 1: Based on Fcy = Fosc/2; Doze mode and PLL are disabled.

2: These clock rate values are for guidance only. The actual clock rate can be affected by various system-level parameters. The actual clock rate should be measured in its intended application.

TABLE 18-2: I2Cx RESERVED ADDRESSES⁽¹⁾

Slave Address	R/W Bit	Description
0000 000	0	General Call Address ⁽²⁾
0000 000	1	Start Byte
0000 001	Х	Cbus Address
0000 01x	Х	Reserved
0000 1xx	Х	HS Mode Master Code
1111 0xx	Х	10-Bit Slave Upper Byte ⁽³⁾
1111 1xx	Х	Reserved

- Note 1: The address bits listed here will never cause an address match independent of address mask settings.
 - 2: This address will be Acknowledged only if GCEN = 1.
 - 3: A match on this address can only occur on the upper byte in 10-Bit Addressing mode.

18.4 SMBus Support

The dsPIC33CK256MP508 family devices have support for SMBus through options in the input voltage thresholds. There are two control bits to select one of three options: SMEN (I2CxCONL<8>) and Configuration bit, SMBEN (FDEVOPT<10>). Table 18-3 details the setting of these control bits.

TABLE 18-3: I²C PIN VOLTAGE THRESHOLD

	SMEN SFR Bit (I2CxCONL<8>)	SMBEN Configuration Bit (FDEVOPT<10>)
I ² C (default)	0	Х
SMBus 2.0	1	0
SMBus 3.0	1	1

18.5 Control Registers

REGISTER 18-1: I2CxCONL: I2Cx CONTROL REGISTER LOW

R/W-0	U-0	HC/R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0
I2CEN	_	I2CSIDL	SCLREL ⁽¹⁾	STRICT	A10M	DISSLW	SMEN
bit 15							bit 8

R/W-0	R/W-0	R/W-0	HC/R/W-0	HC/R/W-0	HC/R/W-0	HC/R/W-0	HC/R/W-0
GCEN	STREN	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN
bit 7							bit 0

Legend: HC = Hardware Clearable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **I2CEN:** I2Cx Enable bit (writable from software only)

1 = Enables the I2Cx module, and configures the SDAx and SCLx pins as serial port pins

0 = Disables the I2Cx module; all I²C pins are controlled by port functions

bit 14 **Unimplemented:** Read as '0'

bit 13 I2CSIDL: I2Cx Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 SCLREL: SCLx Release Control bit (I²C Slave mode only)⁽¹⁾

1 = Releases the SCLx clock

0 = Holds the SCLx clock low (clock stretch)

If STREN = 1:(2)

User software may write '0' to initiate a clock stretch and write '1' to release the clock. Hardware clears at the beginning of every Slave data byte transmission. Hardware clears at the end of every Slave address byte reception. Hardware clears at the end of every Slave data byte reception.

If STREN = 0:

User software may only write '1' to release the clock. Hardware clears at the beginning of every Slave data byte transmission. Hardware clears at the end of every Slave address byte reception.

bit 11 STRICT: I2Cx Strict Reserved Address Rule Enable bit

1 = Strict reserved addressing is enforced; for reserved addresses, refer to Table 18-2.
 (In Slave Mode) – The device doesn't respond to reserved address space and addresses falling in that category are NACKed.

(In Master Mode) – The device is allowed to generate addresses with reserved address space.

0 = Reserved addressing would be Acknowledged.

(In Slave Mode) – The device will respond to an address falling in the reserved address space. When there is a match with any of the reserved addresses, the device will generate an ACK. (In Master Mode) – Reserved.

bit 10 A10M: 10-Bit Slave Address Flag bit

1 = I2CxADD is a 10-bit Slave address

0 = I2CxADD is a 7-bit Slave address

bit 9 DISSLW: Slew Rate Control Disable bit

1 = Slew rate control is disabled for Standard Speed mode (100 kHz, also disabled for 1 MHz mode)

0 = Slew rate control is enabled for High-Speed mode (400 kHz)

Note 1: Automatically cleared to '0' at the beginning of Slave transmission; automatically cleared to '0' at the end of Slave reception.

2: Automatically cleared to '0' at the beginning of Slave transmission.

REGISTER 18-1: I2CxCONL: I2Cx CONTROL REGISTER LOW (CONTINUED)

bit 8 SMEN: SMBus Input Levels Enable bit

1 = Enables input logic so thresholds are compliant with the SMBus specification

0 = Disables SMBus-specific inputs

bit 7 GCEN: General Call Enable bit (I²C Slave mode only)

1 = Enables interrupt when a general call address is received in I2CxRSR; module is enabled for reception

0 = General call address is disabled.

bit 6 STREN: SCLx Clock Stretch Enable bit

In I²C Slave mode only; used in conjunction with the SCLREL bit.

1 = Enables clock stretching

0 = Disables clock stretching

bit 5 ACKDT: Acknowledge Data bit

In I²C Master mode during Master Receive mode. The value that will be transmitted when the user initiates an Acknowledge sequence at the end of a receive.

In I^2C Slave mode when AHEN = 1 or DHEN = 1. The value that the Slave will transmit when it initiates an Acknowledge sequence at the end of an address or data reception.

1 = NACK is sent

0 = ACK is sent

bit 4 ACKEN: Acknowledge Sequence Enable bit

In I²C Master mode only; applicable during Master Receive mode.

1 = Initiates Acknowledge sequence on SDAx and SCLx pins, and transmits ACKDT data bit

0 = Acknowledge sequence is Idle

bit 3 **RCEN:** Receive Enable bit (I²C Master mode only)

1 = Enables Receive mode for I²C; automatically cleared by hardware at end of 8-bit receive data byte

0 = Receive sequence is not in progress

bit 2 **PEN:** Stop Condition Enable bit (I²C Master mode only)

1 = Initiates Stop condition on SDAx and SCLx pins

0 = Stop condition is Idle

bit 1 **RSEN:** Restart Condition Enable bit (I²C Master mode only)

1 = Initiates Restart condition on SDAx and SCLx pins

0 = Restart condition is Idle

bit 0 **SEN:** Start Condition Enable bit (I²C Master mode only)

1 = Initiates Start condition on SDAx and SCLx pins

0 = Start condition is Idle

Note 1: Automatically cleared to '0' at the beginning of Slave transmission; automatically cleared to '0' at the end of Slave reception.

2: Automatically cleared to '0' at the beginning of Slave transmission.

REGISTER 18-2: I2CxCONH: I2Cx CONTROL REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	R/W-0						
_	PCIE	SCIE	BOEN	SDAHT	SBCDE	AHEN	DHEN
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-7 Unimplemented: Read as '0'

bit 6 **PCIE:** Stop Condition Interrupt Enable bit (I²C Slave mode only).

1 = Enables interrupt on detection of Stop condition

0 = Stop detection interrupts are disabled

bit 5 SCIE: Start Condition Interrupt Enable bit (I²C Slave mode only)

1 = Enables interrupt on detection of Start or Restart conditions

0 = Start detection interrupts are disabled

bit 4 **BOEN:** Buffer Overwrite Enable bit (I²C Slave mode only)

1 = I2CxRCV is updated and an ACK is generated for a received address/data byte, ignoring the state of the I2COV bit only if RBF bit = 0

0 = I2CxRCV is only updated when I2COV is clear

bit 3 SDAHT: SDAx Hold Time Selection bit

1 = Minimum of 300 ns hold time on SDAx after the falling edge of SCLx

0 = Minimum of 100 ns hold time on SDAx after the falling edge of SCLx

bit 2 **SBCDE**: Slave Mode Bus Collision Detect Enable bit (I²C Slave mode only)

If, on the rising edge of SCLx, SDAx is sampled low when the module is outputting a high state, the BCL bit is set and the bus goes Idle. This Detection mode is only valid during data and ACK transmit sequences.

1 = Enables Slave bus collision interrupts

0 = Slave bus collision interrupts are disabled

bit 1 AHEN: Address Hold Enable bit (I²C Slave mode only)

1 = Following the 8th falling edge of SCLx for a matching received address byte; SCLREL bit (I2CxCONL<12>) will be cleared and the SCLx will be held low

0 = Address holding is disabled

bit 0 **DHEN:** Data Hold Enable bit (I²C Slave mode only)

1 = Following the 8th falling edge of SCLx for a received data byte; Slave hardware clears the SCLREL bit (I2CxCONL<12>) and SCLx is held low

0 = Data holding is disabled

REGISTER 18-3: I2CxSTAT: I2Cx STATUS REGISTER

HSC/R-0	HSC/R-0	HSC/R-0	U-0	U-0	HSC/R/C-0	HSC/R-0	HSC/R-0
ACKSTAT	TRSTAT	ACKTIM	_	_	BCL	GCSTAT	ADD10
bit 15							bit 8

HS/R/C-0	HS/R/C-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0
IWCOL	I2COV	D/Ā	Р	S	R/W	RBF	TBF
bit 7							bit 0

Legend:	C = Clearable bit	HSC = Hardware Settable/Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, rea	d as '0'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	HS = Hardware Settable bit	

bit 15 ACKSTAT: Acknowledge Status bit (updated in all Master and Slave modes)

1 = Acknowledge was not received from Slave

0 = Acknowledge was received from Slave

bit 14 **TRSTAT:** Transmit Status bit (when operating as I²C Master; applicable to Master transmit operation)

1 = Master transmit is in progress (8 bits + ACK)

0 = Master transmit is not in progress

bit 13 **ACKTIM**: Acknowledge Time Status bit (valid in I²C Slave mode only)

1 = Indicates I²C bus is in an Acknowledge sequence, set on 8th falling edge of SCLx clock

0 = Not an Acknowledge sequence, cleared on 9th rising edge of SCLx clock

bit 12-11 Unimplemented: Read as '0'

bit 10 **BCL:** Bus Collision Detect bit (Master/Slave mode; cleared when I²C module is disabled, I2CEN = 0)

1 = A bus collision has been detected during a Master or Slave transmit operation

0 = No bus collision has been detected

bit 9 GCSTAT: General Call Status bit (cleared after Stop detection)

1 = General call address was received

0 = General call address was not received

bit 8 **ADD10:** 10-Bit Address Status bit (cleared after Stop detection)

1 = 10-bit address was matched

0 = 10-bit address was not matched

bit 7 IWCOL: I2Cx Write Collision Detect bit

1 = An attempt to write to the I2CxTRN register failed because the I²C module is busy; must be cleared in software

0 = No collision

bit 6 I2COV: I2Cx Receive Overflow Flag bit

1 = A byte was received while the I2CxRCV register is still holding the previous byte; I2COV is a "don't care" in Transmit mode, must be cleared in software

0 = No overflow

bit 5 D/A: Data/Address bit (when operating as I²C Slave)

1 = Indicates that the last byte received was data

0 = Indicates that the last byte received or transmitted was an address

bit 4 **P:** I2Cx Stop bit

Updated when Start, Reset or Stop is detected; cleared when the I^2C module is disabled, I2CEN = 0.

1 = Indicates that a Stop bit has been detected last

0 = Stop bit was not detected last

REGISTER 18-3: I2CxSTAT: I2Cx STATUS REGISTER (CONTINUED)

bit 3 S: I2Cx Start bit

Updated when Start, Reset or Stop is detected; cleared when the I²C module is disabled, I2CEN = 0.

1 = Indicates that a Start (or Repeated Start) bit has been detected last

0 = Start bit was not detected last

bit 2 R/W: Read/Write Information bit (when operating as I^2C Slave)

1 = Read: Indicates the data transfer is output from the Slave

0 = Write: Indicates the data transfer is input to the Slave

bit 1 RBF: Receive Buffer Full Status bit

1 = Receive is complete, I2CxRCV is full

0 = Receive is not complete, I2CxRCV is empty

bit 0 TBF: Transmit Buffer Full Status bit

1 = Transmit is in progress, I2CxTRN is full (8-bits of data)

0 = Transmit is complete, I2CxTRN is empty

REGISTER 18-4: I2CxMSK: I2Cx SLAVE MODE ADDRESS MASK REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	
_	_	_	_	_	_	MSK	<9:8>	
bit 15						bit		

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | MSK. | <7:0> | | | |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-10 **Unimplemented:** Read as '0'

bit 9-0 MSK<9:0>: I2Cx Mask for Address Bit x Select bits

1 = Enables masking for bit x of the incoming message address; bit match is not required in this position

0 = Disables masking for bit x; bit match is required in this position

<u></u>			
NOTES:			

19.0 PARALLEL MASTER PORT (PMP)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Parallel Master Port (PMP)" (www.microchip.com/DS70005344) in the "dsPIC33/PIC24 Family Reference Manual".


2: Not all device variants include the PMP. Refer to Table 1 and Table 2 for availability.

The Parallel Master Port (PMP) is a parallel 8-bit/16-bit I/O module specifically designed to communicate with a wide variety of parallel devices, such as communication peripherals, LCDs, external memory devices and microcontrollers. Because the interfaces to parallel

peripherals vary significantly, the PMP module is highly configurable. The key features of the PMP module include:

- · Master and Slave Operating modes
- · Up to 16 Programmable Address Lines
- · Up to Two Chip Select Lines
- · Programmable Strobe Options:
 - Individual read and write strobes or read/write strobe with enable strobe
- · Address Auto-Increment/Auto-Decrement
- · Programmable Address/Data Multiplexing
- · Programmable Polarity on Control Signals
- · Legacy Parallel Slave Port Support
- Enhanced Parallel Slave Support:
 - Address support
 - 4 bytes deep, auto-incrementing buffer
- Schmitt Trigger or TTL Input Buffers
- · Programmable Wait States
- Dual Buffer Mode with Separate Read and Write Registers
- · Read Initiate Control

FIGURE 19-1: PMP MODULE PINOUT AND CONNECTIONS TO EXTERNAL DEVICES



19.1 Parallel Master Port Control Registers

REGISTER 19-1: PMCON: PARALLEL MASTER PORT CONTROL REGISTER

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ON	_	SIDL	ADRMUX1	ADRMUX0	PMPTTL	PTWREN	PTRDEN
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
CSF1 ⁽¹⁾	CSF0 ⁽¹⁾	ALP ⁽¹⁾	CS2P ⁽¹⁾	CS1P ⁽¹⁾	_	WRSP	RDSP
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 ON: Parallel Master Port Enable bit

1 = PMP is enabled

0 = PMP is disabled, no off-chip access performed

bit 14 **Unimplemented:** Read as '0'

bit 13 SIDL: PMP Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12-11 ADRMUX<1:0>: Address/Data Multiplexing Selection bits

11 = All 16 bits of address are multiplexed with the 16 bits of data (PMPA<15:0>/PMPD<15:0>) using two phases

10 = All 16 bits of address are multiplexed with the lower 8 bits of data (PMPA<15:8>/PMPA<7:0>/ PMPD<7:0>) using three phases

01 = Lower 8 bits of address are multiplexed with lower 8 bits of data (PMPA<7:0>/PMPD<7:0>)

00 = Address and data appear on separate pins

bit 10 PMPTTL: PMP Module TTL Input Buffer Select bit

1 = PMP module uses TTL input buffers

0 = PMP module uses Schmitt Trigger input buffers

bit 9 PTWREN: PMP Write Enable Strobe Port Enable bit

1 = PMWR/PMENB port is enabled

0 = PMWR/PMENB port is disabled

bit 8 PTRDEN: PMP Read/Write Strobe Port Enable bit

1 = PMRD/PMWR port is enabled 0 = PMRD/PMWR port is disabled

bit 7-6 CSF<1:0>: Chip Select Function bits⁽¹⁾

11 = Reserved

10 = PMCS2 and PMCS1 function as Chip Select

01 = PMCS2 functions as Chip Select, PMCS1 functions as address bit

00 = PMCS2 and PMCS1 function as address bits

bit 5 **ALP:** Address Latch Polarity bit⁽¹⁾

1 = Active-high (PMALL and PMALH)

 $0 = Active-low (\overline{PMALL} \text{ and } \overline{PMALH})$

bit 4 CS2P: Chip Select 2 Polarity bit⁽¹⁾

1 = Active-high

0 = Active-low

Note 1: These bits have no effect when their corresponding pins are used as address lines.

REGISTER 19-1: PMCON: PARALLEL MASTER PORT CONTROL REGISTER (CONTINUED)

bit 3 **CS1P:** Chip Select 1 Polarity bit⁽¹⁾

1 = Active-high
0 = Active-low

bit 2 **Unimplemented:** Read as '0' bit 1 **WRSP:** Write Strobe Polarity bit

For Slave Modes and Master Mode 2 (MODE<1:0> (PMMODE<9:8>) = 00, 01, 10):

1 = Write strobe is active-high (PMWR) 0 = Write strobe is active-low (PMWR)

For Master Mode 1 (MODE<1:0> (PMMODE<9:8>) = 11):

1 = Enables strobe active-high (PMENB) 0 = Enables strobe active-low (PMENB)

bit 0 RDSP: Read Strobe Polarity bit

For Slave Modes and Master Mode 2 (MODE<1:0> (PMMODE<9:8>) = 00, 01, 10):

1 = Read strobe is active-high (PMRD) 0 = Read strobe is active-low (PMRD)

For Master Mode 1 (MODE<1:0> (PMMODE<9:8>) = 11): 1 = Read/write strobe is active-high (PMRD/PMWR) 0 = Read/write strobe is active-low (PMRD/PMWR)

Note 1: These bits have no effect when their corresponding pins are used as address lines.

REGISTER 19-2: PMCONH: PARALLEL MASTER PORT CONTROL HIGH REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W/HC-0	U-0	U-0	U-0	U-0	U-0	R/W-0	U-0
RDSTART ⁽¹⁾	_	_	_	_	_	DUALBUF	_
bit 7							bit 0

Legend: HC = Hardware Clearable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7 **RDSTART:** Start a Read on PMP Bus bit⁽¹⁾

1 = Starts a read cycle on the PMP bus

0 = No effect

bit 6-2 **Unimplemented:** Read as '0'

bit 1 **DUALBUF:** PMP Dual Read/Write Buffers Enable bit (valid in Master mode only)

1 = PMP uses separate registers for reads and writes (PMRADDR, PMDINx, PMWADDR, PMDOUTx)

0 = PMP uses legacy registers (PMADDR, PMDINx)

bit 0 **Unimplemented:** Read as '0'

Note 1: This bit is cleared by HW at the end of the read cycle when BUSY (PMMODE<15>) = 0.

REGISTER 19-3: PMMODE: PARALLEL MASTER PORT MODE REGISTER

R/HS/HC-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
BUSY	IRQM1	IRQM0	INCM1	INCM0	MODE16	MODE1	MODE0
bit 15							bit 8

| R/W-0 |
|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|
| WAITB1 ⁽¹⁾ | WAITB0 ⁽¹⁾ | WAITM3 ⁽¹⁾ | WAITM2 ⁽¹⁾ | WAITM1 ⁽¹⁾ | WAITM0 ⁽¹⁾ | WAITE1 ⁽¹⁾ | WAITE0 ⁽¹⁾ |
| bit 7 | | | | | | | bit 0 |

Legend:	HC = Hardware Clearable bit	HS = Hardware Settable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15 **BUSY:** Busy bit (Master mode only)

1 = Port is busy

0 = Port is not busy

bit 14-13 IRQM<1:0>: Interrupt Request Mode bits

11 = Reserved, do not use

10 = Interrupt generated when Read Buffer 3 is read or Write Buffer 3 is written (Buffered PSP mode), or on a read or write operation when PMA<1:0> = 11 (Addressable Slave mode only)

01 = Interrupt generated at the end of the read/write cycle

00 = No Interrupt generated

bit 12-11 INCM<1:0>: Increment Mode bits

11 = Slave mode read and write buffers auto-increment (MODE<1:0> (PMMODE<9:8>) = 00 only)

10 = Decrements ADDR<15:0> by 1 every read/write cycle^(2,4)

01 = Increments ADDR<15:0> by 1 every read/write cycle^(2,4)

00 = No increment or decrement of address

bit 10 MODE16: 8/16-Bit Mode bit

1 = 16-Bit Mode: A read or write to the Data register invokes a single 16-bit transfer

0 = 8-Bit Mode: A read or write to the Data register invokes a single 8-bit transfer

bit 9-8 MODE<1:0>: PMP Mode Select bits

11 = Master Mode 1 (PMCSx, PMRD/PMWR, PMENB, PMA<x:0>, PMD<7:0> and PMD<8:15>(3))

10 = Master Mode 2 (PMCSx, PMRD, PMWR, PMA<x:0>, PMD<7:0> and PMD<8:15>(3))

01 = Enhanced Slave mode, controls signals (PMRD, PMWR, PMCS, PMD<7:0> and PMA<1:0>)

00 = Legacy Parallel Slave Port, controls signals (PMRD, PMWR, PMCS and PMD<7:0>)

bit 7-6 **WAITB<1:0>:** Data Setup to Read/Write Strobe Wait States bits⁽¹⁾

11 = Data Wait of 4 TP; multiplexed address phase of 4 TP

10 = Data Wait of 3 TP; multiplexed address phase of 3 TP

01 = Data Wait of 2 TP; multiplexed address phase of 2 TP

00 = Data Wait of 1 TP; multiplexed address phase of 1 TP (default)

Note 1: When WAITM<3:0> = 0000, the WAITBx and WAITEx bits are ignored and forced to 1 TP (peripheral clock) cycle for a write operation; WAITBx = 1 TP cycle, WAITEx = 0 TP cycles for a read operation.

2: Address bits, A15 and A14, are not subject to auto-increment/decrement if configured as Chip Select, CS2 and CS1.

3: These pins are active when MODE16 = 1 (16-bit mode).

4: The PMADDR register is always incremented/decremented by 1 regardless of the transfer data width.

REGISTER 19-3: PMMODE: PARALLEL MASTER PORT MODE REGISTER (CONTINUED)

```
WAITM<3:0>: Data Read/Write Strobe Wait States bits(1)
bit 5-2
              1111 = Wait of 16 TP
              0001 = Wait of 2 TP
              0000 = Wait of 1 TP (default)
              WAITE<1:0>: Data Hold After Read/Write Strobe Wait States bits(1)
bit 1-0
              11 = Wait of 4 TP
              10 = Wait of 3 TP
              01 = Wait of 2 TP
              00 = Wait of 1 TP (default)
              For Read Operations:
              11 = Wait of 3 TP
              10 = Wait of 2 TP
              01 = Wait of 1 TP
              00 = Wait of 0 TP (default)
```

- **Note 1:** When WAITM<3:0> = 0000, the WAITBx and WAITEx bits are ignored and forced to 1 TP (peripheral clock) cycle for a write operation; WAITBx = 1 TP cycle, WAITEx = 0 TP cycles for a read operation.
 - 2: Address bits, A15 and A14, are not subject to auto-increment/decrement if configured as Chip Select, CS2 and CS1
 - 3: These pins are active when MODE16 = 1 (16-bit mode).
 - 4: The PMADDR register is always incremented/decremented by 1 regardless of the transfer data width.

REGISTER 19-4: PMADDR: PARALLEL MASTER PORT ADDRESS REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
CS2 ⁽¹⁾	CS1 ⁽¹⁾	ADDP<13:8>							
ADDR15 ⁽¹⁾	ADDR14 ⁽¹⁾		ADDR<13:8>						
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
ADDR<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 CS2: Chip Select 2 bit⁽¹⁾

1 = Chip Select 2 is active

0 = Chip Select 2 is inactive (ADDR15 function is selected)

bit 15 **ADDR15:** Target Address bit 15⁽¹⁾

bit 14 CS1: Chip Select 1 bit⁽¹⁾

1 = Chip Select 1 is active

0 = Chip Select 1 is inactive (ADDR14 function is selected)

bit 14 ADDR14: Target Address bit 14⁽¹⁾

bit 13-0 ADDR<13:0>: Target Address bits

Note 1: The use of these pins as PMA15/PMA14 or CS2/CS1 is selected by the CSF<1:0> bits (PMCON<7:6>).

REGISTER 19-5: PMDOUT1: PARALLEL MASTER PORT DATA OUTPUT LOW REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
DATAOUT<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
DATAOUT<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **DATAOUT<15:0>:** Output Data Port bits

These bits are for 8-bit read operations in Slave mode and write operations for Dual Buffer Master mode.

REGISTER 19-6: PMDOUT2: PARALLEL MASTER PORT DATA OUTPUT HIGH REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
DATAOUT<31:24>										
bit 15							bit 8			

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
DATAOUT<23:16>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **DATAOUT<31:16>:** Output Data Port bits

These bits are for 8-bit write operations in Slave mode.

REGISTER 19-7: PMDIN1: PARALLEL MASTER PORT DATA INPUT/OUTPUT LOW REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0				
	DATAIN<15:8>										
bit 15							bit 8				

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0				
DATAIN<7:0>											
bit 7											

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 DATAIN<15:0>: Input/Output Data Port bits

These bits are for 8-bit or 16-bit read/write operations in Master mode and are the input data port for 8-bit write operations in Slave mode.

REGISTER 19-8: PMDIN2: PARALLEL MASTER PORT DATA INPUT/OUTPUT HIGH REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0				
	DATAIN<31:24>										
bit 15							bit 8				

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0				
DATAIN<23:16>											
bit 7							bit 0				

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **DATAIN<31:16>:** Input/Output Data Port bits

These bits are for 8-bit write operations in Slave mode.

REGISTER 19-9: PMAEN: PARALLEL MASTER PORT PIN ENABLE REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTEN<	15:14>		PTEN<13:8>						
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
	PTEN<7:2>						
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 PTEN<15:14>: PMCSx Strobe Enable bits

1 = PMA15 and PMA14 function as either PMA<15:14> or PMCS2 and PMCS1⁽¹⁾

0 = PMA15 and PMA14 function as port I/Os

bit 13-2 PTEN<13:2>: PMP Address Port Enable bits

1 = PMA<13:2> function as PMP address lines

0 = PMA<13:2> function as port I/Os

bit 1-0 PTEN<1:0>: PMALH/PMALL Strobe Enable bits

1 = PMA1 and PMA0 function as either PMA<1:0> or PMALH and PMALL(2)

0 = PMA1 and PMA0 pads function as port I/Os

Note 1: The use of these pins as address or Chip Select lines is selected by the CSF<1:0> bits (PMCON<7:6>).

2: The use of these pins as PMA1/PMA0 or PMALH/PMALL depends on the Address/Data Multiplex mode selected by the ADRMUX<1:0> bits in the PMCON register.

REGISTER 19-10: PMSTAT: PARALLEL MASTER PORT STATUS REGISTER (SLAVE MODES ONLY)

R-0	R/W-0	U-0	U-0	R-0	R-0	R-0	R-0
IBF	IBOV	_	_	IB3F	IB2F	IB1F	IB0F
bit 15							bit 8

R-1	R/W-0	U-0	U-0	R-1	R-1	R-1	R-1
OBE	OBUF	_	_	OB3E	OB2E	OB1E	OB0E
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 IBF: Input Buffer Full Status bit

1 = All writable Input Buffer registers are full

0 = Some or all of the writable Input Buffer registers are empty

bit 14 IBOV: Input Buffer Overflow Status bit

1 = A write attempt to a full input byte buffer occurred (must be cleared in software)

0 = No overflow occurred

This bit is set (= 1) in hardware; it can only be cleared (= 0) in software.

bit 13-12 Unimplemented: Read as '0'

bit 11-8 **IB<3:0>F:** Input Buffer x Status Full bits

1 = Input buffer contains data that has not been read (reading buffer will clear this bit)

0 = Input buffer does not contain any unread data

bit 7 **OBE:** Output Buffer Empty Status bit

1 = All readable Output Buffer registers are empty

0 = Some or all of the readable Output Buffer registers are full

bit 6 **OBUF:** Output Buffer Underflow Status bit

1 = A read occurred from an empty output byte buffer (must be cleared in software)

0 = No underflow occurred

This bit is set (= 1) in hardware; it can only be cleared (= 0) in software.

bit 5-4 **Unimplemented:** Read as '0'

bit 3-0 **OB<3:0>E:** Output Buffer x Status Empty bits

1 = Output buffer is empty (writing data to the buffer will clear this bit)

0 = Output buffer contains data that has not been transmitted

REGISTER 19-11: PMWADDR: PARALLEL MASTER PORT WRITE ADDRESS REGISTER(2)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
WCS2 ⁽¹⁾	WCS1 ⁽¹⁾			WADD	ND < 12:0 \					
WADDR15 ⁽¹⁾	WADDR14 ⁽¹⁾		WADDR<13:8>							
bit 15							bit 8			

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
WADDR<7:0>										
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 WCS2: Chip Select 2 bit⁽¹⁾

1 = Chip Select 2 is active

0 = Chip Select 2 is inactive (WADDR15 function is selected)

bit 15 **WADDR15**: Target Write Address bit 15⁽¹⁾

bit 14 WCS1: Chip Select 1 bit⁽¹⁾

1 = Chip Select 1 is active

0 = Chip Select 1 is inactive (WADDR14 function is selected)

bit 14 **WADDR14:** Target Write Address bit 14⁽¹⁾

bit 13-0 WADDR<13:0>: Target Write Address bits

Note 1: The use of these pins as PMA15/PMA14 or WCS2/WCS1 is selected by the CSF<1:0> bits

(PMCON<7:6>).

2: This register is only used when the DUALBUF bit (PMCONH<1>) is set to '1'.

REGISTER 19-12: PMRADDR: PARALLEL MASTER PORT READ ADDRESS REGISTER(2)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
RCS2 ⁽¹⁾	RCS1 ⁽¹⁾			DADD	D < 12 · 0 >				
RADDR15 ⁽¹⁾	RADDR14 ⁽¹⁾		RADDR<13:8>						
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
RADDR<7:0>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 RCS2: Chip Select 2 bit⁽¹⁾

1 = Chip Select 2 is active

0 = Chip Select 2 is inactive (RADDR15 function is selected)

bit 15 RADDR15: Target Read Address bit 15⁽¹⁾

bit 14 RCS1: Chip Select 1 bit⁽¹⁾

1 = Chip Select 1 is active

0 = Chip Select 1 is inactive (RADDR14 function is selected)

bit 14 RADDR14: Target Read Address bit 14⁽¹⁾

bit 13-0 RADDR<13:0>: Target Read Address bits

Note 1: The use of these pins as PMA15/PMA14 or RCS2/RCS1 is selected by the CSF<1:0> bits (PMCON<7:6>).

2: This register is only used when the DUALBUF bit (PMCONH<1>) is set to '1'.

REGISTER 19-13: PMRDIN: PARALLEL MASTER PORT READ INPUT DATA REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
RDATAIN<15:8> ⁽²⁾								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
RDATAIN<7:0> ⁽²⁾									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 RDATAIN<15:0>: Port Read Input Data bits⁽²⁾

Note 1: This register is only used when the DUALBUF bit (PMCONH<1>) is set to '1' and exclusively for reads. If the DUALBUF bit is '0', the PMDIN1 register (Register 19-7) is used for reads instead of PMRDIN.

2: Only used when MODE16 = 1.

20.0 SINGLE-EDGE NIBBLE TRANSMISSION (SENT)

Note 1: This data sheet summarizes the features of this group of dsPIC33CK256MP508 family devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Single-Edge Nibble Transmission (SENT) Module" (www.microchip.com/DS70005145) in the "dsPIC33/PIC24 Family Reference Manual".

The Single-Edge Nibble Transmission (SENT) module is based on the SAE J2716, "SENT – Single-Edge Nibble Transmission for Automotive Applications". The SENT protocol is a one-way, single wire time modulated serial communication, based on successive falling edges. It is intended for use in applications where high-resolution sensor data needs to be communicated from a sensor to an Engine Control Unit (ECU).

The SENTx module has the following major features:

- · Selectable Transmit or Receive mode
- Synchronous or Asynchronous Transmit modes
- · Automatic Data Rate Synchronization
- Optional Automatic Detection of CRC Errors in Receive mode
- Optional Hardware Calculation of CRC in Transmit mode
- · Support for Optional Pause Pulse Period
- · Data Buffering for One Message Frame
- Selectable Data Length for Transmit/Receive from Three to Six Nibbles
- · Automatic Detection of Framing Errors

SENT protocol timing is based on a predetermined time unit, TTICK. Both the transmitter and receiver must be preconfigured for TTICK, which can vary from 3 to 90 µs. A SENT message frame starts with a Sync pulse. The purpose of the Sync pulse is to allow the receiver to calculate the data rate of the message encoded by the transmitter. The SENT specification allows messages to be validated with up to a 20% variation in TTICK. This allows for the transmitter and receiver to run from different clocks that may be inaccurate, and drift with time and temperature. The data nibbles are 4 bits in length and are encoded as the data value + 12 ticks. This yields a 0 value of 12 ticks and the maximum value, 0xF, of 27 ticks.

A SENT message consists of the following:

- A synchronization/calibration period of 56 tick times
- · A status nibble of 12-27 tick times
- Up to six data nibbles of 12-27 tick times
- · A CRC nibble of 12-27 tick times
- An optional pause pulse period of 12-768 tick times

Figure 20-1 shows a block diagram of the SENTx module.

Figure 20-2 shows the construction of a typical 6-nibble data frame, with the numbers representing the minimum or maximum number of tick times for each section.







FIGURE 20-2: SENTX PROTOCOL DATA FRAMES



20.1 Transmit Mode

By default, the SENTx module is configured for transmit operation. The module can be configured for continuous asynchronous message frame transmission, or alternatively, for Synchronous mode triggered by software. When enabled, the transmitter will send a Sync, followed by the appropriate number of data nibbles, an optional CRC and optional pause pulse. The tick period used by the SENTx transmitter is set by writing a value to the TICKTIME<15:0> (SENTxCON2<15:0>) bits. The tick period calculations are shown in Equation 20-1.

EQUATION 20-1: TICK PERIOD CALCULATION

$$TICKTIME < 15:0 > = \frac{TTICK}{TCLK} - 1$$

An optional pause pulse can be used in Asynchronous mode to provide a fixed message frame time period. The frame period used by the SENTx transmitter is set by writing a value to the FRAMETIME<15:0> (SENTxCON3<15:0>) bits. The formulas used to calculate the value of frame time are shown in Equation 20-2.

EQUATION 20-2: FRAME TIME CALCULATIONS

FRAMETIME < 15:0 > = TTICK/TFRAME $FRAMETIME < 15:0 > \ge 122 + 27N$ $FRAMETIME < 15:0 > \ge 848 + 12N$

Where:

TFRAME = Total time of the message from ms N = The number of data nibbles in message, 1-6

Note: The module will not produce a pause period with less than 12 ticks, regard-less of the FRAMETIME<15:0> value. FRAMETIME<15:0> values beyond 2047 will have no effect on the length of a data frame.

20.1.1 TRANSMIT MODE CONFIGURATION

20.1.1.1 Initializing the SENTx Module

Perform the following steps to initialize the module:

- Write RCVEN (SENTxCON1<11>) = 0 for Transmit mode.
- Write TXM (SENTxCON1<10>) = 0 for Asynchronous Transmit mode or TXM = 1 for Synchronous mode.
- Write NIBCNT<2:0> (SENTxCON1<2:0>) for the desired data frame length.
- Write CRCEN (SENTxCON1<8>) for hardware or software CRC calculation.
- 5. Write PPP (SENTxCON1<7>) for optional pause pulse.
- 6. If PPP = 1, write TFRAME to SENTxCON3.
- 7. Write SENTxCON2 with the appropriate value for the desired tick period.
- 8. Enable interrupts and set interrupt priority.
- Write initial status and data values to SENTxDATH/L.
- 10. If CRCEN = 0, calculate CRC and write the value to CRC<3:0> (SENTxDATL<3:0>).
- 11. Set the SNTEN (SENTxCON1<15>) bit to enable the module.

User software updates to SENTxDATH/L must be performed after the completion of the CRC and before the next message frame's status nibble. The recommended method is to use the message frame completion interrupt to trigger data writes.

20.2 Receive Mode

The module can be configured for receive operation by setting the RCVEN (SENTxCON1<11>) bit. The time between each falling edge is compared to SYNCMIN<15:0> (SENTxCON3<15:0>) and SYNCMAX<15:0> (SENTxCON2<15:0>), and if the measured time lies between the minimum and maximum limits, the module begins to receive data. The validated Sync time is captured in the SENTxSYNC register and the tick time is calculated. Subsequent falling edges are verified to be within the valid data width and the data is stored in the SENTxDATL/H registers. An interrupt event is generated at the completion of the message and the user software should read the SENTx Data registers before the reception of the next nibble. The equation for SYNCMIN<15:0> and SYNCMAX<15:0> is shown in Equation 20-3.

EQUATION 20-3: SYNCMIN<15:0> AND SYNCMAX<15:0> CALCULATIONS

 $TTICK = TCLK \bullet (TICKTIME < 15:0 > + 1)$ FRAMETIME < 15:0 > = TTICK/TFRAME $SyncCount = 8 \times FRCV \times TTICK$ $SYNCMIN < 15:0 > = 0.8 \times SyncCount$ $SYNCMAX < 15:0 > = 1.2 \times SyncCount$ $FRAMETIME < 15:0 > \geq 122 + 27N$ $FRAMETIME < 15:0 > \geq 848 + 12N$

Where:

TFRAME = Total time of the message from ms N = The number of data nibbles in message, 1-6 FRCV = FCY x Prescaler TCLK = FCY/Prescaler

For TTICK = 3.0 μs and FCLK = 4 MHz, SYNCMIN<15:0> = 76.

Note: To ensu

To ensure a Sync period can be identified, the value written to SYNCMIN<15:0> must be less than the value written to SYNCMAX<15:0>.

20.2.1 RECEIVE MODE CONFIGURATION

20.2.1.1 Initializing the SENTx Module

Perform the following steps to initialize the module:

- Write RCVEN (SENTxCON1<11>) = 1 for Receive mode.
- Write NIBCNT<2:0> (SENTxCON1<2:0>) for the desired data frame length.
- 3. Write CRCEN (SENTxCON1<8>) for hardware or software CRC validation.
- 4. Write PPP (SENTxCON1<7>) = 1 if pause pulse is present.
- 5. Write SENTxCON2 with the value of SYNCMAXx (Nominal Sync Period + 20%).
- 6. Write SENTxCON3 with the value of SYNCMINx (Nominal Sync Period 20%).
- 7. Enable interrupts and set interrupt priority.
- 8. Set the SNTEN (SENTxCON1<15>) bit to enable the module.

The data should be read from the SENTxDATL/H registers after the completion of the CRC and before the next message frame's status nibble. The recommended method is to use the message frame completion interrupt trigger.

20.3 Control Registers

REGISTER 20-1: SENTxCON1: SENTx CONTROL REGISTER 1

R/W-0	U-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
SNTEN	_	SNTSIDL	_	RCVEN	TXM ⁽¹⁾	TXPOL ⁽¹⁾	CRCEN
bit 15		•					bit 8

R/W-0	R/W-0	U-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
PPP	SPCEN ⁽²⁾	_	PS	_	NIBCNT2	NIBCNT1	NIBCNT0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 SNTEN: SENTx Enable bit

1 = SENTx is enabled

0 = SENTx is disabled

bit 14 **Unimplemented:** Read as '0'

bit 13 SNTSIDL: SENTx Stop in Idle Mode bit

1 = Discontinues module operation when the device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 **Unimplemented:** Read as '0'

bit 11 RCVEN: SENTx Receive Enable bit

1 = SENTx operates as a receiver

0 = SENTx operates as a transmitter (sensor)

bit 10 **TXM:** SENTx Transmit Mode bit⁽¹⁾

1 = SENTx transmits data frame only when triggered using the SYNCTXEN status bit

0 = SENTx transmits data frames continuously while SNTEN = 1

bit 9 **TXPOL:** SENTx Transmit Polarity bit⁽¹⁾

1 = SENTx data output pin is low in the Idle state

0 = SENTx data output pin is high in the Idle state

bit 8 CRCEN: CRC Enable bit

Module in Receive Mode (RCVEN = 1):

1 = SENTx performs CRC verification on received data using the preferred J2716 method

0 = SENTx does not perform CRC verification on received data

Module in Transmit Mode (RCVEN = 1):

1 = SENTx automatically calculates CRC using the preferred J2716 method

0 = SENTx does not calculate CRC

bit 7 PPP: Pause Pulse Present bit

1 = SENTx is configured to transmit/receive SENT messages with pause pulse

0 = SENTx is configured to transmit/receive SENT messages without pause pulse

bit 6 SPCEN: Short PWM Code Enable bit⁽²⁾

1 = SPC control from external source is enabled

0 = SPC control from external source is disabled

bit 5 **Unimplemented:** Read as '0'

Note 1: This bit has no function in Receive mode (RCVEN = 1).

2: This bit has no function in Transmit mode (RCVEN = 0).

REGISTER 20-1: SENTxCON1: SENTx CONTROL REGISTER 1 (CONTINUED)

bit 4 PS: SENTx Module Clock Prescaler (divider) bits

1 = Divide-by-4
0 = Divide-by-1

bit 3 **Unimplemented:** Read as '0'

bit 2-0 NIBCNT<2:0>: Nibble Count Control bits

111 = Reserved; do not use

110 = Module transmits/receives six data nibbles in a SENT data pocket 101 = Module transmits/receives five data nibbles in a SENT data pocket 100 = Module transmits/receives four data nibbles in a SENT data pocket 011 = Module transmits/receives three data nibbles in a SENT data pocket 010 = Module transmits/receives two data nibbles in a SENT data pocket 001 = Module transmits/receives one data nibble in a SENT data pocket

000 = Reserved; do not use

Note 1: This bit has no function in Receive mode (RCVEN = 1).

2: This bit has no function in Transmit mode (RCVEN = 0).

REGISTER 20-2: SENTXSTAT: SENTX STATUS REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R-0	R-0	R-0	R-0	R/C-0	R/C-0	R-0	HC/R/W-0
PAUSE	NIB2	NIB1	NIB0	CRCERR	FRMERR	RXIDLE	SYNCTXEN ⁽¹⁾
bit 7							bit 0

Legend:	C = Clearable bit	HC = Hardware Clearal	ble bit
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7 PAUSE: Pause Period Status bit

1 = The module is transmitting/receiving a pause period

0 = The module is not transmitting/receiving a pause period

bit 6-4 NIB<2:0>: Nibble Status bits

Module in Transmit Mode (RCVEN = 0):

111 = Module is transmitting a CRC nibble

110 = Module is transmitting Data Nibble 6

101 = Module is transmitting Data Nibble 5

100 = Module is transmitting Data Nibble 4

011 = Module is transmitting Data Nibble 3

010 = Module is transmitting Data Nibble 2

001 = Module is transmitting Data Nibble 1

000 = Module is transmitting a status nibble or pause period, or is not transmitting

Module in Receive Mode (RCVEN = 1):

111 = Module is receiving a CRC nibble or was receiving this nibble when an error occurred

110 = Module is receiving Data Nibble 6 or was receiving this nibble when an error occurred

101 = Module is receiving Data Nibble 5 or was receiving this nibble when an error occurred

100 = Module is receiving Data Nibble 4 or was receiving this nibble when an error occurred

011 = Module is receiving Data Nibble 3 or was receiving this nibble when an error occurred

010 = Module is receiving Data Nibble 2 or was receiving this nibble when an error occurred

001 = Module is receiving Data Nibble 1 or was receiving this nibble when an error occurred

000 = Module is receiving a status nibble or waiting for Sync

bit 3 CRCERR: CRC Status bit (Receive mode only)

1 = A CRC error has occurred for the 1-6 data nibbles in SENTxDATL/H

0 = A CRC error has not occurred

bit 2 FRMERR: Framing Error Status bit (Receive mode only)

1 = A data nibble was received with less than 12 tick periods or greater than 27 tick periods

0 = Framing error has not occurred

bit 1 RXIDLE: SENTx Receiver Idle Status bit (Receive mode only)

1 = The SENTx data bus has been Idle (high) for a period of SYNCMAX<15:0> or greater

0 = The SENTx data bus is not Idle

Note 1: In Receive mode (RCVEN = 1), the SYNCTXEN bit is read-only.

REGISTER 20-2: SENTxSTAT: SENTx STATUS REGISTER (CONTINUED)

bit 0 SYNCTXEN: SENTx Synchronization Period Status/Transmit Enable bit⁽¹⁾

Module in Receive Mode (RCVEN = 1):

- 1 = A valid synchronization period was detected; the module is receiving nibble data
- 0 = No synchronization period has been detected; the module is not receiving nibble data

Module in Asynchronous Transmit Mode (RCVEN = 0, TXM = 0):

The bit always reads as '1' when the module is enabled, indicating the module transmits SENTx data frames continuously. The bit reads '0' when the module is disabled.

Module in Synchronous Transmit Mode (RCVEN = 0, TXM = 1):

- 1 = The module is transmitting a SENTx data frame
- 0 = The module is not transmitting a data frame, user software may set SYNCTXEN to start another data frame transmission

Note 1: In Receive mode (RCVEN = 1), the SYNCTXEN bit is read-only.

REGISTER 20-3: SENTxDATL: SENTx RECEIVE DATA REGISTER LOW(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
	DATA4	<3:0>		DATA5<3:0>				
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
	DATA6	<3:0>		CRC<3:0>				
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 DATA4<3:0>: Data Nibble 4 Data bits
bit 11-8 DATA5<3:0>: Data Nibble 5 Data bits
bit 7-4 DATA6<3:0>: Data Nibble 6 Data bits
bit 3-0 CRC<3:0>: CRC Nibble Data bits

Note 1: Register bits are read-only in Receive mode (RCVEN = 1). In Transmit mode, the CRC<3:0> bits are read-only when automatic CRC calculation is enabled (RCVEN = 0, CRCEN = 1).

REGISTER 20-4: SENTxDATH: SENTx RECEIVE DATA REGISTER HIGH⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
	STAT<	<3:0>		DATA1<3:0>				
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
	DATA2	<3:0>		DATA3<3:0>				
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 STAT<3:0>: Status Nibble Data bits
bit 11-8 DATA1<3:0>: Data Nibble 1 Data bits
bit 7-4 DATA2<3:0>: Data Nibble 2 Data bits
bit 3-0 DATA3<3:0>: Data Nibble 3 Data bits

Note 1: Register bits are read-only in Receive mode (RCVEN = 1). In Transmit mode, the CRC<3:0> bits are read-only when automatic CRC calculation is enabled (RCVEN = 0, CRCEN = 1).

NOTES:			
10120.			

21.0 TIMER1

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Timers" (www.microchip.com/DS70362) in the "dsPIC33/PIC24 Family Reference Manual".

The Timer1 module is a 16-bit timer that can operate as a free-running interval timer/counter.

The Timer1 module has the following unique features over other timers:

- · Can be Operated in Asynchronous Counter mode
- · Asynchronous Timer
- · Operational during CPU Sleep mode
- Software Selectable Prescalers 1:1, 1:8, 1:64 and 1:256
- · External Clock Selection Control
- The Timer1 External Clock Input (T1CK) can
 Optionally be Synchronized to the Internal Device
 Clock and the Clock Synchronization is Performed
 after the Prescaler


If Timer1 is used for SCCP, the timer should be running in Synchronous mode.

The Timer1 module can operate in one of the following modes:

- · Timer mode
- · Gated Timer mode
- · Synchronous Counter mode
- Asynchronous Counter mode

A block diagram of Timer1 is shown in Figure 21-1.

FIGURE 21-1: 16-BIT TIMER1 MODULE BLOCK DIAGRAM



21.1 Timer1 Control Register

REGISTER 21-1: T1CON: TIMER1 CONTROL REGISTER

R/W-0	U-0	R/W-0	R/W-0	R-0	R-0	R/W-0	R/W-0
TON ⁽¹⁾	_	SIDL	TMWDIS	TMWIP	PRWIP	TECS1	TECS0
bit 15							bit 8

R/W-0	U-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	U-0
TGATE	_	TCKPS1	TCKPS0	_	TSYNC ⁽¹⁾	TCS ⁽¹⁾	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **TON:** Timer1 On bit⁽¹⁾

1 = Starts 16-bit Timer1
0 = Stops 16-bit Timer1

bit 14 Unimplemented: Read as '0'

bit 13 SIDL: Timer1 Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 TMWDIS: Asynchronous Timer1 Write Disable bit

1 = Timer writes are ignored while a posted write to TMR1 or PR1 is synchronized to the asynchronous clock domain

0 = Back-to-back writes are enabled in Asynchronous mode

bit 11 TMWIP: Asynchronous Timer1 Write in Progress bit

 $\ensuremath{\mathtt{1}}$ = Write to the timer in Asynchronous mode is pending

0 = Write to the timer in Asynchronous mode is complete

bit 10 **PRWIP:** Asynchronous Period Write in Progress bit

1 = Write to the Period register in Asynchronous mode is pending

0 = Write to the Period register in Asynchronous mode is complete

bit 9-8 TECS<1:0>: Timer1 Extended Clock Select bits

11 = FRC clock

10 = Fosc

01 = Tcy

00 = External Clock comes from the T1CK pin

bit 7 TGATE: Timer1 Gated Time Accumulation Enable bit

 $\frac{\text{When TCS} = 1:}{\text{This bit is ignored.}}$

M// TOO

When TCS = 0:

1 = Gated time accumulation is enabled

0 = Gated time accumulation is disabled

bit 6 Unimplemented: Read as '0'

Note 1: When Timer1 is enabled in External Synchronous Counter mode (TCS = 1, TSYNC = 1, TON = 1), any attempts by user software to write to the TMR1 register are ignored.

REGISTER 21-1: T1CON: TIMER1 CONTROL REGISTER (CONTINUED)

bit 5-4

TCKPS<1:0>: Timer1 Input Clock Prescale Select bits

11 = 1:256

10 = 1:64

01 = 1:8

00 = 1:1

bit 3

Unimplemented: Read as '0'

TSYNC: Timer1 External Clock Input Synchronization Select bit (1)

When TCS = 1:

1 = Synchronizes the External Clock input

When TCS = 0: This bit is ignored.

bit 1 TCS: Timer1 Clock Source Select bit⁽¹⁾

1 = External Clock source selected by TECS<1:0>

0 = Does not synchronize the External Clock input

0 = Internal peripheral clock (FP)

bit 0 **Unimplemented:** Read as '0'

Note 1: When Timer1 is enabled in External Synchronous Counter mode (TCS = 1, TSYNC = 1, TON = 1), any attempts by user software to write to the TMR1 register are ignored.

<u> </u>			
NOTES:			

22.0 CAPTURE/COMPARE/PWM/ TIMER MODULES (SCCP/MCCP)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. For more information on the MCCP/SCCP modules, refer to "Capture/Compare/PWM/Timer (MCCP and SCCP)" (www.microchip.com/DS33035) in the "dsPIC33/PIC24 Family Reference Manual".

dsPIC33CK256MP508 family devices include eight SCCP and one MCCP Capture/Compare/PWM/Timer base modules, which provide the functionality of three different peripherals from earlier PIC24F devices. The module can operate in one of three major modes:

- · General Purpose Timer
- · Input Capture
- · Output Compare/PWM

The module is provided in two different forms, distinguished by the number of PWM outputs that the module can generate. Single Capture/Compare/PWM (SCCP) output modules provide only one PWM output.

Multiple Capture/Compare/PWM (MCCP) output modules can provide up to six outputs and an extended range of power control features, depending on the pin count of the particular device. All other features of the modules are identical.

The SCCPx and MCCPx modules can be operated in only one of the three major modes at any time. The other modes are not available unless the module is reconfigured for the new mode.

A conceptual block diagram for the module is shown in Figure 22-1. All three modes share a time base generator and a common Timer register pair (CCPxTMRH/L); other shared hardware components are added as a particular mode requires.

Each module has a total of six control and status registers:

- CCPxCON1L (Register 22-1)
- CCPxCON1H (Register 22-2)
- CCPxCON2L (Register 22-3)
- CCPxCON2H (Register 22-4)
- CCPxCON3H (Register 22-6)
- CCPxSTATL (Register 22-7)

Each module also includes eight buffer/counter registers that serve as Timer Value registers or data holding buffers:

- CCPxTMRH/CCPxTMRL (CCPx Timer High/Low Counters)
- CCPxPRH/CCPxPRL (CCPx Timer Period High/Low)
- CCPxRA (CCPx Primary Output Compare Data Buffer)
- CCPxRB (CCPx Secondary Output Compare Data Buffer)
- CCPxBUFH/CCPxBUFL (CCPx Input Capture High/Low Buffers)





FIGURE 22-1: SCCPx CONCEPTUAL BLOCK DIAGRAM

22.1 Time Base Generator

The Timer Clock Generator (TCG) generates a clock for the module's internal time base, using one of the clock signals already available on the microcontroller. This is used as the time reference for the module in its three major modes. The internal time base is shown in Figure 22-2.

There are eight inputs available to the clock generator, which are selected using the CLKSEL<2:0> bits (CCPxCON1L<10:8>). Available sources include the FRC and LPRC, the Secondary Oscillator and the TCLKI External Clock inputs. The system clock is the default source (CLKSEL<2:0> = 000).

FIGURE 22-2: TIMER CLOCK GENERATOR



22.2 General Purpose Timer

Timer mode is selected when CCSEL = 0 and MOD<3:0> = 0000. The timer can function as a 32-bit timer or a dual 16-bit timer, depending on the setting of the T32 bit (Table 22-1).

TABLE 22-1: TIMER OPERATION MODE

T32 (CCPxCON1L<5>)	Operating Mode			
0	Dual Timer Mode (16-bit)			
1	Timer Mode (32-bit)			

Dual 16-Bit Timer mode provides a simple timer function with two independent 16-bit timer/counters. The primary timer uses CCPxTMRL and CCPxPRL. Only the primary timer can interact with other modules on the device. It generates the SCCPx sync out signals for use by other SCCP modules. It can also use the SYNC<4:0> bits signal generated by other modules.

The secondary timer uses CCPxTMRH and CCPxPRH. It is intended to be used only as a periodic interrupt source for scheduling CPU events. It does not generate an output sync/trigger signal like the primary time base. In Dual Timer mode, the CCPx Secondary Timer Period register, CCPxPRH, generates the SCCP compare event (CCPxIF) used by many other modules on the device.

The 32-Bit Timer mode uses the CCPxTMRL and CCPxTMRH registers, together, as a single 32-bit timer. When CCPxTMRL overflows, CCPxTMRH increments by one. This mode provides a simple timer function when it is important to track long time periods. Note that

the T32 bit (CCPxCON1L<5>) should be set before the CCPxTMRL or CCPxPRH registers are written to initialize the 32-bit timer.

22.2.1 SYNC AND TRIGGER OPERATION

In both 16-bit and 32-bit modes, the timer can also function in either synchronization ("sync") or trigger operation. Both use the SYNC<4:0> bits (CCPxCON1H<4:0>) to determine the input signal source. The difference is how that signal affects the timer.

In sync operation, the timer Reset or clear occurs when the input selected by SYNC<4:0> is asserted. The timer immediately begins to count again from zero unless it is held for some other reason. Sync operation is used whenever the TRIGEN bit (CCPxCON1H<7>) is cleared. SYNC<4:0> can have any value, except '11111'.

In trigger operation, the timer is held in Reset until the input selected by SYNC<4:0> is asserted; when it occurs, the timer starts counting. Trigger operation is used whenever the TRIGEN bit is set. In Trigger mode, the timer will continue running after a trigger event as long as the CCPTRIG bit (CCPxSTATL<7>) is set. To clear CCPTRIG, the TRCLR bit (CCPxSTATL<5>) must be set to clear the trigger event, reset the timer and hold it at zero until another trigger event occurs. On dsPIC33CK256MP508 family devices, trigger operation can only be used when the system clock is the time base source (CLKSEL<2:0> = 000).

22.3 Output Compare Mode

Output Compare mode compares the Timer register value with the value of one or two Compare registers, depending on its mode of operation. The Output Compare x module, on compare match events, has the ability to generate a single output transition or a train of

output pulses. Like most PIC[®] MCU peripherals, the Output Compare x module can also generate interrupts on a compare match event.

Table 22-2 shows the various modes available in Output Compare modes.

TABLE 22-2: OUTPUT COMPARE x/PWMx MODES

MOD<3:0> (CCPxCON1L<3:0>)	T32 (CCPxCON1L<5>)	Operating Mode			
0001	0	Output High on Compare (16-bit)			
0001	1	Output High on Compare (32-bit)			
0010	0	Output Low on Compare (16-bit)	Cingle Edge Mede		
0010	1	Output Low on Compare (32-bit)	Single Edge Mode		
0011	0	Output Toggle on Compare (16-bit)			
0011	1	Output Toggle on Compare (32-bit)			
0100	0	Dual Edge Compare (16-bit)	Dual Edge Mode		
0101	0	Dual Edge Compare (16-bit buffered)	PWM Mode		

22.4 Input Capture Mode

Input Capture mode is used to capture a timer value from an independent timer base, upon an event, on an input pin or other internal trigger source. The input capture features are useful in applications requiring frequency (time period) and pulse measurement.

Input Capture mode uses a dedicated 16/32-bit, synchronous, up counting timer for the capture function. The timer value is written to the FIFO when a capture event occurs. The internal value may be read (with a synchronization delay) using the CCPxTMRH/L register.

To use Input Capture mode, the CCSEL bit (CCPxCON1L<4>) must be set. The T32 and the MOD<3:0> bits are used to select the proper Capture mode, as shown in Table 22-3.

TABLE 22-3: INPUT CAPTURE x MODES

MOD<3:0> (CCPxCON1L<3:0>)	T32 (CCPxCON1L<5>)	Operating Mode		
0000	0	Edge Detect (16-bit capture)		
0000	1	Edge Detect (32-bit capture)		
0001	0	Every Rising (16-bit capture)		
0001	1	Every Rising (32-bit capture)		
0010	0	Every Falling (16-bit capture)		
0010	1	Every Falling (32-bit capture)		
0011	0	Every Rising/Falling (16-bit capture)		
0011	1	Every Rising/Falling (32-bit capture)		
0100	0	Every 4th Rising (16-bit capture)		
0100	1	Every 4th Rising (32-bit capture)		
0101	0	Every 16th Rising (16-bit capture)		
0101	1	Every 16th Rising (32-bit capture)		

22.5 Auxiliary Output

The SCCPx modules have an auxiliary (secondary) output that provides other peripherals access to internal module signals. The auxiliary output is intended to connect to other SCCP modules, or other digital peripherals, to provide these types of functions:

- · Time Base Synchronization
- Peripheral Trigger and Clock Inputs
- · Signal Gating

AUXOUT<1:0> control bits (CCPxCON2H<4:3>). The type of output signal is also dependent on the module operating mode.

The type of output signal is selected using the

TABLE 22-4: AUXILIARY OUTPUT

AUXOUT<1:0>	CCSEL	MOD<3:0>	Comments	Signal Description
00	Х	XXXX	Auxiliary output disabled	No Output
01	0	0000	Time Base modes	Time Base Period Reset or Rollover
10				Special Event Trigger Output
11				No Output
01	0	0001	Output Compare modes	Time Base Period Reset or Rollover
10		through		Output Compare Event Signal
11		1111		Output Compare Signal
01	1	xxxx	Input Capture modes	Time Base Period Reset or Rollover
10				Reflects the Value of the ICDIS bit
11				Input Capture Event Signal

22.6 Control Registers

REGISTER 22-1: CCPxCON1L: CCPx CONTROL 1 LOW REGISTERS

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CCPON	_	CCPSIDL	CCPSLP	TMRSYNC	CLKSEL2	CLKSEL1	CLKSEL0
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TMRPS1	TMRPS0	T32	CCSEL	MOD3	MOD2	MOD1	MOD0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 CCPON: CCPx Module Enable bit

1 = Module is enabled with an operating mode specified by the MOD<3:0> control bits

0 = Module is disabled

bit 14 **Unimplemented:** Read as '0'

bit 13 CCPSIDL: CCPx Stop in Idle Mode Bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12 CCPSLP: CCPx Sleep Mode Enable bit

1 = Module continues to operate in Sleep modes

0 = Module does not operate in Sleep modes

bit 11 TMRSYNC: Time Base Clock Synchronization bit

1 = Asynchronous module time base clock is selected and synchronized to the internal system clocks (CLKSEL<2:0> ≠ 000)

0 = Synchronous module time base clock is selected and does not require synchronization (CLKSEL<2:0> = 000)

bit 10-8 CLKSEL<2:0>: CCPx Time Base Clock Select bits

111 = PPS TxCK input

110 **= CLC4**

101 **= CLC3**

100 **= CLC2**

011 = CLC1

010 **= Fosc**

001 = Reference Clock (REFCLKO)

000 = Fosc/2 (FP)

bit 7-6 TMRPS<1:0>: Time Base Prescale Select bits

11 = 1:64 Prescaler

10 = 1:16 Prescaler

01 = 1:4 Prescaler

00 = 1:1 Prescaler

bit 5 T32: 32-Bit Time Base Select bit

1 = Uses 32-bit time base for timer, single edge output compare or input capture function

0 = Uses 16-bit time base for timer, single edge output compare or input capture function

bit 4 CCSEL: Capture/Compare Mode Select bit

1 = Input Capture peripheral

0 = Output Compare/PWM/Timer peripheral (exact function is selected by the MOD<3:0> bits)

REGISTER 22-1: CCPxCON1L: CCPx CONTROL 1 LOW REGISTERS (CONTINUED)

bit 3-0 MOD<3:0>: CCPx Mode Select bits

For CCSEL = 1 (Input Capture modes):

1xxx = Reserved

011x = Reserved

0101 = Capture every 16th rising edge

0100 = Capture every 4th rising edge

0011 = Capture every rising and falling edge

0010 = Capture every falling edge

0001 = Capture every rising edge

0000 = Capture every rising and falling edge (Edge Detect mode)

For CCSEL = 0 (Output Compare/Timer modes):

1111 = External Input mode: Pulse generator is disabled, source is selected by ICS<2:0>

1110 = Reserved

110x = Reserved

10xx = Reserved

0111 = Reserved

0110 = Reserved

0101 = Dual Edge Compare mode, buffered

0100 = Dual Edge Compare mode

0011 = 16-Bit/32-Bit Single Edge mode, toggles output on compare match

0010 = 16-Bit/32-Bit Single Edge mode, drives output low on compare match

0001 = 16-Bit/32-Bit Single Edge mode, drives output high on compare match

0000 = 16-Bit/32-Bit Timer mode, output functions are disabled

REGISTER 22-2: CCPxCON1H: CCPx CONTROL 1 HIGH REGISTERS

R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
OPSSRC ⁽¹⁾	RTRGEN ⁽²⁾	_	_	OPS3 ⁽³⁾	OPS2 ⁽³⁾	OPS1 ⁽³⁾	OPS0 ⁽³⁾
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
TRIGEN	ONESHOT	ALTSYNC	SYNC4	SYNC3	SYNC2	SYNC1	SYNC0
bit 7							bit 0

Legend:					
R = Readable bit	Readable bit W = Writable bit U = Unimplemented bit, read as '0'				
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15 OPSSRC: Output Postscaler Source Select bit⁽¹⁾

1 = Output postscaler scales module trigger output events

0 = Output postscaler scales time base interrupt events

bit 14 RTRGEN: Retrigger Enable bit⁽²⁾

1 = Time base can be retriggered when TRIGEN bit = 1

0 = Time base may not be retriggered when TRIGEN bit = 1

bit 13-12 Unimplemented: Read as '0'

bit 11-8 **OPS3<3:0>:** CCPx Interrupt Output Postscale Select bits⁽³⁾

1111 = Interrupt every 16th time base period match

1110 = Interrupt every 15th time base period match

. . .

0100 = Interrupt every 5th time base period match

0011 = Interrupt every 4th time base period match or 4th input capture event

0010 = Interrupt every 3rd time base period match or 3rd input capture event

0001 = Interrupt every 2nd time base period match or 2nd input capture event

0000 = Interrupt after each time base period match or input capture event

bit 7 TRIGEN: CCPx Trigger Enable bit

1 = Trigger operation of time base is enabled

0 = Trigger operation of time base is disabled

bit 6 ONESHOT: One-Shot Trigger Mode Enable bit

1 = One-Shot Trigger mode is enabled; trigger duration is set by OSCNT<2:0>

0 = One-Shot Trigger mode is disabled

bit 5 ALTSYNC: CCPx Clock Select bits

1 = An alternate signal is used as the module synchronization output signal

0 = The module synchronization output signal is the Time Base Reset/rollover event

bit 4-0 **SYNC<4:0>:** CCPx Synchronization Source Select bits

See Table 22-5 for the definition of inputs.

Note 1: This control bit has no function in Input Capture modes.

2: This control bit has no function when TRIGEN = 0.

3: Output postscale settings, from 1:5 to 1:16 (0100-1111), will result in a FIFO buffer overflow for Input Capture modes.

TABLE 22-5: SYNCHRONIZATION SOURCES

SYNC<4:0>	Synchronization Source
00000	None; Timer with Rollover on CCPxPR Match or FFFFh
00001	Module's Own Timer Sync Out
00010	Sync Output SCCP2
00011	Sync Output SCCP3
00100	Sync Output SCCP4
00101	Sync Output SCCP5
00110	Sync Output SCCP6
00111	Sync Output SCCP7
01000	Sync Output SCCP8
01001	INT0
01010	INT1
01011	INT2
01100	UART1 RX Edge Detect
01101	UART1 TX Edge Detect
01110	UART2 RX Edge Detect
01111	UART2 TX Edge Detect
10000	CLC1 Output
10001	CLC2 Output
10010	CLC3 Output
10011	CLC4 Output
10100	UART3 RX Edge Detect
10101	UART3 TX Edge Detect
10110	Sync Output MCCP9
10111	Comparator 1 Output
11000	Comparator 2 Output
11001	Comparator 3 Output
11010-11110	Reserved
11111	None; Timer with Auto-Rollover (FFFFh → 0000h)

REGISTER 22-3: CCPxCON2L: CCPx CONTROL 2 LOW REGISTERS

R/W-0	R/W-0	U-0	R/W-0	U-0	U-0	U-0	U-0	
PWMRSEN	ASDGM	_	SSDG	_	_	_	_	
bit 15	bit 15 bit 8							

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| ASDG7 | ASDG6 | ASDG5 | ASDG4 | ASDG3 | ASDG2 | ASDG1 | ASDG0 |
| bit 7 | | | | | | | bit 0 |

Legend:					
R = Readable bit	= Readable bit W = Writable bit U = Unimplemented bit, read as '0'				
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 15 **PWMRSEN:** CCPx PWM Restart Enable bit

1 = ASEVT bit clears automatically at the beginning of the next PWM period, after the shutdown input has ended

0 = ASEVT bit must be cleared in software to resume PWM activity on output pins

bit 14 ASDGM: CCPx Auto-Shutdown Gate Mode Enable bit

1 = Waits until the next Time Base Reset or rollover for shutdown to occur

0 = Shutdown event occurs immediately

bit 13 **Unimplemented:** Read as '0'

bit 12 SSDG: CCPx Software Shutdown/Gate Control bit

1 = Manually forces auto-shutdown, timer clock gate or input capture signal gate event (setting of ASDGM bit still applies)

0 = Normal module operation

bit 11-8 **Unimplemented:** Read as '0'

bit 7-0 ASDG<7:0>: CCPx Auto-Shutdown/Gating Source Enable bits

1 = ASDGx Source n is enabled (see Table 22-6 for auto-shutdown/gating sources)

0 = ASDGx Source n is disabled

TABLE 22-6: AUTO-SHUTDOWN AND GATING SOURCES

ASDG <x></x>	Auto-Shutdown/Gating Source										
Bit	SCCP1	SCCP2	SCCP3	SCCP4	SCCP5	SCCP6	SCCP7	SCCP8	МССР9		
0		Comparator 1 Output									
1		Comparator 2 Output									
2	OCFC										
3					OCFD						
4	ICM1 ⁽¹⁾	ICM2 ⁽¹⁾	ICM3 ⁽¹⁾	ICM4 ⁽¹⁾	ICM5 ⁽¹⁾	ICM6 ⁽¹⁾	ICM7 ⁽¹⁾	ICM8 ⁽¹⁾	ICM9 ⁽¹⁾		
5		CLC1 ⁽¹⁾									
6		OCFA ⁽¹⁾									
7					OCFB ⁽¹⁾						

Note 1: Selected by Peripheral Pin Select (PPS).

REGISTER 22-4: CCPxCON2H: CCPx CONTROL 2 HIGH REGISTERS

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
OENSYNC	_	OCFEN ⁽¹⁾	OCEEN ⁽¹⁾	OCDEN ⁽¹⁾	OCCEN ⁽¹⁾	OCBEN ⁽¹⁾	OCAEN
bit 15							bit 8

R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ICGSM1	ICGSM0	_	AUXOUT1	AUXOUT0	ICS2	ICS1	ICS0
bit 7			•				bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 **OENSYNC:** Output Enable Synchronization bit

1 = Update by output enable bits occurs on the next Time Base Reset or rollover

0 = Update by output enable bits occurs immediately

bit 14 **Unimplemented:** Read as '0'

bit 13-8 OC<F:A>EN: Output Enable/Steering Control bits⁽¹⁾

1 = OCMx pin is controlled by the CCPx module and produces an output compare or PWM signal

0 = OCMx pin is not controlled by the CCPx module; the pin is available to the port logic or another peripheral multiplexed on the pin

bit 7-6 ICGSM<1:0>: Input Capture Gating Source Mode Control bits

11 = Reserved

10 = One-Shot mode: Falling edge from gating source disables future capture events (ICDIS = 1)

01 = One-Shot mode: Rising edge from gating source enables future capture events (ICDIS = 0)

00 = Level-Sensitive mode: A high level from gating source will enable future capture events; a low level will disable future capture events

bit 5 **Unimplemented:** Read as '0'

bit 4-3 **AUXOUT<1:0>:** Auxiliary Output Signal on Event Selection bits

11 = Input capture or output compare event; no signal in Timer mode

10 = Signal output is defined by module operating mode (see Table 22-4)

01 = Time base rollover event (all modes)

00 = Disabled

bit 2-0 ICS<2:0>: Input Capture Source Select bits

111 = CLC4 output

110 = CLC3 output

101 = CLC2 output

100 = CLC1 output

011 = Comparator 3 output

010 = Comparator 2 output

001 = Comparator 1 output

000 = SCCP Input Capture x (ICx) pin (PPS)

Note 1: OCFEN through OCBEN (bits<13:9>) are implemented in the MCCP9 module only.

REGISTER 22-5: CCPxCON3L: CCPx CONTROL 3 LOW REGISTERS⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
_	_		DT<5:0>						
bit 7		•					bit 0		

Legend:				
R = Readable bit	W = Writable bit U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 15-6 **Unimplemented:** Read as '0' bit 5-0 **DT<5:0>:** CCPx Dead-Time Select bits

111111 = Inserts 63 dead-time delay periods between complementary output signals

111110 = Inserts 62 dead-time delay periods between complementary output signals

. . .

000010 = Inserts 2 dead-time delay periods between complementary output signals 000001 = Inserts 1 dead-time delay period between complementary output signals

000000 = Dead-time logic is disabled

Note 1: This register is implemented in the MCCP9 module only.

REGISTER 22-6: CCPxCON3H: CCPx CONTROL 3 HIGH REGISTERS

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
OETRIG	OSCNT2	OSCNT1	OSCNT0	_	OUTM2 ⁽¹⁾	OUTM1 ⁽¹⁾	OUTM0 ⁽¹⁾
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	POLACE	POLBDF ⁽¹⁾	PSSACE1	PSSACE0	PSSBDF1 ⁽¹⁾	PSSBDF0 ⁽¹⁾
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 OETRIG: CCPx Dead-Time Select bit

1 = For Triggered mode (TRIGEN = 1): Module does not drive enabled output pins until triggered

0 = Normal output pin operation

bit 14-12 OSCNT<2:0>: One-Shot Event Count bits

111 = Extends one-shot event by seven time base periods (eight time base periods total)

110 = Extends one-shot event by six time base periods (seven time base periods total)

101 = Extends one-shot event by five time base periods (six time base periods total)

100 = Extends one-shot event by four time base periods (five time base periods total)

011 = Extends one-shot event by three time base periods (four time base periods total)

010 = Extends one-shot event by two time base periods (three time base periods total)

001 = Extends one-shot event by one time base period (two time base periods total)

000 = Does not extend one-shot Trigger event

bit 11 **Unimplemented:** Read as '0'

bit 10-8 **OUTM<2:0>:** PWMx Output Mode Control bits⁽¹⁾

111 = Reserved

110 = Output Scan mode

101 = Brush DC Output mode, forward

100 = Brush DC Output mode, reverse

011 = Reserved

010 = Half-Bridge Output mode

001 = Push-Pull Output mode

000 = Steerable Single Output mode

bit 7-6 **Unimplemented:** Read as '0'

bit 5 POLACE: CCPx Output Pins, OCMxA, OCMxC and OCMxE, Polarity Control bit

1 = Output pin polarity is active-low

0 = Output pin polarity is active-high

bit 4 **POLBDF:** CCPx Output Pins, OCMxB, OCMxD and OCMxF, Polarity Control bit⁽¹⁾

1 = Output pin polarity is active-low

0 = Output pin polarity is active-high

bit 3-2 PSSACE<1:0>: PWMx Output Pins, OCMxA, OCMxC and OCMxE, Shutdown State Control bits

11 = Pins are driven active when a shutdown event occurs

10 = Pins are driven inactive when a shutdown event occurs

0x = Pins are tri-stated when a shutdown event occurs

bit 1-0 PSSBDF<1:0>: PWMx Output Pins, OCMxB, OCMxD, and OCMxF, Shutdown State Control bits⁽¹⁾

11 = Pins are driven active when a shutdown event occurs

10 = Pins are driven inactive when a shutdown event occurs

0x = Pins are in a high-impedance state when a shutdown event occurs

Note 1: These bits are implemented in the MCCP9 module only.

REGISTER 22-7: CCPxSTATL: CCPx STATUS REGISTER

U-0	U-0	U-0	U-0	U-0	W1-0	U-0	U-0
_	_	_	_	_	ICGARM	_	_
bit 15							bit 8

R-0	W1-0	W1-0	R/C-0	R/C-0	R/C-0	R/C-0	R/C-0
CCPTRIG	TRSET	TRCLR	ASEVT	SCEVT	ICDIS	ICOV	ICBNE
bit 7							bit 0

Legend:	C = Clearable bit		
R = Readable bit	W1 = Write '1' Only bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15-11 **Unimplemented:** Read as '0'

bit 10 ICGARM: Input Capture Gate Arm bit

A write of '1' to this location will arm the input capture gating logic for a one-shot gate event when

ICGSM<1:0> = 01 or 10. Bit always reads as '0'.

bit 9-8 **Unimplemented:** Read as '0'

bit 7 CCPTRIG: CCPx Trigger Status bit

1 = Timer has been triggered and is running

0 = Timer has not been triggered and is held in Reset

bit 6 TRSET: CCPx Trigger Set Request bit

Writes '1' to this location to trigger the timer when TRIGEN = 1 (location always reads as '0').

bit 5 TRCLR: CCPx Trigger Clear Request bit

Writes '1' to this location to cancel the timer trigger when TRIGEN = 1 (location always reads as '0').

bit 4 ASEVT: CCPx Auto-Shutdown Event Status/Control bit

1 = A shutdown event is in progress; CCPx outputs are in the shutdown state

0 = CCPx outputs operate normally

bit 3 SCEVT: Single Edge Compare Event Status bit

1 = A single edge compare event has occurred

0 = A single edge compare event has not occurred

bit 2 ICDIS: Input Capture x Disable bit

1 = Event on Input Capture x pin (ICx) does not generate a capture event

0 = Event on Input Capture x pin will generate a capture event

bit 1 ICOV: Input Capture x Buffer Overflow Status bit

1 = The Input Capture x FIFO buffer has overflowed

0 = The Input Capture x FIFO buffer has not overflowed

bit 0 ICBNE: Input Capture x Buffer Status bit

1 = Input Capture x buffer has data available

0 = Input Capture x buffer is empty

NOTES:			
10123.			

23.0 CONFIGURABLE LOGIC CELL (CLC)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. For more information, refer to "Configurable Logic Cell (CLC)" (www.microchip.com/DS70005298) in the "dsPIC33/PIC24 Family Reference Manual". The information in this data sheet supersedes the information in the FRM.

The Configurable Logic Cell (CLC) module allows the user to specify combinations of signals as inputs to a logic function and to use the logic output to control other peripherals or I/O pins. This provides greater flexibility and potential in embedded designs, since the CLC module can operate outside the limitations of software execution, and supports a vast amount of output designs.

There are four input gates to the selected logic function. These four input gates select from a pool of up to 32 signals that are selected using four data source selection multiplexers. Figure 23-1 shows an overview of the module.

Figure 23-3 shows the details of the data source multiplexers and Figure 23-2 shows the logic input gate connections.

FIGURE 23-1: CLCx MODULE






FIGURE 23-2: CLCx LOGIC FUNCTION COMBINATORIAL OPTIONS





23.1 Control Registers

The CLCx module is controlled by the following registers:

- CLCxCONL
- CLCxCONH
- CLCxSEL
- CLCxGLSL
- CLCxGLSH

The CLCx Control registers (CLCxCONL and CLCxCONH) are used to enable the module and interrupts, control the output enable bit, select output polarity and select the logic function. The CLCx Control registers also allow the user to control the logic polarity of not only the cell output, but also some intermediate variables.

The CLCx Input MUX Select register (CLCxSEL) allows the user to select up to four data input sources using the four data input selection multiplexers. Each multiplexer has a list of eight data sources available.

The CLCx Gate Logic Input Select registers (CLCxGLSL and CLCxGLSH) allow the user to select which outputs from each of the selection MUXes are used as inputs to the input gates of the logic cell. Each data source MUX outputs both a true and a negated version of its output. All of these eight signals are enabled, ORed together by the logic cell input gates. If no gate inputs are selected, the input to the gate will be zero or one, depending on the GxPOL bits.

REGISTER 23-1: CLCxCONL: CLCx CONTROL REGISTER (LOW)

R/W-0	U-0	U-0	U-0	R/W-0	R/W-0	U-0	U-0
LCEN	_	_	_	INTP	INTN	_	_
bit 15							bit 8

R-0	R-0	R/W-0	U-0	U-0	R/W-0	R/W-0	R/W-0
LCOE	LCOUT	LCPOL	_	_	MODE2	MODE1	MODE0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 LCEN: CLCx Enable bit

1 = CLCx is enabled and mixing input signals0 = CLCx is disabled and has logic zero outputs

bit 14-12 **Unimplemented:** Read as '0'

bit 11 INTP: CLCx Positive Edge Interrupt Enable bit

1 = Interrupt will be generated when a rising edge occurs on LCOUT

0 = Interrupt will not be generated

bit 10 INTN: CLCx Negative Edge Interrupt Enable bit

1 = Interrupt will be generated when a falling edge occurs on LCOUT

0 = Interrupt will not be generated

bit 9-8 **Unimplemented:** Read as '0'

bit 7 LCOE: CLCx Port Enable bit

1 = CLCx port pin output is enabled 0 = CLCx port pin output is disabled

bit 6 LCOUT: CLCx Data Output Status bit

1 = CLCx output high 0 = CLCx output low

bit 5 LCPOL: CLCx Output Polarity Control bit

1 = The output of the module is inverted0 = The output of the module is not inverted

bit 4-3 **Unimplemented:** Read as '0'

REGISTER 23-1: CLCxCONL: CLCx CONTROL REGISTER (LOW) (CONTINUED)

bit 2-0 MODE<2:0>: CLCx Mode bits

111 = Single input transparent latch with S and R

110 = JK flip-flop with R

101 = Two-input D flip-flop with R

100 = Single input D flip-flop with S and R

011 = SR latch

010 = Four-input AND

001 = Four-input OR-XOR

000 = Four-input AND-OR

REGISTER 23-2: CLCxCONH: CLCx CONTROL REGISTER (HIGH)

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	G4POL	G3POL	G2POL	G1POL
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-4 **Unimplemented:** Read as '0'

bit 3 **G4POL:** Gate 4 Polarity Control bit

1 = Channel 4 logic output is inverted when applied to the logic cell

0 = Channel 4 logic output is not inverted

bit 2 G3POL: Gate 3 Polarity Control bit

1 = Channel 3 logic output is inverted when applied to the logic cell

0 = Channel 3 logic output is not inverted

bit 1 **G2POL:** Gate 2 Polarity Control bit

1 = Channel 2 logic output is inverted when applied to the logic cell

0 = Channel 2 logic output is not inverted

bit 0 **G1POL:** Gate 1 Polarity Control bit

1 = Channel 1 logic output is inverted when applied to the logic cell

0 = Channel 1 logic output is not inverted

REGISTER 23-3: CLCxSEL: CLCx INPUT MUX SELECT REGISTER

U-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
_		DS4<2:0>		_		DS3<2:0>	
bit 15							bit 8

U-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
_		DS2<2:0>		_		DS1<2:0>	
bit 7			_				bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **Unimplemented:** Read as '0'

bit 14-12 DS4<2:0>: Data Selection MUX 4 Signal Selection bits

111 = SCCP3 auxiliary out

110 = SCCP1 auxiliary out

101 = CLCIND pin

100 = Reserved

011 = SPI1 Input (SDIx)(1)

010 = Comparator 3 output

001 = CLC2 output

000 = PWM Event A

bit 11 **Unimplemented:** Read as '0'

bit 10-8 DS3<2:0>: Data Selection MUX 3 Signal Selection bits

111 = SCCP4 Compare Event Flag (CCP4IF)

110 = SCCP3 Compare Event Flag (CCP3IF)

101 = CLC4 out

100 = UART1 RX output corresponding to CLCx module

011 = SPI1 Output (SDOx) corresponding to CLCx module⁽¹⁾

010 = Comparator 2 output

001 = CLC1 output

000 = CLCINC I/O pin

bit 7 **Unimplemented:** Read as '0'

bit 6-4 DS2<2:0>: Data Selection MUX 2 Signal Selection bits

111 = SCCP2 OC (CCP2IF) out

110 = SCCP1 OC (CCP1IF) out

101 = Reserved

100 = Reserved

011 = UART1 TX input corresponding to CLCx module

010 = Comparator 1 output

001 = Reserved

000 = CLCINB I/O pin

bit 3 **Unimplemented:** Read as '0'

Note 1: Valid only when SPI is used on PPS.

REGISTER 23-3: CLCxSEL: CLCx INPUT MUX SELECT REGISTER (CONTINUED)

bit 2-0 DS1<2:0>: Data Selection MUX 1 Signal Selection bits

111 = SCCP4 auxiliary out

110 = SCCP2 auxiliary out

101 = Reserved

100 = REFCLKO output

011 = INTRC/LPRC clock source

010 = CLC3 out

001 = System clock (FCY)

000 = CLCINA I/O pin

Note 1: Valid only when SPI is used on PPS.

REGISTER 23-4: CLCxGLSL: CLCx GATE LOGIC INPUT SELECT LOW REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
G2D4T	G2D4N	G2D3T	G2D3N	G2D2T	G2D2N	G2D1T	G2D1N
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| G1D4T | G1D4N | G1D3T | G1D3N | G1D2T | G1D2N | G1D1T | G1D1N |
| bit 7 | | | | | | | bit 0 |

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15	G2D4T: Gate 2 Data Source 4 True Enable bit
	1 = Data Source 4 signal is enabled for Gate 2
	0 = Data Source 4 signal is disabled for Gate 2
bit 14	G2D4N: Gate 2 Data Source 4 Negated Enable bit
	1 = Data Source 4 inverted signal is enabled for Gate 2
	0 = Data Source 4 inverted signal is disabled for Gate 2
bit 13	G2D3T: Gate 2 Data Source 3 True Enable bit
	1 = Data Source 3 signal is enabled for Gate 2
	0 = Data Source 3 signal is disabled for Gate 2
bit 12	G2D3N: Gate 2 Data Source 3 Negated Enable bit
	1 = Data Source 3 inverted signal is enabled for Gate 2
	0 = Data Source 3 inverted signal is disabled for Gate 2
bit 11	G2D2T: Gate 2 Data Source 2 True Enable bit
	1 = Data Source 2 signal is enabled for Gate 2
	0 = Data Source 2 signal is disabled for Gate 2
bit 10	G2D2N: Gate 2 Data Source 2 Negated Enable bit
	1 = Data Source 2 inverted signal is enabled for Gate 2
	0 = Data Source 2 inverted signal is disabled for Gate 2
bit 9	G2D1T: Gate 2 Data Source 1 True Enable bit
	1 = Data Source 1 signal is enabled for Gate 2
	0 = Data Source 1 signal is disabled for Gate 2
bit 8	G2D1N: Gate 2 Data Source 1 Negated Enable bit
	1 = Data Source 1 inverted signal is enabled for Gate 2
	0 = Data Source 1 inverted signal is disabled for Gate 2
bit 7	G1D4T: Gate 1 Data Source 4 True Enable bit
	1 = Data Source 4 signal is enabled for Gate 1
	0 = Data Source 4 signal is disabled for Gate 1
bit 6	G1D4N: Gate 1 Data Source 4 Negated Enable bit
	1 = Data Source 4 inverted signal is enabled for Gate 1
	0 = Data Source 4 inverted signal is disabled for Gate 1
bit 5	G1D3T: Gate 1 Data Source 3 True Enable bit
	1 = Data Source 3 signal is enabled for Gate 1
	0 = Data Source 3 signal is disabled for Gate 1
bit 4	G1D3N: Gate 1 Data Source 3 Negated Enable bit
	1 = Data Source 3 inverted signal is enabled for Gate 1
	0 = Data Source 3 inverted signal is disabled for Gate 1

REGISTER 23-4: CLCxGLSL: CLCx GATE LOGIC INPUT SELECT LOW REGISTER (CONTINUED)

bit 3	G1D2T: Gate 1 Data Source 2 True Enable bit
	1 = Data Source 2 signal is enabled for Gate 1
	0 = Data Source 2 signal is disabled for Gate 1
bit 2	G1D2N: Gate 1 Data Source 2 Negated Enable bit
	1 = Data Source 2 inverted signal is enabled for Gate 1
	0 = Data Source 2 inverted signal is disabled for Gate 1
bit 1	G1D1T: Gate 1 Data Source 1 True Enable bit
	1 = Data Source 1 signal is enabled for Gate 1
	0 = Data Source 1 signal is disabled for Gate 1
bit 0	G1D1N: Gate 1 Data Source 1 Negated Enable bit
	1 = Data Source 1 inverted signal is enabled for Gate 1
	0 = Data Source 1 inverted signal is disabled for Gate 1

REGISTER 23-5: CLCxGLSH: CLCx GATE LOGIC INPUT SELECT HIGH REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
G4D4T	G4D4N	G4D3T	G4D3N	G4D2T	G4D2N	G4D1T	G4D1N
bit 15							bit 8

| R/W-0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| G3D4T | G3D4N | G3D3T | G3D3N | G3D2T | G3D2N | G3D1T | G3D1N |
| bit 7 | | | | | | | bit 0 |

Legend	:
--------	---

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15	G4D4T: Gate 4 Data Source 4 True Enable bit
	1 = Data Source 4 signal is enabled for Gate 4
	0 = Data Source 4 signal is disabled for Gate 4
bit 14	G4D4N: Gate 4 Data Source 4 Negated Enable bit
	1 = Data Source 4 inverted signal is enabled for Gate 4
	0 = Data Source 4 inverted signal is disabled for Gate 4
bit 13	G4D3T: Gate 4 Data Source 3 True Enable bit
	1 = Data Source 3 signal is enabled for Gate 4
	0 = Data Source 3 signal is disabled for Gate 4
bit 12	G4D3N: Gate 4 Data Source 3 Negated Enable bit
	1 = Data Source 3 inverted signal is enabled for Gate 4
	0 = Data Source 3 inverted signal is disabled for Gate 4
bit 11	G4D2T: Gate 4 Data Source 2 True Enable bit
	1 = Data Source 2 signal is enabled for Gate 4
	0 = Data Source 2 signal is disabled for Gate 4
bit 10	G4D2N: Gate 4 Data Source 2 Negated Enable bit
	1 = Data Source 2 inverted signal is enabled for Gate 4
	0 = Data Source 2 inverted signal is disabled for Gate 4
bit 9	G4D1T: Gate 4 Data Source 1 True Enable bit
	1 = Data Source 1 signal is enabled for Gate 4
	0 = Data Source 1 signal is disabled for Gate 4
bit 8	G4D1N: Gate 4 Data Source 1 Negated Enable bit
	1 = Data Source 1 inverted signal is enabled for Gate 4
	0 = Data Source 1 inverted signal is disabled for Gate 4
bit 7	G3D4T: Gate 3 Data Source 4 True Enable bit
	1 = Data Source 4 signal is enabled for Gate 3
	0 = Data Source 4 signal is disabled for Gate 3
bit 6	G3D4N: Gate 3 Data Source 4 Negated Enable bit
	1 = Data Source 4 inverted signal is enabled for Gate 3
	0 = Data Source 4 inverted signal is disabled for Gate 3
bit 5	G3D3T: Gate 3 Data Source 3 True Enable bit
	1 = Data Source 3 signal is enabled for Gate 3
	0 = Data Source 3 signal is disabled for Gate 3
bit 4	G3D3N: Gate 3 Data Source 3 Negated Enable bit
	1 = Data Source 3 inverted signal is enabled for Gate 3
	0 = Data Source 3 inverted signal is disabled for Gate 3

REGISTER 23-5: CLCxGLSH: CLCx GATE LOGIC INPUT SELECT HIGH REGISTER (CONTINUED)

bit 3	G3D2T: Gate 3 Data Source 2 True Enable bit 1 = Data Source 2 signal is enabled for Gate 3 0 = Data Source 2 signal is disabled for Gate 3
bit 2	G3D2N: Gate 3 Data Source 2 Negated Enable bit
	1 = Data Source 2 inverted signal is enabled for Gate 30 = Data Source 2 inverted signal is disabled for Gate 3
bit 1	G3D1T: Gate 3 Data Source 1 True Enable bit
	1 = Data Source 1 signal is enabled for Gate 30 = Data Source 1 signal is disabled for Gate 3
bit 0	G3D1N: Gate 3 Data Source 1 Negated Enable bit
	1 = Data Source 1 inverted signal is enabled for Gate 30 = Data Source 1 inverted signal is disabled for Gate 3

	 	<u> </u>	
NOTES:			

24.0 PERIPHERAL TRIGGER GENERATOR (PTG)


Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Peripheral Trigger Generator (PTG)" (www.microchip.com/DS70000669) in the "dsPIC33/PIC24 Family Reference Manual".

The dsPIC33CK256MP508 family Peripheral Trigger Generator (PTG) module is a user-programmable sequencer that is capable of generating complex trigger signal sequences to coordinate the operation of other peripherals. The PTG module is designed to interface with the modules, such as an Analog-to-Digital Converter (ADC), output compare and PWM modules, timers and interrupt controllers.

24.1 Features

- Behavior is Step Command Driven:
 - Step commands are eight bits wide
- · Commands are Stored in a Step Queue:
 - Queue depth is up to 32 entries
 - Programmable Step execution time (Step delay)
- · Supports the Command Sequence Loop:
 - Can be nested one-level deep
 - Conditional or unconditional loop
 - Two 16-bit loop counters
- 15 Hardware Input Triggers:
 - Sensitive to either positive or negative edges, or a high or low level
- · One Software Input Trigger
- Generates up to 32 Unique Output Trigger Signals
- Generates Two Types of Trigger Outputs:
 - Individual
 - Broadcast
- · Strobed Output Port for Literal Data Values:
 - 5-bit literal write (literal part of a command)
 - 16-bit literal write (literal held in the PTGL0 register)
- Generates up to Ten Unique Interrupt Signals
- Two 16-Bit General Purpose Timers
- Flexible Self-Contained Watchdog Timer (WDT) to Set an Upper Limit to Trigger Wait Time
- · Single Step Command Capability in Debug mode
- Selectable Clock (System, Pulse-Width Modulator (PWM) or ADC)
- · Programmable Clock Divider

FIGURE 24-1: PTG BLOCK DIAGRAM



24.2 PTG Registers

REGISTER 24-1: PTGCST: PTG CONTROL/STATUS LOW REGISTER

R/W-0	U-0	R/W-0	R/W-0	U-0	HC/R/W-0	R/W-0	R/W-0
PTGEN	_	PTGSIDL	PTGTOGL	_	PTGSWT ⁽²⁾	PTGSSEN ⁽³⁾	PTGIVIS
bit 15							bit 8

HC/R/W-0	HS/R/W-0	HS/HC/R/W-0	U-0	U-0	U-0	R/W-0	R/W-0
PTGSTRT	PTGWDTO	PTGBUSY	_	_	_	PTGITM1 ⁽¹⁾	PTGITM0 ⁽¹⁾
bit 7 bi							

Legend:	HC = Hardware Clearable bit	HS = Hardware Settable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared $x = Bit$ is unknown		

bit 15 **PTGEN:** PTG Enable bit

1 = PTG is enabled

0 = PTG is disabled

bit 14 Unimplemented: Read as '0'

bit 13 PTGSIDL: PTG Freeze in Debug Mode bit

1 = Halts PTG operation when device is Idle

0 = PTG operation continues when device is Idle

bit 12 **PTGTOGL:** PTG Toggle Trigger Output bit

1 = Toggles state of TRIG output for each execution of PTGTRIG

0 = Generates a single TRIG pulse for each execution of PTGTRIG

bit 11 **Unimplemented:** Read as '0'

bit 10 **PTGSWT:** PTG Software Trigger bit⁽²⁾

1 = Toggles state of TRIG output for each execution of PTGTRIG

0 = Generates a single TRIG pulse for each execution of PTGTRIG

bit 9 **PTGSSEN:** PTG Single-Step Command bit⁽³⁾

1 = Enables single Step when in Debug mode

0 = Disables single Step

bit 8 PTGIVIS: PTG Counter/Timer Visibility bit

1 = Reading the PTGSDLIM, PTGCxLIM or PTGTxLIM registers returns the current values of their corresponding Counter/Timer registers (PTGSDLIM, PTGCxLIM and PTGTxLIM)

0 = Reading the PTGSDLIM, PTGCxLIM or PTGTxLIM registers returns the value of these Limit registers

bit 7 PTGSTRT: PTG Start Sequencer bit

1 = Starts to sequentially execute the commands (Continuous mode)

0 = Stops executing the commands

bit 6 PTGWDTO: PTG Watchdog Timer Time-out Status bit

1 = PTG Watchdog Timer has timed out

0 = PTG Watchdog Timer has not timed out

bit 5 PTGBUSY: PTG State Machine Busy bit

1 = PTG is running on the selected clock source; no SFR writes are allowed to PTGCLK<2:0> or PTGDIV<4:0>

0 = PTG state machine is not running

Note 1: These bits apply to the PTGWHI and PTGWLO commands only.

2: This bit is only used with the PTGCTRL Step command software trigger option.

3: The PTGSSEN bit may only be written when in Debug mode.

REGISTER 24-1: PTGCST: PTG CONTROL/STATUS LOW REGISTER (CONTINUED)

- bit 4-2 Unimplemented: Read as '0'
- bit 1-0 **PTGITM<1:0>:** PTG Input Trigger Operation Selection bit⁽¹⁾
 - 11 = Single-level detect with Step delay not executed on exit of command (regardless of the PTGCTRL command) (Mode 3)
 - 10 = Single-level detect with Step delay executed on exit of command (Mode 2)
 - 01 = Continuous edge detect with Step delay not executed on exit of command (regardless of the PTGCTRL command) (Mode 1)
 - 00 = Continuous edge detect with Step delay executed on exit of command (Mode 0)
- Note 1: These bits apply to the PTGWHI and PTGWLO commands only.
 - 2: This bit is only used with the PTGCTRL Step command software trigger option.
 - 3: The PTGSSEN bit may only be written when in Debug mode.

REGISTER 24-2: PTGCON: PTG CONTROL/STATUS HIGH REGISTER

| R/W-0 |
|---------|---------|---------|---------|---------|---------|---------|---------|
| PTGCLK2 | PTGCLK1 | PTGCLK0 | PTGDIV4 | PTGDIV3 | PTGDIV2 | PTGDIV1 | PTGDIV0 |
| bit 15 | | | | | | | bit 8 |

R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0
PTGPWD3	PTGPWD2	PTGPWD1	PTGPWD0	_	PTGWDT2	PTGWDT1	PTGWDT0
bit 7							

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 PTGCLK<2:0>: PTG Module Clock Source Selection bits

111 = CLC1

110 = PLL VCO DIV 4 output

101 = PTG module clock source will be SCCP7

100 = PTG module clock source will be SCCP8

011 = Input from Timer1 Clock pin, T1CK

010 = PTG module clock source will be ADC clock

001 = PTG module clock source will be Fosc

000 = PTG module clock source will be Fosc/2 (FP)

bit 12-8 PTGDIV<4:0>: PTG Module Clock Prescaler (Divider) bits

11111 = Divide-by-32

11110 = Divide-by-31

. . .

00001 = Divide-by-2

00000 = Divide-by-1

bit 7-4 PTGPWD<3:0>: PTG Trigger Output Pulse-Width (in PTG clock cycles) bits

1111 = All trigger outputs are 16 PTG clock cycles wide

1110 = All trigger outputs are 15 PTG clock cycles wide

. . .

0001 = All trigger outputs are 2 PTG clock cycles wide

0000 = All trigger outputs are 1 PTG clock cycle wide

bit 3 **Unimplemented:** Read as '0'

bit 2-0 **PTGWDT<2:0>:** PTG Watchdog Timer Time-out Selection bits

111 = Watchdog Timer will time out after 512 PTG clocks

110 = Watchdog Timer will time out after 256 PTG clocks

101 = Watchdog Timer will time out after 128 PTG clocks

100 = Watchdog Timer will time out after 64 PTG clocks

011 = Watchdog Timer will time out after 32 PTG clocks

010 = Watchdog Timer will time out after 16 PTG clocks

001 = Watchdog Timer will time out after 8 PTG clocks

000 = Watchdog Timer is disabled

REGISTER 24-3: PTGBTE: PTG BROADCAST TRIGGER ENABLE LOW REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PTGBTE<	:15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PTGBTE-	<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PTGBTE<15:0>:** PTG Broadcast Trigger Enable bits

1 = Generates trigger when the broadcast command is executed

0 = Does not generate trigger when the broadcast command is executed

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-4: PTGBTEH: PTG BROADCAST TRIGGER ENABLE HIGH REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PTGBTE<31:24>							
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PTGBTE<23:16>							
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PTGBTE<31:16>:** PTG Broadcast Trigger Enable bits

1 = Generates trigger when the broadcast command is executed

0 = Does not generate trigger when the broadcast command is executed

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-5: PTGHOLD: PTG HOLD REGISTER(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PTGHOLD<15:8>							
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PTGHOLD<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PTGHOLD<15:0>: PTG General Purpose Hold Register bits

This register holds the user-supplied data to be copied to the PTGTxLIM, PTGCxLIM, PTGSDLIM or PTGL0 register using the PTGCOPY command.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-6: PTGT0LIM: PTG TIMER0 LIMIT REGISTER(1)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PTGT0LIM<15:8>								
bit 15							bit 8	

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PTGT0LIM<7:0>								
bit 7		bit 0						

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PTGT0LIM<15:0>: PTG Timer0 Limit Register bits

General Purpose Timer0 Limit register.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-7: PTGT1LIM: PTG TIMER1 LIMIT REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			PTGT1LI	M<15:8>			
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
	PTGT1LIM<7:0>									
bit 7										

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PTGT1LIM<15:0>:** PTG Timer1 Limit Register bits

General Purpose Timer1 Limit register.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-8: PTGSDLIM: PTG STEP DELAY LIMIT REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	PTGSDLIM<15:8>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	
PTGSDLIM<7:0>								
bit 7							bit 0	

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PTGSDLIM<15:0>: PTG Step Delay Limit Register bits

This register holds a PTG Step delay value representing the number of additional PTG clocks between the start of a Step command and the completion of a Step command.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-9: PTGC0LIM: PTG COUNTER 0 LIMIT REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	PTGC0LIM<15:8>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGC0LIM<7:0>									
bit 7 bit									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PTGC0LIM<15:0>:** PTG Counter 0 Limit Register bits

This register is used to specify the loop count for the PTGJMPC0 Step command or as a Limit register for the General Purpose Counter 0.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-10: PTGC1LIM: PTG COUNTER 1 LIMIT REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGC1LIM<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGC1LIM<7:0>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PTGC1LIM<15:0>: PTG Counter 1 Limit Register bits

This register is used to specify the loop count for the PTGJMPC1 Step command or as a Limit register for the General Purpose Counter 1.

Note 1: These bits are read-only when the module is executing step commands.

REGISTER 24-11: PTGADJ: PTG ADJUST REGISTER⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGADJ<15:8>									
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGADJ<7:0>									
bit 7									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PTGADJ<15:0>:** PTG Adjust Register bits

This register holds the user-supplied data to be added to the PTGTxLIM, PTGCxLIM, PTGSDLIM or PTGL0 register using the PTGADD command.

Note 1: These bits are read-only when the module is executing Step commands.

REGISTER 24-12: PTGL0: PTG LITERAL 0 REGISTER^(1,2)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGL0<15:8>									
bit 15									

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
PTGL0<7:0>									
bit 7 bit 0									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PTGL0<15:0>: PTG Literal 0 Register bits

This register holds the 6-bit value to be written to the CNVCHSEL<5:0> bits (ADCON3L<5:0>) with the PTGCTRL Step command.

- **Note 1:** These bits are read-only when the module is executing Step commands.
 - 2: The PTG strobe output is typically connected to the ADC Channel Select register. This allows the PTG to directly control ADC channel switching. See the specific device data sheet for connections of the PTG output.

REGISTER 24-13: PTGQPTR: PTG STEP QUEUE POINTER REGISTER(1)

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0	
_	_	_	_	_	_	_	_	
bit 15 bit 8								

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_			PTGQPTR<4:0	>	
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-5 **Unimplemented:** Read as '0'

bit 4-0 PTGQPTR<4:0>: PTG Step Queue Pointer Register bits

This register points to the currently active Step command in the Step queue.

Note 1: These bits are read-only when the module is executing step commands.

REGISTER 24-14: PTGQUEn: PTG STEP QUEUE n POINTER REGISTER (n = 0-15)⁽¹⁾

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
STEP2n+1<7:0> ⁽²⁾									
bit 15 bit 8									

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
STEP2n<7:0> ⁽²⁾									
bit 7 bi									

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **STEP2n+1<7:0>:** PTG Command 4n+1 bits⁽²⁾

A queue location for storage of the STEP2n+1 command byte, where 'n' is from PTGQUEn.

bit STEP2n<7:0>: PTG Command 4n+2 bits⁽²⁾

A queue location for storage of the STEP2n command byte, where 'n' is the odd numbered Step

Queue Pointers.

Note 1: These bits are read-only when the module is executing Step commands.

2: Refer to Table 24-1 for the Step command encoding.

TABLE 24-1: PTG STEP COMMAND FORMAT AND DESCRIPTION

Step Command Byte		
	STEPx<7:0>	
CMD<3:0>	OPTION<3:0>	
bit 7	bit 4 bit 3	bit 0

bit 7-4	Step Command	CMD<3:0>	Command Description		
	PTGCTRL	0000	Execute the control command as described by the OPTION<3:0> bits.		
	PTGADD	0001	Add contents of the PTGADJ register to the target register as described by OPTION<3:0> bits.		
	PTGCOPY		Copy contents of the PTGHOLD register to the target register as described by the OPTION<3:0> bits.		
	PTGSTRB	001x	Copy the values contained in the bits, CMD<0>:OPTION<3:0> to the strobe output bits <4:0>.		
	PTGWHI	0100	Wait for a low-to-high edge input from a selected PTG trigger input as described by the OPTION<3:0> bits.		
	PTGWLO	0101	Wait for a high-to-low edge input from a selected PTG trigger input as described by the OPTION<3:0> bits.		
	_	0110	Reserved; do not use. ⁽¹⁾		
	PTGIRQ	0111	Generate individual interrupt request as described by the OPTION<3:0> bits.		
	PTGTRIG	100x	Generate individual trigger output as described by the bits, CMD<0>:OPTION<3:0>.		
	PTGJMP	101x	Copy the values contained in the bits, CMD<0>:OPTION<3:0> to the PTGQPTR register, and jump to that Step queue.		
	PTGJMPC0	110x	PTGC0 = PTGC0LIM: Increment the PTGQPTR register.		
			PTGC0 ≠ PTGC0LIM: Increment Counter 0 (PTGC0) and copy the values contained in the bits, CMD<0>:OPTION<3:0> to the PTGQPTR register, and jump to that Step queue.		
	PTGJMPC1	111x	PTGC1 = PTGC1LIM: Increment the PTGQPTR register.		
			PTGC1 ≠ PTGC1LIM: Increment Counter 1 (PTGC1) and copy the values contained in the bits, CMD<0>:OPTION<3:0> to the PTGQPTR register, and jump to that Step queue.		

Note 1: All reserved commands or options will execute, but they do not have any affect (i.e., execute as a NOP instruction).

TABLE 24-2: PTG COMMAND OPTIONS

bit 3-0	Step Command	OPTION<3:0>	Command Description
	PTGCTRL ⁽¹⁾	0000	NOP.
		0001	Reserved; do not use.
		0010	Disable Step delay timer (PTGSD).
		0011	Reserved; do not use.
		0100	Reserved; do not use.
		0101	Reserved; do not use.
		0110	Enable Step delay timer (PTGSD).
		0111	Reserved; do not use.
		1000	Start and wait for the PTG Timer0 to match the PTGT0LIM register.
		1001	Start and wait for the PTG Timer1 to match the PTGT1LIM register.
		1010	Wait for the software trigger (level, PTGSWT = 1).
		1011	Wait for the software trigger (positive edge, PTGSWT = 0 to 1).
		1100	Copy the PTGC0LIM register contents to the strobe output.
		1101	Copy the PTGC1LIM register contents to the strobe output.
		1110	Copy the PTGL0 register contents to the strobe output.
		1111	Generate the triggers indicated in the PTGBTE register.
	PTGADD ⁽¹⁾	0000	Add the PTGADJ register contents to the PTGC0LIM register.
		0001	Add the PTGADJ register contents to the PTGC1LIM register.
		0010	Add the PTGADJ register contents to the PTGT0LIM register.
		0011	Add the PTGADJ register contents to the PTGT1LIM register.
		0100	Add the PTGADJ register contents to the PTGSDLIM register.
		0101	Add the PTGADJ register contents to the PTGL0 register.
		0110	Reserved; do not use.
		0111	Reserved; do not use.
	PTGCOPY ⁽¹⁾	1000	Copy the PTGHOLD register contents to the PTGC0LIM register.
		1001	Copy the PTGHOLD register contents to the PTGC1LIM register.
		1010	Copy the PTGHOLD register contents to the PTGT0LIM register.
		1011	Copy the PTGHOLD register contents to the PTGT1LIM register.
		1100	Copy the PTGHOLD register contents to the PTGSDLIM register.
		1101	Copy the PTGHOLD register contents to the PTGL0 register.
		1110	Reserved; do not use.
		1111	Reserved; do not use.

Note 1: All reserved commands or options will execute, but they do not have any affect (i.e., execute as a NOP instruction).

TABLE 24-2: PTG COMMAND OPTIONS (CONTINUED)

bit 3-0	Step Command	OPTION<3:0>	Option Description
	PTGWHI(1)	0000	PTGI0 (see Table 24-3 for input assignments).
	or PTGWLO(1)	•	•
	P'I'GWLO('')	•	•
		•	•
		1111	PTGI15 (see Table 24-3 for input assignments).
	PTGIRQ ⁽¹⁾	0000	Generate PTG Interrupt 0.
		•	•
		•	•
		•	•
		0111	Generate PTG Interrupt 7.
		1000	Reserved; do not use.
		•	•
		•	•
		1111	Pagamindu da matura
-	DECEDIC	1111	Reserved; do not use.
	PTGTRIG	00000	PTGO0 (see Table 24-4 for output assignments).
		00001	PTGO1 (see Table 24-4 for output assignments).
		•	•
		11110	PTGO30 (see Table 24-4 for output assignments).
		11111	PTGO31 (see Table 24-4 for output assignments).
	PTGWHI(1)	0000	PTGI0 (see specific device data sheet for input assignments).
	or	•	•
	PTGWLO ⁽¹⁾	•	•
		•	•
		1111	PTGI15 (see specific device data sheet for input assignments).
	PTGIRQ ⁽¹⁾	0000	Generate PTG Interrupt 0 (see specific device data sheet for interrupt assignments).
		•	•
		•	•
		•	•
		0111	Generate PTG Interrupt 7 (see specific device data sheet for interrupt assignments).
		1000	Reserved; do not use.
		•	•
		•	•
		•	•
		1111	Reserved; do not use.
	PTGTRIG	00000	PTGO0 (see specific device data sheet for assignments).
		00001	PTGO1 (see specific device data sheet for assignments).

Note 1: All reserved commands or options will execute, but they do not have any affect (i.e., execute as a NOP instruction).

TABLE 24-3: PTG INPUT DESCRIPTIONS

PTG Input Number	PTG Input Description
PTG Trigger Input 0	Trigger Input from PWM1 ADC Trigger 2
PTG Trigger Input 1	Trigger Input from PWM2 ADC Trigger 2
PTG Trigger Input 2	Trigger Input from PWM3 ADC Trigger 2
PTG Trigger Input 3	Trigger Input from PWM4 ADC Trigger 2
PTG Trigger Input 4	Trigger Input from PWM5 ADC Trigger 2
PTG Trigger Input 5	Trigger Input from PWM6 ADC Trigger 2
PTG Trigger Input 6	Trigger Input from PWM7 ADC Trigger 2
PTG Trigger Input 7	Trigger Input from SCCP4
PTG Trigger Input 8	Trigger Input from SCCP5
PTG Trigger Input 9	Trigger Input from Comparator 1
PTG Trigger Input 10	Trigger Input from Comparator 2
PTG Trigger Input 11	Trigger Input from Comparator 3
PTG Trigger Input 12	Trigger Input from CLC1
PTG Trigger Input 13	Trigger Input ADC Done Group Interrupt
PTG Trigger Input 14	Reserved
PTG Trigger Input 15	Trigger Input from INT2 PPS

TABLE 24-4: PTG OUTPUT DESCRIPTIONS

PTG Output Number	PTG Output Description
PTGO0 to PTGO11	Reserved
PTGO12	ADC TRGSRC<30>
PTGO13 to PTGO23	Reserved
PTGO24	PPS Output RP46
PTGO25	PPS Output RP47
PTGO26	PPS Input RP6
PTGO27	PPS Input RP7
PTGO28 to PTGO31	Reserved

NOTES:			
NOTES.			

25.0 32-BIT PROGRAMMABLE CYCLIC REDUNDANCY CHECK (CRC) GENERATOR


Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. For more information, refer to "32-Bit Programmable Cyclic Redundancy Check (CRC)" (www.microchip.com/DS30009729) in the "dsPIC33/PIC24 Family Reference Manual".

The 32-bit programmable CRC generator provides a hardware implemented method of quickly generating checksums for various networking and security applications. It offers the following features:

- User-Programmable CRC Polynomial Equation, up to 32 Bits
- Programmable Shift Direction (little or big-endian)
- · Independent Data and Polynomial Lengths
- · Configurable Interrupt Output
- · Data FIFO

A simple version of the CRC shift engine is displayed in Figure 25-1.

FIGURE 25-1: CRC MODULE BLOCK DIAGRAM



25.1 Control Registers

REGISTER 25-1: CRCCONL: CRC CONTROL REGISTER LOW

R/W-0	U-0	R/W-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0	HSC/R-0
CRCEN	_	CSIDL	VWORD4	VWORD3	VWORD2	VWORD1	VWORD0
bit 15							bit 8

HSC/R-0	HSC/R-1	R/W-0	HC/R/W-0	R/W-0	R/W-0	U-0	U-0
CRCFUL	CRCMPT	CRCISEL	CRCGO	LENDIAN	MOD	_	_
bit 7							bit 0

Legend: HC = Hardware Clearable bit		HSC = Hardware Settable/Clearable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared $x = Bit$ is unknown		

bit 15 CRCEN: CRC Enable bit

1 = Enables module0 = Disables module

bit 14 Unimplemented: Read as '0'

bit 13 CSIDL: CRC Stop in Idle Mode bit

1 = Discontinues module operation when device enters Idle mode

0 = Continues module operation in Idle mode

bit 12-8 **VWORD<4:0>:** Pointer Value bits

Indicates the number of valid words in the FIFO. Has a maximum value of 8 when PLEN<4:0> ≥ 7 or

16 when PLEN<4:0> \leq 7.

bit 7 CRCFUL: CRC FIFO Full bit

1 = FIFO is full 0 = FIFO is not full

bit 6 CRCMPT: CRC FIFO Empty bit

1 = FIFO is empty
0 = FIFO is not empty

bit 5 CRCISEL: CRC Interrupt Selection bit

1 = Interrupt on FIFO is empty; the final word of data is still shifting through the CRC

0 = Interrupt on shift is complete and results are ready

bit 4 CRCGO: CRC Start bit

1 = Starts CRC serial shifter

0 = CRC serial shifter is turned off

bit 3 LENDIAN: Data Shift Direction Select bit

1 = Data word is shifted into the FIFO, starting with the LSb (little-endian)

0 = Data word is shifted into the FIFO, starting with the MSb (big-endian)

bit 2 MOD: CRC Calculation Mode bit

1 = Alternate mode0 = Legacy mode bit

bit 1-0 **Unimplemented:** Read as '0'

REGISTER 25-2: CRCCONH: CRC CONTROL REGISTER HIGH

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	DWIDTH4	DWIDTH3	DWIDTH2	DWIDTH1	DWIDTH0
bit 15							bit 8

U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	PLEN4	PLEN3	PLEN2	PLEN1	PLEN0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-13 Unimplemented: Read as '0'

bit 12-8 **DWIDTH<4:0>:** Data Word Width Configuration bits

Configures the width of the data word (Data Word Width -1).

bit 7-5 **Unimplemented:** Read as '0'

bit 4-0 **PLEN<4:0>:** Polynomial Length Configuration bits

Configures the length of the polynomial (Polynomial Length – 1).

REGISTER 25-3: CRCXORL: CRC XOR POLYNOMIAL REGISTER, LOW BYTE

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	X<15:8>								
bit 15							bit 8		

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0
			X<7:1>				_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-1 X<15:1>: XOR of Polynomial Term xⁿ Enable bits

bit 0 Unimplemented: Read as '0'

REGISTER 25-4: CRCXORH: CRC XOR POLYNOMIAL REGISTER, HIGH BYTE

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
	X<31:24>									
bit 15							bit 8			

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
	X<23:16>									
bit 7							bit 0			

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 X<31:16>: XOR of Polynomial Term xⁿ Enable bits

26.0 CURRENT BIAS GENERATOR (CBG)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Current Bias Generator (CBG)" (www.microchip.com/DS70005253) in the "dsPIC33/PIC24 Family Reference Manual".

2: Some registers and associated bits described in this section may not be available on all devices. Refer to Table 26-1 for CBG channel availability on package variants.

The Current Bias Generator (CBG) consists of two classes of current sources: 10 μA and 50 μA sources. The major features of each current source are:


- 10 μA Current Sources:
 - Current sourcing only
 - Up to four independent sources
- 50 μA Current Sources:
 - Selectable current sourcing or sinking
 - Selectable current mirroring for sourcing and sinking

A simplified block diagram of the CBG module is shown in Figure 26-1.

TABLE 26-1: CBG CHANNEL AVAILABILITY

Package Type	ISRCx	IBIASx
28-pin	_	0,3
36-pin	0,1	0,2,3
48-pin	0,1,2,3	0,1,2,3
64-pin	0,1,2,3	0,1,2,3
80-pin	0,1,2,3	0,1,2,3

FIGURE 26-1: CONSTANT-CURRENT SOURCE MODULE BLOCK DIAGRAM⁽²⁾



Note 1: RESD is typically 300 Ohms; for more information, refer to the device data sheet.

2: In Figure 26-1 only, the ADC analog input is shown for clarity. Each analog peripheral connected to the pin has a separate Electrostatic Discharge (ESD) resistor.

26.1 Current Bias Generator Control Registers

REGISTER 26-1: BIASCON: CURRENT BIAS GENERATOR CONTROL REGISTER

R/W-0	U-0						
ON	_		_		_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	I10EN3	I10EN2	I10EN1	I10EN0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 ON: Current Bias Module Enable bit

1 = Module is enabled 0 = Module is disabled

bit 14-4 **Unimplemented:** Read as '0'

bit 3 I10EN3: 10 µA Enable for Output 3 bit

1 = 10 μA output is enabled 0 = 10 μA output is disabled

bit 2 I10EN2: 10 µA Enable for Output 2 bit

1 = 10 μA output is enabled 0 = 10 μA output is disabled

bit 1 I10EN1: 10 µA Enable for Output 1 bit

1 = 10 μA output is enabled 0 = 10 μA output is disabled

bit 0 I10EN0: 10 µA Enable for Output 0 bit

1 = 10 μA output is enabled 0 = 10 μA output is disabled

REGISTER 26-2: IBIASCONH: CURRENT BIAS GENERATOR 50 µA CURRENT SOURCE CONTROL HIGH REGISTER

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	SHRSRCEN3	SHRSNKEN3	GENSRCEN3	GENSNKEN3	SRCEN3	SNKEN3
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	SHRSRCEN2	SHRSNKEN2	GENSRCEN2	GENSNKEN2	SRCEN2	SNKEN2
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13 SHRSRCEN3: Share Source Enable for Output #3 bit

1 = Sourcing Current Mirror mode is enabled (uses reference from another source)

0 = Sourcing Current Mirror mode is disabled

bit 12 SHRSNKEN3: Share Sink Enable for Output #3 bit

1 = Sinking Current Mirror mode is enabled (uses reference from another source)

0 = Sinking Current Mirror mode is disabled

bit 11 **GENSRCEN3:** Generated Source Enable for Output #3 bit

1 = Source generates the current source mirror reference

0 = Source does not generate the current source mirror reference

bit 10 **GENSNKEN3:** Generated Sink Enable for Output #3 bit

1 = Source generates the current sink mirror reference

0 = Source does not generate the current sink mirror reference

bit 9 SRCEN3: Source Enable for Output #3 bit

1 = Current source is enabled

0 = Current source is disabled

bit 8 SNKEN3: Sink Enable for Output #3 bit

1 = Current sink is enabled

0 = Current sink is disabled

bit 7-6 **Unimplemented:** Read as '0'

bit 5 SHRSRCEN2: Share Source Enable for Output #2 bit

1 = Sourcing Current Mirror mode is enabled (uses reference from another source)

0 = Sourcing Current Mirror mode is disabled

bit 4 SHRSNKEN2: Share Sink Enable for Output #2 bit

1 = Sinking Current Mirror mode is enabled (uses reference from another source)

0 = Sinking Current Mirror mode is disabled

bit 3 GENSRCEN2: Generated Source Enable for Output #2 bit

1 = Source generates the current source mirror reference

0 = Source does not generate the current source mirror reference

bit 2 GENSNKEN2: Generated Sink Enable for Output #2 bit

1 = Source generates the current sink mirror reference

0 = Source does not generate the current sink mirror reference

bit 1 SRCEN2: Source Enable for Output #2 bit

1 = Current source is enabled

0 = Current source is disabled

bit 0 SNKEN2: Sink Enable for Output #2 bit

1 = Current sink is enabled

0 = Current sink is disabled

REGISTER 26-3: IBIASCONL: CURRENT BIAS GENERATOR 50 µA CURRENT SOURCE CONTROL LOW REGISTER

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	SHRSRCEN1	SHRSNKEN1	GENSRCEN1	GENSNKEN1	SRCEN1	SNKEN1
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	SHRSRCEN0	SHRSNKEN0	GENSRCEN0	GENSNKEN0	SRCEN0	SNKEN0
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13 SHRSRCEN1: Share Source Enable for Output #1 bit

1 = Sourcing Current Mirror mode is enabled (uses reference from another source)

0 = Sourcing Current Mirror mode is disabled

bit 12 SHRSNKEN1: Share Sink Enable for Output #1 bit

1 = Sinking Current Mirror mode is enabled (uses reference from another source)

0 = Sinking Current Mirror mode is disabled

bit 11 **GENSRCEN1:** Generated Source Enable for Output #1 bit

1 = Source generates the current source mirror reference

0 = Source does not generate the current source mirror reference

bit 10 **GENSNKEN1:** Generated Sink Enable for Output #1 bit

1 = Source generates the current sink mirror reference

0 = Source does not generate the current sink mirror reference

bit 9 SRCEN1: Source Enable for Output #1 bit

1 = Current source is enabled0 = Current source is disabled

bit 8 SNKEN1: Sink Enable for Output #1 bit

1 = Current sink is enabled

0 = Current sink is disabled

bit 7-6 **Unimplemented:** Read as '0'

bit 5 SHRSRCEN0: Share Source Enable for Output #0 bit

1 = Sourcing Current Mirror mode is enabled (uses reference from another source)

0 = Sourcing Current Mirror mode is disabled

bit 4 SHRSNKEN0: Share Sink Enable for Output #0 bit

1 = Sinking Current Mirror mode is enabled (uses reference from another source)

0 = Sinking Current Mirror mode is disabled

bit 3 **GENSRCENO:** Generated Source Enable for Output #0 bit

1 = Source generates the current source mirror reference

0 = Source does not generate the current source mirror reference

bit 2 **GENSNKEN0:** Generated Sink Enable for Output #0 bit

1 = Source generates the current sink mirror reference

0 = Source does not generate the current sink mirror reference

bit 1 SRCEN0: Source Enable for Output #0 bit

1 = Current source is enabled

0 = Current source is disabled

bit 0 SNKEN0: Sink Enable for Output #0 bit

1 = Current sink is enabled


0 = Current sink is disabled

27.0 OPERATIONAL AMPLIFIER

Note: Some device variants support only two op amp instances. Refer to Table 1 and Table 2 for availability.

The dsPIC33CK256MP508 family implements three instances of operational amplifiers (op amps). The op amps can be used for a wide variety of purposes, including signal conditioning and filtering. The three op amps are functionally identical. The block diagram for a single amplifier is shown in Figure 27-1.

FIGURE 27-1: SINGLE OPERATIONAL AMPLIFIER BLOCK DIAGRAM



The op amps are controlled by two SFR registers: AMPCON1L and AMPCON1H. They remain in a low-power state until the AMPON bit is set. Each op amp can then be enabled independently by setting the corresponding AMPENx bit (x = 1, 2, 3).

The NCHDISx bit provides some flexibility regarding input range verses Integral Nonlinearity (INL). When NCHDISx = 0 (default), the op amps have a wider input voltage range (see Table 33-41 in **Section 33.0 "Electrical Characteristics"**). When NCHDISx = 1, the wider input range is traded for improved INL performance (lower INL).

27.1 Operational Amplifier Control Registers

REGISTER 27-1: AMPCON1L: OP AMP CONTROL REGISTER LOW

R/W-0	U-0						
AMPON	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	AMPEN3	AMPEN2	AMPEN1
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 AMPON: Op Amp Enable/On bit

1 = Enables op amp modules if their respective AMPENx bits are also asserted

0 = Disables all op amp modules

bit 14-3 **Unimplemented:** Read as '0'

bit 2 AMPEN3: Op Amp #3 Enable bit

1 = Enables Op Amp #3 if the AMPON bit is also asserted

0 = Disables Op Amp #3

bit 1 AMPEN2: Op Amp #2 Enable bit

1 = Enables Op Amp #2 if the AMPON bit is also asserted

0 = Disables Op Amp #2

bit 0 AMPEN1: Op Amp #1 Enable bit

1 = Enables Op Amp #1 if the AMPON bit is also asserted

0 = Disables Op Amp #1

REGISTER 27-2: AMPCON1H: OP AMP CONTROL REGISTER HIGH

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_	_	_	NCHDIS3	NCHDIS2	NCHDIS1
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-3 **Unimplemented:** Read as '0'

bit 2 NCHDIS3: Op Amp #3 N Channel Disable bit

1 = Disables Op Amp #3 N channels input stage; reduced INL, but lowered input voltage range

0 = Wide input range for Op Amp #3

bit 1 NCHDIS2: Op Amp #2 N Channel Disable bit

1 = Disables Op Amp #2 N channels input stage; reduced INL, but lowered input voltage range

0 = Wide input range for Op Amp #2

bit 0 NCHDIS1: Op Amp #1 N Channel Disable bit

1 = Disables Op Amp #1 N channels input stage; reduced INL, but lowered input voltage range

0 = Wide input range for Op Amp #1

NOTES:			
NOTES.			

28.0 DEADMAN TIMER (DMT)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Deadman Timer (DMT)" (www.microchip.com/DS70005155) in the "dsPIC33/PIC24 Family Reference Manual".

The primary function of the Deadman Timer (DMT) is to interrupt the processor in the event of a software malfunction. The DMT, which works on the system clock, is a free-running instruction fetch timer, which is clocked


whenever an instruction fetch occurs, until a count match occurs. Instructions are not fetched when the processor is in Sleep mode.

DMT can be enabled in the Configuration fuse or by software in the DMTCON register by setting the ON bit. The DMT consists of a 32-bit counter with a time-out count match value, as specified by the two 16-bit Configuration Fuse registers: FDMTCNTL and FDMTCNTH.

A DMT is typically used in mission-critical and safety-critical applications, where any single failure of the software functionality and sequencing must be detected.

Figure 28-1 shows a block diagram of the Deadman Timer module.

FIGURE 28-1: DEADMAN TIMER BLOCK DIAGRAM



28.1 Deadman Timer Control Registers

REGISTER 28-1: DMTCON: DEADMAN TIMER CONTROL REGISTER

R/W-0	U-0						
ON ⁽¹⁾	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15 **ON:** DMT Module Enable bit⁽¹⁾

1 = Deadman Timer module is enabled0 = Deadman Timer module is not enabled

bit 14-0 **Unimplemented:** Read as '0'

Note 1: This bit has control only when DMTDIS = 0 in the FDMT register.

REGISTER 28-2: DMTPRECLR: DEADMAN TIMER PRECLEAR REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
	STEP1<7:0>								
bit 15							bit 8		

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 STEP1<7:0>: DMT Preclear Enable bits

01000000 = Enables the Deadman Timer preclear (Step 1)

All Other

Write Patterns = Sets the BAD1 flag; these bits are cleared when a DMT Reset event occurs.

STEP1<7:0> bits are also cleared if the STEP2<7:0> bits are loaded with the correct

value in the correct sequence.

bit 7-0 **Unimplemented:** Read as '0'

REGISTER 28-3: DMTCLR: DEADMAN TIMER CLEAR REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
STEP2<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0' bit 7-0 **STEP2<7:0>:** DMT Clear Timer bits

00001000
 = Clears STEP1<7:0>, STEP2<7:0> and the Deadman Timer if preceded by the correct loading of the STEP1<7:0> bits in the correct sequence. The write to these bits may be verified by reading the DMTCNTL/H register and observing the counter being reset.

All Other

Write Patterns = Sets the BAD2 bit; the value of STEP1<7:0> will remain unchanged and the new value being written to STEP2<7:0> will be captured. These bits are cleared when a DMT Reset event occurs.

REGISTER 28-4: DMTSTAT: DEADMAN TIMER STATUS REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_	_	_	_
bit 15							bit 8

HC/R-0	HC/R-0	HC/R-0	U-0	U-0	U-0	U-0	R-0
BAD1	BAD2	DMTEVENT	_	_	_	_	WINOPN
bit 7							bit 0

Legend: HC = Hardware Clearable bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-8 **Unimplemented:** Read as '0'

bit 7 BAD1: Deadman Timer Bad STEP1<7:0> Value Detect bit

1 = Incorrect STEP1<7:0> value was detected 0 = Incorrect STEP1<7:0> value was not detected

bit 6 BAD2: Deadman Timer Bad STEP2<7:0> Value Detect bit

1 = Incorrect STEP2<7:0> value was detected 0 = Incorrect STEP2<7:0> value was not detected

bit 5 **DMTEVENT:** Deadman Timer Event bit

 $_1$ = Deadman Timer event was detected (counter expired, or bad STEP1<7:0> or STEP2<7:0> value

was entered prior to counter increment)

0 = Deadman Timer event was not detected

bit 4-1 **Unimplemented:** Read as '0'

bit 0 WINOPN: Deadman Timer Clear Window bit

1 = Deadman Timer clear window is open

0 = Deadman Timer clear window is not open

REGISTER 28-5: DMTCNTL: DEADMAN TIMER COUNT REGISTER LOW

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0				
	COUNTER<15:8>										
bit 15							bit 8				

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			COUNTE	ER<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **COUNTER<15:0>:** Read Current Contents of Lower DMT Counter bits

REGISTER 28-6: DMTCNTH: DEADMAN TIMER COUNT REGISTER HIGH

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			COUNTE	R<31:24>			
bit 15							bit 8

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0
			COUNTE	R<23:16>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 COUNTER<31:16>: Read Current Contents of Higher DMT Counter bits

REGISTER 28-7: DMTPSCNTL: DMT POST-CONFIGURE COUNT STATUS REGISTER LOW

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y		
PSCNT<15:8>									
bit 15							bit 8		

Ry	R-y								
PSCNT<7:0>									
bit 7							bit 0		

Legend: y = Value from Configuration bit on POR

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 PSCNT<15:0>: Lower DMT Instruction Count Value Configuration Status bits

This is always the value of the FDMTCNTL Configuration register.

REGISTER 28-8: DMTPSCNTH: DMT POST-CONFIGURE COUNT STATUS REGISTER HIGH

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y	
PSCNT<31:24>								
bit 15							bit 8	

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y			
PSCNT<23:16>										
bit 7							bit 0			

Legend: y = Value from Configuration bit on POR

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PSCNT<31:16>:** Higher DMT Instruction Count Value Configuration Status bits This is always the value of the FDMTCNTH Configuration register.

REGISTER 28-9: DMTPSINTVL: DMT POST-CONFIGURE INTERVAL STATUS REGISTER LOW

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y	
PSINTV<15:8>								
bit 15							bit 8	

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y	
PSINTV<7:0>								
bit 7							bit 0	

Legend: y = Value from Configuration bit on POR

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PSINTV<15:0>:** Lower DMT Window Interval Configuration Status bits

This is always the value of the FDMTIVTL Configuration register.

REGISTER 28-10: DMTPSINTVH: DMT POST-CONFIGURE INTERVAL STATUS REGISTER HIGH

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y
PSINTV<31:24>							
bit 15							bit 8

R-y	R-y	R-y	R-y	R-y	R-y	R-y	R-y		
PSINTV<23:16>									
bit 7							bit 0		

Legend: y = Value from Configuration bit on POR

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 **PSINTV<31:16>:** Higher DMT Window Interval Configuration Status bits

This is always the value of the FDMTIVTH Configuration register.

REGISTER 28-11: DMTHOLDREG: DMT HOLD REGISTER⁽¹⁾

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
UPRCNT<15:8>									
bit 15							bit 8		

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
UPRCNT<7:0>									
bit 7							bit 0		

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 UPRCNT<15:0>: DMTCNTH Register Value when DMTCNTL and DMTCNTH were Last Read bits

Note 1: The DMTHOLDREG register is initialized to '0' on Reset, and is only loaded when the DMTCNTL and DMTCNTH registers are read.

29.0 POWER-SAVING FEATURES

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Watchdog Timer and Power-Saving Modes" (www.microchip.com/DS70615) in the "dsPIC33/PIC24 Family Reference Manual".

The dsPIC33CK256MP508 family devices provide the ability to manage power consumption by selectively managing clocking to the CPU and the peripherals. In general, a lower clock frequency and a reduction in the number of peripherals being clocked constitutes lower consumed power.

dsPIC33CK256MP508 family devices can manage power consumption in four ways:

- Clock Frequency
- · Instruction-Based Sleep and Idle modes
- · Software-Controlled Doze mode
- · Selective Peripheral Control in Software

Combinations of these methods can be used to selectively tailor an application's power consumption while still maintaining critical application features, such as timing-sensitive communications.

29.1 Clock Frequency and Clock Switching

The dsPIC33CK256MP508 family devices allow a wide range of clock frequencies to be selected under application control. If the system clock configuration is not locked, users can choose low-power or high-precision oscillators by simply changing the NOSCx bits (OSCCON<10:8>). The process of changing a system clock during operation, as well as limitations to the process, are discussed in more detail in Section 9.0 "Oscillator with High-Frequency PLL".

29.2 Instruction-Based Power-Saving Modes

The dsPIC33CK256MP508 family devices have two special power-saving modes that are entered through the execution of a special PWRSAV instruction. Sleep mode stops clock operation and halts all code execution. Idle mode halts the CPU and code execution, but allows peripheral modules to continue operation. The assembler syntax of the PWRSAV instruction is shown in Example 29-1.

Note: SLEEP_MODE and IDLE_MODE are constants defined in the assembler include file for the selected device.

Sleep and Idle modes can be exited as a result of an enabled interrupt, WDT time-out or a device Reset. When the device exits these modes, it is said to "wake-up".

EXAMPLE 29-1: PWRSAV INSTRUCTION SYNTAX IN ASSEMBLY

```
PWRSAV #SLEEP_MODE ; Put the device into Sleep mode
PWRSAV #IDLE_MODE ; Put the device into Idle mode
```

EXAMPLE 29-2: PWRSAV INSTRUCTION SYNTAX IN C LANGUAGE

```
Sleep() // Put the device into Sleep mode
Idle () // Put the device into Idle mode
```

29.2.1 SLEEP MODE

The following occurs in Sleep mode:

- The system clock source is shut down. If an on-chip oscillator is used, it is turned off.
- The device current consumption is reduced to a minimum, provided that no I/O pin is sourcing current.
- The Fail-Safe Clock Monitor does not operate, since the system clock source is disabled.
- The LPRC clock continues to run in Sleep mode if the WDT is enabled.
- The WDT, if enabled, is automatically cleared prior to entering Sleep mode.
- Some device features or peripherals can continue to operate. This includes items such as the Input Change Notification on the I/O ports or peripherals that use an External Clock input.
- Any peripheral that requires the system clock source for its operation is disabled.

The device wakes up from Sleep mode on any of the these events:

- · Any interrupt source that is individually enabled
- · Any form of device Reset
- · A WDT time-out

On wake-up from Sleep mode, the processor restarts with the same clock source that was active when Sleep mode was entered.

For optimal power savings, the regulators can be configured to go into standby when Sleep mode is entered by clearing the VREGS (RCON<8>) bit (default configuration).

If the application requires a faster wake-up time, and can accept higher current requirements, the VREGS (RCON<8>) bit can be set to keep the regulators active during Sleep mode. The available Low-Power Sleep modes are shown in Table 29-1. Additional regulator information is available in Section 30.4 "On-Chip Voltage Regulators".

TABLE 29-1: LOW-POWER SLEEP MODES

Relative Power	LPWREN	VREGS	MODE
Highest	0	1	Full power, active
_	0	0	Full power, standby
_	1(1)	1	Low power, active
Lowest	1(1)	0	Low power, standby

Note 1: Low-Power modes, when LPWREN = 1, can only be used in the industrial temperature range.

29.2.2 IDLE MODE

The following occurs in Idle mode:

- · The CPU stops executing instructions.
- · The WDT is automatically cleared.
- The system clock source remains active. By default, all peripheral modules continue to operate normally from the system clock source, but can also be selectively disabled (see Section 29.4 "Peripheral Module Disable").
- If the WDT or FSCM is enabled, the LPRC also remains active.

The device wakes from Idle mode on any of these events:

- · Any interrupt that is individually enabled
- · Any device Reset
- · A WDT time-out

On wake-up from Idle mode, the clock is reapplied to the CPU and instruction execution will begin (2-4 clock cycles later), starting with the instruction following the PWRSAV instruction or the first instruction in the ISR.

All peripherals also have the option to discontinue operation when Idle mode is entered to allow for increased power savings. This option is selectable in the control register of each peripheral; for example, the SIDL bit in the Timer1 Control register (T1CON<13>).

29.2.3 INTERRUPTS COINCIDENT WITH POWER SAVE INSTRUCTIONS

Any interrupt that coincides with the execution of a PWRSAV instruction is held off until entry into Sleep or Idle mode has completed. The device then wakes up from Sleep or Idle mode.

29.3 Doze Mode

The preferred strategies for reducing power consumption are changing clock speed and invoking one of the power-saving modes. In some circumstances, this cannot be practical. For example, it may be necessary for an application to maintain uninterrupted synchronous communication, even while it is doing nothing else. Reducing system clock speed can introduce communication errors, while using a power-saving mode can stop communications completely.

Doze mode is a simple and effective alternative method to reduce power consumption while the device is still executing code. In this mode, the system clock continues to operate from the same source and at the same speed. Peripheral modules continue to be clocked at the same speed, while the CPU clock speed is reduced. Synchronization between the two clock domains is maintained, allowing the peripherals to access the SFRs while the CPU executes code at a slower rate.

Doze mode is enabled by setting the DOZEN bit (CLKDIV<11>). The ratio between peripheral and core clock speed is determined by the DOZE<2:0> bits (CLKDIV<14:12>). There are eight possible configurations, from 1:1 to 1:128, with 1:1 being the default setting.

Programs can use Doze mode to selectively reduce power consumption in event-driven applications. This allows clock-sensitive functions, such as synchronous communications, to continue without interruption while the CPU Idles, waiting for something to invoke an interrupt routine. An automatic return to full-speed CPU operation on interrupts can be enabled by setting the ROI bit (CLKDIV<15>). By default, interrupt events have no effect on Doze mode operation.

29.4 Peripheral Module Disable

The Peripheral Module Disable (PMD) registers provide a method to disable a peripheral module by stopping all clock sources supplied to that module. When a peripheral is disabled using the appropriate PMD control bit, the peripheral is in a minimum power consumption state. The control and status registers associated with the peripheral are also disabled, so writes to those registers do not have any effect and read values are invalid.

A peripheral module is enabled only if both the associated bit in the PMD register is cleared and the peripheral is supported by the specific dsPIC® DSC variant. If the peripheral is present in the device, it is enabled in the PMD register by default.

Note 1: If a PMD bit is set, the corresponding module is disabled after a delay of one instruction cycle. Similarly, if a PMD bit is cleared, the corresponding module is enabled after a delay of one instruction cycle (assuming the module control registers are already configured to enable module operation).

29.5 Power-Saving Resources

Many useful resources are provided on the main product page of the Microchip website for the devices listed in this data sheet. This product page contains the latest updates and additional information.

29.5.1 KEY RESOURCES

- "Watchdog Timer and Power-Saving Modes" (DS70615) in the "dsPIC33/PIC24 Family Reference Manual"
- · Code Samples
- Application Notes
- · Software Libraries
- · Webinars
- All related "dsPIC33/PIC24 Family Reference Manual" Sections
- · Development Tools

REGISTER 29-1: PMD1: PERIPHERAL MODULE DISABLE 1 CONTROL REGISTER

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	U-0
_	_	_	_	T1MD	QEI1MD	PWMMD	_
bit 15							bit 8

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
I2C1MD	U2MD	U1MD	SPI2MD	SPI1MD	_	C1MD ⁽¹⁾	ADC1MD
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 Unimplemented: Read as '0' bit 11 T1MD: Timer1 Module Disable bit 1 = Timer1 module is disabled 0 = Timer1 module is enabled bit 10 **QEI1MD:** QEI1 Module Disable bit 1 = QEI1 module is disabled 0 = QEI1 module is enabled bit 9 PWMMD: PWM Module Disable bit 1 = PWM module is disabled 0 = PWM module is enabled bit 8 Unimplemented: Read as '0' bit 7

I2C1MD: I2C1 Module Disable bit

1 = I2C1 module is disabled 0 = I2C1 module is enabled

bit 6 U2MD: UART2 Module Disable bit 1 = UART2 module is disabled

0 = UART2 module is enabled

bit 5 U1MD: UART1 Module Disable bit

1 = UART1 module is disabled 0 = UART1 module is enabled

bit 4 SPI2MD: SPI2 Module Disable bit

> 1 = SPI2 module is disabled 0 = SPI2 module is enabled

bit 3 SPI1MD: SPI1 Module Disable bit

> 1 = SPI1 module is disabled 0 = SPI1 module is enabled

bit 2 Unimplemented: Read as '0'

C1MD: CAN1 Module Disable bit(1) bit 1

> 1 = CAN1 module is disabled 0 = CAN1 module is enabled

bit 0 ADC1MD: ADC Module Disable bit

> 1 = ADC module is disabled 0 = ADC module is enabled

Note 1: Availability is dependent on the supported peripherals, refer to Table 1 and Table 2.

REGISTER 29-2: PMD2: PERIPHERAL MODULE DISABLE 2 CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	CCP9MD
bit 15							bit 8

| R/W-0 |
|--------|--------|--------|--------|--------|--------|--------|--------|
| CCP8MD | CCP7MD | CCP6MD | CCP5MD | CCP4MD | CCP3MD | CCP2MD | CCP1MD |
| bit 7 | | | | | | | bit 0 |

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-9 **Unimplemented:** Read as '0'

bit 8 CCP9MD: MCCP9 Module Disable bit

1 = MCCP9 module is disabled 0 = MCCP9 module is enabled

bit 7 CCP8MD: SCCP8 Module Disable bit

1 = SCCP8 module is disabled 0 = SCCP8 module is enabled

bit 6 CCP7MD: SCCP7 Module Disable bit

1 = SCCP7 module is disabled 0 = SCCP7 module is enabled

bit 5 CCP6MD: SCCP6 Module Disable bit

1 = SCCP6 module is disabled 0 = SCCP6 module is enabled

bit 4 CCP5MD: SCCP5 Module Disable bit

1 = SCCP5 module is disabled 0 = SCCP5 module is enabled

bit 3 CCP4MD: SCCP4 Module Disable bit

1 = SCCP4 module is disabled 0 = SCCP4 module is enabled

bit 2 CCP3MD: SCCP3 Module Disable bit

1 = SCCP3 module is disabled 0 = SCCP3 module is enabled

bit 1 CCP2MD: SCCP2 Module Disable bit

1 = SCCP2 module is disabled0 = SCCP2 module is enabled

bit 0 CCP1MD: SCCP1 Module Disable bit

1 = SCCP1 module is disabled 0 = SCCP1 module is enabled

REGISTER 29-3: PMD3: PERIPHERAL MODULE DISABLE 3 CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	PMPMD ⁽¹⁾
bit 15							bit 8

R/W-0	U-0	R/W-0	U-0	R/W-0	R/W-0	R/W-0	U-0
CRCMD	_	QEI2MD	_	U3MD	I2C3MD	I2C2MD	_
bit 7							bit 0

Legend:

bit 6

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-9 **Unimplemented:** Read as '0'

bit 8 **PMPMD:** PMP Module Disable bit⁽¹⁾

1 = PMP module is disabled

0 = PMP module is enabled

bit 7 CRCMD: CRC Module Disable bit

1 = CRC module is disabled 0 = CRC module is enabled

Unimplemented: Read as '0'

bit 5 **QEI2MD:** QEI2 Module Disable bit

1 = QEI2 module is disabled0 = QEI2 module is enabled

bit 4 **Unimplemented:** Read as '0'

bit 3 **U3MD:** UART3 Module Disable bit

1 = UART3 module is disabled

0 = UART3 module is enabled

bit 2 I2C3MD: I2C3 Module Disable bit

1 = I2C3 module is disabled

0 = I2C3 module is enabled

bit 1 I2C2MD: I2C2 Module Disable bit

1 = I2C2 module is disabled

0 = I2C2 module is enabled

bit 0 **Unimplemented:** Read as '0'

Note 1: Availability is dependent on the supported peripherals, refer to Table 1 and Table 2.

REGISTER 29-4: PMD4: PERIPHERAL MODULE DISABLE 4 CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
_	_	_	_	_			
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	U-0	U-0	U-0
_	_	_	_	REFOMD	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-4 **Unimplemented:** Read as '0'

bit 3 REFOMD: Reference Clock Module Disable bit

1 = Reference clock module is disabled0 = Reference clock module is enabled

bit 2-0 **Unimplemented:** Read as '0'

REGISTER 29-5: PMD6: PERIPHERAL MODULE DISABLE 6 CONTROL REGISTER

U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	_	_	DMA3MD	DMA2MD	DMA1MD	DMA0MD
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
_	_	_	_	_	_	_	SPI3MD
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-12 **Unimplemented:** Read as '0'

bit 11 DMA3MD: DMA3 Module Disable bit

1 = DMA3 module is disabled 0 = DMA3 module is enabled

bit 10 DMA2MD: DMA2 Module Disable bit

1 = DMA2 module is disabled0 = DMA2 module is enabled

bit 9 **DMA1MD:** DMA1 Module Disable bit

1 = DMA1 module is disabled 0 = DMA1 module is enabled

bit 8 DMA0MD: DMA0 Module Disable bit

1 = DMA0 module is disabled0 = DMA0 module is enabled

bit 7-1 **Unimplemented:** Read as '0' bit 0 **SPI3MD:** SPI3 Module Disable bit

1 = SPI3 module is disabled 0 = SPI3 module is enabled

REGISTER 29-6: PMD7: PERIPHERAL MODULE DISABLE 7 CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0	R/W-0
_	_	_			CMP3MD	CMP2MD	CMP1MD
bit 15							bit 8

U-0	U-0	U-0	U-0	R/W-0	U-0	U-0	U-0
_	_	_	_	PTGMD	_	_	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-11 **Unimplemented:** Read as '0'

bit 10 **CMP3MD:** Comparator 3 Module Disable bit

1 = Comparator 3 module is disabled0 = Comparator 3 module is enabled

bit 9 CMP2MD: Comparator 2 Module Disable bit

1 = Comparator 2 module is disabled0 = Comparator 2 module is enabled

bit 8 **CMP1MD:** Comparator 1 Module Disable bit

1 = Comparator 1 module is disabled0 = Comparator 1 module is enabled

bit 7-4 Unimplemented: Read as '0'

bit 3 **PTGMD**: PTG Module Disable bit

1 = PTG module is disabled 0 = PTG module is enabled

bit 2-0 Unimplemented: Read as '0'

REGISTER 29-7: PMD8: PERIPHERAL MODULE DISABLE 8 CONTROL REGISTER

U-0	U-0	R/W-0	R/W-0	R/W-0	U-0	U-0	R/W-0
_	_	OPAMPMD	SENT2MD	SENT1MD	_	_	DMTMD
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0
_	_	CLC4MD	CLC3MD	CLC2MD	CLC1MD	BIASMD	_
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-14 **Unimplemented:** Read as '0'

bit 13 **OPAMPMD:** Op Amp Module Disable bit

1 = Op amp modules are disabled 0 = Op amp modules are enabled

bit 12 SENT2MD: SENT2 Module Disable bit

1 = SENT2 module is disabled 0 = SENT2 module is enabled

bit 11 SENT1MD: SENT1 Module Disable bit

1 = SENT1 module is disabled 0 = SENT1 module is enabled

bit 10-9 **Unimplemented:** Read as '0'

bit 8 **DMTMD:** Deadman Timer Module Disable bit

1 = DMT module is disabled 0 = DMT module is enabled

bit 7-6 **Unimplemented:** Read as '0'

bit 5 CLC4MD: CLC4 Module Disable bit

1 = CLC4 module is disabled 0 = CLC4 module is enabled

bit 4 CLC3MD: CLC3 Module Disable bit

1 = CLC3 module is disabled 0 = CLC3 module is enabled

bit 3 CLC2MD: CLC2 Module Disable bit

1 = CLC2 module is disabled 0 = CLC2 module is enabled

bit 2 CLC1MD: CLC1 Module Disable bit

1 = CLC1 module is disabled0 = CLC1 module is enabled

bit 1 BIASMD: Constant-Current Source Module Disable bit

1 = Constant-current source module is disabled0 = Constant-current source module is enabled

bit 0 **Unimplemented:** Read as '0'

ADC1MD CCP1MD **SPI3MD** Bit 0 BIASMD 12C2MD C1MD Bit 1 CLC1MD **CCP3MD** 12C3MD Bit 2 CCP4MD CLC2MD SP11MD REFOMD PTGMD U3MD Bit 3 SPI2MD **CCP5MD CLC3MD** Bit 4 CLC4MD CCP6MD QE12MD U1MD Bit 5 CCP7MD Bit 6 UZMD CCP8MD CRCMD Bit 7 PMPMD DMTMD CCP9MD **DMA0MD** CMP1MD Bit 8 DMA1MD CMP2MD PWMMD Bit 9 DMA2MD CMP3MD QEIMD Bit 10 SENT1MD **DMA3MD** Bit 11 T1MD OPAMPMD SENT2MD Bit 12 **PMD REGISTERS** Bit 13 Bit14 Bit 15 **FABLE 29-2:** Register PMD2 PMD3 PMD6 PMD8 PMD1 PMD4 PMD7

NOTES:			

30.0 SPECIAL FEATURES

Note: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to the related section of the "dsPIC33/PIC24 Family Reference Manual", which is available from the Microchip website (www.microchip.com).

The dsPIC33CK256MP508 family devices include several features intended to maximize application flexibility and reliability, and minimize cost through elimination of external components. These are:

- · Flexible Configuration
- Watchdog Timer (WDT)
- Code Protection and CodeGuard™ Security
- · JTAG Boundary Scan Interface
- In-Circuit Serial Programming™ (ICSP™)
- · In-Circuit Emulation
- Brown-out Reset (BOR)

30.1 Configuration Bits

In dsPIC33CK256MP508 family devices, the Configuration Words are implemented as volatile memory. This means that configuration data will get loaded to volatile memory (from the Flash Configuration Words) each time the device is powered up. Configuration data is stored at the end of the on-chip program memory space, known as the Flash Configuration Words. Their specific locations are shown in Table 30-1. The configuration data is automatically loaded from the Flash Configuration Words to the proper Configuration Shadow registers during device Resets. The BSEQx bits (FBTSEQ<11:0>) determine which panel is the Active Partition at start-up and the Configuration Words from that panel are loaded into the Configuration Shadow registers.

Note: Configuration data is reloaded on all types of device Resets.

When creating applications for these devices, users should always specifically allocate the location of the Flash Configuration Words for configuration data in their code for the compiler. This is to make certain that program code is not stored in this address when the code is compiled. Program code executing out of configuration space will cause a device Reset.

Note: Performing a page erase operation on the last page of program memory clears the Flash Configuration Words.

TABLE 30-1: dsPIC33CKXXXMPX0X CONFIGURATION ADDRESSES

Dominton Name	Single F	Partition	Dual Partit	ion, Active	Dual Partiti	on, Inactive
Register Name	256k	128k	256k	128k	256k	128k
FSEC ⁽²⁾	0x02BF00	0x015F00	0x015F00	0x00AF00	0x415F00	0x40AF00
FBSLIM ⁽²⁾	0x02BF10	0x015F10	0x015F10	0x00AF10	0x415F10	0x40AF10
FSIGN ⁽²⁾	0x02BF14	0x015F14	0x015F14	0x00AF14	0x415F14	0x40AF14
FOSCSEL	0x02BF18	0x015F18	0x015F18	0x00AF18	0x415F18	0x40AF18
FOSC	0x02BF1C	0x015F1C	0x015F1C	0x00AF1C	0x415F1C	0x40AF1C
FWDT	0x02BF20	0x015F20	0x015F20	0x00AF20	0x415F20	0x40AF20
FPOR	0x02BF24	0x015F24	0x015F24	0x00AF24	0x415F24	0x40AF24
FICD	0x02BF28	0x015F28	0x015F28	0x00AF28	0x415F28	0x40AF28
FDMTIVTL	0x02BF2C	0x015F2C	0x015F2C	0x00AF2C	0x415F2C	0x40AF2C
FDMTIVTH	0x02BF30	0x015F30	0x015F30	0x00AF30	0x415F30	0x40AF30
FDMTCNTL	0x02BF34	0x015F34	0x015F34	0x00AF34	0x415F34	0x40AF34
FDMTCNTH	0x02BF38	0x015F38	0x015F38	0x00AF38	0x415F38	0x40AF38
FDMT	0x02BF3C	0x015F3C	0x015F3C	0x00AF3C	0x415F3C	0x40AF3C
FDEVOPT	0x02BF40	0x015F40	0x015F40	0x00AF40	0x415F40	0x40AF40
FALTREG	0x02BF44	0x015F44	0x015F44	0x00AF44	0x415F44	0x40AF44
FBTSEQ	0x02BFFC	0x015FFC	0x015FFC	0x00AFFC	0x415FFC	0x40AFFC
FBOOT ⁽¹⁾			0x80	1800		

Note 1: FBOOT resides in calibration memory space.

2: Changes to the Inactive Partition Configuration Words affect how the Active Partition accesses the Inactive Partition.

TABLE 30-2: dsPIC33CKXXMPX0X CONFIGURATION ADDRESSES

Dominton Name	Single F	Partition	Dual Partit	ion, Active	Dual Partiti	on, Inactive
Register Name	64k	32k	64k	32k	64k	32k
FSEC ⁽²⁾	0x00AF00	0x005F00	0x005F00	0x002F00	0x405F00	0x402F00
FBSLIM ⁽²⁾	0x00AF10	0x005F10	0x005F10	0x002F10	0x405F10	0x402F10
FSIGN ⁽²⁾	0x00AF14	0x005F14	0x005F14	0x002F14	0x405F14	0x402F14
FOSCSEL	0x00AF18	0x005F18	0x005F18	0x002F18	0x405F18	0x402F18
FOSC	0x00AF1C	0x005F1C	0x005F1C	0x002F1C	0x405F1C	0x402F1C
FWDT	0x00AF20	0x005F20	0x005F20	0x002F20	0x405F20	0x402F20
FPOR	0x00AF24	0x005F24	0x005F24	0x002F24	0x405F24	0x402F24
FICD	0x00AF28	0x005F28	0x005F28	0x002F28	0x405F28	0x402F28
FDMTIVTL	0x00AF2C	0x005F2C	0x005F2C	0x002F2C	0x405F2C	0x402F2C
FDMTIVTH	0x00AF30	0x005F30	0x005F30	0x002F30	0x405F30	0x402F30
FDMTCNTL	0x00AF34	0x005F34	0x005F34	0x002F34	0x405F34	0x402F34
FDMTCNTH	0x00AF38	0x005F38	0x005F38	0x002F38	0x405F38	0x402F38
FDMT	0x00AF3C	0x005F3C	0x005F3C	0x002F3C	0x405F3C	0x402F3C
FDEVOPT	0x00AF40	0x005F40	0x005F40	0x002F40	0x405F40	0x402F40
FALTREG	0x00AF44	0x005F44	0x005F44	0x002F44	0x405F44	0x402F44
FBTSEQ	0x00AFFC	0x005FFC	0x005FFC	0x002FFC	0x405FFC	0x402FFC
FBOOT ⁽¹⁾			0x80	1800		_

Note 1: FBOOT resides in calibration memory space.

^{2:} Changes to the Inactive Partition Configuration Words affect how the Active Partition accesses the Inactive Partition.

CONFIGURATION REGISTERS MAP TABLE 30-3:

)												
Register Name	Bits 23-16	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
FSEC	I	AIVTDIS	Ι	I	I		CSS<2:0>		CWRP	SSS	GSS<1:0>	GWRP	1	BSEN	BSS<1:0>	1:0>	BWRP
FBSLIM	I	I	1	I							BSLIM<12:0>	Δ					
FSIGN	I	r(2)	1	I	I	I	ı	I	I	ı	I	I	ı	I	I	I	1
FOSCSEL	I	Ι	I	I	1	I	I	I	Ι	IESO	I	I	I	I		FNOSC<2:0>	
FOSC	I	Ι	1	I	XTBST	XTCF(XTCFG<1:0>	I	PLLKEN	FCKS	FCKSM<1:0>	I	I	I	OSCIOFCN	POSCMD<1:0>	D<1:0>
FWDT	I	FWDTEN			SWDTPS<4:0>	^ 0:		WDTW	WDTWIN<1:0>	WINDIS	RCLKSEL<1:0>	=L<1:0>			RWDTPS<4:0>		
FPOR	I	Ι	I	I	I	I	(1)	I	Ι	I	BISTDIS	(1)	(1)	I	I	I	I
FICD	I	NOBTSWP	1	I	1	_	I	I	Ι	(1) ¹	I	JTAGEN	I	_	I	ICS<1:0>	1:0>
FDMTIVTL	I								DMTI	DMTIVT<15:0>							
FDMTIVTH	I								VILMO	DMTIVT<31:16>							
FDMTCNTL	I								DMTC	DMTCNT<15:0>							
FDMTCNTH	I								DMTC	DMTCNT<31:16>							
FDMT	I	I	1	I	1	_	I	I	Ι	I	Ι	-	I	_	I	I	DMTDIS
FDEVOPT	I	I	1	SPI2PIN	1	_	SMBEN	⁽²⁾	⁽²⁾	(1) ¹	I	ALT12C3	ALTI2C2	ALT12C1	L(1)	I	I
FALTREG	I	I		CTXT4<2:0>	٨	_		CTXT3<2:0>		I		CTXT2<2:0>		_		CTXT1<2:0>	
FBTSEQ	IBSEQ<11:4>		IBSEQ<3:0>	<3:0>							BSEQ	BSEQ<11:0>					
FBOOT	I	I	1	I	1	_	I	I	Ι	I	Ι	-	I	_	I	BTMODE<1:0>	E<1:0>
Legend: —	== unimplemented bit, read as '1'; r = reserved bit.	ed bit, read a	18 '1'; r = re	erved bit.													

Legend: Note 1:

Bit reserved, maintain as '1'. Bit reserved, maintain as '0'.

REGISTER 30-1: FSEC CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	U-1	U-1	U-1	R/P0-1	R/PO-1	R/PO-1	R/PO-1
AIVTDIS	_	_	_		CSS<2:0>		CWRP
bit 15							bit 8

R/PO-1	R/PO-1	R/PO-1	U-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
GSS	<1:0>	GWRP	_	BSEN	BSS.	<1:0>	BWRP
bit 7							bit 0

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15 AIVTDIS: Alternate Interrupt Vector Table Disable bit

1 = Disables AIVT
0 = Enables AIVT

bit 14-12 **Unimplemented:** Read as '1'

bit 11-9 CSS<2:0>: Configuration Segment Code Flash Protection Level bits

111 = No protection (other than CWRP write protection)

110 = Standard security 10x = Enhanced security 0xx = High security

bit 8 **CWRP:** Configuration Segment Write-Protect bit

1 = Configuration Segment is not write-protected0 = Configuration Segment is write-protected

bit 7-6 GSS<1:0>: General Segment Code Flash Protection Level bits

11 = No protection (other than GWRP write protection)

10 = Standard security
0x = High security

bit 5 **GWRP:** General Segment Write-Protect bit

1 = User program memory is not write-protected0 = User program memory is write-protected

bit 4 **Unimplemented:** Read as '1'

bit 3 BSEN: Boot Segment Control bit

1 = No Boot Segment

0 = Boot Segment size is determined by BSLIM<12:0>

bit 2-1 BSS<1:0>: Boot Segment Code Flash Protection Level bits

11 = No protection (other than BWRP write protection)

10 = Standard security 0x = High security

bit 0 **BWRP:** Boot Segment Write-Protect bit

1 = User program memory is not write-protected0 = User program memory is write-protected

REGISTER 30-2: FBSLIM CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	U-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
_	_	_			BSLIM<12:8>		
bit 15							bit 8

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
			BSLIN	/1<7:0>			
bit 7							bit 0

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-13 Unimplemented: Read as '1'

bit 12-0 BSLIM<12:0>: Boot Segment Code Flash Page Address Limit bits

Contains the page address of the first active General Segment page. The value to be programmed is the inverted page address, such that programming additional '0's can only increase the Boot Segment size.

REGISTER 30-3: FSIGN CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_		_	_	_	_	_
bit 23							bit 16

r-0	U-1						
_	_	_	_	_	_	_	_
bit 15							bit 8

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 7							bit 0

Legend: r = Reserved bit PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 Unimplemented: Read as '1' bit 15 Reserved: Maintain as '0' Unimplemented: Read as '1'

REGISTER 30-4: FOSCSEL CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 15							bit 8

R/PO-1	U-1	U-1	U-1	U-1	R/PO-1	R/PO-1	R/PO-1
IESO	_	_	_	_		FNOSC<2:0>	
bit 7							bit 0

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-8 **Unimplemented:** Read as '1'

bit 7 **IESO:** Internal External Switchover bit

1 = Internal External Switchover mode is enabled (Two-Speed Start-up is enabled)

0 = Internal External Switchover mode is disabled (Two-Speed Start-up is disabled)

bit 6-3 **Unimplemented:** Read as '1'

bit 2-0 FNOSC<2:0>: Initial Oscillator Source Selection bits

111 = Internal Fast RC (FRC) Oscillator with Postscaler

110 = Backup Fast RC (BFRC)

101 = LPRC Oscillator

100 = Reserved

011 = Primary Oscillator with PLL (XTPLL, HSPLL, ECPLL)

010 = Primary (XT, HS, EC) Oscillator

001 = Internal Fast RC Oscillator with PLL (FRCPLL)

000 = Fast RC (FRC) Oscillator

REGISTER 30-5: FOSC CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	U-1	R/PO-1	R/PO-1	R/PO-1	U-1	R/PO-1
_	_	_	XTBST	XTCF	G<1:0>	_	PLLKEN ⁽¹⁾
bit 15							bit 8

R/PO-1	R/PO-1	U-1	U-1	U-1	R/PO-1	R/PO-1	R/PO-1
FCKSN	Л<1:0>	_		_	OSCIOFNC	POSCN	1D<1:0>
bit 7	7					bit 0	

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-13 **Unimplemented:** Read as '1'

bit 12 XTBST: Oscillator Kick-Start Programmability bit

1 = Boosts the kick-start0 = Default kick-start

bit 11-10 XTCFG<1:0>: Crystal Oscillator Drive Select bits

Current gain programmability for oscillator (output drive).

11 = Gain3 (use for 24-32 MHz crystals)

10 = Gain2 (use for 16-24 MHz crystals)

01 = Gain1 (use for 8-16 MHz crystals)

00 = Gain0 (use for 4-8 MHz crystals)

bit 9 Unimplemented: Read as '1'

bit 8 PLLKEN: PLL Lock Status Control bit⁽¹⁾

1 = PLL lock signal will be used to disable PLL clock output if lock is lost

0 = PLL lock signal is not used; the PLL clock output will not be disabled if lock is lost

bit 7-6 **FCKSM<1:0>:** Clock Switching Mode bits

1x = Clock switching is disabled, Fail-Safe Clock Monitor is disabled

01 = Clock switching is enabled, Fail-Safe Clock Monitor is disabled

00 = Clock switching is enabled, Fail-Safe Clock Monitor is enabled

bit 5-3 **Unimplemented:** Read as '1'

bit 2 **OSCIOFNC:** OSCO Pin Function bit (except in XT and HS modes)

1 = OSCO is the clock output

0 = OSCO is the general purpose digital I/O pin

bit 1-0 POSCMD<1:0>: Primary Oscillator Mode Select bits

11 = Primary Oscillator is disabled

10 = HS Crystal Oscillator mode (10 MHz-32 MHz)

01 = XT Crystal Oscillator mode (3.5 MHz-10 MHz)

00 = EC (External Clock) mode

Note 1: A time-out period will occur when the system clock switching logic requests the PLL clock source and the PLL is not already enabled.

REGISTER 30-6: FWDT CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
FWDTEN				WDTW	IN<1:0>		
bit 15							bit 8

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
WINDIS	RCLKS	EL<1:0>			RWDTPS<4:0	>	
bit 7							bit 0

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15 FWDTEN: Watchdog Timer Enable bit

1 = WDT is enabled in hardware

0 = WDT controller via the ON bit (WDTCONL<15>)

bit 14-10 **SWDTPS<4:0>:** Sleep Mode Watchdog Timer Period Select bits

11111 = Divide by 2 ^ 31 = 2,147,483,648 11110 = Divide by 2 ^ 30 = 1,073,741,824

. . .

00001 = Divide by 2 ^ 1, 2 00000 = Divide by 2 ^ 0, 1

bit 9-8 WDTWIN<1:0>: Watchdog Timer Window Select bits

11 = WDT window is 25% of the WDT period

10 = WDT window is 37.5% of the WDT period

01 = WDT window is 50% of the WDT period

00 = WDT Window is 75% of the WDT period

bit 7 WINDIS: Watchdog Timer Window Enable bit

1 = Watchdog Timer is in Non-Window mode

0 = Watchdog Timer is in Window mode

bit 6-5 RCLKSEL<1:0>: Watchdog Timer Clock Select bits

11 = LPRC clock

10 = Uses FRC when WINDIS = 0, system clock is not INTOSC/LPRC and device is not in Sleep; otherwise, uses INTOSC/LPRC

01 = Uses peripheral clock when system clock is not INTOSC/LPRC and device is not in Sleep; otherwise, uses INTOSC/LPRC

00 = Reserved

bit 4-0 RWDTPS<4:0>: Run Mode Watchdog Timer Period Select bits

 $11111 = Divide by 2 ^ 31 = 2,147,483,648$

11110 = Divide by 2 ^ 30 = 1,073,741,824

. . .

00001 = Divide by 2 ^ 1, 2

00000 = Divide by 2 ^ 0, 1

REGISTER 30-7: FPOR CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	U-1	U-1	U-1	r-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 15							bit 8

U-1	R/PO-1	r-1	r-1	U-1	U-1	U-1	U-1
_	BISTDIS ⁽¹⁾	_	_	_	_	_	_
bit 7							bit 0

Legend: PO = Program Once bit r = Reserved bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-11 Unimplemented: Read as '1' bit 10 Reserved: Maintain as '1' bit 9-7 Unimplemented: Read as '1'

bit 6 BISTDIS: Memory BIST Feature Disable bit (1)

1 = MBIST on Reset feature is disabled 0 = MBIST on Reset feature is enabled

bit 5-4 Reserved: Maintain as '0b11' bit 3-0 Unimplemented: Read as '1'

Note 1: Applies to a Power-on Reset (POR) only.

REGISTER 30-8: FICD CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	U-1						
NOBTSWP	_	_	_	_	_	_	_
bit 15							bit 8

r-1	U-1	R/PO-1	U-1	U-1	U-1	R/PO-1	R/PO-1
_	_	JTAGEN	_	_	_	ICS<	<1:0>
bit 7							bit 0

Legend: PO = Program Once bit r = Reserved bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15 NOBTSWP: BOOTSWP Instruction Disable bit

1 = BOOTSWP instruction is disabled 0 = BOOTSWP instruction is enabled

bit 14-8 Unimplemented: Read as '1'
bit 7 Reserved: Maintain as '1'
bit 6 Unimplemented: Read as '1'
bit 5 JTAGEN: JTAG Enable bit

1 = JTAG port is enabled 0 = JTAG port is disabled

bit 4-2 **Unimplemented:** Read as '1'

bit 1-0 ICS<1:0>: ICD Communication Channel Select bits

11 = Communicates on PGC1 and PGD1 10 = Communicates on PGC2 and PGD2 01 = Communicates on PGC3 and PGD3

00 = Reserved, do not use

REGISTER 30-9: FDMTIVTL CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1		
	DMTIVT<15:8>								
bit 15							bit 8		

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1			
DMTIVT<7:0>										
bit 7		bit 7								

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 Unimplemented: Read as '1'

bit 15-0 **DMTIVT<15:0>:** DMT Window Interval Lower 16 bits

REGISTER 30-10: FDMTIVTH CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1
DMTIVT<31:24>							
bit 15							

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	
DMTIVT<23:16>								
bit 7								

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15-0 **DMTIVT<31:16>:** DMT Window Interval Higher 16 bits

REGISTER 30-11: FDMTCNTL CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_		_	_
bit 23							bit 16

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1			
	DMTCNT<15:8>									
bit 15										

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/P0-1	R/PO-1	
DMTCNT<7:0>								
bit 7				bit 0				

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15-0 DMTCNT<15:0>: DMT Instruction Count Time-out Value Lower 16 bits

REGISTER 30-12: FDMTCNTH CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1		
DMTCNT<31:24>									
bit 15							bit 8		

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1			
	DMTCNT<23:16>									
bit 7							bit 0			

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-16 **Unimplemented:** Read as '1'

bit 15-0 DMTCNT<31:16>: DMT Instruction Count Time-out Value Upper 16 bits

REGISTER 30-13: FDMT CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 15							bit 8

U-1	U-1	U-1	U-1	U-1	U-1	U-1	R/PO-1
_	_	_	_	_	_	_	DMTDIS
bit 7							bit 0

Legend: PO = Program Once bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-1 **Unimplemented:** Read as '1' bit 0 **DMTDIS:** DMT Disable bit

1 = DMT is disabled 0 = DMT is enabled

REGISTER 30-14: FDEVOPT CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	U-1	R/PO-1	U-1	U-1	R/PO-1	r-0	r-0
_	_	SPI2PIN ⁽¹⁾	_	_	SMBEN	_	_
bit 15							bit 8

r-1	U-1	R/PO-1	R/PO-1	R/PO-1	r-1	U-1	U-1
_	_	ALTI2C3	ALTI2C2	ALTI2C1	_	_	_
bit 7							bit 0

Legend: PO = Program Once bit r = Reserved bit

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 23-14 Unimplemented: Read as '1'

bit 13 SPI2PIN: Master SPI #2 Fast I/O Pad Disable bit(1)

1 = Master SPI2 uses PPS (I/O remap) to make connections with device pins

0 = Master SPI2 uses direct connections with specified device pins

bit 12-11 **Unimplemented:** Read as '1'

bit 10 SMBEN: Select Input Voltage Threshold for I²C Pads to be SMBus 3.0 Compliant bit

1 = Enables SMBus 3.0 input threshold voltage

 $0 = I^2C$ pad input buffer operation

bit 9-8 **Reserved:** Maintain as '0' bit 7 **Reserved:** Maintain as '1'

bit 6 **Unimplemented:** Read as '1'

bit 5 ALTI2C3: Alternate I2C3 Pin Mapping bit

1 = Default location for SCL3/SDA3 pins

0 = Alternate location for SCL3/SDA3 pins (ASCL3/ASDA3)

bit 4 ALTI2C2: Alternate I2C2 Pin Mapping bit

1 = Default location for SCL2/SDA2 pins

0 = Alternate location for SCL2/SDA2 pins (ASCL2/ASDA2)

bit 3 ALTI2C1: Alternate I2C1 Pin Mapping bit

1 = Default location for SCL1/SDA1 pins

0 = Alternate location for SCL1/SDA1 pins (ASCL1/ASDA1)

bit 2 Reserved: Maintain as '1'

bit 1-0 **Unimplemented:** Read as '1'

Note 1: Fixed pin option is only available for higher pin packages (48-pin, 64-pin and 80-pin).

REGISTER 30-15: FALTREG CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

U-1	R/PO-1	R/PO-1	R/PO-1	U-1	R/PO-1	R/PO-1	R/PO-1
_		CTXT4<2:0>		_		CTXT3<2:0>	
bit 15							bit 8

U-1	R/PO-1	R/PO-1	R/PO-1	U-1	R/PO-1	R/PO-1	R/PO-1
_		CTXT2<2:0>		_		CTXT1<2:0>	
bit 7							bit 0

Legend:PO = Program Once bitR = Readable bitW = Writable bitU = Unimplemented bit, read as '0'-n = Value at POR'1' = Bit is set'0' = Bit is clearedx = Bit is unknown

bit 23-15 **Unimplemented:** Read as '1'

bit 14-12 CTXT4<2:0>: Specifies the Alternate Working Register Set #4 with Interrupt Priority Levels (IPL) bits

111 = Not assigned

110 = Alternate Register Set #4 is assigned to IPL Level 7

101 = Alternate Register Set #4 is assigned to IPL Level 6

100 = Alternate Register Set #4 is assigned to IPL Level 5

011 = Alternate Register Set #4 is assigned to IPL Level 4

010 = Alternate Register Set #4 is assigned to IPL Level 3

001 = Alternate Register Set #4 is assigned to IPL Level 2

000 = Alternate Register Set #4 is assigned to IPL Level 1

bit 11 **Unimplemented:** Read as '1'

bit 10-8 CTXT3<2:0>: Specifies the Alternate Working Register Set #3 with Interrupt Priority Levels (IPL) bits

111 = Not assigned

110 = Alternate Register Set #3 is assigned to IPL Level 7

101 = Alternate Register Set #3 is assigned to IPL Level 6

100 = Alternate Register Set #3 is assigned to IPL Level 5

011 = Alternate Register Set #3 is assigned to IPL Level 4

010 = Alternate Register Set #2 is assigned to IR Level 7

010 = Alternate Register Set #3 is assigned to IPL Level 3

001 = Alternate Register Set #3 is assigned to IPL Level 2

000 = Alternate Register Set #3 is assigned to IPL Level 1

bit 7 **Unimplemented:** Read as '1'

bit 6-4 CTXT2<2:0>: Specifies the Alternate Working Register Set #2 with Interrupt Priority Levels (IPL) bits

111 = Not assigned

110 = Alternate Register Set #2 is assigned to IPL Level 7

101 = Alternate Register Set #2 is assigned to IPL Level 6

100 = Alternate Register Set #2 is assigned to IPL Level 5

011 = Alternate Register Set #2 is assigned to IPL Level 4

010 = Alternate Register Set #2 is assigned to IPL Level 3

001 = Alternate Register Set #2 is assigned to IPL Level 2 000 = Alternate Register Set #2 is assigned to IPL Level 1

Unimplemented: Read as '1'

bit 3

REGISTER 30-15: FALTREG CONFIGURATION REGISTER (CONTINUED)

bit 2-0 CTXT1<2:0>: Specifies the Alternate Working Register Set #1 with Interrupt Priority Levels (IPL) bits

111 = Not assigned

110 = Alternate Register Set #1 is assigned to IPL Level 7

101 = Alternate Register Set #1 is assigned to IPL Level 6

100 = Alternate Register Set #1 is assigned to IPL Level 5

011 = Alternate Register Set #1 is assigned to IPL Level 4

010 = Alternate Register Set #1 is assigned to IPL Level 3

001 = Alternate Register Set #1 is assigned to IPL Level 2

000 = Alternate Register Set #1 is assigned to IPL Level 1

REGISTER 30-16: FBTSEQ CONFIGURATION REGISTER

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1		
IBSEQ<11:4>									
bit 23					bit 16				

R/PO-1	R/PO-1	R/P0-1	R/PO-1	R/PO-1	R/PO-1	R/P0-1	R/PO-1	
	IBSEC	Q<3:0>		BSEQ<11:8>				
bit 15							bit 8	

R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	R/PO-1	
BSEQ<7:0>								
bit 7							bit 0	

Legend:	PO = Program Once bit			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	, read as '1'	
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown	

bit 23-12 **IBSEQ<11:0>:** Inverse Boot Sequence Number bits (Dual Partition modes only)

The one's complement of BSEQ<11:0>; must be calculated by the user and written into device programming.

bit 11-0 **BSEQ<11:0>:** Boot Sequence Number bits (Dual Partition modes only)

Relative value defining which partition will be active after a device Reset; the partition containing a lower boot number will be active.

REGISTER 30-17: FBOOT CONFIGURATION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 15							bit 8

U-1	U-1	U-1	U-1	U-1	U-1	R/PO-1	R/PO-1
_	_	_	_	_	_	BTMOE)E<1:0>
bit 7							bit 0

 Legend:
 PO = Program Once bit

 R = Readable bit
 W = Writable bit
 U = Unimplemented bit, read as '1'

 -n = Value at POR
 '1' = Bit is set
 '0' = Bit is cleared
 x = Bit is unknown

bit 15-2 **Unimplemented:** Read as '1'

bit 1-0 BTMODE<1:0>: Device Partition Mode Configuration Status bits

11 = Single Partition mode10 = Dual Partition mode

01 = Protected Dual Partition mode (Partition 1 is write-protected when inactive)

00 = Reserved; do not use

30.2 Device Calibration and Identification

The dsPIC33CK256MP508 devices have two Identification registers, near the end of configuration memory space, that store the Device ID (DEVID) and Device

Revision (DEVREV). These registers are used to determine the mask, variant and manufacturing information about the device. These registers are read-only and are shown in Register 30-18 and Register 30-19.

REGISTER 30-18: DEVREV: DEVICE REVISION REGISTER

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

r-0	U-1						
_	_	_	_	_	_	_	_
bit 15							bit 8

U-1	U-1	U-1	U-1	R	R	R	R
_	_	_	_		DEVRE	:V<3:0>	
bit 7							bit 0

Legend: R = Read-only bit r = Reserved bit U = Unimplemented bit

bit 23-16 Unimplemented: Read as '1' bit 15 Reserved: Maintain as '0' Unimplemented: Read as '1' Unimplemented: Read as '1'

bit 3-0 **DEVREV<3:0>:** Device Revision bits

REGISTER 30-19: DEVID: DEVICE ID REGISTERS

U-1	U-1	U-1	U-1	U-1	U-1	U-1	U-1
_	_	_	_	_	_	_	_
bit 23							bit 16

R	R	R	R	R	R	R	R			
FAMID<7:0>										
bit 15							bit 8			

R	R	R	R	R	R	R	R
			DEV<	7:0> ⁽¹⁾			
bit 7							bit 0

Legend: R = Read-only bit U = Unimplemented bit

bit 23-16 Unimplemented: Read as '1'

bit 15-8 **FAMID<7:0>:** Device Family Identifier bits

0111 1100 = dsPIC33CK256MP508 family

bit 7-0 **DEV<7:0>:** Individual Device Identifier bits⁽¹⁾

Note 1: See Table 30-4 for the list of Device Identifier bits.

TABLE 30-4: DEVICE IDs FOR THE dsPIC33CK256MP508 FAMILY

Device	DEVID
Device IDs for dsPIC33CK256MP508 Family with CAN	FD
dsPIC33CK256MP508	0x7C74
dsPIC33CK256MP506	0x7C73
dsPIC33CK256MP505	0x7C72
dsPIC33CK256MP503	0x7C71
dsPIC33CK256MP502	0x7C70
dsPIC33CK128MP508	0x7C64
dsPIC33CK128MP506	0x7C63
dsPIC33CK128MP505	0x7C62
dsPIC33CK128MP503	0x7C61
dsPIC33CK128MP502	0x7C60
dsPIC33CK64MP508	0x7C54
dsPIC33CK64MP506	0x7C53
dsPIC33CK64MP505	0x7C52
dsPIC33CK64MP503	0x7C51
dsPIC33CK64MP502	0x7C50
dsPIC33CK32MP506	0x7C43
dsPIC33CK32MP505	0x7C42
dsPIC33CK32MP503	0x7C41
dsPIC33CK32MP502	0x7C40
Device IDs for dsPIC33CK256MP508 Family without C	AN FD
dsPIC33CK256MP208	0x7C34
dsPIC33CK256MP206	0x7C33
dsPIC33CK256MP205	0x7C32
dsPIC33CK256MP203	0x7C31
dsPIC33CK256MP202	0x7C30
dsPIC33CK128MP208	0x7C24
dsPIC33CK128MP206	0x7C23
dsPIC33CK128MP205	0x7C22
dsPIC33CK128MP203	0x7C21
dsPIC33CK128MP202	0x7C20
dsPIC33CK64MP208	0x7C14
dsPIC33CK64MP206	0x7C13
dsPIC33CK64MP205	0x7C12
dsPIC33CK64MP203	0x7C11
dsPIC33CK64MP202	0x7C10
dsPIC33CK32MP206	0x7C03
dsPIC33CK32MP205	0x7C02
dsPIC33CK32MP203	0x7C01
dsPIC33CK32MP202	0x7C00

30.3 User OTP Memory

The dsPIC33CK256MP508 family devices contain 64 One-Time-Programmable (OTP) double words, located at addresses, 801700h through 8017FEh. Each 48-bit OTP double word can only be written one time. The OTP Words can be used for storing checksums, code revisions, manufacturing dates, manufacturing lot numbers or any other application-specific information.

The OTP area is not cleared by any erase command. This memory can be written only once.

30.4 On-Chip Voltage Regulators


dsPIC33CK256MP508 family devices have a capacitorless internal voltage regulator to supply power to the core at 1.2V (typical). A pair of voltage regulators, VREG1 and VREG2 together, provide power for the core. The PLL is powered using a separate regulator, VREGPLL, as shown in Figure 30-1.

The regulators have Low-Power and Standby modes for use in Sleep modes. For additional information about Sleep, see Section 29.2.1 "Sleep Mode".

When the regulators are in Low-Power mode (LPWREN = 1), the power available to the core is limited. Before the LPWREN bit is set, the device should be placed into a lower power state by disabling peripherals and lowering CPU frequency (e.g., 8 MHz FRC without PLL).

The output voltages of the three regulators can be controlled independently by the user, which gives the capability to save additional power during Sleep mode.

FIGURE 30-1: INTERNAL REGULATOR



REGISTER 30-20: VREGCON: VOLTAGE REGULATOR CONTROL REGISTER

R/W-0	U-0						
LPWREN ⁽¹⁾	_	_	_	_	_	_	_
bit 15							bit 8

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
_	_	VREG30V<1:0>		VREG20V<1:0>		VREG10	OV<1:0>
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15	LPWREN: Low-Power Mode Enable bit ⁽¹⁾ 1 = Voltage regulators are in Low-Power mode 0 = Voltage regulators are in Full Power mode
bit 14-6	Unimplemented: Read as '1'
bit 5-4	VREG3OV<1:0>: Low-Power Mode Enable bits
	11/00 = VOUT = 1.5 * VBG = 1.2V 10 = VOUT = 1.25 * VBG = 1.0V 01 = VOUT = VBG = 0.8V
bit 3-2	VREG2OV<1:0>: Low-Power Mode Enable bits
	11/00 = VOUT = 1.5 * VBG = 1.2V 10 = VOUT = 1.25 * VBG = 1.0V 01 = VOUT = VBG = 0.8V
bit 1-0	VREG10V<1:0>: Low-Power Mode Enable bits
	11/00 = Vout = 1.5 * VBG = 1.2V 10 = Vout = 1.25 * VBG = 1.0V 01 = Vout = VBG = 0.8V

Note 1: Low-Power mode can only be used within the industrial temperature range. The CPU should be run at slow speed (8 MHz or less) before setting this bit.

30.5 Brown-out Reset (BOR)

The Brown-out Reset (BOR) module is based on an internal voltage reference circuit that monitors the regulated supply voltage. The main purpose of the BOR module is to generate a device Reset when a brown-out condition occurs. Brown-out conditions are generally caused by glitches on the AC mains (for example, missing portions of the AC cycle waveform due to bad power transmission lines or voltage sags due to excessive current draw when a large inductive load is turned on).

A BOR generates a Reset pulse which resets the device. The BOR selects the clock source based on the device Configuration bit selections.

If an Oscillator mode is selected, the BOR activates the Oscillator Start-up Timer (OST). The system clock is held until OST expires. If the PLL is used, the clock is held until the LOCK bit (OSCCON<5>) is '1'.

Concurrently, the PWRT Time-out (TPWRT) is applied before the internal Reset is released. If TPWRT = 0 and a crystal oscillator is being used, then a nominal delay of TFSCM is applied. The total delay in this case is TFSCM. Refer to Parameter SY35 in Table 33-25 of **Section 33.0** "Electrical Characteristics" for specific TFSCM values.

The BOR status bit (RCON<1>) is set to indicate that a BOR has occurred. The BOR circuit continues to operate while in Sleep or Idle mode and resets the device should VDD fall below the BOR threshold voltage.

30.6 Dual Watchdog Timer (WDT)

Note 1: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to "Dual Watchdog Timer", (DS70005250) in the "dsPIC33/PIC24 Family Reference Manual", which is available from the Microchip website (www.microchip.com).


The dsPIC33 dual Watchdog Timer (WDT) is described in this section. Refer to Figure 30-2 for a block diagram of the WDT.

The WDT, when enabled, operates from the internal Low-Power RC (LPRC) Oscillator clock source or a selectable clock source in Run mode. The WDT can be used to detect system software malfunctions by resetting the device if the WDT is not cleared periodically in software. The WDT can be configured in Windowed mode or Non-Windowed mode. Various WDT time-out periods can be selected using the WDT postscaler. The WDT can also be used to wake the device from Sleep or Idle mode (Power Save mode). If the WDT expires and issues a device Reset, the WTDO bit in RCON (Register 6-1) will be set.

The following are some of the key features of the WDT modules:

- · Configuration or Software Controlled
- Separate User-Configurable Time-out Periods for Run and Sleep/Idle
- · Can Wake the Device from Sleep or Idle
- · User-Selectable Clock Source in Run mode
- · Operates from LPRC in Sleep/Idle mode

FIGURE 30-2: WATCHDOG TIMER BLOCK DIAGRAM



REGISTER 30-21: WDTCONL: WATCHDOG TIMER CONTROL REGISTER LOW

R/W-0	U-0	U-0	R-y	R-y	R-y	R-y	R-y
ON ^(1,2)	_	_	RUNDIV4 ⁽³⁾	RUNDIV3 ⁽³⁾	RUNDIV2 ⁽³⁾	RUNDIV1 ⁽³⁾	RUNDIV0 ⁽³⁾
bit 15							bit 8

R	R	R-y	R-y	R-y	R-y	R-y	HS/R/W-0
CLKSEL1 ^(3,5)	CLKSEL0 ^(3,5)	SLPDIV4 ⁽³⁾	SLPDIV3 ⁽³⁾	SLPDIV2 ⁽³⁾	SLPDIV1 ⁽³⁾	SLPDIV0 ⁽³⁾	WDTWINEN ⁽⁴⁾
bit 7							bit 0

Legend:	HS = Hardware Settable bit	y = Value from Configuratio	n bit on POR
R = Readable bit	W = Writable bit	U = Unimplemented bit, rea	nd as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 15 **ON:** Watchdog Timer Enable bit^(1,2)

1 = Enables the Watchdog Timer if it is not enabled by the device configuration

0 = Disables the Watchdog Timer if it was enabled in software

bit 14-13 **Unimplemented:** Read as '0'

bit 12-8 RUNDIV<4:0>: WDT Run Mode Postscaler Status bits⁽³⁾

11111 = Divide by 2 ^ 31 = 2,147,483,648 11110 = Divide by 2 ^ 30 = 1,073,741,824

. . .

00001 = Divide by 2^{1} , 2^{2}

00000 = Divide by 2 ^ 0, 1

bit 7-6 CLKSEL<1:0>: WDT Run Mode Clock Select Status bits (3,5)

11 = LPRC Oscillator

10 = FRC Oscillator

01 = Reserved

00 = SYSCLK

bit 5-1 SLPDIV<4:0>: Sleep and Idle Mode WDT Postscaler Status bits⁽³⁾

 $11111 = Divide by 2 ^ 31 = 2,147,483,648$

11110 = Divide by 2 ^ 30 = 1,073,741,824

. .

00001 = Divide by 2 ^ 1. 2

00000 = Divide by 2 ^ 0, 1

bit 0 **WDTWINEN:** Watchdog Timer Window Enable bit (4)

1 = Enables Window mode

0 = Disables Window mode

- Note 1: A read of this bit will result in a '1' if the WDT is enabled by the device configuration or by software.
 - 2: The user's software should not read or write the peripheral's SFRs in the SYSCLK cycle immediately following the instruction that clears the module's ON bit.
 - 3: These bits reflect the value of the Configuration bits.
 - **4:** The WDTWINEN bit reflects the status of the Configuration bit if the bit is set. If the bit is cleared, the value is controlled by software.
 - 5: The available clock sources are device-dependent.

REGISTER 30-22: WDTCONH: WATCHDOG TIMER CONTROL REGISTER HIGH

W-0	W-0	W-0	W-0	W-0	W-0	W-0	W-0
			WDTCLRK	EY<15:8>			
bit 15							bit 8

W-0	W-0	W-0	W-0	W-0	W-0	W-0	W-0
			WDTCLRK	(EY<7:0>			
bit 7							bit 0

Legend:

R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'

-n = Value at POR '1' = Bit is set '0' = Bit is cleared x = Bit is unknown

bit 15-0 WDTCLRKEY<15:0>: Watchdog Timer Clear Key bits

To clear the Watchdog Timer to prevent a time-out, software must write the value, 0x5743, to this location using a single 16-bit write.

30.7 JTAG Interface

The dsPIC33CK256MP508 family devices implement a JTAG interface, which supports boundary scan device testing. Detailed information on this interface will be provided in future revisions of this document.

Note: Refer to "Programming and Diagnostics" (DS70608) in the "dsPIC33/PIC24 Family Reference Manual" for further information on usage, configuration and operation of the JTAG interface.

30.8 In-Circuit Serial Programming™ (ICSP™)

The dsPIC33CK256MP508 family devices can be serially programmed while in the end application circuit. This is done with two lines for clock and data, and three other lines for power, ground and the programming sequence. Serial programming allows customers to manufacture boards with unprogrammed devices and then program the device just before shipping the product. Serial programming also allows the most recent firmware or a custom firmware to be programmed. Refer to the "dsPIC33CK256MP508 Family Flash Programming Specification" (DS70005300) for details about In-Circuit Serial Programming (ICSP).

Any of the three pairs of programming clock/data pins can be used:

- PGC1 and PGD1
- PGC2 and PGD2
- · PGC3 and PGD3

30.9 In-Circuit Debugger

When MPLAB[®] ICD 3 or the REAL ICE™ emulator is selected as a debugger, the in-circuit debugging functionality is enabled. This function allows simple debugging functions when used with MPLAB IDE. Debugging functionality is controlled through the PGCx (Emulation/Debug Clock) and PGDx (Emulation/Debug Data) pin functions.

Any of the three pairs of debugging clock/data pins can be used:

- PGC1 and PGD1
- · PGC2 and PGD2
- · PGC3 and PGD3

To use the in-circuit debugger function of the device, the design must implement ICSP connections to MCLR, VDD, VSS and the PGCx/PGDx pin pair. In addition, when the feature is enabled, some of the resources are not available for general use. These resources include the first 80 bytes of data RAM and two I/O pins (PGCx and PGDx).

30.10 Code Protection and CodeGuard™ Security


dsPIC33CK256MP508 family devices offer multiple levels of security for protecting individual intellectual property. The program Flash protection can be broken up into three segments: Boot Segment (BS), General Segment (GS) and Configuration Segment (CS). Boot Segment has the highest security privilege and can be thought to have limited restrictions when accessing other segments. General Segment has the least security and is intended for the end user system code. Configuration Segment contains only the device user configuration data, which is located at the end of the program memory space.

The code protection features are controlled by the Configuration registers, FSEC and FBSLIM. The FSEC register controls the code-protect level for each segment and if that segment is write-protected. The size of BS and GS will depend on the BSLIM<12:0> bits setting and if the Alternate Interrupt Vector Table (AIVT) is enabled. The BSLIM<12:0> bits define the number of pages for BS with each page containing 1024 IW. The smallest BS size is one page, which will consist of the Interrupt Vector Table (IVT) and 512 IW of code protection.

If the AIVT is enabled, the last page of BS will contain the AIVT and will not contain any BS code. With AIVT enabled, the smallest BS size is now two pages (2048 IW), with one page for the IVT and BS code, and the other page for the AIVT. Write protection of the BS does not cover the AIVT. The last page of BS can always be programmed or erased by BS code. The General Segment will start at the next page and will consume the rest of program Flash, except for the Flash Configuration Words. The IVT will assume GS security only if BS is not enabled. The IVT is protected from being programmed or page erased when either security segment has enabled write protection.

The different device security segments are shown in Figure 30-3. Here, all three segments are shown, but are not required. If only basic code protection is required, then GS can be enabled independently or combined with CS. if desired.

FIGURE 30-3: SECURITY SEGMENTS EXAMPLE




The dsPIC33CK256MP508 family can be operated in Dual Partition mode, where security is required for each partition. When operating in Dual Partition mode, the Active and Inactive Partitions both contain unique copies of the Reset vector and Interrupt Vector Tables (IVT, if enabled). Both partitions have the three security segments described previously. Code may not be executed from the Inactive Partition, but it may be programmed by, and read from, the Active Partition, subject to defined code protection. Figure 30-4 shows the different security segments for a device operating in Dual Partition mode.

The device may also operate in a Protected Dual Partition mode or in Privileged Dual Partition mode. In Protected Dual Partition mode, Partition 1 is permanently erase/write-protected. This implementation allows for a "Factory Default" mode, which provides a fail-safe backup image to be stored in Partition 1. For example, a fail-safe bootloader can be placed in Partition 1, along with a fail-safe backup code image, which can be used or rewritten into Partition 2 in the event of a failed Flash update to Partition 2.

Privileged Dual Partition mode performs the same function as Protected Dual Partition mode, except additional constraints are applied in an effort to prevent code in the Boot Segment and General Segment from being used against each other.

FIGURE 30-4: SECURITY SEGMENTS
EXAMPLE (DUAL
PARTITION MODES)



31.0 INSTRUCTION SET SUMMARY

Note: This data sheet summarizes the features of the dsPIC33CK256MP508 family of devices. It is not intended to be a comprehensive reference source. To complement the information in this data sheet, refer to the "16-Bit MCU and DSC Programmer's Reference Manual" (www.microchip.com/DS70000157), which is available from the Microchip website.

The dsPIC33CK256MP508 family instruction set is almost identical to that of the dsPIC30F and dsPIC33F.

Most instructions are a single program memory word (24 bits). Only three instructions require two program memory locations.

Each single-word instruction is a 24-bit word, divided into an 8-bit opcode, which specifies the instruction type and one or more operands, which further specify the operation of the instruction.

The instruction set is highly orthogonal and is grouped into five basic categories:

- · Word or byte-oriented operations
- · Bit-oriented operations
- Literal operations
- DSP operations
- · Control operations

Table 31-1 lists the general symbols used in describing the instructions.

The dsPIC33 instruction set summary in Table 31-2 lists all the instructions, along with the status flags affected by each instruction.

Most word or byte-oriented W register instructions (including barrel shift instructions) have three operands:

- The first source operand, which is typically a register 'Wb' without any address modifier
- The second source operand, which is typically a register 'Ws' with or without an address modifier
- The destination of the result, which is typically a register 'Wd' with or without an address modifier

However, word or byte-oriented file register instructions have two operands:

- · The file register specified by the value 'f'
- The destination, which could be either the file register 'f' or the W0 register, which is denoted as 'WREG'

Most bit-oriented instructions (including simple rotate/ shift instructions) have two operands:

- The W register (with or without an address modifier) or file register (specified by the value of 'Ws' or 'f')
- The bit in the W register or file register (specified by a literal value or indirectly by the contents of register 'Wb')

The literal instructions that involve data movement can use some of the following operands:

- A literal value to be loaded into a W register or file register (specified by 'k')
- The W register or file register where the literal value is to be loaded (specified by 'Wb' or 'f')

However, literal instructions that involve arithmetic or logical operations use some of the following operands:

- The first source operand, which is a register 'Wb' without any address modifier
- The second source operand, which is a literal value
- The destination of the result (only if not the same as the first source operand), which is typically a register 'Wd' with or without an address modifier

The MAC class of DSP instructions can use some of the following operands:

- The accumulator (A or B) to be used (required operand)
- The W registers to be used as the two operands
- The X and Y address space prefetch operations
- The X and Y address space prefetch destinations
- · The accumulator write-back destination

The other DSP instructions do not involve any multiplication and can include:

- · The accumulator to be used (required)
- The source or destination operand (designated as Wso or Wdo, respectively) with or without an address modifier
- The amount of shift specified by a W register 'Wn' or a literal value

The control instructions can use some of the following operands:

- · A program memory address
- The mode of the Table Read and Table Write instructions

Most instructions are a single word. Certain double-word instructions are designed to provide all the required information in these 48 bits. In the second word, the eight MSbs are '0's. If this second word is executed as an instruction (by itself), it executes as a NOP.

The double-word instructions execute in two instruction cycles.

Most single-word instructions are executed in a single instruction cycle, unless a conditional test is true or the Program Counter is changed as a result of the instruction, or a PSV or Table Read is performed. In these cases, the execution takes multiple instruction cycles, with the additional instruction cycle(s) executed as a NOP. Certain instructions that involve skipping over the subsequent instruction require either two or three

cycles if the skip is performed, depending on whether the instruction being skipped is a single-word or twoword instruction. Moreover, double-word moves require two cycles.

Note: In dsPIC33CK256MP508 devices, read and Read-Modify-Write operations on non-CPU Special Function Registers require an additional cycle when compared to dsPIC30F, dsPIC33F, PIC24F and PIC24H devices.

Note: For more details on the instruction set, refer to the "16-Bit MCU and DSC Programmer's Reference Manual" (DS70000157).

TABLE 31-1: SYMBOLS USED IN OPCODE DESCRIPTIONS

Field	Description
#text	Means literal defined by "text"
(text)	Means "content of text"
[text]	Means "the location addressed by text"
{}	Optional field or operation
$a \in \{b, c, d\}$	a is selected from the set of values b, c, d
<n:m></n:m>	Register bit field
.b	Byte mode selection
.d	Double-Word mode selection
.S	Shadow register select
.W	Word mode selection (default)
Acc	One of two accumulators {A, B}
AWB	Accumulator Write-Back Destination Address register ∈ {W13, [W13]+ = 2}
bit4	4-bit bit selection field (used in word-addressed instructions) $\in \{015\}$
C, DC, N, OV, Z	MCU Status bits: Carry, Digit Carry, Negative, Overflow, Sticky Zero
Expr	Absolute address, label or expression (resolved by the linker)
f	File register address ∈ {0x00000x1FFF}
lit1	1-bit unsigned literal ∈ {0,1}
lit4	4-bit unsigned literal ∈ {015}
lit5	5-bit unsigned literal ∈ {031}
lit8	8-bit unsigned literal ∈ {0255}
lit10	10-bit unsigned literal \in {0255} for Byte mode, {0:1023} for Word mode
lit14	14-bit unsigned literal ∈ {016384}
lit16	16-bit unsigned literal ∈ {065535}
lit23	23-bit unsigned literal ∈ {08388608}; LSb must be '0'
None	Field does not require an entry, can be blank
OA, OB, SA, SB	DSP Status bits: ACCA Overflow, ACCB Overflow, ACCA Saturate, ACCB Saturate
PC	Program Counter
Slit10	10-bit signed literal ∈ {-512511}
Slit16	16-bit signed literal ∈ {-3276832767}
Slit6	6-bit signed literal ∈ {-1616}
Wb	Base W register ∈ {W0W15}
Wd	Destination W register ∈ { Wd, [Wd], [Wd++], [Wd], [++Wd], [Wd] }
Wdo	Destination W register ∈ { Wnd, [Wnd], [Wnd++], [Wnd], [++Wnd], [Wnd], [Wnd+Wb] }
Wm,Wn	Dividend, Divisor Working register pair (direct addressing)

TABLE 31-1: SYMBOLS USED IN OPCODE DESCRIPTIONS (CONTINUED)

Field	Description			
Wm*Wm	Multiplicand and Multiplier Working register pair for Square instructions ∈ {W4 * W4,W5 * W5,W6 * W6,W7 * W7}			
Wm*Wn	Multiplicand and Multiplier Working register pair for DSP instructions ∈ {W4 * W5,W4 * W6,W4 * W7,W5 * W6,W5 * W7,W6 * W7}			
Wn	One of 16 Working registers ∈ {W0W15}			
Wnd	One of 16 Destination Working registers ∈ {W0W15}			
Wns	One of 16 Source Working registers ∈ {W0W15}			
WREG	W0 (Working register used in file register instructions)			
Ws	Source W register ∈ { Ws, [Ws], [Ws++], [Ws], [++Ws], [Ws] }			
Wso	Source W register ∈ { Wns, [Wns++], [Wns], [++Wns], [Wns], [Wns+Wb] }			
Wx X Data Space Prefetch Address register for DSP instructions ∈ {[W8] + = 6, [W8] + = 4, [W8] + = 2, [W8], [W8] - = 6, [W8] - = 4, [W8] - = 2, [W9] + = 6, [W9] + = 4, [W9] + = 2, [W9], [W9] - = 6, [W9] - = 4, [W9] - = 2, [W9 + W12], none}				
Wxd	X Data Space Prefetch Destination register for DSP instructions ∈ {W4W7}			
Wy	Y Data Space Prefetch Address register for DSP instructions ∈ {[W10] + = 6, [W10] + = 4, [W10] + = 2, [W10], [W10] - = 6, [W10] - = 4, [W10] - = 2, [W11] + = 6, [W11] + = 4, [W11] + = 2, [W11], [W11] - = 6, [W11] - = 4, [W11] - = 2, [W11 + W12], none}			
Wyd	Y Data Space Prefetch Destination register for DSP instructions ∈ {W4W7}			

TABLE 31-2: INSTRUCTION SET OVERVIEW

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
1	ADD	ADD	Acc	Add Accumulators	1	1	OA,OB,SA,SB
		ADD	f	f = f + WREG	1	1	C,DC,N,OV,Z
		ADD	f,WREG	WREG = f + WREG	1	1	C,DC,N,OV,Z
		ADD	#lit10,Wn	Wd = lit10 + Wd	1	1	C,DC,N,OV,Z
		ADD	Wb, Ws, Wd	Wd = Wb + Ws	1	1	C,DC,N,OV,Z
		ADD	Wb,#lit5,Wd	Wd = Wb + lit5	1	1	C,DC,N,OV,Z
		ADD	Wso,#Slit4,Acc	16-bit Signed Add to Accumulator	1	1	OA,OB,SA,SB
2	ADDC	ADDC	f	f = f + WREG + (C)	1	1	C,DC,N,OV,Z
		ADDC	f,WREG	WREG = f + WREG + (C)	1	1	C,DC,N,OV,Z
		ADDC	#lit10,Wn	Wd = lit10 + Wd + (C)	1	1	C,DC,N,OV,Z
		ADDC	Wb, Ws, Wd	Wd = Wb + Ws + (C)	1	1	C,DC,N,OV,Z
		ADDC	Wb,#lit5,Wd	Wd = Wb + lit5 + (C)	1	1	C,DC,N,OV,Z
3	AND	AND	f	f = f .AND. WREG	1	1	N,Z
		AND	f,WREG	WREG = f .AND. WREG	1	1	N,Z
		AND	#lit10,Wn	Wd = lit10 .AND. Wd	1	1	N,Z
		AND	Wb, Ws, Wd	Wd = Wb .AND. Ws	1	1	N,Z
		AND	Wb,#lit5,Wd	Wd = Wb .AND. lit5	1	1	N,Z
4	ASR	ASR	f	f = Arithmetic Right Shift f	1	1	C,N,OV,Z
		ASR	f,WREG	WREG = Arithmetic Right Shift f	1	1	C,N,OV,Z
		ASR	Ws,Wd	Wd = Arithmetic Right Shift Ws	1	1	C,N,OV,Z
		ASR	Wb, Wns, Wnd	Wnd = Arithmetic Right Shift Wb by Wns	1	1	N,Z
		ASR	Wb,#lit5,Wnd	Wnd = Arithmetic Right Shift Wb by lit5	1	1	N,Z
5	BCLR	BCLR	f,#bit4	Bit Clear f	1	1	None
		BCLR	Ws,#bit4	Bit Clear Ws	1	1	None
6	BFEXT	BFEXT	bit4,wid5,Ws,Wb	Bit Field Extract from Ws to Wb	2	2	None
		BFEXT	bit4,wid5,f,Wb	Bit Field Extract from f to Wb	2	2	None
7	BFINS	BFINS	bit4,wid5,Wb,Ws	Bit Field Insert from Wb into Ws	2	2	None
		BFINS	bit4,wid5,Wb,f	Bit Field Insert from Wb into f	2	2	None
		BFINS	bit4,wid5,lit8,Ws	Bit Field Insert from #lit8 to Ws	2	2	None
8	BOOTSWP	BOOTSWP		Swap the Active and Inactive Program Flash Space	1	2	None

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.
2: The divide instructions must be preceded with a "REPEAT #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
9	BRA	BRA	C, Expr	Branch if Carry	1	1 (4)	None
		BRA	GE, Expr	Branch if Greater Than or Equal	1	1 (4)	None
		BRA	GEU, Expr	Branch if unsigned Greater Than or Equal	1	1 (4)	None
		BRA	GT,Expr	Branch if Greater Than	1	1 (4)	None
		BRA	GTU, Expr	Branch if Unsigned Greater Than	1	1 (4)	None
		BRA	LE, Expr	Branch if Less Than or Equal	1	1 (4)	None
		BRA	LEU, Expr	Branch if Unsigned Less Than or Equal	1	1 (4)	None
		BRA	LT,Expr	Branch if Less Than	1	1 (4)	None
		BRA	LTU, Expr	Branch if Unsigned Less Than	1	1 (4)	None
		BRA	N, Expr	Branch if Negative	1	1 (4)	None
		BRA	NC, Expr	Branch if Not Carry	1	1 (4)	None
		BRA	NN, Expr	Branch if Not Negative	1	1 (4)	None
		BRA	NOV, Expr	Branch if Not Overflow	1	1 (4)	None
		BRA	NZ,Expr	Branch if Not Zero	1	1 (4)	None
		BRA	OA, Expr	Branch if Accumulator A Overflow	1	1 (4)	None
		BRA	OB, Expr	Branch if Accumulator B Overflow	1	1 (4)	None
		BRA	OV,Expr	Branch if Overflow	1	1 (4)	None
		BRA	SA, Expr	Branch if Accumulator A Saturated	1	1 (4)	None
		BRA	SB,Expr	Branch if Accumulator B Saturated	1	1 (4)	None
		BRA	Expr	Branch Unconditionally	1	4	None
		BRA	Z,Expr	Branch if Zero	1	1 (4)	None
		BRA	Wn	Computed Branch	1	4	None
10	BREAK	BREAK		Stop User Code Execution	1	1	None
11	BSET	BSET	f,#bit4	Bit Set f	1	1	None
			Ws,#bit4	Bit Set Ws	1	1	None
12	BSW	BSW.C	Ws,Wb	Write C bit to Ws <wb></wb>	1	1	None
		BSW.Z	Ws,Wb	Write Z bit to Ws <wb></wb>	1	1	None
13	BTG	BTG	f,#bit4	Bit Toggle f	1	1	None
		BTG	Ws,#bit4	Bit Toggle Ws	1	1	None
14	BTSC	BTSC	f,#bit4	Bit Test f, Skip if Clear	1	1 (2 or 3)	None
		BTSC	Ws,#bit4	Bit Test Ws, Skip if Clear	1	1 (2 or 3)	None
15	BTSS	BTSS	f,#bit4	Bit Test f, Skip if Set	1	1 (2 or 3)	None
		BTSS	Ws,#bit4	Bit Test Ws, Skip if Set	1	1 (2 or 3)	None
16	BTST	BTST	f,#bit4	Bit Test f	1	1	Z
		BTST.C	Ws,#bit4	Bit Test Ws to C	1	1	С
		BTST.Z	Ws,#bit4	Bit Test Ws to Z	1	1	Z
		BTST.C	Ws,Wb	Bit Test Ws <wb> to C</wb>	1	1	С
		BTST.Z	Ws,Wb	Bit Test Ws <wb> to Z</wb>	1	1	Z
17	BTSTS	BTSTS	f,#bit4	Bit Test then Set f	1	1	Z
		BTSTS.C	Ws,#bit4	Bit Test Ws to C, then Set	1	1	С
		BTSTS.Z	Ws,#bit4	Bit Test Ws to Z, then Set	1	1	Z
18	CALL	CALL	lit23	Call Subroutine	2	4	SFA
		CALL	Wn	Call Indirect Subroutine	1	4	SFA
		CALL.L	Wn	Call Indirect Subroutine (long address)	1	4	SFA
19	CLR	CLR	f	f = 0x0000	1	1	None
		CLR	WREG	WREG = 0x0000	1	1	None
		CLR	Ws	Ws = 0x0000	1	1	None
		CLR	Acc, Wx, Wxd, Wy, Wyd, AW	TB Clear Accumulator	1	1	OA,OB,SA,SB

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
20	CLRWDT	CLRWDT		Clear Watchdog Timer	1	1	WDTO,Sleep
21	COM	COM	f	$f = \bar{f}$	1	1	N,Z
		COM	f,WREG	WREG = f	1	1	N,Z
		COM	Ws,Wd	Wd = Ws	1	1	N,Z
22	CP	CP	f	Compare f with WREG	1	1	C,DC,N,OV,Z
		CP	Wb,#lit8	Compare Wb with lit8	1	1	C,DC,N,OV,Z
		CP	Wb,Ws	Compare Wb with Ws (Wb – Ws)	1	1	C,DC,N,OV,Z
23	CP0	CP0	f	Compare f with 0x0000	1	1	C,DC,N,OV,Z
		CP0	Ws	Compare Ws with 0x0000	1	1	C,DC,N,OV,Z
24	CPB	CPB	f	Compare f with WREG, with Borrow	1	1	C,DC,N,OV,Z
		CPB	Wb,#lit8	Compare Wb with lit8, with Borrow	1	1	C,DC,N,OV,Z
		CPB	Wb,Ws	Compare Wb with Ws, with Borrow (Wb – Ws – \overline{C})	1	1	C,DC,N,OV,Z
25	CPSEQ	CPSEQ	Wb,Wn	Compare Wb with Wn, Skip if =	1	1 (2 or 3)	None
	CPBEQ	CPBEQ	Wb,Wn,Expr	Compare Wb with Wn, Branch if =	1	1 (5)	None
26	CPSGT	CPSGT	Wb,Wn	Compare Wb with Wn, Skip if >	1	1 (2 or 3)	None
	CPBGT	CPBGT	Wb,Wn,Expr	Compare Wb with Wn, Branch if >	1	1 (5)	None
27	CPSLT	CPSLT	Wb,Wn	Compare Wb with Wn, Skip if <	1	1 (2 or 3)	None
		CPBLT	Wb,Wn,Expr	Compare Wb with Wn, Branch if <	1	1 (5)	None
28	CPSNE	CPSNE	Wb,Wn	Compare Wb with Wn, Skip if ≠	1	1 (2 or 3)	None
		CPBNE	Wb,Wn,Expr	Compare Wb with Wn, Branch if ≠	1	1 (5)	None
29	CTXTSWP	CTXTSWP	#1it3	Switch CPU Register Context to Context Defined by lit3	1	2	None
30	CTXTSWP	CTXTSWP	Wn	Switch CPU Register Context to Context Defined by Wn	1	2	None
31	DAW.B	DAW.B	Wn	Wn = Decimal Adjust Wn	1	1	С
32	DEC	DEC	f	f = f - 1	1	1	C,DC,N,OV,Z
		DEC	f,WREG	WREG = f – 1	1	1	C,DC,N,OV,Z
		DEC	Ws,Wd	Wd = Ws - 1	1	1	C,DC,N,OV,Z
33	DEC2	DEC2	f	f = f - 2	1	1	C,DC,N,OV,Z
		DEC2	f,WREG	WREG = f – 2	1	1	C,DC,N,OV,Z
		DEC2	Ws,Wd	Wd = Ws - 2	1	1	C,DC,N,OV,Z
34	DISI	DISI	#lit14	Disable Interrupts for k Instruction Cycles	1	1	None
35	DIVF	DIVF	Wm,Wn	Signed 16/16-bit Fractional Divide	1	18	N,Z,C,OV
36	DIV.S ⁽²⁾	DIV.S	Wm,Wn	Signed 16/16-bit Integer Divide	1	18	N,Z,C,OV
	(4)	DIV.SD	Wm,Wn	Signed 32/16-bit Integer Divide	1	18	N,Z,C,OV
37	DIV.U ⁽²⁾	DIV.U	Wm,Wn	Unsigned 16/16-bit Integer Divide	1	18	N,Z,C,OV
	(0)	DIV.UD	Wm, Wn	Unsigned 32/16-bit Integer Divide	1	18	N,Z,C,OV
38	DIVF2(2)	DIVF2	Wm,Wn	Signed 16/16-bit Fractional Divide (W1:W0 preserved)	1	6	N,Z,C,OV
39	DIV2.S ⁽²⁾	DIV2.S	Wm,Wn	Signed 16/16-bit Integer Divide (W1:W0 preserved)	1	6	N,Z,C,OV
<u> </u>		DIV2.SD	Wm,Wn	Signed 32/16-bit Integer Divide (W1:W0 preserved)	1	6	N,Z,C,OV
40	DIV2.U ⁽²⁾	DIV2.U	Wm,Wn	Unsigned 16/16-bit Integer Divide (W1:W0 preserved)	1	6	N,Z,C,OV
		DIV2.UD	Wm,Wn	Unsigned 32/16-bit Integer Divide (W1:W0 preserved)	1	6	N,Z,C,OV
41	DO	DO	#lit15,Expr	Do Code to PC + Expr, lit15 + 1 Times	2	2	None
		DO	Wn,Expr	Do code to PC + Expr, (Wn) + 1 Times	2	2	None
_			· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·			

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT" #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
42	ED	ED	Wm*Wm, Acc, Wx, Wy, Wxd	Euclidean Distance (no accumulate)	1	1	OA,OB,OAB, SA,SB,SAB
43	EDAC	EDAC	Wm*Wm, Acc, Wx, Wy, Wxd	Euclidean Distance	1	1	OA,OB,OAB, SA,SB,SAB
44	EXCH	EXCH	Wns, Wnd	Swap Wns with Wnd	1	1	None
46	FBCL	FBCL	Ws, Wnd	Find Bit Change from Left (MSb) Side	1	1	С
47	FF1L	FF1L	Ws, Wnd	Find First One from Left (MSb) Side	1	1	С
48	FF1R	FF1R	Ws, Wnd	Find First One from Right (LSb) Side	1	1	С
49	FLIM	FLIM	Wb, Ws	Force Data (Upper and Lower) Range Limit without Limit Excess Result	1	1	N,Z,OV
		FLIM.V	Wb, Ws, Wd	Force Data (Upper and Lower) Range Limit with Limit Excess Result	1	1	N,Z,OV
50	GOTO	GOTO	Expr	Go to Address	2	4	None
		GOTO	Wn	Go to Indirect	1	4	None
		GOTO.L	Wn	Go to Indirect (long address)	1	4	None
51	INC	INC	f	f = f + 1	1	1	C,DC,N,OV,Z
		INC	f,WREG	WREG = f + 1	1	1	C,DC,N,OV,Z
		INC	Ws,Wd	Wd = Ws + 1	1	1	C,DC,N,OV,Z
52	INC2	INC2	f	f = f + 2	1	1	C,DC,N,OV,Z
		INC2	f,WREG	WREG = f + 2	1	1	C,DC,N,OV,Z
		INC2	Ws,Wd	Wd = Ws + 2	1	1	C,DC,N,OV,Z
53	IOR	IOR	f	f = f .IOR. WREG	1	1	N,Z
		IOR	f,WREG	WREG = f.IOR. WREG	1	1	N,Z
		IOR	#lit10,Wn	Wd = lit10 .IOR. Wd	1	1	N,Z
		IOR	Wb, Ws, Wd	Wd = Wb .IOR. Ws	1	1	N,Z
		IOR	Wb,#lit5,Wd	Wd = Wb .IOR. lit5	1	1	N,Z
54	LAC	LAC	Wso,#Slit4,Acc	Load Accumulator	1	1	OA,OB,OAB, SA,SB,SAB
		LAC.D	Wso, #Slit4, Acc	Load Accumulator Double	1	2	OA,SA,OB,SB
56	LNK	LNK	#lit14	Link Frame Pointer	1	1	SFA
57	LSR	LSR	f	f = Logical Right Shift f	1	1	C,N,OV,Z
		LSR	f,WREG	WREG = Logical Right Shift f	1	1	C,N,OV,Z
		LSR	Ws,Wd	Wd = Logical Right Shift Ws	1	1	C,N,OV,Z
		LSR	Wb, Wns, Wnd	Wnd = Logical Right Shift Wb by Wns	1	1	N,Z
		LSR	Wb,#lit5,Wnd	Wnd = Logical Right Shift Wb by lit5	1	1	N,Z
58	MAC	MAC	Wm*Wn,Acc,Wx,Wxd,Wy,Wyd, AWB	Multiply and Accumulate	1	1	OA,OB,OAB, SA,SB,SAB
		MAC	Wm*Wm, Acc, Wx, Wxd, Wy, Wyd	Square and Accumulate	1	1	OA,OB,OAB, SA,SB,SAB
59	MAX	MAX	Acc	Force Data Maximum Range Limit	1	1	N,OV,Z
		MAX.V	Acc, Wnd	Force Data Maximum Range Limit with Result	1	1	N,OV,Z
60	MIN	MIN	Acc	If Accumulator A Less than B Load Accumulator with B or vice versa	1	1	N,OV,Z
		MIN.V	Acc, Wd	If Accumulator A Less than B Accumulator Force Minimum Data Range Limit with Limit Excess Result	1	1	N,OV,Z
		MINZ	Acc	Accumulator Force Minimum Data Range Limit	1	1	N,OV,Z
		MINZ.V	Acc, Wd	Accumulator Force Minimum Data Range Limit with Limit Excess Result	1	1	N,OV,Z

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT" #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
61	MOV	MOV	f,Wn	Move f to Wn	1	1	None
		MOV	f	Move f to f	1	1	None
		MOV	f,WREG	Move f to WREG	1	1	None
		MOV	#lit16,Wn	Move 16-bit Literal to Wn	1	1	None
		MOV.b	#lit8,Wn	Move 8-bit Literal to Wn	1	1	None
		MOV	Wn,f	Move Wn to f	1	1	None
		MOV	Wso, Wdo	Move Ws to Wd	1	1	None
		MOV	WREG, f	Move WREG to f	1	1	None
		MOV.D	Wns,Wd	Move Double from W(ns):W(ns + 1) to Wd	1	2	None
		MOV.D	Ws, Wnd	Move Double from Ws to W(nd + 1):W(nd)	1	2	None
62	MOVPAG	MOVPAG	#lit10,DSRPAG	Move 10-bit Literal to DSRPAG	1	1	None
		MOVPAG	#lit8,TBLPAG	Move 8-bit Literal to TBLPAG	1	1	None
		MOVPAG	Ws, DSRPAG	Move Ws<9:0> to DSRPAG	1	1	None
		MOVPAG	Ws, TBLPAG	Move Ws<7:0> to TBLPAG	1	1	None
64	MOVSAC	MOVSAC	Acc, Wx, Wxd, Wy, Wyd, AWB	Prefetch and Store Accumulator	1	1	None
65	MPY	MPY	Wm*Wn, Acc, Wx, Wxd, Wy, Wyd	Multiply Wm by Wn to Accumulator	1	1	OA,OB,OAB, SA,SB,SAB
		MPY	Wm*Wm, Acc, Wx, Wxd, Wy, Wyd	Square Wm to Accumulator	1	1	OA,OB,OAB, SA,SB,SAB
66	MPY.N	MPY.N	Wm*Wn, Acc, Wx, Wxd, Wy, Wyd	-(Multiply Wm by Wn) to Accumulator	1	1	None
67	MSC	MSC	Wm*Wm, Acc, Wx, Wxd, Wy, Wyd, AWB	Multiply and Subtract from Accumulator	1	1	OA,OB,OAB, SA,SB,SAB
68	MUL	MUL.SS	Wb, Ws, Wnd	{Wnd + 1, Wnd} = Signed(Wb) * Signed(Ws)	1	1	None
		MUL.SS	Wb, Ws, Acc	Accumulator = Signed(Wb) * Signed(Ws)	1	1	None
		MUL.SU	Wb, Ws, Wnd	{Wnd + 1, Wnd} = Signed(Wb) * Unsigned(Ws)	1	1	None
		MUL.SU	Wb, Ws, Acc	Accumulator = Signed(Wb) * Unsigned(Ws)	1	1	None
		MUL.SU	Wb,#lit5,Acc	Accumulator = Signed(Wb) * Unsigned(lit5)	1	1	None
		MUL.US	Wb, Ws, Wnd	{Wnd + 1, Wnd} = Unsigned(Wb) * Signed(Ws)	1	1	None
		MUL.US	Wb, Ws, Acc	Accumulator = Unsigned(Wb) * Signed(Ws)	1	1	None
		MUL.UU	Wb, Ws, Wnd	{Wnd + 1, Wnd} = Unsigned(Wb) * Unsigned(Ws)	1	1	None
		MUL.UU	Wb,#lit5,Acc	Accumulator = Unsigned(Wb) * Unsigned(lit5)	1	1	None
		MUL.UU	Wb, Ws, Acc	Accumulator = Unsigned(Wb) * Unsigned(Ws)	1	1	None
		MULW.SS	Wb, Ws, Wnd	Wnd = Signed(Wb) * Signed(Ws)	1	1	None
		MULW.SU	Wb, Ws, Wnd	Wnd = Signed(Wb) * Unsigned(Ws)	1	1	None
		MULW.US	Wb, Ws, Wnd	Wnd = Unsigned(Wb) * Signed(Ws)	1	1	None
		MULW.UU	Wb, Ws, Wnd	Wnd = Unsigned(Wb) * Unsigned(Ws)	1	1	None
		MUL.SU	Wb,#lit5,Wnd	{Wnd + 1, Wnd} = Signed(Wb) * Unsigned(lit5)	1	1	None
		MUL.SU	Wb,#lit5,Wnd	Wnd = Signed(Wb) * Unsigned(lit5)	1	1	None
		MUL.UU	Wb,#lit5,Wnd	{Wnd + 1, Wnd} = Unsigned(Wb) * Unsigned(lit5)	1	1	None
		MUL.UU	Wb,#lit5,Wnd	Wnd = Unsigned(Wb) * Unsigned(lit5)	1	1	None
		MUL	f	W3:W2 = f * WREG	1	1	None
					•		

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic			Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
69	NEG	NEG Acc		Negate Accumulator	1	1	OA,OB,OAB, SA,SB,SAB
		NEG	f	$f = \overline{f} + 1$	1	1	C,DC,N,OV,Z
		NEG	f,WREG	WREG = \bar{f} + 1	1	1	C,DC,N,OV,Z
		NEG	Ws,Wd	$Wd = \overline{Ws} + 1$	1	1	C,DC,N,OV,Z
70	NOP	NOP		No Operation	1	1	None
		NOPR		No Operation	1	1	None
71	NORM	NORM	Acc, Wd	Normalize Accumulator	1	1	N,OV,Z
72	POP	POP	f	Pop f from Top-of-Stack (TOS)	1	1	None
		POP	Wdo	Pop from Top-of-Stack (TOS) to Wdo	1	1	None
		POP.D	Wnd	Pop from Top-of-Stack (TOS) to W(nd):W(nd + 1)	1	2	None
		POP.S		Pop Shadow Registers	1	1	All
73	PUSH	PUSH	f	Push f to Top-of-Stack (TOS)	1	1	None
		PUSH	Wso	Push Wso to Top-of-Stack (TOS)	1	1	None
		PUSH.D	Wns	Push W(ns):W(ns + 1) to Top-of-Stack (TOS)	1	2	None
		PUSH.S		Push Shadow Registers	1	1	None
74	PWRSAV	PWRSAV	#lit1	Go into Sleep or Idle mode	1	1	WDTO,Sleep
75	RCALL	RCALL	Expr	Relative Call	1	4	SFA
		RCALL	Wn	Computed Call	1	4	SFA
76	REPEAT	REPEAT	#lit15	Repeat Next Instruction lit15 + 1 times	1	1	None
		REPEAT	Wn	Repeat Next Instruction (Wn) + 1 times	1	1	None
77	RESET	RESET		Software Device Reset	1	1	None
78	RETFIE	RETFIE		Return from Interrupt	1	6 (5)	SFA
79	RETLW	RETLW	#lit10,Wn	Return with Literal in Wn	1	6 (5)	SFA
80	RETURN	RETURN		Return from Subroutine	1	6 (5)	SFA
81	RLC	RLC	f	f = Rotate Left through Carry f	1	1	C,N,Z
		RLC	f,WREG	WREG = Rotate Left through Carry f	1	1	C,N,Z
		RLC	Ws,Wd	Wd = Rotate Left through Carry Ws	1	1	C,N,Z
82	RLNC	RLNC	f	f = Rotate Left (No Carry) f	1	1	N,Z
		RLNC	f,WREG	WREG = Rotate Left (No Carry) f	1	1	N,Z
		RLNC	Ws,Wd	Wd = Rotate Left (No Carry) Ws	1	1	N,Z
83	RRC	RRC	f	f = Rotate Right through Carry f	1	1	C,N,Z
		RRC	f,WREG	WREG = Rotate Right through Carry f	1	1	C,N,Z
		RRC	Ws,Wd	Wd = Rotate Right through Carry Ws	1	1	C,N,Z
84	RRNC	RRNC	f	f = Rotate Right (No Carry) f	1	1	N,Z
		RRNC	f,WREG	WREG = Rotate Right (No Carry) f	1	1	N,Z
		RRNC	Ws,Wd	Wd = Rotate Right (No Carry) Ws	1	1	N,Z
85	SAC	SAC	Acc, #Slit4, Wdo	Store Accumulator	1	1	None
		SAC.R	Acc, #Slit4, Wdo	Store Rounded Accumulator	1	1	None
86	SE	SE	Ws, Wnd	Wnd = Sign-Extended Ws	1	1	C,N,Z
87	SETM	SETM	f	f = 0xFFFF	1	1	None
		SETM	WREG	WREG = 0xFFFF	1	1	None
		SETM	Ws	Ws = 0xFFFF	1	1	None
88	SFTAC	SFTAC	Acc, Wn	Arithmetic Shift Accumulator by (Wn)	1	1	OA,OB,OAB, SA,SB,SAB
		SFTAC	Acc, #Slit6	Arithmetic Shift Accumulator by Slit6	1	1	OA,OB,OAB, SA,SB,SAB

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT #5" instruction, such that they are executed six consecutive times.

TABLE 31-2: INSTRUCTION SET OVERVIEW (CONTINUED)

Base Instr #	Assembly Mnemonic		Assembly Syntax	Description	# of Words	# of Cycles ⁽¹⁾	Status Flags Affected
89	SL	SL	f	f = Left Shift f	1	1	C,N,OV,Z
		SL	f,WREG	WREG = Left Shift f	1	1	C,N,OV,Z
		SL	Ws,Wd	Wd = Left Shift Ws	1	1	C,N,OV,Z
		SL	Wb, Wns, Wnd	Wnd = Left Shift Wb by Wns	1	1	N,Z
		SL	Wb,#lit5,Wnd	Wnd = Left Shift Wb by lit5	1	1	N,Z
91	SUB	SUB	Acc	Subtract Accumulators	1	1	OA,OB,OAB, SA,SB,SAB
		SUB	f	f = f – WREG	1	1	C,DC,N,OV,Z
		SUB	f,WREG	WREG = f – WREG	1	1	C,DC,N,OV,Z
		SUB	#lit10,Wn	Wn = Wn – lit10	1	1	C,DC,N,OV,Z
		SUB	Wb,Ws,Wd	Wd = Wb – Ws	1	1	C,DC,N,OV,Z
		SUB	Wb,#lit5,Wd	Wd = Wb - lit5	1	1	C,DC,N,OV,Z
92	SUBB	SUBB	f	$f = f - WREG - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBB	f,WREG	$WREG = f - WREG - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBB	#lit10,Wn	$Wn = Wn - lit10 - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBB	Wb,Ws,Wd	$Wd = Wb - Ws - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBB	Wb,#lit5,Wd	$Wd = Wb - lit5 - (\overline{C})$	1	1	C,DC,N,OV,Z
93	SUBR	SUBR	f	f = WREG – f	1	1	C,DC,N,OV,Z
		SUBR	f,WREG	WREG = WREG - f	1	1	C,DC,N,OV,Z
		SUBR	Wb, Ws, Wd	Wd = Ws - Wb	1	1	C,DC,N,OV,Z
		SUBR	Wb,#lit5,Wd	Wd = lit5 – Wb	1	1	C,DC,N,OV,Z
94	SUBBR	SUBBR	f	$f = WREG - f - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBBR	f,WREG	WREG = WREG $- f - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBBR	Wb,Ws,Wd	$Wd = Ws - Wb - (\overline{C})$	1	1	C,DC,N,OV,Z
		SUBBR	Wb,#lit5,Wd	$Wd = lit5 - Wb - (\overline{C})$	1	1	C,DC,N,OV,Z
95	SWAP	SWAP.b	Wn	Wn = Nibble Swap Wn	1	1	None
		SWAP	Wn	Wn = Byte Swap Wn	1	1	None
96	TBLRDH	TBLRDH	Ws,Wd	Read Prog<23:16> to Wd<7:0>	1	5	None
97	TBLRDL	TBLRDL	Ws,Wd	Read Prog<15:0> to Wd	1	5	None
98	TBLWTH	TBLWTH	Ws,Wd	Write Ws<7:0> to Prog<23:16>	1	2	None
99	TBLWTL	TBLWTL	Ws,Wd	Write Ws to Prog<15:0>	1	2	None
101	ULNK	ULNK		Unlink Frame Pointer	1	1	SFA
104	XOR	XOR	f	f = f .XOR. WREG	1	1	N,Z
		XOR	f,WREG	WREG = f.XOR. WREG	1	1	N,Z
		XOR	#lit10,Wn	Wd = lit10 .XOR. Wd	1	1	N,Z
		XOR	Wb,Ws,Wd	Wd = Wb .XOR. Ws	1	1	N,Z
		XOR	Wb,#lit5,Wd	Wd = Wb .XOR. lit5	1	1	N,Z
105	ZE	ZE	Ws, Wnd	Wnd = Zero-Extend Ws	1	1	C,Z,N

Note 1: Read and Read-Modify-Write (e.g., bit operations and logical operations) on non-CPU SFRs incur an additional instruction cycle.

^{2:} The divide instructions must be preceded with a "REPEAT" #5" instruction, such that they are executed six consecutive times.

32.0 DEVELOPMENT SUPPORT

The PIC[®] microcontrollers (MCU) and dsPIC[®] digital signal controllers (DSC) are supported with a full range of software and hardware development tools:

- · Integrated Development Environment
 - MPLAB® X IDE Software
- · Compilers/Assemblers/Linkers
 - MPLAB XC Compiler
 - MPASMTM Assembler
 - MPLINK[™] Object Linker/ MPLIB[™] Object Librarian
 - MPLAB Assembler/Linker/Librarian for Various Device Families
- Simulators
 - MPLAB X SIM Software Simulator
- Emulators
 - MPLAB REAL ICE™ In-Circuit Emulator
- In-Circuit Debuggers/Programmers
 - MPLAB ICD 3
 - PICkit™ 3
- · Device Programmers
 - MPLAB PM3 Device Programmer
- Low-Cost Demonstration/Development Boards, Evaluation Kits and Starter Kits
- · Third-party development tools

32.1 MPLAB X Integrated Development Environment Software

The MPLAB X IDE is a single, unified graphical user interface for Microchip and third-party software, and hardware development tool that runs on Windows[®], Linux and Mac OS[®] X. Based on the NetBeans IDE, MPLAB X IDE is an entirely new IDE with a host of free software components and plug-ins for high-performance application development and debugging. Moving between tools and upgrading from software simulators to hardware debugging and programming tools is simple with the seamless user interface.

With complete project management, visual call graphs, a configurable watch window and a feature-rich editor that includes code completion and context menus, MPLAB X IDE is flexible and friendly enough for new users. With the ability to support multiple tools on multiple projects with simultaneous debugging, MPLAB X IDE is also suitable for the needs of experienced users.

Feature-Rich Editor:

- Color syntax highlighting
- Smart code completion makes suggestions and provides hints as you type
- Automatic code formatting based on user-defined rules
- · Live parsing

User-Friendly, Customizable Interface:

- Fully customizable interface: toolbars, toolbar buttons, windows, window placement, etc.
- · Call graph window

Project-Based Workspaces:

- · Multiple projects
- · Multiple tools
- · Multiple configurations
- · Simultaneous debugging sessions

File History and Bug Tracking:

- · Local file history feature
- Built-in support for Bugzilla issue tracker

32.2 MPLAB XC Compilers

The MPLAB XC Compilers are complete ANSI C compilers for all of Microchip's 8, 16 and 32-bit MCU and DSC devices. These compilers provide powerful integration capabilities, superior code optimization and ease of use. MPLAB XC Compilers run on Windows, Linux or MAC OS X.

For easy source level debugging, the compilers provide debug information that is optimized to the MPLAB X IDE.

The free MPLAB XC Compiler editions support all devices and commands, with no time or memory restrictions, and offer sufficient code optimization for most applications.

MPLAB XC Compilers include an assembler, linker and utilities. The assembler generates relocatable object files that can then be archived or linked with other relocatable object files and archives to create an executable file. MPLAB XC Compiler uses the assembler to produce its object file. Notable features of the assembler include:

- · Support for the entire device instruction set
- · Support for fixed-point and floating-point data
- · Command-line interface
- · Rich directive set
- Flexible macro language
- · MPLAB X IDE compatibility

32.3 MPASM Assembler

The MPASM Assembler is a full-featured, universal macro assembler for PIC10/12/16/18 MCUs.

The MPASM Assembler generates relocatable object files for the MPLINK Object Linker, Intel® standard HEX files, MAP files to detail memory usage and symbol reference, absolute LST files that contain source lines and generated machine code, and COFF files for debugging.

The MPASM Assembler features include:

- Integration into MPLAB X IDE projects
- User-defined macros to streamline assembly code
- Conditional assembly for multipurpose source files
- Directives that allow complete control over the assembly process

32.4 MPLINK Object Linker/ MPLIB Object Librarian

The MPLINK Object Linker combines relocatable objects created by the MPASM Assembler. It can link relocatable objects from precompiled libraries, using directives from a linker script.

The MPLIB Object Librarian manages the creation and modification of library files of precompiled code. When a routine from a library is called from a source file, only the modules that contain that routine will be linked in with the application. This allows large libraries to be used efficiently in many different applications.

The object linker/library features include:

- Efficient linking of single libraries instead of many smaller files
- Enhanced code maintainability by grouping related modules together
- Flexible creation of libraries with easy module listing, replacement, deletion and extraction

32.5 MPLAB Assembler, Linker and Librarian for Various Device Families

MPLAB Assembler produces relocatable machine code from symbolic assembly language for PIC24, PIC32 and dsPIC DSC devices. MPLAB XC Compiler uses the assembler to produce its object file. The assembler generates relocatable object files that can then be archived or linked with other relocatable object files and archives to create an executable file. Notable features of the assembler include:

- Support for the entire device instruction set
- Support for fixed-point and floating-point data
- · Command-line interface
- · Rich directive set
- · Flexible macro language
- · MPLAB X IDE compatibility

32.6 MPLAB X SIM Software Simulator

The MPLAB X SIM Software Simulator allows code development in a PC-hosted environment by simulating the PIC MCUs and dsPIC DSCs on an instruction level. On any given instruction, the data areas can be examined or modified and stimuli can be applied from a comprehensive stimulus controller. Registers can be logged to files for further run-time analysis. The trace buffer and logic analyzer display extend the power of the simulator to record and track program execution, actions on I/O, most peripherals and internal registers.

The MPLAB X SIM Software Simulator fully supports symbolic debugging using the MPLAB XC Compilers, and the MPASM and MPLAB Assemblers. The software simulator offers the flexibility to develop and debug code outside of the hardware laboratory environment, making it an excellent, economical software development tool.

32.7 MPLAB REAL ICE In-Circuit Emulator System

The MPLAB REAL ICE In-Circuit Emulator System is Microchip's next generation high-speed emulator for Microchip Flash DSC and MCU devices. It debugs and programs all 8, 16 and 32-bit MCU, and DSC devices with the easy-to-use, powerful graphical user interface of the MPLAB X IDE.

The emulator is connected to the design engineer's PC using a high-speed USB 2.0 interface and is connected to the target with either a connector compatible with in-circuit debugger systems (RJ-11) or with the new high-speed, noise tolerant, Low-Voltage Differential Signal (LVDS) interconnection (CAT5).

The emulator is field upgradable through future firmware downloads in MPLAB X IDE. MPLAB REAL ICE offers significant advantages over competitive emulators including full-speed emulation, run-time variable watches, trace analysis, complex breakpoints, logic probes, a ruggedized probe interface and long (up to three meters) interconnection cables.

32.8 MPLAB ICD 3 In-Circuit Debugger System

The MPLAB ICD 3 In-Circuit Debugger System is Microchip's most cost-effective, high-speed hardware debugger/programmer for Microchip Flash DSC and MCU devices. It debugs and programs PIC Flash microcontrollers and dsPIC DSCs with the powerful, yet easy-to-use graphical user interface of the MPLAB IDE.

The MPLAB ICD 3 In-Circuit Debugger probe is connected to the design engineer's PC using a high-speed USB 2.0 interface and is connected to the target with a connector compatible with the MPLAB ICD 2 or MPLAB REAL ICE systems (RJ-11). MPLAB ICD 3 supports all MPLAB ICD 2 headers.

32.9 PICkit 3 In-Circuit Debugger/ Programmer

The MPLAB PICkit 3 allows debugging and programming of PIC and dsPIC Flash microcontrollers at a most affordable price point using the powerful graphical user interface of the MPLAB IDE. The MPLAB PICkit 3 is connected to the design engineer's PC using a full-speed USB interface and can be connected to the target via a Microchip debug (RJ-11) connector (compatible with MPLAB ICD 3 and MPLAB REAL ICE). The connector uses two device I/O pins and the Reset line to implement in-circuit debugging and In-Circuit Serial Programming™ (ICSP™).

32.10 MPLAB PM3 Device Programmer

The MPLAB PM3 Device Programmer is a universal, CE compliant device programmer with programmable voltage verification at VDDMIN and VDDMAX for maximum reliability. It features a large LCD display (128 x 64) for menus and error messages, and a modular, detachable socket assembly to support various package types. The ICSP cable assembly is included as a standard item. In Stand-Alone mode, the MPLAB PM3 Device Programmer can read, verify and program PIC devices without a PC connection. It can also set code protection in this mode. The MPLAB PM3 connects to the host PC via an RS-232 or USB cable. The MPLAB PM3 has high-speed communications and optimized algorithms for quick programming of large memory devices, and incorporates an MMC card for file storage and data applications.

32.11 Demonstration/Development Boards, Evaluation Kits and Starter Kits

A wide variety of demonstration, development and evaluation boards for various PIC MCUs and dsPIC DSCs allows quick application development on fully functional systems. Most boards include prototyping areas for adding custom circuitry and provide application firmware and source code for examination and modification.

The boards support a variety of features, including LEDs, temperature sensors, switches, speakers, RS-232 interfaces, LCD displays, potentiometers and additional EEPROM memory.

The demonstration and development boards can be used in teaching environments, for prototyping custom circuits and for learning about various microcontroller applications.

In addition to the PICDEM™ and dsPICDEM™ demonstration/development board series of circuits, Microchip has a line of evaluation kits and demonstration software for analog filter design, KEELoq® security ICs, CAN, IrDA®, PowerSmart battery management, SEEVAL® evaluation system, Sigma-Delta ADC, flow rate sensing, plus many more.

Also available are starter kits that contain everything needed to experience the specified device. This usually includes a single application and debug capability, all on one board.

Check the Microchip web page (www.microchip.com) for the complete list of demonstration, development and evaluation kits.

32.12 Third-Party Development Tools

Microchip also offers a great collection of tools from third-party vendors. These tools are carefully selected to offer good value and unique functionality.

- Device Programmers and Gang Programmers from companies, such as SoftLog and CCS
- Software Tools from companies, such as Gimpel and Trace Systems
- Protocol Analyzers from companies, such as Saleae and Total Phase
- Demonstration Boards from companies, such as MikroElektronika, Digilent[®] and Olimex
- Embedded Ethernet Solutions from companies, such as EZ Web Lynx, WIZnet and IPLogika[®]

33.0 ELECTRICAL CHARACTERISTICS

This section provides an overview of the dsPIC33CK256MP508 family electrical characteristics. Additional information will be provided in future revisions of this document as it becomes available.

Absolute maximum ratings for the dsPIC33CK256MP508 family are listed below. Exposure to these maximum rating conditions for extended periods may affect device reliability. Functional operation of the device at these, or any other conditions above the parameters indicated in the operation listings of this specification, is not implied.

Absolute Maximum Ratings⁽¹⁾

Ambient temperature under bias	40°C to +125°C
Storage temperature	65°C to +150°C
Voltage on VDD with respect to Vss	0.3V to +4.0V
Voltage on any pin that is not 5V tolerant with respect to Vss ⁽³⁾	0.3V to (VDD + 0.3V)
Voltage on any 5V tolerant pin with respect to Vss when $VDD \ge 3.0V^{(3)}$	0.3V to +5.5V
Voltage on any 5V tolerant pin with respect to Vss when VDD < 3.0V ⁽³⁾	0.3V to +3.6V
Maximum current out of Vss pin	300 mA
Maximum current into VDD pin ⁽²⁾	300 mA
Maximum current sunk/sourced by any 4x I/O pin	15 mA
Maximum current sunk/sourced by any 8x I/O pin	25 mA
Maximum current sunk by all ports ⁽²⁾	200 mA

- **Note 1:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those, or any other conditions above those indicated in the operation listings of this specification, is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.
 - 2: Maximum allowable current is a function of device maximum power dissipation (see Table 33-2).
 - 3: See the "Pin Diagrams" section for the 5V tolerant pins.

33.1 DC Characteristics

TABLE 33-1: OPERATING MIPS vs. VOLTAGE

VDD Range	Temperature Range	Maximum CPU Clock Frequency
3.0V to 3.6V	-40°C to +85°C	100
3.0V to 3.6V	-40°C to +125°C	100

TABLE 33-2: THERMAL OPERATING CONDITIONS

Rating	Symbol	Min.	Max.	Unit
Industrial Temperature Devices				
Operating Junction Temperature Range	TJ	-40	+125	°C
Operating Ambient Temperature Range	TA	-40	+85	°C
Extended Temperature Devices				
Operating Junction Temperature Range	TJ	-40	+140	°C
Operating Ambient Temperature Range	TA	-40	+125	°C
Power Dissipation: Internal Chip Power Dissipation: $PINT = VDD \ x \ (IDD - \Sigma \ IOH)$	Po	PINT ·	+ Pı/o	W
I/O Pin Power Dissipation: I/O = Σ ({VDD - VOH} x IOH) + Σ (VOL x IOL)				
Maximum Allowed Power Dissipation	PDMAX	(TJ – ¯	ΓΑ)/θJΑ	W

TABLE 33-3: THERMAL PACKAGING CHARACTERISTICS⁽¹⁾

Characteristic	Symbol	Тур.	Unit
Package Thermal Resistance, 80-Pin TQFP 12x12x1 mm	θЈА	50.67	°C/W
Package Thermal Resistance, 64-Pin TQFP 10x10x1.0 mm	θJA	45.7	°C/W
Package Thermal Resistance, 64-Pin QFN 9x9 mm	θJA	18.7	°C/W
Package Thermal Resistance, 48-Pin TQFP 7x7 mm	θJΑ	62.76	°C/W
Package Thermal Resistance, 48-Pin UQFN 6x6 mm	θJA	27.6	°C/W
Package Thermal Resistance, 36-Pin UQFN 5x5 mm	θJA	29.2	°C/W
Package Thermal Resistance, 28-Pin UQFN 6x6 mm	θJΑ	22.41	°C/W
Package Thermal Resistance, 28-Pin SSOP 5.30 mm	θЈА	52.84	°C/W

Note 1: Junction to ambient thermal resistance, Theta-JA (θ JA) numbers are achieved by package simulations.

TABLE 33-4: OPERATING VOLTAGE SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)⁽¹⁾ Operating temperature -40°C ≤ TA ≤ +85°C for Industrial $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended **Param** Units Symbol Characteristic Min. Тур. Max. **Conditions** No. **Operating Voltage** DC10 VDD **Supply Voltage** 3.0 3.6 ٧ DC16 **V**POR **VDD Start Voltage** Vss to Ensure Internal Power-on Reset Signal SVDD DC17 V_{DD} Rise Rate 1.0 V/ms 0V-3V in 3 ms

Note 1: Device is functional at VBORMIN < VDD < VDDMIN. Analog modules (ADC and comparators) may have degraded performance.

2.68

2.84

2.99

٧

BOR Event on VDD Transition

to Ensure Internal Power-on Reset Signal

High-to-Low(2)

BO10

VBOR

^{2:} Parameters are characterized but not tested.

TABLE 33-5: OPERATING CURRENT (IDD)(2)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} < \text{TA} \le +125^{\circ}\text{C}$ for Extended

-40°C ≤ TA ≤ +125°C for Extended									
Parameter No.	Typ. ⁽¹⁾	Max.	Units	Conditions					
DC20	7.76	10.7	mA	-40°C					
	7.49	10	mA	+25°C	2.21/	10 MIPS (N1 = 1, N2 = 5, N3 = 2,			
	7.82	15.5	mA	+85°C	3.3V	M = 50, Fvco = 400 MHz, FPLLO = 40 MHz)			
	10.32	23.5	mA	+125°C					
DC21	10.36	13.1	mA	-40°C					
	10.09	12.45	mA	+25°C	3.3V	20 MIPS (N1 = 1, N2 = 5, N3 = 1, M = 50, Fvco = 400 MHz,			
	10.42	17.5	mA	+85°C	3.30	FPLLO = 80 MHz)			
	12.89	25.5	mA	+125°C					
DC22	14.54	17.45	mA	-40°C					
	14.26	16.7	mA	+25°C	3.3V	40 MIPS (N1 = 1, N2 = 3, N3 = 1, M = 60, Fvco = 480 MHz,			
	14.58	22	mA	+85°C		FPLLO = 160 MHz)			
	17.06	30	mA	+125°C		,			
DC23	22.2	25.4	mA	-40°C					
	21.91	24.9	mA	+25°C	3.3V	70 MIPS (N1 = 1, N2 = 2, N3 = 1, M = 70, Fvco = 560 MHz,			
	22.21	30.75	mA	+85°C	3.5 V	FPLLO = 280 MHz)			
	24.65	37.5	mA	+125°C					
DC24	27.36	30.7	mA	-40°C					
	26.96	30.5	mA	+25°C	3.3V	90 MIPS (N1 = 1, N2 = 2, N3 = 1, M = 90, Fvco = 720 MHz,			
	26.68	35	mA	+85°C	3.3 V	FPLLO = 360 MHz)			
	29.01	42	mA	+125°C		,			
DC25	27.14	30.9	mA	-40°C					
	26.54	30.1	mA	+25°C	3.3V	100 MIPS (N1 = 1, N2 = 1, N3 = 1, M = 50, Fvco = 400 MHz,			
	26.79	35	mA	+85°C	J.JV	FPLLO = 400 MHz)			
	29.23	42.5	mA	+125°C		,			

Note 1: Data in the "Typ." column are for design guidance only and are not tested.

- 2: Base Run current (IDD) is measured as follows:
 - · Oscillator is switched to EC+PLL mode in software
 - OSC1 pin is driven with external 8 MHz square wave with levels from 0.3V to VDD 0.3V
 - OSC2 is configured as an I/O in the Configuration Words (OSCIOFCN (FOSC<2>) = 0)
 - FSCM is disabled (FCKSM<1:0> (FOSC<7:6>) = 01)
 - Watchdog Timer is disabled (FWDT<15> = 0 and WDTCONL<15> = 0)
 - · All I/O pins (except OSC1) are configured as outputs and driving low
 - No peripheral modules are operating or being clocked (defined PMDx bits are all '1's)
 - JTAG is disabled (JTAGEN (FICD<5>) = 0)
 - NOP instructions are executed in while (1) loop

TABLE 33-6: IDLE CURRENT (IIDLE)(2)

	3. 0V to 3.6 -40°C ≤ TA -40°C ≤ TA	4 ≤ +85°C	for Indu	strial				
Parameter No.	Typ. ⁽¹⁾	Max.	Units	Conditions				
DC40	6.41	8.47	mA	-40°C				
	6.15 7.57 mA +25°C	3.3V	10 MIPS (N1 = 1, N2 = 5, N3 = 2,					
	6.45	13	mA	+85°C	3.30	M = 50, Fvco = 400 MHz, FPLLO = 40 MHz)		
	8.95	22	mA	+125°C	1			
DC41	7.31	10.1	mA	-40°C				
	7.04	9.1	mA	+25°C	3.3V	20 MIPS (N1 = 1, N2 = 5, N3 = 1, M = 50, Fvco = 400 MHz,		
	7.36	14.75	mA	+85°C	3.3	FPLLO = 80 MHz)		
	9.83	22.75	mA	+125°C				
DC42	9.4	12.3	mA	-40°C	3.3V			
	9.13	11.2	mA	+25°C		40 MIPS (N1 = 1, N2 = 3, N3 = 1, M = 60, FVCO = 480 MHz,		
	9.45	16.5	mA	+85°C		FPLLO = 160 MHz)		
	11.92	25	mA	+125°C				
DC43	12.39	15.3	mA	-40°C				
	12.11	14.3	mA	+25°C	3.3V	70 MIPS (N1 = 1, N2 = 2, N3 = 1, M = 70, Fvco = 560 MHz,		
	12.43	19.75	mA	+85°C	3.34	FPLLO = 280 MHz)		
	14.89	28.25	mA	+125°C				
DC44	14.78	17.85	mA	-40°C				
	14.5	16.9	mA	+25°C	3.3V	90 MIPS (N1 = 1, N2 = 2, N3 = 1, M = 90, FVCO = 720 MHz,		
	14.81	22.5	mA	+85°C	3.34	FPLLO = 360 MHz)		
	17.26	29.5	mA	+125°C				
DC45	14.44	17.55	mA	-40°C				
	14.15	16.5	mA	+25°C	3.3V	100 MIPS (N1 = 1, N2 = 1, N3 = 1, M = 50, FVCO = 400 MHz,		
	14.46	22.25	mA	+85°C	3.3V	FPLLO = 400 MHz)		
	16.9	30	mA	+125°C				

Note 1: Data in the "Typ." column are for design guidance only and are not tested.

- 2: Base Idle current (IIDLE) is measured as follows:
 - · Oscillator is switched to EC+PLL mode in software
 - OSC1 pin is driven with external 8 MHz square wave with levels from 0.3V to VDD 0.3V
 - OSC2 is configured as an I/O in the Configuration Words (OSCIOFCN (FOSC<2>) = 0)
 - FSCM is disabled (FCKSM<1:0> (FOSC<7:6>) = 01)
 - Watchdog Timer is disabled (FWDT<15> = 0 and WDTCONL<15> = 0)
 - · All I/O pins (except OSC1) are configured as outputs and driving low
 - No peripheral modules are operating or being clocked (defined PMDx bits are all '1's)
 - JTAG is disabled (JTAGEN (FICD<5>) = 0)
 - Flash in standby with NVMSIDL (NVMCON<12>) = 1

TABLE 33-7: POWER-DOWN CURRENT (IPD)(2)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Parameter No.	Characteristic	Typ. ⁽¹⁾	Max.	Units	Conditions		
DC60	Base Power-Down Current	270	383	μΑ	-40°C		
		418.99	1000	μA	+25°C	3.3V	
		939.53	7250	μΑ	+85°C	3.3V	
		5.59	18.5	mA	+125°C ⁽³⁾		

Note 1: Data in the "Typ." column are for design guidance only and are not tested.

2: Base Sleep current (IPD) is measured as follows:

- OSC1 pin is driven with external 8 MHz square wave with levels from 0.3V to VDD-0.3V
- OSC2 is configured as an I/O in the Configuration Words (OSCIOFCN (FOSC<2>) = 0)
- FSCM is disabled (FCKSM<1:0> (FOSC<7:6>) = 01)
- Watchdog Timer is disabled (FWDT<15> = 0 and WDTCONL<15> = 0)
- · All I/O pins (except OSC1) are configured as outputs and driving low
- No peripheral modules are operating or being clocked (defined PMDx bits are all '1's)
- JTAG is disabled (JTAGEN (FICD<5>) = 0)
- The regulators are in Standby mode (VREGS (RCON<8>) = 0
- The regulators are in Low-Power mode (LPWREN (VREGCON<15>) = 1
- 3: The regulators are in High-Power mode (LPWREN (VREGCON<15>) = 0.

TABLE 33-8: DOZE CURRENT (IDOZE)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended										
Parameter No.	Typ. ⁽¹⁾	Max.	Doze Ratio	Units	Conditions					
DC70	18.19	20	1:2	mA	-40°C					
	12.66	15	1:128	mA	-40 C					
	17.54	20.15	1:2	mA	+25°C					
	12.39	14.7	1:128	mA	+25 C	3.3V	70 MIPS			
	17.85	25	1:2	mA	+85°C	3.30	70 101173			
	12.7	20	1:128	mA	+03 C					
	20.32	32.5	1:2	mA	1405°0					
	15.17	28.5	1:128	mA	+125°C					
DC71	22.3	25.55	1:2	mA	-40°C					
	14.83	17.25	1:128	mA	-40 C					
	21.86	25.05	1:2	mA	+25°C					
	14.55	16.95	1:128	mA	+25 C	2 21/	100 MIDS			
	22.16	30	1:2	mA	105°C	3.3V 100 MIP	100 MIPS			
	14.86	22	1:128	mA	+85°C					
	24.62	36.5	1:2	mA	±125°C					
	17.31	30	1:128	mA	+125°C					

Note 1: Data in the "Typ." column are for design guidance only and are not tested.

TABLE 33-9: WATCHDOG TIMER DELTA CURRENT (△IWDT)⁽¹⁾

Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended										
Parameter No.	Тур.	Max.	Units Conditions							
DC61	0.75	5	μΑ	-40°C						
	2.0	12	μΑ	+25°C	3.3V					
	3.88	24	μΑ	+85°C	3.3V					
	5.69	40	μΑ	+125°C						

Note 1: The ΔIWDT current is the additional current consumed when the module is enabled. This current should be added to the base IPD current. All parameters are characterized but not tested during manufacturing.

TABLE 33-10: PWM DELTA CURRENT(1)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended											
Parameter No.	Тур.	Max.	Units			Conditions					
DC100	5.96	6.6	mA	-40°C		PWM Output Frequency = 500 kHz,					
	5.99	6.7	mA	+25°C	2 21/	PWM Input (AFPLLO = 500 MHz)					
	5.92	6.9	mA	+85°C	3.3V	(AVCO = 1000 MHz, PLLFBD = 125,					
	5.47	7	mA	+125°C		APLLDIV1 = 2)					
DC101	4.89	5.4	mA	-40°C		PWM Output Frequency = 500 kHz,					
	4.91	5.5	mA	+25°C	3.3V	PWM Input (AFPLLO = 400 MHz),					
	4.85	5.7	mA	+85°C	3.30	(AVCO = 400 MHz, PLLFBD = 50,					
	4.42	5.7	mA	+125°C		APLLDIV1 = 1)					
DC102	2.77	3.7	mA	-40°C		PWM Output Frequency = 500 kHz,					
	2.75	3.7	mA	+25°C	3.3V	PWM Input (AFPLLO = 200 MHz),					
	2.7	3.7	mA	+85°C	3.3V	(AVCO = 400 MHz, PLLFBD = 50,					
	2.26	3.7	mA	+125°C		APLLDIV1 = 2)					
DC103	1.67	2	mA	-40°C		PWM Output Frequency = 500 kHz,					
	1.66	2.2	mA	+25°C	3.3V	PWM Input (AFPLLO = 100 MHz),					
	1.63	2.3	mA	+85°C	3.3v	(AVCO = 400 MHz, PLLFBD = 50,					
	1.17	2.3	mA	+125°C		APLLDIV1 = 4)					

Note 1: APLL current is not included. The APLL current will be the same if more than one PWM is running. Listed delta currents are for only one PWM instance when HREN = 0 (PGxCONL<7>). All parameters are characterized but not tested during manufacturing.

TABLE 33-11: APLL DELTA CURRENT

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

	-40°C ≤ TA ≤ +125°C for Extended											
Parameter No.	Тур.	Max.	Units			Conditions ⁽¹⁾						
DC110	5.93	6.6	mA	-40°C								
	5.95	7	mA	+25°C	3.3V	AFPLLO = 500 MHz						
	6.15	7.6	mA	+85°C	3.34	(AVCO = 1000 MHz, PLLFBD = 125, APLLDIV1 = 2)						
	7.15	9	mA	+125°C		,						
DC111	2.72	3.3	mA	-40°C								
	2.74	3.7	mA	+25°C	3.3V	AFPLLO = 400 MHz (AVCO = 400 MHz , PLLFBD = 50 ,						
	2.92	4.3	mA	+85°C	3.34	APLLDIV1 = 1)						
	3.87	5.6	mA	+125°C		,						
DC112	1.39	2.7	mA	-40°C								
	1.49	2.7	mA	+25°C	3.3V	AFPLLO = 200 MHz (AVCO = 400 MHz, PLLFBD = 50,						
	1.65	3	mA	+85°C	J.5V	APLLDIV1 = 2)						
	2.6	4.4	mA	+125°C		,						
DC113	0.79	1.1	mA	-40°C								
	0.84	1.4	mA	+25°C	3.3V	AFPLLO = 100 MHz (AVCO = 400 MHz, PLLFBD = 50,						
	0.96	2.3	mA	+85°C	J.50	APLLDIV1 = 4)						
	1.93	3.6	mA	+125°C		,						

Note 1: The APLL current will be the same if more than one PWM or DAC is run to the APLL clock. All parameters are characterized but not tested during manufacturing.

TABLE 33-12: ADC DELTA CURRENT⁽¹⁾

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}C \leq TA \leq +85^{\circ}C$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Parameter No.	Тур.	Max.	Units	Conditions						
DC120	3.61	4	mA	-40°C						
	3.68	4.1	mA	+25°C	3.3V	TAD = 14.3 ns				
	3.69	4.2	mA	+85°C	3.30	(3.5 Msps conversion rate)				
	3.89	4.6	mA	+125°C						

Note 1: Shared core continuous conversion. TAD = 14.3 nS (3.5 Msps conversion rate). Listed delta currents are for only one ADC core. All parameters are characterized but not tested during manufacturing.

TABLE 33-13: COMPARATOR + DAC DELTA CURRENT

Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended									
Parameter No.	Тур.	Max.	Units	Conditions					
DC130	1.2	1.35	mA	-40°C					
	1.23	1.65	mA	+25°C	3.3V	AFPLLO @ 500 MHz ⁽¹⁾			
	1.23	1.65	mA	+85°C	3.34	AFPLLO @ 500 MHZ			
	1.24	1.65	mA	+125°C					

Note 1: APLL current is not included. Listed delta currents are for only one comparator + DAC instance. All parameters are characterized but not tested during manufacturing.

TABLE 33-14: OP AMP DELTA CURRENT⁽¹⁾

Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended								
Parameter No.	Тур.	Max.	Units	Conditions				
DC140	0.25	1	mA	-40°C				
	0.27	1.1	mA	+25°C	3.3V			
	0.32	1.4	mA	+85°C	3.30			
	0.46	1.7	mA	+125°C				

Note 1: Listed delta currents are for only one op amp instance. All parameters are characterized but not tested during manufacturing.

TABLE 33-15: I/O PIN INPUT SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for Industrial $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min. ⁽⁵⁾	Typ. ⁽¹⁾	Max. ⁽⁶⁾	Units	Conditions
	VIL	Input Low Voltage					
DI10		Any I/O Pin and MCLR	Vss	_	0.2 VDD	V	
DI18		I/O Pins with SDAx, SCLx	Vss	_	0.3 VDD	V	SMBus disabled
DI19		I/O Pins with SDAx, SCLx	Vss	_	0.8	V	SMBus enabled
DI20	VIH	Input High Voltage					
		I/O Pins Not 5V Tolerant ⁽³⁾	0.8 VDD	_	VDD	V	
		5V Tolerant I/O Pins and MCLR ⁽³⁾	0.8 VDD	_	5.5	V	
		5V Tolerant I/O Pins with SDAx, SCLx(3)	0.8 VDD	_	5.5	V	SMBus disabled
		5V Tolerant I/O Pins with SDAx, SCLx(3)	2.1	_	5.5	V	SMBus enabled
		I/O Pins with SDAx, SCLx Not 5V Tolerant ⁽³⁾	0.8 VDD	_	VDD	V	SMBus disabled
		I/O Pins with SDAx, SCLx Not 5V Tolerant ⁽³⁾	2.1	_	VDD	V	SMBus enabled
DI30	ICNPU	Input Change Notification Pull-up Current ^(2,4)	175	360	545	μA	VDD = 3.6V, VPIN = VSS
DI31	ICNPD	Input Change Notification Pull-Down Current ⁽⁴⁾	65	215	360	μΑ	VDD = 3.6V, VPIN = VDD
DI50	lıL	Input Leakage Current ⁽²⁾					
		I/O Pins 5V Tolerant ⁽³⁾	-700	_	700	nA	
		I/O Pins Not 5V Tolerant ⁽³⁾	-700	_	700	nA	
		MCLR	-700	_	700	nA	
		OSCI	-700	_	700	nA	XT and HS modes

- 2: Negative current is defined as current sourced by the pin.
- 3: See the "Pin Diagrams" section for the 5V tolerant I/O pins.
- 4: Characterized but not tested.
- 5: VPIN = VSS.
- 6: VPIN = VDD.

TABLE 33-16: I/O PIN INPUT INJECTION CURRENT SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Max.	Units	Conditions
DI60a	licl	Input Low Injection Current	0	-5 ^(1,4)	mA	All pins
DI60b	lich	Input High Injection Current	0	+5(2,3,4)		All pins, excepting all 5V tolerant pins and SOSCI
DI60c	∑lict	Total Input Injection Current (sum of all I/O and control pins) ⁽⁵⁾	-20	+20		Absolute instantaneous sum of all \pm input injection currents from all I/O pins (IICL + IICH) $\leq \sum$ IICT

Note 1: VIL Source < (VSS - 0.3).

- 2: VIH Source > (VDD + 0.3) for non-5V tolerant pins only.
- **3:** 5V tolerant pins do not have an internal high-side diode to VDD, and therefore, cannot tolerate any "positive" input injection current.
- 4: Injection currents can affect the ADC results.
- 5: Any number and/or combination of I/O pins, not excluded under IICL or IICH conditions, are permitted in the sum.

TABLE 33-17: I/O PIN OUTPUT SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for Industrial

-40°C \leq TA \leq +125°C for Extended

		40 0 3 IA 3 1 IZO 0 II	JI EXICII	aca			
Param.	Symbol	Characteristic	Min.	Тур.	Max.	Units	Conditions
DO10	Vol	Output Low Voltage 4x Sink Driver Pins	_	_	0.42	V	VDD = 3.6V, IOL < 9 mA
		Output Low Voltage 8x Sink Driver Pins ⁽¹⁾	_	_	0.4	V	VDD = 3.6V, IOL < 11 mA
DO20	Vон	Output High Voltage 4x Source Driver Pins	2.4	_	_	V	VDD = 3.6V, IOH > -8 mA
		Output High Voltage 8x Source Driver Pins ⁽¹⁾	2.4	_	_	V	VDD = 3.6V, IOH > -12 mA

Note 1: The 8x sink/source pins are RB1, RC8, RC9 and RD8.

TABLE 33-18: PROGRAM MEMORY

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Max.	Units	Conditions
		Program Flash Memory				
D130	EР	Cell Endurance	10,000	_	E/W	-40°C to +125°C
D131	VPR	VDD for Read	3.0	3.6	V	
D132b	VPEW	VDD for Self-Timed Write	3.0	3.6	V	
D134	TRETD	Characteristic Retention	20	_	Year	Provided no other specifications are violated, -40°C to +125°C
D137a	TPE	Page Erase Time	15.3	16.82	ms	TPE = 128,454 FRC cycles (Note 1)
D138a	Tww	Word Write Time	47.7	52.3	μs	Tww = 400 FRC cycles (Note 1)
D139a	TRW	Row Write Time	2.0	2.2	ms	TRW = 16,782 FRC cycles (Note 1)

Note 1: Other conditions: FRC = 8 MHz, TUN<5:0> = 0111111 (for Minimum), TUN<5:0> = 100000 (for Maximum). This parameter depends on the FRC accuracy (see Table 33-22) and the value of the FRC Oscillator Tuning register (see Register 9-4). For complete details on calculating the Minimum and Maximum time, see Section 5.3 "Programming Operations".

33.2 AC Characteristics and Timing Parameters

FIGURE 33-1: LOAD CONDITIONS FOR I/O SPECIFICATIONS




FIGURE 33-2: EXTERNAL CLOCK TIMING




TABLE 33-19: EXTERNAL CLOCK TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}C \leq \text{TA} \leq +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Sym	Characteristic	Min.	Typ. ⁽¹⁾	Max.	Units	Conditions
OS10	FIN	External CLKI Frequency	DC	_	64	MHz	
		Oscillator Crystal Frequency	3.5	_	10	MHz	XT
			10	_	32	MHz	HS
OS20	Tosci	External Clock Period	15.63	_	DC	ns	
OS25	TCY	Instruction Cycle Time	10	_	DC	ns	
OS30	TosL, TosH	External Clock in (OSCI) High or Low Time	0.45 x Tosc	_	0.55 x Tosc	ns	
OS31	TosR, TosF	External Clock in (OSCI) Rise or Fall Time	_	_	5.2	ns	When FIN = 64 MHz
OS40	TckR	CLKO Rise Time ^(2,3)	_	5.4	_	ns	
OS41	TckF	CLKO Fall Time ^(2,3)	_	6.4		ns	
OS42	Gм	External Oscillator Transconductance ⁽³⁾	2.7	_	4	mA/V	XTCFG<1:0> = 00, XTBST = 0
			4	_	7	mA/V	XTCFG<1:0> = 00, XTBST = 1
			4.5	_	7	mA/V	XTCFG<1:0> = 01, XTBST = 0
			6	_	11.9	mA/V	XTCFG<1:0> = 01, XTBST = 1
			5.9	_	9.7	mA/V	XTCFG<1:0> = 10, XTBST = 0
			6.9	_	15.9	mA/V	XTCFG<1:0> = 10, XTBST = 1
			6.7	_	12	mA/V	XTCFG<1:0> = 11, XTBST = 0
			7.5	_	19	mA/V	XTCFG<1:0> = 11, XTBST = 1

- 2: Measurements are taken in EC mode. The CLKO signal is measured on the OSCO pin.
- 3: This parameter is characterized but not tested in manufacturing.

TABLE 33-20: PLL TIMING SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 -40° C \leq TA \leq +125 $^{\circ}$ C for Extended

Param No.	Symbol	Characteristic	Min.	Typ. ⁽¹⁾	Max.	Units	Conditions
OS50	FPLLI	PLL Voltage Controlled Oscillator (VCO) Input Frequency Range	8 ⁽²⁾		64	MHz	ECPLL, XTPLL modes
OS51	Fvco	On-Chip VCO System Frequency	400	_	1600	MHz	
OS52	TLOCK	PLL Start-up Time (Lock Time)		125	_	μs	

Note 1: Data in "Typ." column is at 3.3V, +25°C unless otherwise stated. Parameters are for design guidance only and are not tested.

2: Inclusive of FRC Tolerance Specification F20a.

TABLE 33-21: AUXILIARY PLL TIMING SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Typ. ⁽¹⁾	Max.	Units	Conditions
OS50	AFPLLI	APLL Voltage Controlled Oscillator (VCO) Input Frequency Range	8 ⁽²⁾	_	64	MHz	ECPLL, XTPLL modes
OS51	AFvco	On-Chip VCO System Frequency	400		1600	MHz	
OS52	TLOCK	APLL Start-up Time (Lock Time)		125		μs	

Note 1: Data in "Typ." column is at 3.3V, +25°C unless otherwise stated. Parameters are for design guidance only and are not tested.

2: Inclusive of FRC Tolerance Specification F20a.

TABLE 33-22: INTERNAL FRC ACCURACY

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Characteristic	Min.	Max.	Units	Conditions					
Internal	Internal FRC Accuracy @ FRC Frequency = 8 MHz ⁽¹⁾									
F20a	FRC	-3	+3	%	$-40^{\circ}C \le TA \le 0^{\circ}C$					
		-1.5	+1.5	%	0°C ≤ TA ≤ +85°C					
		-2	+2	%	$+85^{\circ}C \le TA \le +125^{\circ}C$					
F22	BFRC	-17	+17	%	$-40^{\circ}C \le TA \le -125^{\circ}C$					

Note 1: Frequency is calibrated at +25°C and 3.3V.

TABLE 33-23: INTERNAL LPRC ACCURACY

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Characteristic	Min.	Max.	Units	Conditions				
LPRC @ 32 kHz									
F21	LPRC	-25	+25	%	$-40^{\circ}C \le TA \le 0^{\circ}C$				
		-10	+10	%	$0^{\circ}\text{C} \leq \text{TA} \leq +85^{\circ}\text{C}$				
		-15	+15	%	$+85^{\circ}C \le TA \le +125^{\circ}C$				

FIGURE 33-3: I/O TIMING CHARACTERISTICS




TABLE 33-24: I/O TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{Ta} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Typ. ⁽¹⁾	Max.	Units	Conditions
DO31	TioR	Port Output Rise Time ⁽²⁾	_	6.5	9.7	ns	
DO32	TioF	Port Output Fall Time ⁽²⁾	_	3.2	4.2	ns	
DI35	TINP	INTx Pin High or Low Time (input)	20	_	_	ns	
DI40	TRBP	CNx High or Low Time (input)	2	_		Tcy	

Note 1: Data in "Typ." column is at 3.3V, +25°C unless otherwise stated.

2: This parameter is characterized but not tested in manufacturing.

FIGURE 33-4: BOR AND MASTER CLEAR RESET TIMING CHARACTERISTICS




TABLE 33-25: RESET, WATCHDOG TIMER, OSCILLATOR START-UP TIMER, POWER-UP TIMER TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions
SY00	Tpu	Power-up Period	_	200	_	μs	FNOSC<2:0> are FRC
SY10	Tost	Oscillator Start-up Time	_	1024 Tosc	_	_	Tosc = OSCI period
SY13	Tioz	I/O High-Impedance from MCLR Low or Watchdog Timer Reset		1.5	_	μs	
SY20	TMCLR	MCLR Pulse Width (low)	2	_	_	μs	
SY30	TBOR	BOR Pulse Width (low)	1	_	_	μs	
SY35	TFSCM	Fail-Safe Clock Monitor Delay	1	_	40	μs	Clock fail to BFRC switch
SY37	Toscdfrc	FRC Oscillator Start-up Delay	_	_	15	μs	From POR event
SY38	TOSCDLPRC	LPRC Oscillator Start-up Delay	_	_	50	μs	From Reset event

Note 1: These parameters are characterized but not tested in manufacturing.

^{2:} Data in "Typ." column is at 3.3V, +25°C unless otherwise stated.

FIGURE 33-5: HIGH-SPEED PWMx MODULE FAULT TIMING CHARACTERISTICS




FIGURE 33-6: HIGH-SPEED PWMx MODULE TIMING CHARACTERISTICS




TABLE 33-26: HIGH-SPEED PWMx MODULE TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)
Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Max.	Units	Conditions
MP00	FIN	PWM Input Frequency	_	500	MHz	(Note 2)
MP10	TFPWM	PWMx Output Fall Time	_	_	ns	See Parameter DO32
MP11	TRPWM	PWMx Output Rise Time			ns	See Parameter DO31
MP20	TFD	Fault Input to PWMx I/O Change	_	26	ns	PCI Inputs 19 through 22
MP30	TFH	Fault Input Pulse Width	8	_	ns	

 $\textbf{Note 1:} \quad \text{These parameters are characterized but not tested in manufacturing}.$

^{2:} Input frequency of 500 MHz must be used for High-Resolution mode.

TABLE 33-27: SPIx MAXIMUM DATA/CLOCK RATE SUMMARY

SPI Master Transmit Only (Half- Duplex)	SPI Master Transmit/Receive (Full-Duplex)	SPI Slave Transmit/Receive (Full-Duplex)	CKE
Figure 33-7 Table 33-28	_	_	0
Figure 33-8 Table 33-28	_	_	1
_	Figure 33-9 Table 33-29	_	0
_	Figure 33-10 Table 33-30	_	1
_			0
_	_	Figure 33-12 Table 33-33	1

FIGURE 33-7: SPIX MASTER MODE (HALF-DUPLEX, TRANSMIT ONLY, CKE = 0) TIMING CHARACTERISTICS




FIGURE 33-8: SPIx MASTER MODE (HALF-DUPLEX, TRANSMIT ONLY, CKE = 1) **TIMING CHARACTERISTICS**




TABLE 33-28: SPIX MASTER MODE (HALF-DUPLEX, TRANSMIT ONLY) TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions	
SP10	FscP	Maximum SCKx Frequency	_	_	15	MHz	Using PPS pins	
			_	_	40	MHz	SPIx dedicated pins	
SP20	TscF	SCKx Output Fall Time	_	_	_	ns	See Parameter DO32	
SP21	TscR	SCKx Output Rise Time	_	_	_	ns	See Parameter DO31	
SP30	TdoF	SDOx Data Output Fall Time	_	_	_	ns	See Parameter DO32	
SP31	TdoR	SDOx Data Output Rise Time	_	_	_	ns	See Parameter DO31	
SP35	TscH2doV, TscL2doV	SDOx Data Output Valid After SCKx Edge	_	6	20	ns		
SP36	TdiV2scH,	SDOx Data Output Setup to	30	_	_	ns	Using PPS pins	
	TdiV2scL	First SCKx Edge	3	_	_	ns	SPIx dedicated pins	

Note 1: These parameters are characterized but not tested in manufacturing.

FIGURE 33-9: SPIX MASTER MODE (FULL-DUPLEX, CKE = 1, CKP = x, SMP = 1) TIMING CHARACTERISTICS




TABLE 33-29: SPIX MASTER MODE (FULL-DUPLEX, CKE = 1, CKP = x, SMP = 1) TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{Ta} \le +85^{\circ}\text{C}$ for Industrial

-40°C < TA < +125°C for Extended

	-40°C ≤ TA ≤ +125°C for Extended									
Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions			
SP10	FscP	Maximum SCKx Frequency	_	_	15	MHz	Using PPS pins			
			_	_	40	MHz	SPIx dedicated pins			
SP20	TscF	SCKx Output Fall Time	_	_	_	ns	See Parameter DO32			
SP21	TscR	SCKx Output Rise Time	_	_	_	ns	See Parameter DO31			
SP30	TdoF	SDOx Data Output Fall Time	_	_	_	ns	See Parameter DO32			
SP31	TdoR	SDOx Data Output Rise Time	_	_	_	ns	See Parameter DO31			
SP35	TscH2doV, TscL2doV	SDOx Data Output Valid After SCKx Edge	_	6	20	ns				
SP36	TdoV2sc,	SDOx Data Output Setup	30	_	_	ns	Using PPS pins			
	TdoV2scL	to First SCKx Edge	3	_		ns	SPIx dedicated pins			
SP40	TdiV2scH,	Setup Time of SDIx Data	30	_	_	ns	Using PPS pins			
	TdiV2scL	Input to SCKx Edge	10	_		ns	SPIx dedicated pins			
SP41	TscH2diL,	Hold Time of SDIx Data	30	_		ns	Using PPS pins			
	TscL2diL	Input to SCKx Edge	15	_	_	ns	SPIx dedicated pins			

Note 1: These parameters are characterized but not tested in manufacturing.

FIGURE 33-10: SPIX MASTER MODE (FULL-DUPLEX, CKE = 0, CKP = x, SMP = 1) TIMING CHARACTERISTICS




TABLE 33-30: SPIx MASTER MODE (FULL-DUPLEX, CKE = 0, CKP = x, SMP = 1) TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $\text{-40}^{\circ}\text{C} \leq \text{Ta} \leq \text{+125}^{\circ}\text{C for Extended}$

	-40°C ≤ IA ≤ +125°C for Extended								
Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions		
SP10	FscP	Maximum SCKx Frequency	_	_	15	MHz	Using PPS pins		
			_	_	40	MHz	SPIx dedicated pins		
SP20	TscF	SCKx Output Fall Time	_	_	_	ns	See Parameter DO32		
SP21	TscR	SCKx Output Rise Time	_	_	_	ns	See Parameter DO31		
SP30	TdoF	SDOx Data Output Fall Time	_	_	_	ns	See Parameter DO32		
SP31	TdoR	SDOx Data Output Rise Time	_	_	_	ns	See Parameter DO31		
SP35	TscH2doV, TscL2doV	SDOx Data Output Valid After SCKx Edge	_	6	20	ns			
SP36	TdoV2scH,	SDOx Data Output Setup to	30	_	_	ns	Using PPS pins		
	TdoV2scL	First SCKx Edge	20	_	_	ns	SPIx dedicated pins		
SP40	TdiV2scH,	Setup Time of SDIx Data	30	_	_	ns	Using PPS pins		
	TdiV2scL	Input to SCKx Edge	10	_	_	ns	SPIx dedicated pins		
SP41	TscH2diL,	Hold Time of SDIx Data Input	30	_		ns	Using PPS pins		
	TscL2diL	to SCKx Edge	15	_	_	ns	SPIx dedicated pins		

Note 1: These parameters are characterized but not tested in manufacturing.

FIGURE 33-11: SPIX SLAVE MODE (FULL-DUPLEX, CKE = 0, CKP = x, SMP = 0) TIMING CHARACTERISTICS




TABLE 33-31: SPIX SLAVE MODE (FULL-DUPLEX, CKE = 0, CKP = x, SMP = 0) TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for Industrial $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions
SP10	FscP	Maximum SCKx Input Frequency	_	_	15	MHz	Using PPS pins
			_	_	40	MHz	SPIx dedicated pins
SP72	TscF	SCKx Input Fall Time	_	_	_	ns	See Parameter DO32
SP73	TscR	SCKx Input Rise Time	_	_	_	ns	See Parameter DO31
SP30	TdoF	SDOx Data Output Fall Time	_	_		ns	See Parameter DO32
SP31	TdoR	SDOx Data Output Rise Time	_	_		ns	See Parameter DO31
SP35	TscH2doV, TscL2doV	SDOx Data Output Valid After SCKx Edge	_	6	20	ns	
SP36	TdoV2scH,	SDOx Data Output Setup to	30	_	_	ns	Using PPS pins
	TdoV2scL	First SCKx Edge	20	_		ns	SPIx dedicated pins
SP40	TdiV2scH,	Setup Time of SDIx Data Input	30	_		ns	Using PPS pins
	TdiV2scL	to SCKx Edge	10	_	_	ns	SPIx dedicated pins
SP41	TscH2diL,	Hold Time of SDIx Data Input	30	_		ns	Using PPS pins
	TscL2diL	to SCKx Edge	15	_		ns	SPIx dedicated pins
SP50	TssL2scH, TssL2scL	SSx ↓ to SCKx ↑ or SCKx ↓ Input	120	_	_	ns	
SP51	TssH2doZ	SSx ↑ to SDOx Output High-Impedance	8	_	50	ns	
SP52	TscH2ssH, TscL2ssH	SSx ↑ After SCKx Edge	1.5 Tcy + 40	_	_	ns	

Note 1: These parameters are characterized but not tested in manufacturing.

FIGURE 33-12: SPIX SLAVE MODE (FULL-DUPLEX, CKE = 1, CKP = x, SMP = 0) TIMING CHARACTERISTICS




TABLE 33-32: SPIx SLAVE MODE (FULL-DUPLEX, CKE = 1, CKP = x, SMP = 0) TIMING REQUIREMENTS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Symbol	Characteristic ⁽¹⁾	Min.	Typ. ⁽²⁾	Max.	Units	Conditions
SP10	FscP	Maximum SCKx Input	_	_	15	MHz	Using PPS pins
		Frequency	_	_	40	MHz	SPIx dedicated pins
SP72	TscF	SCKx Input Fall Time	_	_		ns	See Parameter DO32
SP73	TscR	SCKx Input Rise Time	_			ns	See Parameter DO31
SP30	TdoF	SDOx Data Output Fall Time	_			ns	See Parameter DO32
SP31	TdoR	SDOx Data Output Rise Time	_	_	_	ns	See Parameter DO31
SP35	TscH2doV, TscL2doV	SDOx Data Output Valid After SCKx Edge	_	6	20	ns	
SP36	TdoV2scH,	SDOx Data Output Setup to	30	_	_	ns	Using PPS pins
	TdoV2scL	First SCKx Edge	20	_	_	ns	SPIx dedicated pins
SP40	TdiV2scH,	Setup Time of SDIx Data Input	30			ns	Using PPS pins
	TdiV2scL	to SCKx Edge	10			ns	SPIx dedicated pins
SP41	TscH2diL,	Hold Time of SDIx Data Input	30			ns	Using PPS pins
	TscL2diL	to SCKx Edge	15	_	_	ns	SPIx dedicated pins
SP50	TssL2scH, TssL2scL	SSx ↓ to SCKx ↑ or SCKx ↓ Input	120	_	_	ns	
SP51	TssH2doZ	SSx ↑ to SDOx Output High-Impedance	8		50	ns	
SP52	TscH2ssH, TscL2ssH	SSx ↑ After SCKx Edge	1.5 Tcy + 40	_	_	ns	
SP60	TssL2doV	SDOx Data Output Valid After SSx Edge	_	_	50	ns	

Note 1: These parameters are characterized but not tested in manufacturing.

^{2:} Data in "Typ." column is at 3.3V, +25°C unless otherwise stated.

FIGURE 33-13: I2Cx BUS START/STOP BITS TIMING CHARACTERISTICS (MASTER MODE)




FIGURE 33-14: I2Cx BUS DATA TIMING CHARACTERISTICS (MASTER MODE)




TABLE 33-33: I2Cx BUS DATA TIMING REQUIREMENTS (MASTER MODE)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Symbol	Characteristic ⁽⁴⁾		Min. ⁽¹⁾	Max.	Units	Conditions	
IM10	TLO:SCL	Clock Low Time	100 kHz mode	Tcy (BRG + 1)	_	μs		
			400 kHz mode	Tcy (BRG + 1)	_	μs		
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs		
IM11	THI:SCL	Clock High Time	100 kHz mode	Tcy (BRG + 1)	_	μs		
			400 kHz mode	Tcy (BRG + 1)	_	μs		
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs		
IM20	TF:SCL	SDAx and SCLx	100 kHz mode	_	300	ns	CB is specified to be	
		Fall Time	400 kHz mode	20 x (VDD/5.5V)	300	ns	from 10 to 400 pF	
			1 MHz mode ⁽²⁾	20 x (VDD/5.5V)	120	ns		
IM21	TR:SCL	SDAx and SCLx	100 kHz mode	_	1000	ns	CB is specified to be	
		Rise Time	400 kHz mode	20 + 0.1 CB	300	ns	from 10 to 400 pF	
			1 MHz mode ⁽²⁾	_	120	ns		
IM25	Tsu:dat	Data Input	100 kHz mode	250	_	ns		
		Setup Time	400 kHz mode	100	_	ns		
			1 MHz mode ⁽²⁾	50	_	ns	1	
IM26	THD:DAT	Data Input	100 kHz mode	0	_	μs		
		Hold Time	400 kHz mode	0	0.9	μs		
			1 MHz mode ⁽²⁾	0	0.3	μs		
IM30	Tsu:sta	Start Condition	100 kHz mode	Tcy (BRG + 1)	_	μs	Only relevant for	
		Setup Time	400 kHz mode	Tcy (BRG + 1)	_	μs	Repeated Start	
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs	condition	
IM31	THD:STA	Start Condition	100 kHz mode	Tcy (BRG + 1)	_	μs	After this period, the	
		Hold Time	400 kHz mode	Tcy (BRG + 1)	_	μs	first clock pulse is	
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs	generated	
IM33	Tsu:sto	Stop Condition	100 kHz mode	Tcy (BRG + 1)	_	μs		
		Setup Time	400 kHz mode	Tcy (BRG + 1)	_	μs		
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs		
IM34	THD:STO	Stop Condition	100 kHz mode	Tcy (BRG + 1)	_	μs		
		Hold Time	400 kHz mode	Tcy (BRG + 1)	_	μs		
			1 MHz mode ⁽²⁾	Tcy (BRG + 1)	_	μs		
IM40	TAA:SCL	Output Valid	100 kHz mode	_	3450	ns		
		from Clock	400 kHz mode	_	900	ns		
			1 MHz mode ⁽²⁾	_	450	ns		
IM45	TBF:SDA	Bus Free Time	100 kHz mode	4.7	_	μs	Time the bus must be	
			400 kHz mode	1.3	_	μs	free before a new	
			1 MHz mode ⁽²⁾	0.5	_	μs	transmission can start	
IM50	Св	Bus Capacitive L	oading	_	400	pF		
IM51	TPGD	Pulse Gobbler De	elay	65	390	ns	(Note 3)	

Note 1: BRG is the value of the I²C Baud Rate Generator.

- 2: Maximum Pin Capacitance = 10 pF for all I2Cx pins (for 1 MHz mode only).
- **3:** Typical value for this parameter is 130 ns.
- **4:** These parameters are characterized but not tested in manufacturing.

FIGURE 33-15: I2Cx BUS START/STOP BITS TIMING CHARACTERISTICS (SLAVE MODE)




FIGURE 33-16: I2Cx BUS DATA TIMING CHARACTERISTICS (SLAVE MODE)




TABLE 33-34: I2Cx BUS DATA TIMING REQUIREMENTS (SLAVE MODE)

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Symbol	Characte	eristic ⁽³⁾	Min.	Max.	Units	Conditions	
IS10	TLO:SCL	Clock Low Time	100 kHz mode	4.7	_	μs		
			400 kHz mode	1.3	_	μs		
			1 MHz mode ⁽¹⁾	0.5	_	μs		
IS11	THI:SCL	Clock High Time	100 kHz mode	4.0	_	μs	Device must operate at a minimum of 1.5 MHz	
			400 kHz mode	0.6	_	μs	Device must operate at a minimum of 10 MHz	
			1 MHz mode ⁽¹⁾	0.26	_	μs		
IS20	TF:SCL	SDAx and SCLx	100 kHz mode	_	300	ns	CB is specified to be from	
		Fall Time	400 kHz mode	20 x (VDD/5.5V)	300	ns	10 to 400 pF	
			1 MHz mode ⁽¹⁾	20 x (VDD/5.5V)	120	ns		
IS21	TR:SCL	SDAx and SCLx	100 kHz mode	_	1000	ns	CB is specified to be from	
		Rise Time	400 kHz mode	20 + 0.1 CB	300	ns	10 to 400 pF	
			1 MHz mode ⁽¹⁾	_	120	ns		
IS25	TSU:DAT	Data Input	100 kHz mode	250	_	ns		
		Setup Time	400 kHz mode	100	_	ns		
			1 MHz mode ⁽¹⁾	50	_	ns		
IS26	THD:DAT	Data Input	100 kHz mode	0	_	μs		
		Hold Time	400 kHz mode	0	0.9	μs		
			1 MHz mode ⁽¹⁾	0	0.3	μs		
IS30	Tsu:sta	Start Condition	100 kHz mode	4.7	_	μs	Only relevant for Repeated	
		Setup Time	400 kHz mode	0.6	_	μs	Start condition	
			1 MHz mode ⁽¹⁾	0.26	_	μs		
IS31	THD:STA	Start Condition	100 kHz mode	4.0	_	μs	After this period, the first	
		Hold Time	400 kHz mode	0.6	_	μs	clock pulse is generated	
			1 MHz mode ⁽¹⁾	0.26	_	μs		
IS33	Tsu:sto	Stop Condition	100 kHz mode	4.0	_	μs		
		Setup Time	400 kHz mode	0.6	_	μs		
			1 MHz mode ⁽¹⁾	0.26	_	μs		
IS34	THD:STO	Stop Condition	100 kHz mode	>0	_	μs		
		Hold Time	400 kHz mode	>0	_	μs		
			1 MHz mode ⁽¹⁾	>0		μs		
IS40	TAA:SCL	Output Valid from	100 kHz mode	0	3450	ns		
		Clock	400 kHz mode	0	900	ns		
			1 MHz mode ⁽¹⁾	0	450	ns		
IS45	TBF:SDA	Bus Free Time	100 kHz mode	4.7	_	μs	Time the bus must be free	
			400 kHz mode	1.3	_	μs	before a new transmission	
			1 MHz mode ⁽¹⁾	0.5	_	μs	can start	
IS50	Св	Bus Capacitive Lo		_	400	pF		
IS51	TPGD	Pulse Gobbler Del		65	390	ns	(Note 2)	

Note 1: Maximum Pin Capacitance = 10 pF for all I2Cx pins (for 1 MHz mode only).

^{2:} Typical value for this parameter is 130 ns.

^{3:} These parameters are characterized but not tested in manufacturing.

FIGURE 33-17: UARTX MODULE I/O TIMING CHARACTERISTICS




TABLE 33-35: UARTx MODULE I/O TIMING REQUIREMENTS

	Operating Conditions: 3.0V to 3.6V (unless otherwise stated) Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$								
Param No. Symbol Characteristic ⁽¹⁾ Min. Typ. ⁽²⁾ Max. Units Conditions									
UA10	TUABAUD	UARTx Baud Time	40	_	_	ns			
UA11	FBAUD	UARTx Baud Frequency	_	_	25	Mbps			
UA20									

Note 1: These parameters are characterized but not tested in manufacturing.

2: Data in "Typ." column is at 3.3V, +25°C unless otherwise stated. Parameters are for design guidance only and are not tested.

TABLE 33-36: ADC MODULE SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)⁽⁴⁾

Operating temperature $-40^{\circ}\text{C} \le \text{Ta} \le +85^{\circ}\text{C}$ for Industrial

-40°C ≤ TA ≤ +125°C for Extended

	-40°C ≤ IA ≤ +125°C for Extended									
Param No.	Symbol	Characteristics	Min.	Typical	Max.	Units	Conditions			
			Analog	Input						
AD12	VINH-VINL	Full-Scale Input Span	AVss	_	AVDD	V				
AD14	VIN	Absolute Input Voltage	AVss - 0.3	_	AVDD + 0.3	V				
AD17	Rin	Recommended Impedance of Analog Voltage Source	_	100	_	Ω	For minimum sampling time (Note 1)			
AD66	VBG	Internal Voltage Reference Source		1.2	_	V				
	ADC Accuracy									
AD20c	Nr	Resolution	1	2 data bits	1	bits				
AD21c	INL	Integral Nonlinearity	> -11.3		< 11.3	LSb	AVss = 0V, AVDD = 3.3V			
AD22c	DNL	Differential Nonlinearity	> -1.5	_	< 11.5	LSb	AVss = 0V, AVDD = 3.3V			
AD23c	GERR	Gain Error	> -12	_	< 12	LSb	AVss = 0V, AVDD = 3.3V			
AD24c	Eoff	Offset Error	> -7.5		< 7.5	LSb	AVss = 0V, AVDD = 3.3V			
			Dynamic Pe	erformanc	е					
AD31b	SINAD	Signal-to-Noise and Distortion	56	1	70	dB	(Notes 2, 3)			
AD34b	ENOB	Effective Number of Bits	9.0		11.4	bits	(Notes 2, 3)			
AD50	TAD	ADC Clock Period	14.3	_	_	ns				
AD51	FTP	Throughput Rate	_	_	3.5	Msps	Dedicated Cores 0 and 1			
			_	_	3.5	Msps	Shared core			

- Note 1: These parameters are not characterized or tested in manufacturing.
 - 2: These parameters are characterized but not tested in manufacturing.
 - 3: Characterized with a 1 kHz sine wave.
 - **4:** The ADC module is functional at VBORMIN < VDD < VDDMIN, but with degraded performance. Unless otherwise stated, module functionality is ensured, but not characterized.

TABLE 33-37: HIGH-SPEED ANALOG COMPARATOR MODULE SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)⁽²⁾

Operating temperature $-40^{\circ}C \leq TA \leq +85^{\circ}C$ for Industrial $-40^{\circ}C \leq TA \leq +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Тур.	Max.	Units	Comments
CM09	FIN	Input Frequency	400	500	550	MHz	
CM10	VIOFF	Input Offset Voltage	-20	_	+20	mV	
CM11	VICM	Input Common-Mode Voltage Range ⁽¹⁾	AVss	_	AVDD	V	
CM13	CMRR	Common-Mode Rejection Ratio ⁽¹⁾	65	_	_	dB	
CM14	TRESP	Large Signal Response		15	_	ns	V+ input step of 100 mV while V- input is held at AVDD/2
CM15	VHYST	Input Hysteresis	15	_	45	mV	Depends on HYSSEL<1:0>

Note 1: These parameters are for design guidance only and are not tested in manufacturing.

^{2:} The comparator module is functional at VBORMIN < VDD < VDDMIN, but with degraded performance. Unless otherwise stated, module functionality is tested, but not characterized.

TABLE 33-38: DACX MODULE SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial $-40^{\circ}\text{C} \le \text{TA} \le +125^{\circ}\text{C}$ for Extended

Param No.	Symbol	Characteristic	Min.	Typ. ⁽¹⁾	Max.	Units	Comments
DA02	CVRES	Resolution		12		bits	
DA03	INL	Integral Nonlinearity Error	-38	_	0	LSB	
DA04	DNL	Differential Nonlinearity Error	-5	_	5	LSB	
DA05	EOFF	Offset Error	-3.5	_	21.5	LSB	Internal node at comparator input
DA06	EG	Gain Error	0	_	41	LSB	Internal node at comparator input
DA07	TSET	Settling Time	_	750	_	ns	Output within 1% of desired output voltage with a 5%-95% or 95%-5% step
DA08	Vout	Voltage Output Range	0.165	_	3.135	V	VDD = 3.3V

Note 1: Parameters are for design guidance only and are not tested in manufacturing.

TABLE 33-39: DACx OUTPUT (DACOUT1 PIN) SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)^(1,2)

Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Тур.	Max.	Units	Comments
DA11	RLOAD	Resistive Output Load Impedance	10K	_	_	Ohm	
DA11a	CLOAD	Output Load Capacitance	_	_	30	pF	Including output pin capacitance
DA12	IOUT	Output Current Drive Strength	_	3	_	mA	Sink and source

Note 1: The DACx module is functional at VBORMIN < VDD < VDDMIN, but with degraded performance. Unless otherwise stated, module functionality is tested, but not characterized.

2: Using other pin functions may degrade DAC performance.

TABLE 33-40: CONSTANT-CURRENT SOURCE SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)⁽¹⁾

Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Symbol	Characteristic	Min.	Тур.	Max.	Units	Conditions
CC02	IREG	Current Regulation	_	±3	_	%	
CC03	IOUT	Current Output at Terminal	_	10	_	μA	ISRCx pin
			_	50	_	μA	IBIASx pin

Note 1: The constant-current source module is functional at VBORMIN < VDD < VDDMIN, but with degraded performance. Unless otherwise stated, module functionality is tested, but not characterized.

TABLE 33-41: OPERATIONAL AMPLIFIER SPECIFICATIONS

Operating Conditions: 3.0V to 3.6V (unless otherwise stated)⁽¹⁾

Operating temperature $-40^{\circ}\text{C} \le \text{TA} \le +85^{\circ}\text{C}$ for Industrial

 $-40^{\circ}C \le TA \le +125^{\circ}C$ for Extended

Param No.	Sym	Characteristic	Min	Typ ⁽¹⁾	Max	Units	Comments
OA01	GBWP	Gain Bandwidth Product		20	_	MHz	
OA02	SR	Slew Rate	_	40	_	V/µs	
OA03	VIOFF	Input Offset Voltage	-15	5	15	mV	NCHDISx = 0
			-20	_	20	mV	NCHDISx = 1
OA04	VIBC	Input Bias Current	_		_	nA	(Note 2)
OA05	VICM	Common-Mode Input Voltage	AVss		AVDD	V	NCHDISx = 0
		Range	AVss	_	2.8	V	NCHDISx = 1
OA07	CMRR	Common-Mode Rejection Ratio	_	68	_	dB	
0A08	PSRR	Power Supply Rejection Ratio	_	74	_	dB	
OA09	Vor	Output Voltage Range	AVss	_	AVDD	mV	0.5V input overdrive, no output loading
OA10	RLOAD	Resistive Output Load Impedance	10K	_	_	Ohm	
OA11	CLOAD	Output Load Capacitance	_	_	30	pF	Including output pin capacitance
OA12	IOUT	Output Current Drive Strength	_	3	_	mA	Sink and source
OA13	PMARGIN	Phase Margin	44	_	_	degree	Unity gain
OA14	GMARGIN	Gain Margin	7	_	_	dB	Unity gain
OA15	OLG	Open-Loop Gain	68	75	_	dB	
OA16	RfB	Feedback Resistance	AV _{DD} / (Gain * 200 nA)		15	kOhm	

Note 1: These parameters are for design guidance only and are not tested in manufacturing.

^{2:} The op amps use CMOS input circuitry with negligible input bias current. The maximum "effective bias current" is the I/O pin leakage specified by electrical Parameter DI50.

34.0 PACKAGING INFORMATION

34.1 Package Marking Information

28-Lead SSOP (5.30 mm)




28-Lead UQFN (6x6 mm)



36-Lead UQFN (5x5 mm)



48-Lead TQFP (7x7 mm)



Example



Example



Example



Example



Legend: XX...X Customer-specific information
Year code (last digit of calendary)

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

be: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

34.1 Package Marking Information (Continued)


48-Lead UQFN (6x6 mm)



Example



64-Lead TQFP (10x10x1 mm)



Example



64-Lead QFN (9x9x0.9 mm)



Example



80-Lead TQFP (12x12x1 mm)




Example




34.2 Package Details

28-Lead Plastic Shrink Small Outline (SS) - 5.30 mm Body [SSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-073 Rev C Sheet 1 of 2

28-Lead Plastic Shrink Small Outline (SS) - 5.30 mm Body [SSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	MILLIMETERS				
Dimension	on Limits	MIN	NOM	MAX		
Number of Pins	N		28			
Pitch	е		0.65 BSC			
Overall Height	Α	•	-	2.00		
Molded Package Thickness	A2	1.65	1.75	1.85		
Standoff	A1	0.05	-	-		
Overall Width	Е	7.40	7.80	8.20		
Molded Package Width	E1	5.00	5.30	5.60		
Overall Length	D	9.90	10.20	10.50		
Foot Length	L	0.55	0.75	0.95		
Footprint	L1		1.25 REF			
Lead Thickness	С	0.09	-	0.25		
Foot Angle	φ	0°	0° 4° 8°			
Lead Width	b	0.22	-	0.38		

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.20mm per side.
- 3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-073 Rev C Sheet 2 of 2

28-Lead Plastic Shrink Small Outline (SS) - 5.30 mm Body [SSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	Dimension Limits		NOM	MAX
Contact Pitch	Е	0.65 BSC		
Contact Pad Spacing	С		7.00	
Contact Pad Width (X28)	X1			0.45
Contact Pad Length (X28)	Y1			1.85
Contact Pad to Center Pad (X26)	G1	0.20		


Notes:

- Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2073 Rev B

28-Lead Ultra Thin Plastic Quad Flat, No Lead Package (2N) - 6x6x0.55 mm Body [UQFN] With 4.65x4.65 mm Exposed Pad and Corner Anchors


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-385 Rev C Sheet 1 of 2

28-Lead Ultra Thin Plastic Quad Flat, No Lead Package (2N) - 6x6x0.55 mm Body [UQFN] With 4.65x4.65 mm Exposed Pad and Corner Anchors

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS				
Dimension	Limits	MIN	NOM	MAX	
Number of Terminals	Ν		28		
Pitch	е		0.65 BSC		
Overall Height	Α	0.45	0.50	0.55	
Standoff	A1	0.00	0.02	0.05	
Terminal Thickness	A3		0.127 REF		
Overall Width	Е	6.00 BSC			
Exposed Pad Width	E2	4.55	4.65	4.75	
Overall Length	D		6.00 BSC		
Exposed Pad Length	D2	4.55	4.65	4.75	
Exposed Pad Corner Chamfer	Р	ı	0.35	-	
Terminal Width	b	0.25	0.30	0.35	
Corner Anchor Pad	b1	0.35	0.35 0.40 0.43		
Corner Pad, Metal Free Zone	b2	0.15	0.20	0.25	
Terminal Length	L	0.30 0.40 0.50			
Terminal-to-Exposed-Pad	K	0.20	-	-	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-385 Rev C Sheet 2 of 2

28-Lead Ultra Thin Plastic Quad Flat, No Lead Package (2N) - 6x6x0.55 mm Body [UQFN] With 4.65x4.65 mm Exposed Pad and Corner Anchors

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units			MILLIMETERS			
Dimension	Limits	MIN	NOM	MAX			
Contact Pitch	Е		0.65 BSC				
Optional Center Pad Width	X2			4.75			
Optional Center Pad Length	Y2			4.75			
Contact Pad Spacing	C1		6.00				
Contact Pad Spacing	C2		6.00				
Contact Pad Width (X28)	X1			0.35			
Contact Pad Length (X28)	Y1			0.80			
Corner Anchor (X4)	Х3			1.00			
Corner Anchor (X4)	Y3			1.00			
Corner Anchor Chamfer (X4)	X4			0.35			
Corner Anchor Chamfer (X4)	Y4			0.35			
Contact Pad to Pad (X28)	G1	0.20					
Contact Pad to Center Pad (X28)	G2	0.20					
Thermal Via Diameter	V		0.33				
Thermal Via Pitch	EV		1.20				


Notes:

- Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2385B

36-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M5) - 5x5 mm Body [UQFN] With Corner Anchors


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-436A-M5 Sheet 1 of 2

36-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M5) - 5x5 mm Body [UQFN] With Corner Anchors

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		36	
Pitch	е		0.40 BSC	
Overall Height	Α	0.50	0.55	0.60
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.152 REF		
Overall Length	D	5.00 BSC		
Exposed Pad Length	D2	3.60	3.70	3.80
Overall Width	Е		5.00 BSC	
Exposed Pad Width	E2	3.60	3.70	3.80
Terminal Width	b	0.15 0.20 0.25		
Terminal Length	L	0.30	0.40	0.50
Terminal-to-Exposed-Pad	K		0.25 REF	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M $\,$


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-436A-M5 Sheet 2 of 2

36-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M5) - 5x5 mm Body [UQFN] With Corner Anchors

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units			MILLIMETERS		
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	Е		0.40 BSC		
Optional Center Pad Width	X2			3.80	
Optional Center Pad Length	Y2			3.80	
Contact Pad Spacing	C1		5.00		
Contact Pad Spacing	C2		5.00		
Contact Pad Width (X36)	X1			0.20	
Contact Pad Length (X36)	Y1			0.80	
Corner Pad Width (X4)	Х3			0.20	
Corner Pad Length (X36)	Y3			0.85	
Corner Pad Radius	R1		0.10		
Contact Pad to Center Pad (X36)	G1	0.20			
Thermal Via Diameter	V		0.30		
Thermal Via Pitch	EV		1.00		


Notes:

- 1. Dimensioning and tolerancing per ASME Y14.5M
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2436A-M5

48-Lead Thin Quad Flatpack (PT) - 7x7x1.0 mm Body [TQFP]


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-300-PT Rev A Sheet 1 of 2

48-Lead Thin Quad Flatpack (PT) - 7x7x1.0 mm Body [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS		
Dimension	Limits	MIN	NOM	MAX
Number of Leads	N		48	
Lead Pitch	е		0.50 BSC	
Overall Height	Α	ı	-	1.20
Standoff	A1	0.05	-	0.15
Molded Package Thickness	A2	0.95	1.00	1.05
Foot Length	L	0.45	0.60	0.75
Footprint	L1	1.00 REF		
Foot Angle	ф	0°	3.5°	7°
Overall Width	Е		9.00 BSC	
Overall Length	D		9.00 BSC	
Molded Package Width	E1		7.00 BSC	
Molded Package Length	D1	7.00 BSC		
Lead Thickness	С	0.09 - 0.16		
Lead Width	b	0.17	0.22	0.27
Mold Draft Angle Top	α	11°	12°	13°
Mold Draft Angle Bottom	β	11°	12°	13°


Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Chamfers at corners are optional; size may vary.
- 3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
 - REF: Reference Dimension, usually without tolerance, for information purposes only.
- 5. Datums A-B and to be determined at center line between leads where leads exit plastic body at datum plane

Microchip Technology Drawing C04-300-PT Rev A Sheet 2 of 2

48-Lead Thin Quad Flatpack (PT) - 7x7x1.0 mm Body [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units	N	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	Е	0.50 BSC			
Contact Pad Spacing	C1		8.40		
Contact Pad Spacing	C2		8.40		
Contact Pad Width (X48)	X1			0.30	
Contact Pad Length (X48)	Y1			1.50	
Distance Between Pads	G	0.20			


Notes:

- Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2300-PT Rev A

48-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M4) - 6x6 mm Body [UQFN] With Corner Anchors and 4.6x4.6 mm Exposed Pad


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-442A-M4 Sheet 1 of 2

48-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M4) - 6x6 mm Body [UQFN] With Corner Anchors and 4.6x4.6 mm Exposed Pad

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS		
Dimension	Limits	MIN	NOM	MAX
Number of Terminals	N		48	
Pitch	е		0.40 BSC	
Overall Height	Α	0.50	0.55	0.60
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3		0.15 REF	
Overall Length	D	6.00 BSC		
Exposed Pad Length	D2	4.50	4.60	4.70
Overall Width	Е		6.00 BSC	
Exposed Pad Width	E2	4.50	4.60	4.70
Terminal Width	b	0.15	0.20	0.25
Corner Anchor Pad	b1		0.45 REF	
Corner Anchor Pad, Metal-free Zone	b2		0.23 REF	
Terminal Length	L	0.35	0.40	0.45
Terminal-to-Exposed-Pad	K		0.30 REF	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-442A-M4 Sheet 2 of 2

48-Lead Ultra Thin Plastic Quad Flat, No Lead Package (M4) - 6x6 mm Body [UQFN] With Corner Anchors and 4.6x4.6 mm Exposed Pad

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimensior	n Limits	MIN	NOM	MAX
Contact Pitch	E	0.40 BSC		
Center Pad Width	X2			4.70
Center Pad Length	Y2			4.70
Contact Pad Spacing	C1		6.00	
Contact Pad Spacing	C2		6.00	
Contact Pad Width (X48)	X1			0.20
Contact Pad Length (X48)	Y1			0.80
Corner Anchor Pad Width (X4)	Х3			0.90
Corner Anchor Pad Length (X4)	Y3			0.90
Pad Corner Radius (X 20)	R			0.10
Contact Pad to Center Pad (X48)	G1	0.25		
Contact Pad to Contact Pad	G2	0.20		
Thermal Via Diameter	V		0.33	
Thermal Via Pitch	EV	_	1.20	


Notes:

- 1. Dimensioning and tolerancing per ASME Y14.5M $\,$
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process


Microchip Technology Drawing C04-2442A-M4

64-Lead Plastic Thin Quad Flatpack (PT)-10x10x1 mm Body, 2.00 mm Footprint [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging




TOP VIEW



Microchip Technology Drawing C04-085C Sheet 1 of 2

64-Lead Plastic Thin Quad Flatpack (PT)-10x10x1 mm Body, 2.00 mm Footprint [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS				
Dimensio	n Limits	MIN	NOM	MAX	
Number of Leads	N		64		
Lead Pitch	е		0.50 BSC		
Overall Height	Α	-	-	1.20	
Molded Package Thickness	A2	0.95	1.00	1.05	
Standoff	A1	0.05	-	0.15	
Foot Length	L	0.45	0.60	0.75	
Footprint	L1	1.00 REF			
Foot Angle	ф	0°	3.5°	7°	
Overall Width	E		12.00 BSC		
Overall Length	D		12.00 BSC		
Molded Package Width	E1		10.00 BSC		
Molded Package Length	D1		10.00 BSC		
Lead Thickness	С	0.09	-	0.20	
Lead Width	b	0.17	0.22	0.27	
Mold Draft Angle Top	α	11°	12°	13°	
Mold Draft Angle Bottom	β	11°	12°	13°	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Chamfers at corners are optional; size may vary.
- Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-085C Sheet 2 of 2

64-Lead Plastic Thin Quad Flatpack (PT)-10x10x1 mm Body, 2.00 mm Footprint [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units	N	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	E	0.50 BSC			
Contact Pad Spacing	C1		11.40		
Contact Pad Spacing	C2		11.40		
Contact Pad Width (X28)	X1			0.30	
Contact Pad Length (X28)	Y1			1.50	
Distance Between Pads	G	0.20			

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2085B Sheet 1 of 1


64-Lead Plastic Quad Flat, No Lead Package (MR) – 9x9x0.9 mm Body with 5.40 x 5.40 Exposed Pad [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging D В Ε 0.25 C Ν NOTE 1 0.25 C **TOP VIEW** // 0.10 C SEATING PLANE 向 (A3) ○ 0.08 C ⊕ 0.10M C A B D2 ⊕ 0.10M C A B е (DATUM B) E2 NOTE 1 e/2 (DATUM A) Κ 64X b 0.10(M) C A B 0.05(M) C **BOTTOM VIEW**

Microchip Technology Drawing C04-154A Sheet 1 of 2

64-Lead Plastic Quad Flat, No Lead Package (MR) – 9x9x0.9 mm Body with 5.40 x 5.40 Exposed Pad [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS		
Dimension	Dimension Limits		NOM	MAX	
Number of Pins	N		64		
Pitch	е		0.50 BSC		
Overall Height	Α	0.80	0.90	1.00	
Standoff	A1	0.00	0.02	0.05	
Contact Thickness	A3	0.20 REF			
Overall Width	Е	9.00 BSC			
Exposed Pad Width	E2	5.30	5.40	5.50	
Overall Length	D		9.00 BSC		
Exposed Pad Length	D2	5.30	5.40	5.50	
Contact Width	b	0.20	0.25	0.30	
Contact Length	L	0.30	0.40	0.50	
Contact-to-Exposed Pad	K	0.20	-	-	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated.
- 3. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-154A Sheet 2 of 2

64-Lead Plastic Quad Flat, No Lead Package (MR) – 9x9x0.9 mm Body [QFN] With 0.40 mm Contact Length and 5.40x5.40mm Exposed Pad

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		0.50 BSC	
Optional Center Pad Width	W2			5.50
Optional Center Pad Length	T2			5.50
Contact Pad Spacing	C1		8.90	
Contact Pad Spacing	C2		8.90	
Contact Pad Width (X64)	X1			0.30
Contact Pad Length (X64)	Y1			0.85
Distance Between Pads	G	0.20		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2154A

80-Lead Plastic Thin Quad Flatpack (PT) - 12x12x1 mm Body, 2.00 mm [TQFP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS		
	Dimension Limits	MIN	NOM	MAX	
Number of Leads	N	80			
Lead Pitch	е		0.50 BSC		
Overall Height	A	1	_	1.20	
Molded Package Thickness	A2	0.95	1.00	1.05	
Standoff	A1	0.05	_	0.15	
Foot Length	L	0.45	0.60	0.75	
Footprint	L1		1.00 REF		
Foot Angle	ф	0°	3.5°	7°	
Overall Width	E		14.00 BSC		
Overall Length	О		14.00 BSC		
Molded Package Width	E1		12.00 BSC		
Molded Package Length	D1		12.00 BSC		
Lead Thickness	С	0.09	_	0.20	
Lead Width	b	0.17	0.22	0.27	
Mold Draft Angle Top	α	11°	12°	13°	
Mold Draft Angle Bottom	β	11°	12°	13°	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Chamfers at corners are optional; size may vary.
- 3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25 mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-092B

80-Lead Plastic Thin Quad Flatpack (PT)-12x12x1mm Body, 2.00 mm Footprint [TQFP]

ote: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	N	IILLI METER	S
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е	0.50 BSC		
Contact Pad Spacing	C1		13.40	
Contact Pad Spacing	C2		13.40	
Contact Pad Width (X80)	X1			0.30
Contact Pad Length (X80)	Y1			1.50
Distance Between Pads	G	0.20		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2092B

NOTES:			

APPENDIX A: REVISION HISTORY

Revision A (December 2017)

This is the initial version of the document.

Revision B (May 2018)

This revision incorporates the following updates:

- · Sections:
 - Updated Section 4.2.7 "BIST at Start-up", Section 4.2.8 "BIST at Run Time", Section 15.0 "Quadrature Encoder Interface (QEI)", Section 30.2 "Device Calibration and Identification", Section 30.10 "Code Protection and CodeGuard™ Security" and Section 34.1 "Package Marking Information".
 - Added Section 5.3.2 "Error Correcting Code (ECC)" and Section 5.5.4 "ECC Control Registers".
- Tables
 - Updated Table 4-3, Table 4-9, Table 7-3,
 Table 7-4, Table 7-5, Table 8-7, Table 15-1,
 Table 24-3, Table 30-3, Table 33-1,
 Table 33-3, Table 33-5, Table 33-6 (was Table 33-9), Table 33-7 (was Table 33-11),
 Table 33-22, Table 33-37 and Table 33-40.
 - Deleted Table 33-6, Table 33-7, Table 33-8 and Table 33-10.
 - Added Table 33-10, Table 33-11, Table 33-12 and Table 33-13.
- · Figures:
 - Updated Figure 3-1, Figure 4-1, Figure 4-12, Figure 15-2, Figure 30-3 and Figure 30-4.
- · Registers:
 - Updated Register 4-1, Register 14-1, Register 14-6, Register 14-7, Register 14-9, Register 15-1, Register 15-2, Register 15-3, Register 15-5, Register 15-6, Register 15-7, Register 15-9, Register 15-11, Register 15-17, Register 27-1, Register 27-2, Register 30-5 and Register 30-7.
 - Added Register 5-7, Register 5-8, Register 5-9, Register 5-10, Register 5-11, Register 5-12, Register 15-18 and Register 15-19.
 - Deleted Register 15-8, Register 15-12 and Register 15-20.
- · Examples:
 - Updated Example 29-1.
 - Added Example 29-2.
- · Equations:
 - Deleted Equation 4-1.

Revision C (July 2018)

This revision incorporates the following updates:

- Tables
 - Updated Table 1-1, Table 33-10, Table 33-20, Table 33-21, Table 33-26 and Table 33-41.
- Registers
 - Updated Register 4-1, Register 10-1, Register 12-12, Register 12-13, Register 13-30, Register 14-6, Register 14-7, Register 15-2, Register 16-4, Register 20-2, Register 22-7, Register 28-5, Register 28-6, Register 28-7, Register 28-8, Register 28-9, Register 28-10 and Register 28-11.
- · Figures:
 - Updated Figure 13-1 and Figure 13-2.

Revision D (September 2018)

This revision incorporates the following updates:

- · Sections:
 - Updated Section 18.0 "Inter-Integrated Circuit (I²C)".
 - Added Section 18.4 "SMBus Support".
 - Updated the packaging diagrams for the 28-Lead SSOP and 28-Lead UQFN in Section 34.0 "Packaging Information".
- · Tables:
 - Updated Table 33-5, Table 33-6, Table 33-7, Table 33-8, Table 33-13 and Table 33-23.
 - Added Table 18-3.
- · Registers:
 - Updated Register 12-9, Register 13-3, Register 30-6 and Register 30-21.
- · Figures:
 - Updated Figure 9-4.

Revision E (December 2018)

This revision incorporates the following updates:

- · Sections:
 - Updated the "Operating Conditions", "Safety Features" and "Pin Diagrams" sections.
 - Updated Section 5.0 "Flash Program Memory", Section 5.2 "RTSP Operation", Section 5.3.1 "Programming Algorithm for Flash Program Memory", Section 5.3.3 "ECC Fault Injection", Section 8.5.5 "Input Mapping", Section 12.0 "High-Resolution PWM with Fine Edge Placement", Section 23.1 "Control Registers" and the "Product Identification System" section.
 - Added Section 8.5.3 "Controlling Configuration Changes", Section 8.5.3.1 "Control Register Lock", Section 8.5.4 "Considerations for Peripheral Pin Selection", Section 9.6 "OSCCON Unlock Sequence", Section 12.3 "Lock and Write Restrictions" and Section 34.0 "High-Temperature Electrical Characteristics".
- · Tables:
 - Added Table 7-1 and Table 12-1.
 - Updated Table 7-2, Table 26-1, Table 33-4, Table 33-39 and Table 33-41.
- · Registers:
 - Added Register 3-3 and Register 5-6.
 - Updated Register 5-5, Register 8-13, Register 9-1, Register 9-4, Register 12-1, Register 13-6, Register 16-1, Register 17-1 and Register 30-14.
- · Figures:
 - Updated Figure 17-1 and Figure 17-2.
- · Examples:
 - Added Example 5-1 and Example 8-1.

INDEX

Α		Secu
Absolute Maximum Ratings	547	Secu
AC Characteristics		SEN [*]
Load Conditions		Shar
Alternate Interrupt Vector Table		Simp
Analog-to-Digital Converter. See ADC.		SPIx
Arithmetic Logic Unit (ALU)	30	SPIx
Assembler		SPIx
MPASM Assembler	544	
MPLAB Assembler, Linker, Librarian		SPIx
Auto-Shutdown and Gating Sources		SPIx
Auto-Shutdown and Gating Sources		SPIx
В		SPIx
Bit-Reversed Addressing	74	SPIx
Example		Sugg
Implementation		Time
Sequence Table (16-Entry)		Wato
Block Diagrams	13	Brown-out
16-Bit Timer1 Module	420	Built-In Se
ADC Module		At Ru
		At St
Addressing for Table Degisters		Flow
Addressing for Table Registers		Built-In Se
APLL and VCO Detail		
CALL Stack Frame		С
CAN FD Module		C Compile
CLCx Input Source Selection		MPL
CLCx Logic Function Combinatorial Options		CAN FD N
CLCx Module		Cont
Conceptual SCCPx Modules		Feat
Constant-Current Source		Mess
CPU Core		Capture/C
CRC Module	475	Auto
Data Access from Program Space		Auxil
Address Generation		Cont
Deadman Timer Module		Gene
Dedicated ADC Core		Input
dsPIC33CK256MP508 Core Clock Sources	183	Outp
dsPIC33CK256MP508 Core		Sync
Oscillator Subsystem		Time
dsPIC33CK256MP508 Family		Capture/C
Functional Direct Memory Access (DMA)		Capture/C CLC
High-Speed Analog Comparator	324	Cont
I2Cx Module	396	Code Exa
Interleaved PFC	26	Code Exa
Internal Regulator		Flash
Master Reset System	95	
MCLR Pin Connections	24	PWRS
Multiplexing Remappable Outputs for RPn		PWRS
Off-Line UPS	28	Using
Operational Amplifier	483	Using
Phase-Shifted Full-Bridge Converter	27	Using
PLL and VCO	185	Code Prot
PMP Pinout and Connections to		CodeGua
External Devices	405	Comparat
Programmer's Model	32	Cont
PSV Read Address Generation		Feat
PTG		Configura
PWM High-Level Module	262	Configura
QEI Module		Configura
Recommended Minimum Connection		Bit V
Remappable Input for U1RX		Controller
11 1 2 2	-	

Security Segments	
Security Segments (Dual Partition)	532
SENTx Module	420
Shared Port Structure	121
Simplified UARTx	356
SPIx Master, Frame Master Connection	393
SPIx Master, Frame Slave Connection	
SPIx Master/Slave Connection	
(Enhanced Buffer Modes)	303
SPIx Master/Slave Connection (Standard Mode)	
SPIx Module (Enhanced Mode)	
SPIx Module (Standard Mode)	
SPIx Slave, Frame Master Connection	
SPIx Slave, Frame Slave Connection	
Suggested Oscillator Circuit Placement	
Timer Clock Generator	
Watchdog Timer (WDT)	
Brown-out Reset (BOR)507,	
Built-In Self-Test (BIST)	
At Run Time	
At Start-up	. 50
Flowchart	. 50
Built-In Self-Test. See BIST.	
•	
C Compilers	
MPLAB XC	544
CAN FD Module	
Control Registers	219
Features	217
Message Reception	217
Capture/Compare/PWM/Timer	
Auto-Shutdown and Gating Sources	441
Auxiliary Output	436
Control Registers	437
General Purpose Timer	
Input Capture Mode	
Output Compare Mode	
Synchronization Sources	
Time Base Generator	
Capture/Compare/PWM/Timer (SCCP/MCCP)	
CLC	-100
Control Registers	450
Code Examples	
Configuring UART1 Input and Output Functions	131
Flash Write/Read	
PWRSAV Instruction Syntax in Assembly	
PWRSAV Instruction Syntax in C Language	
Using Auxiliary PLL with Internal FRC Oscillator	
Using PLL (50 MIPS) with POSC	
Using Primary PLL with 8 MHz Internal FRC	
Code Protection 507,	
CodeGuard Security 507,	531
Comparator/DAC	
Control Registers	
Features Overview	
Configurable Logic Cell (CLC)	447
Configurable Logic Cell. See CLC.	
Configuration Bits	
Bit Values for Clock Selection	192
Controller Area Network. See CAN.	

CPU		Comparator + DAC Delta Current	
Addressing Modes	29	Constant-Current Source Specifications	582
Control Registers		DACx Output (DACOUT1 Pin) Specifications	581
Data Space Addressing	29	DACx Specifications	
Instruction Set		Doze Current (IDOZE)	552
Registers	29	External Clock Requirements	
Resources		High-Speed Analog Comparator Specifications	
CRC		High-Speed PWMx Timing Requirements	
Control Registers	476	I/O Pin Input Injection Current Specifications	
Current Bias Generator	•	I/O Pin Input Specifications	
Control Registers	480	I/O Pin Output Specifications	
Current Bias Generator (CBG)		I/O Timing Requirements	
Current Bias Generator, See CBG.	47 5	I2Cx Bus Data Timing Requirements	000
Customer Change Notification Service	610	(Master Mode)	575
Customer Notification Service		I2Cx Bus Data Timing Requirements	57 0
Customer Support		(Slave Mode)	577
• • • • • • • • • • • • • • • • • • • •	019		
Cyclic Redundancy Check. See CRC.		Idle Current (IIDLE)	
D		Internal FRC Accuracy	
Data Address Chass	45	Internal LPRC Accuracy	
Data Address Space		Op Amp Delta Current	
Memory Map for dsPIC33CK128MPX0X Devices .		Operating Current (IDD)	
Memory Map for dsPIC33CK256MP508 Devices	47	Operating Voltage Specifications	
Memory Map for dsPIC33CK64MPX0X and		Operational Amplifier Specifications	
dsPIC33CK32MPX0X Devices		PLL Timing Specifications	
Near Data Space		Power-Down Current (IPD)	552
Organization, Alignment		Program Memory	558
SFR Space	46	PWM Delta Current	553
Width	45	Reset, WDT, OST, PWRT Timing Requirements	564
Data Space		SPIx Master Mode (Full-Duplex, CKE = 0,	
Extended X	70	CKP = x, SMP = 1) Timing Requirements	569
Paged Data Memory Space (figure)	68	SPIx Master Mode (Full-Duplex, CKE = 1,	
Paged Memory Scheme		CKP = x, SMP = 1) Timing Requirements	568
DC Characteristics		SPIx Master Mode (Half-Duplex, Transmit Only)	
Operating MIPS vs. Voltage	548	Timing Requirements	567
Deadman Timer (DMT)		SPIx Maximum Data/Clock Rate Summary	
Control Registers		SPIx Slave Mode (Full-Duplex, CKE = 0,	
Deadman Timer. See DMT.		CKP = x, SMP = 0) Timing Requirements	571
Demo/Development Boards, Evaluation and		SPIx Slave Mode (Full-Duplex, CKE = 1,	01
Starter Kits	546	CKP = x, SMP = 0) Timing Requirements	573
Development Support		, , , , , , , , , , , , , , , , , , , ,	
Device Calibration		UARTx I/O Timing Requirements	
and Identification		Watchdog Timer Delta Current (∆IWDT)	၁၁၁
Device Overview		Equations	400
Device Programmer	17	AFPLLO Calculation	
•	E4E	AFvco Calculation	
MPLAB PM3	545	FPLLO Calculation	
Direct Memory Access Controller. See DMA.		Frame Time Calculations	
DMA	- · -	Fvco Calculation	
Channel Trigger Sources		I ² C Baud Rate Reload Calculation	397
Control Registers		Relationship Between Device and	
Peripheral Module Disable (PMD)		SPIx Clock Speed	394
Summary of Operations	209	SYNCMINx and SYNCMAXx Calculations	422
Types of Data Transfers	210	Tick Period Calculation	421
Typical Setup	211	Errata	15
Doze Mode	497	Error Correcting Code (ECC)	82
DSP Engine	39	Fault Injection	
Dual Watchdog Timer (Dual WDT)	528		
_		F	
E		Flash Program Memory	
ECC		and Table Instructions	79
Control Registers	92	Control Registers	
Electrical Characteristics		Dual Partition Flash Configuration	
AC		Operations	
ADC Delta Current		RTSP Operation	
ADC Specifications		Flexible Configuration	
APLL Delta Current		Lionidio Comigaration	501
APLL Timing Specifications			

G	
Getting Started Guidelines	23
Connection Requirements	
Decoupling Capacitors	23
External Oscillator Pins	25
ICSP Pins	
Master Clear (MCLR) Pin	24
Oscillator Value Conditions on Start-up	26
Targeted Applications	26
Unused I/Os	26
Н	
High-Resolution PWM (HSPWM) with	
Fine Edge Placement2	.61
High-Speed Analog Comparator with	
Slope Compensation DAC	23
High-Speed, 12-Bit Analog-to-Digital	
Converter (ADC)	
Control Registers	
Features Overview	
Resources	.97
HSPWM	
Architecture	
Control Registers	
Lock and Write Restrictions	
PWM Output Availability (table)2	.61
1	
•	
I/O Ports	~~
Configuring Analog/Digital Port Pins	
Control Registers	
Helpful Tips	
Parallel I/O (PIO)1	
Resources	
Write/Read Timing1	22
	07
Clock Rates	97
Communicating as Master in Single	OF
Master Environment	
9	
Reserved Addresses	
Setting Baud Rate as Bus Master	
Slave Address Masking	
SMBus Support	
ICSP Write InhibitActivation	റാ
In-Circuit Debugger5	
MPLAB ICD 35	
PICkit 3 Programmer5	
In-Circuit Emulation	
In-Circuit Serial Programming (ICSP)507, 5	21
Input Change Notification (ICN)1	20
Instruction Addressing Modes	
File Register Instructions	
Fundamental Modes Supported	
MAC Instructions	
MCU Instructions	
Move and Accumulator Instructions	
Other Instructions	
Instruction Set Summary	
Overview	
Symbols Used in Opcode Descriptions	

Instruction-Based Power-Saving Modes	
ldle	
Sleep	496
Inter-Integrated Circuit. See I ² C.	
Internet Address	619
Interrupt Controller	
Alternate Interrupt Vector Table (AIVT)	
Control and Status Registers	110
INTCON1	
INTCON2	
INTCON3	
INTCON4	
INTTREG	
Interrupt Vector Details	
Interrupt Vector Table (IVT)	99
Reset Sequence	99
Resources	110
Trap Vector Details	102
Interrupt Vector Table	100
Interrupts Coincident with Power Save Instructions	496
•	
J	
JTAG Boundary Scan Interface	507
JTAG Interface	531
ı	
L	400
Low-Power Sleep Modes (table)	496
M	
Memory Organization	41
Resources	
Microchip Internet Website	
Modulo Addressing	
Applicability	74
Operation Example	
Start and End Address	
W Address Register Selection	
MPLAB REAL ICE In-Circuit Emulator System	
MPLAB X Integrated Development	0-10
Environment Software	543
MPLINK Object Linker/MPLIB Object Librarian	
INIT EINIT Object Ellintel/Wil Elb Object Elbianam	
0	
Operational Amplifier	483
Control Registers	
Oscillator	
Configuration	192
Control Registers	
CPU Clocking	
Internal Fast RC (FRC)	
Low-Power RC (LPRC)	
OSCCON Unlock Sequence	
Primary (POSC)	
Oscillator with High-Frequency PLL	
_	-
P	
Packaging	
Details	
Marking	
Parallel Master Port (PMP)	
Peripheral Module Disable (PMD)	497

Peripheral Pin Select (PPS)	129	PORTA	. 143
Available Peripherals	129	PORTB	. 143
Available Pins	129	PORTC	. 144
Control Registers		PORTD	. 144
Controlling Configuration Changes		PORTE	
Input Mapping		PPS Input Control	
Output Mapping		PPS Output Control	
Output Selection for Remappable Pins		Registers	102
		•	200
Remappable Output Pin Registers		ACLKCON1 (Auxiliary Clock Control)	200
Remappable Pin Inputs		ADCMPxCON (ADC Digital	0.40
Selectable Input Sources		Comparator x Control)	. 319
Peripheral Trigger Generator (PTG)	459	ADCMPxENH (ADC Digital Comparator x	
Peripheral Trigger Generator. See PTG.		Channel Enable High)	. 320
Pin and ANSELx Availability		ADCMPxENL (ADC Digital Comparator x	
Pinout I/O Descriptions (table)	18	Channel Enable Low)	
PMP		ADCON1H (ADC Control 1 High)	. 299
Control Registers		ADCON1L (ADC Control 1 Low)	. 298
Power-Saving Features	495	ADCON2H (ADC Control 2 High)	. 301
Clock Frequency and Switching	495	ADCON2L (ADC Control 2 Low)	. 300
Resources	497	ADCON3H (ADC Control 3 High)	. 303
Program Address Space		ADCON3L (ADC Control 3 Low)	
Memory Map for dsPIC33CK128MP50X/20X		ADCON4H (ADC Control 4 High)	
Devices	42	ADCON4L (ADC Control 4 Low)	
Memory Map for dsPIC33CK256MP50X/20X		ADCON5H (ADC Control 5 High)	
Devices	42	ADCON5L (ADC Control 5 Low)	
Memory Map for dsPIC33CK32MP50X/20X		ADCOREXH (Dedicated ADC Core x	000
Devices	13	Control High)	300
Memory Map for dsPIC33CK64MP50X/20X	43	ADCORExL (Dedicated ADC Core x	. 508
•	42	,	200
Devices	43	Control Low)	
Memory Map for dsPIC33CKXXXMP50X/20X	4.4	ADEIEH (ADC Early Interrupt Enable High)	
Devices	41	ADEIEL (ADC Early Interrupt Enable Low)	
Program Memory		ADEISTATH (ADC Early Interrupt Status High)	
Address Space		ADEISTATL (ADC Early Interrupt Status Low)	
Construction	76	ADFLxCON (ADC Digital Filter x Control)	
Data Access from Program Memory Using		ADIEH (ADC Interrupt Enable High)	
Table Instructions	77	ADIEL (ADC Interrupt Enable Low)	. 315
Table Read High Instructions (TBLRDH)	77	ADLVLTRGH (ADC Level-Sensitive Trigger	
Table Read Low Instructions (TBLRDL)	77	Control High)	. 310
Interfacing with Data Memory Spaces	76	ADLVLTRGL (ADC Level-Sensitive Trigger	
Organization	44	Control Low)	. 310
Reset Vector	44	ADMOD0H (ADC Input Mode Control 0 High)	. 313
Programmer's Model	31	ADMOD0L (ADC Input Mode Control 0 Low)	. 313
Register Descriptions		ADMOD1H (ADC Input Mode Control 1 High)	
PTG		ADMOD1L (ADC Input Mode Control 1 Low)	
Command Options	471	ADSTATH (ADC Data Ready Status High)	
Control Registers		ADSTATL (ADC Data Ready Status Low)	
Features		ADTRIGNL/ADTRIGNH (ADC Channel Trigger n(x)	0.0
Input Descriptions		Selection Low/High)	317
Output Descriptions		AMPCON1H (Op Amp Control High)	
Step Command Format/Description		AMPCON1L (Op Amp Control Low)	
Step Command Formar Description	470		
Q		ANSELx (Analog Select for PORTx)	
QEI		APLLDIV1 (APLL Output Divider)	
	220	APLLFBD1 (APLL Feedback Divider)	
Control and Status Registers		BIASCON (Current Bias Generator Control)	
Truth Table		C1BDIAG0H (CAN Bus Diagnostics 0 High)	
Quadrature Encoder Interface (QEI)	335	C1BDIAG0L (CAN Bus Diagnostics 0 Low)	
Quadrature Encoder Interface. See QEI.		C1BDIAG1H (CAN Bus Diagnostics 1 High)	
R		C1BDIAG1L (CAN Bus Diagnostics 1 Low)	
	4.5	C1CONH (CAN Control High)	
Referenced Sources	16	C1CONL (CAN Control Low)	. 221
Register Maps		C1DBTCFGH (CAN Data Bit Time	
Configuration		Configuration High)	. 223
Interrupt Enable		C1DBTCFGL (CAN Data Bit Time	
Interrupt Flag		Configuration Low)	. 223
Interrupt Priority	108		
PMD	505		

C1FIFOBAH (CAN Message Memory Base		C1VECH (CAN Interrupt Code High)	. 228
Address High)	237	C1VECL (CAN Interrupt Code Low)	. 229
C1FIFOBAL (CAN Message Memory Base		CANCLKCON (CAN Clock Control)	. 203
Address Low)	237	CCPxCON1H (CCPx Control 1 High)	. 439
C1FIFOCONHx (CAN FIFO Control x High)	241	CCPxCON1L (CCPx Control 1 Low)	. 437
C1FIFOCONLx (CAN FIFO Control x Low)	242	CCPxCON2H (CCPx Control 2 High)	. 442
C1FIFOSTAx (CAN FIFO Status x)	244	CCPxCON2L (CCPx Control 2 Low)	. 441
C1FIFOUAHx (CAN FIFO User Address x High)	249	CCPxCON3H (CCPx Control 3 High)	. 444
C1FIFOUALx (CAN FIFO User Address x Low)	249	CCPxCON3L (CCPx Control 3 Low)	
C1FLTCONxH (CAN Filter Control x High)	256	CCPxSTATL (CCPx Status)	. 445
C1FLTCONxL (CAN Filter Control x Low)	257	CLCxCONH (CLCx Control High)	. 451
C1FLTOBJxH (CAN Filter Object x High)	258	CLCxCONL (CLCx Control Low)	. 450
C1FLTOBJxL (CAN Filter Object x Low)	258	CLCxGLSH (CLCx Gate Logic Input Select High)	. 456
C1INTH (CAN Interrupt High)	230	CLCxGLSL (CLCx Gate Logic Input Select Low)	. 454
C1INTL (CAN Interrupt Low)	231	CLCxSEL (CLCx Input MUX Select)	. 452
C1MASKxH (CAN Mask x High)	259	CLKDIV (Clock Divider)	. 195
C1MASKxL (CAN Mask x Low)	259	CMBTRIGH (Combinational Trigger High)	. 268
C1NBTCFGH (CAN Nominal Bit Time		CMBTRIGL (Combinational Trigger Low)	. 267
Configuration High)	222	CNCONx (Change Notification Control	
C1NBTCFGL (CAN Nominal Bit Time		for PORTx)	. 126
Configuration Low)	222	CNEN0x (Interrupt Change Notification Enable	
C1RXIFH (CAN Receive Interrupt Status High)	232	for PORTx)	. 126
C1RXIFL (CAN Receive Interrupt Status Low)	232	CNEN1x (Interrupt Change Notification Edge Select	t
C1RXOVIFH (CAN Receive Overflow Interrupt		for PORTx)	. 127
Status High)	233	CNFx (Interrupt Change Notification Flag	
C1RXOVIFL (CAN Receive Overflow Interrupt		for PORTx)	. 128
Status Low)	233	CNPDx (Change Notification Pull-Down Enable	
C1TBCH (CAN Time Base Counter High)		for PORTx)	. 125
C1TBCL (CAN Time Base Counter Low)	226	CNPUx (Change Notification Pull-up Enable	
C1TDCH (CAN Transmitter Delay		for PORTx)	. 125
Compensation High)	224	CNSTATx (Interrupt Change Notification Status	
C1TDCL (CAN Transmitter Delay		for PORTx)	. 127
Compensation Low)	225	CORCON (Core Control)36,	
C1TEFCONH (CAN Transmit Event		CRCCONH (CRC Control High)	. 477
FIFO Control High)	246	CRCCONL (CRC Control Low)	. 476
C1TEFCONL (CAN Transmit Event		CRCXORH (CRC XOR Polynomial, High Byte)	
FIFO Control Low)		CRCXORL (CRC XOR Polynomial, Low Byte)	
C1TEFSTA (CAN Transmit Event FIFO Status)	248	CTXTSTAT (CPU W Register Context Status)	
C1TEFUAH (CAN Transmit Event		DACCTRL1L (DAC Control 1 Low)	
FIFO User Address High)	250	DACCTRL2H (DAC Control 2 High)	
C1TEFUAL (CAN Transmit Event		DACCTRL2L (DAC Control 2 Low)	
FIFO User Address Low)	250	DACXCONH (DACX Control High)	
C1TRECH (CAN Transmit/Receive		DACXCONL (DACX Control Low)	
Error Count High)	252	DACxDATH (DACx Data High)	
C1TRECL (CAN Transmit/Receive		DACxDATL (DACx Data Low)	
Error Count Low)		DEVID (Device ID)	
C1TSCONH (CAN Timestamp Control High)		DEVREV (Device Revision)	
C1TSCONL (CAN Timestamp Control Low)	227	DMACHn (DMA Channel n Control)	
C1TXATIFH (CAN Transmit Attempt Interrupt	005	DMACON (DMA Engine Control)	
Status High)	235	DMAINTn (DMA Channel n Interrupt)	
C1TXATIFL (CAN Transmit Attempt Interrupt	005	DMTCLR (Deadman Timer Clear)	
Status Low)		DMTCNTH (Deadman Timer Count High)	
C1TXIFH (CAN Transmit Interrupt Status High)		DMTCNTL (Deadman Timer Count Low)	
C1TXIFL (CAN Transmit Interrupt Status Low)	234	DMTCON (Deadman Timer Control)	
C1TXQCONH (CAN Transmit Queue	220	DMTHOLDREG (DMT Hold)	
Control High)	230	DMTPRECLR (Deadman Timer Preclear)	. 400
C1TXQCONL (CAN Transmit Queue	220	DMTPSCNTH (DMT Post-Configure Count	400
CONTROL CONTRO		Status High)	. 492
C1TXQSTA (CAN Transmit Queue Status)	∠40	DMTPSCNTL (DMT Post-Configure Count	400
C1TXQUAH (CAN Transmit Queue User	251	Status Low) DMTPSINTVH (DMT Post-Configure Interval	. 492
Address High)	201		400
C1TXQUAL (CAN Transmit Queue User Address Low)	251	Status High) DMTPSINTVL (DMT Post-Configure Interval	. 493
C1TXREQH (CAN Transmit Request High)		Status Low)	ΔΩ 2
OTTAINE WIT (OAN TRANSHIIL NEQUEST HIGH)			
C1TXREQL (CAN Transmit Request Low)		DMTSTAT (Deadman Timer Status)	

ECCADDRH (ECC Fault Inject Address		NVMSRCADRL (NVM Source Data	
Compare High)	93	Address Low)	
ECCADDRL (ECC Fault Inject Address		ODCx (Open-Drain Enable for PORTx)	124
Compare Low)	93	OSCCON (Oscillator Control)	193
ECCCONH (ECC Fault Injection		OSCTUN (FRC Oscillator Tuning)	
Configuration High)	92	PCLKCON (PWM Clock Control)	263
ECCCONL (ECC Fault Injection		PGxCAP (PWM Generator x Capture)	293
Configuration Low)	92	PGxCONH (PWM Generator x Control High)	275
ECCSTATH (ECC System Status Display High)	94	PGxCONL (PWM Generator x Control Low)	274
ECCSTATL (ECC System Status Display Low)	94	PGxDC (PWM Generator x Duty Cycle)	289
FALTREG Configuration	521	PGxDCA (PWM Generator x	
FBOOT Configuration	523	Duty Cycle Adjustment)	290
FBSLIM Configuration	511	PGxDTH (PWM Generator x Dead-Time High)	292
FBTSEQ Configuration	522	PGxDTL (PWM Generator x Dead-Time Low)	292
FDEVOPT Configuration		PGxEVTH (PWM Generator x Event High)	282
FDMT Configuration		PGxEVTL (PWM Generator x Event Low)	281
FDMTCNTH Configuration		PGxIOCONH (PWM Generator x	
FDMTCNTL Configuration	518	I/O Control High)	280
FDMTIVTH Configuration		PGxIOCONL (PWM Generator x	
FDMTIVTL Configuration		I/O Control Low)	279
FICD Configuration		PGxLEBH (PWM Generator x Leading-Edge	
FOSC Configuration		Blanking High)	288
FOSCSEL Configuration		PGxLEBL (PWM Generator x Leading-Edge	
FPOR Configuration		Blanking Low)	287
FSCL (Frequency Scale)		PGxPER (PWM Generator x Period)	
FSEC Configuration		PGxPHASE (PWM Generator x Phase)	
FSIGN Configuration		PGxSTAT (PWM Generator x Status)	
FSMINPER (Frequency Scaling		PGxTRIGA (PWM Generator x Trigger A)	
Minimum Period)	264	PGxTRIGB (PWM Generator x Trigger B)	
FWDT Configuration		PGxTRIGC (PWM Generator x Trigger C)	
I2CxCONH (I2Cx Control High)		PGxyPCIH (PWM Generator xy PCI High)	
I2CxCONL (I2Cx Control Low)		PGxyPCIL (PWM Generator xy PCI Low)	
I2CxMSK (I2Cx Slave Mode Address Mask)		PLLDIV (PLL Output Divider)	
I2CxSTAT (I2Cx Status)		PLLFBD (PLL Feedback Divider)	
IBIASCONH (Current Bias Generator Current	402	PMADDR (PMP Address)	
Source Control High)	481	PMAEN (PMP Pin Enable)	
IBIASCONL (Current Bias Generator Current	401	PMCON (PMP Control)	
Source Control Low)	482	PMCONH (PMP Control High)	
INDXxCNTH (Index x Counter High)		PMD1 (PMD1 Control)	
INDXxCNTL (Index x Counter Low)		PMD2 (PMD2 Control)	
INDXxHLD (Index x Counter Hold)		PMD3 (PMD3 Control)	
INTCON1 (Interrupt Control 1)		PMD4 (PMD4 Control)	
INTCON1 (Interrupt Control 2)		PMD6 (PMD6 Control)	
INTCON2 (Interrupt Control 3)		PMD7 (PMD7 Control)	
INTCON3 (Interrupt Control 4)		PMD8 (PMD8 Control)	
INTTREG (Interrupt Control and Status)		PMDIN1 (PMP Data Input/Output Low)	
INTXTMRH (Interval x Timer High)		PMDIN2 (PMP Data Input/Output High)	
· · · · · · · · · · · · · · · · · · ·			
INTxTMRL (Interval x Timer Low)INTXxHLDH (Interval x Timer Hold High)		PMDOUT1 (PMP Data Output Low)PMDOUT2 (PMP Data Output High)	
` ,		· · · · · · · · · · · · · · · · · · ·	
INTXxHLDL (Interval x Timer Hold Low)		PMMODE (PMP Mode)	
LATx (Output Data for PORTx)		PMRADDR (PMP Read Address)	
LFSR (Linear Feedback Shift)	2/3	PMRDIN (PMP Read Input Data)	
LOGCONy (Combinatorial PWM Logic	000	PMSTAT (PMP Status)	
Control y)		PMWADDR (PMP Write Address)	
MBISTCON (MBIST Control)		PORTx (Input Data for PORTx)	
MDC (Master Duty Cycle)		POSxCNTH (Position x Counter High)	
MPER (Master Period)		POSxCNTL (Position x Counter Low)	
MPHASE (Master Phase)		POSxHLD (Position x Counter Hold)	
MSTRPR (EDS Bus Master Priority Control)		PTGADJ (PTG Adjust)	
NVMADR (Nonvolatile Memory Lower Address)		PTGBTE (PTG Broadcast Trigger Enable Low)	464
NVMADRU (Nonvolatile Memory Upper Address	•	PTGBTEH (PTG Broadcast Trigger	
NVMCON (Nonvolatile Memory (NVM) Control).		Enable High)	
NVMKEY (Nonvolatile Memory Key)	90	PTGC0LIM (PTG Counter 0 Limit)	
NVMSRCADRH (NVM Source Data		PTGC1LIM (PTG Counter 1 Limit)	
Address High)	91	PTGCON (PTG Control/Status High)	463

PTGCST (PTG Control/Status Low)	461	RPINR9 (Peripheral Pin Select Input 9)	151
PTGHOLD (PTG Hold)		RPOR0 (Peripheral Pin Select Output 0)	
PTGL0 (PTG Literal 0)		RPOR1 (Peripheral Pin Select Output 1)	
PTGQPTR (PTG Step Queue Pointer)		RPOR10 (Peripheral Pin Select Output 10)	
PTGQUEn (PTG Step Queue n Pointer)		RPOR11 (Peripheral Pin Select Output 11)	
PTGSDLIM (PTG Step Delay Limit)		RPOR12 (Peripheral Pin Select Output 12)	
PTGT0LIM (PTG Timer0 Limit)		RPOR13 (Peripheral Pin Select Output 13)	
PTGT1LIM (PTG Timer1 Limit)		RPOR14 (Peripheral Pin Select Output 14)	
PWMEVTy (PWM Event Output Control y)		RPOR15 (Peripheral Pin Select Output 15)	
QEIXCON (QEIX Control)		RPOR16 (Peripheral Pin Select Output 16)	
QEIXGECH (QEIX Greater Than or Equal	550	RPOR17 (Peripheral Pin Select Output 17)	
	254	, , ,	
Compare High)	354	RPOR18 (Peripheral Pin Select Output 18)	
QEIxGECL (QEIx Greater Than or Equal	254	RPOR19 (Peripheral Pin Select Output 19)	
Compare Low)		RPOR2 (Peripheral Pin Select Output 2)	
QEIxICH (QEIx Initialization/Capture High)		RPOR20 (Peripheral Pin Select Output 20)	
QEIxICL (QEIx Initialization/Capture Low)		RPOR21 (Peripheral Pin Select Output 21)	
QEIxIOC (QEIx I/O Control)		RPOR22 (Peripheral Pin Select Output 22)	
QEIxIOCH (QEIx I/O Control High)	341	RPOR23 (Peripheral Pin Select Output 23)	178
QEIxLECH (QEIx Less Than or Equal		RPOR24 (Peripheral Pin Select Output 24)	
Compare High)	353	RPOR25 (Peripheral Pin Select Output 25)	179
QEIxLECL (QEIx Less Than or Equal		RPOR26 (Peripheral Pin Select Output 26)	180
Compare Low)	353	RPOR3 (Peripheral Pin Select Output 3)	168
QEIxSTAT (QEIx Status)	342	RPOR4 (Peripheral Pin Select Output 4)	169
RCON (Reset Control)	97	RPOR5 (Peripheral Pin Select Output 5)	169
REFOCONH (Reference Clock Control High)	205	RPOR6 (Peripheral Pin Select Output 6)	170
REFOCONL (Reference Clock Control Low)	204	RPOR7 (Peripheral Pin Select Output 7)	
RPCON (Peripheral Remapping Configuration)		RPOR8 (Peripheral Pin Select Output 8)	
RPINR0 (Peripheral Pin Select Input 0)		RPOR9 (Peripheral Pin Select Output 9)	
RPINR1 (Peripheral Pin Select Input 1)		SENTxCON1 (SENTx Control 1)	
RPINR10 (Peripheral Pin Select Input 10)		SENTxDATH (SENTx Receive Data High)	
RPINR11 (Peripheral Pin Select Input 11)		SENTxDATL (SENTx Receive Data Low)	
RPINR12 (Peripheral Pin Select Input 12)		SENTxSTAT (SENTx Status)	
RPINR13 (Peripheral Pin Select Input 13)		SLPxCONH (DACx Slope Control High)	
RPINR14 (Peripheral Pin Select Input 14)		SLPxCONL (DACx Slope Control Low)	
RPINR15 (Peripheral Pin Select Input 15)		SLPxDAT (DACx Slope Data)	
RPINR16 (Peripheral Pin Select Input 16)		SPIxCON1H (SPIx Control 1 High)	
RPINR17 (Peripheral Pin Select Input 17)		SPIxCON1L (SPIx Control 1 Low)	
RPINR18 (Peripheral Pin Select Input 18)		SPIxCON2L (SPIx Control 2 Low)	
RPINR19 (Peripheral Pin Select Input 19)		SPIxIMSKH (SPIx Interrupt Mask High)	
RPINR2 (Peripheral Pin Select Input 2)		SPIxIMSKL (SPIx Interrupt Mask Low)	
RPINR20 (Peripheral Pin Select Input 20)		SPIxSTATH (SPIx Status High)	
RPINR21 (Peripheral Pin Select Input 21)		SPIXSTATT (SPIX Status Low)	
RPINR22 (Peripheral Pin Select Input 21)		SR (CPU STATUS)	
` ' '		T1CON (Timer1 Control)	
RPINR23 (Peripheral Pin Select Input 23)			
RPINR26 (Peripheral Pin Select Input 26)		TRISx (Output Enable for PORTx)	
RPINR27 (Peripheral Pin Select Input 27)		UxBRG (UARTx Baud Rate)	
RPINR29 (Peripheral Pin Select Input 29)		UxBRGH (UARTx Baud Rate High)	
RPINR3 (Peripheral Pin Select Input 3)		UxINT (UARTx Interrupt)	
RPINR30 (Peripheral Pin Select Input 30)		UxMODE (UARTx Configuration)	
RPINR32 (Peripheral Pin Select Input 32)		UxMODEH (UARTx Configuration High)	
RPINR33 (Peripheral Pin Select Input 33)		UxP1 (UARTx Timing Parameter 1)	
RPINR37 (Peripheral Pin Select Input 37)		UxP2 (UARTx Timing Parameter 2)	
RPINR38 (Peripheral Pin Select Input 38)	162	UxP3 (UARTx Timing Parameter 3)	370
RPINR4 (Peripheral Pin Select Input 4)	148	UxP3H (UARTx Timing Parameter 3 High)	
RPINR42 (Peripheral Pin Select Input 42)	162	UxRXCHK (UARTx Receive Checksum)	372
RPINR43 (Peripheral Pin Select Input 43)	163	UxRXREG (UARTx Receive Buffer)	367
RPINR44 (Peripheral Pin Select Input 44)	163	UxSCCON (UARTx Smart Card Configuration)	373
RPINR45 (Peripheral Pin Select Input 45)	164	UxSCINT (UARTx Smart Card Interrupt)	374
RPINR46 (Peripheral Pin Select Input 46)	164	UxSTA (UARTx Status)	
RPINR47 (Peripheral Pin Select Input 47)	165	UxSTAH (UARTx Status High)	364
RPINR48 (Peripheral Pin Select Input 48)		UxTXCHK (UARTx Transmit Checksum)	
RPINR49 (Peripheral Pin Select Input 49)		UxTXREG (UARTx Transmit Buffer)	
RPINR5 (Peripheral Pin Select Input 5)		VELxCNT (Velocity x Counter)	
RPINR6 (Peripheral Pin Select Input 6)		VELxCNTH (Velocity x Counter High)	
RPINR7 (Peripheral Pin Select Input 7)		VELxHLD (Velocity x Counter Hold)	
RPINR8 (Peripheral Pin Select Input 8)		VREGCON (Voltage Regulator Control)	
· ((

WDTCONH (Watchdog Timer Control High)	
WDTCONL (Watchdog Timer Control Low)	529
Resets	95
Brown-out Reset (BOR)	
Configuration Mismatch Reset (CM)	95
Illegal Condition Reset (IOPUWR)	95
Illegal Opcode	95
Security	
Uninitialized W Register	
Master Clear (MCLR) Pin Reset	95
Power-on Reset (POR)	
RESET Instruction (SWR)	95
Resources	96
Trap Conflict Reset (TRAPR)	95
Watchdog Timer Time-out Reset (WDTO)	
Revision History	
S	
SENTx Protocol Data Frames	420
Serial Peripheral Interface (SPI)	377
Serial Peripheral Interface. See SPI.	
SFR Blocks	
000h	52
100h	53
200h	
300h	
400h	
500h	
600h	
800h	
900h	
A00h	
B00h	
C00h	
D00h	
E00h	
F00h	
Single-Edge Nibble Transmission (SENT)	
Control Registers	
Receive Mode	
Configuration	
Transmit Mode	
ConfigurationSingle-Edge Nibble Transmission for	421
	440
Automotive Applications	419
Single-Edge Nibble Transmission. See SENT.	
Software Simulator	
MPLAB X SIM	
Special Features of the CPU	507
SPI	
Control Posistors	303

Т	
Thermal Operating Conditions	548
Thermal Packaging Characteristics	
Third-Party Development Tools	546
Timer1	
Control Register	430
Timing Diagrams	
BOR and Master Clear Reset Characteristics Clock/Instruction Cycle	
External Clock	
High-Speed PWMx Fault Characteristics	
High-Speed PWMx Module Characteristics	
I/O Characteristics	
I2Cx Bus Data (Master Mode)	574
I2Cx Bus Data (Slave Mode)	
I2Cx Bus Start/Stop Bits (Master Mode)	
I2Cx Bus Start/Stop Bits (Slave Mode)	
QEI Interface Signals	335
SPIx Master Mode (Full-Duplex, CKE = 0,	
CKP = x, SMP = 1)	569
SPIx Master Mode (Full-Duplex, CKE = 1, CKP = x, SMP = 1)	568
SPIx Master Mode (Half-Duplex, Transmit Only,	300
CKE = 0)	566
SPIx Master Mode (Half-Duplex, Transmit Only,	
CKE = 1)	567
SPIx Slave Mode (Full-Duplex, CKE = 0,	
CKP = x, SMP = 0)	570
SPIx Slave Mode (Full-Duplex, CKE = 1,	
CKP = x, SMP = 0)	
UARTx I/O Characteristics	5/8
U	
UART	
Architectural Overview	356
Character Frame	357
Control Registers	358
Data Buffers	357
Protocol Extensions	
Unique Device Identifier (UDID)	. 45
Unique Device Identifier. See UDID.	
Universal Asynchronous Receiver	0==
Transmitter (UART)	
User OTP Memory	
	520
V	
Voltage Regulator (On-Chip)	526
W	
Watchdog Timer (WDT)	507
WWW Address	
WWW On-Line Support	15

THE MICROCHIP WEBSITE

Microchip provides online support via our WWW site at www.microchip.com. This website is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the website contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip website at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

CUSTOMER SUPPORT

Users of Microchip products can receive assistance through several channels:

- · Distributor or Representative
- · Local Sales Office
- Field Application Engineer (FAE)
- · Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.


Technical support is available through the website at: http://microchip.com/support

dsPIC33CK256MP508

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.



NOTES:			

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our
 knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data
 Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, AVR, AVR logo, AVR Freaks, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, Kleer, LANCheck, LINK MD, maXStylus, maXTouch, MediaLB, megaAVR, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, Prochip Designer, QTouch, SAM-BA, SpyNIC, SST, SST Logo, SuperFlash, tinyAVR, UNI/O, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries

ClockWorks, The Embedded Control Solutions Company, EtherSynch, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and Quiet-Wire are registered trademarks of Microchip Technology Incorporated in the U.S.A. Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM, net. PICkit, PICtail, PowerSmart, PureSilicon. QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2018, Microchip Technology Incorporated, All Rights Reserved. ISBN: 978-1-5224-3930-1



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CATel: 408-735-9110
Tel: 408-436-4270 **Canada - Toronto**

Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138

China - Zhuhai Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

Japan - Osaka Tel: 81-6-6152-7160

Japan - Tokyo Tel: 81-3-6880- 3770

Korea - Daegu

Tel: 82-53-744-4301 **Korea - Seoul** Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

Germany - Haan Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-67-3636

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820