




LOC		DIST		REV				REVISIONS			
				P		LYR		DESCRIPTION		DATE	OWN
											APVD
											STM
											BM
											STM
											STM

- 1 MATERIAL: SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - BERYLIUM COPPER, ALLOY UNS C17300 CONDITION TD04, PER ASTM B196.
INSULATORS - TEFLON (PTFE) ROD, PER ASTM D 1710.
MODULE BODY & OSMM CONNECTORS - STAINLESS STEEL, PER UNS S30300
SLOTTED SPRIN PIN - NICKEL STAINLESS STEEL
- 2 FINISH: MODULE BODY, CONNECTOR BODIES & CENTER CONTACT - GOLD PLATE OVER NICKEL
SLOTTED SPRING PIN - PASSIVATED
- 3 FINISH: MODULE BODY, OSMM CONNECTOR BODY & SLOTTED SPRING PIN - PASSIVATED
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - GOLD PLATE OVER NICKEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN RJM3	04FEB2011	 TE Connectivity
		CHK STM	04FEB2011	
		APVD STM	04FEB2011	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
INCHES				
		0 PLC ± 1 PLC ±.1 2 PLC ±.01 3 PLC ±.001 4 PLC ±.0005		
WATERL		FINISH		
		SEE TABLE		
		CUSTOMER DRAWING		

NAME		8 POSITION P.C.B. MOUNT RF MODULE, 8 OSM CONTACTS VITA 67 BACKPLANE - C'SINK MTG. HOLES	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A100779		C=1996777	
SCALE		8:1	SHEET 1 OF 1
REV		F	