


DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012



NOTE 1 LEAD CO-PLANARITY IS 0.1mm MAX.
2 CONTACTS ARE 3 STEPS SEQUENTIAL. (MF CONTACT A=>SIGNAL CONTACT=>MF CONTACT B)
WHEN USING THIS SEQUENTIAL STRUCTURE, PLEASE AVOID ANGLED INSERTION.
3 MF CONTACT A AND MF CONTACT B CAN BE USED AS POWER SUPPLY CONTACT. (3A/PIN MAX)
4 IT SHOWS CONNECTOR'S CENTRE OF GRAVITY AND VACUUM PICKUP AREA.
5 THIS IS PACKAGED IN TRAY. (40pcs/TRAY)
6 BLEMISH AND HIT MARK CAN BE OCCURED THROUGH OUT THE MANUFACTURING PROCESS WHICH DOESN' T AFFECT QUALITY LEVEL.
7 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCES.

3	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.1µm	6	POLYSTYRENE	CONTACT AREA:GOLD 0.1µm
		LEAD AREA:GOLD 0.03µm	5	PHOSPHOR BRONZE	LEAD AREA:TIN-PLATING 1µm
		UNDER PLATING:NICKEL 1.3µm			UNDER PLATING:NICKEL 1.3µm
2	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.1µm			CONTACT AREA:GOLD 0.1µm
		LEAD AREA:GOLD 0.03µm			LEAD AREA:TIN-PLATING 1µm
		UNDER PLATING:NICKEL 1.3µm	4	PHOSPHOR BRONZE	UNDER PLATING:NICKEL 1.3µm
1	POLYAMIDE	BLACK UL94V-0			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
		APPROVED : HS. OKAWA	11.09.29	DRAWING NO.	EDC3-159084-00
		CHECED : KI. HIROKAWA	11.09.29	PART NO.	FX18-100S-0.8SH
		DESIGNED : TH. SANO	11.09.29	CODE NO.	CL579-0012-9-00
		DRAWN : TH. SANO	11.09.29		

